

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332458-940

Luminaire Tested: **S123RDIW-S1000D1030U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332458-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1030U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7209.2 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48	42
2	90	83	77	72	83	77	72	67	65	61	58	54	52	49	44	43	41	36
3	82	73	66	61	76	68	62	57	58	53	50	49	45	42	40	38	36	32
4	76	65	58	52	69	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	58	50	45	64	54	47	42	47	41	37	39	35	32	33	30	27	24
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	24	22
7	59	48	40	34	55	44	37	33	38	33	29	33	28	25	27	24	22	19
8	55	43	36	31	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	52	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	1.9
10°-20°	435.5	6.0
20°-30°	684.2	9.5
30°-40°	713.8	9.9
40°-50°	610.9	8.5
50°-60°	465.6	6.5
60°-70°	298.4	4.1
70°-80°	143.6	2.0
80°-90°	41.4	0.6
90°-100°	43.8	0.6
100°-110°	208.9	2.9
110°-120°	501.7	7.0
120°-130°	638.9	8.9
130°-140°	682.7	9.5
140°-150°	638.4	8.9
150°-160°	514.9	7.1
160°-170°	332.3	4.6
170°-180°	114.5	1.6
0°-30°	1259.1	17.5
0°-40°	1973.0	27.4
0°-60°	3049.5	42.3
0°-90°	3532.9	49.0
90°-120°	754.5	10.5
90°-150°	2714.5	37.7
90°-180°	3676.0	51.0
0°-180°	7209.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	27	1	27	1	27	13
95°	34	55	34	55	34	28
105°	39	267	39	267	39	90
115°	527	501	527	501	527	487
125°	720	706	720	706	720	643
135°	888	879	888	879	888	684
145°	1024	1014	1024	1014	1024	639
155°	1115	1117	1115	1117	1115	514
165°	1175	1178	1175	1178	1175	332
175°	1201	1206	1201	1206	1201	114
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	10.3	11.1	10.1	10.4	10.4	10.8	10.6	10.4	11.2	10.6	10.6
90°	26.8	26.5	26.0	25.7	25.2	24.7	23.9	23.1	22.3	21.5	18.9
92.5°	29.7	29.5	29.2	29.0	28.8	28.0	26.8	25.5	24.2	22.9	21.0
95°	34.1	34.1	34.1	34.1	34.1	33.3	31.9	30.6	29.2	27.7	25.6
97.5°	36.9	36.7	36.5	36.3	36.1	35.2	33.6	32.0	30.4	28.8	43.2
100°	37.6	37.5	37.2	37.0	36.8	35.9	34.3	32.7	31.1	29.5	60.6
102.5°	38.3	38.0	37.6	37.3	36.9	39.1	44.1	49.0	54.0	58.9	92.8
105°	39.4	39.0	38.6	38.3	37.8	55.2	90.4	125.7	161.0	196.2	214.1
107.5°	123.8	150.3	176.9	203.4	230.0	256.2	282.0	307.8	333.7	359.5	356.7
110°	246.3	274.7	303.2	331.7	360.2	377.6	384.2	390.8	397.3	403.9	401.7



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.6	428.6	434.6	440.6	446.6	449.5	449.4	449.3	449.2	449.1	446.9
115°	526.6	525.8	525.0	524.2	523.4	522.1	520.0	518.1	516.1	514.1	512.3
117.5°	585.1	584.9	584.7	584.5	584.4	583.5	581.9	580.3	578.7	577.1	576.2
120°	625.2	625.2	625.2	625.2	625.2	624.4	622.8	621.2	619.6	618.0	617.4
122.5°	664.6	664.4	664.2	664.1	664.0	663.3	662.2	661.0	660.0	658.8	658.1
125°	720.1	719.7	719.3	718.9	718.5	718.1	717.7	717.3	716.9	716.5	715.7
127.5°	773.5	773.9	774.3	774.6	775.1	775.0	774.3	773.6	773.0	772.4	771.4
130°	807.9	808.2	808.7	809.0	809.5	809.2	808.4	807.7	806.9	806.1	805.3
132.5°	839.4	840.0	840.5	841.1	841.6	841.5	840.7	839.9	839.1	838.3	837.7
135°	887.6	888.1	888.8	889.4	889.9	889.9	889.4	888.8	888.1	887.6	886.8
137.5°	932.9	933.3	933.7	934.1	934.5	934.2	933.3	932.3	931.3	930.4	930.0
140°	960.1	960.6	960.9	961.4	961.7	961.5	960.7	959.9	959.1	958.3	957.7
142.5°	985.2	985.8	986.3	986.9	987.4	987.4	986.8	986.1	985.5	984.8	984.3
145°	1023.7	1023.7	1023.7	1023.7	1023.7	1023.5	1023.1	1022.7	1022.3	1021.9	1021.5
147.5°	1052.4	1053.3	1054.2	1055.2	1056.1	1056.3	1055.9	1055.5	1055.1	1054.7	1054.3
150°	1073.9	1074.5	1075.0	1075.7	1076.3	1076.4	1075.9	1075.6	1075.1	1074.8	1074.3
152.5°	1091.1	1092.0	1092.9	1093.8	1094.8	1094.8	1094.1	1093.4	1092.7	1092.0	1091.7
155°	1115.1	1116.2	1117.5	1118.7	1119.8	1120.0	1118.9	1117.9	1117.0	1116.0	1115.8
157.5°	1135.3	1136.8	1138.4	1140.0	1141.5	1141.7	1140.5	1139.3	1138.1	1136.9	1137.1
160°	1148.2	1149.6	1151.0	1152.4	1153.8	1153.9	1152.7	1151.5	1150.3	1149.1	1149.3
162.5°	1160.4	1161.6	1162.9	1164.1	1165.3	1165.3	1164.0	1162.5	1161.2	1159.8	1160.0
165°	1175.1	1176.4	1177.9	1179.3	1180.6	1180.5	1178.9	1177.3	1175.8	1174.2	1174.4
167.5°	1185.6	1187.2	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6	1185.6
170°	1192.1	1193.6	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1	1192.1
172.5°	1195.7	1197.4	1199.2	1201.0	1202.7	1202.7	1201.1	1199.6	1198.0	1196.4	1196.2
175°	1201.0	1202.7	1204.3	1205.9	1207.5	1207.6	1206.1	1204.7	1203.4	1201.9	1201.8
177.5°	1202.7	1204.3	1205.9	1207.5	1209.1	1209.2	1207.9	1206.7	1205.4	1204.1	1203.9
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	11.1	10.0	10.5	10.0	11.1	11.1	13.6	15.7	16.6	15.1	15.4
90°	16.3	13.7	11.1	8.8	6.9	4.9	2.9	0.9	2.9	4.9	6.9
92.5°	19.0	17.1	15.2	14.4	15.0	15.5	16.1	16.7	16.1	15.5	15.0
95°	23.4	21.2	19.0	22.0	30.1	38.3	46.5	54.7	46.5	38.3	30.1
97.5°	57.5	71.9	86.1	95.1	98.8	102.5	106.1	109.8	106.1	102.5	98.8
100°	91.7	122.7	153.7	167.3	163.3	159.3	155.3	151.3	155.3	159.3	163.3
102.5°	126.8	160.7	194.6	210.1	207.2	204.4	201.5	198.7	201.5	204.4	207.2
105°	231.9	249.9	267.8	275.6	273.5	271.3	269.1	266.9	269.1	271.3	273.5
107.5°	353.8	351.1	348.2	345.9	344.2	342.4	340.6	338.9	340.6	342.4	344.2
110°	399.6	397.3	395.2	393.2	391.7	390.1	388.5	386.9	388.5	390.1	391.7



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	444.7	442.5	440.3	438.5	437.1	435.6	434.2	432.7	434.2	435.6	437.1
115°	510.5	508.7	506.9	505.4	504.3	503.0	501.9	500.7	501.9	503.0	504.3
117.5°	575.3	574.4	573.5	572.3	570.8	569.4	567.8	566.4	567.8	569.4	570.8
120°	616.8	616.2	615.6	614.4	612.6	610.8	609.0	607.3	609.0	610.8	612.6
122.5°	657.3	656.6	655.8	654.7	653.2	651.8	650.2	648.8	650.2	651.8	653.2
125°	714.9	714.1	713.4	712.1	710.5	708.9	707.4	705.8	707.4	708.9	710.5
127.5°	770.5	769.5	768.6	767.3	765.7	764.1	762.5	760.9	762.5	764.1	765.7
130°	804.5	803.7	802.9	801.7	800.1	798.5	796.9	795.3	796.9	798.5	800.1
132.5°	837.0	836.4	835.8	834.6	833.0	831.4	829.9	828.3	829.9	831.4	833.0
135°	886.0	885.2	884.4	883.4	882.2	881.0	879.9	878.6	879.9	881.0	882.2
137.5°	929.5	929.1	928.6	927.6	926.1	924.6	923.1	921.6	923.1	924.6	926.1
140°	957.2	956.5	955.9	955.0	953.9	952.7	951.5	950.3	951.5	952.7	953.9
142.5°	983.6	983.0	982.5	981.6	980.3	979.2	977.9	976.8	977.9	979.2	980.3
145°	1021.1	1020.7	1020.3	1019.4	1018.1	1016.6	1015.2	1013.9	1015.2	1016.6	1018.1
147.5°	1053.9	1053.5	1053.1	1052.5	1051.5	1050.6	1049.7	1048.8	1049.7	1050.6	1051.5
150°	1074.0	1073.5	1073.2	1072.6	1072.1	1071.5	1070.9	1070.3	1070.9	1071.5	1072.1
152.5°	1091.5	1091.3	1091.0	1090.7	1090.5	1090.2	1089.9	1089.7	1089.9	1090.2	1090.5
155°	1115.5	1115.4	1115.2	1115.3	1115.7	1116.1	1116.4	1116.9	1116.4	1116.1	1115.7
157.5°	1137.3	1137.6	1137.7	1137.8	1137.9	1137.9	1138.0	1138.0	1138.0	1137.9	1137.9
160°	1149.5	1149.7	1149.9	1150.1	1150.3	1150.5	1150.7	1150.9	1150.7	1150.5	1150.3
162.5°	1160.3	1160.5	1160.7	1161.0	1161.5	1162.1	1162.5	1163.1	1162.5	1162.1	1161.5
165°	1174.6	1174.7	1175.0	1175.4	1176.0	1176.6	1177.1	1177.8	1177.1	1176.6	1176.0
167.5°	1185.6	1185.6	1185.6	1186.1	1186.9	1187.7	1188.5	1189.2	1188.5	1187.7	1186.9
170°	1192.1	1192.1	1192.1	1192.5	1193.3	1194.1	1194.9	1195.7	1194.9	1194.1	1193.3
172.5°	1196.1	1195.9	1195.8	1196.1	1197.1	1198.1	1199.0	1200.0	1199.0	1198.1	1197.1
175°	1201.6	1201.3	1201.1	1201.6	1202.6	1203.5	1204.5	1205.5	1204.5	1203.5	1202.6
177.5°	1203.8	1203.6	1203.5	1203.8	1204.6	1205.4	1206.1	1206.9	1206.1	1205.4	1204.6
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.3	17.3	18.3	19.3	20.3	20.3	21.0	21.1	21.8	21.9	22.0
90°	8.8	11.1	13.7	16.3	18.9	21.5	22.3	23.1	23.9	24.7	25.2
92.5°	14.4	15.2	17.1	19.0	21.0	22.9	24.2	25.5	26.8	28.0	28.8
95°	22.0	19.0	21.2	23.4	25.6	27.7	29.2	30.6	31.9	33.3	34.1
97.5°	95.1	86.1	71.9	57.5	43.2	28.8	30.4	32.0	33.6	35.2	36.1
100°	167.3	153.7	122.7	91.7	60.6	29.5	31.1	32.7	34.3	35.9	36.8
102.5°	210.1	194.6	160.7	126.8	92.8	58.9	54.0	49.0	44.1	39.1	36.9
105°	275.6	267.8	249.9	231.9	214.1	196.2	161.0	125.7	90.4	55.2	37.8
107.5°	345.9	348.2	351.1	353.8	356.7	359.5	333.7	307.8	282.0	256.2	230.0
110°	393.2	395.2	397.3	399.6	401.7	403.9	397.3	390.8	384.2	377.6	360.2



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	438.5	440.3	442.5	444.7	446.9	449.1	449.2	449.3	449.4	449.5	446.6
115°	505.4	506.9	508.7	510.5	512.3	514.1	516.1	518.1	520.0	522.1	523.4
117.5°	572.3	573.5	574.4	575.3	576.2	577.1	578.7	580.3	581.9	583.5	584.4
120°	614.4	615.6	616.2	616.8	617.4	618.0	619.6	621.2	622.8	624.4	625.2
122.5°	654.7	655.8	656.6	657.3	658.1	658.8	660.0	661.0	662.2	663.3	664.0
125°	712.1	713.4	714.1	714.9	715.7	716.5	716.9	717.3	717.7	718.1	718.5
127.5°	767.3	768.6	769.5	770.5	771.4	772.4	773.0	773.6	774.3	775.0	775.1
130°	801.7	802.9	803.7	804.5	805.3	806.1	806.9	807.7	808.4	809.2	809.5
132.5°	834.6	835.8	836.4	837.0	837.7	838.3	839.1	839.9	840.7	841.5	841.6
135°	883.4	884.4	885.2	886.0	886.8	887.6	888.1	888.8	889.4	889.9	889.9
137.5°	927.6	928.6	929.1	929.5	930.0	930.4	931.3	932.3	933.3	934.2	934.5
140°	955.0	955.9	956.5	957.2	957.7	958.3	959.1	959.9	960.7	961.5	961.7
142.5°	981.6	982.5	983.0	983.6	984.3	984.8	985.5	986.1	986.8	987.4	987.4
145°	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3	1022.7	1023.1	1023.5	1023.7
147.5°	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1	1055.5	1055.9	1056.3	1056.1
150°	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1	1075.6	1075.9	1076.4	1076.3
152.5°	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7	1093.4	1094.1	1094.8	1094.8
155°	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0	1117.9	1118.9	1120.0	1119.8
157.5°	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1	1139.3	1140.5	1141.7	1141.5
160°	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3	1151.5	1152.7	1153.9	1153.8
162.5°	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2	1162.5	1164.0	1165.3	1165.3
165°	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8	1177.3	1178.9	1180.5	1180.6
167.5°	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2	1188.8	1190.4	1192.0	1192.0
170°	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6	1195.2	1196.9	1198.5	1198.5
172.5°	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0	1199.6	1201.1	1202.7	1202.7
175°	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4	1204.7	1206.1	1207.6	1207.5
177.5°	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4	1206.7	1207.9	1209.2	1209.1
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	23.1	22.2	22.3	22.8	22.3	22.2	23.1	22.0	21.9	21.8	21.1
90°	25.7	26.0	26.5	26.8	26.5	26.0	25.7	25.2	24.7	23.9	23.1
92.5°	29.0	29.2	29.5	29.7	29.5	29.2	29.0	28.8	28.0	26.8	25.5
95°	34.1	34.1	34.1	34.1	34.1	34.1	34.1	34.1	33.3	31.9	30.6
97.5°	36.3	36.5	36.7	36.9	36.7	36.5	36.3	36.1	35.2	33.6	32.0
100°	37.0	37.2	37.5	37.6	37.5	37.2	37.0	36.8	35.9	34.3	32.7
102.5°	37.3	37.6	38.0	38.3	38.0	37.6	37.3	36.9	39.1	44.1	49.0
105°	38.3	38.6	39.0	39.4	39.0	38.6	38.3	37.8	55.2	90.4	125.7
107.5°	203.4	176.9	150.3	123.8	150.3	176.9	203.4	230.0	256.2	282.0	307.8
110°	331.7	303.2	274.7	246.3	274.7	303.2	331.7	360.2	377.6	384.2	390.8



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	440.6	434.6	428.6	422.6	428.6	434.6	440.6	446.6	449.5	449.4	449.3
115°	524.2	525.0	525.8	526.6	525.8	525.0	524.2	523.4	522.1	520.0	518.1
117.5°	584.5	584.7	584.9	585.1	584.9	584.7	584.5	584.4	583.5	581.9	580.3
120°	625.2	625.2	625.2	625.2	625.2	625.2	625.2	625.2	624.4	622.8	621.2
122.5°	664.1	664.2	664.4	664.6	664.4	664.2	664.1	664.0	663.3	662.2	661.0
125°	718.9	719.3	719.7	720.1	719.7	719.3	718.9	718.5	718.1	717.7	717.3
127.5°	774.6	774.3	773.9	773.5	773.9	774.3	774.6	775.1	775.0	774.3	773.6
130°	809.0	808.7	808.2	807.9	808.2	808.7	809.0	809.5	809.2	808.4	807.7
132.5°	841.1	840.5	840.0	839.4	840.0	840.5	841.1	841.6	841.5	840.7	839.9
135°	889.4	888.8	888.1	887.6	888.1	888.8	889.4	889.9	889.9	889.4	888.8
137.5°	934.1	933.7	933.3	932.9	933.3	933.7	934.1	934.5	934.2	933.3	932.3
140°	961.4	960.9	960.6	960.1	960.6	960.9	961.4	961.7	961.5	960.7	959.9
142.5°	986.9	986.3	985.8	985.2	985.8	986.3	986.9	987.4	987.4	986.8	986.1
145°	1023.7	1023.7	1023.7	1023.7	1023.7	1023.7	1023.7	1023.7	1023.5	1023.1	1022.7
147.5°	1055.2	1054.2	1053.3	1052.4	1053.3	1054.2	1055.2	1056.1	1056.3	1055.9	1055.5
150°	1075.7	1075.0	1074.5	1073.9	1074.5	1075.0	1075.7	1076.3	1076.4	1075.9	1075.6
152.5°	1093.8	1092.9	1092.0	1091.1	1092.0	1092.9	1093.8	1094.8	1094.8	1094.1	1093.4
155°	1118.7	1117.5	1116.2	1115.1	1116.2	1117.5	1118.7	1119.8	1120.0	1118.9	1117.9
157.5°	1140.0	1138.4	1136.8	1135.3	1136.8	1138.4	1140.0	1141.5	1141.7	1140.5	1139.3
160°	1152.4	1151.0	1149.6	1148.2	1149.6	1151.0	1152.4	1153.8	1153.9	1152.7	1151.5
162.5°	1164.1	1162.9	1161.6	1160.4	1161.6	1162.9	1164.1	1165.3	1165.3	1164.0	1162.5
165°	1179.3	1177.9	1176.4	1175.1	1176.4	1177.9	1179.3	1180.6	1180.5	1178.9	1177.3
167.5°	1190.4	1188.8	1187.2	1185.6	1187.2	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8
170°	1196.9	1195.2	1193.6	1192.1	1193.6	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2
172.5°	1201.0	1199.2	1197.4	1195.7	1197.4	1199.2	1201.0	1202.7	1202.7	1201.1	1199.6
175°	1205.9	1204.3	1202.7	1201.0	1202.7	1204.3	1205.9	1207.5	1207.6	1206.1	1204.7
177.5°	1207.5	1205.9	1204.3	1202.7	1204.3	1205.9	1207.5	1209.1	1209.2	1207.9	1206.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	21.0	20.3	20.3	19.3	18.3	17.3	15.3	15.4	15.1	16.6	15.7
90°	22.3	21.5	18.9	16.3	13.7	11.1	8.8	6.9	4.9	2.9	0.9
92.5°	24.2	22.9	21.0	19.0	17.1	15.2	14.4	15.0	15.5	16.1	16.7
95°	29.2	27.7	25.6	23.4	21.2	19.0	22.0	30.1	38.3	46.5	54.7
97.5°	30.4	28.8	43.2	57.5	71.9	86.1	95.1	98.8	102.5	106.1	109.8
100°	31.1	29.5	60.6	91.7	122.7	153.7	167.3	163.3	159.3	155.3	151.3
102.5°	54.0	58.9	92.8	126.8	160.7	194.6	210.1	207.2	204.4	201.5	198.7
105°	161.0	196.2	214.1	231.9	249.9	267.8	275.6	273.5	271.3	269.1	266.9
107.5°	333.7	359.5	356.7	353.8	351.1	348.2	345.9	344.2	342.4	340.6	338.9
110°	397.3	403.9	401.7	399.6	397.3	395.2	393.2	391.7	390.1	388.5	386.9



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	449.2	449.1	446.9	444.7	442.5	440.3	438.5	437.1	435.6	434.2	432.7
115°	516.1	514.1	512.3	510.5	508.7	506.9	505.4	504.3	503.0	501.9	500.7
117.5°	578.7	577.1	576.2	575.3	574.4	573.5	572.3	570.8	569.4	567.8	566.4
120°	619.6	618.0	617.4	616.8	616.2	615.6	614.4	612.6	610.8	609.0	607.3
122.5°	660.0	658.8	658.1	657.3	656.6	655.8	654.7	653.2	651.8	650.2	648.8
125°	716.9	716.5	715.7	714.9	714.1	713.4	712.1	710.5	708.9	707.4	705.8
127.5°	773.0	772.4	771.4	770.5	769.5	768.6	767.3	765.7	764.1	762.5	760.9
130°	806.9	806.1	805.3	804.5	803.7	802.9	801.7	800.1	798.5	796.9	795.3
132.5°	839.1	838.3	837.7	837.0	836.4	835.8	834.6	833.0	831.4	829.9	828.3
135°	888.1	887.6	886.8	886.0	885.2	884.4	883.4	882.2	881.0	879.9	878.6
137.5°	931.3	930.4	930.0	929.5	929.1	928.6	927.6	926.1	924.6	923.1	921.6
140°	959.1	958.3	957.7	957.2	956.5	955.9	955.0	953.9	952.7	951.5	950.3
142.5°	985.5	984.8	984.3	983.6	983.0	982.5	981.6	980.3	979.2	977.9	976.8
145°	1022.3	1021.9	1021.5	1021.1	1020.7	1020.3	1019.4	1018.1	1016.6	1015.2	1013.9
147.5°	1055.1	1054.7	1054.3	1053.9	1053.5	1053.1	1052.5	1051.5	1050.6	1049.7	1048.8
150°	1075.1	1074.8	1074.3	1074.0	1073.5	1073.2	1072.6	1072.1	1071.5	1070.9	1070.3
152.5°	1092.7	1092.0	1091.7	1091.5	1091.3	1091.0	1090.7	1090.5	1090.2	1089.9	1089.7
155°	1117.0	1116.0	1115.8	1115.5	1115.4	1115.2	1115.3	1115.7	1116.1	1116.4	1116.9
157.5°	1138.1	1136.9	1137.1	1137.3	1137.6	1137.7	1137.8	1137.9	1137.9	1138.0	1138.0
160°	1150.3	1149.1	1149.3	1149.5	1149.7	1149.9	1150.1	1150.3	1150.5	1150.7	1150.9
162.5°	1161.2	1159.8	1160.0	1160.3	1160.5	1160.7	1161.0	1161.5	1162.1	1162.5	1163.1
165°	1175.8	1174.2	1174.4	1174.6	1174.7	1175.0	1175.4	1176.0	1176.6	1177.1	1177.8
167.5°	1187.2	1185.6	1185.6	1185.6	1185.6	1185.6	1186.1	1186.9	1187.7	1188.5	1189.2
170°	1193.6	1192.1	1192.1	1192.1	1192.1	1192.1	1192.5	1193.3	1194.1	1194.9	1195.7
172.5°	1198.0	1196.4	1196.2	1196.1	1195.9	1195.8	1196.1	1197.1	1198.1	1199.0	1200.0
175°	1203.4	1201.9	1201.8	1201.6	1201.3	1201.1	1201.6	1202.6	1203.5	1204.5	1205.5
177.5°	1205.4	1204.1	1203.9	1203.8	1203.6	1203.5	1203.8	1204.6	1205.4	1206.1	1206.9
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.6	11.1	11.1	10.0	10.5	10.0	11.1	10.6	10.6	11.2	10.4
90°	2.9	4.9	6.9	8.8	11.1	13.7	16.3	18.9	21.5	22.3	23.1
92.5°	16.1	15.5	15.0	14.4	15.2	17.1	19.0	21.0	22.9	24.2	25.5
95°	46.5	38.3	30.1	22.0	19.0	21.2	23.4	25.6	27.7	29.2	30.6
97.5°	106.1	102.5	98.8	95.1	86.1	71.9	57.5	43.2	28.8	30.4	32.0
100°	155.3	159.3	163.3	167.3	153.7	122.7	91.7	60.6	29.5	31.1	32.7
102.5°	201.5	204.4	207.2	210.1	194.6	160.7	126.8	92.8	58.9	54.0	49.0
105°	269.1	271.3	273.5	275.6	267.8	249.9	231.9	214.1	196.2	161.0	125.7
107.5°	340.6	342.4	344.2	345.9	348.2	351.1	353.8	356.7	359.5	333.7	307.8
110°	388.5	390.1	391.7	393.2	395.2	397.3	399.6	401.7	403.9	397.3	390.8



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	434.2	435.6	437.1	438.5	440.3	442.5	444.7	446.9	449.1	449.2	449.3
115°	501.9	503.0	504.3	505.4	506.9	508.7	510.5	512.3	514.1	516.1	518.1
117.5°	567.8	569.4	570.8	572.3	573.5	574.4	575.3	576.2	577.1	578.7	580.3
120°	609.0	610.8	612.6	614.4	615.6	616.2	616.8	617.4	618.0	619.6	621.2
122.5°	650.2	651.8	653.2	654.7	655.8	656.6	657.3	658.1	658.8	660.0	661.0
125°	707.4	708.9	710.5	712.1	713.4	714.1	714.9	715.7	716.5	716.9	717.3
127.5°	762.5	764.1	765.7	767.3	768.6	769.5	770.5	771.4	772.4	773.0	773.6
130°	796.9	798.5	800.1	801.7	802.9	803.7	804.5	805.3	806.1	806.9	807.7
132.5°	829.9	831.4	833.0	834.6	835.8	836.4	837.0	837.7	838.3	839.1	839.9
135°	879.9	881.0	882.2	883.4	884.4	885.2	886.0	886.8	887.6	888.1	888.8
137.5°	923.1	924.6	926.1	927.6	928.6	929.1	929.5	930.0	930.4	931.3	932.3
140°	951.5	952.7	953.9	955.0	955.9	956.5	957.2	957.7	958.3	959.1	959.9
142.5°	977.9	979.2	980.3	981.6	982.5	983.0	983.6	984.3	984.8	985.5	986.1
145°	1015.2	1016.6	1018.1	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3	1022.7
147.5°	1049.7	1050.6	1051.5	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1	1055.5
150°	1070.9	1071.5	1072.1	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1	1075.6
152.5°	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7	1093.4
155°	1116.4	1116.1	1115.7	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0	1117.9
157.5°	1138.0	1137.9	1137.9	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1	1139.3
160°	1150.7	1150.5	1150.3	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3	1151.5
162.5°	1162.5	1162.1	1161.5	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2	1162.5
165°	1177.1	1176.6	1176.0	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8	1177.3
167.5°	1188.5	1187.7	1186.9	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2	1188.8
170°	1194.9	1194.1	1193.3	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6	1195.2
172.5°	1199.0	1198.1	1197.1	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0	1199.6
175°	1204.5	1203.5	1202.6	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4	1204.7
177.5°	1206.1	1205.4	1204.6	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4	1206.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	10.6	10.8	10.4	10.4	10.1	11.1	10.3
90°	23.9	24.7	25.2	25.7	26.0	26.5	26.8
92.5°	26.8	28.0	28.8	29.0	29.2	29.5	29.7
95°	31.9	33.3	34.1	34.1	34.1	34.1	34.1
97.5°	33.6	35.2	36.1	36.3	36.5	36.7	36.9
100°	34.3	35.9	36.8	37.0	37.2	37.5	37.6
102.5°	44.1	39.1	36.9	37.3	37.6	38.0	38.3
105°	90.4	55.2	37.8	38.3	38.6	39.0	39.4
107.5°	282.0	256.2	230.0	203.4	176.9	150.3	123.8
110°	384.2	377.6	360.2	331.7	303.2	274.7	246.3



TEST NUMBER: P332458-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	449.4	449.5	446.6	440.6	434.6	428.6	422.6
115°	520.0	522.1	523.4	524.2	525.0	525.8	526.6
117.5°	581.9	583.5	584.4	584.5	584.7	584.9	585.1
120°	622.8	624.4	625.2	625.2	625.2	625.2	625.2
122.5°	662.2	663.3	664.0	664.1	664.2	664.4	664.6
125°	717.7	718.1	718.5	718.9	719.3	719.7	720.1
127.5°	774.3	775.0	775.1	774.6	774.3	773.9	773.5
130°	808.4	809.2	809.5	809.0	808.7	808.2	807.9
132.5°	840.7	841.5	841.6	841.1	840.5	840.0	839.4
135°	889.4	889.9	889.9	889.4	888.8	888.1	887.6
137.5°	933.3	934.2	934.5	934.1	933.7	933.3	932.9
140°	960.7	961.5	961.7	961.4	960.9	960.6	960.1
142.5°	986.8	987.4	987.4	986.9	986.3	985.8	985.2
145°	1023.1	1023.5	1023.7	1023.7	1023.7	1023.7	1023.7
147.5°	1055.9	1056.3	1056.1	1055.2	1054.2	1053.3	1052.4
150°	1075.9	1076.4	1076.3	1075.7	1075.0	1074.5	1073.9
152.5°	1094.1	1094.8	1094.8	1093.8	1092.9	1092.0	1091.1
155°	1118.9	1120.0	1119.8	1118.7	1117.5	1116.2	1115.1
157.5°	1140.5	1141.7	1141.5	1140.0	1138.4	1136.8	1135.3
160°	1152.7	1153.9	1153.8	1152.4	1151.0	1149.6	1148.2
162.5°	1164.0	1165.3	1165.3	1164.1	1162.9	1161.6	1160.4
165°	1178.9	1180.5	1180.6	1179.3	1177.9	1176.4	1175.1
167.5°	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6
170°	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1
172.5°	1201.1	1202.7	1202.7	1201.0	1199.2	1197.4	1195.7
175°	1206.1	1207.6	1207.5	1205.9	1204.3	1202.7	1201.0
177.5°	1207.9	1209.2	1209.1	1207.5	1205.9	1204.3	1202.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5

(END OF REPORT)