

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333097-830

Luminaire Tested: **S124RDIW-S1195D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333097-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D470U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6309.7 lumens
Efficiency: N/A
Efficacy: 120.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	61
2	94	87	81	75	89	83	77	72	75	70	66	67	64	61	60	58	56	52
3	86	77	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	48	45	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	34
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	22
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15868	15868	15868
5°	15904	15709	15807
10°	15805	15521	15521
15°	15623	15195	15082
20°	15374	14766	14495
25°	15055	14264	13903
30°	14746	13736	13160
35°	14402	13186	12415
40°	13990	12562	11610
45°	13609	11942	10791
50°	13175	11228	9923
55°	12711	10486	8981
60°	12198	9671	8018
65°	11731	8653	7072
70°	11049	7532	6005
75°	10187	6245	4885
80°	8884	4761	4477
85°	7521	4326	4039



TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	2.9
10°-20°	514.9	8.2
20°-30°	743.5	11.8
30°-40°	842.8	13.4
40°-50°	813.8	12.9
50°-60°	676.7	10.7
60°-70°	467.3	7.4
70°-80°	236.9	3.8
80°-90°	62.4	1.0
90°-100°	19.5	0.3
100°-110°	124.6	2.0
110°-120°	238.3	3.8
120°-130°	302.4	4.8
130°-140°	323.6	5.1
140°-150°	302.6	4.8
150°-160°	244.0	3.9
160°-170°	157.4	2.5
170°-180°	54.2	0.9
0°-30°	1443.1	22.9
0°-40°	2285.8	36.2
0°-60°	3776.4	59.9
0°-90°	4543.0	72.0
90°-120°	382.4	6.1
90°-150°	1311.0	20.8
90°-180°	1767.0	28.0
0°-180°	6309.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1966	1966	1966	1966	1966	
5°	1963	1956	1938	1953	1951	186
15°	1869	1854	1818	1815	1805	526
25°	1690	1661	1601	1576	1561	778
35°	1461	1412	1338	1288	1260	913
45°	1192	1134	1046	975	945	919
55°	903	841	745	669	638	807
65°	614	548	453	391	370	606
75°	327	270	200	167	157	345
85°	81	53	47	44	44	91
90°	1	6	9	12	13	5
95°	24	10	9	12	12	30
105°	129	131	133	136	122	135
115°	240	241	241	242	242	236
125°	337	339	338	340	340	301
135°	419	418	420	421	422	322
145°	483	484	484	484	485	301
155°	529	530	528	530	529	244
165°	558	556	556	559	556	158
175°	571	569	569	572	568	54
180°	571	571	571	571	571	



TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1970.4	1969.3	1968.3	1967.2	1966.1	1964.2	1961.2	1958.2	1955.3	1952.4	1955.3
5°	1962.6	1961.2	1959.9	1958.6	1957.3	1954.6	1950.6	1946.5	1942.6	1938.5	1941.8
7.5°	1944.8	1943.4	1942.0	1940.6	1939.2	1935.9	1930.7	1925.5	1920.2	1915.1	1917.2
10°	1928.0	1926.3	1924.7	1923.0	1921.3	1917.4	1911.5	1905.4	1899.4	1893.4	1894.7
12.5°	1906.3	1904.4	1902.4	1900.4	1898.6	1894.0	1887.0	1879.9	1872.7	1865.7	1866.5
15°	1869.3	1866.2	1863.3	1860.3	1857.3	1851.5	1843.2	1834.8	1826.5	1818.1	1817.4
17.5°	1824.5	1820.0	1815.7	1811.4	1807.0	1799.9	1789.8	1779.8	1769.7	1759.7	1757.8
20°	1789.5	1785.2	1780.8	1776.5	1772.2	1764.3	1752.9	1741.5	1730.1	1718.8	1716.1
22.5°	1751.0	1746.2	1741.3	1736.4	1731.5	1723.0	1710.7	1698.6	1686.4	1674.2	1670.2
25°	1690.2	1684.1	1678.1	1672.2	1666.1	1656.2	1642.6	1628.8	1615.1	1601.4	1595.7
27.5°	1626.4	1618.8	1611.3	1603.7	1596.1	1585.1	1570.4	1555.8	1541.1	1526.4	1519.4
30°	1581.9	1573.5	1565.1	1556.7	1548.4	1536.3	1520.6	1504.9	1489.2	1473.5	1465.1
32.5°	1534.8	1525.4	1516.0	1506.6	1497.1	1484.3	1468.0	1451.8	1435.5	1419.3	1409.6
35°	1461.4	1450.7	1440.0	1429.3	1418.6	1404.9	1388.2	1371.5	1354.7	1338.0	1326.6
37.5°	1382.9	1371.8	1360.7	1349.7	1338.7	1323.9	1305.4	1286.9	1268.4	1249.8	1237.1
40°	1327.5	1316.4	1305.4	1294.4	1283.3	1268.3	1249.2	1230.1	1211.1	1192.0	1178.0
42.5°	1274.5	1262.9	1251.3	1239.7	1228.2	1212.5	1192.6	1172.7	1152.9	1133.0	1118.7
45°	1192.0	1179.6	1167.2	1154.9	1142.6	1126.2	1106.3	1086.2	1066.1	1046.0	1029.6
47.5°	1106.8	1094.0	1081.3	1068.5	1055.7	1038.9	1018.0	997.1	976.3	955.5	938.4
50°	1049.0	1035.9	1022.9	1009.9	996.8	979.6	958.2	936.8	915.4	894.0	877.3
52.5°	990.0	977.2	964.5	951.7	939.0	921.5	899.7	877.7	855.7	833.8	816.8
55°	903.1	889.7	876.3	862.9	849.5	832.0	810.2	788.5	766.8	745.0	727.6
57.5°	816.9	803.0	789.1	775.2	761.3	743.7	722.3	700.8	679.4	658.0	640.4
60°	755.5	742.2	728.8	715.4	702.0	684.7	663.3	641.9	620.4	599.0	581.6
62.5°	700.1	686.3	672.3	658.5	644.5	626.6	604.6	582.7	560.7	538.9	522.7
65°	614.1	599.6	585.3	570.9	556.6	538.7	517.3	495.9	474.5	453.0	438.7
67.5°	524.6	510.9	497.1	483.3	469.6	452.7	432.8	413.0	393.1	373.2	360.9
70°	468.1	454.0	440.0	425.9	411.9	395.3	376.3	357.2	338.2	319.1	308.0
72.5°	407.8	395.2	382.5	369.8	357.0	341.7	323.7	305.7	287.7	269.7	260.2
75°	326.6	314.2	301.8	289.5	277.1	263.1	247.3	231.6	215.9	200.2	192.5
77.5°	244.1	233.7	223.1	212.6	202.1	190.5	177.8	165.1	152.4	139.7	135.2
80°	191.1	181.4	171.7	162.0	152.3	142.5	132.4	122.4	112.4	102.4	101.3
82.5°	145.4	136.5	127.6	118.7	109.8	102.5	96.7	91.0	85.2	79.5	78.7
85°	81.2	74.6	67.9	61.2	54.5	50.7	49.7	48.6	47.7	46.7	46.0
87.5°	28.0	26.0	24.1	22.1	20.3	19.2	19.0	18.9	18.9	18.8	18.6
90°	1.3	2.4	3.4	4.4	5.5	6.3	7.2	7.9	8.7	9.4	10.0
92.5°	5.4	5.5	5.5	5.6	5.7	6.0	6.8	7.5	8.3	9.0	9.6
95°	23.5	20.3	17.1	13.9	10.6	9.0	9.1	9.2	9.3	9.4	10.0
97.5°	49.9	51.9	53.9	55.9	58.0	53.6	43.1	32.4	21.9	11.3	11.3
100°	70.0	71.7	73.5	75.2	76.9	71.2	58.1	45.0	31.9	18.8	17.2
102.5°	92.7	93.9	95.1	96.3	97.6	97.4	95.7	94.0	92.3	90.6	73.1
105°	128.6	129.1	129.7	130.3	130.8	131.4	131.9	132.3	132.8	133.3	134.1
107.5°	162.0	162.3	162.6	162.9	163.2	163.6	164.2	164.9	165.5	166.2	166.5
110°	184.5	184.8	185.1	185.4	185.7	186.1	186.6	187.3	187.8	188.4	188.6



TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	206.4	206.9	207.5	207.9	208.5	208.9	209.2	209.3	209.6	209.9	209.9
115°	240.1	240.3	240.6	240.9	241.2	241.3	241.2	241.1	241.0	240.9	241.1
117.5°	270.4	270.8	271.2	271.5	271.9	272.2	272.4	272.6	272.9	273.1	273.0
120°	290.9	291.2	291.6	292.0	292.4	292.6	292.5	292.4	292.3	292.2	292.4
122.5°	310.0	310.3	310.5	310.8	310.9	311.1	311.2	311.4	311.5	311.7	311.8
125°	337.4	337.8	338.2	338.6	338.9	339.0	338.8	338.7	338.5	338.3	338.6
127.5°	363.4	363.5	363.6	363.7	363.8	364.1	364.5	365.0	365.4	365.8	365.8
130°	380.1	380.2	380.4	380.5	380.6	380.8	381.1	381.4	381.6	381.9	382.0
132.5°	395.6	395.7	395.9	396.1	396.2	396.5	396.9	397.2	397.6	397.9	398.0
135°	418.6	418.5	418.4	418.3	418.2	418.4	418.8	419.1	419.5	419.9	420.1
137.5°	439.0	439.0	439.1	439.1	439.2	439.4	439.8	440.3	440.6	441.1	441.3
140°	452.3	452.5	452.7	452.9	453.1	453.3	453.5	453.7	453.9	454.1	454.4
142.5°	464.3	464.7	465.1	465.3	465.7	465.9	466.0	466.2	466.3	466.4	466.6
145°	482.7	483.0	483.2	483.5	483.8	484.0	484.0	484.0	484.0	484.0	484.1
147.5°	497.3	497.9	498.3	498.9	499.5	499.6	499.5	499.5	499.4	499.3	499.4
150°	507.9	508.3	508.7	509.1	509.4	509.5	509.4	509.3	509.3	509.2	509.2
152.5°	516.8	517.1	517.4	517.6	518.0	518.0	517.9	517.7	517.6	517.4	517.6
155°	529.2	529.3	529.4	529.5	529.6	529.5	529.2	529.0	528.7	528.4	528.8
157.5°	539.8	539.7	539.6	539.6	539.5	539.3	539.0	538.7	538.4	538.1	538.6
160°	545.9	545.6	545.4	545.1	544.8	544.6	544.5	544.4	544.3	544.2	544.8
162.5°	551.4	551.0	550.6	550.3	550.0	549.7	549.6	549.5	549.4	549.3	549.9
165°	558.3	557.8	557.3	556.9	556.4	556.2	556.2	556.2	556.2	556.2	556.9
167.5°	563.7	563.3	562.8	562.3	561.8	561.5	561.5	561.4	561.4	561.3	562.1
170°	566.8	566.3	565.7	565.1	564.6	564.3	564.4	564.5	564.6	564.7	565.4
172.5°	568.9	568.4	567.8	567.2	566.7	566.4	566.5	566.6	566.7	566.8	567.5
175°	571.1	570.5	570.0	569.4	568.8	568.6	568.7	568.8	568.9	569.0	569.9
177.5°	572.1	571.7	571.1	570.5	570.0	569.9	570.0	570.1	570.2	570.4	571.0
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1



TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6	1965.6
2.5°	1958.2	1961.2	1964.2	1965.5	1965.2	1964.9	1964.6	1964.4
5°	1945.2	1948.5	1951.9	1953.2	1952.6	1951.9	1951.3	1950.6
7.5°	1919.3	1921.5	1923.6	1924.1	1923.1	1922.0	1920.9	1919.9
10°	1896.0	1897.3	1898.8	1898.8	1897.3	1896.0	1894.7	1893.4
12.5°	1867.3	1868.1	1868.9	1868.3	1866.5	1864.6	1862.7	1860.9
15°	1816.8	1816.1	1815.4	1813.9	1811.6	1809.2	1806.9	1804.6
17.5°	1756.0	1754.1	1752.2	1749.5	1746.0	1742.4	1738.9	1735.3
20°	1713.4	1710.7	1708.1	1704.6	1700.3	1695.9	1691.5	1687.2
22.5°	1666.2	1662.2	1658.2	1654.4	1650.9	1647.3	1643.8	1640.2
25°	1590.0	1584.3	1578.7	1574.1	1570.7	1567.4	1564.1	1560.8
27.5°	1512.4	1505.3	1498.4	1492.4	1487.6	1482.8	1478.0	1473.2
30°	1456.7	1448.4	1440.0	1433.1	1427.8	1422.5	1417.1	1411.7
32.5°	1399.9	1390.2	1380.4	1373.1	1368.0	1362.9	1357.8	1352.7
35°	1315.2	1303.9	1292.5	1283.8	1277.8	1271.8	1265.7	1259.7
37.5°	1224.4	1211.6	1199.0	1189.6	1183.6	1177.5	1171.6	1165.5
40°	1163.9	1149.9	1135.9	1125.8	1119.7	1113.7	1107.8	1101.7
42.5°	1104.4	1090.1	1075.7	1065.5	1059.1	1052.9	1046.6	1040.3
45°	1013.2	996.8	980.4	969.2	963.3	957.2	951.2	945.2
47.5°	921.4	904.5	887.5	875.6	869.0	862.4	855.7	849.1
50°	860.5	843.9	827.1	815.6	809.3	802.9	796.5	790.1
52.5°	799.8	782.9	765.8	754.0	747.4	740.8	734.1	727.5
55°	710.2	692.9	675.4	663.5	657.2	650.8	644.5	638.1
57.5°	622.7	605.0	587.4	576.2	571.4	566.5	561.7	556.9
60°	564.2	546.9	529.4	518.1	512.7	507.4	502.0	496.6
62.5°	506.7	490.7	474.6	464.4	460.1	455.9	451.6	447.3
65°	424.2	409.9	395.5	386.3	382.3	378.2	374.3	370.2
67.5°	348.6	336.1	323.8	315.4	310.9	306.5	302.1	297.7
70°	297.0	286.0	274.9	267.8	264.4	261.1	257.7	254.4
72.5°	250.8	241.4	232.0	225.7	222.6	219.6	216.5	213.4
75°	184.8	177.1	169.4	164.6	162.6	160.5	158.5	156.6
77.5°	130.7	126.2	121.8	119.2	118.6	118.0	117.4	116.8
80°	100.4	99.3	98.3	97.6	97.4	97.0	96.7	96.3
82.5°	78.0	77.3	76.5	76.0	75.7	75.3	75.0	74.6
85°	45.3	44.7	44.0	43.6	43.6	43.6	43.6	43.6
87.5°	18.5	18.3	18.1	18.2	18.5	18.9	19.1	19.4
90°	10.6	11.1	11.7	12.1	12.3	12.4	12.6	12.8
92.5°	10.2	10.7	11.3	11.6	11.7	11.7	11.8	11.8
95°	10.6	11.1	11.7	12.0	12.1	12.2	12.3	12.3
97.5°	11.4	11.4	11.5	11.6	11.7	11.8	11.9	12.0
100°	15.6	13.9	12.3	11.6	11.7	11.8	11.9	12.0
102.5°	55.7	38.4	20.9	12.3	12.3	12.3	12.3	12.3
105°	135.0	135.8	136.7	135.4	132.0	128.6	125.2	121.8
107.5°	167.0	167.4	167.9	168.2	168.6	168.9	169.3	169.7
110°	188.8	189.0	189.2	189.4	189.6	189.9	190.2	190.5



TEST NUMBER: P333097-830

CATALOG NUMBER: S124RDIW-S1195D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	209.8	209.8	209.7	209.9	210.3	210.7	211.0	211.3
115°	241.3	241.5	241.7	241.8	241.8	241.8	241.8	241.8
117.5°	273.0	273.0	272.9	272.9	272.8	272.8	272.8	272.7
120°	292.6	292.8	292.9	292.9	292.8	292.6	292.4	292.2
122.5°	311.9	312.0	312.1	312.1	311.9	311.7	311.5	311.3
125°	338.8	339.1	339.4	339.6	339.7	339.8	339.9	340.0
127.5°	365.7	365.6	365.6	365.5	365.4	365.3	365.3	365.2
130°	382.1	382.2	382.3	382.3	382.3	382.3	382.3	382.3
132.5°	398.1	398.2	398.3	398.3	398.2	398.2	398.1	398.0
135°	420.3	420.5	420.7	420.8	421.0	421.2	421.4	421.6
137.5°	441.5	441.7	442.0	442.0	442.0	441.9	441.9	441.8
140°	454.7	455.0	455.2	455.4	455.5	455.6	455.7	455.8
142.5°	466.7	467.0	467.2	467.3	467.3	467.4	467.4	467.4
145°	484.2	484.3	484.4	484.5	484.7	484.8	485.0	485.2
147.5°	499.5	499.5	499.5	499.6	499.7	499.8	499.9	500.0
150°	509.2	509.2	509.2	509.3	509.3	509.4	509.5	509.6
152.5°	517.6	517.8	518.0	518.0	518.0	517.9	517.8	517.8
155°	529.1	529.5	529.9	530.0	529.7	529.4	529.1	528.9
157.5°	539.0	539.5	540.0	540.0	539.5	539.0	538.6	538.1
160°	545.4	545.9	546.5	546.5	545.9	545.4	544.8	544.2
162.5°	550.4	551.0	551.6	551.6	550.9	550.3	549.6	549.0
165°	557.7	558.5	559.2	559.1	558.3	557.4	556.6	555.7
167.5°	563.0	563.8	564.7	564.6	563.6	562.7	561.8	560.8
170°	566.2	566.9	567.8	567.7	566.7	565.7	564.8	563.8
172.5°	568.3	569.0	569.8	569.7	568.6	567.6	566.6	565.5
175°	570.7	571.6	572.4	572.2	571.1	570.0	568.8	567.7
177.5°	571.7	572.2	572.9	572.7	571.8	570.9	570.0	569.1
180°	571.1	571.1	571.1	571.1	571.1	571.1	571.1	571.1

(END OF REPORT)