

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332460-940

Luminaire Tested: **S123RDIW-S1000D1030U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332460-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1030U940-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7060.2 lumens  
Efficiency: N/A  
Efficacy: 115.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.5	2.0
10°-20°	391.0	5.5
20°-30°	563.0	8.0
30°-40°	634.1	9.0
40°-50°	606.7	8.6
50°-60°	496.8	7.0
60°-70°	335.2	4.7
70°-80°	168.6	2.4
80°-90°	48.0	0.7
90°-100°	43.8	0.6
100°-110°	208.9	3.0
110°-120°	501.7	7.1
120°-130°	638.9	9.0
130°-140°	682.7	9.7
140°-150°	638.4	9.0
150°-160°	514.9	7.3
160°-170°	332.3	4.7
170°-180°	114.5	1.6
0°-30°	1094.5	15.5
0°-40°	1728.6	24.5
0°-60°	2832.1	40.1
0°-90°	3384.0	47.9
90°-120°	754.5	10.7
90°-150°	2714.5	38.4
90°-180°	3676.0	52.1
0°-180°	7060.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	10	22	25	27	6
95°	55	20	28	34	34	68
105°	267	272	196	46	39	283
115°	501	506	514	523	527	494
125°	706	713	716	718	720	630
135°	879	884	888	890	888	676
145°	1014	1020	1022	1024	1024	634
155°	1117	1115	1116	1120	1115	514
165°	1178	1175	1174	1181	1175	333
175°	1206	1201	1202	1208	1201	115
180°	1206	1206	1206	1206	1206	



TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.5	19.5	17.6	15.6	14.9	15.3	15.9	16.4	16.9	16.9
90°	0.9	2.9	4.9	6.9	8.8	11.1	13.7	16.3	18.9	21.5	22.3
92.5°	16.7	16.1	15.5	15.0	14.4	15.2	17.1	19.0	21.0	22.9	24.2
95°	54.7	46.5	38.3	30.1	22.0	19.0	21.2	23.4	25.6	27.7	29.2
97.5°	109.8	106.1	102.5	98.8	95.1	86.1	71.9	57.5	43.2	28.8	30.4
100°	151.3	155.3	159.3	163.3	167.3	153.7	122.7	91.7	60.6	29.5	31.1
102.5°	198.7	201.5	204.4	207.2	210.1	194.6	160.7	126.8	92.8	58.9	54.0
105°	266.9	269.1	271.3	273.5	275.6	267.8	249.9	231.9	214.1	196.2	161.0
107.5°	338.9	340.6	342.4	344.2	345.9	348.2	351.1	353.8	356.7	359.5	333.7
110°	386.9	388.5	390.1	391.7	393.2	395.2	397.3	399.6	401.7	403.9	397.3



TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	432.7	434.2	435.6	437.1	438.5	440.3	442.5	444.7	446.9	449.1	449.2
115°	500.7	501.9	503.0	504.3	505.4	506.9	508.7	510.5	512.3	514.1	516.1
117.5°	566.4	567.8	569.4	570.8	572.3	573.5	574.4	575.3	576.2	577.1	578.7
120°	607.3	609.0	610.8	612.6	614.4	615.6	616.2	616.8	617.4	618.0	619.6
122.5°	648.8	650.2	651.8	653.2	654.7	655.8	656.6	657.3	658.1	658.8	660.0
125°	705.8	707.4	708.9	710.5	712.1	713.4	714.1	714.9	715.7	716.5	716.9
127.5°	760.9	762.5	764.1	765.7	767.3	768.6	769.5	770.5	771.4	772.4	773.0
130°	795.3	796.9	798.5	800.1	801.7	802.9	803.7	804.5	805.3	806.1	806.9
132.5°	828.3	829.9	831.4	833.0	834.6	835.8	836.4	837.0	837.7	838.3	839.1
135°	878.6	879.9	881.0	882.2	883.4	884.4	885.2	886.0	886.8	887.6	888.1
137.5°	921.6	923.1	924.6	926.1	927.6	928.6	929.1	929.5	930.0	930.4	931.3
140°	950.3	951.5	952.7	953.9	955.0	955.9	956.5	957.2	957.7	958.3	959.1
142.5°	976.8	977.9	979.2	980.3	981.6	982.5	983.0	983.6	984.3	984.8	985.5
145°	1013.9	1015.2	1016.6	1018.1	1019.4	1020.3	1020.7	1021.1	1021.5	1021.9	1022.3
147.5°	1048.8	1049.7	1050.6	1051.5	1052.5	1053.1	1053.5	1053.9	1054.3	1054.7	1055.1
150°	1070.3	1070.9	1071.5	1072.1	1072.6	1073.2	1073.5	1074.0	1074.3	1074.8	1075.1
152.5°	1089.7	1089.9	1090.2	1090.5	1090.7	1091.0	1091.3	1091.5	1091.7	1092.0	1092.7
155°	1116.9	1116.4	1116.1	1115.7	1115.3	1115.2	1115.4	1115.5	1115.8	1116.0	1117.0
157.5°	1138.0	1138.0	1137.9	1137.9	1137.8	1137.7	1137.6	1137.3	1137.1	1136.9	1138.1
160°	1150.9	1150.7	1150.5	1150.3	1150.1	1149.9	1149.7	1149.5	1149.3	1149.1	1150.3
162.5°	1163.1	1162.5	1162.1	1161.5	1161.0	1160.7	1160.5	1160.3	1160.0	1159.8	1161.2
165°	1177.8	1177.1	1176.6	1176.0	1175.4	1175.0	1174.7	1174.6	1174.4	1174.2	1175.8
167.5°	1189.2	1188.5	1187.7	1186.9	1186.1	1185.6	1185.6	1185.6	1185.6	1185.6	1187.2
170°	1195.7	1194.9	1194.1	1193.3	1192.5	1192.1	1192.1	1192.1	1192.1	1192.1	1193.6
172.5°	1200.0	1199.0	1198.1	1197.1	1196.1	1195.8	1195.9	1196.1	1196.2	1196.4	1198.0
175°	1205.5	1204.5	1203.5	1202.6	1201.6	1201.1	1201.3	1201.6	1201.8	1201.9	1203.4
177.5°	1206.9	1206.1	1205.4	1204.6	1203.8	1203.5	1203.6	1203.8	1203.9	1204.1	1205.4
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5



TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	16.8	16.8	16.7	16.6	16.5	16.3	16.2	16.1
90°	23.1	23.9	24.7	25.2	25.7	26.0	26.5	26.8
92.5°	25.5	26.8	28.0	28.8	29.0	29.2	29.5	29.7
95°	30.6	31.9	33.3	34.1	34.1	34.1	34.1	34.1
97.5°	32.0	33.6	35.2	36.1	36.3	36.5	36.7	36.9
100°	32.7	34.3	35.9	36.8	37.0	37.2	37.5	37.6
102.5°	49.0	44.1	39.1	36.9	37.3	37.6	38.0	38.3
105°	125.7	90.4	55.2	37.8	38.3	38.6	39.0	39.4
107.5°	307.8	282.0	256.2	230.0	203.4	176.9	150.3	123.8
110°	390.8	384.2	377.6	360.2	331.7	303.2	274.7	246.3





TEST NUMBER: P332460-940

CATALOG NUMBER: S123RDIW-S1000D1030U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	449.3	449.4	449.5	446.6	440.6	434.6	428.6	422.6
115°	518.1	520.0	522.1	523.4	524.2	525.0	525.8	526.6
117.5°	580.3	581.9	583.5	584.4	584.5	584.7	584.9	585.1
120°	621.2	622.8	624.4	625.2	625.2	625.2	625.2	625.2
122.5°	661.0	662.2	663.3	664.0	664.1	664.2	664.4	664.6
125°	717.3	717.7	718.1	718.5	718.9	719.3	719.7	720.1
127.5°	773.6	774.3	775.0	775.1	774.6	774.3	773.9	773.5
130°	807.7	808.4	809.2	809.5	809.0	808.7	808.2	807.9
132.5°	839.9	840.7	841.5	841.6	841.1	840.5	840.0	839.4
135°	888.8	889.4	889.9	889.9	889.4	888.8	888.1	887.6
137.5°	932.3	933.3	934.2	934.5	934.1	933.7	933.3	932.9
140°	959.9	960.7	961.5	961.7	961.4	960.9	960.6	960.1
142.5°	986.1	986.8	987.4	987.4	986.9	986.3	985.8	985.2
145°	1022.7	1023.1	1023.5	1023.7	1023.7	1023.7	1023.7	1023.7
147.5°	1055.5	1055.9	1056.3	1056.1	1055.2	1054.2	1053.3	1052.4
150°	1075.6	1075.9	1076.4	1076.3	1075.7	1075.0	1074.5	1073.9
152.5°	1093.4	1094.1	1094.8	1094.8	1093.8	1092.9	1092.0	1091.1
155°	1117.9	1118.9	1120.0	1119.8	1118.7	1117.5	1116.2	1115.1
157.5°	1139.3	1140.5	1141.7	1141.5	1140.0	1138.4	1136.8	1135.3
160°	1151.5	1152.7	1153.9	1153.8	1152.4	1151.0	1149.6	1148.2
162.5°	1162.5	1164.0	1165.3	1165.3	1164.1	1162.9	1161.6	1160.4
165°	1177.3	1178.9	1180.5	1180.6	1179.3	1177.9	1176.4	1175.1
167.5°	1188.8	1190.4	1192.0	1192.0	1190.4	1188.8	1187.2	1185.6
170°	1195.2	1196.9	1198.5	1198.5	1196.9	1195.2	1193.6	1192.1
172.5°	1199.6	1201.1	1202.7	1202.7	1201.0	1199.2	1197.4	1195.7
175°	1204.7	1206.1	1207.6	1207.5	1205.9	1204.3	1202.7	1201.0
177.5°	1206.7	1207.9	1209.2	1209.1	1207.5	1205.9	1204.3	1202.7
180°	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5	1205.5

(END OF REPORT)