

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332462-940

Luminaire Tested: **S123RDIW-S1000D1320U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332462-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1320U940-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8240.2 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43									43																			
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	45	44	43	37									37																			
2	88	81	76	71	81	75	70	66	62	59	56	51	48	46	40	38	37	32									32																			
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28									28																			
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24									24																			
5	68	57	49	44	62	53	46	41	44	39	35	37	33	30	29	27	25	21									21																			
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22	19									19																			
7	58	47	39	33	53	43	36	31	36	31	27	30	26	23	24	22	20	17									17																			
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18	15									15																			
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14									14																			
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13									13																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	1.7
10°-20°	435.5	5.3
20°-30°	684.2	8.3
30°-40°	713.8	8.7
40°-50°	610.9	7.4
50°-60°	465.6	5.7
60°-70°	298.4	3.6
70°-80°	143.6	1.7
80°-90°	42.3	0.5
90°-100°	56.1	0.7
100°-110°	267.4	3.2
110°-120°	642.3	7.8
120°-130°	818.0	9.9
130°-140°	874.0	10.6
140°-150°	817.3	9.9
150°-160°	659.2	8.0
160°-170°	425.5	5.2
170°-180°	146.6	1.8
0°-30°	1259.1	15.3
0°-40°	1973.0	23.9
0°-60°	3049.5	37.0
0°-90°	3533.8	42.9
90°-120°	965.9	11.7
90°-150°	3475.0	42.2
90°-180°	4706.0	57.1
0°-180°	8240.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	25
90°	34	1	34	1	34	16
95°	44	70	44	70	44	36
105°	50	342	50	342	50	115
115°	674	641	674	641	674	623
125°	922	904	922	904	922	823
135°	1136	1125	1136	1125	1136	876
145°	1310	1298	1310	1298	1310	818
155°	1428	1430	1428	1430	1428	658
165°	1504	1508	1504	1508	1504	425
175°	1538	1543	1538	1543	1538	146
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	11.8	12.6	11.5	11.9	11.8	12.1	11.9	11.8	12.5	11.8	11.7
90°	34.4	33.9	33.3	32.9	32.4	31.6	30.6	29.5	28.5	27.6	24.2
92.5°	38.1	37.7	37.5	37.2	36.8	35.8	34.2	32.6	30.9	29.3	26.8
95°	43.6	43.6	43.6	43.6	43.6	42.7	40.9	39.1	37.4	35.6	32.7
97.5°	47.3	47.0	46.7	46.5	46.2	45.0	43.1	41.0	39.0	36.9	35.3
100°	48.2	47.9	47.6	47.3	47.2	46.0	44.0	41.9	39.9	37.8	37.6
102.5°	49.0	48.6	48.2	47.7	47.3	50.2	56.4	62.8	69.1	75.4	118.9
105°	50.5	49.9	49.4	49.0	48.4	70.7	115.8	160.9	206.0	251.1	274.0
107.5°	158.5	192.4	226.4	260.5	294.4	328.0	361.1	394.1	427.1	460.2	456.6
110°	315.3	351.8	388.2	424.6	461.0	483.5	491.9	500.2	508.7	517.1	514.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	541.0	548.7	556.3	564.0	571.8	575.5	575.3	575.2	575.1	574.9	572.1
115°	674.2	673.2	672.2	671.1	670.1	668.3	665.8	663.3	660.7	658.2	655.9
117.5°	748.9	748.8	748.5	748.3	748.1	747.0	744.9	743.0	740.9	738.9	737.7
120°	800.3	800.3	800.3	800.3	800.3	799.3	797.3	795.2	793.2	791.1	790.4
122.5°	850.8	850.6	850.3	850.2	850.0	849.2	847.7	846.3	844.9	843.5	842.5
125°	921.9	921.3	920.9	920.3	919.8	919.3	918.8	918.3	917.7	917.3	916.2
127.5°	990.2	990.7	991.2	991.8	992.2	992.1	991.2	990.4	989.6	988.8	987.6
130°	1034.2	1034.7	1035.3	1035.7	1036.3	1036.0	1035.0	1033.9	1033.0	1031.9	1030.9
132.5°	1074.6	1075.3	1076.0	1076.7	1077.5	1077.3	1076.3	1075.2	1074.2	1073.2	1072.4
135°	1136.3	1137.0	1137.8	1138.5	1139.3	1139.3	1138.5	1137.8	1137.0	1136.3	1135.2
137.5°	1194.3	1194.8	1195.3	1195.8	1196.3	1196.0	1194.7	1193.6	1192.3	1191.1	1190.5
140°	1229.1	1229.7	1230.1	1230.7	1231.2	1230.9	1229.9	1228.9	1227.9	1226.8	1226.1
142.5°	1261.2	1261.9	1262.7	1263.4	1264.1	1264.1	1263.2	1262.4	1261.6	1260.8	1260.0
145°	1310.5	1310.5	1310.5	1310.5	1310.5	1310.3	1309.7	1309.3	1308.8	1308.2	1307.8
147.5°	1347.2	1348.4	1349.6	1350.8	1351.9	1352.3	1351.7	1351.2	1350.8	1350.2	1349.7
150°	1374.8	1375.6	1376.3	1377.1	1377.8	1378.0	1377.4	1376.9	1376.4	1375.9	1375.4
152.5°	1396.8	1397.9	1399.1	1400.3	1401.5	1401.6	1400.7	1399.7	1398.8	1397.9	1397.6
155°	1427.5	1429.1	1430.6	1432.1	1433.6	1433.8	1432.4	1431.2	1429.9	1428.6	1428.4
157.5°	1453.4	1455.4	1457.4	1459.4	1461.3	1461.6	1460.1	1458.6	1457.0	1455.5	1455.7
160°	1469.9	1471.7	1473.5	1475.2	1477.0	1477.2	1475.7	1474.1	1472.6	1471.1	1471.3
162.5°	1485.5	1487.1	1488.7	1490.2	1491.8	1491.7	1490.0	1488.3	1486.6	1484.8	1485.1
165°	1504.3	1506.1	1507.9	1509.7	1511.4	1511.4	1509.3	1507.3	1505.2	1503.2	1503.4
167.5°	1517.9	1519.9	1522.0	1523.9	1526.0	1526.0	1523.9	1522.0	1519.9	1517.9	1517.9
170°	1526.1	1528.1	1530.2	1532.2	1534.3	1534.3	1532.2	1530.2	1528.1	1526.1	1526.1
172.5°	1530.7	1532.9	1535.2	1537.4	1539.6	1539.8	1537.8	1535.7	1533.7	1531.6	1531.4
175°	1537.6	1539.6	1541.7	1543.7	1545.7	1545.9	1544.1	1542.3	1540.5	1538.7	1538.5
177.5°	1539.6	1541.7	1543.7	1545.8	1547.8	1548.0	1546.4	1544.7	1543.1	1541.5	1541.2
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	11.9	10.8	11.1	10.5	11.5	11.4	13.8	15.8	16.8	15.3	15.9
90°	20.9	17.6	14.3	11.3	8.8	6.2	3.7	1.2	3.7	6.2	8.8
92.5°	24.3	21.8	19.4	18.5	19.2	19.9	20.6	21.3	20.6	19.9	19.2
95°	30.0	27.1	24.3	28.2	38.6	49.0	59.5	69.9	59.5	49.0	38.6
97.5°	73.7	91.9	110.3	121.8	126.5	131.2	135.9	140.5	135.9	131.2	126.5
100°	117.3	157.1	196.8	214.2	209.0	203.9	198.9	193.8	198.9	203.9	209.0
102.5°	162.3	205.7	249.1	269.0	265.3	261.6	258.0	254.3	258.0	261.6	265.3
105°	296.9	319.9	342.9	352.8	350.1	347.3	344.5	341.7	344.5	347.3	350.1
107.5°	453.0	449.4	445.8	442.8	440.6	438.4	436.1	433.9	436.1	438.4	440.6
110°	511.5	508.7	505.9	503.5	501.4	499.4	497.4	495.3	497.4	499.4	501.4



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	569.3	566.5	563.7	561.3	559.5	557.7	555.9	554.0	555.9	557.7	559.5
115°	653.5	651.2	649.0	647.0	645.5	644.0	642.5	641.0	642.5	644.0	645.5
117.5°	736.6	735.3	734.1	732.6	730.8	728.9	727.0	725.1	727.0	728.9	730.8
120°	789.6	788.8	788.1	786.6	784.3	781.9	779.7	777.4	779.7	781.9	784.3
122.5°	841.5	840.5	839.5	838.1	836.2	834.4	832.5	830.6	832.5	834.4	836.2
125°	915.3	914.2	913.2	911.7	909.6	907.6	905.5	903.5	905.5	907.6	909.6
127.5°	986.4	985.2	983.9	982.3	980.3	978.2	976.2	974.1	976.2	978.2	980.3
130°	1029.9	1028.9	1027.9	1026.4	1024.3	1022.3	1020.2	1018.2	1020.2	1022.3	1024.3
132.5°	1071.6	1070.8	1070.0	1068.5	1066.5	1064.4	1062.4	1060.3	1062.4	1064.4	1066.5
135°	1134.3	1133.2	1132.2	1131.0	1129.4	1127.8	1126.3	1124.8	1126.3	1127.8	1129.4
137.5°	1190.0	1189.4	1188.8	1187.6	1185.6	1183.7	1181.8	1179.8	1181.8	1183.7	1185.6
140°	1225.3	1224.6	1223.8	1222.6	1221.1	1219.6	1218.1	1216.6	1218.1	1219.6	1221.1
142.5°	1259.3	1258.5	1257.8	1256.6	1255.1	1253.6	1252.0	1250.4	1252.0	1253.6	1255.1
145°	1307.2	1306.7	1306.2	1305.1	1303.3	1301.5	1299.8	1298.0	1299.8	1301.5	1303.3
147.5°	1349.2	1348.7	1348.2	1347.4	1346.1	1345.0	1343.8	1342.6	1343.8	1345.0	1346.1
150°	1374.8	1374.4	1373.9	1373.2	1372.4	1371.7	1370.9	1370.2	1370.9	1371.7	1372.4
152.5°	1397.3	1397.0	1396.7	1396.3	1396.0	1395.6	1395.3	1394.9	1395.3	1395.6	1396.0
155°	1428.2	1427.9	1427.6	1427.7	1428.3	1428.8	1429.3	1429.8	1429.3	1428.8	1428.3
157.5°	1456.0	1456.3	1456.5	1456.6	1456.7	1456.8	1456.8	1456.9	1456.8	1456.8	1456.7
160°	1471.6	1471.9	1472.1	1472.3	1472.6	1472.8	1473.1	1473.4	1473.1	1472.8	1472.6
162.5°	1485.3	1485.6	1485.9	1486.3	1486.9	1487.6	1488.3	1489.0	1488.3	1487.6	1486.9
165°	1503.7	1504.0	1504.2	1504.7	1505.5	1506.2	1507.0	1507.8	1507.0	1506.2	1505.5
167.5°	1517.9	1517.9	1517.9	1518.3	1519.4	1520.4	1521.4	1522.4	1521.4	1520.4	1519.4
170°	1526.1	1526.1	1526.1	1526.6	1527.7	1528.7	1529.6	1530.7	1529.6	1528.7	1527.7
172.5°	1531.2	1531.0	1530.8	1531.3	1532.5	1533.7	1535.0	1536.2	1535.0	1533.7	1532.5
175°	1538.2	1537.9	1537.7	1538.2	1539.4	1540.8	1542.0	1543.3	1542.0	1540.8	1539.4
177.5°	1541.1	1540.9	1540.7	1541.1	1542.1	1543.1	1544.1	1545.2	1544.1	1543.1	1542.1
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	15.9	17.9	19.1	20.2	21.3	21.5	22.2	22.4	23.1	23.3	23.5
90°	11.3	14.3	17.6	20.9	24.2	27.6	28.5	29.5	30.6	31.6	32.4
92.5°	18.5	19.4	21.8	24.3	26.8	29.3	30.9	32.6	34.2	35.8	36.8
95°	28.2	24.3	27.1	30.0	32.7	35.6	37.4	39.1	40.9	42.7	43.6
97.5°	121.8	110.3	91.9	73.7	55.3	36.9	39.0	41.0	43.1	45.0	46.2
100°	214.2	196.8	157.1	117.3	77.6	37.8	39.9	41.9	44.0	46.0	47.2
102.5°	269.0	249.1	205.7	162.3	118.9	75.4	69.1	62.8	56.4	50.2	47.3
105°	352.8	342.9	319.9	296.9	274.0	251.1	206.0	160.9	115.8	70.7	48.4
107.5°	442.8	445.8	449.4	453.0	456.6	460.2	427.1	394.1	361.1	328.0	294.4
110°	503.5	505.9	508.7	511.5	514.3	517.1	508.7	500.2	491.9	483.5	461.0



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	561.3	563.7	566.5	569.3	572.1	574.9	575.1	575.2	575.3	575.5	571.8
115°	647.0	649.0	651.2	653.5	655.9	658.2	660.7	663.3	665.8	668.3	670.1
117.5°	732.6	734.1	735.3	736.6	737.7	738.9	740.9	743.0	744.9	747.0	748.1
120°	786.6	788.1	788.8	789.6	790.4	791.1	793.2	795.2	797.3	799.3	800.3
122.5°	838.1	839.5	840.5	841.5	842.5	843.5	844.9	846.3	847.7	849.2	850.0
125°	911.7	913.2	914.2	915.3	916.2	917.3	917.7	918.3	918.8	919.3	919.8
127.5°	982.3	983.9	985.2	986.4	987.6	988.8	989.6	990.4	991.2	992.1	992.2
130°	1026.4	1027.9	1028.9	1029.9	1030.9	1031.9	1033.0	1033.9	1035.0	1036.0	1036.3
132.5°	1068.5	1070.0	1070.8	1071.6	1072.4	1073.2	1074.2	1075.2	1076.3	1077.3	1077.5
135°	1131.0	1132.2	1133.2	1134.3	1135.2	1136.3	1137.0	1137.8	1138.5	1139.3	1139.3
137.5°	1187.6	1188.8	1189.4	1190.0	1190.5	1191.1	1192.3	1193.6	1194.7	1196.0	1196.3
140°	1222.6	1223.8	1224.6	1225.3	1226.1	1226.8	1227.9	1228.9	1229.9	1230.9	1231.2
142.5°	1256.6	1257.8	1258.5	1259.3	1260.0	1260.8	1261.6	1262.4	1263.2	1264.1	1264.1
145°	1305.1	1306.2	1306.7	1307.2	1307.8	1308.2	1308.8	1309.3	1309.7	1310.3	1310.5
147.5°	1347.4	1348.2	1348.7	1349.2	1349.7	1350.2	1350.8	1351.2	1351.7	1352.3	1351.9
150°	1373.2	1373.9	1374.4	1374.8	1375.4	1375.9	1376.4	1376.9	1377.4	1378.0	1377.8
152.5°	1396.3	1396.7	1397.0	1397.3	1397.6	1397.9	1398.8	1399.7	1400.7	1401.6	1401.5
155°	1427.7	1427.6	1427.9	1428.2	1428.4	1428.6	1429.9	1431.2	1432.4	1433.8	1433.6
157.5°	1456.6	1456.5	1456.3	1456.0	1455.7	1455.5	1457.0	1458.6	1460.1	1461.6	1461.3
160°	1472.3	1472.1	1471.9	1471.6	1471.3	1471.1	1472.6	1474.1	1475.7	1477.2	1477.0
162.5°	1486.3	1485.9	1485.6	1485.3	1485.1	1484.8	1486.6	1488.3	1490.0	1491.7	1491.8
165°	1504.7	1504.2	1504.0	1503.7	1503.4	1503.2	1505.2	1507.3	1509.3	1511.4	1511.4
167.5°	1518.3	1517.9	1517.9	1517.9	1517.9	1517.9	1519.9	1522.0	1523.9	1526.0	1526.0
170°	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1	1530.2	1532.2	1534.3	1534.3
172.5°	1531.3	1530.8	1531.0	1531.2	1531.4	1531.6	1533.7	1535.7	1537.8	1539.8	1539.6
175°	1538.2	1537.7	1537.9	1538.2	1538.5	1538.7	1540.5	1542.3	1544.1	1545.9	1545.7
177.5°	1541.1	1540.7	1540.9	1541.1	1541.2	1541.5	1543.1	1544.7	1546.4	1548.0	1547.8
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	24.5	23.6	23.8	24.3	23.8	23.6	24.5	23.5	23.3	23.1	22.4
90°	32.9	33.3	33.9	34.4	33.9	33.3	32.9	32.4	31.6	30.6	29.5
92.5°	37.2	37.5	37.7	38.1	37.7	37.5	37.2	36.8	35.8	34.2	32.6
95°	43.6	43.6	43.6	43.6	43.6	43.6	43.6	43.6	42.7	40.9	39.1
97.5°	46.5	46.7	47.0	47.3	47.0	46.7	46.5	46.2	45.0	43.1	41.0
100°	47.3	47.6	47.9	48.2	47.9	47.6	47.3	47.2	46.0	44.0	41.9
102.5°	47.7	48.2	48.6	49.0	48.6	48.2	47.7	47.3	50.2	56.4	62.8
105°	49.0	49.4	49.9	50.5	49.9	49.4	49.0	48.4	70.7	115.8	160.9
107.5°	260.5	226.4	192.4	158.5	192.4	226.4	260.5	294.4	328.0	361.1	394.1
110°	424.6	388.2	351.8	315.3	351.8	388.2	424.6	461.0	483.5	491.9	500.2



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	564.0	556.3	548.7	541.0	548.7	556.3	564.0	571.8	575.5	575.3	575.2
115°	671.1	672.2	673.2	674.2	673.2	672.2	671.1	670.1	668.3	665.8	663.3
117.5°	748.3	748.5	748.8	748.9	748.8	748.5	748.3	748.1	747.0	744.9	743.0
120°	800.3	800.3	800.3	800.3	800.3	800.3	800.3	800.3	799.3	797.3	795.2
122.5°	850.2	850.3	850.6	850.8	850.6	850.3	850.2	850.0	849.2	847.7	846.3
125°	920.3	920.9	921.3	921.9	921.3	920.9	920.3	919.8	919.3	918.8	918.3
127.5°	991.8	991.2	990.7	990.2	990.7	991.2	991.8	992.2	992.1	991.2	990.4
130°	1035.7	1035.3	1034.7	1034.2	1034.7	1035.3	1035.7	1036.3	1036.0	1035.0	1033.9
132.5°	1076.7	1076.0	1075.3	1074.6	1075.3	1076.0	1076.7	1077.5	1077.3	1076.3	1075.2
135°	1138.5	1137.8	1137.0	1136.3	1137.0	1137.8	1138.5	1139.3	1139.3	1138.5	1137.8
137.5°	1195.8	1195.3	1194.8	1194.3	1194.8	1195.3	1195.8	1196.3	1196.0	1194.7	1193.6
140°	1230.7	1230.1	1229.7	1229.1	1229.7	1230.1	1230.7	1231.2	1230.9	1229.9	1228.9
142.5°	1263.4	1262.7	1261.9	1261.2	1261.9	1262.7	1263.4	1264.1	1264.1	1263.2	1262.4
145°	1310.5	1310.5	1310.5	1310.5	1310.5	1310.5	1310.5	1310.5	1310.3	1309.7	1309.3
147.5°	1350.8	1349.6	1348.4	1347.2	1348.4	1349.6	1350.8	1351.9	1352.3	1351.7	1351.2
150°	1377.1	1376.3	1375.6	1374.8	1375.6	1376.3	1377.1	1377.8	1378.0	1377.4	1376.9
152.5°	1400.3	1399.1	1397.9	1396.8	1397.9	1399.1	1400.3	1401.5	1401.6	1400.7	1399.7
155°	1432.1	1430.6	1429.1	1427.5	1429.1	1430.6	1432.1	1433.6	1433.8	1432.4	1431.2
157.5°	1459.4	1457.4	1455.4	1453.4	1455.4	1457.4	1459.4	1461.3	1461.6	1460.1	1458.6
160°	1475.2	1473.5	1471.7	1469.9	1471.7	1473.5	1475.2	1477.0	1477.2	1475.7	1474.1
162.5°	1490.2	1488.7	1487.1	1485.5	1487.1	1488.7	1490.2	1491.8	1491.7	1490.0	1488.3
165°	1509.7	1507.9	1506.1	1504.3	1506.1	1507.9	1509.7	1511.4	1511.4	1509.3	1507.3
167.5°	1523.9	1522.0	1519.9	1517.9	1519.9	1522.0	1523.9	1526.0	1526.0	1523.9	1522.0
170°	1532.2	1530.2	1528.1	1526.1	1528.1	1530.2	1532.2	1534.3	1534.3	1532.2	1530.2
172.5°	1537.4	1535.2	1532.9	1530.7	1532.9	1535.2	1537.4	1539.6	1539.8	1537.8	1535.7
175°	1543.7	1541.7	1539.6	1537.6	1539.6	1541.7	1543.7	1545.7	1545.9	1544.1	1542.3
177.5°	1545.8	1543.7	1541.7	1539.6	1541.7	1543.7	1545.8	1547.8	1548.0	1546.4	1544.7
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	22.2	21.5	21.3	20.2	19.1	17.9	15.9	15.9	15.3	16.8	15.8
90°	28.5	27.6	24.2	20.9	17.6	14.3	11.3	8.8	6.2	3.7	1.2
92.5°	30.9	29.3	26.8	24.3	21.8	19.4	18.5	19.2	19.9	20.6	21.3
95°	37.4	35.6	32.7	30.0	27.1	24.3	28.2	38.6	49.0	59.5	69.9
97.5°	39.0	36.9	55.3	73.7	91.9	110.3	121.8	126.5	131.2	135.9	140.5
100°	39.9	37.8	77.6	117.3	157.1	196.8	214.2	209.0	203.9	198.9	193.8
102.5°	69.1	75.4	118.9	162.3	205.7	249.1	269.0	265.3	261.6	258.0	254.3
105°	206.0	251.1	274.0	296.9	319.9	342.9	352.8	350.1	347.3	344.5	341.7
107.5°	427.1	460.2	456.6	453.0	449.4	445.8	442.8	440.6	438.4	436.1	433.9
110°	508.7	517.1	514.3	511.5	508.7	505.9	503.5	501.4	499.4	497.4	495.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	575.1	574.9	572.1	569.3	566.5	563.7	561.3	559.5	557.7	555.9	554.0
115°	660.7	658.2	655.9	653.5	651.2	649.0	647.0	645.5	644.0	642.5	641.0
117.5°	740.9	738.9	737.7	736.6	735.3	734.1	732.6	730.8	728.9	727.0	725.1
120°	793.2	791.1	790.4	789.6	788.8	788.1	786.6	784.3	781.9	779.7	777.4
122.5°	844.9	843.5	842.5	841.5	840.5	839.5	838.1	836.2	834.4	832.5	830.6
125°	917.7	917.3	916.2	915.3	914.2	913.2	911.7	909.6	907.6	905.5	903.5
127.5°	989.6	988.8	987.6	986.4	985.2	983.9	982.3	980.3	978.2	976.2	974.1
130°	1033.0	1031.9	1030.9	1029.9	1028.9	1027.9	1026.4	1024.3	1022.3	1020.2	1018.2
132.5°	1074.2	1073.2	1072.4	1071.6	1070.8	1070.0	1068.5	1066.5	1064.4	1062.4	1060.3
135°	1137.0	1136.3	1135.2	1134.3	1133.2	1132.2	1131.0	1129.4	1127.8	1126.3	1124.8
137.5°	1192.3	1191.1	1190.5	1190.0	1189.4	1188.8	1187.6	1185.6	1183.7	1181.8	1179.8
140°	1227.9	1226.8	1226.1	1225.3	1224.6	1223.8	1222.6	1221.1	1219.6	1218.1	1216.6
142.5°	1261.6	1260.8	1260.0	1259.3	1258.5	1257.8	1256.6	1255.1	1253.6	1252.0	1250.4
145°	1308.8	1308.2	1307.8	1307.2	1306.7	1306.2	1305.1	1303.3	1301.5	1299.8	1298.0
147.5°	1350.8	1350.2	1349.7	1349.2	1348.7	1348.2	1347.4	1346.1	1345.0	1343.8	1342.6
150°	1376.4	1375.9	1375.4	1374.8	1374.4	1373.9	1373.2	1372.4	1371.7	1370.9	1370.2
152.5°	1398.8	1397.9	1397.6	1397.3	1397.0	1396.7	1396.3	1396.0	1395.6	1395.3	1394.9
155°	1429.9	1428.6	1428.4	1428.2	1427.9	1427.6	1427.7	1428.3	1428.8	1429.3	1429.8
157.5°	1457.0	1455.5	1455.7	1456.0	1456.3	1456.5	1456.6	1456.7	1456.8	1456.8	1456.9
160°	1472.6	1471.1	1471.3	1471.6	1471.9	1472.1	1472.3	1472.6	1472.8	1473.1	1473.4
162.5°	1486.6	1484.8	1485.1	1485.3	1485.6	1485.9	1486.3	1486.9	1487.6	1488.3	1489.0
165°	1505.2	1503.2	1503.4	1503.7	1504.0	1504.2	1504.7	1505.5	1506.2	1507.0	1507.8
167.5°	1519.9	1517.9	1517.9	1517.9	1517.9	1517.9	1518.3	1519.4	1520.4	1521.4	1522.4
170°	1528.1	1526.1	1526.1	1526.1	1526.1	1526.1	1526.6	1527.7	1528.7	1529.6	1530.7
172.5°	1533.7	1531.6	1531.4	1531.2	1531.0	1530.8	1531.3	1532.5	1533.7	1535.0	1536.2
175°	1540.5	1538.7	1538.5	1538.2	1537.9	1537.7	1538.2	1539.4	1540.8	1542.0	1543.3
177.5°	1543.1	1541.5	1541.2	1541.1	1540.9	1540.7	1541.1	1542.1	1543.1	1544.1	1545.2
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.8	11.4	11.5	10.5	11.1	10.8	11.9	11.7	11.8	12.5	11.8
90°	3.7	6.2	8.8	11.3	14.3	17.6	20.9	24.2	27.6	28.5	29.5
92.5°	20.6	19.9	19.2	18.5	19.4	21.8	24.3	26.8	29.3	30.9	32.6
95°	59.5	49.0	38.6	28.2	24.3	27.1	30.0	32.7	35.6	37.4	39.1
97.5°	135.9	131.2	126.5	121.8	110.3	91.9	73.7	55.3	36.9	39.0	41.0
100°	198.9	203.9	209.0	214.2	196.8	157.1	117.3	77.6	37.8	39.9	41.9
102.5°	258.0	261.6	265.3	269.0	249.1	205.7	162.3	118.9	75.4	69.1	62.8
105°	344.5	347.3	350.1	352.8	342.9	319.9	296.9	274.0	251.1	206.0	160.9
107.5°	436.1	438.4	440.6	442.8	445.8	449.4	453.0	456.6	460.2	427.1	394.1
110°	497.4	499.4	501.4	503.5	505.9	508.7	511.5	514.3	517.1	508.7	500.2



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	555.9	557.7	559.5	561.3	563.7	566.5	569.3	572.1	574.9	575.1	575.2
115°	642.5	644.0	645.5	647.0	649.0	651.2	653.5	655.9	658.2	660.7	663.3
117.5°	727.0	728.9	730.8	732.6	734.1	735.3	736.6	737.7	738.9	740.9	743.0
120°	779.7	781.9	784.3	786.6	788.1	788.8	789.6	790.4	791.1	793.2	795.2
122.5°	832.5	834.4	836.2	838.1	839.5	840.5	841.5	842.5	843.5	844.9	846.3
125°	905.5	907.6	909.6	911.7	913.2	914.2	915.3	916.2	917.3	917.7	918.3
127.5°	976.2	978.2	980.3	982.3	983.9	985.2	986.4	987.6	988.8	989.6	990.4
130°	1020.2	1022.3	1024.3	1026.4	1027.9	1028.9	1029.9	1030.9	1031.9	1033.0	1033.9
132.5°	1062.4	1064.4	1066.5	1068.5	1070.0	1070.8	1071.6	1072.4	1073.2	1074.2	1075.2
135°	1126.3	1127.8	1129.4	1131.0	1132.2	1133.2	1134.3	1135.2	1136.3	1137.0	1137.8
137.5°	1181.8	1183.7	1185.6	1187.6	1188.8	1189.4	1190.0	1190.5	1191.1	1192.3	1193.6
140°	1218.1	1219.6	1221.1	1222.6	1223.8	1224.6	1225.3	1226.1	1226.8	1227.9	1228.9
142.5°	1252.0	1253.6	1255.1	1256.6	1257.8	1258.5	1259.3	1260.0	1260.8	1261.6	1262.4
145°	1299.8	1301.5	1303.3	1305.1	1306.2	1306.7	1307.2	1307.8	1308.2	1308.8	1309.3
147.5°	1343.8	1345.0	1346.1	1347.4	1348.2	1348.7	1349.2	1349.7	1350.2	1350.8	1351.2
150°	1370.9	1371.7	1372.4	1373.2	1373.9	1374.4	1374.8	1375.4	1375.9	1376.4	1376.9
152.5°	1395.3	1395.6	1396.0	1396.3	1396.7	1397.0	1397.3	1397.6	1397.9	1398.8	1399.7
155°	1429.3	1428.8	1428.3	1427.7	1427.6	1427.9	1428.2	1428.4	1428.6	1429.9	1431.2
157.5°	1456.8	1456.8	1456.7	1456.6	1456.5	1456.3	1456.0	1455.7	1455.5	1457.0	1458.6
160°	1473.1	1472.8	1472.6	1472.3	1472.1	1471.9	1471.6	1471.3	1471.1	1472.6	1474.1
162.5°	1488.3	1487.6	1486.9	1486.3	1485.9	1485.6	1485.3	1485.1	1484.8	1486.6	1488.3
165°	1507.0	1506.2	1505.5	1504.7	1504.2	1504.0	1503.7	1503.4	1503.2	1505.2	1507.3
167.5°	1521.4	1520.4	1519.4	1518.3	1517.9	1517.9	1517.9	1517.9	1517.9	1519.9	1522.0
170°	1529.6	1528.7	1527.7	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1	1530.2
172.5°	1535.0	1533.7	1532.5	1531.3	1530.8	1531.0	1531.2	1531.4	1531.6	1533.7	1535.7
175°	1542.0	1540.8	1539.4	1538.2	1537.7	1537.9	1538.2	1538.5	1538.7	1540.5	1542.3
177.5°	1544.1	1543.1	1542.1	1541.1	1540.7	1540.9	1541.1	1541.2	1541.5	1543.1	1544.7
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	11.9	12.1	11.8	11.9	11.5	12.6	11.8
90°	30.6	31.6	32.4	32.9	33.3	33.9	34.4
92.5°	34.2	35.8	36.8	37.2	37.5	37.7	38.1
95°	40.9	42.7	43.6	43.6	43.6	43.6	43.6
97.5°	43.1	45.0	46.2	46.5	46.7	47.0	47.3
100°	44.0	46.0	47.2	47.3	47.6	47.9	48.2
102.5°	56.4	50.2	47.3	47.7	48.2	48.6	49.0
105°	115.8	70.7	48.4	49.0	49.4	49.9	50.5
107.5°	361.1	328.0	294.4	260.5	226.4	192.4	158.5
110°	491.9	483.5	461.0	424.6	388.2	351.8	315.3



TEST NUMBER: P332462-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	575.3	575.5	571.8	564.0	556.3	548.7	541.0
115°	665.8	668.3	670.1	671.1	672.2	673.2	674.2
117.5°	744.9	747.0	748.1	748.3	748.5	748.8	748.9
120°	797.3	799.3	800.3	800.3	800.3	800.3	800.3
122.5°	847.7	849.2	850.0	850.2	850.3	850.6	850.8
125°	918.8	919.3	919.8	920.3	920.9	921.3	921.9
127.5°	991.2	992.1	992.2	991.8	991.2	990.7	990.2
130°	1035.0	1036.0	1036.3	1035.7	1035.3	1034.7	1034.2
132.5°	1076.3	1077.3	1077.5	1076.7	1076.0	1075.3	1074.6
135°	1138.5	1139.3	1139.3	1138.5	1137.8	1137.0	1136.3
137.5°	1194.7	1196.0	1196.3	1195.8	1195.3	1194.8	1194.3
140°	1229.9	1230.9	1231.2	1230.7	1230.1	1229.7	1229.1
142.5°	1263.2	1264.1	1264.1	1263.4	1262.7	1261.9	1261.2
145°	1309.7	1310.3	1310.5	1310.5	1310.5	1310.5	1310.5
147.5°	1351.7	1352.3	1351.9	1350.8	1349.6	1348.4	1347.2
150°	1377.4	1378.0	1377.8	1377.1	1376.3	1375.6	1374.8
152.5°	1400.7	1401.6	1401.5	1400.3	1399.1	1397.9	1396.8
155°	1432.4	1433.8	1433.6	1432.1	1430.6	1429.1	1427.5
157.5°	1460.1	1461.6	1461.3	1459.4	1457.4	1455.4	1453.4
160°	1475.7	1477.2	1477.0	1475.2	1473.5	1471.7	1469.9
162.5°	1490.0	1491.7	1491.8	1490.2	1488.7	1487.1	1485.5
165°	1509.3	1511.4	1511.4	1509.7	1507.9	1506.1	1504.3
167.5°	1523.9	1526.0	1526.0	1523.9	1522.0	1519.9	1517.9
170°	1532.2	1534.3	1534.3	1532.2	1530.2	1528.1	1526.1
172.5°	1537.8	1539.8	1539.6	1537.4	1535.2	1532.9	1530.7
175°	1544.1	1545.9	1545.7	1543.7	1541.7	1539.6	1537.6
177.5°	1546.4	1548.0	1547.8	1545.8	1543.7	1541.7	1539.6
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3

(END OF REPORT)