

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333025-830

Luminaire Tested: **S124RDIW-S350D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333025-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1050U830-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5299.3 lumens  
Efficiency: N/A  
Efficacy: 139.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4704	4704	4704
5°	4714	4657	4686
10°	4685	4601	4601
15°	4631	4504	4471
20°	4558	4376	4296
25°	4464	4228	4121
30°	4371	4072	3901
35°	4269	3909	3680
40°	4147	3724	3442
45°	4035	3540	3199
50°	3905	3328	2941
55°	3768	3108	2663
60°	3615	2868	2377
65°	3477	2565	2096
70°	3274	2231	1780
75°	3019	1853	1447
80°	2631	1409	1330
85°	2232	1288	1195



TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.7	1.0
10°-20°	152.6	2.9
20°-30°	220.4	4.2
30°-40°	249.8	4.7
40°-50°	241.2	4.6
50°-60°	200.6	3.8
60°-70°	138.5	2.6
70°-80°	70.2	1.3
80°-90°	21.7	0.4
90°-100°	43.7	0.8
100°-110°	278.4	5.3
110°-120°	532.6	10.1
120°-130°	676.2	12.8
130°-140°	723.4	13.7
140°-150°	676.5	12.8
150°-160°	545.5	10.3
160°-170°	351.9	6.6
170°-180°	121.3	2.3
0°-30°	427.8	8.1
0°-40°	677.6	12.8
0°-60°	1119.4	21.1
0°-90°	1349.9	25.5
90°-120°	854.7	16.1
90°-150°	2930.8	55.3
90°-180°	3949.0	74.5
0°-180°	5299.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	583	583	583	583	583	
5°	582	580	575	579	578	55
15°	554	550	539	538	535	156
25°	501	492	475	467	463	231
35°	433	418	397	382	373	271
45°	353	336	310	289	280	272
55°	268	249	221	198	189	239
65°	182	162	134	116	110	180
75°	97	80	59	50	46	102
85°	24	16	14	13	13	27
90°	3	13	21	27	29	4
95°	52	22	21	26	28	68
105°	288	293	298	304	272	301
115°	537	539	539	540	540	528
125°	754	758	756	759	760	673
135°	936	935	939	941	942	721
145°	1079	1082	1082	1083	1085	674
155°	1183	1184	1181	1185	1182	545
165°	1248	1244	1243	1250	1242	353
175°	1277	1271	1272	1280	1269	122
180°	1277	1277	1277	1277	1277	



TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	584.1	583.7	583.4	583.2	582.8	582.2	581.4	580.5	579.6	578.7	579.6
5°	581.7	581.4	581.0	580.6	580.1	579.4	578.2	577.0	575.8	574.7	575.6
7.5°	576.5	576.1	575.7	575.2	574.9	573.8	572.3	570.7	569.2	567.7	568.3
10°	571.5	571.0	570.5	570.0	569.5	568.4	566.6	564.8	563.0	561.3	561.7
12.5°	565.1	564.5	563.9	563.4	562.8	561.5	559.3	557.2	555.2	553.0	553.3
15°	554.1	553.2	552.3	551.4	550.5	548.8	546.4	543.8	541.4	538.9	538.8
17.5°	540.8	539.5	538.2	537.0	535.6	533.5	530.6	527.5	524.6	521.6	521.0
20°	530.5	529.1	527.9	526.6	525.3	523.0	519.6	516.2	512.8	509.4	508.7
22.5°	519.1	517.6	516.1	514.7	513.2	510.7	507.1	503.5	499.9	496.2	495.1
25°	501.1	499.3	497.5	495.7	493.9	491.0	486.9	482.9	478.7	474.7	473.0
27.5°	482.1	479.8	477.6	475.4	473.2	469.9	465.5	461.2	456.9	452.5	450.3
30°	468.9	466.4	463.9	461.5	459.0	455.4	450.7	446.1	441.4	436.8	434.3
32.5°	455.0	452.1	449.4	446.6	443.7	440.0	435.2	430.4	425.6	420.8	417.8
35°	433.2	430.0	426.9	423.7	420.5	416.4	411.5	406.5	401.6	396.6	393.2
37.5°	409.9	406.6	403.4	400.1	396.8	392.5	386.9	381.4	376.0	370.5	366.7
40°	393.5	390.2	386.9	383.7	380.4	376.0	370.3	364.7	359.0	353.4	349.2
42.5°	377.8	374.4	370.9	367.5	364.1	359.4	353.5	347.6	341.8	335.8	331.6
45°	353.4	349.7	346.0	342.3	338.7	333.8	327.9	322.0	316.0	310.1	305.2
47.5°	328.1	324.3	320.6	316.7	312.9	307.9	301.8	295.6	289.4	283.2	278.1
50°	310.9	307.1	303.2	299.4	295.5	290.4	284.1	277.7	271.4	265.0	260.0
52.5°	293.5	289.6	285.9	282.1	278.3	273.1	266.6	260.1	253.6	247.1	242.1
55°	267.7	263.7	259.8	255.8	251.8	246.6	240.2	233.8	227.2	220.8	215.7
57.5°	242.1	238.0	233.9	229.8	225.6	220.5	214.1	207.7	201.4	195.0	189.8
60°	223.9	220.0	216.0	212.1	208.1	202.9	196.6	190.2	183.9	177.6	172.4
62.5°	207.5	203.4	199.3	195.2	191.1	185.8	179.3	172.8	166.3	159.8	155.0
65°	182.0	177.8	173.5	169.3	164.9	159.7	153.4	146.9	140.6	134.3	130.1
67.5°	155.5	151.5	147.3	143.3	139.2	134.2	128.3	122.4	116.5	110.7	107.0
70°	138.7	134.6	130.4	126.3	122.1	117.2	111.5	105.8	100.2	94.5	91.3
72.5°	120.9	117.2	113.4	109.6	105.8	101.3	96.0	90.6	85.3	79.9	77.2
75°	96.8	93.1	89.4	85.8	82.1	77.9	73.3	68.6	64.0	59.4	57.0
77.5°	72.4	69.3	66.2	63.1	59.9	56.5	52.7	48.9	45.1	41.4	40.1
80°	56.6	53.8	50.9	48.1	45.1	42.2	39.3	36.3	33.3	30.3	30.1
82.5°	43.1	40.4	37.8	35.2	32.5	30.3	28.7	27.0	25.3	23.6	23.4
85°	24.1	22.1	20.2	18.1	16.1	15.0	14.7	14.4	14.1	13.9	13.7
87.5°	8.8	8.6	8.5	8.3	8.1	8.2	8.4	8.7	9.0	9.2	9.3
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	12.1	12.2	12.3	12.4	12.5	13.5	15.2	16.9	18.6	20.3	21.5
95°	52.5	45.3	38.1	30.9	23.7	20.2	20.4	20.5	20.8	21.0	22.2
97.5°	111.5	116.0	120.6	125.1	129.5	120.0	96.2	72.6	48.9	25.2	25.4
100°	156.7	160.4	164.3	168.1	171.9	159.2	129.9	100.6	71.4	42.0	38.5
102.5°	207.1	209.8	212.6	215.5	218.2	217.7	214.0	210.1	206.2	202.5	163.5
105°	287.5	288.7	290.0	291.2	292.6	293.7	294.7	295.9	296.9	297.9	299.8
107.5°	362.1	362.8	363.4	364.0	364.7	365.7	367.1	368.6	370.0	371.5	372.4
110°	412.6	413.2	413.8	414.4	415.1	416.0	417.4	418.6	419.9	421.1	421.6



TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.5	462.6	463.7	464.9	466.0	466.9	467.5	468.1	468.6	469.3	469.2
115°	536.7	537.3	538.0	538.6	539.2	539.4	539.2	539.0	538.9	538.6	539.0
117.5°	604.5	605.3	606.1	607.0	607.8	608.5	609.0	609.4	609.9	610.4	610.3
120°	650.4	651.2	652.1	652.9	653.7	654.0	653.8	653.7	653.4	653.2	653.7
122.5°	693.1	693.6	694.1	694.7	695.1	695.6	695.9	696.2	696.4	696.7	697.0
125°	754.4	755.3	756.1	757.0	757.8	758.0	757.6	757.1	756.8	756.3	757.0
127.5°	812.5	812.7	812.9	813.1	813.3	813.9	814.9	815.9	816.8	817.8	817.7
130°	849.9	850.2	850.4	850.6	850.7	851.2	851.9	852.4	853.1	853.8	853.9
132.5°	884.3	884.7	885.0	885.4	885.8	886.5	887.2	888.1	888.8	889.7	889.9
135°	935.9	935.7	935.5	935.2	935.0	935.4	936.2	937.1	937.9	938.8	939.1
137.5°	981.5	981.6	981.7	981.8	981.8	982.3	983.3	984.2	985.1	986.1	986.6
140°	1011.3	1011.7	1012.2	1012.6	1013.0	1013.4	1013.9	1014.3	1014.7	1015.1	1015.8
142.5°	1038.0	1038.8	1039.5	1040.4	1041.1	1041.6	1041.9	1042.1	1042.4	1042.6	1043.1
145°	1079.1	1079.8	1080.3	1081.0	1081.7	1081.9	1081.9	1081.9	1081.9	1081.9	1082.2
147.5°	1111.7	1113.0	1114.2	1115.3	1116.5	1117.0	1116.8	1116.6	1116.3	1116.2	1116.3
150°	1135.5	1136.3	1137.2	1138.0	1138.9	1139.2	1139.0	1138.8	1138.5	1138.3	1138.3
152.5°	1155.3	1156.0	1156.7	1157.3	1158.0	1158.2	1157.8	1157.4	1157.1	1156.7	1157.0
155°	1183.2	1183.5	1183.6	1183.8	1184.0	1183.8	1183.2	1182.6	1181.9	1181.3	1182.1
157.5°	1206.7	1206.5	1206.5	1206.3	1206.2	1205.8	1205.0	1204.3	1203.6	1202.9	1204.0
160°	1220.4	1219.8	1219.2	1218.5	1217.9	1217.5	1217.3	1217.0	1216.8	1216.6	1217.9
162.5°	1232.7	1231.9	1231.1	1230.2	1229.5	1228.9	1228.7	1228.5	1228.3	1228.0	1229.4
165°	1248.1	1247.1	1246.0	1244.9	1243.9	1243.4	1243.4	1243.4	1243.4	1243.4	1245.1
167.5°	1260.4	1259.2	1258.2	1257.1	1255.9	1255.4	1255.2	1255.1	1255.0	1254.8	1256.7
170°	1267.2	1265.9	1264.7	1263.4	1262.2	1261.6	1261.8	1262.1	1262.3	1262.4	1264.1
172.5°	1271.8	1270.5	1269.2	1268.0	1266.7	1266.2	1266.4	1266.6	1266.9	1267.1	1268.8
175°	1276.8	1275.5	1274.2	1273.0	1271.7	1271.2	1271.4	1271.6	1271.8	1272.1	1273.9
177.5°	1279.0	1277.9	1276.7	1275.5	1274.3	1273.9	1274.2	1274.6	1274.9	1275.3	1276.6
180°	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8



TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	582.7	582.7	582.7	582.7	582.7	582.7	582.7	582.7
2.5°	580.5	581.4	582.2	582.6	582.5	582.5	582.4	582.3
5°	576.6	577.6	578.6	579.0	578.8	578.6	578.3	578.2
7.5°	568.9	569.6	570.2	570.3	570.0	569.8	569.4	569.1
10°	562.0	562.4	562.8	562.8	562.4	562.0	561.7	561.3
12.5°	553.5	553.7	554.0	553.8	553.3	552.7	552.1	551.6
15°	538.6	538.4	538.1	537.7	537.0	536.3	535.6	534.9
17.5°	520.5	520.0	519.4	518.6	517.6	516.5	515.5	514.4
20°	507.9	507.1	506.3	505.3	504.0	502.7	501.4	500.1
22.5°	493.9	492.7	491.5	490.4	489.4	488.3	487.3	486.2
25°	471.3	469.7	468.0	466.7	465.6	464.6	463.6	462.6
27.5°	448.3	446.2	444.1	442.4	440.9	439.5	438.1	436.7
30°	431.8	429.3	426.9	424.8	423.2	421.7	420.1	418.5
32.5°	415.0	412.1	409.3	407.0	405.5	404.0	402.5	401.0
35°	389.8	386.5	383.1	380.6	378.8	377.0	375.2	373.4
37.5°	363.0	359.2	355.4	352.6	350.8	349.0	347.2	345.4
40°	345.0	340.8	336.7	333.8	332.0	330.2	328.4	326.6
42.5°	327.3	323.1	318.9	315.8	314.0	312.1	310.2	308.4
45°	300.4	295.5	290.6	287.3	285.5	283.7	281.9	280.2
47.5°	273.1	268.1	263.1	259.6	257.6	255.6	253.6	251.8
50°	255.1	250.2	245.2	241.8	239.9	238.0	236.1	234.2
52.5°	237.0	232.1	227.1	223.5	221.6	219.6	217.6	215.7
55°	210.6	205.4	200.2	196.7	194.8	192.9	191.1	189.2
57.5°	184.5	179.4	174.1	170.8	169.4	168.0	166.5	165.0
60°	167.2	162.1	156.9	153.5	151.9	150.4	148.8	147.2
62.5°	150.2	145.4	140.7	137.7	136.4	135.2	133.8	132.6
65°	125.7	121.5	117.3	114.5	113.3	112.2	110.9	109.7
67.5°	103.3	99.6	96.0	93.5	92.2	90.9	89.5	88.2
70°	88.0	84.7	81.5	79.4	78.3	77.4	76.3	75.4
72.5°	74.4	71.5	68.8	66.9	66.0	65.1	64.2	63.2
75°	54.8	52.5	50.2	48.8	48.2	47.6	47.0	46.4
77.5°	38.7	37.4	36.1	35.3	35.2	35.0	34.8	34.6
80°	29.8	29.4	29.1	28.9	28.8	28.7	28.7	28.6
82.5°	23.1	22.9	22.7	22.5	22.4	22.3	22.2	22.1
85°	13.5	13.2	13.0	12.9	12.9	12.9	12.9	12.9
87.5°	9.5	9.7	9.9	10.1	10.3	10.4	10.6	10.7
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	22.8	24.0	25.4	26.0	26.1	26.2	26.3	26.4
95°	23.6	24.8	26.1	26.9	27.1	27.2	27.5	27.7
97.5°	25.4	25.6	25.7	25.9	26.1	26.3	26.5	26.8
100°	34.8	31.2	27.6	25.9	26.1	26.3	26.5	26.8
102.5°	124.6	85.7	46.8	27.3	27.3	27.4	27.4	27.5
105°	301.8	303.7	305.6	302.7	295.1	287.5	279.8	272.2
107.5°	373.3	374.3	375.2	376.1	376.9	377.7	378.5	379.3
110°	422.0	422.4	422.8	423.4	424.0	424.6	425.3	425.9





TEST NUMBER: P333025-830

CATALOG NUMBER: S124RDIW-S350D1050U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	469.1	469.0	468.9	469.3	470.1	470.9	471.7	472.5
115°	539.4	539.9	540.3	540.5	540.5	540.5	540.5	540.5
117.5°	610.2	610.2	610.1	610.0	609.9	609.8	609.7	609.6
120°	654.0	654.5	654.9	654.9	654.5	654.0	653.7	653.2
122.5°	697.3	697.5	697.8	697.7	697.3	696.8	696.4	696.0
125°	757.6	758.3	758.8	759.3	759.5	759.7	760.0	760.2
127.5°	817.6	817.5	817.3	817.2	817.0	816.8	816.6	816.5
130°	854.1	854.4	854.6	854.7	854.7	854.7	854.7	854.7
132.5°	890.0	890.3	890.5	890.5	890.3	890.1	890.0	889.9
135°	939.6	940.0	940.5	940.8	941.3	941.7	942.2	942.5
137.5°	987.0	987.5	988.0	988.2	988.0	987.9	987.8	987.6
140°	1016.4	1017.0	1017.7	1018.1	1018.3	1018.5	1018.7	1019.0
142.5°	1043.6	1044.1	1044.5	1044.7	1044.8	1044.8	1044.9	1044.9
145°	1082.4	1082.6	1082.8	1083.2	1083.5	1084.0	1084.4	1084.9
147.5°	1116.5	1116.6	1116.8	1117.0	1117.3	1117.5	1117.7	1117.9
150°	1138.3	1138.3	1138.3	1138.4	1138.6	1138.9	1139.1	1139.3
152.5°	1157.3	1157.6	1158.0	1158.1	1158.0	1157.8	1157.7	1157.6
155°	1183.0	1183.8	1184.7	1184.8	1184.1	1183.6	1182.9	1182.2
157.5°	1205.0	1206.2	1207.3	1207.3	1206.2	1205.0	1204.0	1202.9
160°	1219.2	1220.4	1221.7	1221.7	1220.4	1219.2	1217.9	1216.6
162.5°	1230.6	1231.9	1233.1	1233.1	1231.6	1230.2	1228.8	1227.3
165°	1246.8	1248.5	1250.2	1250.0	1248.1	1246.2	1244.3	1242.4
167.5°	1258.6	1260.5	1262.3	1262.2	1260.1	1257.9	1255.8	1253.7
170°	1265.8	1267.5	1269.2	1269.0	1266.9	1264.8	1262.6	1260.6
172.5°	1270.5	1272.1	1273.8	1273.6	1271.2	1268.9	1266.7	1264.3
175°	1275.8	1277.7	1279.7	1279.3	1276.8	1274.2	1271.7	1269.1
177.5°	1278.0	1279.3	1280.7	1280.3	1278.3	1276.3	1274.2	1272.2
180°	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8	1276.8

(END OF REPORT)