

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332464-940

Luminaire Tested: **S123RDIW-S1000D1320U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332464-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1320U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8091.3 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	42	36
2	88	81	75	70	80	74	69	65	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	23
5	68	56	48	43	61	52	45	40	43	38	34	35	31	29	28	25	23	20
6	62	50	43	37	57	46	40	35	39	34	30	32	28	25	25	23	20	17
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	16
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	21	19	16	14
9	50	38	30	26	45	35	28	24	30	24	21	25	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.5	1.7
10°-20°	391.0	4.8
20°-30°	563.0	7.0
30°-40°	634.1	7.8
40°-50°	606.7	7.5
50°-60°	496.8	6.1
60°-70°	335.2	4.1
70°-80°	168.6	2.1
80°-90°	48.9	0.6
90°-100°	56.1	0.7
100°-110°	267.4	3.3
110°-120°	642.3	7.9
120°-130°	818.0	10.1
130°-140°	874.0	10.8
140°-150°	817.3	10.1
150°-160°	659.2	8.1
160°-170°	425.5	5.3
170°-180°	146.6	1.8
0°-30°	1094.5	13.5
0°-40°	1728.6	21.4
0°-60°	2832.1	35.0
0°-90°	3384.9	41.8
90°-120°	965.9	11.9
90°-150°	3475.0	42.9
90°-180°	4706.0	58.2
0°-180°	8091.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	13	28	32	34	6
95°	70	26	36	43	44	86
105°	342	348	251	60	50	362
115°	641	648	658	669	674	632
125°	904	912	917	920	922	807
135°	1125	1132	1136	1139	1136	866
145°	1298	1306	1308	1310	1310	812
155°	1430	1428	1429	1434	1428	658
165°	1508	1504	1503	1511	1504	426
175°	1543	1538	1539	1546	1538	147
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.7	19.8	17.9	16.1	15.5	16.1	16.8	17.5	18.1	18.1
90°	1.2	3.7	6.2	8.8	11.3	14.3	17.6	20.9	24.2	27.6	28.5
92.5°	21.3	20.6	19.9	19.2	18.5	19.4	21.8	24.3	26.8	29.3	30.9
95°	69.9	59.5	49.0	38.6	28.2	24.3	27.1	30.0	32.7	35.6	37.4
97.5°	140.5	135.9	131.2	126.5	121.8	110.3	91.9	73.7	55.3	36.9	39.0
100°	193.8	198.9	203.9	209.0	214.2	196.8	157.1	117.3	77.6	37.8	39.9
102.5°	254.3	258.0	261.6	265.3	269.0	249.1	205.7	162.3	118.9	75.4	69.1
105°	341.7	344.5	347.3	350.1	352.8	342.9	319.9	296.9	274.0	251.1	206.0
107.5°	433.9	436.1	438.4	440.6	442.8	445.8	449.4	453.0	456.6	460.2	427.1
110°	495.3	497.4	499.4	501.4	503.5	505.9	508.7	511.5	514.3	517.1	508.7



TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	554.0	555.9	557.7	559.5	561.3	563.7	566.5	569.3	572.1	574.9	575.1
115°	641.0	642.5	644.0	645.5	647.0	649.0	651.2	653.5	655.9	658.2	660.7
117.5°	725.1	727.0	728.9	730.8	732.6	734.1	735.3	736.6	737.7	738.9	740.9
120°	777.4	779.7	781.9	784.3	786.6	788.1	788.8	789.6	790.4	791.1	793.2
122.5°	830.6	832.5	834.4	836.2	838.1	839.5	840.5	841.5	842.5	843.5	844.9
125°	903.5	905.5	907.6	909.6	911.7	913.2	914.2	915.3	916.2	917.3	917.7
127.5°	974.1	976.2	978.2	980.3	982.3	983.9	985.2	986.4	987.6	988.8	989.6
130°	1018.2	1020.2	1022.3	1024.3	1026.4	1027.9	1028.9	1029.9	1030.9	1031.9	1033.0
132.5°	1060.3	1062.4	1064.4	1066.5	1068.5	1070.0	1070.8	1071.6	1072.4	1073.2	1074.2
135°	1124.8	1126.3	1127.8	1129.4	1131.0	1132.2	1133.2	1134.3	1135.2	1136.3	1137.0
137.5°	1179.8	1181.8	1183.7	1185.6	1187.6	1188.8	1189.4	1190.0	1190.5	1191.1	1192.3
140°	1216.6	1218.1	1219.6	1221.1	1222.6	1223.8	1224.6	1225.3	1226.1	1226.8	1227.9
142.5°	1250.4	1252.0	1253.6	1255.1	1256.6	1257.8	1258.5	1259.3	1260.0	1260.8	1261.6
145°	1298.0	1299.8	1301.5	1303.3	1305.1	1306.2	1306.7	1307.2	1307.8	1308.2	1308.8
147.5°	1342.6	1343.8	1345.0	1346.1	1347.4	1348.2	1348.7	1349.2	1349.7	1350.2	1350.8
150°	1370.2	1370.9	1371.7	1372.4	1373.2	1373.9	1374.4	1374.8	1375.4	1375.9	1376.4
152.5°	1394.9	1395.3	1395.6	1396.0	1396.3	1396.7	1397.0	1397.3	1397.6	1397.9	1398.8
155°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.6	1427.9	1428.2	1428.4	1428.6	1429.9
157.5°	1456.9	1456.8	1456.8	1456.7	1456.6	1456.5	1456.3	1456.0	1455.7	1455.5	1457.0
160°	1473.4	1473.1	1472.8	1472.6	1472.3	1472.1	1471.9	1471.6	1471.3	1471.1	1472.6
162.5°	1489.0	1488.3	1487.6	1486.9	1486.3	1485.9	1485.6	1485.3	1485.1	1484.8	1486.6
165°	1507.8	1507.0	1506.2	1505.5	1504.7	1504.2	1504.0	1503.7	1503.4	1503.2	1505.2
167.5°	1522.4	1521.4	1520.4	1519.4	1518.3	1517.9	1517.9	1517.9	1517.9	1517.9	1519.9
170°	1530.7	1529.6	1528.7	1527.7	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1
172.5°	1536.2	1535.0	1533.7	1532.5	1531.3	1530.8	1531.0	1531.2	1531.4	1531.6	1533.7
175°	1543.3	1542.0	1540.8	1539.4	1538.2	1537.7	1537.9	1538.2	1538.5	1538.7	1540.5
177.5°	1545.2	1544.1	1543.1	1542.1	1541.1	1540.7	1540.9	1541.1	1541.2	1541.5	1543.1
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	18.1	18.1	18.1	18.0	17.9	17.7	17.7	17.6
90°	29.5	30.6	31.6	32.4	32.9	33.3	33.9	34.4
92.5°	32.6	34.2	35.8	36.8	37.2	37.5	37.7	38.1
95°	39.1	40.9	42.7	43.6	43.6	43.6	43.6	43.6
97.5°	41.0	43.1	45.0	46.2	46.5	46.7	47.0	47.3
100°	41.9	44.0	46.0	47.2	47.3	47.6	47.9	48.2
102.5°	62.8	56.4	50.2	47.3	47.7	48.2	48.6	49.0
105°	160.9	115.8	70.7	48.4	49.0	49.4	49.9	50.5
107.5°	394.1	361.1	328.0	294.4	260.5	226.4	192.4	158.5
110°	500.2	491.9	483.5	461.0	424.6	388.2	351.8	315.3



TEST NUMBER: P332464-940

CATALOG NUMBER: S123RDIW-S1000D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	575.2	575.3	575.5	571.8	564.0	556.3	548.7	541.0
115°	663.3	665.8	668.3	670.1	671.1	672.2	673.2	674.2
117.5°	743.0	744.9	747.0	748.1	748.3	748.5	748.8	748.9
120°	795.2	797.3	799.3	800.3	800.3	800.3	800.3	800.3
122.5°	846.3	847.7	849.2	850.0	850.2	850.3	850.6	850.8
125°	918.3	918.8	919.3	919.8	920.3	920.9	921.3	921.9
127.5°	990.4	991.2	992.1	992.2	991.8	991.2	990.7	990.2
130°	1033.9	1035.0	1036.0	1036.3	1035.7	1035.3	1034.7	1034.2
132.5°	1075.2	1076.3	1077.3	1077.5	1076.7	1076.0	1075.3	1074.6
135°	1137.8	1138.5	1139.3	1139.3	1138.5	1137.8	1137.0	1136.3
137.5°	1193.6	1194.7	1196.0	1196.3	1195.8	1195.3	1194.8	1194.3
140°	1228.9	1229.9	1230.9	1231.2	1230.7	1230.1	1229.7	1229.1
142.5°	1262.4	1263.2	1264.1	1264.1	1263.4	1262.7	1261.9	1261.2
145°	1309.3	1309.7	1310.3	1310.5	1310.5	1310.5	1310.5	1310.5
147.5°	1351.2	1351.7	1352.3	1351.9	1350.8	1349.6	1348.4	1347.2
150°	1376.9	1377.4	1378.0	1377.8	1377.1	1376.3	1375.6	1374.8
152.5°	1399.7	1400.7	1401.6	1401.5	1400.3	1399.1	1397.9	1396.8
155°	1431.2	1432.4	1433.8	1433.6	1432.1	1430.6	1429.1	1427.5
157.5°	1458.6	1460.1	1461.6	1461.3	1459.4	1457.4	1455.4	1453.4
160°	1474.1	1475.7	1477.2	1477.0	1475.2	1473.5	1471.7	1469.9
162.5°	1488.3	1490.0	1491.7	1491.8	1490.2	1488.7	1487.1	1485.5
165°	1507.3	1509.3	1511.4	1511.4	1509.7	1507.9	1506.1	1504.3
167.5°	1522.0	1523.9	1526.0	1526.0	1523.9	1522.0	1519.9	1517.9
170°	1530.2	1532.2	1534.3	1534.3	1532.2	1530.2	1528.1	1526.1
172.5°	1535.7	1537.8	1539.8	1539.6	1537.4	1535.2	1532.9	1530.7
175°	1542.3	1544.1	1545.9	1545.7	1543.7	1541.7	1539.6	1537.6
177.5°	1544.7	1546.4	1548.0	1547.8	1545.8	1543.7	1541.7	1539.6
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3

(END OF REPORT)