

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333027-830

Luminaire Tested: **S124RDIW-S350D1340U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333027-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U830-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6460.3 lumens
Efficiency: N/A
Efficacy: 138.6 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ··· 90°-270° - · 135°-315°



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	88	84	81	81	78	75	72	59	57	56	42	41	40	27	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	37	36	34	24	23	22	16
3	76	67	61	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4469	4469	4469	4469
5°	5185	4483	3963	4483
10°	6133	4464	3536	4464
15°	7084	4422	3039	4422
20°	7887	4365	2748	4365
25°	8143	4309	2551	4309
30°	7128	4242	2433	4242
35°	5549	4142	2361	4142
40°	4161	4027	2323	4027
45°	3286	3843	2302	3843
50°	2773	3631	2236	3631
55°	2417	3398	2115	3398
60°	2175	3155	1873	3155
65°	1918	2894	1612	2894
70°	1725	2622	1452	2622
75°	1447	2324	1238	2324
80°	1223	1980	1162	1980
85°	1028	1556	1028	1556



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	0.8
10°-20°	161.8	2.5
20°-30°	253.1	3.9
30°-40°	281.4	4.4
40°-50°	249.6	3.9
50°-60°	194.5	3.0
60°-70°	127.4	2.0
70°-80°	62.6	1.0
80°-90°	20.2	0.3
90°-100°	55.9	0.9
100°-110°	356.4	5.5
110°-120°	681.9	10.6
120°-130°	865.6	13.4
130°-140°	926.1	14.3
140°-150°	866.0	13.4
150°-160°	698.4	10.8
160°-170°	450.5	7.0
170°-180°	155.3	2.4
0°-30°	468.6	7.3
0°-40°	749.9	11.6
0°-60°	1194.1	18.5
0°-90°	1404.2	21.7
90°-120°	1094.2	16.9
90°-150°	3752.0	58.1
90°-180°	5056.0	78.3
0°-180°	6460.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	554	554	554	554	554	
5°	640	553	489	553	640	65
15°	848	529	364	529	848	241
25°	914	484	286	484	914	406
35°	563	420	240	420	563	353
45°	288	337	202	337	288	228
55°	172	241	150	241	172	156
65°	100	152	84	152	100	101
75°	46	74	40	74	46	51
85°	11	17	11	17	11	14
90°	37	4	37	4	37	16
95°	35	67	35	67	35	28
105°	348	368	348	368	348	304
115°	692	687	692	687	692	685
125°	973	966	973	966	973	867
135°	1207	1198	1207	1198	1207	929
145°	1389	1382	1389	1382	1389	868
155°	1514	1515	1514	1515	1514	698
165°	1590	1598	1590	1598	1590	449
175°	1625	1635	1625	1635	1625	155
180°	1635	1635	1635	1635	1635	



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	584.0	585.6	584.0	583.8	582.0	581.5	580.8	578.4	574.2	571.7	572.2
5°	639.8	645.4	642.2	641.8	636.9	632.0	628.9	621.7	614.1	609.0	604.7
7.5°	704.3	707.5	705.5	702.4	694.5	689.9	682.7	673.4	659.7	649.3	639.8
10°	748.2	750.8	750.0	744.1	738.4	726.5	719.8	706.7	689.5	675.9	663.2
12.5°	791.4	794.2	786.4	786.6	775.6	766.3	755.7	739.1	719.3	701.8	685.9
15°	847.6	844.0	844.0	839.6	827.4	814.5	803.5	786.1	761.1	740.2	718.0
17.5°	891.7	893.0	891.2	880.6	871.0	857.6	837.5	817.3	794.1	765.9	743.4
20°	918.1	918.1	916.2	909.0	896.5	882.2	860.6	838.5	809.1	780.7	755.4
22.5°	928.9	929.5	927.2	921.3	910.1	896.2	877.7	855.3	824.9	793.1	761.6
25°	914.2	918.4	918.8	917.3	913.9	905.4	889.6	866.7	839.4	804.8	770.9
27.5°	839.2	844.6	849.3	857.1	867.3	872.6	873.4	861.7	837.9	804.6	770.5
30°	764.7	769.1	783.6	802.6	817.3	830.7	842.4	845.5	832.1	802.2	766.3
32.5°	681.8	688.0	702.5	722.8	747.3	770.1	796.1	809.4	809.0	791.1	757.9
35°	563.0	567.5	580.9	602.3	631.7	665.4	706.7	738.8	760.6	759.1	738.8
37.5°	454.1	459.1	472.6	490.4	519.0	560.6	600.6	644.9	685.2	707.9	701.2
40°	394.8	395.0	408.2	426.5	453.3	489.7	533.1	582.2	627.3	664.1	671.2
42.5°	348.1	348.1	356.8	376.5	395.8	430.0	471.6	520.3	573.1	615.6	634.4
45°	287.8	289.7	296.9	308.7	323.9	352.9	386.2	431.4	490.5	540.9	572.4
47.5°	243.6	246.7	251.2	260.8	272.9	292.2	319.7	360.4	408.5	463.9	508.7
50°	220.8	221.3	227.1	232.4	242.9	258.4	282.4	316.3	360.5	413.8	463.5
52.5°	201.2	201.1	204.6	211.4	219.9	231.9	251.4	282.2	321.4	369.2	420.6
55°	171.7	172.9	175.6	180.9	187.4	195.9	211.2	234.4	265.2	306.0	352.7
57.5°	149.4	150.0	152.0	154.3	160.2	166.5	178.0	194.1	220.0	253.4	296.9
60°	134.7	135.0	135.6	138.9	143.6	149.5	157.3	170.9	192.7	223.3	257.7
62.5°	120.5	120.8	121.9	124.3	128.0	132.0	140.2	151.1	169.2	195.3	226.2
65°	100.4	100.6	102.2	103.0	105.9	109.5	115.6	122.9	135.4	157.3	180.7
67.5°	83.9	83.9	84.0	85.2	87.2	89.5	93.1	99.1	108.5	121.9	142.5
70°	73.1	73.1	73.6	74.3	75.4	77.4	79.5	83.9	90.8	101.7	117.5
72.5°	63.2	63.3	63.8	63.9	64.5	66.2	67.7	70.5	75.6	83.9	96.7
75°	46.4	47.0	48.2	49.1	50.2	50.0	51.6	53.3	54.9	59.8	67.1
77.5°	34.5	34.2	34.3	35.1	35.2	35.4	36.6	37.9	39.1	41.4	44.0
80°	26.3	26.3	27.0	27.2	27.0	27.2	28.4	29.0	29.4	30.3	32.8
82.5°	19.9	20.3	20.1	20.3	20.4	20.6	21.6	21.7	22.1	22.5	23.5
85°	11.1	11.4	11.6	11.1	11.1	11.1	11.6	11.8	12.3	12.1	12.5
87.5°	11.2	10.9	11.0	10.9	11.0	10.7	10.5	10.5	9.8	9.7	9.2
90°	36.7	36.1	35.6	35.1	34.5	33.5	31.8	30.2	28.6	26.9	24.7
92.5°	33.7	33.6	33.6	33.5	33.3	32.4	30.8	29.2	27.5	25.9	23.8
95°	35.4	35.2	34.9	34.6	34.4	33.5	31.8	30.2	28.6	26.9	26.6
97.5°	34.2	33.9	33.6	33.5	33.2	32.9	32.8	32.6	32.4	32.2	62.6
100°	34.2	33.9	33.6	33.5	33.2	35.3	40.0	44.6	49.2	53.8	91.2
102.5°	35.3	35.2	35.1	35.1	35.0	59.9	109.7	159.6	209.3	259.2	264.1
105°	348.5	358.2	368.0	377.8	387.6	391.2	388.8	386.3	383.9	381.4	380.0
107.5°	485.6	484.6	483.5	482.5	481.5	480.3	479.2	478.0	476.7	475.6	473.7
110°	545.3	544.4	543.7	542.8	542.0	541.3	540.7	540.3	539.7	539.1	537.5



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	604.9	603.9	602.9	601.8	600.8	600.3	600.4	600.5	600.7	600.8	600.0
115°	691.9	691.9	691.9	691.9	691.9	691.6	691.2	690.6	690.0	689.5	689.8
117.5°	780.4	780.6	780.7	780.8	780.9	781.0	781.1	781.2	781.4	781.5	780.8
120°	836.2	836.8	837.3	837.8	838.4	838.4	837.8	837.3	836.8	836.2	836.5
122.5°	891.0	891.6	892.0	892.6	893.2	893.2	893.0	892.6	892.3	891.9	891.6
125°	973.2	972.9	972.6	972.3	972.0	971.5	970.7	969.9	969.0	968.3	968.7
127.5°	1045.3	1045.5	1045.7	1045.9	1046.1	1046.3	1046.5	1046.7	1046.8	1047.0	1045.8
130°	1094.2	1094.2	1094.2	1094.2	1094.2	1094.0	1093.7	1093.4	1093.3	1093.0	1092.1
132.5°	1139.2	1139.3	1139.6	1139.8	1140.0	1140.0	1139.7	1139.4	1139.2	1138.9	1137.8
135°	1206.6	1206.1	1205.5	1205.0	1204.5	1203.9	1203.3	1202.9	1202.3	1201.7	1200.7
137.5°	1264.3	1264.5	1264.7	1264.8	1265.0	1264.8	1264.1	1263.6	1263.0	1262.3	1261.2
140°	1304.5	1304.2	1303.9	1303.6	1303.3	1302.8	1302.0	1301.2	1300.3	1299.6	1299.0
142.5°	1337.7	1337.7	1337.6	1337.6	1337.5	1337.2	1336.5	1336.0	1335.4	1334.7	1334.5
145°	1388.8	1388.3	1387.7	1387.1	1386.7	1386.2	1385.9	1385.6	1385.4	1385.2	1385.2
147.5°	1431.1	1430.8	1430.6	1430.3	1430.0	1429.7	1429.6	1429.4	1429.1	1428.9	1429.2
150°	1458.5	1458.2	1457.9	1457.6	1457.4	1457.3	1457.3	1457.3	1457.3	1457.3	1457.5
152.5°	1482.0	1482.1	1482.2	1482.4	1482.6	1482.4	1482.1	1481.6	1481.2	1480.7	1481.2
155°	1513.5	1514.3	1515.1	1516.0	1516.7	1516.6	1515.5	1514.5	1513.3	1512.3	1513.1
157.5°	1539.9	1541.3	1542.8	1544.2	1545.6	1545.6	1544.2	1542.8	1541.3	1539.9	1540.9
160°	1557.6	1559.2	1560.8	1562.4	1564.1	1564.1	1562.4	1560.8	1559.2	1557.6	1557.7
162.5°	1571.2	1573.0	1574.9	1576.8	1578.6	1578.7	1577.1	1575.5	1573.8	1572.2	1572.4
165°	1590.5	1593.0	1595.4	1597.9	1600.2	1600.4	1598.3	1596.1	1593.9	1591.8	1591.8
167.5°	1605.0	1607.7	1610.3	1613.1	1615.8	1616.0	1613.5	1611.2	1608.8	1606.4	1606.6
170°	1613.7	1616.5	1619.2	1621.9	1624.6	1624.8	1622.7	1620.5	1618.3	1616.2	1615.9
172.5°	1618.6	1621.6	1624.5	1627.4	1630.4	1630.8	1628.6	1626.4	1624.2	1622.0	1621.7
175°	1624.8	1628.0	1631.3	1634.6	1637.8	1638.2	1635.8	1633.3	1630.9	1628.4	1628.1
177.5°	1628.6	1631.3	1633.9	1636.4	1639.1	1639.6	1637.8	1636.1	1634.3	1632.6	1632.1
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	570.4	568.0	566.7	563.8	560.4	558.6	557.0	554.7	551.7	548.5	546.2
5°	599.4	594.0	587.3	579.3	572.2	565.2	559.2	553.2	546.3	539.1	532.1
7.5°	629.1	618.6	607.2	594.0	581.3	569.6	558.8	548.7	537.1	526.6	517.2
10°	649.8	635.6	619.7	602.9	586.3	571.7	557.4	544.5	530.3	517.6	506.8
12.5°	666.6	649.8	630.7	609.9	589.7	572.2	555.8	538.9	522.7	509.0	494.6
15°	694.4	671.5	645.8	620.8	594.7	570.8	548.7	529.1	510.6	491.2	477.6
17.5°	713.6	686.3	655.1	625.1	594.3	566.1	540.6	517.3	495.9	476.1	459.9
20°	725.0	694.8	660.3	626.1	591.5	561.5	534.0	508.1	486.1	464.7	447.9
22.5°	731.4	698.0	660.3	624.5	588.7	556.1	526.0	499.1	475.0	453.6	435.1
25°	733.5	697.8	659.2	618.1	578.9	544.3	513.0	483.8	457.0	435.6	416.0
27.5°	730.6	688.5	649.0	606.9	566.4	530.0	497.2	466.5	439.7	416.7	396.5
30°	726.3	681.3	638.9	595.1	554.1	519.1	484.5	455.1	427.2	403.3	383.0
32.5°	717.0	672.3	626.7	581.9	540.4	504.3	471.5	441.9	414.5	390.1	368.5
35°	698.6	653.4	603.9	557.9	517.1	479.6	448.8	420.3	394.2	368.1	345.3
37.5°	674.4	628.2	578.9	528.6	487.7	452.3	424.1	397.3	371.8	348.0	322.8
40°	651.6	609.4	558.6	508.6	466.7	432.5	406.4	382.1	356.5	332.8	307.6
42.5°	624.0	588.1	536.6	486.4	445.1	412.2	387.9	364.1	340.7	317.8	291.5
45°	577.8	550.5	502.4	454.2	412.5	379.8	357.6	336.6	316.1	294.3	269.5
47.5°	524.8	506.4	464.9	415.5	376.9	347.6	326.0	308.9	291.5	269.7	248.0
50°	488.0	476.3	436.1	391.1	354.2	327.3	305.2	289.1	274.6	253.6	234.2
52.5°	448.8	442.5	408.6	365.5	330.0	303.5	284.6	270.2	255.5	238.1	220.0
55°	389.0	392.4	363.6	326.3	292.8	270.6	253.4	241.4	228.8	214.1	200.1
57.5°	327.9	340.2	320.8	288.1	256.7	236.1	223.2	213.1	202.6	190.4	178.3
60°	291.3	301.6	290.7	261.8	234.4	215.3	203.2	195.4	184.9	173.8	164.7
62.5°	255.6	266.6	260.1	236.9	211.4	194.9	184.3	177.0	169.2	159.5	150.0
65°	210.8	217.9	214.8	198.8	180.7	166.6	156.8	151.5	144.3	137.2	128.8
67.5°	161.5	175.2	173.4	164.9	149.3	138.3	131.9	127.1	120.6	115.4	109.6
70°	132.7	145.4	145.2	138.3	129.8	119.6	115.1	111.1	105.3	100.2	95.5
72.5°	108.7	120.3	122.1	116.7	110.9	103.1	98.9	96.1	90.5	87.0	83.1
75°	76.1	84.5	86.8	86.8	84.1	80.1	76.3	74.5	70.5	67.4	65.1
77.5°	49.9	55.2	58.7	59.5	59.9	58.5	55.4	54.2	51.1	50.0	47.9
80°	35.3	38.8	42.8	44.2	45.2	44.9	43.5	42.6	39.7	38.5	37.7
82.5°	24.3	26.3	29.6	32.6	32.2	33.5	32.2	31.6	29.3	28.9	28.1
85°	12.7	12.9	13.4	15.4	16.5	17.0	17.2	16.8	16.0	16.0	14.5
87.5°	8.8	8.2	8.1	7.5	7.2	7.3	7.3	6.8	6.9	6.9	7.0
90°	22.5	20.4	18.2	15.6	12.6	9.6	6.7	3.7	6.7	9.6	12.6
92.5°	21.6	19.4	17.2	16.0	15.9	15.7	15.6	15.4	15.6	15.7	15.9
95°	26.4	26.1	25.8	30.3	39.5	48.7	58.0	67.2	58.0	48.7	39.5
97.5°	92.9	123.2	153.5	165.8	160.0	154.3	148.5	142.8	148.5	154.3	160.0
100°	128.8	166.3	203.8	220.1	215.2	210.3	205.4	200.5	205.4	210.3	215.2
102.5°	269.0	273.8	278.7	279.4	275.8	272.2	268.6	265.0	268.6	272.2	275.8
105°	378.7	377.4	376.0	374.5	372.9	371.3	369.6	368.0	369.6	371.3	372.9
107.5°	471.8	470.0	468.2	466.8	466.0	465.2	464.4	463.5	464.4	465.2	466.0
110°	535.8	534.2	532.6	531.4	530.6	529.8	529.0	528.1	529.0	529.8	530.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	599.3	598.5	597.7	596.6	595.1	593.7	592.2	590.7	592.2	593.7	595.1
115°	690.0	690.3	690.6	690.3	689.5	688.7	687.9	687.0	687.9	688.7	689.5
117.5°	780.2	779.7	779.0	778.2	777.1	776.0	775.0	773.8	775.0	776.0	777.1
120°	836.8	837.1	837.3	836.9	835.8	834.7	833.6	832.5	833.6	834.7	835.8
122.5°	891.2	890.8	890.4	889.9	889.3	888.6	888.0	887.3	888.0	888.6	889.3
125°	969.3	969.9	970.4	970.2	969.0	968.0	966.9	965.8	966.9	968.0	969.0
127.5°	1044.4	1043.2	1042.0	1041.2	1040.9	1040.7	1040.4	1040.1	1040.4	1040.7	1040.9
130°	1091.3	1090.5	1089.7	1089.1	1088.8	1088.6	1088.4	1088.1	1088.4	1088.6	1088.8
132.5°	1136.8	1135.9	1134.8	1134.0	1133.5	1133.0	1132.6	1132.1	1132.6	1133.0	1133.5
135°	1199.6	1198.4	1197.4	1197.0	1197.3	1197.5	1197.8	1198.1	1197.8	1197.5	1197.3
137.5°	1260.0	1258.8	1257.6	1257.0	1256.9	1256.7	1256.6	1256.5	1256.6	1256.7	1256.9
140°	1298.4	1297.9	1297.4	1296.8	1296.3	1295.7	1295.2	1294.7	1295.2	1295.7	1296.3
142.5°	1334.1	1333.8	1333.4	1332.8	1331.8	1330.9	1329.8	1328.9	1329.8	1330.9	1331.8
145°	1385.2	1385.2	1385.2	1384.7	1383.9	1383.1	1382.2	1381.5	1382.2	1383.1	1383.9
147.5°	1429.5	1429.7	1430.0	1429.4	1427.9	1426.3	1424.7	1423.2	1424.7	1426.3	1427.9
150°	1457.8	1458.1	1458.3	1457.9	1456.9	1455.8	1454.7	1453.6	1454.7	1455.8	1456.9
152.5°	1481.7	1482.2	1482.7	1482.5	1481.6	1480.7	1479.9	1479.0	1479.9	1480.7	1481.6
155°	1513.9	1514.8	1515.5	1515.8	1515.5	1515.2	1514.9	1514.8	1514.9	1515.2	1515.5
157.5°	1541.7	1542.7	1543.6	1544.2	1544.3	1544.5	1544.6	1544.8	1544.6	1544.5	1544.3
160°	1558.0	1558.3	1558.6	1559.2	1559.9	1560.8	1561.6	1562.4	1561.6	1560.8	1559.9
162.5°	1572.7	1573.0	1573.3	1574.0	1575.0	1576.0	1577.0	1578.0	1577.0	1576.0	1575.0
165°	1591.8	1591.8	1591.8	1592.4	1593.7	1595.2	1596.5	1597.9	1596.5	1595.2	1593.7
167.5°	1606.8	1606.9	1607.0	1607.9	1609.3	1610.7	1612.1	1613.5	1612.1	1610.7	1609.3
170°	1615.6	1615.3	1615.1	1615.8	1617.4	1619.0	1620.7	1622.3	1620.7	1619.0	1617.4
172.5°	1621.6	1621.3	1621.0	1621.6	1623.2	1624.9	1626.5	1628.1	1626.5	1624.9	1623.2
175°	1627.9	1627.6	1627.3	1628.0	1629.7	1631.3	1632.9	1634.6	1632.9	1631.3	1629.7
177.5°	1631.7	1631.3	1630.8	1631.4	1632.9	1634.4	1636.0	1637.5	1636.0	1634.4	1632.9
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	543.7	541.9	539.6	536.9	533.7	530.8	529.5	530.7	531.2	529.7	529.5
5°	527.1	521.5	517.1	510.4	505.0	500.6	497.5	496.1	496.5	492.9	492.1
7.5°	508.5	501.9	494.6	486.6	479.3	472.7	469.3	467.4	463.5	461.9	459.2
10°	496.5	487.7	480.5	471.1	462.6	454.9	451.0	447.9	444.1	442.3	438.6
12.5°	484.3	473.9	466.0	456.3	447.6	438.3	434.6	428.9	422.9	419.1	414.2
15°	466.8	454.4	444.8	433.2	422.9	412.3	402.7	391.9	388.0	379.5	374.6
17.5°	446.6	433.9	422.1	406.5	390.7	377.3	367.1	356.8	350.7	345.3	342.8
20°	433.2	421.6	405.1	387.0	369.4	354.7	346.4	339.7	333.0	329.2	326.6
22.5°	420.6	405.7	386.5	367.0	349.4	337.9	330.9	324.0	318.6	315.0	311.4
25°	399.3	379.8	359.6	337.2	325.3	315.2	307.6	302.0	298.7	294.0	292.2
27.5°	377.5	353.9	331.6	316.6	304.1	294.8	288.2	284.1	279.8	276.8	274.5
30°	360.7	336.9	316.8	302.5	289.7	282.2	276.8	271.9	268.5	266.1	264.4
32.5°	344.1	320.3	303.4	288.0	278.0	270.6	264.9	261.2	258.5	255.4	254.3
35°	320.1	298.9	284.2	270.3	260.1	253.4	248.9	245.2	242.9	242.0	241.4
37.5°	297.0	279.7	263.8	252.5	243.4	238.1	232.8	230.9	229.4	227.8	228.6
40°	282.4	266.1	252.0	240.1	232.6	226.9	223.8	221.5	220.2	220.2	220.2
42.5°	269.8	253.8	240.1	229.3	222.0	217.1	213.6	211.7	211.2	211.0	212.2
45°	250.1	235.4	221.5	212.5	206.3	201.4	199.4	197.8	197.8	198.8	199.0
47.5°	230.5	216.8	205.7	195.7	189.9	186.9	185.1	184.4	184.5	185.3	186.3
50°	218.6	205.0	194.1	185.1	179.8	176.9	175.3	174.8	175.3	175.3	176.9
52.5°	205.6	193.4	182.7	175.1	169.1	166.4	165.5	164.9	165.1	165.9	166.5
55°	186.5	175.6	165.3	158.2	153.7	151.9	149.9	150.1	149.7	150.1	150.1
57.5°	167.3	157.5	148.0	142.3	138.4	135.8	133.7	134.2	133.6	133.5	133.1
60°	155.0	144.3	136.8	131.6	127.1	124.9	122.9	123.4	122.7	122.2	121.3
62.5°	141.7	132.7	125.5	120.6	117.0	114.4	112.4	112.0	110.4	108.9	106.9
65°	122.2	114.9	108.4	103.8	100.4	98.4	96.8	95.5	92.1	88.6	86.8
67.5°	103.4	98.0	92.0	88.0	85.3	82.8	79.7	77.5	74.4	72.4	71.3
70°	91.2	86.1	81.0	77.2	74.3	71.8	68.5	66.9	64.7	63.8	62.7
72.5°	79.6	74.8	70.1	66.6	63.6	61.6	59.0	57.5	56.5	56.1	55.0
75°	62.0	58.2	54.7	51.6	49.1	47.7	46.7	45.5	45.1	43.1	41.9
77.5°	45.2	42.7	40.5	38.3	36.6	35.6	33.5	32.2	31.5	30.5	30.3
80°	35.3	33.5	31.2	29.9	27.4	26.6	25.6	25.4	25.2	25.0	24.8
82.5°	26.5	24.7	22.5	21.7	21.0	20.5	20.0	19.7	19.5	19.6	19.6
85°	13.4	12.5	12.5	12.3	12.1	11.8	11.6	11.6	11.4	11.6	11.4
87.5°	7.5	7.9	8.4	8.5	9.0	9.5	9.6	10.0	10.5	10.5	10.7
90°	15.6	18.2	20.4	22.5	24.7	26.9	28.6	30.2	31.8	33.5	34.5
92.5°	16.0	17.2	19.4	21.6	23.8	25.9	27.5	29.2	30.8	32.4	33.3
95°	30.3	25.8	26.1	26.4	26.6	26.9	28.6	30.2	31.8	33.5	34.4
97.5°	165.8	153.5	123.2	92.9	62.6	32.2	32.4	32.6	32.8	32.9	33.2
100°	220.1	203.8	166.3	128.8	91.2	53.8	49.2	44.6	40.0	35.3	33.2
102.5°	279.4	278.7	273.8	269.0	264.1	259.2	209.3	159.6	109.7	59.9	35.0
105°	374.5	376.0	377.4	378.7	380.0	381.4	383.9	386.3	388.8	391.2	387.6
107.5°	466.8	468.2	470.0	471.8	473.7	475.6	476.7	478.0	479.2	480.3	481.5
110°	531.4	532.6	534.2	535.8	537.5	539.1	539.7	540.3	540.7	541.3	542.0



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	596.6	597.7	598.5	599.3	600.0	600.8	600.7	600.5	600.4	600.3	600.8
115°	690.3	690.6	690.3	690.0	689.8	689.5	690.0	690.6	691.2	691.6	691.9
117.5°	778.2	779.0	779.7	780.2	780.8	781.5	781.4	781.2	781.1	781.0	780.9
120°	836.9	837.3	837.1	836.8	836.5	836.2	836.8	837.3	837.8	838.4	838.4
122.5°	889.9	890.4	890.8	891.2	891.6	891.9	892.3	892.6	893.0	893.2	893.2
125°	970.2	970.4	969.9	969.3	968.7	968.3	969.0	969.9	970.7	971.5	972.0
127.5°	1041.2	1042.0	1043.2	1044.4	1045.8	1047.0	1046.8	1046.7	1046.5	1046.3	1046.1
130°	1089.1	1089.7	1090.5	1091.3	1092.1	1093.0	1093.3	1093.4	1093.7	1094.0	1094.2
132.5°	1134.0	1134.8	1135.9	1136.8	1137.8	1138.9	1139.2	1139.4	1139.7	1140.0	1140.0
135°	1197.0	1197.4	1198.4	1199.6	1200.7	1201.7	1202.3	1202.9	1203.3	1203.9	1204.5
137.5°	1257.0	1257.6	1258.8	1260.0	1261.2	1262.3	1263.0	1263.6	1264.1	1264.8	1265.0
140°	1296.8	1297.4	1297.9	1298.4	1299.0	1299.6	1300.3	1301.2	1302.0	1302.8	1303.3
142.5°	1332.8	1333.4	1333.8	1334.1	1334.5	1334.7	1335.4	1336.0	1336.5	1337.2	1337.5
145°	1384.7	1385.2	1385.2	1385.2	1385.2	1385.2	1385.4	1385.6	1385.9	1386.2	1386.7
147.5°	1429.4	1430.0	1429.7	1429.5	1429.2	1428.9	1429.1	1429.4	1429.6	1429.7	1430.0
150°	1457.9	1458.3	1458.1	1457.8	1457.5	1457.3	1457.3	1457.3	1457.3	1457.3	1457.4
152.5°	1482.5	1482.7	1482.2	1481.7	1481.2	1480.7	1481.2	1481.6	1482.1	1482.4	1482.6
155°	1515.8	1515.5	1514.8	1513.9	1513.1	1512.3	1513.3	1514.5	1515.5	1516.6	1516.7
157.5°	1544.2	1543.6	1542.7	1541.7	1540.9	1539.9	1541.3	1542.8	1544.2	1545.6	1545.6
160°	1559.2	1558.6	1558.3	1558.0	1557.7	1557.6	1559.2	1560.8	1562.4	1564.1	1564.1
162.5°	1574.0	1573.3	1573.0	1572.7	1572.4	1572.2	1573.8	1575.5	1577.1	1578.7	1578.6
165°	1592.4	1591.8	1591.8	1591.8	1591.8	1591.8	1593.9	1596.1	1598.3	1600.4	1600.2
167.5°	1607.9	1607.0	1606.9	1606.8	1606.6	1606.4	1608.8	1611.2	1613.5	1616.0	1615.8
170°	1615.8	1615.1	1615.3	1615.6	1615.9	1616.2	1618.3	1620.5	1622.7	1624.8	1624.6
172.5°	1621.6	1621.0	1621.3	1621.6	1621.7	1622.0	1624.2	1626.4	1628.6	1630.8	1630.4
175°	1628.0	1627.3	1627.6	1627.9	1628.1	1628.4	1630.9	1633.3	1635.8	1638.2	1637.8
177.5°	1631.4	1630.8	1631.3	1631.7	1632.1	1632.6	1634.3	1636.1	1637.8	1639.6	1639.1
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	528.5	528.9	527.6	527.3	527.6	528.9	528.5	529.5	529.7	531.2	530.7
5°	490.3	489.8	488.7	489.0	488.7	489.8	490.3	492.1	492.9	496.5	496.1
7.5°	457.6	455.9	456.4	454.6	456.4	455.9	457.6	459.2	461.9	463.5	467.4
10°	437.6	435.2	433.2	431.4	433.2	435.2	437.6	438.6	442.3	444.1	447.9
12.5°	410.4	408.2	405.6	406.0	405.6	408.2	410.4	414.2	419.1	422.9	428.9
15°	371.6	368.3	363.0	363.6	363.0	368.3	371.6	374.6	379.5	388.0	391.9
17.5°	338.8	338.8	336.4	337.1	336.4	338.8	338.8	342.8	345.3	350.7	356.8
20°	321.9	320.4	320.6	319.9	320.6	320.4	321.9	326.6	329.2	333.0	339.7
22.5°	310.1	308.2	306.6	305.3	306.6	308.2	310.1	311.4	315.0	318.6	324.0
25°	290.2	288.9	286.9	286.4	286.9	288.9	290.2	292.2	294.0	298.7	302.0
27.5°	272.7	272.5	271.6	270.6	271.6	272.5	272.7	274.5	276.8	279.8	284.1
30°	262.6	262.1	261.6	261.0	261.6	262.1	262.6	264.4	266.1	268.5	271.9
32.5°	253.4	253.2	252.7	252.8	252.7	253.2	253.4	254.3	255.4	258.5	261.2
35°	240.4	240.3	239.8	239.6	239.8	240.3	240.4	241.4	242.0	242.9	245.2
37.5°	228.4	228.9	228.7	228.6	228.7	228.9	228.4	228.6	227.8	229.4	230.9
40°	220.0	220.2	220.6	220.4	220.6	220.2	220.0	220.2	220.2	220.2	221.5
42.5°	213.0	213.0	213.7	212.9	213.7	213.0	213.0	212.2	211.0	211.2	211.7
45°	200.6	201.9	201.6	201.6	201.6	201.9	200.6	199.0	198.8	197.8	197.8
47.5°	186.9	188.1	188.4	188.3	188.4	188.1	186.9	186.3	185.3	184.5	184.4
50°	178.0	177.6	178.2	178.0	178.2	177.6	178.0	176.9	175.3	175.3	174.8
52.5°	167.1	167.2	167.2	166.9	167.2	167.2	167.1	166.5	165.9	165.1	164.9
55°	150.3	150.6	150.1	150.3	150.1	150.6	150.3	150.1	150.1	149.7	150.1
57.5°	132.1	131.1	131.5	131.0	131.5	131.1	132.1	133.1	133.5	133.6	134.2
60°	119.1	117.3	116.9	116.0	116.9	117.3	119.1	121.3	122.2	122.7	123.4
62.5°	104.5	103.2	101.7	102.5	101.7	103.2	104.5	106.9	108.9	110.4	112.0
65°	85.0	84.1	83.4	84.4	83.4	84.1	85.0	86.8	88.6	92.1	95.5
67.5°	70.3	69.8	69.8	69.5	69.8	69.8	70.3	71.3	72.4	74.4	77.5
70°	62.7	62.0	62.0	61.5	62.0	62.0	62.7	62.7	63.8	64.7	66.9
72.5°	54.9	54.2	54.4	54.1	54.4	54.2	54.9	55.0	56.1	56.5	57.5
75°	40.6	39.5	39.5	39.7	39.5	39.5	40.6	41.9	43.1	45.1	45.5
77.5°	30.3	30.1	30.3	30.0	30.3	30.1	30.3	30.3	30.5	31.5	32.2
80°	24.8	24.5	24.3	25.0	24.3	24.5	24.8	24.8	25.0	25.2	25.4
82.5°	19.2	19.2	19.1	20.0	19.1	19.2	19.2	19.6	19.6	19.5	19.7
85°	11.6	11.1	11.6	11.1	11.6	11.1	11.6	11.4	11.6	11.4	11.6
87.5°	11.1	11.0	10.9	11.2	10.9	11.0	11.1	10.7	10.5	10.5	10.0
90°	35.1	35.6	36.1	36.7	36.1	35.6	35.1	34.5	33.5	31.8	30.2
92.5°	33.5	33.6	33.6	33.7	33.6	33.6	33.5	33.3	32.4	30.8	29.2
95°	34.6	34.9	35.2	35.4	35.2	34.9	34.6	34.4	33.5	31.8	30.2
97.5°	33.5	33.6	33.9	34.2	33.9	33.6	33.5	33.2	32.9	32.8	32.6
100°	33.5	33.6	33.9	34.2	33.9	33.6	33.5	33.2	35.3	40.0	44.6
102.5°	35.1	35.1	35.2	35.3	35.2	35.1	35.1	35.0	59.9	109.7	159.6
105°	377.8	368.0	358.2	348.5	358.2	368.0	377.8	387.6	391.2	388.8	386.3
107.5°	482.5	483.5	484.6	485.6	484.6	483.5	482.5	481.5	480.3	479.2	478.0
110°	542.8	543.7	544.4	545.3	544.4	543.7	542.8	542.0	541.3	540.7	540.3



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	601.8	602.9	603.9	604.9	603.9	602.9	601.8	600.8	600.3	600.4	600.5
115°	691.9	691.9	691.9	691.9	691.9	691.9	691.9	691.9	691.6	691.2	690.6
117.5°	780.8	780.7	780.6	780.4	780.6	780.7	780.8	780.9	781.0	781.1	781.2
120°	837.8	837.3	836.8	836.2	836.8	837.3	837.8	838.4	838.4	837.8	837.3
122.5°	892.6	892.0	891.6	891.0	891.6	892.0	892.6	893.2	893.2	893.0	892.6
125°	972.3	972.6	972.9	973.2	972.9	972.6	972.3	972.0	971.5	970.7	969.9
127.5°	1045.9	1045.7	1045.5	1045.3	1045.5	1045.7	1045.9	1046.1	1046.3	1046.5	1046.7
130°	1094.2	1094.2	1094.2	1094.2	1094.2	1094.2	1094.2	1094.2	1094.0	1093.7	1093.4
132.5°	1139.8	1139.6	1139.3	1139.2	1139.3	1139.6	1139.8	1140.0	1140.0	1139.7	1139.4
135°	1205.0	1205.5	1206.1	1206.6	1206.1	1205.5	1205.0	1204.5	1203.9	1203.3	1202.9
137.5°	1264.8	1264.7	1264.5	1264.3	1264.5	1264.7	1264.8	1265.0	1264.8	1264.1	1263.6
140°	1303.6	1303.9	1304.2	1304.5	1304.2	1303.9	1303.6	1303.3	1302.8	1302.0	1301.2
142.5°	1337.6	1337.6	1337.7	1337.7	1337.7	1337.6	1337.6	1337.5	1337.2	1336.5	1336.0
145°	1387.1	1387.7	1388.3	1388.8	1388.3	1387.7	1387.1	1386.7	1386.2	1385.9	1385.6
147.5°	1430.3	1430.6	1430.8	1431.1	1430.8	1430.6	1430.3	1430.0	1429.7	1429.6	1429.4
150°	1457.6	1457.9	1458.2	1458.5	1458.2	1457.9	1457.6	1457.4	1457.3	1457.3	1457.3
152.5°	1482.4	1482.2	1482.1	1482.0	1482.1	1482.2	1482.4	1482.6	1482.4	1482.1	1481.6
155°	1516.0	1515.1	1514.3	1513.5	1514.3	1515.1	1516.0	1516.7	1516.6	1515.5	1514.5
157.5°	1544.2	1542.8	1541.3	1539.9	1541.3	1542.8	1544.2	1545.6	1545.6	1544.2	1542.8
160°	1562.4	1560.8	1559.2	1557.6	1559.2	1560.8	1562.4	1564.1	1564.1	1562.4	1560.8
162.5°	1576.8	1574.9	1573.0	1571.2	1573.0	1574.9	1576.8	1578.6	1578.7	1577.1	1575.5
165°	1597.9	1595.4	1593.0	1590.5	1593.0	1595.4	1597.9	1600.2	1600.4	1598.3	1596.1
167.5°	1613.1	1610.3	1607.7	1605.0	1607.7	1610.3	1613.1	1615.8	1616.0	1613.5	1611.2
170°	1621.9	1619.2	1616.5	1613.7	1616.5	1619.2	1621.9	1624.6	1624.8	1622.7	1620.5
172.5°	1627.4	1624.5	1621.6	1618.6	1621.6	1624.5	1627.4	1630.4	1630.8	1628.6	1626.4
175°	1634.6	1631.3	1628.0	1624.8	1628.0	1631.3	1634.6	1637.8	1638.2	1635.8	1633.3
177.5°	1636.4	1633.9	1631.3	1628.6	1631.3	1633.9	1636.4	1639.1	1639.6	1637.8	1636.1
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	529.5	530.8	533.7	536.9	539.6	541.9	543.7	546.2	548.5	551.7	554.7
5°	497.5	500.6	505.0	510.4	517.1	521.5	527.1	532.1	539.1	546.3	553.2
7.5°	469.3	472.7	479.3	486.6	494.6	501.9	508.5	517.2	526.6	537.1	548.7
10°	451.0	454.9	462.6	471.1	480.5	487.7	496.5	506.8	517.6	530.3	544.5
12.5°	434.6	438.3	447.6	456.3	466.0	473.9	484.3	494.6	509.0	522.7	538.9
15°	402.7	412.3	422.9	433.2	444.8	454.4	466.8	477.6	491.2	510.6	529.1
17.5°	367.1	377.3	390.7	406.5	422.1	433.9	446.6	459.9	476.1	495.9	517.3
20°	346.4	354.7	369.4	387.0	405.1	421.6	433.2	447.9	464.7	486.1	508.1
22.5°	330.9	337.9	349.4	367.0	386.5	405.7	420.6	435.1	453.6	475.0	499.1
25°	307.6	315.2	325.3	337.2	359.6	379.8	399.3	416.0	435.6	457.0	483.8
27.5°	288.2	294.8	304.1	316.6	331.6	353.9	377.5	396.5	416.7	439.7	466.5
30°	276.8	282.2	289.7	302.5	316.8	336.9	360.7	383.0	403.3	427.2	455.1
32.5°	264.9	270.6	278.0	288.0	303.4	320.3	344.1	368.5	390.1	414.5	441.9
35°	248.9	253.4	260.1	270.3	284.2	298.9	320.1	345.3	368.1	394.2	420.3
37.5°	232.8	238.1	243.4	252.5	263.8	279.7	297.0	322.8	348.0	371.8	397.3
40°	223.8	226.9	232.6	240.1	252.0	266.1	282.4	307.6	332.8	356.5	382.1
42.5°	213.6	217.1	222.0	229.3	240.1	253.8	269.8	291.5	317.8	340.7	364.1
45°	199.4	201.4	206.3	212.5	221.5	235.4	250.1	269.5	294.3	316.1	336.6
47.5°	185.1	186.9	189.9	195.7	205.7	216.8	230.5	248.0	269.7	291.5	308.9
50°	175.3	176.9	179.8	185.1	194.1	205.0	218.6	234.2	253.6	274.6	289.1
52.5°	165.5	166.4	169.1	175.1	182.7	193.4	205.6	220.0	238.1	255.5	270.2
55°	149.9	151.9	153.7	158.2	165.3	175.6	186.5	200.1	214.1	228.8	241.4
57.5°	133.7	135.8	138.4	142.3	148.0	157.5	167.3	178.3	190.4	202.6	213.1
60°	122.9	124.9	127.1	131.6	136.8	144.3	155.0	164.7	173.8	184.9	195.4
62.5°	112.4	114.4	117.0	120.6	125.5	132.7	141.7	150.0	159.5	169.2	177.0
65°	96.8	98.4	100.4	103.8	108.4	114.9	122.2	128.8	137.2	144.3	151.5
67.5°	79.7	82.8	85.3	88.0	92.0	98.0	103.4	109.6	115.4	120.6	127.1
70°	68.5	71.8	74.3	77.2	81.0	86.1	91.2	95.5	100.2	105.3	111.1
72.5°	59.0	61.6	63.6	66.6	70.1	74.8	79.6	83.1	87.0	90.5	96.1
75°	46.7	47.7	49.1	51.6	54.7	58.2	62.0	65.1	67.4	70.5	74.5
77.5°	33.5	35.6	36.6	38.3	40.5	42.7	45.2	47.9	50.0	51.1	54.2
80°	25.6	26.6	27.4	29.9	31.2	33.5	35.3	37.7	38.5	39.7	42.6
82.5°	20.0	20.5	21.0	21.7	22.5	24.7	26.5	28.1	28.9	29.3	31.6
85°	11.6	11.8	12.1	12.3	12.5	12.5	13.4	14.5	16.0	16.0	16.8
87.5°	9.6	9.5	9.0	8.5	8.4	7.9	7.5	7.0	6.9	6.9	6.8
90°	28.6	26.9	24.7	22.5	20.4	18.2	15.6	12.6	9.6	6.7	3.7
92.5°	27.5	25.9	23.8	21.6	19.4	17.2	16.0	15.9	15.7	15.6	15.4
95°	28.6	26.9	26.6	26.4	26.1	25.8	30.3	39.5	48.7	58.0	67.2
97.5°	32.4	32.2	62.6	92.9	123.2	153.5	165.8	160.0	154.3	148.5	142.8
100°	49.2	53.8	91.2	128.8	166.3	203.8	220.1	215.2	210.3	205.4	200.5
102.5°	209.3	259.2	264.1	269.0	273.8	278.7	279.4	275.8	272.2	268.6	265.0
105°	383.9	381.4	380.0	378.7	377.4	376.0	374.5	372.9	371.3	369.6	368.0
107.5°	476.7	475.6	473.7	471.8	470.0	468.2	466.8	466.0	465.2	464.4	463.5
110°	539.7	539.1	537.5	535.8	534.2	532.6	531.4	530.6	529.8	529.0	528.1



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	600.7	600.8	600.0	599.3	598.5	597.7	596.6	595.1	593.7	592.2	590.7
115°	690.0	689.5	689.8	690.0	690.3	690.6	690.3	689.5	688.7	687.9	687.0
117.5°	781.4	781.5	780.8	780.2	779.7	779.0	778.2	777.1	776.0	775.0	773.8
120°	836.8	836.2	836.5	836.8	837.1	837.3	836.9	835.8	834.7	833.6	832.5
122.5°	892.3	891.9	891.6	891.2	890.8	890.4	889.9	889.3	888.6	888.0	887.3
125°	969.0	968.3	968.7	969.3	969.9	970.4	970.2	969.0	968.0	966.9	965.8
127.5°	1046.8	1047.0	1045.8	1044.4	1043.2	1042.0	1041.2	1040.9	1040.7	1040.4	1040.1
130°	1093.3	1093.0	1092.1	1091.3	1090.5	1089.7	1089.1	1088.8	1088.6	1088.4	1088.1
132.5°	1139.2	1138.9	1137.8	1136.8	1135.9	1134.8	1134.0	1133.5	1133.0	1132.6	1132.1
135°	1202.3	1201.7	1200.7	1199.6	1198.4	1197.4	1197.0	1197.3	1197.5	1197.8	1198.1
137.5°	1263.0	1262.3	1261.2	1260.0	1258.8	1257.6	1257.0	1256.9	1256.7	1256.6	1256.5
140°	1300.3	1299.6	1299.0	1298.4	1297.9	1297.4	1296.8	1296.3	1295.7	1295.2	1294.7
142.5°	1335.4	1334.7	1334.5	1334.1	1333.8	1333.4	1332.8	1331.8	1330.9	1329.8	1328.9
145°	1385.4	1385.2	1385.2	1385.2	1385.2	1385.2	1384.7	1383.9	1383.1	1382.2	1381.5
147.5°	1429.1	1428.9	1429.2	1429.5	1429.7	1430.0	1429.4	1427.9	1426.3	1424.7	1423.2
150°	1457.3	1457.3	1457.5	1457.8	1458.1	1458.3	1457.9	1456.9	1455.8	1454.7	1453.6
152.5°	1481.2	1480.7	1481.2	1481.7	1482.2	1482.7	1482.5	1481.6	1480.7	1479.9	1479.0
155°	1513.3	1512.3	1513.1	1513.9	1514.8	1515.5	1515.8	1515.5	1515.2	1514.9	1514.8
157.5°	1541.3	1539.9	1540.9	1541.7	1542.7	1543.6	1544.2	1544.3	1544.5	1544.6	1544.8
160°	1559.2	1557.6	1557.7	1558.0	1558.3	1558.6	1559.2	1559.9	1560.8	1561.6	1562.4
162.5°	1573.8	1572.2	1572.4	1572.7	1573.0	1573.3	1574.0	1575.0	1576.0	1577.0	1578.0
165°	1593.9	1591.8	1591.8	1591.8	1591.8	1591.8	1592.4	1593.7	1595.2	1596.5	1597.9
167.5°	1608.8	1606.4	1606.6	1606.8	1606.9	1607.0	1607.9	1609.3	1610.7	1612.1	1613.5
170°	1618.3	1616.2	1615.9	1615.6	1615.3	1615.1	1615.8	1617.4	1619.0	1620.7	1622.3
172.5°	1624.2	1622.0	1621.7	1621.6	1621.3	1621.0	1621.6	1623.2	1624.9	1626.5	1628.1
175°	1630.9	1628.4	1628.1	1627.9	1627.6	1627.3	1628.0	1629.7	1631.3	1632.9	1634.6
177.5°	1634.3	1632.6	1632.1	1631.7	1631.3	1630.8	1631.4	1632.9	1634.4	1636.0	1637.5
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	557.0	558.6	560.4	563.8	566.7	568.0	570.4	572.2	571.7	574.2	578.4
5°	559.2	565.2	572.2	579.3	587.3	594.0	599.4	604.7	609.0	614.1	621.7
7.5°	558.8	569.6	581.3	594.0	607.2	618.6	629.1	639.8	649.3	659.7	673.4
10°	557.4	571.7	586.3	602.9	619.7	635.6	649.8	663.2	675.9	689.5	706.7
12.5°	555.8	572.2	589.7	609.9	630.7	649.8	666.6	685.9	701.8	719.3	739.1
15°	548.7	570.8	594.7	620.8	645.8	671.5	694.4	718.0	740.2	761.1	786.1
17.5°	540.6	566.1	594.3	625.1	655.1	686.3	713.6	743.4	765.9	794.1	817.3
20°	534.0	561.5	591.5	626.1	660.3	694.8	725.0	755.4	780.7	809.1	838.5
22.5°	526.0	556.1	588.7	624.5	660.3	698.0	731.4	761.6	793.1	824.9	855.3
25°	513.0	544.3	578.9	618.1	659.2	697.8	733.5	770.9	804.8	839.4	866.7
27.5°	497.2	530.0	566.4	606.9	649.0	688.5	730.6	770.5	804.6	837.9	861.7
30°	484.5	519.1	554.1	595.1	638.9	681.3	726.3	766.3	802.2	832.1	845.5
32.5°	471.5	504.3	540.4	581.9	626.7	672.3	717.0	757.9	791.1	809.0	809.4
35°	448.8	479.6	517.1	557.9	603.9	653.4	698.6	738.8	759.1	760.6	738.8
37.5°	424.1	452.3	487.7	528.6	578.9	628.2	674.4	701.2	707.9	685.2	644.9
40°	406.4	432.5	466.7	508.6	558.6	609.4	651.6	671.2	664.1	627.3	582.2
42.5°	387.9	412.2	445.1	486.4	536.6	588.1	624.0	634.4	615.6	573.1	520.3
45°	357.6	379.8	412.5	454.2	502.4	550.5	577.8	572.4	540.9	490.5	431.4
47.5°	326.0	347.6	376.9	415.5	464.9	506.4	524.8	508.7	463.9	408.5	360.4
50°	305.2	327.3	354.2	391.1	436.1	476.3	488.0	463.5	413.8	360.5	316.3
52.5°	284.6	303.5	330.0	365.5	408.6	442.5	448.8	420.6	369.2	321.4	282.2
55°	253.4	270.6	292.8	326.3	363.6	392.4	389.0	352.7	306.0	265.2	234.4
57.5°	223.2	236.1	256.7	288.1	320.8	340.2	327.9	296.9	253.4	220.0	194.1
60°	203.2	215.3	234.4	261.8	290.7	301.6	291.3	257.7	223.3	192.7	170.9
62.5°	184.3	194.9	211.4	236.9	260.1	266.6	255.6	226.2	195.3	169.2	151.1
65°	156.8	166.6	180.7	198.8	214.8	217.9	210.8	180.7	157.3	135.4	122.9
67.5°	131.9	138.3	149.3	164.9	173.4	175.2	161.5	142.5	121.9	108.5	99.1
70°	115.1	119.6	129.8	138.3	145.2	145.4	132.7	117.5	101.7	90.8	83.9
72.5°	98.9	103.1	110.9	116.7	122.1	120.3	108.7	96.7	83.9	75.6	70.5
75°	76.3	80.1	84.1	86.8	86.8	84.5	76.1	67.1	59.8	54.9	53.3
77.5°	55.4	58.5	59.9	59.5	58.7	55.2	49.9	44.0	41.4	39.1	37.9
80°	43.5	44.9	45.2	44.2	42.8	38.8	35.3	32.8	30.3	29.4	29.0
82.5°	32.2	33.5	32.2	32.6	29.6	26.3	24.3	23.5	22.5	22.1	21.7
85°	17.2	17.0	16.5	15.4	13.4	12.9	12.7	12.5	12.1	12.3	11.8
87.5°	7.3	7.3	7.2	7.5	8.1	8.2	8.8	9.2	9.7	9.8	10.5
90°	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6	30.2
92.5°	15.6	15.7	15.9	16.0	17.2	19.4	21.6	23.8	25.9	27.5	29.2
95°	58.0	48.7	39.5	30.3	25.8	26.1	26.4	26.6	26.9	28.6	30.2
97.5°	148.5	154.3	160.0	165.8	153.5	123.2	92.9	62.6	32.2	32.4	32.6
100°	205.4	210.3	215.2	220.1	203.8	166.3	128.8	91.2	53.8	49.2	44.6
102.5°	268.6	272.2	275.8	279.4	278.7	273.8	269.0	264.1	259.2	209.3	159.6
105°	369.6	371.3	372.9	374.5	376.0	377.4	378.7	380.0	381.4	383.9	386.3
107.5°	464.4	465.2	466.0	466.8	468.2	470.0	471.8	473.7	475.6	476.7	478.0
110°	529.0	529.8	530.6	531.4	532.6	534.2	535.8	537.5	539.1	539.7	540.3



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	592.2	593.7	595.1	596.6	597.7	598.5	599.3	600.0	600.8	600.7	600.5
115°	687.9	688.7	689.5	690.3	690.6	690.3	690.0	689.8	689.5	690.0	690.6
117.5°	775.0	776.0	777.1	778.2	779.0	779.7	780.2	780.8	781.5	781.4	781.2
120°	833.6	834.7	835.8	836.9	837.3	837.1	836.8	836.5	836.2	836.8	837.3
122.5°	888.0	888.6	889.3	889.9	890.4	890.8	891.2	891.6	891.9	892.3	892.6
125°	966.9	968.0	969.0	970.2	970.4	969.9	969.3	968.7	968.3	969.0	969.9
127.5°	1040.4	1040.7	1040.9	1041.2	1042.0	1043.2	1044.4	1045.8	1047.0	1046.8	1046.7
130°	1088.4	1088.6	1088.8	1089.1	1089.7	1090.5	1091.3	1092.1	1093.0	1093.3	1093.4
132.5°	1132.6	1133.0	1133.5	1134.0	1134.8	1135.9	1136.8	1137.8	1138.9	1139.2	1139.4
135°	1197.8	1197.5	1197.3	1197.0	1197.4	1198.4	1199.6	1200.7	1201.7	1202.3	1202.9
137.5°	1256.6	1256.7	1256.9	1257.0	1257.6	1258.8	1260.0	1261.2	1262.3	1263.0	1263.6
140°	1295.2	1295.7	1296.3	1296.8	1297.4	1297.9	1298.4	1299.0	1299.6	1300.3	1301.2
142.5°	1329.8	1330.9	1331.8	1332.8	1333.4	1333.8	1334.1	1334.5	1334.7	1335.4	1336.0
145°	1382.2	1383.1	1383.9	1384.7	1385.2	1385.2	1385.2	1385.2	1385.2	1385.4	1385.6
147.5°	1424.7	1426.3	1427.9	1429.4	1430.0	1429.7	1429.5	1429.2	1428.9	1429.1	1429.4
150°	1454.7	1455.8	1456.9	1457.9	1458.3	1458.1	1457.8	1457.5	1457.3	1457.3	1457.3
152.5°	1479.9	1480.7	1481.6	1482.5	1482.7	1482.2	1481.7	1481.2	1480.7	1481.2	1481.6
155°	1514.9	1515.2	1515.5	1515.8	1515.5	1514.8	1513.9	1513.1	1512.3	1513.3	1514.5
157.5°	1544.6	1544.5	1544.3	1544.2	1543.6	1542.7	1541.7	1540.9	1539.9	1541.3	1542.8
160°	1561.6	1560.8	1559.9	1559.2	1558.6	1558.3	1558.0	1557.7	1557.6	1559.2	1560.8
162.5°	1577.0	1576.0	1575.0	1574.0	1573.3	1573.0	1572.7	1572.4	1572.2	1573.8	1575.5
165°	1596.5	1595.2	1593.7	1592.4	1591.8	1591.8	1591.8	1591.8	1591.8	1593.9	1596.1
167.5°	1612.1	1610.7	1609.3	1607.9	1607.0	1606.9	1606.8	1606.6	1606.4	1608.8	1611.2
170°	1620.7	1619.0	1617.4	1615.8	1615.1	1615.3	1615.6	1615.9	1616.2	1618.3	1620.5
172.5°	1626.5	1624.9	1623.2	1621.6	1621.0	1621.3	1621.6	1621.7	1622.0	1624.2	1626.4
175°	1632.9	1631.3	1629.7	1628.0	1627.3	1627.6	1627.9	1628.1	1628.4	1630.9	1633.3
177.5°	1636.0	1634.4	1632.9	1631.4	1630.8	1631.3	1631.7	1632.1	1632.6	1634.3	1636.1
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	553.6	553.6	553.6	553.6	553.6	553.6	553.6
2.5°	580.8	581.5	582.0	583.8	584.0	585.6	584.0
5°	628.9	632.0	636.9	641.8	642.2	645.4	639.8
7.5°	682.7	689.9	694.5	702.4	705.5	707.5	704.3
10°	719.8	726.5	738.4	744.1	750.0	750.8	748.2
12.5°	755.7	766.3	775.6	786.6	786.4	794.2	791.4
15°	803.5	814.5	827.4	839.6	844.0	844.0	847.6
17.5°	837.5	857.6	871.0	880.6	891.2	893.0	891.7
20°	860.6	882.2	896.5	909.0	916.2	918.1	918.1
22.5°	877.7	896.2	910.1	921.3	927.2	929.5	928.9
25°	889.6	905.4	913.9	917.3	918.8	918.4	914.2
27.5°	873.4	872.6	867.3	857.1	849.3	844.6	839.2
30°	842.4	830.7	817.3	802.6	783.6	769.1	764.7
32.5°	796.1	770.1	747.3	722.8	702.5	688.0	681.8
35°	706.7	665.4	631.7	602.3	580.9	567.5	563.0
37.5°	600.6	560.6	519.0	490.4	472.6	459.1	454.1
40°	533.1	489.7	453.3	426.5	408.2	395.0	394.8
42.5°	471.6	430.0	395.8	376.5	356.8	348.1	348.1
45°	386.2	352.9	323.9	308.7	296.9	289.7	287.8
47.5°	319.7	292.2	272.9	260.8	251.2	246.7	243.6
50°	282.4	258.4	242.9	232.4	227.1	221.3	220.8
52.5°	251.4	231.9	219.9	211.4	204.6	201.1	201.2
55°	211.2	195.9	187.4	180.9	175.6	172.9	171.7
57.5°	178.0	166.5	160.2	154.3	152.0	150.0	149.4
60°	157.3	149.5	143.6	138.9	135.6	135.0	134.7
62.5°	140.2	132.0	128.0	124.3	121.9	120.8	120.5
65°	115.6	109.5	105.9	103.0	102.2	100.6	100.4
67.5°	93.1	89.5	87.2	85.2	84.0	83.9	83.9
70°	79.5	77.4	75.4	74.3	73.6	73.1	73.1
72.5°	67.7	66.2	64.5	63.9	63.8	63.3	63.2
75°	51.6	50.0	50.2	49.1	48.2	47.0	46.4
77.5°	36.6	35.4	35.2	35.1	34.3	34.2	34.5
80°	28.4	27.2	27.0	27.2	27.0	26.3	26.3
82.5°	21.6	20.6	20.4	20.3	20.1	20.3	19.9
85°	11.6	11.1	11.1	11.1	11.6	11.4	11.1
87.5°	10.5	10.7	11.0	10.9	11.0	10.9	11.2
90°	31.8	33.5	34.5	35.1	35.6	36.1	36.7
92.5°	30.8	32.4	33.3	33.5	33.6	33.6	33.7
95°	31.8	33.5	34.4	34.6	34.9	35.2	35.4
97.5°	32.8	32.9	33.2	33.5	33.6	33.9	34.2
100°	40.0	35.3	33.2	33.5	33.6	33.9	34.2
102.5°	109.7	59.9	35.0	35.1	35.1	35.2	35.3
105°	388.8	391.2	387.6	377.8	368.0	358.2	348.5
107.5°	479.2	480.3	481.5	482.5	483.5	484.6	485.6
110°	540.7	541.3	542.0	542.8	543.7	544.4	545.3



TEST NUMBER: P333027-830

CATALOG NUMBER: S124RDIW-S350D1340U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	600.4	600.3	600.8	601.8	602.9	603.9	604.9
115°	691.2	691.6	691.9	691.9	691.9	691.9	691.9
117.5°	781.1	781.0	780.9	780.8	780.7	780.6	780.4
120°	837.8	838.4	838.4	837.8	837.3	836.8	836.2
122.5°	893.0	893.2	893.2	892.6	892.0	891.6	891.0
125°	970.7	971.5	972.0	972.3	972.6	972.9	973.2
127.5°	1046.5	1046.3	1046.1	1045.9	1045.7	1045.5	1045.3
130°	1093.7	1094.0	1094.2	1094.2	1094.2	1094.2	1094.2
132.5°	1139.7	1140.0	1140.0	1139.8	1139.6	1139.3	1139.2
135°	1203.3	1203.9	1204.5	1205.0	1205.5	1206.1	1206.6
137.5°	1264.1	1264.8	1265.0	1264.8	1264.7	1264.5	1264.3
140°	1302.0	1302.8	1303.3	1303.6	1303.9	1304.2	1304.5
142.5°	1336.5	1337.2	1337.5	1337.6	1337.6	1337.7	1337.7
145°	1385.9	1386.2	1386.7	1387.1	1387.7	1388.3	1388.8
147.5°	1429.6	1429.7	1430.0	1430.3	1430.6	1430.8	1431.1
150°	1457.3	1457.3	1457.4	1457.6	1457.9	1458.2	1458.5
152.5°	1482.1	1482.4	1482.6	1482.4	1482.2	1482.1	1482.0
155°	1515.5	1516.6	1516.7	1516.0	1515.1	1514.3	1513.5
157.5°	1544.2	1545.6	1545.6	1544.2	1542.8	1541.3	1539.9
160°	1562.4	1564.1	1564.1	1562.4	1560.8	1559.2	1557.6
162.5°	1577.1	1578.7	1578.6	1576.8	1574.9	1573.0	1571.2
165°	1598.3	1600.4	1600.2	1597.9	1595.4	1593.0	1590.5
167.5°	1613.5	1616.0	1615.8	1613.1	1610.3	1607.7	1605.0
170°	1622.7	1624.8	1624.6	1621.9	1619.2	1616.5	1613.7
172.5°	1628.6	1630.8	1630.4	1627.4	1624.5	1621.6	1618.6
175°	1635.8	1638.2	1637.8	1634.6	1631.3	1628.0	1624.8
177.5°	1637.8	1639.6	1639.1	1636.4	1633.9	1631.3	1628.6
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6

(END OF REPORT)