

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332469-940

Luminaire Tested: **S123RDIW-S1000D1535U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332469-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8128.3 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	38	37	35	30
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	36	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	40	34	39	34	30	32	28	25	25	23	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14
9	50	38	30	26	45	35	28	24	30	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	22	27	22	19	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16108	16108	16108
5°	16170	15946	16038
10°	16078	15746	15692
15°	15905	15377	15216
20°	15668	14917	14569
25°	15423	14400	13938
30°	15100	13803	13048
35°	14767	13205	12232
40°	14462	12500	11221
45°	14059	11805	10310
50°	13618	11015	9287
55°	13165	10113	8336
60°	12751	9145	7289
65°	12210	8099	6243
70°	11534	6801	5042
75°	10551	5352	4741
80°	9403	4736	4364
85°	7941	4199	3903



TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	140.5	1.7
10°-20°	391.0	4.8
20°-30°	563.0	6.9
30°-40°	634.1	7.8
40°-50°	606.7	7.5
50°-60°	496.8	6.1
60°-70°	335.2	4.1
70°-80°	168.6	2.1
80°-90°	49.7	0.6
90°-100°	111.5	1.4
100°-110°	333.8	4.1
110°-120°	567.7	7.0
120°-130°	746.7	9.2
130°-140°	839.3	10.3
140°-150°	825.0	10.1
150°-160°	694.5	8.5
160°-170°	462.3	5.7
170°-180°	161.9	2.0
0°-30°	1094.5	13.5
0°-40°	1728.6	21.3
0°-60°	2832.1	34.8
0°-90°	3385.7	41.7
90°-120°	1013.0	12.5
90°-150°	3423.9	42.1
90°-180°	4743.0	58.4
0°-180°	8128.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1496	1496	1496	1496	1496	
5°	1496	1490	1476	1486	1484	142
15°	1427	1413	1380	1374	1365	402
25°	1299	1267	1212	1188	1174	597
35°	1124	1078	1005	954	931	703
45°	924	867	776	709	677	712
55°	702	640	539	471	444	629
65°	479	411	318	261	245	474
75°	254	195	129	117	114	270
85°	64	39	34	32	32	72
90°	1	15	32	38	40	8
95°	79	89	100	105	105	89
105°	303	306	317	318	320	324
115°	572	575	573	574	573	565
125°	836	840	838	832	827	746
135°	1085	1093	1092	1087	1084	836
145°	1316	1319	1323	1322	1316	822
155°	1507	1507	1509	1513	1505	694
165°	1642	1638	1638	1645	1636	463
175°	1708	1703	1702	1709	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1501.3	1500.4	1499.6	1498.7	1497.8	1496.1	1493.5	1490.9	1488.4	1485.8	1488.1
5°	1496.5	1495.0	1493.7	1492.4	1491.0	1488.7	1485.5	1482.3	1479.1	1475.8	1478.2
7.5°	1482.6	1481.1	1479.7	1478.2	1476.8	1473.9	1469.7	1465.5	1461.3	1457.1	1458.5
10°	1471.0	1469.1	1467.1	1465.3	1463.4	1460.0	1455.2	1450.3	1445.5	1440.6	1440.9
12.5°	1454.5	1452.3	1450.3	1448.1	1446.0	1442.0	1436.1	1430.1	1424.2	1418.3	1418.1
15°	1427.3	1424.3	1421.3	1418.4	1415.4	1410.2	1402.6	1395.0	1387.5	1379.9	1378.6
17.5°	1393.0	1389.6	1386.2	1382.7	1379.2	1372.7	1363.1	1353.5	1343.9	1334.3	1331.4
20°	1367.8	1363.5	1359.1	1354.9	1350.5	1343.3	1333.0	1322.8	1312.5	1302.3	1298.8
22.5°	1339.6	1334.7	1329.7	1324.7	1319.8	1311.9	1300.9	1290.0	1279.2	1268.3	1263.9
25°	1298.6	1291.9	1285.1	1278.4	1271.7	1262.0	1249.6	1237.2	1224.9	1212.5	1206.8
27.5°	1248.8	1241.4	1233.9	1226.5	1219.1	1208.4	1194.6	1180.8	1167.0	1153.2	1145.3
30°	1214.9	1206.8	1198.7	1190.6	1182.5	1170.9	1155.8	1140.7	1125.6	1110.5	1101.4
32.5°	1180.9	1171.7	1162.5	1153.3	1144.2	1131.7	1115.7	1099.7	1083.7	1067.7	1057.7
35°	1123.8	1114.1	1104.4	1094.8	1085.0	1071.7	1055.1	1038.3	1021.6	1004.9	993.3
37.5°	1066.0	1055.3	1044.5	1033.7	1022.9	1008.6	990.8	972.9	955.0	937.2	924.0
40°	1029.2	1017.4	1005.4	993.5	981.7	966.2	947.1	927.9	908.7	889.6	875.6
42.5°	987.4	975.5	963.7	951.8	940.0	924.2	904.4	884.6	864.8	845.0	829.6
45°	923.6	911.4	899.3	887.2	875.0	858.6	837.9	817.1	796.3	775.5	760.2
47.5°	859.8	846.4	833.1	819.7	806.5	789.4	768.7	747.9	727.1	706.3	689.6
50°	813.2	800.5	787.8	775.2	762.4	745.2	723.4	701.5	679.7	657.8	641.1
52.5°	771.4	757.7	743.9	730.1	716.4	698.7	677.1	655.4	633.8	612.2	594.8
55°	701.5	688.3	675.0	661.8	648.6	630.5	607.6	584.7	561.8	538.9	523.3
57.5°	636.9	622.5	608.1	593.7	579.3	560.6	537.5	514.5	491.5	468.5	453.7
60°	592.3	577.5	562.6	547.8	532.9	514.3	492.0	469.6	447.2	424.8	410.2
62.5°	547.6	532.8	517.9	503.1	488.3	469.7	447.3	424.9	402.5	380.1	366.4
65°	479.4	464.6	449.7	434.9	420.1	402.2	381.1	360.1	339.0	318.0	304.8
67.5°	411.2	396.2	381.2	366.2	351.2	333.6	313.4	293.3	273.1	252.9	243.1
70°	366.5	352.0	337.4	322.8	308.3	291.6	272.7	253.8	234.9	216.1	206.6
72.5°	321.8	307.6	293.2	278.8	264.5	248.7	231.6	214.5	197.2	180.1	172.4
75°	253.7	240.7	227.7	214.8	201.9	188.0	173.2	158.3	143.5	128.7	125.9
77.5°	191.5	179.8	168.1	156.4	144.7	134.0	124.5	114.9	105.4	95.9	94.4
80°	151.7	140.6	129.6	118.5	107.5	99.2	93.5	87.7	82.1	76.4	75.6
82.5°	113.9	104.3	94.8	85.2	75.6	69.6	66.9	64.3	61.6	58.9	58.1
85°	64.3	58.4	52.4	46.5	40.6	37.2	36.4	35.6	34.8	34.0	33.4
87.5°	23.5	21.8	20.1	18.3	16.5	16.0	16.8	17.6	18.3	19.1	19.1
90°	1.3	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4
92.5°	32.5	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6
95°	79.4	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7
97.5°	140.9	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1
100°	182.9	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6
102.5°	231.3	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9
105°	302.6	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4
107.5°	385.4	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8
110°	437.0	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6



TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.8	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4
115°	571.5	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1
117.5°	652.7	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8
120°	703.3	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3
122.5°	756.0	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6
125°	836.3	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5
127.5°	910.6	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5
130°	960.1	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6
132.5°	1009.6	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9
135°	1085.1	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7
137.5°	1155.0	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0
140°	1203.5	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1247.6	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4
145°	1316.4	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9
147.5°	1376.6	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3
150°	1418.6	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0
152.5°	1453.0	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9
155°	1507.3	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9
157.5°	1553.6	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3
160°	1582.7	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4
162.5°	1608.5	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3
165°	1641.8	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6
167.5°	1668.5	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0
170°	1683.5	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3
172.5°	1695.3	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8
175°	1707.7	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1
177.5°	1712.8	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5	1496.5
2.5°	1490.5	1492.9	1495.2	1496.2	1495.8	1495.4	1495.0	1494.5
5°	1480.7	1483.1	1485.5	1486.5	1485.9	1485.4	1484.9	1484.3
7.5°	1459.8	1461.2	1462.5	1462.8	1461.8	1460.9	1460.0	1459.0
10°	1441.2	1441.5	1441.7	1441.2	1439.8	1438.4	1437.1	1435.7
12.5°	1417.9	1417.8	1417.6	1416.8	1415.2	1413.6	1412.1	1410.5
15°	1377.2	1375.9	1374.6	1372.9	1371.0	1369.1	1367.3	1365.4
17.5°	1328.6	1325.7	1322.9	1320.0	1317.2	1314.4	1311.6	1308.8
20°	1295.2	1291.7	1288.3	1284.9	1281.7	1278.4	1275.1	1271.9
22.5°	1259.5	1255.2	1250.8	1247.1	1244.1	1241.1	1238.1	1235.0
25°	1201.1	1195.4	1189.8	1185.4	1182.5	1179.6	1176.6	1173.6
27.5°	1137.5	1129.6	1121.7	1115.5	1111.0	1106.4	1101.9	1097.4
30°	1092.2	1083.0	1073.8	1067.1	1062.7	1058.5	1054.1	1049.8
32.5°	1047.7	1037.7	1027.6	1020.4	1015.8	1011.3	1006.7	1002.2
35°	981.7	970.1	958.5	950.3	945.5	940.6	935.8	930.9
37.5°	910.9	897.7	884.6	874.9	869.0	863.0	857.0	851.0
40°	861.6	847.6	833.5	823.4	817.2	811.0	804.8	798.6
42.5°	814.3	799.0	783.6	773.2	767.7	762.1	756.5	751.0
45°	744.8	729.4	714.0	703.1	696.6	690.2	683.7	677.3
47.5°	672.9	656.2	639.4	628.2	622.4	616.7	610.9	605.1
50°	624.4	607.6	590.9	579.4	573.3	567.0	560.9	554.6
52.5°	577.5	560.1	542.7	531.2	525.7	520.1	514.6	509.0
55°	507.6	492.0	476.3	465.7	460.4	455.0	449.6	444.2
57.5°	438.9	424.1	409.4	399.7	395.1	390.5	385.9	381.3
60°	395.7	381.1	366.5	357.0	352.4	347.8	343.2	338.6
62.5°	352.7	339.0	325.3	316.0	311.3	306.5	301.7	296.9
65°	291.6	278.3	265.1	257.0	254.0	251.1	248.2	245.1
67.5°	233.2	223.3	213.5	206.9	203.8	200.5	197.3	194.2
70°	197.2	187.7	178.3	172.1	169.1	166.1	163.2	160.2
72.5°	164.7	156.9	149.3	144.8	143.6	142.3	141.1	139.8
75°	123.2	120.6	117.9	116.3	115.7	115.1	114.6	114.0
77.5°	93.0	91.5	90.1	89.1	88.5	88.0	87.5	86.9
80°	74.8	74.0	73.2	72.6	72.1	71.5	70.9	70.4
82.5°	57.3	56.5	55.7	55.3	55.2	55.1	54.9	54.8
85°	32.9	32.4	31.8	31.6	31.6	31.6	31.6	31.6
87.5°	19.1	19.2	19.2	19.2	19.0	18.9	18.8	18.7
90°	34.7	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	53.5	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	101.9	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	158.5	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	199.5	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	246.8	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	393.8	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	444.8	445.9	447.2	447.5	446.8	446.3	445.7	445.1





TEST NUMBER: P332469-940

CATALOG NUMBER: S123RDIW-S1000D1535U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.8	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	704.0	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.8	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	835.4	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	912.9	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	964.4	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1014.5	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1089.5	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1162.8	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.9	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1256.2	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.5	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.4	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1511.1	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1555.6	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1583.0	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1608.7	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1641.4	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1693.6	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1705.9	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1711.4	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)