

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332450-940

Luminaire Tested: **S123RDIW-S1000D460U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332450-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D460U940-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5175.4 lumens  
Efficiency: N/A  
Efficacy: 112.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68
1	103	99	95	91	97	93	90	87	83	81	79	74	72	71	66	64	63	59
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	56	54	51
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	41	38
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	40	37	34
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33	30
7	63	51	43	37	59	49	41	36	44	38	34	40	35	31	36	32	29	27
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15259	15259	15259	15259
5°	18189	15324	13493	15324
10°	22710	15235	12191	15235
15°	26658	15081	11117	15081
20°	29751	14848	10204	14848
25°	29276	14602	9644	14602
30°	21044	14375	9066	14375
35°	14051	14082	8692	14082
40°	10352	13728	8304	13728
45°	8683	13108	7926	13108
50°	7661	12295	7398	12295
55°	6718	11365	6673	11365
60°	5983	10478	6114	10478
65°	5254	9521	5687	9521
70°	4126	8670	5196	8670
75°	3635	7573	4741	7573
80°	3161	6434	4668	6434
85°	2544	5175	4940	5175



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.4	2.7
10°-20°	435.5	8.4
20°-30°	684.2	13.2
30°-40°	713.8	13.8
40°-50°	610.9	11.8
50°-60°	465.6	9.0
60°-70°	298.4	5.8
70°-80°	143.6	2.8
80°-90°	39.5	0.8
90°-100°	19.6	0.4
100°-110°	93.4	1.8
110°-120°	224.4	4.3
120°-130°	285.8	5.5
130°-140°	305.4	5.9
140°-150°	285.5	5.5
150°-160°	230.3	4.5
160°-170°	148.7	2.9
170°-180°	51.2	1.0
0°-30°	1259.1	24.3
0°-40°	1973.0	38.1
0°-60°	3049.5	58.9
0°-90°	3531.0	68.2
90°-120°	337.5	6.5
90°-150°	1214.2	23.5
90°-180°	1644.0	31.8
0°-180°	5175.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1418	1418	1418	1418	1418	
5°	1683	1418	1249	1418	1683	174
15°	2392	1353	998	1353	2392	678
25°	2465	1230	812	1230	2465	1059
35°	1069	1072	662	1072	1069	701
45°	570	861	521	861	570	449
55°	358	606	356	606	358	324
65°	206	374	223	374	206	203
75°	87	182	114	182	87	94
85°	21	42	40	42	21	24
90°	12	0	12	0	12	6
95°	15	24	15	24	15	13
105°	18	119	18	119	18	40
115°	236	224	236	224	236	218
125°	322	316	322	316	322	288
135°	397	393	397	393	397	306
145°	458	454	458	454	458	286
155°	499	500	499	500	499	230
165°	526	527	526	527	526	148
175°	537	539	537	539	537	51
180°	539	539	539	539	539	



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1509.8	1511.7	1505.5	1504.5	1497.2	1495.2	1495.2	1485.1	1478.7	1470.5	1465.6
5°	1683.4	1693.1	1688.2	1677.3	1659.1	1654.8	1643.3	1625.1	1604.5	1579.0	1566.8
7.5°	1900.1	1913.3	1908.3	1891.4	1872.3	1856.9	1824.4	1794.2	1751.9	1714.7	1682.9
10°	2077.8	2063.9	2052.9	2036.6	2018.9	1990.4	1956.4	1909.7	1855.7	1813.2	1765.9
12.5°	2210.8	2208.5	2194.7	2177.8	2152.9	2125.8	2084.1	2027.2	1964.4	1903.1	1848.9
15°	2392.2	2395.8	2386.7	2369.1	2333.9	2286.0	2222.9	2199.2	2109.3	2042.6	1975.9
17.5°	2517.7	2516.9	2515.7	2491.4	2455.4	2421.3	2362.8	2300.5	2219.2	2125.1	2035.2
20°	2597.3	2591.2	2592.4	2565.1	2538.4	2498.9	2442.0	2351.5	2284.7	2176.1	2083.3
22.5°	2595.3	2594.1	2598.7	2589.3	2570.0	2539.8	2494.8	2418.5	2333.3	2223.7	2119.2
25°	2465.0	2460.1	2488.7	2496.5	2527.5	2532.9	2519.6	2477.7	2397.0	2284.1	2154.9
27.5°	2063.0	2060.3	2113.3	2179.5	2263.5	2328.8	2391.9	2422.4	2397.0	2316.2	2186.7
30°	1693.1	1750.2	1776.8	1872.7	1979.5	2106.9	2218.6	2324.8	2350.9	2315.7	2209.5
32.5°	1405.7	1455.5	1477.7	1560.0	1659.6	1808.8	1976.4	2126.7	2232.9	2259.9	2195.9
35°	1069.3	1069.9	1120.8	1157.3	1249.5	1403.0	1565.7	1767.1	1967.4	2119.1	2134.8
37.5°	853.2	856.2	887.1	923.4	992.6	1073.7	1216.9	1384.5	1615.8	1848.7	1985.2
40°	736.7	742.2	765.3	801.0	850.8	912.0	1023.8	1181.5	1374.5	1633.6	1845.4
42.5°	661.9	670.8	682.7	710.2	741.1	798.4	888.8	1010.7	1186.2	1431.2	1675.5
45°	570.4	575.2	584.4	597.1	625.0	665.1	725.8	807.7	953.3	1150.6	1395.1
47.5°	503.2	500.6	510.2	520.6	539.1	566.4	607.1	674.0	777.8	936.1	1143.5
50°	457.5	456.9	463.6	471.5	489.1	509.2	542.5	592.9	675.4	806.5	996.4
52.5°	414.8	417.1	421.9	431.7	444.4	460.6	490.5	526.8	597.7	710.9	869.2
55°	358.0	359.9	366.5	372.0	381.1	397.4	416.3	446.7	495.2	574.1	704.5
57.5°	310.0	309.2	315.6	316.9	327.2	340.5	355.1	378.7	413.8	472.5	560.4
60°	277.9	276.1	281.6	285.8	291.3	302.2	314.3	337.4	365.3	408.4	483.7
62.5°	248.8	248.0	252.0	256.2	260.7	270.6	280.9	298.5	320.7	357.0	416.7
65°	206.3	208.1	210.0	211.8	214.2	220.3	230.0	242.1	257.3	282.8	325.8
67.5°	162.1	164.0	164.6	168.4	173.5	177.4	183.2	194.0	204.6	226.1	250.7
70°	131.1	130.5	131.1	132.9	139.6	146.2	154.2	162.0	168.7	183.9	204.5
72.5°	112.6	111.6	113.2	113.5	116.7	118.6	123.6	131.0	139.6	149.9	164.7
75°	87.4	87.4	87.4	87.4	89.8	91.0	92.8	94.7	97.7	102.5	113.5
77.5°	64.6	64.6	65.5	66.2	66.6	67.3	68.5	70.3	71.3	73.9	78.6
80°	51.0	51.5	51.0	51.5	51.5	52.8	53.4	55.2	55.8	58.9	60.7
82.5°	38.3	38.0	38.3	39.0	39.0	40.2	40.3	41.6	41.7	43.3	45.1
85°	20.6	19.4	20.6	20.1	21.2	20.1	20.6	21.8	21.8	22.5	24.9
87.5°	7.2	8.2	7.2	7.7	7.6	8.0	7.9	7.8	8.8	8.2	8.5
90°	12.0	11.9	11.7	11.5	11.3	11.1	10.7	10.3	10.0	9.6	8.5
92.5°	13.3	13.2	13.1	13.0	12.8	12.6	11.9	11.4	10.8	10.3	9.4
95°	15.2	15.2	15.2	15.2	15.2	14.9	14.3	13.6	13.0	12.4	11.4
97.5°	16.5	16.4	16.3	16.2	16.1	15.8	15.1	14.4	13.6	12.9	19.4
100°	16.9	16.8	16.7	16.6	16.5	16.1	15.3	14.6	13.9	13.2	27.1
102.5°	17.1	16.9	16.9	16.7	16.5	17.6	19.7	21.9	24.2	26.4	41.6
105°	17.7	17.5	17.3	17.1	16.9	24.7	40.5	56.2	72.0	87.7	95.8
107.5°	55.4	67.2	79.1	91.0	102.9	114.6	126.2	137.7	149.3	160.8	159.5
110°	110.2	122.9	135.6	148.4	161.1	168.9	171.8	174.8	177.7	180.7	179.7



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	189.0	191.7	194.4	197.1	199.7	201.1	201.0	201.0	200.9	200.9	199.9
115°	235.6	235.2	234.9	234.5	234.2	233.5	232.6	231.8	230.9	230.0	229.2
117.5°	261.7	261.6	261.5	261.4	261.4	261.0	260.3	259.6	258.9	258.2	257.8
120°	279.6	279.6	279.6	279.6	279.6	279.3	278.6	277.9	277.1	276.4	276.2
122.5°	297.3	297.2	297.1	297.0	296.9	296.7	296.2	295.7	295.2	294.7	294.4
125°	322.1	321.9	321.7	321.6	321.4	321.2	321.0	320.8	320.7	320.5	320.1
127.5°	346.0	346.2	346.3	346.5	346.7	346.6	346.3	346.1	345.8	345.5	345.1
130°	361.3	361.5	361.7	361.9	362.0	361.9	361.6	361.2	360.9	360.5	360.3
132.5°	375.5	375.7	375.9	376.2	376.5	376.4	376.0	375.7	375.3	375.0	374.7
135°	397.0	397.3	397.5	397.8	398.1	398.1	397.8	397.5	397.3	397.0	396.6
137.5°	417.3	417.5	417.7	417.9	418.0	417.9	417.4	417.1	416.6	416.2	416.0
140°	429.4	429.6	429.8	430.0	430.2	430.1	429.7	429.4	429.0	428.6	428.4
142.5°	440.7	441.0	441.2	441.4	441.7	441.7	441.4	441.1	440.8	440.5	440.2
145°	457.9	457.9	457.9	457.9	457.9	457.8	457.6	457.4	457.3	457.1	456.9
147.5°	470.7	471.2	471.5	472.0	472.3	472.5	472.3	472.2	472.0	471.8	471.6
150°	480.4	480.6	480.9	481.2	481.4	481.4	481.3	481.1	480.9	480.7	480.5
152.5°	488.0	488.5	488.8	489.3	489.6	489.7	489.4	489.1	488.7	488.5	488.3
155°	498.8	499.3	499.8	500.3	500.9	501.0	500.5	500.1	499.6	499.2	499.1
157.5°	507.8	508.5	509.3	509.9	510.6	510.7	510.1	509.6	509.1	508.5	508.6
160°	513.6	514.2	514.9	515.5	516.1	516.1	515.6	515.1	514.5	514.0	514.1
162.5°	519.1	519.6	520.1	520.7	521.3	521.2	520.7	520.0	519.4	518.8	518.9
165°	525.7	526.3	526.9	527.4	528.1	528.1	527.4	526.6	525.9	525.2	525.3
167.5°	530.4	531.1	531.8	532.4	533.2	533.2	532.4	531.8	531.1	530.4	530.4
170°	533.2	534.0	534.7	535.4	536.1	536.1	535.4	534.7	534.0	533.2	533.2
172.5°	534.8	535.7	536.4	537.2	538.0	538.0	537.3	536.5	535.8	535.1	535.1
175°	537.3	538.0	538.7	539.4	540.1	540.1	539.5	538.9	538.2	537.6	537.5
177.5°	538.0	538.7	539.4	540.1	540.8	540.9	540.3	539.8	539.1	538.6	538.5
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1463.7	1462.2	1455.5	1447.7	1437.4	1430.7	1425.3	1422.5	1413.7	1403.0	1395.7
5°	1554.1	1535.9	1516.5	1492.8	1471.0	1448.5	1434.6	1418.2	1398.1	1375.7	1359.9
7.5°	1651.0	1615.2	1576.8	1537.1	1497.9	1462.8	1431.6	1405.1	1373.1	1341.0	1318.4
10°	1725.3	1673.0	1619.1	1563.8	1513.4	1466.2	1429.7	1393.9	1355.7	1318.7	1290.8
12.5°	1792.7	1724.0	1661.8	1593.9	1529.5	1472.9	1420.5	1378.4	1332.4	1292.9	1261.1
15°	1878.1	1807.8	1732.5	1629.3	1543.8	1472.2	1408.5	1353.3	1297.4	1248.8	1217.9
17.5°	1958.0	1852.1	1751.0	1664.9	1553.7	1464.3	1386.5	1320.4	1259.2	1207.7	1169.7
20°	1991.0	1888.5	1778.6	1668.8	1559.6	1459.5	1369.0	1296.2	1232.5	1174.2	1139.1
22.5°	2010.9	1894.8	1779.1	1661.1	1545.0	1441.0	1351.6	1271.5	1202.4	1147.0	1103.6
25°	2034.1	1895.8	1768.4	1651.8	1533.5	1420.6	1314.4	1229.5	1154.9	1095.9	1049.8
27.5°	2049.4	1886.7	1736.1	1606.5	1486.5	1374.1	1276.8	1186.7	1111.0	1048.7	999.3
30°	2052.4	1879.4	1711.3	1571.1	1449.1	1345.9	1242.8	1156.6	1076.6	1010.4	964.3
32.5°	2056.2	1861.4	1677.8	1528.8	1404.0	1301.8	1208.4	1126.1	1044.0	978.8	931.7
35°	2040.2	1851.5	1626.9	1455.8	1330.8	1231.9	1147.5	1071.7	991.0	927.8	879.9
37.5°	1971.2	1812.0	1574.2	1373.5	1242.8	1151.2	1082.4	1016.4	942.3	874.2	829.0
40°	1901.8	1773.2	1533.5	1323.5	1187.0	1092.9	1031.0	977.0	905.4	841.7	793.2
42.5°	1798.4	1720.3	1494.7	1271.0	1123.8	1033.2	981.0	930.4	867.5	802.8	757.2
45°	1608.7	1619.1	1415.1	1187.6	1036.4	945.5	896.3	861.1	805.3	751.9	705.2
47.5°	1370.8	1467.3	1321.8	1098.6	944.3	858.9	815.9	785.2	747.6	695.2	652.6
50°	1215.5	1353.3	1247.1	1038.9	886.6	801.6	759.1	734.2	701.5	660.2	619.6
52.5°	1072.3	1220.2	1156.7	972.4	823.9	746.3	704.8	684.3	658.3	619.5	582.6
55°	874.4	1024.3	1009.8	872.0	730.0	660.2	628.7	605.6	588.0	558.9	529.8
57.5°	707.3	849.4	856.9	760.4	647.3	578.3	551.2	533.8	522.3	500.2	473.3
60°	602.0	732.5	758.0	685.1	588.0	527.4	500.6	486.7	477.6	459.9	439.3
62.5°	514.6	625.6	654.5	602.1	531.2	474.4	453.5	440.1	433.9	418.7	400.6
65°	393.9	486.1	514.0	484.8	447.8	402.3	385.3	373.8	368.4	359.9	346.5
67.5°	296.1	363.4	394.0	373.4	360.1	331.4	320.6	314.3	309.5	303.6	292.5
70°	237.9	287.7	319.2	313.7	302.8	287.7	279.7	275.5	270.6	265.8	256.1
72.5°	191.3	225.5	255.1	257.9	249.0	245.9	239.0	237.2	234.3	228.5	223.1
75°	126.8	150.5	171.1	179.1	182.6	185.7	182.6	182.1	181.5	176.6	173.5
77.5°	83.1	95.9	108.9	122.3	128.0	132.2	133.1	135.4	133.8	131.2	129.7
80°	63.8	66.8	75.9	87.4	96.5	100.1	102.5	103.8	103.2	102.5	100.1
82.5°	46.3	48.8	53.1	61.2	68.8	74.9	76.3	76.1	77.4	77.8	75.9
85°	24.9	25.5	26.7	27.9	32.2	38.9	40.7	41.9	43.1	43.1	39.4
87.5°	9.2	8.5	9.3	9.0	10.3	10.6	13.4	15.6	16.3	14.5	14.7
90°	7.3	6.2	5.0	3.9	3.0	2.1	1.2	0.4	1.2	2.1	3.0
92.5°	8.5	7.7	6.8	6.4	6.7	7.0	7.2	7.5	7.2	7.0	6.7
95°	10.4	9.5	8.5	9.8	13.5	17.1	20.8	24.4	20.8	17.1	13.5
97.5°	25.7	32.1	38.5	42.5	44.2	45.8	47.4	49.1	47.4	45.8	44.2
100°	41.0	54.9	68.8	74.8	73.0	71.2	69.5	67.7	69.5	71.2	73.0
102.5°	56.7	71.9	87.0	94.0	92.7	91.4	90.2	88.8	90.2	91.4	92.7
105°	103.8	111.7	119.8	123.3	122.3	121.4	120.4	119.4	120.4	121.4	122.3
107.5°	158.3	157.0	155.8	154.7	153.9	153.2	152.4	151.6	152.4	153.2	153.9
110°	178.7	177.7	176.7	175.9	175.2	174.5	173.8	173.1	173.8	174.5	175.2





TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	198.9	198.0	197.0	196.2	195.5	194.8	194.2	193.6	194.2	194.8	195.5
115°	228.4	227.6	226.8	226.0	225.5	225.0	224.4	223.9	224.4	225.0	225.5
117.5°	257.3	256.9	256.5	256.0	255.3	254.7	254.0	253.3	254.0	254.7	255.3
120°	275.9	275.6	275.4	274.8	274.0	273.2	272.4	271.6	272.4	273.2	274.0
122.5°	294.0	293.7	293.4	292.8	292.2	291.5	290.9	290.3	290.9	291.5	292.2
125°	319.8	319.4	319.1	318.5	317.8	317.1	316.4	315.7	316.4	317.1	317.8
127.5°	344.6	344.2	343.8	343.2	342.5	341.8	341.1	340.4	341.1	341.8	342.5
130°	359.9	359.5	359.2	358.6	357.9	357.2	356.5	355.8	356.5	357.2	357.9
132.5°	374.4	374.2	373.8	373.4	372.6	371.9	371.2	370.5	371.2	371.9	372.6
135°	396.3	395.9	395.6	395.1	394.6	394.0	393.5	393.0	393.5	394.0	394.6
137.5°	415.8	415.6	415.4	414.9	414.3	413.6	413.0	412.2	413.0	413.6	414.3
140°	428.1	427.8	427.6	427.2	426.7	426.1	425.6	425.1	425.6	426.1	426.7
142.5°	440.0	439.7	439.4	439.1	438.5	438.0	437.5	436.9	437.5	438.0	438.5
145°	456.7	456.6	456.4	456.0	455.4	454.8	454.1	453.5	454.1	454.8	455.4
147.5°	471.4	471.3	471.1	470.7	470.4	469.9	469.6	469.1	469.6	469.9	470.4
150°	480.4	480.2	480.0	479.8	479.6	479.3	479.0	478.8	479.0	479.3	479.6
152.5°	488.2	488.1	488.0	487.9	487.8	487.7	487.5	487.4	487.5	487.7	487.8
155°	499.0	498.9	498.8	498.9	499.1	499.2	499.4	499.5	499.4	499.2	499.1
157.5°	508.7	508.8	508.9	509.0	509.0	509.0	509.0	509.1	509.0	509.0	509.0
160°	514.2	514.2	514.3	514.4	514.5	514.6	514.7	514.8	514.7	514.6	514.5
162.5°	519.0	519.1	519.2	519.3	519.6	519.8	520.0	520.2	520.0	519.8	519.6
165°	525.4	525.5	525.6	525.8	526.0	526.3	526.6	526.8	526.6	526.3	526.0
167.5°	530.4	530.4	530.4	530.6	530.9	531.3	531.6	532.0	531.6	531.3	530.9
170°	533.2	533.2	533.2	533.4	533.8	534.1	534.5	534.8	534.5	534.1	533.8
172.5°	535.0	534.9	534.8	535.0	535.5	535.9	536.4	536.7	536.4	535.9	535.5
175°	537.4	537.3	537.3	537.4	537.9	538.3	538.8	539.2	538.8	538.3	537.9
177.5°	538.4	538.4	538.3	538.4	538.8	539.1	539.5	539.8	539.5	539.1	538.8
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1393.3	1387.0	1382.6	1372.9	1366.6	1359.8	1353.0	1357.4	1356.9	1356.4	1356.4
5°	1346.6	1332.6	1319.9	1303.5	1293.2	1280.4	1270.7	1269.5	1271.9	1263.5	1258.6
7.5°	1300.2	1281.1	1263.1	1245.0	1225.8	1210.5	1201.0	1196.4	1190.3	1185.0	1179.6
10°	1267.7	1245.3	1227.6	1205.1	1184.5	1166.4	1154.9	1146.9	1142.6	1138.4	1130.5
12.5°	1234.2	1212.2	1189.8	1164.4	1144.8	1123.6	1115.0	1106.2	1098.1	1093.2	1082.4
15°	1185.2	1156.6	1133.0	1106.3	1084.4	1063.8	1051.7	1034.0	1031.6	1025.6	1014.7
17.5°	1136.0	1105.0	1072.4	1052.7	1028.0	1006.5	988.0	982.1	964.7	958.2	948.7
20°	1097.2	1068.6	1043.7	1017.7	981.9	961.8	947.3	939.4	925.4	916.9	910.9
22.5°	1063.6	1034.7	1005.9	975.4	945.9	923.5	912.8	900.5	892.9	881.0	874.4
25°	1015.8	984.3	949.7	916.9	895.7	878.7	861.7	850.8	839.9	834.4	822.2
27.5°	960.3	927.3	894.9	870.0	844.0	827.2	811.8	802.1	789.0	779.8	773.1
30°	929.7	890.8	862.9	840.4	807.1	791.3	779.8	767.7	758.0	748.2	741.5
32.5°	894.2	858.8	832.3	804.6	778.9	761.7	746.8	736.1	727.8	718.6	711.9
35°	838.7	809.0	781.6	753.7	734.9	717.3	699.7	690.5	682.7	674.2	668.2
37.5°	788.4	760.6	734.7	708.2	684.8	670.6	656.4	649.4	638.7	633.0	626.9
40°	757.3	730.0	702.1	676.6	652.4	641.4	628.7	618.4	608.7	604.4	597.7
42.5°	723.4	696.1	672.5	645.1	625.2	610.4	598.6	587.3	580.1	573.8	570.1
45°	673.0	648.7	625.6	598.3	579.5	566.8	553.4	543.1	536.5	532.2	525.5
47.5°	624.1	599.8	576.4	552.6	534.4	519.8	506.5	499.3	490.4	485.3	480.7
50°	588.6	566.8	541.9	520.0	501.9	487.3	476.4	467.3	459.4	452.7	449.7
52.5°	556.1	532.8	511.3	491.0	471.7	455.2	445.3	435.7	429.8	422.1	418.6
55°	502.5	480.0	461.8	441.8	422.9	409.0	396.9	388.3	382.3	373.8	369.0
57.5°	452.1	431.9	410.2	392.9	373.4	361.7	351.6	340.1	332.7	326.0	321.3
60°	418.1	395.0	376.2	359.9	342.9	327.7	318.6	309.5	301.6	294.9	290.7
62.5°	382.6	362.6	344.6	326.8	311.3	298.1	287.5	279.9	273.0	268.7	264.5
65°	328.3	312.5	294.4	279.7	265.2	255.5	247.0	240.3	235.4	232.4	228.8
67.5°	278.3	263.0	247.1	232.8	223.1	215.7	210.1	204.4	202.0	198.0	195.6
70°	245.8	230.0	216.1	205.1	195.4	189.9	186.3	182.1	179.6	174.8	172.4
72.5°	210.4	198.9	188.9	179.9	172.1	167.1	162.5	157.3	153.4	148.0	145.6
75°	165.7	155.3	147.5	141.4	136.5	129.8	123.1	117.7	115.9	114.0	113.5
77.5°	122.7	116.2	110.5	105.3	99.2	94.4	93.0	91.8	91.4	90.4	90.4
80°	96.5	90.4	86.1	80.1	76.4	76.4	76.4	75.3	75.9	75.9	75.9
82.5°	71.7	66.2	63.8	61.6	60.9	61.4	61.4	61.6	61.3	62.2	61.8
85°	37.0	37.6	38.9	38.3	38.9	38.9	40.0	39.4	40.0	38.9	40.0
87.5°	14.4	16.1	16.8	17.5	18.2	17.9	18.5	18.5	19.2	19.2	19.3
90°	3.9	5.0	6.2	7.3	8.5	9.6	10.0	10.3	10.7	11.1	11.3
92.5°	6.4	6.8	7.7	8.5	9.4	10.3	10.8	11.4	11.9	12.6	12.8
95°	9.8	8.5	9.5	10.4	11.4	12.4	13.0	13.6	14.3	14.9	15.2
97.5°	42.5	38.5	32.1	25.7	19.4	12.9	13.6	14.4	15.1	15.8	16.1
100°	74.8	68.8	54.9	41.0	27.1	13.2	13.9	14.6	15.3	16.1	16.5
102.5°	94.0	87.0	71.9	56.7	41.6	26.4	24.2	21.9	19.7	17.6	16.5
105°	123.3	119.8	111.7	103.8	95.8	87.7	72.0	56.2	40.5	24.7	16.9
107.5°	154.7	155.8	157.0	158.3	159.5	160.8	149.3	137.7	126.2	114.6	102.9
110°	175.9	176.7	177.7	178.7	179.7	180.7	177.7	174.8	171.8	168.9	161.1



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	196.2	197.0	198.0	198.9	199.9	200.9	200.9	201.0	201.0	201.1	199.7
115°	226.0	226.8	227.6	228.4	229.2	230.0	230.9	231.8	232.6	233.5	234.2
117.5°	256.0	256.5	256.9	257.3	257.8	258.2	258.9	259.6	260.3	261.0	261.4
120°	274.8	275.4	275.6	275.9	276.2	276.4	277.1	277.9	278.6	279.3	279.6
122.5°	292.8	293.4	293.7	294.0	294.4	294.7	295.2	295.7	296.2	296.7	296.9
125°	318.5	319.1	319.4	319.8	320.1	320.5	320.7	320.8	321.0	321.2	321.4
127.5°	343.2	343.8	344.2	344.6	345.1	345.5	345.8	346.1	346.3	346.6	346.7
130°	358.6	359.2	359.5	359.9	360.3	360.5	360.9	361.2	361.6	361.9	362.0
132.5°	373.4	373.8	374.2	374.4	374.7	375.0	375.3	375.7	376.0	376.4	376.5
135°	395.1	395.6	395.9	396.3	396.6	397.0	397.3	397.5	397.8	398.1	398.1
137.5°	414.9	415.4	415.6	415.8	416.0	416.2	416.6	417.1	417.4	417.9	418.0
140°	427.2	427.6	427.8	428.1	428.4	428.6	429.0	429.4	429.7	430.1	430.2
142.5°	439.1	439.4	439.7	440.0	440.2	440.5	440.8	441.1	441.4	441.7	441.7
145°	456.0	456.4	456.6	456.7	456.9	457.1	457.3	457.4	457.6	457.8	457.9
147.5°	470.7	471.1	471.3	471.4	471.6	471.8	472.0	472.2	472.3	472.5	472.3
150°	479.8	480.0	480.2	480.4	480.5	480.7	480.9	481.1	481.3	481.4	481.4
152.5°	487.9	488.0	488.1	488.2	488.3	488.5	488.7	489.1	489.4	489.7	489.6
155°	498.9	498.8	498.9	499.0	499.1	499.2	499.6	500.1	500.5	501.0	500.9
157.5°	509.0	508.9	508.8	508.7	508.6	508.5	509.1	509.6	510.1	510.7	510.6
160°	514.4	514.3	514.2	514.2	514.1	514.0	514.5	515.1	515.6	516.1	516.1
162.5°	519.3	519.2	519.1	519.0	518.9	518.8	519.4	520.0	520.7	521.2	521.3
165°	525.8	525.6	525.5	525.4	525.3	525.2	525.9	526.6	527.4	528.1	528.1
167.5°	530.6	530.4	530.4	530.4	530.4	530.4	531.1	531.8	532.4	533.2	533.2
170°	533.4	533.2	533.2	533.2	533.2	533.2	534.0	534.7	535.4	536.1	536.1
172.5°	535.0	534.8	534.9	535.0	535.1	535.1	535.8	536.5	537.3	538.0	538.0
175°	537.4	537.3	537.3	537.4	537.5	537.6	538.2	538.9	539.5	540.1	540.1
177.5°	538.4	538.3	538.4	538.4	538.5	538.6	539.1	539.8	540.3	540.9	540.8
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1350.6	1350.1	1350.6	1348.6	1350.6	1350.1	1350.6	1356.4	1356.4	1356.9	1357.4
5°	1256.8	1256.2	1254.4	1248.8	1254.4	1256.2	1256.8	1258.6	1263.5	1271.9	1269.5
7.5°	1174.8	1174.0	1168.7	1168.8	1168.7	1174.0	1174.8	1179.6	1185.0	1190.3	1196.4
10°	1126.3	1126.9	1119.6	1115.4	1119.6	1126.9	1126.3	1130.5	1138.4	1142.6	1146.9
12.5°	1079.2	1076.4	1070.6	1065.9	1070.6	1076.4	1079.2	1082.4	1093.2	1098.1	1106.2
15°	1017.1	1011.0	996.4	997.6	996.4	1011.0	1017.1	1014.7	1025.6	1031.6	1034.0
17.5°	943.9	939.4	939.1	930.7	939.1	939.4	943.9	948.7	958.2	964.7	982.1
20°	901.2	898.1	899.3	890.8	899.3	898.1	901.2	910.9	916.9	925.4	939.4
22.5°	867.6	864.6	859.5	856.8	859.5	864.6	867.6	874.4	881.0	892.9	900.5
25°	818.6	813.8	809.0	812.0	809.0	813.8	818.6	822.2	834.4	839.9	850.8
27.5°	769.6	766.0	761.1	760.5	761.1	766.0	769.6	773.1	779.8	789.0	802.1
30°	738.5	734.9	732.5	729.4	732.5	734.9	738.5	741.5	748.2	758.0	767.7
32.5°	706.9	706.2	701.9	701.2	701.9	706.2	706.9	711.9	718.6	727.8	736.1
35°	665.7	662.1	660.8	661.5	660.8	662.1	665.7	668.2	674.2	682.7	690.5
37.5°	626.5	621.6	619.5	617.2	619.5	621.6	626.5	626.9	633.0	638.7	649.4
40°	598.3	593.5	592.3	591.0	592.3	593.5	598.3	597.7	604.4	608.7	618.4
42.5°	566.8	564.8	564.1	562.0	564.1	564.8	566.8	570.1	573.8	580.1	587.3
45°	523.7	523.1	519.4	520.7	519.4	523.1	523.7	525.5	532.2	536.5	543.1
47.5°	478.3	475.6	473.1	474.7	473.1	475.6	478.3	480.7	485.3	490.4	499.3
50°	447.3	446.0	440.6	441.8	440.6	446.0	447.3	449.7	452.7	459.4	467.3
52.5°	416.2	411.5	409.5	408.8	409.5	411.5	416.2	418.6	422.1	429.8	435.7
55°	364.7	359.3	356.9	355.6	356.9	359.3	364.7	369.0	373.8	382.3	388.3
57.5°	314.2	312.7	310.9	312.2	310.9	312.7	314.2	321.3	326.0	332.7	340.1
60°	284.6	284.6	284.6	284.0	284.6	284.6	284.6	290.7	294.9	301.6	309.5
62.5°	261.8	260.3	259.8	260.7	259.8	260.3	261.8	264.5	268.7	273.0	279.9
65°	226.9	226.3	223.9	223.3	223.9	226.3	226.9	228.8	232.4	235.4	240.3
67.5°	194.0	191.9	191.2	190.3	191.2	191.9	194.0	195.6	198.0	202.0	204.4
70°	169.3	168.1	164.4	165.1	164.4	168.1	169.3	172.4	174.8	179.6	182.1
72.5°	142.6	141.4	140.6	139.8	140.6	141.4	142.6	145.6	148.0	153.4	157.3
75°	112.9	112.3	111.6	114.0	111.6	112.3	112.9	113.5	114.0	115.9	117.7
77.5°	90.4	90.4	90.8	89.8	90.8	90.4	90.4	90.4	90.4	91.4	91.8
80°	75.9	75.9	75.3	75.3	75.3	75.9	75.9	75.9	75.9	75.9	75.3
82.5°	60.8	61.3	61.6	60.7	61.6	61.3	60.8	61.8	62.2	61.3	61.6
85°	40.0	39.4	40.7	40.0	40.7	39.4	40.0	40.0	38.9	40.0	39.4
87.5°	20.2	19.4	19.4	19.9	19.4	19.4	20.2	19.3	19.2	19.2	18.5
90°	11.5	11.7	11.9	12.0	11.9	11.7	11.5	11.3	11.1	10.7	10.3
92.5°	13.0	13.1	13.2	13.3	13.2	13.1	13.0	12.8	12.6	11.9	11.4
95°	15.2	15.2	15.2	15.2	15.2	15.2	15.2	15.2	14.9	14.3	13.6
97.5°	16.2	16.3	16.4	16.5	16.4	16.3	16.2	16.1	15.8	15.1	14.4
100°	16.6	16.7	16.8	16.9	16.8	16.7	16.6	16.5	16.1	15.3	14.6
102.5°	16.7	16.9	16.9	17.1	16.9	16.9	16.7	16.5	17.6	19.7	21.9
105°	17.1	17.3	17.5	17.7	17.5	17.3	17.1	16.9	24.7	40.5	56.2
107.5°	91.0	79.1	67.2	55.4	67.2	79.1	91.0	102.9	114.6	126.2	137.7
110°	148.4	135.6	122.9	110.2	122.9	135.6	148.4	161.1	168.9	171.8	174.8



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	197.1	194.4	191.7	189.0	191.7	194.4	197.1	199.7	201.1	201.0	201.0
115°	234.5	234.9	235.2	235.6	235.2	234.9	234.5	234.2	233.5	232.6	231.8
117.5°	261.4	261.5	261.6	261.7	261.6	261.5	261.4	261.4	261.0	260.3	259.6
120°	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.6	279.3	278.6	277.9
122.5°	297.0	297.1	297.2	297.3	297.2	297.1	297.0	296.9	296.7	296.2	295.7
125°	321.6	321.7	321.9	322.1	321.9	321.7	321.6	321.4	321.2	321.0	320.8
127.5°	346.5	346.3	346.2	346.0	346.2	346.3	346.5	346.7	346.6	346.3	346.1
130°	361.9	361.7	361.5	361.3	361.5	361.7	361.9	362.0	361.9	361.6	361.2
132.5°	376.2	375.9	375.7	375.5	375.7	375.9	376.2	376.5	376.4	376.0	375.7
135°	397.8	397.5	397.3	397.0	397.3	397.5	397.8	398.1	398.1	397.8	397.5
137.5°	417.9	417.7	417.5	417.3	417.5	417.7	417.9	418.0	417.9	417.4	417.1
140°	430.0	429.8	429.6	429.4	429.6	429.8	430.0	430.2	430.1	429.7	429.4
142.5°	441.4	441.2	441.0	440.7	441.0	441.2	441.4	441.7	441.7	441.4	441.1
145°	457.9	457.9	457.9	457.9	457.9	457.9	457.9	457.9	457.8	457.6	457.4
147.5°	472.0	471.5	471.2	470.7	471.2	471.5	472.0	472.3	472.5	472.3	472.2
150°	481.2	480.9	480.6	480.4	480.6	480.9	481.2	481.4	481.4	481.3	481.1
152.5°	489.3	488.8	488.5	488.0	488.5	488.8	489.3	489.6	489.7	489.4	489.1
155°	500.3	499.8	499.3	498.8	499.3	499.8	500.3	500.9	501.0	500.5	500.1
157.5°	509.9	509.3	508.5	507.8	508.5	509.3	509.9	510.6	510.7	510.1	509.6
160°	515.5	514.9	514.2	513.6	514.2	514.9	515.5	516.1	516.1	515.6	515.1
162.5°	520.7	520.1	519.6	519.1	519.6	520.1	520.7	521.3	521.2	520.7	520.0
165°	527.4	526.9	526.3	525.7	526.3	526.9	527.4	528.1	528.1	527.4	526.6
167.5°	532.4	531.8	531.1	530.4	531.1	531.8	532.4	533.2	533.2	532.4	531.8
170°	535.4	534.7	534.0	533.2	534.0	534.7	535.4	536.1	536.1	535.4	534.7
172.5°	537.2	536.4	535.7	534.8	535.7	536.4	537.2	538.0	538.0	537.3	536.5
175°	539.4	538.7	538.0	537.3	538.0	538.7	539.4	540.1	540.1	539.5	538.9
177.5°	540.1	539.4	538.7	538.0	538.7	539.4	540.1	540.8	540.9	540.3	539.8
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1353.0	1359.8	1366.6	1372.9	1382.6	1387.0	1393.3	1395.7	1403.0	1413.7	1422.5
5°	1270.7	1280.4	1293.2	1303.5	1319.9	1332.6	1346.6	1359.9	1375.7	1398.1	1418.2
7.5°	1201.0	1210.5	1225.8	1245.0	1263.1	1281.1	1300.2	1318.4	1341.0	1373.1	1405.1
10°	1154.9	1166.4	1184.5	1205.1	1227.6	1245.3	1267.7	1290.8	1318.7	1355.7	1393.9
12.5°	1115.0	1123.6	1144.8	1164.4	1189.8	1212.2	1234.2	1261.1	1292.9	1332.4	1378.4
15°	1051.7	1063.8	1084.4	1106.3	1133.0	1156.6	1185.2	1217.9	1248.8	1297.4	1353.3
17.5°	988.0	1006.5	1028.0	1052.7	1072.4	1105.0	1136.0	1169.7	1207.7	1259.2	1320.4
20°	947.3	961.8	981.9	1017.7	1043.7	1068.6	1097.2	1139.1	1174.2	1232.5	1296.2
22.5°	912.8	923.5	945.9	975.4	1005.9	1034.7	1063.6	1103.6	1147.0	1202.4	1271.5
25°	861.7	878.7	895.7	916.9	949.7	984.3	1015.8	1049.8	1095.9	1154.9	1229.5
27.5°	811.8	827.2	844.0	870.0	894.9	927.3	960.3	999.3	1048.7	1111.0	1186.7
30°	779.8	791.3	807.1	840.4	862.9	890.8	929.7	964.3	1010.4	1076.6	1156.6
32.5°	746.8	761.7	778.9	804.6	832.3	858.8	894.2	931.7	978.8	1044.0	1126.1
35°	699.7	717.3	734.9	753.7	781.6	809.0	838.7	879.9	927.8	991.0	1071.7
37.5°	656.4	670.6	684.8	708.2	734.7	760.6	788.4	829.0	874.2	942.3	1016.4
40°	628.7	641.4	652.4	676.6	702.1	730.0	757.3	793.2	841.7	905.4	977.0
42.5°	598.6	610.4	625.2	645.1	672.5	696.1	723.4	757.2	802.8	867.5	930.4
45°	553.4	566.8	579.5	598.3	625.6	648.7	673.0	705.2	751.9	805.3	861.1
47.5°	506.5	519.8	534.4	552.6	576.4	599.8	624.1	652.6	695.2	747.6	785.2
50°	476.4	487.3	501.9	520.0	541.9	566.8	588.6	619.6	660.2	701.5	734.2
52.5°	445.3	455.2	471.7	491.0	511.3	532.8	556.1	582.6	619.5	658.3	684.3
55°	396.9	409.0	422.9	441.8	461.8	480.0	502.5	529.8	558.9	588.0	605.6
57.5°	351.6	361.7	373.4	392.9	410.2	431.9	452.1	473.3	500.2	522.3	533.8
60°	318.6	327.7	342.9	359.9	376.2	395.0	418.1	439.3	459.9	477.6	486.7
62.5°	287.5	298.1	311.3	326.8	344.6	362.6	382.6	400.6	418.7	433.9	440.1
65°	247.0	255.5	265.2	279.7	294.4	312.5	328.3	346.5	359.9	368.4	373.8
67.5°	210.1	215.7	223.1	232.8	247.1	263.0	278.3	292.5	303.6	309.5	314.3
70°	186.3	189.9	195.4	205.1	216.1	230.0	245.8	256.1	265.8	270.6	275.5
72.5°	162.5	167.1	172.1	179.9	188.9	198.9	210.4	223.1	228.5	234.3	237.2
75°	123.1	129.8	136.5	141.4	147.5	155.3	165.7	173.5	176.6	181.5	182.1
77.5°	93.0	94.4	99.2	105.3	110.5	116.2	122.7	129.7	131.2	133.8	135.4
80°	76.4	76.4	76.4	80.1	86.1	90.4	96.5	100.1	102.5	103.2	103.8
82.5°	61.4	61.4	60.9	61.6	63.8	66.2	71.7	75.9	77.8	77.4	76.1
85°	40.0	38.9	38.9	38.3	38.9	37.6	37.0	39.4	43.1	43.1	41.9
87.5°	18.5	17.9	18.2	17.5	16.8	16.1	14.4	14.7	14.5	16.3	15.6
90°	10.0	9.6	8.5	7.3	6.2	5.0	3.9	3.0	2.1	1.2	0.4
92.5°	10.8	10.3	9.4	8.5	7.7	6.8	6.4	6.7	7.0	7.2	7.5
95°	13.0	12.4	11.4	10.4	9.5	8.5	9.8	13.5	17.1	20.8	24.4
97.5°	13.6	12.9	19.4	25.7	32.1	38.5	42.5	44.2	45.8	47.4	49.1
100°	13.9	13.2	27.1	41.0	54.9	68.8	74.8	73.0	71.2	69.5	67.7
102.5°	24.2	26.4	41.6	56.7	71.9	87.0	94.0	92.7	91.4	90.2	88.8
105°	72.0	87.7	95.8	103.8	111.7	119.8	123.3	122.3	121.4	120.4	119.4
107.5°	149.3	160.8	159.5	158.3	157.0	155.8	154.7	153.9	153.2	152.4	151.6
110°	177.7	180.7	179.7	178.7	177.7	176.7	175.9	175.2	174.5	173.8	173.1



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	200.9	200.9	199.9	198.9	198.0	197.0	196.2	195.5	194.8	194.2	193.6
115°	230.9	230.0	229.2	228.4	227.6	226.8	226.0	225.5	225.0	224.4	223.9
117.5°	258.9	258.2	257.8	257.3	256.9	256.5	256.0	255.3	254.7	254.0	253.3
120°	277.1	276.4	276.2	275.9	275.6	275.4	274.8	274.0	273.2	272.4	271.6
122.5°	295.2	294.7	294.4	294.0	293.7	293.4	292.8	292.2	291.5	290.9	290.3
125°	320.7	320.5	320.1	319.8	319.4	319.1	318.5	317.8	317.1	316.4	315.7
127.5°	345.8	345.5	345.1	344.6	344.2	343.8	343.2	342.5	341.8	341.1	340.4
130°	360.9	360.5	360.3	359.9	359.5	359.2	358.6	357.9	357.2	356.5	355.8
132.5°	375.3	375.0	374.7	374.4	374.2	373.8	373.4	372.6	371.9	371.2	370.5
135°	397.3	397.0	396.6	396.3	395.9	395.6	395.1	394.6	394.0	393.5	393.0
137.5°	416.6	416.2	416.0	415.8	415.6	415.4	414.9	414.3	413.6	413.0	412.2
140°	429.0	428.6	428.4	428.1	427.8	427.6	427.2	426.7	426.1	425.6	425.1
142.5°	440.8	440.5	440.2	440.0	439.7	439.4	439.1	438.5	438.0	437.5	436.9
145°	457.3	457.1	456.9	456.7	456.6	456.4	456.0	455.4	454.8	454.1	453.5
147.5°	472.0	471.8	471.6	471.4	471.3	471.1	470.7	470.4	469.9	469.6	469.1
150°	480.9	480.7	480.5	480.4	480.2	480.0	479.8	479.6	479.3	479.0	478.8
152.5°	488.7	488.5	488.3	488.2	488.1	488.0	487.9	487.8	487.7	487.5	487.4
155°	499.6	499.2	499.1	499.0	498.9	498.8	498.9	499.1	499.2	499.4	499.5
157.5°	509.1	508.5	508.6	508.7	508.8	508.9	509.0	509.0	509.0	509.0	509.1
160°	514.5	514.0	514.1	514.2	514.2	514.3	514.4	514.5	514.6	514.7	514.8
162.5°	519.4	518.8	518.9	519.0	519.1	519.2	519.3	519.6	519.8	520.0	520.2
165°	525.9	525.2	525.3	525.4	525.5	525.6	525.8	526.0	526.3	526.6	526.8
167.5°	531.1	530.4	530.4	530.4	530.4	530.4	530.6	530.9	531.3	531.6	532.0
170°	534.0	533.2	533.2	533.2	533.2	533.2	533.4	533.8	534.1	534.5	534.8
172.5°	535.8	535.1	535.1	535.0	534.9	534.8	535.0	535.5	535.9	536.4	536.7
175°	538.2	537.6	537.5	537.4	537.3	537.3	537.4	537.9	538.3	538.8	539.2
177.5°	539.1	538.6	538.5	538.4	538.4	538.3	538.4	538.8	539.1	539.5	539.8
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1425.3	1430.7	1437.4	1447.7	1455.5	1462.2	1463.7	1465.6	1470.5	1478.7	1485.1
5°	1434.6	1448.5	1471.0	1492.8	1516.5	1535.9	1554.1	1566.8	1579.0	1604.5	1625.1
7.5°	1431.6	1462.8	1497.9	1537.1	1576.8	1615.2	1651.0	1682.9	1714.7	1751.9	1794.2
10°	1429.7	1466.2	1513.4	1563.8	1619.1	1673.0	1725.3	1765.9	1813.2	1855.7	1909.7
12.5°	1420.5	1472.9	1529.5	1593.9	1661.8	1724.0	1792.7	1848.9	1903.1	1964.4	2027.2
15°	1408.5	1472.2	1543.8	1629.3	1732.5	1807.8	1878.1	1975.9	2042.6	2109.3	2199.2
17.5°	1386.5	1464.3	1553.7	1664.9	1751.0	1852.1	1958.0	2035.2	2125.1	2219.2	2300.5
20°	1369.0	1459.5	1559.6	1668.8	1778.6	1888.5	1991.0	2083.3	2176.1	2284.7	2351.5
22.5°	1351.6	1441.0	1545.0	1661.1	1779.1	1894.8	2010.9	2119.2	2223.7	2333.3	2418.5
25°	1314.4	1420.6	1533.5	1651.8	1768.4	1895.8	2034.1	2154.9	2284.1	2397.0	2477.7
27.5°	1276.8	1374.1	1486.5	1606.5	1736.1	1886.7	2049.4	2186.7	2316.2	2397.0	2422.4
30°	1242.8	1345.9	1449.1	1571.1	1711.3	1879.4	2052.4	2209.5	2315.7	2350.9	2324.8
32.5°	1208.4	1301.8	1404.0	1528.8	1677.8	1861.4	2056.2	2195.9	2259.9	2232.9	2126.7
35°	1147.5	1231.9	1330.8	1455.8	1626.9	1851.5	2040.2	2134.8	2119.1	1967.4	1767.1
37.5°	1082.4	1151.2	1242.8	1373.5	1574.2	1812.0	1971.2	1985.2	1848.7	1615.8	1384.5
40°	1031.0	1092.9	1187.0	1323.5	1533.5	1773.2	1901.8	1845.4	1633.6	1374.5	1181.5
42.5°	981.0	1033.2	1123.8	1271.0	1494.7	1720.3	1798.4	1675.5	1431.2	1186.2	1010.7
45°	896.3	945.5	1036.4	1187.6	1415.1	1619.1	1608.7	1395.1	1150.6	953.3	807.7
47.5°	815.9	858.9	944.3	1098.6	1321.8	1467.3	1370.8	1143.5	936.1	777.8	674.0
50°	759.1	801.6	886.6	1038.9	1247.1	1353.3	1215.5	996.4	806.5	675.4	592.9
52.5°	704.8	746.3	823.9	972.4	1156.7	1220.2	1072.3	869.2	710.9	597.7	526.8
55°	628.7	660.2	730.0	872.0	1009.8	1024.3	874.4	704.5	574.1	495.2	446.7
57.5°	551.2	578.3	647.3	760.4	856.9	849.4	707.3	560.4	472.5	413.8	378.7
60°	500.6	527.4	588.0	685.1	758.0	732.5	602.0	483.7	408.4	365.3	337.4
62.5°	453.5	474.4	531.2	602.1	654.5	625.6	514.6	416.7	357.0	320.7	298.5
65°	385.3	402.3	447.8	484.8	514.0	486.1	393.9	325.8	282.8	257.3	242.1
67.5°	320.6	331.4	360.1	373.4	394.0	363.4	296.1	250.7	226.1	204.6	194.0
70°	279.7	287.7	302.8	313.7	319.2	287.7	237.9	204.5	183.9	168.7	162.0
72.5°	239.0	245.9	249.0	257.9	255.1	225.5	191.3	164.7	149.9	139.6	131.0
75°	182.6	185.7	182.6	179.1	171.1	150.5	126.8	113.5	102.5	97.7	94.7
77.5°	133.1	132.2	128.0	122.3	108.9	95.9	83.1	78.6	73.9	71.3	70.3
80°	102.5	100.1	96.5	87.4	75.9	66.8	63.8	60.7	58.9	55.8	55.2
82.5°	76.3	74.9	68.8	61.2	53.1	48.8	46.3	45.1	43.3	41.7	41.6
85°	40.7	38.9	32.2	27.9	26.7	25.5	24.9	24.9	22.5	21.8	21.8
87.5°	13.4	10.6	10.3	9.0	9.3	8.5	9.2	8.5	8.2	8.8	7.8
90°	1.2	2.1	3.0	3.9	5.0	6.2	7.3	8.5	9.6	10.0	10.3
92.5°	7.2	7.0	6.7	6.4	6.8	7.7	8.5	9.4	10.3	10.8	11.4
95°	20.8	17.1	13.5	9.8	8.5	9.5	10.4	11.4	12.4	13.0	13.6
97.5°	47.4	45.8	44.2	42.5	38.5	32.1	25.7	19.4	12.9	13.6	14.4
100°	69.5	71.2	73.0	74.8	68.8	54.9	41.0	27.1	13.2	13.9	14.6
102.5°	90.2	91.4	92.7	94.0	87.0	71.9	56.7	41.6	26.4	24.2	21.9
105°	120.4	121.4	122.3	123.3	119.8	111.7	103.8	95.8	87.7	72.0	56.2
107.5°	152.4	153.2	153.9	154.7	155.8	157.0	158.3	159.5	160.8	149.3	137.7
110°	173.8	174.5	175.2	175.9	176.7	177.7	178.7	179.7	180.7	177.7	174.8





TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	194.2	194.8	195.5	196.2	197.0	198.0	198.9	199.9	200.9	200.9	201.0
115°	224.4	225.0	225.5	226.0	226.8	227.6	228.4	229.2	230.0	230.9	231.8
117.5°	254.0	254.7	255.3	256.0	256.5	256.9	257.3	257.8	258.2	258.9	259.6
120°	272.4	273.2	274.0	274.8	275.4	275.6	275.9	276.2	276.4	277.1	277.9
122.5°	290.9	291.5	292.2	292.8	293.4	293.7	294.0	294.4	294.7	295.2	295.7
125°	316.4	317.1	317.8	318.5	319.1	319.4	319.8	320.1	320.5	320.7	320.8
127.5°	341.1	341.8	342.5	343.2	343.8	344.2	344.6	345.1	345.5	345.8	346.1
130°	356.5	357.2	357.9	358.6	359.2	359.5	359.9	360.3	360.5	360.9	361.2
132.5°	371.2	371.9	372.6	373.4	373.8	374.2	374.4	374.7	375.0	375.3	375.7
135°	393.5	394.0	394.6	395.1	395.6	395.9	396.3	396.6	397.0	397.3	397.5
137.5°	413.0	413.6	414.3	414.9	415.4	415.6	415.8	416.0	416.2	416.6	417.1
140°	425.6	426.1	426.7	427.2	427.6	427.8	428.1	428.4	428.6	429.0	429.4
142.5°	437.5	438.0	438.5	439.1	439.4	439.7	440.0	440.2	440.5	440.8	441.1
145°	454.1	454.8	455.4	456.0	456.4	456.6	456.7	456.9	457.1	457.3	457.4
147.5°	469.6	469.9	470.4	470.7	471.1	471.3	471.4	471.6	471.8	472.0	472.2
150°	479.0	479.3	479.6	479.8	480.0	480.2	480.4	480.5	480.7	480.9	481.1
152.5°	487.5	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.5	488.7	489.1
155°	499.4	499.2	499.1	498.9	498.8	498.9	499.0	499.1	499.2	499.6	500.1
157.5°	509.0	509.0	509.0	509.0	508.9	508.8	508.7	508.6	508.5	509.1	509.6
160°	514.7	514.6	514.5	514.4	514.3	514.2	514.2	514.1	514.0	514.5	515.1
162.5°	520.0	519.8	519.6	519.3	519.2	519.1	519.0	518.9	518.8	519.4	520.0
165°	526.6	526.3	526.0	525.8	525.6	525.5	525.4	525.3	525.2	525.9	526.6
167.5°	531.6	531.3	530.9	530.6	530.4	530.4	530.4	530.4	530.4	531.1	531.8
170°	534.5	534.1	533.8	533.4	533.2	533.2	533.2	533.2	533.2	534.0	534.7
172.5°	536.4	535.9	535.5	535.0	534.8	534.9	535.0	535.1	535.1	535.8	536.5
175°	538.8	538.3	537.9	537.4	537.3	537.3	537.4	537.5	537.6	538.2	538.9
177.5°	539.5	539.1	538.8	538.4	538.3	538.4	538.4	538.5	538.6	539.1	539.8
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6	1417.6
2.5°	1495.2	1495.2	1497.2	1504.5	1505.5	1511.7	1509.8
5°	1643.3	1654.8	1659.1	1677.3	1688.2	1693.1	1683.4
7.5°	1824.4	1856.9	1872.3	1891.4	1908.3	1913.3	1900.1
10°	1956.4	1990.4	2018.9	2036.6	2052.9	2063.9	2077.8
12.5°	2084.1	2125.8	2152.9	2177.8	2194.7	2208.5	2210.8
15°	2222.9	2286.0	2333.9	2369.1	2386.7	2395.8	2392.2
17.5°	2362.8	2421.3	2455.4	2491.4	2515.7	2516.9	2517.7
20°	2442.0	2498.9	2538.4	2565.1	2592.4	2591.2	2597.3
22.5°	2494.8	2539.8	2570.0	2589.3	2598.7	2594.1	2595.3
25°	2519.6	2532.9	2527.5	2496.5	2488.7	2460.1	2465.0
27.5°	2391.9	2328.8	2263.5	2179.5	2113.3	2060.3	2063.0
30°	2218.6	2106.9	1979.5	1872.7	1776.8	1750.2	1693.1
32.5°	1976.4	1808.8	1659.6	1560.0	1477.7	1455.5	1405.7
35°	1565.7	1403.0	1249.5	1157.3	1120.8	1069.9	1069.3
37.5°	1216.9	1073.7	992.6	923.4	887.1	856.2	853.2
40°	1023.8	912.0	850.8	801.0	765.3	742.2	736.7
42.5°	888.8	798.4	741.1	710.2	682.7	670.8	661.9
45°	725.8	665.1	625.0	597.1	584.4	575.2	570.4
47.5°	607.1	566.4	539.1	520.6	510.2	500.6	503.2
50°	542.5	509.2	489.1	471.5	463.6	456.9	457.5
52.5°	490.5	460.6	444.4	431.7	421.9	417.1	414.8
55°	416.3	397.4	381.1	372.0	366.5	359.9	358.0
57.5°	355.1	340.5	327.2	316.9	315.6	309.2	310.0
60°	314.3	302.2	291.3	285.8	281.6	276.1	277.9
62.5°	280.9	270.6	260.7	256.2	252.0	248.0	248.8
65°	230.0	220.3	214.2	211.8	210.0	208.1	206.3
67.5°	183.2	177.4	173.5	168.4	164.6	164.0	162.1
70°	154.2	146.2	139.6	132.9	131.1	130.5	131.1
72.5°	123.6	118.6	116.7	113.5	113.2	111.6	112.6
75°	92.8	91.0	89.8	87.4	87.4	87.4	87.4
77.5°	68.5	67.3	66.6	66.2	65.5	64.6	64.6
80°	53.4	52.8	51.5	51.5	51.0	51.5	51.0
82.5°	40.3	40.2	39.0	39.0	38.3	38.0	38.3
85°	20.6	20.1	21.2	20.1	20.6	19.4	20.6
87.5°	7.9	8.0	7.6	7.7	7.2	8.2	7.2
90°	10.7	11.1	11.3	11.5	11.7	11.9	12.0
92.5°	11.9	12.6	12.8	13.0	13.1	13.2	13.3
95°	14.3	14.9	15.2	15.2	15.2	15.2	15.2
97.5°	15.1	15.8	16.1	16.2	16.3	16.4	16.5
100°	15.3	16.1	16.5	16.6	16.7	16.8	16.9
102.5°	19.7	17.6	16.5	16.7	16.9	16.9	17.1
105°	40.5	24.7	16.9	17.1	17.3	17.5	17.7
107.5°	126.2	114.6	102.9	91.0	79.1	67.2	55.4
110°	171.8	168.9	161.1	148.4	135.6	122.9	110.2



TEST NUMBER: P332450-940

CATALOG NUMBER: S123RDIW-S1000D460U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	201.0	201.1	199.7	197.1	194.4	191.7	189.0
115°	232.6	233.5	234.2	234.5	234.9	235.2	235.6
117.5°	260.3	261.0	261.4	261.4	261.5	261.6	261.7
120°	278.6	279.3	279.6	279.6	279.6	279.6	279.6
122.5°	296.2	296.7	296.9	297.0	297.1	297.2	297.3
125°	321.0	321.2	321.4	321.6	321.7	321.9	322.1
127.5°	346.3	346.6	346.7	346.5	346.3	346.2	346.0
130°	361.6	361.9	362.0	361.9	361.7	361.5	361.3
132.5°	376.0	376.4	376.5	376.2	375.9	375.7	375.5
135°	397.8	398.1	398.1	397.8	397.5	397.3	397.0
137.5°	417.4	417.9	418.0	417.9	417.7	417.5	417.3
140°	429.7	430.1	430.2	430.0	429.8	429.6	429.4
142.5°	441.4	441.7	441.7	441.4	441.2	441.0	440.7
145°	457.6	457.8	457.9	457.9	457.9	457.9	457.9
147.5°	472.3	472.5	472.3	472.0	471.5	471.2	470.7
150°	481.3	481.4	481.4	481.2	480.9	480.6	480.4
152.5°	489.4	489.7	489.6	489.3	488.8	488.5	488.0
155°	500.5	501.0	500.9	500.3	499.8	499.3	498.8
157.5°	510.1	510.7	510.6	509.9	509.3	508.5	507.8
160°	515.6	516.1	516.1	515.5	514.9	514.2	513.6
162.5°	520.7	521.2	521.3	520.7	520.1	519.6	519.1
165°	527.4	528.1	528.1	527.4	526.9	526.3	525.7
167.5°	532.4	533.2	533.2	532.4	531.8	531.1	530.4
170°	535.4	536.1	536.1	535.4	534.7	534.0	533.2
172.5°	537.3	538.0	538.0	537.2	536.4	535.7	534.8
175°	539.5	540.1	540.1	539.4	538.7	538.0	537.3
177.5°	540.3	540.9	540.8	540.1	539.4	538.7	538.0
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2

(END OF REPORT)