

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333046-830

Luminaire Tested: **S124RDIW-S575D1050U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333046-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S575D1050U830-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5642.1 lumens  
Efficiency: N/A  
Efficacy: 124.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	34
3	80	70	63	58	72	64	58	53	53	49	45	42	39	37	33	30	29
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	32	25	21	26	22	18	22	18	15	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	1.6
10°-20°	250.9	4.4
20°-30°	362.3	6.4
30°-40°	410.7	7.3
40°-50°	396.6	7.0
50°-60°	329.8	5.8
60°-70°	227.7	4.0
70°-80°	115.4	2.0
80°-90°	33.3	0.6
90°-100°	81.4	1.4
100°-110°	241.2	4.3
110°-120°	409.4	7.3
120°-130°	539.9	9.6
130°-140°	606.3	10.7
140°-150°	595.8	10.6
150°-160°	501.1	8.9
160°-170°	333.4	5.9
170°-180°	116.7	2.1
0°-30°	703.2	12.5
0°-40°	1113.9	19.7
0°-60°	1840.3	32.6
0°-90°	2216.8	39.3
90°-120°	732.1	13.0
90°-150°	2474.1	43.8
90°-180°	3425.0	60.7
0°-180°	5642.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	3	13	21	27	29	5
95°	57	66	73	75	75	64
105°	222	224	227	230	233	236
115°	416	416	414	413	412	410
125°	606	606	605	603	602	540
135°	782	787	788	786	783	605
145°	950	954	955	954	951	594
155°	1088	1088	1088	1091	1088	501
165°	1185	1182	1180	1185	1182	334
175°	1233	1228	1227	1233	1227	117
180°	1235	1235	1235	1235	1235	



TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	14.0	13.5	12.9	12.3	11.8	11.6	11.8	12.0	12.3	12.4	12.5
90°	2.8	5.2	7.5	9.9	12.2	14.2	15.9	17.6	19.3	21.0	22.2
92.5°	20.5	23.1	25.8	28.5	31.1	33.1	34.2	35.4	36.7	37.8	38.5
95°	57.3	59.2	61.1	63.1	64.9	66.6	68.1	69.6	71.1	72.6	73.2
97.5°	100.1	101.6	103.1	104.6	106.2	107.8	109.5	111.3	113.0	114.8	115.6
100°	133.7	134.5	135.3	136.2	137.0	138.5	140.3	142.2	144.2	146.1	146.5
102.5°	168.8	169.2	169.5	169.8	170.1	171.2	173.0	174.7	176.4	178.1	178.8
105°	222.4	222.7	222.9	223.1	223.3	223.9	224.7	225.6	226.4	227.2	227.9
107.5°	278.8	279.1	279.3	279.6	279.8	280.0	280.1	280.3	280.4	280.5	281.2
110°	317.0	317.4	317.8	318.3	318.7	318.8	318.8	318.4	318.2	317.9	317.5



TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	356.8	356.8	356.9	356.9	357.0	356.9	356.6	356.2	355.8	355.4	355.3
115°	416.3	416.3	416.3	416.3	416.3	416.1	415.7	415.3	414.8	414.4	414.2
117.5°	472.5	472.6	472.8	473.0	473.2	473.1	472.8	472.5	472.2	471.8	471.2
120°	509.9	510.8	511.6	512.5	513.3	513.4	512.7	512.1	511.5	510.9	509.8
122.5°	548.8	549.2	549.5	549.9	550.2	550.3	549.9	549.6	549.3	549.0	548.3
125°	606.3	606.3	606.3	606.3	606.3	606.2	606.0	605.8	605.6	605.4	604.9
127.5°	658.5	659.1	659.7	660.3	661.0	661.2	660.8	660.4	660.2	659.8	659.4
130°	695.1	695.8	696.4	697.0	697.7	698.0	698.0	698.0	698.0	698.0	697.6
132.5°	732.5	733.0	733.5	734.0	734.4	734.5	734.4	734.2	734.1	733.9	733.5
135°	782.0	783.3	784.6	785.8	787.1	787.8	787.8	787.8	787.8	787.8	787.3
137.5°	835.8	836.4	837.1	837.6	838.2	838.7	839.1	839.4	839.7	840.1	839.5
140°	871.8	872.2	872.6	873.1	873.5	873.6	873.6	873.6	873.6	873.6	873.5
142.5°	904.7	905.0	905.5	905.9	906.3	906.4	906.3	906.1	906.0	905.8	905.7
145°	950.1	950.9	951.8	952.6	953.5	953.9	954.2	954.4	954.6	954.8	954.6
147.5°	995.1	996.2	997.2	998.2	999.2	999.7	999.5	999.3	999.1	998.9	998.8
150°	1022.7	1023.5	1024.4	1025.2	1026.1	1026.4	1026.4	1026.4	1026.4	1026.4	1026.4
152.5°	1048.6	1049.1	1049.6	1050.1	1050.7	1050.9	1051.1	1051.3	1051.5	1051.7	1052.2
155°	1088.5	1088.5	1088.5	1088.5	1088.5	1088.4	1088.2	1088.0	1087.8	1087.6	1088.4
157.5°	1122.1	1121.7	1121.3	1121.0	1120.6	1120.4	1120.3	1120.3	1120.2	1120.2	1120.9
160°	1142.0	1141.8	1141.5	1141.3	1141.1	1140.9	1140.7	1140.5	1140.3	1140.1	1140.7
162.5°	1160.3	1159.8	1159.2	1158.7	1158.1	1157.7	1157.5	1157.3	1157.1	1156.9	1158.0
165°	1185.0	1184.3	1183.6	1183.1	1182.4	1181.9	1181.5	1181.0	1180.6	1180.2	1181.5
167.5°	1203.8	1203.0	1202.1	1201.2	1200.3	1199.9	1200.0	1200.0	1200.0	1200.0	1201.3
170°	1214.6	1213.5	1212.4	1211.4	1210.3	1209.8	1210.1	1210.3	1210.5	1210.7	1212.0
172.5°	1222.2	1221.3	1220.4	1219.6	1218.6	1218.2	1218.2	1218.3	1218.3	1218.3	1219.8
175°	1232.7	1231.6	1230.6	1229.5	1228.4	1227.9	1227.6	1227.4	1227.2	1227.0	1228.4
177.5°	1236.1	1235.3	1234.4	1233.6	1232.8	1232.3	1232.3	1232.3	1232.3	1232.3	1233.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6



TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	12.6	12.8	12.9	13.1	13.3	13.5	13.8	13.9
90°	23.6	24.8	26.1	27.0	27.3	27.8	28.2	28.7
92.5°	39.3	40.1	40.9	41.4	41.7	41.8	42.1	42.4
95°	73.8	74.5	75.1	75.4	75.4	75.4	75.4	75.4
97.5°	116.3	117.1	117.8	118.2	118.2	118.2	118.2	118.2
100°	146.9	147.3	147.8	148.0	148.0	148.0	148.0	148.0
102.5°	179.4	179.9	180.6	181.0	181.1	181.3	181.4	181.6
105°	228.6	229.1	229.8	230.5	231.1	231.7	232.3	233.0
107.5°	281.7	282.3	283.0	283.1	283.1	283.1	283.0	283.0
110°	317.1	316.7	316.2	316.4	317.0	317.6	318.3	319.0





TEST NUMBER: P333046-830

CATALOG NUMBER: S124RDIW-S575D1050U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.2	355.2	355.1	355.1	355.2	355.3	355.4	355.6
115°	414.0	413.8	413.6	413.3	413.1	412.9	412.7	412.5
117.5°	470.4	469.7	469.0	468.4	468.0	467.6	467.1	466.7
120°	508.7	507.7	506.6	506.2	506.7	507.1	507.6	507.9
122.5°	547.6	546.9	546.1	545.4	544.6	543.8	543.1	542.3
125°	604.5	604.1	603.7	603.2	602.9	602.4	602.0	601.5
127.5°	658.9	658.6	658.1	657.7	657.3	657.0	656.7	656.4
130°	697.1	696.7	696.3	695.7	694.8	694.0	693.1	692.3
132.5°	733.0	732.6	732.2	731.8	731.5	731.1	730.8	730.5
135°	786.9	786.5	786.1	785.5	784.9	784.2	783.6	783.0
137.5°	839.0	838.4	837.8	837.6	837.7	837.9	838.0	838.1
140°	873.3	873.1	872.8	872.6	872.4	872.2	871.9	871.8
142.5°	905.7	905.6	905.6	905.5	905.5	905.5	905.4	905.4
145°	954.4	954.2	953.9	953.6	952.9	952.3	951.7	951.0
147.5°	998.6	998.4	998.2	998.1	997.9	997.7	997.4	997.2
150°	1026.4	1026.4	1026.4	1026.3	1026.1	1026.0	1025.7	1025.5
152.5°	1052.6	1053.2	1053.7	1053.7	1053.1	1052.5	1052.0	1051.5
155°	1089.3	1090.1	1091.0	1091.0	1090.1	1089.3	1088.4	1087.6
157.5°	1121.5	1122.1	1122.8	1122.8	1122.0	1121.2	1120.6	1119.8
160°	1141.3	1142.0	1142.6	1142.4	1141.3	1140.3	1139.3	1138.1
162.5°	1159.1	1160.3	1161.5	1161.5	1160.5	1159.4	1158.3	1157.3
165°	1182.7	1184.0	1185.2	1185.4	1184.6	1183.7	1182.9	1182.0
167.5°	1202.6	1203.8	1205.1	1205.1	1203.8	1202.5	1201.2	1199.9
170°	1213.2	1214.6	1215.8	1215.7	1214.3	1212.8	1211.3	1209.8
172.5°	1221.3	1222.7	1224.2	1224.1	1222.7	1221.2	1219.7	1218.1
175°	1229.9	1231.4	1232.9	1232.9	1231.4	1229.9	1228.4	1227.0
177.5°	1234.7	1235.9	1237.1	1237.0	1235.6	1234.3	1232.9	1231.5
180°	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6	1234.6

(END OF REPORT)