

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333049-830

Luminaire Tested: **S124RDIW-S575D1340U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333049-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U830-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7273.9 lumens
Efficiency: N/A
Efficacy: 135.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	66	61	56	53	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.2
10°-20°	250.9	3.4
20°-30°	362.3	5.0
30°-40°	410.7	5.6
40°-50°	396.6	5.5
50°-60°	329.8	4.5
60°-70°	227.7	3.1
70°-80°	115.4	1.6
80°-90°	34.3	0.5
90°-100°	55.9	0.8
100°-110°	356.4	4.9
110°-120°	681.9	9.4
120°-130°	865.6	11.9
130°-140°	926.1	12.7
140°-150°	866.0	11.9
150°-160°	698.4	9.6
160°-170°	450.5	6.2
170°-180°	155.3	2.1
0°-30°	703.2	9.7
0°-40°	1113.9	15.3
0°-60°	1840.3	25.3
0°-90°	2217.8	30.5
90°-120°	1094.2	15.0
90°-150°	3752.0	51.6
90°-180°	5056.0	69.5
0°-180°	7273.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	4	17	27	34	37	5
95°	67	28	27	34	35	86
105°	368	375	381	389	348	385
115°	687	690	690	692	692	676
125°	966	970	968	972	973	862
135°	1198	1197	1202	1204	1207	923
145°	1382	1385	1385	1386	1389	863
155°	1515	1516	1512	1517	1514	698
165°	1598	1592	1592	1600	1590	451
175°	1635	1628	1628	1638	1625	156
180°	1635	1635	1635	1635	1635	



TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	14.2	13.8	13.4	12.9	12.4	12.3	12.7	13.0	13.3	13.6	13.8
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	15.4	15.6	15.7	15.9	16.0	17.2	19.4	21.6	23.8	25.9	27.5
95°	67.2	58.0	48.7	39.5	30.3	25.8	26.1	26.4	26.6	26.9	28.6
97.5°	142.8	148.5	154.3	160.0	165.8	153.5	123.2	92.9	62.6	32.2	32.4
100°	200.5	205.4	210.3	215.2	220.1	203.8	166.3	128.8	91.2	53.8	49.2
102.5°	265.0	268.6	272.2	275.8	279.4	278.7	273.8	269.0	264.1	259.2	209.3
105°	368.0	369.6	371.3	372.9	374.5	376.0	377.4	378.7	380.0	381.4	383.9
107.5°	463.5	464.4	465.2	466.0	466.8	468.2	470.0	471.8	473.7	475.6	476.7
110°	528.1	529.0	529.8	530.6	531.4	532.6	534.2	535.8	537.5	539.1	539.7



TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	590.7	592.2	593.7	595.1	596.6	597.7	598.5	599.3	600.0	600.8	600.7
115°	687.0	687.9	688.7	689.5	690.3	690.6	690.3	690.0	689.8	689.5	690.0
117.5°	773.8	775.0	776.0	777.1	778.2	779.0	779.7	780.2	780.8	781.5	781.4
120°	832.5	833.6	834.7	835.8	836.9	837.3	837.1	836.8	836.5	836.2	836.8
122.5°	887.3	888.0	888.6	889.3	889.9	890.4	890.8	891.2	891.6	891.9	892.3
125°	965.8	966.9	968.0	969.0	970.2	970.4	969.9	969.3	968.7	968.3	969.0
127.5°	1040.1	1040.4	1040.7	1040.9	1041.2	1042.0	1043.2	1044.4	1045.8	1047.0	1046.8
130°	1088.1	1088.4	1088.6	1088.8	1089.1	1089.7	1090.5	1091.3	1092.1	1093.0	1093.3
132.5°	1132.1	1132.6	1133.0	1133.5	1134.0	1134.8	1135.9	1136.8	1137.8	1138.9	1139.2
135°	1198.1	1197.8	1197.5	1197.3	1197.0	1197.4	1198.4	1199.6	1200.7	1201.7	1202.3
137.5°	1256.5	1256.6	1256.7	1256.9	1257.0	1257.6	1258.8	1260.0	1261.2	1262.3	1263.0
140°	1294.7	1295.2	1295.7	1296.3	1296.8	1297.4	1297.9	1298.4	1299.0	1299.6	1300.3
142.5°	1328.9	1329.8	1330.9	1331.8	1332.8	1333.4	1333.8	1334.1	1334.5	1334.7	1335.4
145°	1381.5	1382.2	1383.1	1383.9	1384.7	1385.2	1385.2	1385.2	1385.2	1385.2	1385.4
147.5°	1423.2	1424.7	1426.3	1427.9	1429.4	1430.0	1429.7	1429.5	1429.2	1428.9	1429.1
150°	1453.6	1454.7	1455.8	1456.9	1457.9	1458.3	1458.1	1457.8	1457.5	1457.3	1457.3
152.5°	1479.0	1479.9	1480.7	1481.6	1482.5	1482.7	1482.2	1481.7	1481.2	1480.7	1481.2
155°	1514.8	1514.9	1515.2	1515.5	1515.8	1515.5	1514.8	1513.9	1513.1	1512.3	1513.3
157.5°	1544.8	1544.6	1544.5	1544.3	1544.2	1543.6	1542.7	1541.7	1540.9	1539.9	1541.3
160°	1562.4	1561.6	1560.8	1559.9	1559.2	1558.6	1558.3	1558.0	1557.7	1557.6	1559.2
162.5°	1578.0	1577.0	1576.0	1575.0	1574.0	1573.3	1573.0	1572.7	1572.4	1572.2	1573.8
165°	1597.9	1596.5	1595.2	1593.7	1592.4	1591.8	1591.8	1591.8	1591.8	1591.8	1593.9
167.5°	1613.5	1612.1	1610.7	1609.3	1607.9	1607.0	1606.9	1606.8	1606.6	1606.4	1608.8
170°	1622.3	1620.7	1619.0	1617.4	1615.8	1615.1	1615.3	1615.6	1615.9	1616.2	1618.3
172.5°	1628.1	1626.5	1624.9	1623.2	1621.6	1621.0	1621.3	1621.6	1621.7	1622.0	1624.2
175°	1634.6	1632.9	1631.3	1629.7	1628.0	1627.3	1627.6	1627.9	1628.1	1628.4	1630.9
177.5°	1637.5	1636.0	1634.4	1632.9	1631.4	1630.8	1631.3	1631.7	1632.1	1632.6	1634.3
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6



TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	13.9	14.1	14.4	14.6	14.8	15.1	15.3	15.6
90°	30.2	31.8	33.5	34.5	35.1	35.6	36.1	36.7
92.5°	29.2	30.8	32.4	33.3	33.5	33.6	33.6	33.7
95°	30.2	31.8	33.5	34.4	34.6	34.9	35.2	35.4
97.5°	32.6	32.8	32.9	33.2	33.5	33.6	33.9	34.2
100°	44.6	40.0	35.3	33.2	33.5	33.6	33.9	34.2
102.5°	159.6	109.7	59.9	35.0	35.1	35.1	35.2	35.3
105°	386.3	388.8	391.2	387.6	377.8	368.0	358.2	348.5
107.5°	478.0	479.2	480.3	481.5	482.5	483.5	484.6	485.6
110°	540.3	540.7	541.3	542.0	542.8	543.7	544.4	545.3



TEST NUMBER: P333049-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	600.5	600.4	600.3	600.8	601.8	602.9	603.9	604.9
115°	690.6	691.2	691.6	691.9	691.9	691.9	691.9	691.9
117.5°	781.2	781.1	781.0	780.9	780.8	780.7	780.6	780.4
120°	837.3	837.8	838.4	838.4	837.8	837.3	836.8	836.2
122.5°	892.6	893.0	893.2	893.2	892.6	892.0	891.6	891.0
125°	969.9	970.7	971.5	972.0	972.3	972.6	972.9	973.2
127.5°	1046.7	1046.5	1046.3	1046.1	1045.9	1045.7	1045.5	1045.3
130°	1093.4	1093.7	1094.0	1094.2	1094.2	1094.2	1094.2	1094.2
132.5°	1139.4	1139.7	1140.0	1140.0	1139.8	1139.6	1139.3	1139.2
135°	1202.9	1203.3	1203.9	1204.5	1205.0	1205.5	1206.1	1206.6
137.5°	1263.6	1264.1	1264.8	1265.0	1264.8	1264.7	1264.5	1264.3
140°	1301.2	1302.0	1302.8	1303.3	1303.6	1303.9	1304.2	1304.5
142.5°	1336.0	1336.5	1337.2	1337.5	1337.6	1337.6	1337.7	1337.7
145°	1385.6	1385.9	1386.2	1386.7	1387.1	1387.7	1388.3	1388.8
147.5°	1429.4	1429.6	1429.7	1430.0	1430.3	1430.6	1430.8	1431.1
150°	1457.3	1457.3	1457.3	1457.4	1457.6	1457.9	1458.2	1458.5
152.5°	1481.6	1482.1	1482.4	1482.6	1482.4	1482.2	1482.1	1482.0
155°	1514.5	1515.5	1516.6	1516.7	1516.0	1515.1	1514.3	1513.5
157.5°	1542.8	1544.2	1545.6	1545.6	1544.2	1542.8	1541.3	1539.9
160°	1560.8	1562.4	1564.1	1564.1	1562.4	1560.8	1559.2	1557.6
162.5°	1575.5	1577.1	1578.7	1578.6	1576.8	1574.9	1573.0	1571.2
165°	1596.1	1598.3	1600.4	1600.2	1597.9	1595.4	1593.0	1590.5
167.5°	1611.2	1613.5	1616.0	1615.8	1613.1	1610.3	1607.7	1605.0
170°	1620.5	1622.7	1624.8	1624.6	1621.9	1619.2	1616.5	1613.7
172.5°	1626.4	1628.6	1630.8	1630.4	1627.4	1624.5	1621.6	1618.6
175°	1633.3	1635.8	1638.2	1637.8	1634.6	1631.3	1628.0	1624.8
177.5°	1636.1	1637.8	1639.6	1639.1	1636.4	1633.9	1631.3	1628.6
180°	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6	1634.6

(END OF REPORT)