

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332484-940

Luminaire Tested: **S123RDIW-S1165D1320U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332484-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1320U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8615.0 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45			45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39			39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33			33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28			28
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	30	28	24			24
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21			21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19			19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15			15
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	1.9
10°-20°	451.6	5.2
20°-30°	650.2	7.5
30°-40°	732.4	8.5
40°-50°	700.7	8.1
50°-60°	573.8	6.7
60°-70°	387.1	4.5
70°-80°	194.8	2.3
80°-90°	55.8	0.6
90°-100°	56.1	0.7
100°-110°	267.4	3.1
110°-120°	642.3	7.5
120°-130°	818.0	9.5
130°-140°	874.0	10.1
140°-150°	817.3	9.5
150°-160°	659.2	7.7
160°-170°	425.5	4.9
170°-180°	146.6	1.7
0°-30°	1264.1	14.7
0°-40°	1996.5	23.2
0°-60°	3270.9	38.0
0°-90°	3908.7	45.4
90°-120°	965.9	11.2
90°-150°	3475.0	40.3
90°-180°	4706.0	54.6
0°-180°	8615.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	1	13	28	32	34	7
95°	70	26	36	43	44	86
105°	342	348	251	60	50	362
115°	641	648	658	669	674	632
125°	904	912	917	920	922	807
135°	1125	1132	1136	1139	1136	866
145°	1298	1306	1308	1310	1310	812
155°	1430	1428	1429	1434	1428	658
165°	1508	1504	1503	1511	1504	426
175°	1543	1538	1539	1546	1538	147
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.1	24.9	22.6	20.4	18.2	17.4	18.1	18.7	19.4	20.1	20.1
90°	1.2	3.7	6.2	8.8	11.3	14.3	17.6	20.9	24.2	27.6	28.5
92.5°	21.3	20.6	19.9	19.2	18.5	19.4	21.8	24.3	26.8	29.3	30.9
95°	69.9	59.5	49.0	38.6	28.2	24.3	27.1	30.0	32.7	35.6	37.4
97.5°	140.5	135.9	131.2	126.5	121.8	110.3	91.9	73.7	55.3	36.9	39.0
100°	193.8	198.9	203.9	209.0	214.2	196.8	157.1	117.3	77.6	37.8	39.9
102.5°	254.3	258.0	261.6	265.3	269.0	249.1	205.7	162.3	118.9	75.4	69.1
105°	341.7	344.5	347.3	350.1	352.8	342.9	319.9	296.9	274.0	251.1	206.0
107.5°	433.9	436.1	438.4	440.6	442.8	445.8	449.4	453.0	456.6	460.2	427.1
110°	495.3	497.4	499.4	501.4	503.5	505.9	508.7	511.5	514.3	517.1	508.7



TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	554.0	555.9	557.7	559.5	561.3	563.7	566.5	569.3	572.1	574.9	575.1
115°	641.0	642.5	644.0	645.5	647.0	649.0	651.2	653.5	655.9	658.2	660.7
117.5°	725.1	727.0	728.9	730.8	732.6	734.1	735.3	736.6	737.7	738.9	740.9
120°	777.4	779.7	781.9	784.3	786.6	788.1	788.8	789.6	790.4	791.1	793.2
122.5°	830.6	832.5	834.4	836.2	838.1	839.5	840.5	841.5	842.5	843.5	844.9
125°	903.5	905.5	907.6	909.6	911.7	913.2	914.2	915.3	916.2	917.3	917.7
127.5°	974.1	976.2	978.2	980.3	982.3	983.9	985.2	986.4	987.6	988.8	989.6
130°	1018.2	1020.2	1022.3	1024.3	1026.4	1027.9	1028.9	1029.9	1030.9	1031.9	1033.0
132.5°	1060.3	1062.4	1064.4	1066.5	1068.5	1070.0	1070.8	1071.6	1072.4	1073.2	1074.2
135°	1124.8	1126.3	1127.8	1129.4	1131.0	1132.2	1133.2	1134.3	1135.2	1136.3	1137.0
137.5°	1179.8	1181.8	1183.7	1185.6	1187.6	1188.8	1189.4	1190.0	1190.5	1191.1	1192.3
140°	1216.6	1218.1	1219.6	1221.1	1222.6	1223.8	1224.6	1225.3	1226.1	1226.8	1227.9
142.5°	1250.4	1252.0	1253.6	1255.1	1256.6	1257.8	1258.5	1259.3	1260.0	1260.8	1261.6
145°	1298.0	1299.8	1301.5	1303.3	1305.1	1306.2	1306.7	1307.2	1307.8	1308.2	1308.8
147.5°	1342.6	1343.8	1345.0	1346.1	1347.4	1348.2	1348.7	1349.2	1349.7	1350.2	1350.8
150°	1370.2	1370.9	1371.7	1372.4	1373.2	1373.9	1374.4	1374.8	1375.4	1375.9	1376.4
152.5°	1394.9	1395.3	1395.6	1396.0	1396.3	1396.7	1397.0	1397.3	1397.6	1397.9	1398.8
155°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.6	1427.9	1428.2	1428.4	1428.6	1429.9
157.5°	1456.9	1456.8	1456.8	1456.7	1456.6	1456.5	1456.3	1456.0	1455.7	1455.5	1457.0
160°	1473.4	1473.1	1472.8	1472.6	1472.3	1472.1	1471.9	1471.6	1471.3	1471.1	1472.6
162.5°	1489.0	1488.3	1487.6	1486.9	1486.3	1485.9	1485.6	1485.3	1485.1	1484.8	1486.6
165°	1507.8	1507.0	1506.2	1505.5	1504.7	1504.2	1504.0	1503.7	1503.4	1503.2	1505.2
167.5°	1522.4	1521.4	1520.4	1519.4	1518.3	1517.9	1517.9	1517.9	1517.9	1517.9	1519.9
170°	1530.7	1529.6	1528.7	1527.7	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1
172.5°	1536.2	1535.0	1533.7	1532.5	1531.3	1530.8	1531.0	1531.2	1531.4	1531.6	1533.7
175°	1543.3	1542.0	1540.8	1539.4	1538.2	1537.7	1537.9	1538.2	1538.5	1538.7	1540.5
177.5°	1545.2	1544.1	1543.1	1542.1	1541.1	1540.7	1540.9	1541.1	1541.2	1541.5	1543.1
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	20.0	20.0	19.9	19.8	19.6	19.5	19.4	19.2
90°	29.5	30.6	31.6	32.4	32.9	33.3	33.9	34.4
92.5°	32.6	34.2	35.8	36.8	37.2	37.5	37.7	38.1
95°	39.1	40.9	42.7	43.6	43.6	43.6	43.6	43.6
97.5°	41.0	43.1	45.0	46.2	46.5	46.7	47.0	47.3
100°	41.9	44.0	46.0	47.2	47.3	47.6	47.9	48.2
102.5°	62.8	56.4	50.2	47.3	47.7	48.2	48.6	49.0
105°	160.9	115.8	70.7	48.4	49.0	49.4	49.9	50.5
107.5°	394.1	361.1	328.0	294.4	260.5	226.4	192.4	158.5
110°	500.2	491.9	483.5	461.0	424.6	388.2	351.8	315.3



TEST NUMBER: P332484-940

CATALOG NUMBER: S123RDIW-S1165D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	575.2	575.3	575.5	571.8	564.0	556.3	548.7	541.0
115°	663.3	665.8	668.3	670.1	671.1	672.2	673.2	674.2
117.5°	743.0	744.9	747.0	748.1	748.3	748.5	748.8	748.9
120°	795.2	797.3	799.3	800.3	800.3	800.3	800.3	800.3
122.5°	846.3	847.7	849.2	850.0	850.2	850.3	850.6	850.8
125°	918.3	918.8	919.3	919.8	920.3	920.9	921.3	921.9
127.5°	990.4	991.2	992.1	992.2	991.8	991.2	990.7	990.2
130°	1033.9	1035.0	1036.0	1036.3	1035.7	1035.3	1034.7	1034.2
132.5°	1075.2	1076.3	1077.3	1077.5	1076.7	1076.0	1075.3	1074.6
135°	1137.8	1138.5	1139.3	1139.3	1138.5	1137.8	1137.0	1136.3
137.5°	1193.6	1194.7	1196.0	1196.3	1195.8	1195.3	1194.8	1194.3
140°	1228.9	1229.9	1230.9	1231.2	1230.7	1230.1	1229.7	1229.1
142.5°	1262.4	1263.2	1264.1	1264.1	1263.4	1262.7	1261.9	1261.2
145°	1309.3	1309.7	1310.3	1310.5	1310.5	1310.5	1310.5	1310.5
147.5°	1351.2	1351.7	1352.3	1351.9	1350.8	1349.6	1348.4	1347.2
150°	1376.9	1377.4	1378.0	1377.8	1377.1	1376.3	1375.6	1374.8
152.5°	1399.7	1400.7	1401.6	1401.5	1400.3	1399.1	1397.9	1396.8
155°	1431.2	1432.4	1433.8	1433.6	1432.1	1430.6	1429.1	1427.5
157.5°	1458.6	1460.1	1461.6	1461.3	1459.4	1457.4	1455.4	1453.4
160°	1474.1	1475.7	1477.2	1477.0	1475.2	1473.5	1471.7	1469.9
162.5°	1488.3	1490.0	1491.7	1491.8	1490.2	1488.7	1487.1	1485.5
165°	1507.3	1509.3	1511.4	1511.4	1509.7	1507.9	1506.1	1504.3
167.5°	1522.0	1523.9	1526.0	1526.0	1523.9	1522.0	1519.9	1517.9
170°	1530.2	1532.2	1534.3	1534.3	1532.2	1530.2	1528.1	1526.1
172.5°	1535.7	1537.8	1539.8	1539.6	1537.4	1535.2	1532.9	1530.7
175°	1542.3	1544.1	1545.9	1545.7	1543.7	1541.7	1539.6	1537.6
177.5°	1544.7	1546.4	1548.0	1547.8	1545.8	1543.7	1541.7	1539.6
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3

(END OF REPORT)