

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333050-830

Luminaire Tested: **S124RDIW-S575D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333050-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U830-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6602.9 lumens
Efficiency: N/A
Efficacy: 122.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7733	7733	7733
5°	7750	7656	7703
10°	7702	7564	7564
15°	7614	7405	7350
20°	7491	7196	7064
25°	7337	6951	6774
30°	7185	6693	6413
35°	7019	6427	6050
40°	6817	6122	5658
45°	6632	5819	5259
50°	6420	5471	4835
55°	6194	5111	4376
60°	5945	4713	3907
65°	5717	4216	3446
70°	5384	3670	2924
75°	4966	3044	2380
80°	4328	2320	2180
85°	3668	2103	1973



TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.4
10°-20°	250.9	3.8
20°-30°	362.3	5.5
30°-40°	410.7	6.2
40°-50°	396.6	6.0
50°-60°	329.8	5.0
60°-70°	227.7	3.4
70°-80°	115.4	1.7
80°-90°	34.3	0.5
90°-100°	104.3	1.6
100°-110°	308.8	4.7
110°-120°	524.1	7.9
120°-130°	691.1	10.5
130°-140°	776.2	11.8
140°-150°	762.7	11.6
150°-160°	641.5	9.7
160°-170°	426.8	6.5
170°-180°	149.5	2.3
0°-30°	703.2	10.7
0°-40°	1113.9	16.9
0°-60°	1840.3	27.9
0°-90°	2217.8	33.6
90°-120°	937.2	14.2
90°-150°	3167.3	48.0
90°-180°	4385.0	66.4
0°-180°	6602.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	958	958	958	958	958	
5°	956	953	945	952	951	91
15°	911	904	886	884	879	257
25°	824	810	780	768	760	379
35°	712	688	652	628	614	445
45°	581	553	510	475	461	448
55°	440	410	363	326	311	394
65°	299	267	221	190	180	295
75°	159	132	98	81	76	168
85°	40	26	23	21	21	45
90°	4	17	27	34	37	7
95°	73	84	93	96	97	82
105°	285	286	291	295	298	302
115°	533	533	530	529	528	525
125°	776	776	775	772	770	692
135°	1001	1008	1008	1006	1002	774
145°	1216	1221	1222	1221	1218	761
155°	1394	1393	1392	1397	1392	641
165°	1517	1513	1511	1518	1513	427
175°	1578	1572	1571	1578	1571	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	960.3	959.7	959.2	958.7	958.2	957.2	955.7	954.3	952.8	951.4	952.8
5°	956.4	955.7	955.1	954.4	953.9	952.5	950.6	948.6	946.6	944.7	946.3
7.5°	947.7	947.1	946.4	945.7	945.0	943.4	940.8	938.3	935.8	933.2	934.2
10°	939.5	938.8	937.9	937.1	936.3	934.4	931.5	928.5	925.6	922.7	923.3
12.5°	929.0	928.0	927.1	926.1	925.2	923.0	919.5	916.1	912.7	909.2	909.6
15°	911.0	909.5	908.0	906.5	905.0	902.3	898.2	894.2	890.0	886.0	885.7
17.5°	889.1	886.9	884.9	882.7	880.6	877.1	872.2	867.3	862.4	857.5	856.7
20°	872.0	870.0	867.8	865.7	863.6	859.8	854.2	848.7	843.1	837.6	836.3
22.5°	853.3	850.9	848.6	846.1	843.8	839.6	833.7	827.7	821.8	815.9	813.9
25°	823.7	820.8	817.7	814.8	811.9	807.1	800.4	793.7	787.0	780.4	777.6
27.5°	792.6	788.9	785.2	781.6	777.8	772.4	765.3	758.2	751.0	743.9	740.5
30°	770.8	766.8	762.7	758.7	754.6	748.7	741.0	733.4	725.7	718.0	714.0
32.5°	748.0	743.4	738.8	734.1	729.6	723.3	715.4	707.5	699.6	691.6	686.9
35°	712.2	707.0	701.7	696.5	691.4	684.7	676.5	668.4	660.2	652.1	646.5
37.5°	673.9	668.5	663.2	657.8	652.3	645.2	636.1	627.1	618.1	609.1	602.9
40°	646.9	641.5	636.1	630.7	625.4	618.0	608.8	599.5	590.2	580.9	574.0
42.5°	621.0	615.5	609.8	604.2	598.5	590.9	581.2	571.5	561.8	552.1	545.2
45°	580.9	574.9	568.8	562.8	556.8	548.8	539.0	529.3	519.5	509.7	501.7
47.5°	539.4	533.2	526.9	520.7	514.4	506.2	496.1	486.0	475.8	465.6	457.3
50°	511.2	504.8	498.5	492.1	485.8	477.4	466.9	456.6	446.1	435.6	427.5
52.5°	482.5	476.3	470.0	463.8	457.5	449.1	438.4	427.7	417.0	406.3	398.0
55°	440.1	433.6	427.1	420.5	414.0	405.4	394.8	384.3	373.6	363.1	354.6
57.5°	398.1	391.3	384.6	377.8	371.0	362.4	351.9	341.5	331.1	320.7	312.1
60°	368.2	361.7	355.2	348.6	342.1	333.7	323.2	312.7	302.4	291.9	283.4
62.5°	341.2	334.4	327.6	320.8	314.1	305.4	294.6	284.0	273.2	262.6	254.8
65°	299.3	292.3	285.2	278.2	271.2	262.5	252.0	241.7	231.2	220.7	213.8
67.5°	255.7	248.9	242.2	235.5	228.8	220.6	210.9	201.2	191.6	181.9	175.9
70°	228.1	221.2	214.4	207.5	200.8	192.7	183.3	174.1	164.8	155.5	150.1
72.5°	198.8	192.6	186.3	180.2	174.0	166.5	157.8	149.0	140.2	131.4	126.9
75°	159.2	153.2	147.1	141.1	135.1	128.2	120.6	112.8	105.2	97.6	93.8
77.5°	118.9	113.9	108.8	103.6	98.5	92.8	86.6	80.5	74.3	68.1	65.9
80°	93.1	88.4	83.7	79.0	74.3	69.5	64.6	59.7	54.8	49.9	49.4
82.5°	70.9	66.5	62.2	57.9	53.5	50.0	47.1	44.3	41.6	38.7	38.4
85°	39.6	36.4	33.1	29.8	26.6	24.7	24.2	23.8	23.2	22.7	22.4
87.5°	14.2	13.8	13.4	12.9	12.4	12.3	12.7	13.0	13.3	13.6	13.8
90°	3.7	6.7	9.6	12.6	15.6	18.2	20.4	22.5	24.7	26.9	28.6
92.5°	26.2	29.6	33.0	36.4	39.9	42.3	43.8	45.3	46.8	48.4	49.4
95°	73.3	75.8	78.2	80.7	83.1	85.3	87.2	89.1	91.0	92.9	93.7
97.5°	128.1	130.1	132.1	133.9	135.9	138.0	140.3	142.5	144.7	146.9	147.9
100°	171.2	172.2	173.3	174.4	175.5	177.2	179.6	182.1	184.5	187.0	187.6
102.5°	216.1	216.6	217.0	217.4	217.8	219.1	221.4	223.7	225.8	228.1	228.8
105°	284.8	285.1	285.4	285.6	285.9	286.5	287.7	288.8	289.8	291.0	291.7
107.5°	356.9	357.2	357.6	357.9	358.3	358.4	358.6	358.8	359.0	359.1	359.9
110°	405.9	406.3	406.9	407.5	408.0	408.1	407.8	407.6	407.4	407.1	406.5



TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	456.7	456.8	456.9	457.0	457.1	456.9	456.5	455.9	455.4	455.0	454.9
115°	532.9	532.9	532.9	532.9	532.9	532.7	532.2	531.6	531.0	530.5	530.3
117.5°	604.8	605.0	605.3	605.5	605.7	605.6	605.2	604.8	604.5	604.1	603.1
120°	652.7	653.8	654.9	656.0	657.0	657.2	656.4	655.6	654.8	653.9	652.6
122.5°	702.6	703.0	703.5	703.9	704.4	704.4	704.0	703.6	703.2	702.9	701.9
125°	776.2	776.2	776.2	776.2	776.2	776.1	775.8	775.5	775.2	775.0	774.4
127.5°	842.9	843.8	844.6	845.4	846.2	846.4	845.9	845.6	845.1	844.6	844.1
130°	889.9	890.7	891.6	892.3	893.2	893.5	893.5	893.5	893.5	893.5	893.0
132.5°	937.8	938.4	939.0	939.6	940.2	940.4	940.2	939.9	939.7	939.5	939.0
135°	1001.1	1002.8	1004.4	1006.0	1007.7	1008.4	1008.4	1008.4	1008.4	1008.4	1008.0
137.5°	1070.1	1070.8	1071.6	1072.3	1073.1	1073.7	1074.1	1074.6	1075.0	1075.4	1074.7
140°	1116.1	1116.5	1117.1	1117.7	1118.2	1118.4	1118.4	1118.4	1118.4	1118.4	1118.2
142.5°	1158.1	1158.6	1159.1	1159.7	1160.3	1160.4	1160.2	1160.0	1159.8	1159.5	1159.5
145°	1216.3	1217.4	1218.4	1219.6	1220.6	1221.3	1221.5	1221.8	1222.1	1222.4	1222.1
147.5°	1273.9	1275.3	1276.6	1277.9	1279.1	1279.7	1279.5	1279.3	1279.0	1278.8	1278.7
150°	1309.2	1310.2	1311.4	1312.4	1313.5	1314.0	1314.0	1314.0	1314.0	1314.0	1314.0
152.5°	1342.4	1343.0	1343.7	1344.3	1345.0	1345.5	1345.7	1345.9	1346.1	1346.3	1347.0
155°	1393.5	1393.5	1393.5	1393.5	1393.5	1393.4	1393.1	1392.8	1392.5	1392.3	1393.4
157.5°	1436.5	1436.1	1435.6	1435.0	1434.5	1434.3	1434.3	1434.2	1434.2	1434.1	1434.9
160°	1462.0	1461.7	1461.4	1461.1	1460.8	1460.6	1460.3	1460.1	1459.8	1459.5	1460.3
162.5°	1485.4	1484.7	1484.0	1483.3	1482.6	1482.1	1481.9	1481.6	1481.3	1481.0	1482.5
165°	1516.9	1516.2	1515.3	1514.5	1513.7	1513.1	1512.5	1511.9	1511.4	1510.8	1512.5
167.5°	1541.2	1540.0	1538.9	1537.8	1536.6	1536.1	1536.2	1536.2	1536.3	1536.3	1537.9
170°	1554.8	1553.5	1552.2	1550.8	1549.4	1548.9	1549.2	1549.4	1549.7	1549.9	1551.6
172.5°	1564.6	1563.5	1562.4	1561.2	1560.1	1559.5	1559.6	1559.6	1559.7	1559.7	1561.6
175°	1578.1	1576.7	1575.4	1574.0	1572.6	1571.8	1571.6	1571.3	1571.0	1570.7	1572.6
177.5°	1582.4	1581.4	1580.3	1579.2	1578.1	1577.6	1577.6	1577.6	1577.6	1577.6	1579.1
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5



TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	957.9	957.9	957.9	957.9	957.9	957.9	957.9	957.9
2.5°	954.3	955.7	957.2	957.8	957.7	957.5	957.4	957.3
5°	947.9	949.6	951.2	951.9	951.5	951.2	950.8	950.6
7.5°	935.3	936.3	937.5	937.6	937.2	936.6	936.1	935.6
10°	924.0	924.6	925.3	925.3	924.6	924.0	923.3	922.7
12.5°	909.9	910.3	910.8	910.5	909.6	908.7	907.8	906.8
15°	885.3	885.0	884.7	884.0	882.8	881.7	880.5	879.4
17.5°	855.7	854.8	853.8	852.5	850.8	849.1	847.3	845.6
20°	835.0	833.7	832.4	830.7	828.6	826.4	824.3	822.2
22.5°	812.0	810.0	808.0	806.3	804.5	802.8	801.1	799.3
25°	774.9	772.0	769.3	767.1	765.4	763.8	762.2	760.5
27.5°	737.0	733.6	730.2	727.3	724.9	722.6	720.3	717.9
30°	709.9	705.8	701.7	698.4	695.8	693.1	690.6	688.0
32.5°	682.2	677.5	672.7	669.1	666.7	664.2	661.7	659.2
35°	640.9	635.4	629.9	625.7	622.7	619.7	616.8	613.9
37.5°	596.6	590.5	584.3	579.8	576.7	573.8	570.9	568.0
40°	567.2	560.3	553.5	548.7	545.6	542.7	539.8	536.9
42.5°	538.2	531.2	524.2	519.2	516.1	513.1	510.0	507.0
45°	493.8	485.8	477.8	472.3	469.4	466.5	463.5	460.6
47.5°	449.0	440.7	432.4	426.7	423.5	420.3	417.1	413.8
50°	419.3	411.2	403.0	397.5	394.4	391.2	388.1	385.0
52.5°	389.7	381.4	373.2	367.5	364.2	361.0	357.8	354.6
55°	346.1	337.6	329.1	323.4	320.3	317.2	314.1	310.9
57.5°	303.4	294.8	286.3	280.8	278.4	276.1	273.7	271.4
60°	274.9	266.5	258.0	252.5	249.9	247.2	244.7	242.0
62.5°	246.9	239.1	231.3	226.3	224.2	222.2	220.1	218.0
65°	206.8	199.7	192.7	188.2	186.3	184.4	182.4	180.4
67.5°	169.8	163.8	157.8	153.7	151.6	149.4	147.2	145.1
70°	144.8	139.4	133.9	130.4	128.8	127.2	125.5	123.9
72.5°	122.2	117.6	113.0	110.0	108.5	107.0	105.5	104.0
75°	90.0	86.3	82.6	80.2	79.2	78.2	77.3	76.3
77.5°	63.7	61.5	59.3	58.1	57.8	57.5	57.2	56.9
80°	48.9	48.4	47.9	47.6	47.4	47.2	47.1	46.9
82.5°	38.0	37.6	37.3	37.0	36.9	36.7	36.6	36.4
85°	22.1	21.8	21.4	21.3	21.3	21.3	21.3	21.3
87.5°	13.9	14.1	14.4	14.6	14.8	15.1	15.3	15.6
90°	30.2	31.8	33.4	34.5	35.1	35.6	36.1	36.7
92.5°	50.3	51.4	52.3	53.0	53.3	53.6	53.9	54.3
95°	94.5	95.4	96.1	96.6	96.6	96.6	96.6	96.6
97.5°	148.9	149.9	150.8	151.4	151.4	151.4	151.4	151.4
100°	188.1	188.7	189.2	189.5	189.5	189.5	189.5	189.5
102.5°	229.6	230.4	231.1	231.6	231.9	232.1	232.2	232.5
105°	292.6	293.4	294.2	295.0	295.8	296.6	297.5	298.2
107.5°	360.6	361.4	362.2	362.5	362.5	362.4	362.4	362.3
110°	406.0	405.4	404.9	405.0	405.9	406.6	407.5	408.3



TEST NUMBER: P333050-830

CATALOG NUMBER: S124RDIW-S575D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	454.8	454.7	454.5	454.6	454.7	454.9	455.1	455.2
115°	530.0	529.7	529.4	529.1	528.9	528.6	528.3	528.1
117.5°	602.3	601.3	600.4	599.6	599.1	598.6	598.0	597.5
120°	651.3	649.9	648.6	648.1	648.7	649.2	649.8	650.3
122.5°	701.0	700.1	699.2	698.2	697.2	696.3	695.3	694.3
125°	773.9	773.4	772.8	772.2	771.8	771.2	770.6	770.1
127.5°	843.6	843.0	842.4	842.0	841.6	841.1	840.7	840.3
130°	892.5	891.9	891.4	890.6	889.5	888.3	887.3	886.2
132.5°	938.4	937.9	937.4	936.9	936.4	935.9	935.6	935.1
135°	1007.4	1006.8	1006.3	1005.6	1004.8	1004.0	1003.1	1002.3
137.5°	1074.0	1073.4	1072.6	1072.3	1072.5	1072.7	1072.8	1073.0
140°	1117.9	1117.7	1117.4	1117.1	1116.8	1116.5	1116.3	1116.1
142.5°	1159.4	1159.4	1159.3	1159.2	1159.2	1159.1	1159.1	1159.0
145°	1221.8	1221.5	1221.3	1220.8	1219.9	1219.1	1218.3	1217.5
147.5°	1278.4	1278.2	1278.0	1277.7	1277.4	1277.1	1277.0	1276.7
150°	1314.0	1314.0	1314.0	1313.9	1313.6	1313.3	1313.1	1312.9
152.5°	1347.6	1348.3	1349.0	1348.9	1348.2	1347.5	1346.8	1346.0
155°	1394.5	1395.5	1396.7	1396.7	1395.5	1394.5	1393.4	1392.3
157.5°	1435.7	1436.5	1437.4	1437.3	1436.3	1435.4	1434.5	1433.6
160°	1461.1	1462.0	1462.7	1462.4	1461.1	1459.8	1458.4	1457.1
162.5°	1483.9	1485.4	1486.9	1487.0	1485.5	1484.2	1482.9	1481.5
165°	1514.1	1515.7	1517.4	1517.7	1516.6	1515.4	1514.4	1513.3
167.5°	1539.5	1541.2	1542.8	1542.8	1541.1	1539.4	1537.8	1536.1
170°	1553.2	1554.8	1556.5	1556.3	1554.4	1552.6	1550.7	1548.8
172.5°	1563.4	1565.3	1567.2	1567.1	1565.2	1563.3	1561.4	1559.5
175°	1574.5	1576.4	1578.4	1578.4	1576.4	1574.5	1572.6	1570.7
177.5°	1580.6	1582.2	1583.7	1583.6	1581.9	1580.1	1578.4	1576.6
180°	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5	1580.5

(END OF REPORT)