

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332489-940

Luminaire Tested: **S123RDIW-S1165D1535U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332489-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8652.0 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18603	18603	18603
5°	18674	18416	18522
10°	18569	18185	18124
15°	18369	17761	17572
20°	18095	17228	16827
25°	17813	16631	16098
30°	17439	15940	15070
35°	17056	15251	14127
40°	16703	14436	12960
45°	16238	13633	11905
50°	15726	12722	10727
55°	15204	11678	9627
60°	14725	10562	8420
65°	14103	9352	7210
70°	13322	7852	5822
75°	12181	6180	5481
80°	10860	5473	5040
85°	9176	4841	4508



TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.3	1.9
10°-20°	451.6	5.2
20°-30°	650.2	7.5
30°-40°	732.4	8.5
40°-50°	700.7	8.1
50°-60°	573.8	6.6
60°-70°	387.1	4.5
70°-80°	194.8	2.3
80°-90°	56.6	0.7
90°-100°	111.5	1.3
100°-110°	333.8	3.9
110°-120°	567.7	6.6
120°-130°	746.7	8.6
130°-140°	839.3	9.7
140°-150°	825.0	9.5
150°-160°	694.5	8.0
160°-170°	462.3	5.3
170°-180°	161.9	1.9
0°-30°	1264.1	14.6
0°-40°	1996.5	23.1
0°-60°	3270.9	37.8
0°-90°	3909.4	45.2
90°-120°	1013.0	11.7
90°-150°	3423.9	39.6
90°-180°	4743.0	54.8
0°-180°	8652.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1728	1728	1728	1728	1728	
5°	1728	1721	1704	1716	1714	164
15°	1648	1632	1594	1587	1577	464
25°	1500	1463	1400	1372	1355	689
35°	1298	1246	1161	1102	1075	812
45°	1067	1001	896	818	782	823
55°	810	739	622	544	513	726
65°	554	475	367	302	283	548
75°	293	225	149	135	132	312
85°	74	45	39	37	36	83
90°	1	15	32	38	40	9
95°	79	89	100	105	105	89
105°	303	306	317	318	320	324
115°	572	575	573	574	573	565
125°	836	840	838	832	827	746
135°	1085	1093	1092	1087	1084	836
145°	1316	1319	1323	1322	1316	822
155°	1507	1507	1509	1513	1505	694
165°	1642	1638	1638	1645	1636	463
175°	1708	1703	1702	1709	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1733.9	1732.9	1731.9	1730.9	1729.9	1727.9	1724.9	1721.9	1719.0	1715.9	1718.7
5°	1728.3	1726.7	1725.2	1723.6	1722.1	1719.4	1715.7	1711.9	1708.2	1704.4	1707.3
7.5°	1712.3	1710.7	1709.0	1707.3	1705.6	1702.3	1697.5	1692.6	1687.7	1682.8	1684.4
10°	1698.9	1696.7	1694.5	1692.3	1690.1	1686.2	1680.6	1675.0	1669.4	1663.8	1664.1
12.5°	1679.8	1677.4	1674.9	1672.5	1670.1	1665.4	1658.6	1651.7	1644.8	1638.0	1637.8
15°	1648.4	1644.9	1641.6	1638.1	1634.7	1628.6	1619.9	1611.1	1602.4	1593.8	1592.1
17.5°	1608.8	1604.9	1600.9	1596.9	1593.0	1585.4	1574.3	1563.2	1552.1	1541.1	1537.8
20°	1579.7	1574.8	1569.8	1564.8	1559.8	1551.4	1539.5	1527.7	1515.8	1504.0	1499.9
22.5°	1547.2	1541.4	1535.7	1530.0	1524.3	1515.1	1502.5	1490.0	1477.4	1464.7	1459.7
25°	1499.8	1492.0	1484.3	1476.4	1468.6	1457.6	1443.2	1429.0	1414.6	1400.3	1393.7
27.5°	1442.3	1433.8	1425.1	1416.6	1407.9	1395.7	1379.7	1363.8	1347.8	1331.9	1322.8
30°	1403.1	1393.7	1384.4	1375.0	1365.7	1352.3	1334.9	1317.4	1300.0	1282.5	1271.9
32.5°	1363.9	1353.3	1342.6	1332.0	1321.5	1307.0	1288.5	1270.1	1251.6	1233.2	1221.6
35°	1298.0	1286.7	1275.5	1264.4	1253.1	1237.9	1218.5	1199.3	1179.9	1160.6	1147.2
37.5°	1231.3	1218.8	1206.3	1193.8	1181.4	1164.8	1144.2	1123.6	1103.0	1082.4	1067.2
40°	1188.7	1174.9	1161.2	1147.5	1133.8	1115.9	1093.8	1071.7	1049.5	1027.4	1011.2
42.5°	1140.4	1126.7	1113.0	1099.3	1085.6	1067.3	1044.5	1021.5	998.7	975.9	958.1
45°	1066.7	1052.7	1038.7	1024.7	1010.6	991.6	967.6	943.6	919.6	895.6	877.9
47.5°	992.9	977.6	962.2	946.8	931.4	911.7	887.7	863.7	839.7	815.8	796.5
50°	939.1	924.5	909.8	895.2	880.6	860.7	835.4	810.2	785.0	759.7	740.4
52.5°	890.9	875.0	859.2	843.3	827.3	806.9	781.9	757.0	732.0	707.0	687.0
55°	810.2	794.9	779.6	764.4	749.1	728.3	701.8	675.3	648.8	622.3	604.3
57.5°	735.6	719.0	702.3	685.7	669.1	647.5	620.9	594.2	567.7	541.1	524.0
60°	684.0	666.9	649.8	632.7	615.5	594.0	568.1	542.3	516.5	490.6	473.8
62.5°	632.4	615.3	598.2	581.0	563.9	542.4	516.6	490.7	464.8	439.0	423.2
65°	553.7	536.5	519.4	502.3	485.2	464.4	440.1	415.8	391.6	367.2	352.0
67.5°	474.9	457.5	440.2	422.9	405.6	385.3	362.0	338.7	315.4	292.1	280.7
70°	423.3	406.5	389.7	372.8	356.1	336.7	315.0	293.1	271.3	249.5	238.6
72.5°	371.8	355.2	338.6	322.0	305.4	287.2	267.4	247.6	227.8	208.0	199.1
75°	292.9	278.0	263.1	248.1	233.2	217.1	200.0	182.8	165.7	148.6	145.4
77.5°	221.1	207.7	194.1	180.7	167.1	154.8	143.8	132.8	121.7	110.8	109.1
80°	175.2	162.5	149.6	136.9	124.1	114.5	107.9	101.4	94.9	88.3	87.4
82.5°	131.4	120.5	109.4	98.4	87.4	80.3	77.3	74.2	71.2	68.1	67.1
85°	74.3	67.4	60.5	53.8	46.9	43.0	42.1	41.1	40.2	39.2	38.6
87.5°	27.2	25.1	22.9	20.8	18.6	17.9	18.7	19.4	20.2	21.0	21.0
90°	1.3	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4
92.5°	32.5	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6
95°	79.4	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7
97.5°	140.9	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1
100°	182.9	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6
102.5°	231.3	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9
105°	302.6	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4
107.5°	385.4	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8
110°	437.0	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6



TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.8	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4
115°	571.5	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1
117.5°	652.7	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8
120°	703.3	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3
122.5°	756.0	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6
125°	836.3	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5
127.5°	910.6	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5
130°	960.1	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6
132.5°	1009.6	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9
135°	1085.1	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7
137.5°	1155.0	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0
140°	1203.5	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1247.6	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4
145°	1316.4	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9
147.5°	1376.6	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3
150°	1418.6	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0
152.5°	1453.0	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9
155°	1507.3	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9
157.5°	1553.6	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3
160°	1582.7	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4
162.5°	1608.5	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3
165°	1641.8	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6
167.5°	1668.5	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0
170°	1683.5	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3
172.5°	1695.3	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8
175°	1707.7	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1
177.5°	1712.8	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3	1728.3
2.5°	1721.4	1724.2	1726.9	1728.0	1727.5	1727.1	1726.5	1726.0
5°	1710.0	1712.9	1715.7	1716.7	1716.1	1715.5	1714.8	1714.2
7.5°	1686.0	1687.6	1689.1	1689.3	1688.3	1687.2	1686.1	1685.1
10°	1664.5	1664.7	1665.1	1664.5	1662.9	1661.3	1659.7	1658.2
12.5°	1637.6	1637.4	1637.3	1636.3	1634.5	1632.6	1630.8	1629.1
15°	1590.6	1589.0	1587.5	1585.6	1583.4	1581.3	1579.0	1576.9
17.5°	1534.5	1531.1	1527.8	1524.6	1521.3	1518.0	1514.8	1511.5
20°	1495.9	1491.8	1487.8	1483.9	1480.2	1476.4	1472.7	1469.0
22.5°	1454.6	1449.7	1444.6	1440.3	1436.8	1433.3	1429.9	1426.4
25°	1387.2	1380.6	1374.1	1369.1	1365.7	1362.3	1358.9	1355.4
27.5°	1313.7	1304.6	1295.5	1288.3	1283.1	1277.9	1272.6	1267.4
30°	1261.3	1250.8	1240.2	1232.4	1227.4	1222.4	1217.5	1212.5
32.5°	1210.1	1198.5	1186.9	1178.5	1173.2	1168.0	1162.8	1157.5
35°	1133.8	1120.4	1107.1	1097.5	1091.9	1086.3	1080.7	1075.1
37.5°	1052.0	1036.8	1021.5	1010.5	1003.6	996.7	989.8	982.8
40°	995.1	978.8	962.7	951.0	943.8	936.7	929.5	922.3
42.5°	940.5	922.7	905.1	893.0	886.6	880.2	873.8	867.4
45°	860.1	842.4	824.7	812.1	804.6	797.1	789.6	782.1
47.5°	777.1	757.9	738.5	725.6	718.9	712.2	705.5	698.9
50°	721.1	701.8	682.4	669.2	662.1	654.9	647.7	640.6
52.5°	666.9	646.8	626.8	613.5	607.1	600.7	594.3	587.9
55°	586.2	568.1	550.1	538.0	531.7	525.5	519.2	513.0
57.5°	506.9	489.8	472.8	461.5	456.3	451.0	445.7	440.4
60°	456.9	440.1	423.3	412.2	407.0	401.6	396.4	391.1
62.5°	407.3	391.6	375.7	365.1	359.4	353.9	348.4	342.9
65°	336.7	321.5	306.2	296.9	293.5	290.0	286.6	283.1
67.5°	269.3	257.9	246.5	239.0	235.3	231.6	227.9	224.3
70°	227.7	216.8	205.9	198.8	195.3	191.9	188.4	185.0
72.5°	190.2	181.3	172.4	167.2	165.8	164.3	162.9	161.5
75°	142.3	139.2	136.1	134.3	133.7	133.0	132.4	131.8
77.5°	107.4	105.7	104.0	102.8	102.2	101.6	100.9	100.3
80°	86.4	85.5	84.5	83.8	83.2	82.6	81.9	81.3
82.5°	66.3	65.4	64.4	63.8	63.8	63.6	63.5	63.4
85°	38.0	37.4	36.7	36.5	36.5	36.5	36.5	36.5
87.5°	21.0	21.0	21.0	21.0	20.8	20.7	20.5	20.4
90°	34.7	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	53.5	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	101.9	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	158.5	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	199.5	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	246.8	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	393.8	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	444.8	445.9	447.2	447.5	446.8	446.3	445.7	445.1



TEST NUMBER: P332489-940

CATALOG NUMBER: S123RDIW-S1165D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.8	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	704.0	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.8	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	835.4	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	912.9	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	964.4	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1014.5	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1089.5	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1162.8	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.9	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1256.2	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.5	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.4	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1511.1	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1555.6	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1583.0	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1608.7	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1641.4	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1693.6	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1705.9	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1711.4	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)