

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332407-940

Luminaire Tested: **S123RDIW-S340D1535U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332407-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1535U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5956.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	20
1	91	87	84	80	81	77	74	72	59	57	55	42	40	39	26	25	25	18
2	83	76	71	66	73	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	61	55	67	60	54	50	46	42	39	33	30	28	21	19	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	18	17	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	21	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	0.8
10°-20°	149.1	2.5
20°-30°	234.2	3.9
30°-40°	244.4	4.1
40°-50°	209.1	3.5
50°-60°	159.4	2.7
60°-70°	102.2	1.7
70°-80°	49.1	0.8
80°-90°	18.1	0.3
90°-100°	111.5	1.9
100°-110°	333.8	5.6
110°-120°	567.7	9.5
120°-130°	746.7	12.5
130°-140°	839.3	14.1
140°-150°	825.0	13.9
150°-160°	694.5	11.7
160°-170°	462.3	7.8
170°-180°	161.9	2.7
0°-30°	431.1	7.2
0°-40°	675.4	11.3
0°-60°	1044.0	17.5
0°-90°	1213.4	20.4
90°-120°	1013.0	17.0
90°-150°	3423.9	57.5
90°-180°	4743.0	79.6
0°-180°	5956.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	9
90°	40	1	40	1	40	20
95°	105	79	105	79	105	108
105°	320	303	320	303	320	340
115°	573	572	573	572	573	567
125°	827	836	827	836	827	739
135°	1084	1085	1084	1085	1084	833
145°	1316	1316	1316	1316	1316	822
155°	1505	1507	1505	1507	1505	693
165°	1636	1642	1636	1642	1636	462
175°	1701	1708	1701	1708	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	9.7	10.0	9.5	9.5	9.5	9.4	9.2	8.9	9.0	8.6	8.0
90°	40.3	39.8	39.1	38.5	38.0	37.1	35.8	34.7	33.4	32.3	28.4
92.5°	54.3	54.7	55.0	55.4	55.7	55.5	54.5	53.5	52.6	51.6	49.4
95°	104.9	104.9	104.9	104.9	104.9	104.2	103.1	101.9	100.7	99.5	97.1
97.5°	161.4	161.5	161.6	161.8	161.8	161.2	159.8	158.5	157.1	155.7	154.0
100°	204.4	203.8	203.2	202.6	202.0	201.3	200.4	199.5	198.6	197.7	196.2
102.5°	248.5	248.6	248.7	248.9	249.0	248.6	247.7	246.8	245.9	245.0	243.0
105°	320.0	319.4	318.9	318.3	317.6	317.4	317.4	317.4	317.4	317.4	314.7
107.5°	394.5	394.8	395.2	395.6	395.9	395.7	394.7	393.8	392.8	391.8	390.7
110°	445.1	445.7	446.3	446.8	447.5	447.2	445.9	444.8	443.6	442.4	441.8



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	498.8	499.0	499.1	499.3	499.4	498.6	497.2	495.8	494.4	492.9	492.8
115°	572.8	573.1	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8	573.5
117.5°	647.8	648.7	649.5	650.3	651.2	651.7	651.8	651.8	651.8	651.9	652.6
120°	700.5	701.2	701.8	702.4	702.9	703.4	703.7	704.0	704.3	704.6	706.1
122.5°	751.1	752.0	752.8	753.7	754.5	755.3	756.1	756.8	757.6	758.4	759.2
125°	827.0	828.1	829.4	830.5	831.7	832.9	834.1	835.4	836.5	837.8	838.3
127.5°	902.5	903.9	905.3	906.7	908.0	909.5	911.2	912.9	914.5	916.2	916.9
130°	952.0	954.1	956.2	958.3	960.4	962.1	963.2	964.4	965.6	966.8	967.7
132.5°	1003.6	1005.2	1006.9	1008.5	1010.1	1011.6	1013.1	1014.5	1015.9	1017.4	1018.0
135°	1083.8	1084.4	1084.9	1085.6	1086.2	1087.1	1088.2	1089.5	1090.7	1091.9	1092.2
137.5°	1154.5	1155.7	1156.8	1157.9	1159.0	1160.3	1161.5	1162.8	1164.0	1165.3	1164.5
140°	1200.8	1202.8	1205.0	1207.0	1209.2	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1248.1	1249.7	1251.3	1252.9	1254.5	1255.5	1255.8	1256.2	1256.4	1256.7	1256.2
145°	1316.4	1317.6	1318.8	1320.0	1321.2	1322.0	1322.2	1322.5	1322.9	1323.1	1322.2
147.5°	1377.2	1378.9	1380.8	1382.6	1384.4	1385.3	1385.3	1385.3	1385.3	1385.3	1384.4
150°	1415.9	1417.7	1419.5	1421.3	1423.1	1424.0	1424.0	1424.0	1424.0	1424.0	1423.3
152.5°	1453.6	1455.1	1456.7	1458.2	1459.8	1460.4	1459.8	1459.4	1458.9	1458.4	1458.0
155°	1504.7	1506.7	1508.9	1510.9	1513.1	1513.5	1512.3	1511.1	1509.9	1508.7	1508.4
157.5°	1551.2	1552.8	1554.5	1556.2	1557.9	1558.1	1556.8	1555.6	1554.3	1553.1	1552.8
160°	1581.3	1582.5	1583.7	1584.9	1586.1	1585.9	1584.5	1583.0	1581.4	1579.9	1579.9
162.5°	1603.9	1605.8	1607.8	1609.6	1611.6	1611.8	1610.3	1608.7	1607.3	1605.8	1605.5
165°	1636.5	1638.5	1640.7	1642.7	1644.8	1644.9	1643.2	1641.4	1639.6	1637.8	1637.8
167.5°	1664.1	1666.0	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1	1663.9
170°	1678.1	1680.3	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1	1678.1
172.5°	1688.9	1691.0	1693.1	1695.1	1697.3	1697.4	1695.5	1693.6	1691.8	1690.0	1690.0
175°	1701.0	1703.1	1705.1	1707.3	1709.3	1709.5	1707.7	1705.9	1704.1	1702.4	1702.4
177.5°	1707.4	1709.1	1710.7	1712.4	1714.1	1714.2	1712.8	1711.4	1709.9	1708.5	1708.5
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	7.6	6.6	6.2	5.5	5.4	5.0	5.4	5.6	6.3	6.2	6.9
90°	24.5	20.6	16.8	13.3	10.3	7.3	4.4	1.3	4.4	7.3	10.3
92.5°	47.2	45.0	42.8	40.7	38.6	36.6	34.6	32.5	34.6	36.6	38.6
95°	94.7	92.3	90.0	87.7	85.6	83.6	81.4	79.4	81.4	83.6	85.6
97.5°	152.2	150.5	148.7	147.1	145.6	144.0	142.5	140.9	142.5	144.0	145.6
100°	194.7	193.1	191.7	190.0	188.2	186.5	184.7	182.9	184.7	186.5	188.2
102.5°	241.0	239.1	237.1	235.6	234.5	233.4	232.4	231.3	232.4	233.4	234.5
105°	311.9	309.2	306.6	305.0	304.3	303.7	303.2	302.6	303.2	303.7	304.3
107.5°	389.7	388.6	387.5	386.8	386.5	386.1	385.8	385.4	385.8	386.1	386.5
110°	441.2	440.6	440.0	439.4	438.8	438.2	437.7	437.0	437.7	438.2	438.8



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	492.7	492.6	492.5	492.2	491.9	491.5	491.2	490.8	491.2	491.5	491.9
115°	574.0	574.6	575.2	575.1	574.2	573.3	572.4	571.5	572.4	573.3	574.2
117.5°	653.4	654.2	655.0	655.1	654.5	653.9	653.3	652.7	653.3	653.9	654.5
120°	707.6	709.1	710.6	710.4	708.6	706.9	705.1	703.3	705.1	706.9	708.6
122.5°	759.9	760.7	761.5	761.3	759.9	758.6	757.2	756.0	757.2	758.6	759.9
125°	838.9	839.5	840.1	840.0	839.1	838.2	837.2	836.3	837.2	838.2	839.1
127.5°	917.6	918.2	918.9	918.3	916.3	914.4	912.5	910.6	912.5	914.4	916.3
130°	968.6	969.5	970.4	969.6	967.2	964.8	962.5	960.1	962.5	964.8	967.2
132.5°	1018.7	1019.3	1020.0	1019.1	1016.7	1014.3	1011.9	1009.6	1011.9	1014.3	1016.7
135°	1092.4	1092.8	1093.1	1092.3	1090.5	1088.7	1086.9	1085.1	1086.9	1088.7	1090.5
137.5°	1163.7	1163.0	1162.2	1161.0	1159.6	1158.1	1156.5	1155.0	1156.5	1158.1	1159.6
140°	1210.9	1210.7	1210.3	1209.4	1207.9	1206.5	1205.0	1203.5	1205.0	1206.5	1207.9
142.5°	1255.6	1255.1	1254.5	1253.6	1252.1	1250.5	1249.0	1247.6	1249.0	1250.5	1252.1
145°	1321.3	1320.4	1319.6	1318.8	1318.2	1317.6	1317.1	1316.4	1317.1	1317.6	1318.2
147.5°	1383.6	1382.8	1381.9	1381.0	1379.9	1378.8	1377.7	1376.6	1377.7	1378.8	1379.9
150°	1422.8	1422.2	1421.6	1421.0	1420.4	1419.8	1419.2	1418.6	1419.2	1419.8	1420.4
152.5°	1457.7	1457.3	1457.0	1456.3	1455.5	1454.7	1453.8	1453.0	1453.8	1454.7	1455.5
155°	1508.1	1507.8	1507.5	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3	1507.3
157.5°	1552.6	1552.4	1552.1	1552.2	1552.6	1552.9	1553.3	1553.6	1553.3	1552.9	1552.6
160°	1579.9	1579.9	1579.9	1580.3	1580.8	1581.4	1582.1	1582.7	1582.1	1581.4	1580.8
162.5°	1605.3	1605.1	1604.8	1605.2	1606.0	1606.8	1607.7	1608.5	1607.7	1606.8	1606.0
165°	1637.8	1637.8	1637.8	1638.3	1639.1	1640.0	1640.9	1641.8	1640.9	1640.0	1639.1
167.5°	1663.7	1663.4	1663.2	1663.7	1664.8	1666.1	1667.2	1668.5	1667.2	1666.1	1664.8
170°	1678.1	1678.1	1678.1	1678.7	1679.9	1681.1	1682.3	1683.5	1682.3	1681.1	1679.9
172.5°	1690.0	1690.0	1690.0	1690.6	1691.8	1692.9	1694.2	1695.3	1694.2	1692.9	1691.8
175°	1702.4	1702.4	1702.4	1702.9	1704.1	1705.3	1706.6	1707.7	1706.6	1705.3	1704.1
177.5°	1708.5	1708.5	1708.5	1709.0	1709.9	1710.9	1711.9	1712.8	1711.9	1710.9	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	7.3	8.5	9.5	10.3	11.3	11.9	12.3	12.6	13.0	13.2	13.4
90°	13.3	16.8	20.6	24.5	28.4	32.3	33.4	34.7	35.8	37.1	38.0
92.5°	40.7	42.8	45.0	47.2	49.4	51.6	52.6	53.5	54.5	55.5	55.7
95°	87.7	90.0	92.3	94.7	97.1	99.5	100.7	101.9	103.1	104.2	104.9
97.5°	147.1	148.7	150.5	152.2	154.0	155.7	157.1	158.5	159.8	161.2	161.8
100°	190.0	191.7	193.1	194.7	196.2	197.7	198.6	199.5	200.4	201.3	202.0
102.5°	235.6	237.1	239.1	241.0	243.0	245.0	245.9	246.8	247.7	248.6	249.0
105°	305.0	306.6	309.2	311.9	314.7	317.4	317.4	317.4	317.4	317.4	317.6
107.5°	386.8	387.5	388.6	389.7	390.7	391.8	392.8	393.8	394.7	395.7	395.9
110°	439.4	440.0	440.6	441.2	441.8	442.4	443.6	444.8	445.9	447.2	447.5



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.2	492.5	492.6	492.7	492.8	492.9	494.4	495.8	497.2	498.6	499.4
115°	575.1	575.2	574.6	574.0	573.5	572.8	573.1	573.5	573.7	574.0	574.0
117.5°	655.1	655.0	654.2	653.4	652.6	651.9	651.8	651.8	651.8	651.7	651.2
120°	710.4	710.6	709.1	707.6	706.1	704.6	704.3	704.0	703.7	703.4	702.9
122.5°	761.3	761.5	760.7	759.9	759.2	758.4	757.6	756.8	756.1	755.3	754.5
125°	840.0	840.1	839.5	838.9	838.3	837.8	836.5	835.4	834.1	832.9	831.7
127.5°	918.3	918.9	918.2	917.6	916.9	916.2	914.5	912.9	911.2	909.5	908.0
130°	969.6	970.4	969.5	968.6	967.7	966.8	965.6	964.4	963.2	962.1	960.4
132.5°	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9	1014.5	1013.1	1011.6	1010.1
135°	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7	1089.5	1088.2	1087.1	1086.2
137.5°	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0	1162.8	1161.5	1160.3	1159.0
140°	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2	1210.9	1210.7	1210.3	1209.2
142.5°	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4	1256.2	1255.8	1255.5	1254.5
145°	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9	1322.5	1322.2	1322.0	1321.2
147.5°	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3	1385.3	1385.3	1385.3	1384.4
150°	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0	1424.0	1424.0	1424.0	1423.1
152.5°	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9	1459.4	1459.8	1460.4	1459.8
155°	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9	1511.1	1512.3	1513.5	1513.1
157.5°	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3	1555.6	1556.8	1558.1	1557.9
160°	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4	1583.0	1584.5	1585.9	1586.1
162.5°	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3	1608.7	1610.3	1611.8	1611.6
165°	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6	1641.4	1643.2	1644.9	1644.8
167.5°	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0	1667.9	1669.7	1671.5	1671.5
170°	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3	1682.3	1684.4	1686.5	1686.5
172.5°	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8	1693.6	1695.5	1697.4	1697.3
175°	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1	1705.9	1707.7	1709.5	1709.3
177.5°	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9	1711.4	1712.8	1714.2	1714.1
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	13.8	13.6	13.7	14.1	13.7	13.6	13.8	13.4	13.2	13.0	12.6
90°	38.5	39.1	39.8	40.3	39.8	39.1	38.5	38.0	37.1	35.8	34.7
92.5°	55.4	55.0	54.7	54.3	54.7	55.0	55.4	55.7	55.5	54.5	53.5
95°	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.9	104.2	103.1	101.9
97.5°	161.8	161.6	161.5	161.4	161.5	161.6	161.8	161.8	161.2	159.8	158.5
100°	202.6	203.2	203.8	204.4	203.8	203.2	202.6	202.0	201.3	200.4	199.5
102.5°	248.9	248.7	248.6	248.5	248.6	248.7	248.9	249.0	248.6	247.7	246.8
105°	318.3	318.9	319.4	320.0	319.4	318.9	318.3	317.6	317.4	317.4	317.4
107.5°	395.6	395.2	394.8	394.5	394.8	395.2	395.6	395.9	395.7	394.7	393.8
110°	446.8	446.3	445.7	445.1	445.7	446.3	446.8	447.5	447.2	445.9	444.8



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	499.3	499.1	499.0	498.8	499.0	499.1	499.3	499.4	498.6	497.2	495.8
115°	573.7	573.5	573.1	572.8	573.1	573.5	573.7	574.0	574.0	573.7	573.5
117.5°	650.3	649.5	648.7	647.8	648.7	649.5	650.3	651.2	651.7	651.8	651.8
120°	702.4	701.8	701.2	700.5	701.2	701.8	702.4	702.9	703.4	703.7	704.0
122.5°	753.7	752.8	752.0	751.1	752.0	752.8	753.7	754.5	755.3	756.1	756.8
125°	830.5	829.4	828.1	827.0	828.1	829.4	830.5	831.7	832.9	834.1	835.4
127.5°	906.7	905.3	903.9	902.5	903.9	905.3	906.7	908.0	909.5	911.2	912.9
130°	958.3	956.2	954.1	952.0	954.1	956.2	958.3	960.4	962.1	963.2	964.4
132.5°	1008.5	1006.9	1005.2	1003.6	1005.2	1006.9	1008.5	1010.1	1011.6	1013.1	1014.5
135°	1085.6	1084.9	1084.4	1083.8	1084.4	1084.9	1085.6	1086.2	1087.1	1088.2	1089.5
137.5°	1157.9	1156.8	1155.7	1154.5	1155.7	1156.8	1157.9	1159.0	1160.3	1161.5	1162.8
140°	1207.0	1205.0	1202.8	1200.8	1202.8	1205.0	1207.0	1209.2	1210.3	1210.7	1210.9
142.5°	1252.9	1251.3	1249.7	1248.1	1249.7	1251.3	1252.9	1254.5	1255.5	1255.8	1256.2
145°	1320.0	1318.8	1317.6	1316.4	1317.6	1318.8	1320.0	1321.2	1322.0	1322.2	1322.5
147.5°	1382.6	1380.8	1378.9	1377.2	1378.9	1380.8	1382.6	1384.4	1385.3	1385.3	1385.3
150°	1421.3	1419.5	1417.7	1415.9	1417.7	1419.5	1421.3	1423.1	1424.0	1424.0	1424.0
152.5°	1458.2	1456.7	1455.1	1453.6	1455.1	1456.7	1458.2	1459.8	1460.4	1459.8	1459.4
155°	1510.9	1508.9	1506.7	1504.7	1506.7	1508.9	1510.9	1513.1	1513.5	1512.3	1511.1
157.5°	1556.2	1554.5	1552.8	1551.2	1552.8	1554.5	1556.2	1557.9	1558.1	1556.8	1555.6
160°	1584.9	1583.7	1582.5	1581.3	1582.5	1583.7	1584.9	1586.1	1585.9	1584.5	1583.0
162.5°	1609.6	1607.8	1605.8	1603.9	1605.8	1607.8	1609.6	1611.6	1611.8	1610.3	1608.7
165°	1642.7	1640.7	1638.5	1636.5	1638.5	1640.7	1642.7	1644.8	1644.9	1643.2	1641.4
167.5°	1669.7	1667.9	1666.0	1664.1	1666.0	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9
170°	1684.4	1682.3	1680.3	1678.1	1680.3	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3
172.5°	1695.1	1693.1	1691.0	1688.9	1691.0	1693.1	1695.1	1697.3	1697.4	1695.5	1693.6
175°	1707.3	1705.1	1703.1	1701.0	1703.1	1705.1	1707.3	1709.3	1709.5	1707.7	1705.9
177.5°	1712.4	1710.7	1709.1	1707.4	1709.1	1710.7	1712.4	1714.1	1714.2	1712.8	1711.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	12.3	11.9	11.3	10.3	9.5	8.5	7.3	6.9	6.2	6.3	5.6
90°	33.4	32.3	28.4	24.5	20.6	16.8	13.3	10.3	7.3	4.4	1.3
92.5°	52.6	51.6	49.4	47.2	45.0	42.8	40.7	38.6	36.6	34.6	32.5
95°	100.7	99.5	97.1	94.7	92.3	90.0	87.7	85.6	83.6	81.4	79.4
97.5°	157.1	155.7	154.0	152.2	150.5	148.7	147.1	145.6	144.0	142.5	140.9
100°	198.6	197.7	196.2	194.7	193.1	191.7	190.0	188.2	186.5	184.7	182.9
102.5°	245.9	245.0	243.0	241.0	239.1	237.1	235.6	234.5	233.4	232.4	231.3
105°	317.4	317.4	314.7	311.9	309.2	306.6	305.0	304.3	303.7	303.2	302.6
107.5°	392.8	391.8	390.7	389.7	388.6	387.5	386.8	386.5	386.1	385.8	385.4
110°	443.6	442.4	441.8	441.2	440.6	440.0	439.4	438.8	438.2	437.7	437.0



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	494.4	492.9	492.8	492.7	492.6	492.5	492.2	491.9	491.5	491.2	490.8
115°	573.1	572.8	573.5	574.0	574.6	575.2	575.1	574.2	573.3	572.4	571.5
117.5°	651.8	651.9	652.6	653.4	654.2	655.0	655.1	654.5	653.9	653.3	652.7
120°	704.3	704.6	706.1	707.6	709.1	710.6	710.4	708.6	706.9	705.1	703.3
122.5°	757.6	758.4	759.2	759.9	760.7	761.5	761.3	759.9	758.6	757.2	756.0
125°	836.5	837.8	838.3	838.9	839.5	840.1	840.0	839.1	838.2	837.2	836.3
127.5°	914.5	916.2	916.9	917.6	918.2	918.9	918.3	916.3	914.4	912.5	910.6
130°	965.6	966.8	967.7	968.6	969.5	970.4	969.6	967.2	964.8	962.5	960.1
132.5°	1015.9	1017.4	1018.0	1018.7	1019.3	1020.0	1019.1	1016.7	1014.3	1011.9	1009.6
135°	1090.7	1091.9	1092.2	1092.4	1092.8	1093.1	1092.3	1090.5	1088.7	1086.9	1085.1
137.5°	1164.0	1165.3	1164.5	1163.7	1163.0	1162.2	1161.0	1159.6	1158.1	1156.5	1155.0
140°	1211.2	1211.6	1211.2	1210.9	1210.7	1210.3	1209.4	1207.9	1206.5	1205.0	1203.5
142.5°	1256.4	1256.7	1256.2	1255.6	1255.1	1254.5	1253.6	1252.1	1250.5	1249.0	1247.6
145°	1322.9	1323.1	1322.2	1321.3	1320.4	1319.6	1318.8	1318.2	1317.6	1317.1	1316.4
147.5°	1385.3	1385.3	1384.4	1383.6	1382.8	1381.9	1381.0	1379.9	1378.8	1377.7	1376.6
150°	1424.0	1424.0	1423.3	1422.8	1422.2	1421.6	1421.0	1420.4	1419.8	1419.2	1418.6
152.5°	1458.9	1458.4	1458.0	1457.7	1457.3	1457.0	1456.3	1455.5	1454.7	1453.8	1453.0
155°	1509.9	1508.7	1508.4	1508.1	1507.8	1507.5	1507.3	1507.3	1507.3	1507.3	1507.3
157.5°	1554.3	1553.1	1552.8	1552.6	1552.4	1552.1	1552.2	1552.6	1552.9	1553.3	1553.6
160°	1581.4	1579.9	1579.9	1579.9	1579.9	1579.9	1580.3	1580.8	1581.4	1582.1	1582.7
162.5°	1607.3	1605.8	1605.5	1605.3	1605.1	1604.8	1605.2	1606.0	1606.8	1607.7	1608.5
165°	1639.6	1637.8	1637.8	1637.8	1637.8	1637.8	1638.3	1639.1	1640.0	1640.9	1641.8
167.5°	1666.0	1664.1	1663.9	1663.7	1663.4	1663.2	1663.7	1664.8	1666.1	1667.2	1668.5
170°	1680.3	1678.1	1678.1	1678.1	1678.1	1678.1	1678.7	1679.9	1681.1	1682.3	1683.5
172.5°	1691.8	1690.0	1690.0	1690.0	1690.0	1690.0	1690.6	1691.8	1692.9	1694.2	1695.3
175°	1704.1	1702.4	1702.4	1702.4	1702.4	1702.4	1702.9	1704.1	1705.3	1706.6	1707.7
177.5°	1709.9	1708.5	1708.5	1708.5	1708.5	1708.5	1709.0	1709.9	1710.9	1711.9	1712.8
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	5.4	5.0	5.4	5.5	6.2	6.6	7.6	8.0	8.6	9.0	8.9
90°	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4	34.7
92.5°	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6	53.5
95°	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7	101.9
97.5°	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1	158.5
100°	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6	199.5
102.5°	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9	246.8
105°	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4	317.4
107.5°	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8	393.8
110°	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6	444.8



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4	495.8
115°	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1	573.5
117.5°	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8	651.8
120°	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3	704.0
122.5°	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6	756.8
125°	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5	835.4
127.5°	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5	912.9
130°	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6	964.4
132.5°	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9	1014.5
135°	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7	1089.5
137.5°	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0	1162.8
140°	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2	1210.9
142.5°	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4	1256.2
145°	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9	1322.5
147.5°	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3	1385.3
150°	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0	1424.0
152.5°	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9	1459.4
155°	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9	1511.1
157.5°	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3	1555.6
160°	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4	1583.0
162.5°	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3	1608.7
165°	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6	1641.4
167.5°	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0	1667.9
170°	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3	1682.3
172.5°	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8	1693.6
175°	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1	1705.9
177.5°	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9	1711.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	9.2	9.4	9.5	9.5	9.5	10.0	9.7
90°	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	445.9	447.2	447.5	446.8	446.3	445.7	445.1



TEST NUMBER: P332407-940

CATALOG NUMBER: S123RDIW-S340D1535U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)