

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332392-940

Luminaire Tested: **S123RDIW-S340D460U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332392-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D460U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2803.2 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	47	44	38	37	35	30
3	80	71	64	58	73	65	59	54	54	49	46	44	40	38	34	32	30	26
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26	22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	28	25	23	20
6	62	50	43	37	57	46	39	34	39	34	30	32	28	25	25	22	20	17
7	57	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	49	38	31	27	32	27	23	26	23	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13
10	46	35	28	23	42	32	26	21	27	22	19	23	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.7
10°-20°	133.9	4.8
20°-30°	192.7	6.9
30°-40°	217.1	7.7
40°-50°	207.7	7.4
50°-60°	170.1	6.1
60°-70°	114.8	4.1
70°-80°	57.7	2.1
80°-90°	16.8	0.6
90°-100°	19.6	0.7
100°-110°	93.4	3.3
110°-120°	224.4	8.0
120°-130°	285.8	10.2
130°-140°	305.4	10.9
140°-150°	285.5	10.2
150°-160°	230.3	8.2
160°-170°	148.7	5.3
170°-180°	51.2	1.8
0°-30°	374.7	13.4
0°-40°	591.8	21.1
0°-60°	969.6	34.6
0°-90°	1158.8	41.3
90°-120°	337.5	12.0
90°-150°	1214.2	43.3
90°-180°	1644.0	58.6
0°-180°	2803.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	0	4	10	11	12	2
95°	24	9	12	15	15	30
105°	119	122	88	21	18	127
115°	224	226	230	234	236	221
125°	316	319	320	321	322	282
135°	393	395	397	398	397	302
145°	454	456	457	458	458	284
155°	500	499	499	501	499	230
165°	527	526	525	528	526	149
175°	539	537	538	540	537	51
180°	539	539	539	539	539	



TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.0	7.4	6.8	6.2	5.5	5.4	5.5	5.8	6.0	6.2	6.2
90°	0.4	1.2	2.1	3.0	3.9	5.0	6.2	7.3	8.5	9.6	10.0
92.5°	7.5	7.2	7.0	6.7	6.4	6.8	7.7	8.5	9.4	10.3	10.8
95°	24.4	20.8	17.1	13.5	9.8	8.5	9.5	10.4	11.4	12.4	13.0
97.5°	49.1	47.4	45.8	44.2	42.5	38.5	32.1	25.7	19.4	12.9	13.6
100°	67.7	69.5	71.2	73.0	74.8	68.8	54.9	41.0	27.1	13.2	13.9
102.5°	88.8	90.2	91.4	92.7	94.0	87.0	71.9	56.7	41.6	26.4	24.2
105°	119.4	120.4	121.4	122.3	123.3	119.8	111.7	103.8	95.8	87.7	72.0
107.5°	151.6	152.4	153.2	153.9	154.7	155.8	157.0	158.3	159.5	160.8	149.3
110°	173.1	173.8	174.5	175.2	175.9	176.7	177.7	178.7	179.7	180.7	177.7



TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	193.6	194.2	194.8	195.5	196.2	197.0	198.0	198.9	199.9	200.9	200.9
115°	223.9	224.4	225.0	225.5	226.0	226.8	227.6	228.4	229.2	230.0	230.9
117.5°	253.3	254.0	254.7	255.3	256.0	256.5	256.9	257.3	257.8	258.2	258.9
120°	271.6	272.4	273.2	274.0	274.8	275.4	275.6	275.9	276.2	276.4	277.1
122.5°	290.3	290.9	291.5	292.2	292.8	293.4	293.7	294.0	294.4	294.7	295.2
125°	315.7	316.4	317.1	317.8	318.5	319.1	319.4	319.8	320.1	320.5	320.7
127.5°	340.4	341.1	341.8	342.5	343.2	343.8	344.2	344.6	345.1	345.5	345.8
130°	355.8	356.5	357.2	357.9	358.6	359.2	359.5	359.9	360.3	360.5	360.9
132.5°	370.5	371.2	371.9	372.6	373.4	373.8	374.2	374.4	374.7	375.0	375.3
135°	393.0	393.5	394.0	394.6	395.1	395.6	395.9	396.3	396.6	397.0	397.3
137.5°	412.2	413.0	413.6	414.3	414.9	415.4	415.6	415.8	416.0	416.2	416.6
140°	425.1	425.6	426.1	426.7	427.2	427.6	427.8	428.1	428.4	428.6	429.0
142.5°	436.9	437.5	438.0	438.5	439.1	439.4	439.7	440.0	440.2	440.5	440.8
145°	453.5	454.1	454.8	455.4	456.0	456.4	456.6	456.7	456.9	457.1	457.3
147.5°	469.1	469.6	469.9	470.4	470.7	471.1	471.3	471.4	471.6	471.8	472.0
150°	478.8	479.0	479.3	479.6	479.8	480.0	480.2	480.4	480.5	480.7	480.9
152.5°	487.4	487.5	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.5	488.7
155°	499.5	499.4	499.2	499.1	498.9	498.8	498.9	499.0	499.1	499.2	499.6
157.5°	509.1	509.0	509.0	509.0	509.0	508.9	508.8	508.7	508.6	508.5	509.1
160°	514.8	514.7	514.6	514.5	514.4	514.3	514.2	514.2	514.1	514.0	514.5
162.5°	520.2	520.0	519.8	519.6	519.3	519.2	519.1	519.0	518.9	518.8	519.4
165°	526.8	526.6	526.3	526.0	525.8	525.6	525.5	525.4	525.3	525.2	525.9
167.5°	532.0	531.6	531.3	530.9	530.6	530.4	530.4	530.4	530.4	530.4	531.1
170°	534.8	534.5	534.1	533.8	533.4	533.2	533.2	533.2	533.2	533.2	534.0
172.5°	536.7	536.4	535.9	535.5	535.0	534.8	534.9	535.0	535.1	535.1	535.8
175°	539.2	538.8	538.3	537.9	537.4	537.3	537.3	537.4	537.5	537.6	538.2
177.5°	539.8	539.5	539.1	538.8	538.4	538.3	538.4	538.4	538.5	538.6	539.1
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.1	6.1
90°	10.3	10.7	11.1	11.3	11.5	11.7	11.9	12.0
92.5°	11.4	11.9	12.6	12.8	13.0	13.1	13.2	13.3
95°	13.6	14.3	14.9	15.2	15.2	15.2	15.2	15.2
97.5°	14.4	15.1	15.8	16.1	16.2	16.3	16.4	16.5
100°	14.6	15.3	16.1	16.5	16.6	16.7	16.8	16.9
102.5°	21.9	19.7	17.6	16.5	16.7	16.9	16.9	17.1
105°	56.2	40.5	24.7	16.9	17.1	17.3	17.5	17.7
107.5°	137.7	126.2	114.6	102.9	91.0	79.1	67.2	55.4
110°	174.8	171.8	168.9	161.1	148.4	135.6	122.9	110.2



TEST NUMBER: P332392-940

CATALOG NUMBER: S123RDIW-S340D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	201.0	201.0	201.1	199.7	197.1	194.4	191.7	189.0
115°	231.8	232.6	233.5	234.2	234.5	234.9	235.2	235.6
117.5°	259.6	260.3	261.0	261.4	261.4	261.5	261.6	261.7
120°	277.9	278.6	279.3	279.6	279.6	279.6	279.6	279.6
122.5°	295.7	296.2	296.7	296.9	297.0	297.1	297.2	297.3
125°	320.8	321.0	321.2	321.4	321.6	321.7	321.9	322.1
127.5°	346.1	346.3	346.6	346.7	346.5	346.3	346.2	346.0
130°	361.2	361.6	361.9	362.0	361.9	361.7	361.5	361.3
132.5°	375.7	376.0	376.4	376.5	376.2	375.9	375.7	375.5
135°	397.5	397.8	398.1	398.1	397.8	397.5	397.3	397.0
137.5°	417.1	417.4	417.9	418.0	417.9	417.7	417.5	417.3
140°	429.4	429.7	430.1	430.2	430.0	429.8	429.6	429.4
142.5°	441.1	441.4	441.7	441.7	441.4	441.2	441.0	440.7
145°	457.4	457.6	457.8	457.9	457.9	457.9	457.9	457.9
147.5°	472.2	472.3	472.5	472.3	472.0	471.5	471.2	470.7
150°	481.1	481.3	481.4	481.4	481.2	480.9	480.6	480.4
152.5°	489.1	489.4	489.7	489.6	489.3	488.8	488.5	488.0
155°	500.1	500.5	501.0	500.9	500.3	499.8	499.3	498.8
157.5°	509.6	510.1	510.7	510.6	509.9	509.3	508.5	507.8
160°	515.1	515.6	516.1	516.1	515.5	514.9	514.2	513.6
162.5°	520.0	520.7	521.2	521.3	520.7	520.1	519.6	519.1
165°	526.6	527.4	528.1	528.1	527.4	526.9	526.3	525.7
167.5°	531.8	532.4	533.2	533.2	532.4	531.8	531.1	530.4
170°	534.7	535.4	536.1	536.1	535.4	534.7	534.0	533.2
172.5°	536.5	537.3	538.0	538.0	537.2	536.4	535.7	534.8
175°	538.9	539.5	540.1	540.1	539.4	538.7	538.0	537.3
177.5°	539.8	540.3	540.9	540.8	540.1	539.4	538.7	538.0
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2

(END OF REPORT)