

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332395-940

Luminaire Tested: **S123RDIW-S340D755U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332395-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U940-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3545.2 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34			34
1	95	91	87	84	85	82	79	76	66	64	62	51	50	48	37	37	36	30			30
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	33	32	31	25			25
3	79	70	63	58	71	64	58	53	52	47	44	40	37	35	30	28	27	22			22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19			19
5	67	56	48	42	60	51	44	39	41	36	33	33	29	26	24	22	20	17			17
6	61	50	42	37	55	45	39	34	37	32	29	29	26	23	22	20	18	15			15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	20	18	16	13			13
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	16	15	12			12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11			11
10	46	34	27	23	41	31	25	21	26	21	18	21	17	15	16	14	12	10			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5224	5224	5224	5224
5°	6227	5246	4620	5246
10°	7774	5216	4173	5216
15°	9126	5162	3806	5162
20°	10186	5082	3494	5082
25°	10023	4999	3301	4999
30°	7204	4922	3104	4922
35°	4809	4820	2975	4820
40°	3544	4700	2843	4700
45°	2973	4488	2714	4488
50°	2624	4210	2532	4210
55°	2301	3890	2284	3890
60°	2047	3587	2093	3587
65°	1798	3260	1946	3260
70°	1413	2968	1778	2968
75°	1243	2591	1626	2591
80°	1085	2201	1599	2201
85°	865	1778	1692	1778



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	1.3
10°-20°	149.1	4.2
20°-30°	234.2	6.6
30°-40°	244.4	6.9
40°-50°	209.1	5.9
50°-60°	159.4	4.5
60°-70°	102.2	2.9
70°-80°	49.1	1.4
80°-90°	15.5	0.4
90°-100°	54.9	1.5
100°-110°	164.3	4.6
110°-120°	279.4	7.9
120°-130°	367.5	10.4
130°-140°	413.1	11.7
140°-150°	406.1	11.5
150°-160°	341.9	9.6
160°-170°	227.6	6.4
170°-180°	79.7	2.2
0°-30°	431.1	12.2
0°-40°	675.4	19.1
0°-60°	1044.0	29.4
0°-90°	1210.8	34.2
90°-120°	498.6	14.1
90°-150°	1685.3	47.5
90°-180°	2334.0	65.8
0°-180°	3545.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	485	485	485	485	485	
5°	576	486	428	486	576	59
15°	819	463	342	463	819	232
25°	844	421	278	421	844	363
35°	366	367	226	367	366	240
45°	195	295	178	295	195	154
55°	123	207	122	207	123	111
65°	71	128	76	128	71	69
75°	30	62	39	62	30	32
85°	7	14	14	14	7	9
90°	20	1	20	1	20	10
95°	52	39	52	39	52	53
105°	158	149	158	149	158	167
115°	282	281	282	281	282	279
125°	407	412	407	412	407	364
135°	533	534	533	534	533	410
145°	648	648	648	648	648	404
155°	741	742	741	742	741	341
165°	806	808	806	808	806	227
175°	837	840	837	840	837	80
180°	843	843	843	843	843	



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	516.9	517.5	515.4	515.1	512.6	511.9	511.9	508.4	506.2	503.5	501.8
5°	576.3	579.6	577.9	574.3	568.0	566.5	562.6	556.3	549.3	540.6	536.5
7.5°	650.5	655.1	653.3	647.6	641.0	635.7	624.6	614.2	599.8	587.0	576.1
10°	711.3	706.6	702.8	697.2	691.2	681.4	669.8	653.8	635.3	620.7	604.6
12.5°	756.9	756.1	751.4	745.6	737.1	727.8	713.5	694.0	672.5	651.5	632.9
15°	818.9	820.2	817.1	811.1	799.0	782.6	761.0	752.9	722.1	699.3	676.5
17.5°	861.9	861.7	861.2	852.9	840.6	828.9	808.9	787.6	759.7	727.5	696.8
20°	889.2	887.1	887.5	878.2	869.1	855.5	836.0	805.0	782.2	745.0	713.2
22.5°	888.5	888.1	889.7	886.4	879.9	869.5	854.1	828.0	798.8	761.3	725.5
25°	843.9	842.2	851.9	854.7	865.3	867.2	862.6	848.3	820.6	781.9	737.7
27.5°	706.2	705.3	723.4	746.2	774.9	797.3	818.9	829.3	820.6	792.9	748.6
30°	579.6	599.1	608.3	641.1	677.7	721.3	759.6	795.9	804.9	792.7	756.4
32.5°	481.3	498.3	506.0	534.0	568.2	619.3	676.6	728.1	764.5	773.6	751.8
35°	366.0	366.2	383.7	396.2	427.8	480.3	536.0	604.9	673.5	725.5	730.8
37.5°	292.1	293.1	303.7	316.1	339.8	367.6	416.6	473.9	553.1	632.8	679.7
40°	252.2	254.0	262.0	274.2	291.2	312.3	350.4	404.5	470.6	559.3	631.8
42.5°	226.6	229.6	233.7	243.2	253.7	273.4	304.3	346.0	406.1	490.0	573.6
45°	195.3	197.0	200.1	204.5	214.0	227.7	248.4	276.5	326.4	393.9	477.6
47.5°	172.3	171.4	174.7	178.2	184.6	193.9	207.9	230.7	266.3	320.5	391.5
50°	156.7	156.4	158.7	161.4	167.5	174.3	185.7	203.0	231.2	276.1	341.2
52.5°	142.0	142.8	144.5	147.8	152.1	157.7	167.9	180.4	204.6	243.3	297.6
55°	122.6	123.2	125.5	127.3	130.5	136.1	142.5	152.9	169.5	196.5	241.2
57.5°	106.1	105.8	108.0	108.5	112.0	116.5	121.5	129.7	141.7	161.8	191.8
60°	95.1	94.5	96.4	97.8	99.7	103.4	107.6	115.5	125.1	139.8	165.6
62.5°	85.2	84.9	86.2	87.7	89.3	92.6	96.1	102.2	109.8	122.2	142.7
65°	70.6	71.2	71.9	72.5	73.3	75.4	78.7	82.9	88.1	96.8	111.6
67.5°	55.6	56.2	56.4	57.6	59.4	60.7	62.8	66.4	70.1	77.4	85.8
70°	44.9	44.7	44.9	45.5	47.8	50.0	52.8	55.5	57.8	63.0	70.0
72.5°	38.5	38.2	38.7	38.9	39.9	40.6	42.3	44.9	47.8	51.3	56.4
75°	29.9	29.9	29.9	29.9	30.8	31.1	31.7	32.4	33.4	35.1	38.9
77.5°	22.1	22.1	22.5	22.6	22.8	23.1	23.5	24.1	24.4	25.3	26.9
80°	17.5	17.7	17.5	17.7	17.7	18.1	18.3	18.9	19.1	20.2	20.8
82.5°	13.1	13.0	13.1	13.4	13.4	13.7	13.8	14.3	14.3	14.8	15.4
85°	7.0	6.7	7.0	6.9	7.3	6.9	7.0	7.5	7.5	7.7	8.6
87.5°	5.6	5.9	5.5	5.6	5.5	5.6	5.5	5.4	5.6	5.4	5.1
90°	19.9	19.5	19.3	19.0	18.6	18.3	17.7	17.0	16.5	15.9	14.0
92.5°	26.8	26.9	27.1	27.3	27.5	27.3	26.8	26.4	25.9	25.4	24.3
95°	51.6	51.6	51.6	51.6	51.6	51.4	50.7	50.1	49.6	49.0	47.8
97.5°	79.5	79.5	79.5	79.6	79.6	79.4	78.6	78.0	77.3	76.7	75.8
100°	100.6	100.3	100.0	99.7	99.4	99.1	98.6	98.2	97.7	97.3	96.6
102.5°	122.3	122.3	122.4	122.5	122.5	122.3	121.9	121.5	121.0	120.6	119.6
105°	157.6	157.2	156.9	156.7	156.3	156.2	156.2	156.2	156.2	156.2	154.9
107.5°	194.2	194.4	194.6	194.7	194.9	194.7	194.3	193.8	193.3	192.9	192.3
110°	219.1	219.4	219.6	220.0	220.3	220.1	219.5	218.9	218.4	217.8	217.5



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	245.6	245.6	245.7	245.8	245.8	245.5	244.8	244.1	243.3	242.6	242.5
115°	282.0	282.1	282.2	282.4	282.6	282.6	282.4	282.2	282.1	282.0	282.2
117.5°	318.9	319.3	319.7	320.1	320.6	320.7	320.7	320.8	320.8	320.8	321.3
120°	344.8	345.1	345.4	345.7	346.0	346.3	346.3	346.5	346.7	346.8	347.6
122.5°	369.7	370.1	370.5	371.0	371.4	371.8	372.1	372.6	372.9	373.3	373.7
125°	407.1	407.6	408.2	408.8	409.4	410.0	410.5	411.2	411.8	412.3	412.6
127.5°	444.3	445.0	445.6	446.3	446.9	447.7	448.5	449.3	450.1	451.0	451.3
130°	468.6	469.7	470.6	471.7	472.7	473.5	474.1	474.7	475.3	475.9	476.4
132.5°	494.0	494.8	495.6	496.4	497.2	497.9	498.6	499.4	500.1	500.8	501.1
135°	533.4	533.8	534.0	534.3	534.7	535.1	535.7	536.3	536.8	537.4	537.6
137.5°	568.3	568.8	569.4	570.0	570.5	571.1	571.7	572.3	572.9	573.5	573.2
140°	591.0	592.1	593.1	594.1	595.1	595.8	595.9	596.0	596.2	596.4	596.2
142.5°	614.3	615.1	615.9	616.7	617.5	618.0	618.1	618.3	618.4	618.6	618.3
145°	648.0	648.5	649.2	649.7	650.3	650.7	650.9	650.9	651.1	651.3	650.9
147.5°	677.9	678.8	679.7	680.6	681.4	681.9	681.9	681.9	681.9	681.9	681.4
150°	697.0	697.9	698.7	699.5	700.4	700.9	700.9	700.9	700.9	700.9	700.6
152.5°	715.5	716.2	717.0	717.7	718.5	718.8	718.5	718.4	718.1	717.8	717.6
155°	740.7	741.6	742.7	743.7	744.8	744.9	744.4	743.8	743.2	742.6	742.4
157.5°	763.5	764.4	765.2	766.0	766.8	767.0	766.3	765.7	765.1	764.5	764.4
160°	778.4	778.9	779.5	780.2	780.7	780.6	779.9	779.2	778.5	777.7	777.7
162.5°	789.4	790.4	791.4	792.3	793.3	793.4	792.6	791.8	791.1	790.4	790.3
165°	805.5	806.6	807.5	808.6	809.6	809.7	808.8	807.9	807.0	806.1	806.1
167.5°	819.1	820.0	820.9	821.9	822.8	822.8	821.9	820.9	820.0	819.1	819.0
170°	826.0	827.1	828.0	829.1	830.1	830.1	829.1	828.0	827.1	826.0	826.0
172.5°	831.3	832.3	833.4	834.4	835.4	835.4	834.6	833.7	832.8	831.8	831.8
175°	837.2	838.3	839.3	840.3	841.4	841.4	840.5	839.7	838.8	837.9	837.9
177.5°	840.4	841.2	842.0	842.9	843.7	843.8	843.1	842.4	841.7	841.0	841.0
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	501.1	500.6	498.3	495.6	492.1	489.8	487.9	487.0	483.9	480.3	477.9
5°	532.1	525.8	519.2	511.0	503.5	495.9	491.2	485.5	478.7	471.0	465.6
7.5°	565.2	552.9	539.8	526.2	512.8	500.8	490.1	481.0	470.1	459.1	451.4
10°	590.7	572.7	554.3	535.4	518.2	501.9	489.5	477.2	464.1	451.5	441.8
12.5°	613.8	590.2	568.9	545.6	523.6	504.3	486.3	471.9	456.1	442.6	431.8
15°	643.0	618.8	593.2	557.8	528.5	504.0	482.1	463.2	444.2	427.6	417.0
17.5°	670.3	634.1	599.4	570.0	531.9	501.3	474.7	452.1	431.1	413.5	400.4
20°	681.6	646.5	608.9	571.3	534.0	499.6	468.7	443.7	422.0	402.0	389.9
22.5°	688.4	648.7	609.0	568.6	529.0	493.3	462.7	435.2	411.6	392.7	377.8
25°	696.3	649.0	605.4	565.5	525.0	486.3	450.0	420.9	395.4	375.2	359.4
27.5°	701.6	645.9	594.3	550.0	508.9	470.5	437.1	406.3	380.3	359.0	342.1
30°	702.6	643.4	585.9	537.9	496.1	460.7	425.4	396.0	368.5	345.9	330.1
32.5°	703.9	637.2	574.4	523.4	480.6	445.7	413.7	385.5	357.4	335.1	319.0
35°	698.5	633.8	557.0	498.4	455.6	421.7	392.9	366.8	339.3	317.6	301.2
37.5°	674.8	620.4	539.0	470.2	425.4	394.1	370.6	347.9	322.6	299.3	283.8
40°	651.1	607.1	525.0	453.1	406.4	374.2	352.9	334.5	310.0	288.1	271.5
42.5°	615.7	588.9	511.7	435.2	384.8	353.7	335.8	318.5	297.0	274.8	259.2
45°	550.7	554.3	484.5	406.5	354.8	323.7	306.8	294.8	275.7	257.4	241.4
47.5°	469.3	502.3	452.5	376.1	323.3	294.1	279.4	268.9	255.9	238.0	223.4
50°	416.2	463.2	427.0	355.7	303.5	274.5	259.9	251.4	240.1	226.0	212.1
52.5°	367.1	417.8	396.0	332.9	282.0	255.5	241.3	234.3	225.3	212.0	199.5
55°	299.3	350.7	345.7	298.5	249.9	226.0	215.3	207.3	201.3	191.4	181.4
57.5°	242.2	290.8	293.4	260.3	221.6	198.0	188.7	182.7	178.8	171.3	162.0
60°	206.1	250.7	259.5	234.5	201.3	180.6	171.4	166.6	163.5	157.5	150.4
62.5°	176.2	214.2	224.1	206.2	181.9	162.4	155.2	150.7	148.6	143.4	137.1
65°	134.8	166.4	175.9	166.0	153.3	137.8	131.9	128.0	126.1	123.2	118.6
67.5°	101.4	124.4	134.9	127.9	123.2	113.4	109.8	107.6	105.9	104.0	100.1
70°	81.4	98.4	109.2	107.5	103.7	98.4	95.8	94.3	92.6	91.0	87.7
72.5°	65.5	77.2	87.3	88.3	85.2	84.2	81.8	81.1	80.2	78.2	76.3
75°	43.4	51.5	58.6	61.3	62.5	63.6	62.5	62.3	62.2	60.5	59.4
77.5°	28.4	32.8	37.3	41.9	43.9	45.2	45.6	46.4	45.7	44.9	44.4
80°	21.8	22.8	25.9	29.9	33.0	34.2	35.1	35.5	35.3	35.1	34.2
82.5°	15.9	16.7	18.2	21.0	23.5	25.6	26.1	26.0	26.5	26.7	25.9
85°	8.6	8.7	9.2	9.5	11.0	13.3	13.9	14.4	14.7	14.7	13.5
87.5°	5.1	4.5	4.5	4.1	4.4	4.2	4.9	5.4	5.9	5.5	5.8
90°	12.0	10.2	8.2	6.5	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	23.3	22.1	21.0	20.0	19.0	18.0	17.0	16.1	17.0	18.0	19.0
95°	46.6	45.5	44.2	43.2	42.2	41.1	40.0	39.1	40.0	41.1	42.2
97.5°	74.9	74.1	73.2	72.4	71.7	70.9	70.1	69.4	70.1	70.9	71.7
100°	95.9	95.1	94.3	93.5	92.6	91.8	90.9	90.0	90.9	91.8	92.6
102.5°	118.7	117.7	116.7	115.9	115.4	114.9	114.4	113.9	114.4	114.9	115.4
105°	153.6	152.2	150.9	150.1	149.8	149.5	149.2	148.9	149.2	149.5	149.8
107.5°	191.8	191.3	190.7	190.4	190.2	190.0	189.8	189.7	189.8	190.0	190.2
110°	217.1	216.9	216.6	216.2	216.0	215.7	215.4	215.1	215.4	215.7	216.0



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	242.5	242.5	242.4	242.3	242.1	241.9	241.7	241.6	241.7	241.9	242.1
115°	282.6	282.9	283.1	283.0	282.6	282.1	281.7	281.3	281.7	282.1	282.6
117.5°	321.6	322.0	322.4	322.4	322.2	321.8	321.6	321.3	321.6	321.8	322.2
120°	348.3	349.0	349.7	349.7	348.8	347.9	347.1	346.2	347.1	347.9	348.8
122.5°	374.1	374.4	374.8	374.7	374.1	373.4	372.7	372.1	372.7	373.4	374.1
125°	413.0	413.2	413.5	413.5	413.0	412.6	412.1	411.7	412.1	412.6	413.0
127.5°	451.7	452.0	452.3	452.0	451.0	450.1	449.2	448.2	449.2	450.1	451.0
130°	476.8	477.2	477.7	477.2	476.1	474.9	473.8	472.6	473.8	474.9	476.1
132.5°	501.4	501.8	502.0	501.7	500.4	499.3	498.1	497.0	498.1	499.3	500.4
135°	537.7	537.9	538.1	537.6	536.8	535.9	535.0	534.1	535.0	535.9	536.8
137.5°	572.8	572.4	572.0	571.5	570.8	570.0	569.3	568.6	569.3	570.0	570.8
140°	596.0	595.9	595.8	595.3	594.6	593.9	593.1	592.4	593.1	593.9	594.6
142.5°	618.0	617.8	617.5	617.0	616.3	615.5	614.8	614.1	614.8	615.5	616.3
145°	650.4	650.0	649.5	649.2	648.8	648.5	648.3	648.0	648.3	648.5	648.8
147.5°	681.0	680.6	680.2	679.8	679.2	678.7	678.1	677.6	678.1	678.7	679.2
150°	700.3	700.0	699.7	699.5	699.2	698.8	698.6	698.3	698.6	698.8	699.2
152.5°	717.5	717.3	717.1	716.8	716.5	716.0	715.6	715.2	715.6	716.0	716.5
155°	742.3	742.2	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0	742.0
157.5°	764.2	764.1	764.0	764.0	764.2	764.4	764.6	764.7	764.6	764.4	764.2
160°	777.7	777.7	777.7	777.8	778.1	778.5	778.7	779.0	778.7	778.5	778.1
162.5°	790.1	790.1	790.0	790.1	790.5	790.9	791.3	791.8	791.3	790.9	790.5
165°	806.1	806.1	806.1	806.4	806.8	807.3	807.7	808.2	807.7	807.3	806.8
167.5°	818.9	818.8	818.7	818.9	819.5	820.1	820.6	821.3	820.6	820.1	819.5
170°	826.0	826.0	826.0	826.3	826.9	827.5	828.0	828.7	828.0	827.5	826.9
172.5°	831.8	831.8	831.8	832.1	832.7	833.3	833.9	834.5	833.9	833.3	832.7
175°	837.9	837.9	837.9	838.2	838.8	839.4	840.0	840.5	840.0	839.4	838.8
177.5°	841.0	841.0	841.0	841.2	841.7	842.1	842.6	843.1	842.6	842.1	841.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	477.0	474.8	473.3	470.0	467.9	465.6	463.2	464.7	464.5	464.4	464.4
5°	461.0	456.2	451.8	446.2	442.7	438.4	435.1	434.6	435.4	432.6	430.9
7.5°	445.1	438.6	432.4	426.2	419.6	414.4	411.2	409.6	407.5	405.7	403.9
10°	434.0	426.3	420.3	412.6	405.6	399.3	395.4	392.6	391.2	389.8	387.0
12.5°	422.5	415.0	407.3	398.6	391.9	384.7	381.7	378.7	375.9	374.3	370.6
15°	405.7	396.0	387.9	378.7	371.2	364.2	360.1	354.0	353.2	351.1	347.3
17.5°	388.9	378.4	367.1	360.3	352.0	344.6	338.2	336.3	330.3	328.1	324.8
20°	375.6	365.9	357.3	348.4	336.2	329.3	324.3	321.6	316.8	313.9	311.8
22.5°	364.2	354.2	344.4	333.9	323.9	316.1	312.5	308.3	305.7	301.6	299.3
25°	347.8	337.0	325.1	313.9	306.7	300.9	295.0	291.2	287.5	285.6	281.5
27.5°	328.8	317.4	306.4	297.8	288.9	283.2	277.9	274.6	270.1	267.0	264.7
30°	318.3	305.0	295.4	287.8	276.3	270.9	267.0	262.8	259.5	256.2	253.9
32.5°	306.1	294.0	285.0	275.4	266.7	260.7	255.7	252.0	249.1	246.0	243.7
35°	287.1	277.0	267.6	258.1	251.6	245.6	239.5	236.4	233.7	230.8	228.7
37.5°	269.9	260.4	251.5	242.5	234.4	229.5	224.7	222.3	218.6	216.7	214.6
40°	259.3	249.9	240.4	231.7	223.4	219.6	215.3	211.7	208.4	206.9	204.6
42.5°	247.6	238.3	230.2	220.9	214.0	208.9	204.9	201.1	198.6	196.4	195.2
45°	230.4	222.1	214.2	204.8	198.4	194.0	189.5	185.9	183.7	182.2	179.9
47.5°	213.7	205.4	197.3	189.2	183.0	178.0	173.3	170.9	167.9	166.1	164.6
50°	201.5	194.0	185.6	178.1	171.8	166.8	163.1	160.0	157.3	155.0	153.9
52.5°	190.4	182.4	175.0	168.1	161.5	155.9	152.5	149.2	147.1	144.5	143.3
55°	172.0	164.3	158.1	151.2	144.8	140.0	135.9	133.0	130.9	128.0	126.4
57.5°	154.8	147.8	140.4	134.5	127.9	123.9	120.4	116.5	113.9	111.6	109.9
60°	143.1	135.3	128.8	123.2	117.3	112.2	109.1	105.9	103.3	100.9	99.5
62.5°	131.0	124.1	118.0	111.9	106.6	102.0	98.4	95.9	93.5	92.0	90.5
65°	112.4	107.0	100.8	95.8	90.8	87.5	84.5	82.3	80.6	79.5	78.3
67.5°	95.2	90.1	84.6	79.7	76.3	73.8	72.0	70.0	69.1	67.8	67.0
70°	84.2	78.7	73.9	70.2	66.9	65.0	63.8	62.3	61.5	59.8	59.0
72.5°	72.1	68.1	64.6	61.6	58.9	57.2	55.6	53.9	52.5	50.6	49.8
75°	56.7	53.1	50.5	48.4	46.7	44.5	42.2	40.3	39.7	39.1	38.9
77.5°	42.0	39.8	37.8	36.0	34.0	32.4	31.8	31.4	31.3	30.9	30.9
80°	33.0	30.9	29.5	27.5	26.2	26.2	26.2	25.8	25.9	25.9	25.9
82.5°	24.5	22.6	21.8	21.1	20.9	21.0	21.0	21.1	21.0	21.3	21.1
85°	12.7	12.8	13.3	13.1	13.3	13.3	13.7	13.5	13.7	13.3	13.7
87.5°	6.0	6.8	7.3	7.9	8.5	8.6	8.9	9.1	9.4	9.5	9.5
90°	6.5	8.2	10.2	12.0	14.0	15.9	16.5	17.0	17.7	18.3	18.6
92.5°	20.0	21.0	22.1	23.3	24.3	25.4	25.9	26.4	26.8	27.3	27.5
95°	43.2	44.2	45.5	46.6	47.8	49.0	49.6	50.1	50.7	51.4	51.6
97.5°	72.4	73.2	74.1	74.9	75.8	76.7	77.3	78.0	78.6	79.4	79.6
100°	93.5	94.3	95.1	95.9	96.6	97.3	97.7	98.2	98.6	99.1	99.4
102.5°	115.9	116.7	117.7	118.7	119.6	120.6	121.0	121.5	121.9	122.3	122.5
105°	150.1	150.9	152.2	153.6	154.9	156.2	156.2	156.2	156.2	156.2	156.3
107.5°	190.4	190.7	191.3	191.8	192.3	192.9	193.3	193.8	194.3	194.7	194.9
110°	216.2	216.6	216.9	217.1	217.5	217.8	218.4	218.9	219.5	220.1	220.3



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	242.3	242.4	242.5	242.5	242.5	242.6	243.3	244.1	244.8	245.5	245.8
115°	283.0	283.1	282.9	282.6	282.2	282.0	282.1	282.2	282.4	282.6	282.6
117.5°	322.4	322.4	322.0	321.6	321.3	320.8	320.8	320.8	320.7	320.7	320.6
120°	349.7	349.7	349.0	348.3	347.6	346.8	346.7	346.5	346.3	346.3	346.0
122.5°	374.7	374.8	374.4	374.1	373.7	373.3	372.9	372.6	372.1	371.8	371.4
125°	413.5	413.5	413.2	413.0	412.6	412.3	411.8	411.2	410.5	410.0	409.4
127.5°	452.0	452.3	452.0	451.7	451.3	451.0	450.1	449.3	448.5	447.7	446.9
130°	477.2	477.7	477.2	476.8	476.4	475.9	475.3	474.7	474.1	473.5	472.7
132.5°	501.7	502.0	501.8	501.4	501.1	500.8	500.1	499.4	498.6	497.9	497.2
135°	537.6	538.1	537.9	537.7	537.6	537.4	536.8	536.3	535.7	535.1	534.7
137.5°	571.5	572.0	572.4	572.8	573.2	573.5	572.9	572.3	571.7	571.1	570.5
140°	595.3	595.8	595.9	596.0	596.2	596.4	596.2	596.0	595.9	595.8	595.1
142.5°	617.0	617.5	617.8	618.0	618.3	618.6	618.4	618.3	618.1	618.0	617.5
145°	649.2	649.5	650.0	650.4	650.9	651.3	651.1	650.9	650.9	650.7	650.3
147.5°	679.8	680.2	680.6	681.0	681.4	681.9	681.9	681.9	681.9	681.9	681.4
150°	699.5	699.7	700.0	700.3	700.6	700.9	700.9	700.9	700.9	700.9	700.4
152.5°	716.8	717.1	717.3	717.5	717.6	717.8	718.1	718.4	718.5	718.8	718.5
155°	742.0	742.0	742.2	742.3	742.4	742.6	743.2	743.8	744.4	744.9	744.8
157.5°	764.0	764.0	764.1	764.2	764.4	764.5	765.1	765.7	766.3	767.0	766.8
160°	777.8	777.7	777.7	777.7	777.7	777.7	778.5	779.2	779.9	780.6	780.7
162.5°	790.1	790.0	790.1	790.1	790.3	790.4	791.1	791.8	792.6	793.4	793.3
165°	806.4	806.1	806.1	806.1	806.1	806.1	807.0	807.9	808.8	809.7	809.6
167.5°	818.9	818.7	818.8	818.9	819.0	819.1	820.0	820.9	821.9	822.8	822.8
170°	826.3	826.0	826.0	826.0	826.0	826.0	827.1	828.0	829.1	830.1	830.1
172.5°	832.1	831.8	831.8	831.8	831.8	831.8	832.8	833.7	834.6	835.4	835.4
175°	838.2	837.9	837.9	837.9	837.9	837.9	838.8	839.7	840.5	841.4	841.4
177.5°	841.2	841.0	841.0	841.0	841.0	841.0	841.7	842.4	843.1	843.8	843.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	462.4	462.2	462.4	461.7	462.4	462.2	462.4	464.4	464.4	464.5	464.7
5°	430.3	430.1	429.4	427.6	429.4	430.1	430.3	430.9	432.6	435.4	434.6
7.5°	402.2	401.9	400.1	400.1	400.1	401.9	402.2	403.9	405.7	407.5	409.6
10°	385.6	385.8	383.3	381.8	383.3	385.8	385.6	387.0	389.8	391.2	392.6
12.5°	369.4	368.5	366.5	364.9	366.5	368.5	369.4	370.6	374.3	375.9	378.7
15°	348.2	346.1	341.2	341.5	341.2	346.1	348.2	347.3	351.1	353.2	354.0
17.5°	323.2	321.6	321.6	318.6	321.6	321.6	323.2	324.8	328.1	330.3	336.3
20°	308.5	307.5	307.9	305.0	307.9	307.5	308.5	311.8	313.9	316.8	321.6
22.5°	297.0	296.0	294.3	293.4	294.3	296.0	297.0	299.3	301.6	305.7	308.3
25°	280.3	278.6	277.0	277.9	277.0	278.6	280.3	281.5	285.6	287.5	291.2
27.5°	263.5	262.3	260.6	260.4	260.6	262.3	263.5	264.7	267.0	270.1	274.6
30°	252.8	251.6	250.7	249.7	250.7	251.6	252.8	253.9	256.2	259.5	262.8
32.5°	242.0	241.7	240.3	240.0	240.3	241.7	242.0	243.7	246.0	249.1	252.0
35°	227.9	226.7	226.2	226.4	226.2	226.7	227.9	228.7	230.8	233.7	236.4
37.5°	214.5	212.9	212.0	211.3	212.0	212.9	214.5	214.6	216.7	218.6	222.3
40°	204.8	203.2	202.8	202.3	202.8	203.2	204.8	204.6	206.9	208.4	211.7
42.5°	194.0	193.4	193.1	192.3	193.1	193.4	194.0	195.2	196.4	198.6	201.1
45°	179.3	179.1	177.8	178.3	177.8	179.1	179.3	179.9	182.2	183.7	185.9
47.5°	163.7	162.8	161.9	162.6	161.9	162.8	163.7	164.6	166.1	167.9	170.9
50°	153.1	152.7	150.8	151.2	150.8	152.7	153.1	153.9	155.0	157.3	160.0
52.5°	142.5	140.9	140.2	139.9	140.2	140.9	142.5	143.3	144.5	147.1	149.2
55°	124.8	123.0	122.2	121.7	122.2	123.0	124.8	126.4	128.0	130.9	133.0
57.5°	107.5	107.1	106.4	106.8	106.4	107.1	107.5	109.9	111.6	113.9	116.5
60°	97.5	97.5	97.5	97.2	97.5	97.5	97.5	99.5	100.9	103.3	105.9
62.5°	89.6	89.1	89.0	89.3	89.0	89.1	89.6	90.5	92.0	93.5	95.9
65°	77.7	77.5	76.7	76.4	76.7	77.5	77.7	78.3	79.5	80.6	82.3
67.5°	66.4	65.7	65.5	65.2	65.5	65.7	66.4	67.0	67.8	69.1	70.0
70°	58.0	57.5	56.3	56.5	56.3	57.5	58.0	59.0	59.8	61.5	62.3
72.5°	48.9	48.4	48.2	47.9	48.2	48.4	48.9	49.8	50.6	52.5	53.9
75°	38.6	38.4	38.3	39.1	38.3	38.4	38.6	38.9	39.1	39.7	40.3
77.5°	30.9	30.9	31.1	30.8	31.1	30.9	30.9	30.9	30.9	31.3	31.4
80°	25.9	25.9	25.8	25.8	25.8	25.9	25.9	25.9	25.9	25.9	25.8
82.5°	20.8	21.0	21.1	20.8	21.1	21.0	20.8	21.1	21.3	21.0	21.1
85°	13.7	13.5	13.9	13.7	13.9	13.5	13.7	13.7	13.3	13.7	13.5
87.5°	10.0	9.6	9.7	10.0	9.7	9.6	10.0	9.5	9.5	9.4	9.1
90°	19.0	19.3	19.5	19.9	19.5	19.3	19.0	18.6	18.3	17.7	17.0
92.5°	27.3	27.1	26.9	26.8	26.9	27.1	27.3	27.5	27.3	26.8	26.4
95°	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.6	51.4	50.7	50.1
97.5°	79.6	79.5	79.5	79.5	79.5	79.5	79.6	79.6	79.4	78.6	78.0
100°	99.7	100.0	100.3	100.6	100.3	100.0	99.7	99.4	99.1	98.6	98.2
102.5°	122.5	122.4	122.3	122.3	122.3	122.4	122.5	122.5	122.3	121.9	121.5
105°	156.7	156.9	157.2	157.6	157.2	156.9	156.7	156.3	156.2	156.2	156.2
107.5°	194.7	194.6	194.4	194.2	194.4	194.6	194.7	194.9	194.7	194.3	193.8
110°	220.0	219.6	219.4	219.1	219.4	219.6	220.0	220.3	220.1	219.5	218.9



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	245.8	245.7	245.6	245.6	245.6	245.7	245.8	245.8	245.5	244.8	244.1
115°	282.4	282.2	282.1	282.0	282.1	282.2	282.4	282.6	282.6	282.4	282.2
117.5°	320.1	319.7	319.3	318.9	319.3	319.7	320.1	320.6	320.7	320.7	320.8
120°	345.7	345.4	345.1	344.8	345.1	345.4	345.7	346.0	346.3	346.3	346.5
122.5°	371.0	370.5	370.1	369.7	370.1	370.5	371.0	371.4	371.8	372.1	372.6
125°	408.8	408.2	407.6	407.1	407.6	408.2	408.8	409.4	410.0	410.5	411.2
127.5°	446.3	445.6	445.0	444.3	445.0	445.6	446.3	446.9	447.7	448.5	449.3
130°	471.7	470.6	469.7	468.6	469.7	470.6	471.7	472.7	473.5	474.1	474.7
132.5°	496.4	495.6	494.8	494.0	494.8	495.6	496.4	497.2	497.9	498.6	499.4
135°	534.3	534.0	533.8	533.4	533.8	534.0	534.3	534.7	535.1	535.7	536.3
137.5°	570.0	569.4	568.8	568.3	568.8	569.4	570.0	570.5	571.1	571.7	572.3
140°	594.1	593.1	592.1	591.0	592.1	593.1	594.1	595.1	595.8	595.9	596.0
142.5°	616.7	615.9	615.1	614.3	615.1	615.9	616.7	617.5	618.0	618.1	618.3
145°	649.7	649.2	648.5	648.0	648.5	649.2	649.7	650.3	650.7	650.9	650.9
147.5°	680.6	679.7	678.8	677.9	678.8	679.7	680.6	681.4	681.9	681.9	681.9
150°	699.5	698.7	697.9	697.0	697.9	698.7	699.5	700.4	700.9	700.9	700.9
152.5°	717.7	717.0	716.2	715.5	716.2	717.0	717.7	718.5	718.8	718.5	718.4
155°	743.7	742.7	741.6	740.7	741.6	742.7	743.7	744.8	744.9	744.4	743.8
157.5°	766.0	765.2	764.4	763.5	764.4	765.2	766.0	766.8	767.0	766.3	765.7
160°	780.2	779.5	778.9	778.4	778.9	779.5	780.2	780.7	780.6	779.9	779.2
162.5°	792.3	791.4	790.4	789.4	790.4	791.4	792.3	793.3	793.4	792.6	791.8
165°	808.6	807.5	806.6	805.5	806.6	807.5	808.6	809.6	809.7	808.8	807.9
167.5°	821.9	820.9	820.0	819.1	820.0	820.9	821.9	822.8	822.8	821.9	820.9
170°	829.1	828.0	827.1	826.0	827.1	828.0	829.1	830.1	830.1	829.1	828.0
172.5°	834.4	833.4	832.3	831.3	832.3	833.4	834.4	835.4	835.4	834.6	833.7
175°	840.3	839.3	838.3	837.2	838.3	839.3	840.3	841.4	841.4	840.5	839.7
177.5°	842.9	842.0	841.2	840.4	841.2	842.0	842.9	843.7	843.8	843.1	842.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	463.2	465.6	467.9	470.0	473.3	474.8	477.0	477.9	480.3	483.9	487.0
5°	435.1	438.4	442.7	446.2	451.8	456.2	461.0	465.6	471.0	478.7	485.5
7.5°	411.2	414.4	419.6	426.2	432.4	438.6	445.1	451.4	459.1	470.1	481.0
10°	395.4	399.3	405.6	412.6	420.3	426.3	434.0	441.8	451.5	464.1	477.2
12.5°	381.7	384.7	391.9	398.6	407.3	415.0	422.5	431.8	442.6	456.1	471.9
15°	360.1	364.2	371.2	378.7	387.9	396.0	405.7	417.0	427.6	444.2	463.2
17.5°	338.2	344.6	352.0	360.3	367.1	378.4	388.9	400.4	413.5	431.1	452.1
20°	324.3	329.3	336.2	348.4	357.3	365.9	375.6	389.9	402.0	422.0	443.7
22.5°	312.5	316.1	323.9	333.9	344.4	354.2	364.2	377.8	392.7	411.6	435.2
25°	295.0	300.9	306.7	313.9	325.1	337.0	347.8	359.4	375.2	395.4	420.9
27.5°	277.9	283.2	288.9	297.8	306.4	317.4	328.8	342.1	359.0	380.3	406.3
30°	267.0	270.9	276.3	287.8	295.4	305.0	318.3	330.1	345.9	368.5	396.0
32.5°	255.7	260.7	266.7	275.4	285.0	294.0	306.1	319.0	335.1	357.4	385.5
35°	239.5	245.6	251.6	258.1	267.6	277.0	287.1	301.2	317.6	339.3	366.8
37.5°	224.7	229.5	234.4	242.5	251.5	260.4	269.9	283.8	299.3	322.6	347.9
40°	215.3	219.6	223.4	231.7	240.4	249.9	259.3	271.5	288.1	310.0	334.5
42.5°	204.9	208.9	214.0	220.9	230.2	238.3	247.6	259.2	274.8	297.0	318.5
45°	189.5	194.0	198.4	204.8	214.2	222.1	230.4	241.4	257.4	275.7	294.8
47.5°	173.3	178.0	183.0	189.2	197.3	205.4	213.7	223.4	238.0	255.9	268.9
50°	163.1	166.8	171.8	178.1	185.6	194.0	201.5	212.1	226.0	240.1	251.4
52.5°	152.5	155.9	161.5	168.1	175.0	182.4	190.4	199.5	212.0	225.3	234.3
55°	135.9	140.0	144.8	151.2	158.1	164.3	172.0	181.4	191.4	201.3	207.3
57.5°	120.4	123.9	127.9	134.5	140.4	147.8	154.8	162.0	171.3	178.8	182.7
60°	109.1	112.2	117.3	123.2	128.8	135.3	143.1	150.4	157.5	163.5	166.6
62.5°	98.4	102.0	106.6	111.9	118.0	124.1	131.0	137.1	143.4	148.6	150.7
65°	84.5	87.5	90.8	95.8	100.8	107.0	112.4	118.6	123.2	126.1	128.0
67.5°	72.0	73.8	76.3	79.7	84.6	90.1	95.2	100.1	104.0	105.9	107.6
70°	63.8	65.0	66.9	70.2	73.9	78.7	84.2	87.7	91.0	92.6	94.3
72.5°	55.6	57.2	58.9	61.6	64.6	68.1	72.1	76.3	78.2	80.2	81.1
75°	42.2	44.5	46.7	48.4	50.5	53.1	56.7	59.4	60.5	62.2	62.3
77.5°	31.8	32.4	34.0	36.0	37.8	39.8	42.0	44.4	44.9	45.7	46.4
80°	26.2	26.2	26.2	27.5	29.5	30.9	33.0	34.2	35.1	35.3	35.5
82.5°	21.0	21.0	20.9	21.1	21.8	22.6	24.5	25.9	26.7	26.5	26.0
85°	13.7	13.3	13.3	13.1	13.3	12.8	12.7	13.5	14.7	14.7	14.4
87.5°	8.9	8.6	8.5	7.9	7.3	6.8	6.0	5.8	5.5	5.9	5.4
90°	16.5	15.9	14.0	12.0	10.2	8.2	6.5	5.1	3.6	2.1	0.6
92.5°	25.9	25.4	24.3	23.3	22.1	21.0	20.0	19.0	18.0	17.0	16.1
95°	49.6	49.0	47.8	46.6	45.5	44.2	43.2	42.2	41.1	40.0	39.1
97.5°	77.3	76.7	75.8	74.9	74.1	73.2	72.4	71.7	70.9	70.1	69.4
100°	97.7	97.3	96.6	95.9	95.1	94.3	93.5	92.6	91.8	90.9	90.0
102.5°	121.0	120.6	119.6	118.7	117.7	116.7	115.9	115.4	114.9	114.4	113.9
105°	156.2	156.2	154.9	153.6	152.2	150.9	150.1	149.8	149.5	149.2	148.9
107.5°	193.3	192.9	192.3	191.8	191.3	190.7	190.4	190.2	190.0	189.8	189.7
110°	218.4	217.8	217.5	217.1	216.9	216.6	216.2	216.0	215.7	215.4	215.1



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	243.3	242.6	242.5	242.5	242.5	242.4	242.3	242.1	241.9	241.7	241.6
115°	282.1	282.0	282.2	282.6	282.9	283.1	283.0	282.6	282.1	281.7	281.3
117.5°	320.8	320.8	321.3	321.6	322.0	322.4	322.4	322.2	321.8	321.6	321.3
120°	346.7	346.8	347.6	348.3	349.0	349.7	349.7	348.8	347.9	347.1	346.2
122.5°	372.9	373.3	373.7	374.1	374.4	374.8	374.7	374.1	373.4	372.7	372.1
125°	411.8	412.3	412.6	413.0	413.2	413.5	413.5	413.0	412.6	412.1	411.7
127.5°	450.1	451.0	451.3	451.7	452.0	452.3	452.0	451.0	450.1	449.2	448.2
130°	475.3	475.9	476.4	476.8	477.2	477.7	477.2	476.1	474.9	473.8	472.6
132.5°	500.1	500.8	501.1	501.4	501.8	502.0	501.7	500.4	499.3	498.1	497.0
135°	536.8	537.4	537.6	537.7	537.9	538.1	537.6	536.8	535.9	535.0	534.1
137.5°	572.9	573.5	573.2	572.8	572.4	572.0	571.5	570.8	570.0	569.3	568.6
140°	596.2	596.4	596.2	596.0	595.9	595.8	595.3	594.6	593.9	593.1	592.4
142.5°	618.4	618.6	618.3	618.0	617.8	617.5	617.0	616.3	615.5	614.8	614.1
145°	651.1	651.3	650.9	650.4	650.0	649.5	649.2	648.8	648.5	648.3	648.0
147.5°	681.9	681.9	681.4	681.0	680.6	680.2	679.8	679.2	678.7	678.1	677.6
150°	700.9	700.9	700.6	700.3	700.0	699.7	699.5	699.2	698.8	698.6	698.3
152.5°	718.1	717.8	717.6	717.5	717.3	717.1	716.8	716.5	716.0	715.6	715.2
155°	743.2	742.6	742.4	742.3	742.2	742.0	742.0	742.0	742.0	742.0	742.0
157.5°	765.1	764.5	764.4	764.2	764.1	764.0	764.0	764.2	764.4	764.6	764.7
160°	778.5	777.7	777.7	777.7	777.7	777.7	777.8	778.1	778.5	778.7	779.0
162.5°	791.1	790.4	790.3	790.1	790.1	790.0	790.1	790.5	790.9	791.3	791.8
165°	807.0	806.1	806.1	806.1	806.1	806.1	806.4	806.8	807.3	807.7	808.2
167.5°	820.0	819.1	819.0	818.9	818.8	818.7	818.9	819.5	820.1	820.6	821.3
170°	827.1	826.0	826.0	826.0	826.0	826.0	826.3	826.9	827.5	828.0	828.7
172.5°	832.8	831.8	831.8	831.8	831.8	831.8	832.1	832.7	833.3	833.9	834.5
175°	838.8	837.9	837.9	837.9	837.9	837.9	838.2	838.8	839.4	840.0	840.5
177.5°	841.7	841.0	841.0	841.0	841.0	841.0	841.2	841.7	842.1	842.6	843.1
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	487.9	489.8	492.1	495.6	498.3	500.6	501.1	501.8	503.5	506.2	508.4
5°	491.2	495.9	503.5	511.0	519.2	525.8	532.1	536.5	540.6	549.3	556.3
7.5°	490.1	500.8	512.8	526.2	539.8	552.9	565.2	576.1	587.0	599.8	614.2
10°	489.5	501.9	518.2	535.4	554.3	572.7	590.7	604.6	620.7	635.3	653.8
12.5°	486.3	504.3	523.6	545.6	568.9	590.2	613.8	632.9	651.5	672.5	694.0
15°	482.1	504.0	528.5	557.8	593.2	618.8	643.0	676.5	699.3	722.1	752.9
17.5°	474.7	501.3	531.9	570.0	599.4	634.1	670.3	696.8	727.5	759.7	787.6
20°	468.7	499.6	534.0	571.3	608.9	646.5	681.6	713.2	745.0	782.2	805.0
22.5°	462.7	493.3	529.0	568.6	609.0	648.7	688.4	725.5	761.3	798.8	828.0
25°	450.0	486.3	525.0	565.5	605.4	649.0	696.3	737.7	781.9	820.6	848.3
27.5°	437.1	470.5	508.9	550.0	594.3	645.9	701.6	748.6	792.9	820.6	829.3
30°	425.4	460.7	496.1	537.9	585.9	643.4	702.6	756.4	792.7	804.9	795.9
32.5°	413.7	445.7	480.6	523.4	574.4	637.2	703.9	751.8	773.6	764.5	728.1
35°	392.9	421.7	455.6	498.4	557.0	633.8	698.5	730.8	725.5	673.5	604.9
37.5°	370.6	394.1	425.4	470.2	539.0	620.4	674.8	679.7	632.8	553.1	473.9
40°	352.9	374.2	406.4	453.1	525.0	607.1	651.1	631.8	559.3	470.6	404.5
42.5°	335.8	353.7	384.8	435.2	511.7	588.9	615.7	573.6	490.0	406.1	346.0
45°	306.8	323.7	354.8	406.5	484.5	554.3	550.7	477.6	393.9	326.4	276.5
47.5°	279.4	294.1	323.3	376.1	452.5	502.3	469.3	391.5	320.5	266.3	230.7
50°	259.9	274.5	303.5	355.7	427.0	463.2	416.2	341.2	276.1	231.2	203.0
52.5°	241.3	255.5	282.0	332.9	396.0	417.8	367.1	297.6	243.3	204.6	180.4
55°	215.3	226.0	249.9	298.5	345.7	350.7	299.3	241.2	196.5	169.5	152.9
57.5°	188.7	198.0	221.6	260.3	293.4	290.8	242.2	191.8	161.8	141.7	129.7
60°	171.4	180.6	201.3	234.5	259.5	250.7	206.1	165.6	139.8	125.1	115.5
62.5°	155.2	162.4	181.9	206.2	224.1	214.2	176.2	142.7	122.2	109.8	102.2
65°	131.9	137.8	153.3	166.0	175.9	166.4	134.8	111.6	96.8	88.1	82.9
67.5°	109.8	113.4	123.2	127.9	134.9	124.4	101.4	85.8	77.4	70.1	66.4
70°	95.8	98.4	103.7	107.5	109.2	98.4	81.4	70.0	63.0	57.8	55.5
72.5°	81.8	84.2	85.2	88.3	87.3	77.2	65.5	56.4	51.3	47.8	44.9
75°	62.5	63.6	62.5	61.3	58.6	51.5	43.4	38.9	35.1	33.4	32.4
77.5°	45.6	45.2	43.9	41.9	37.3	32.8	28.4	26.9	25.3	24.4	24.1
80°	35.1	34.2	33.0	29.9	25.9	22.8	21.8	20.8	20.2	19.1	18.9
82.5°	26.1	25.6	23.5	21.0	18.2	16.7	15.9	15.4	14.8	14.3	14.3
85°	13.9	13.3	11.0	9.5	9.2	8.7	8.6	8.6	7.7	7.5	7.5
87.5°	4.9	4.2	4.4	4.1	4.5	4.5	5.1	5.1	5.4	5.6	5.4
90°	2.1	3.6	5.1	6.5	8.2	10.2	12.0	14.0	15.9	16.5	17.0
92.5°	17.0	18.0	19.0	20.0	21.0	22.1	23.3	24.3	25.4	25.9	26.4
95°	40.0	41.1	42.2	43.2	44.2	45.5	46.6	47.8	49.0	49.6	50.1
97.5°	70.1	70.9	71.7	72.4	73.2	74.1	74.9	75.8	76.7	77.3	78.0
100°	90.9	91.8	92.6	93.5	94.3	95.1	95.9	96.6	97.3	97.7	98.2
102.5°	114.4	114.9	115.4	115.9	116.7	117.7	118.7	119.6	120.6	121.0	121.5
105°	149.2	149.5	149.8	150.1	150.9	152.2	153.6	154.9	156.2	156.2	156.2
107.5°	189.8	190.0	190.2	190.4	190.7	191.3	191.8	192.3	192.9	193.3	193.8
110°	215.4	215.7	216.0	216.2	216.6	216.9	217.1	217.5	217.8	218.4	218.9



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	241.7	241.9	242.1	242.3	242.4	242.5	242.5	242.5	242.6	243.3	244.1
115°	281.7	282.1	282.6	283.0	283.1	282.9	282.6	282.2	282.0	282.1	282.2
117.5°	321.6	321.8	322.2	322.4	322.4	322.0	321.6	321.3	320.8	320.8	320.8
120°	347.1	347.9	348.8	349.7	349.7	349.0	348.3	347.6	346.8	346.7	346.5
122.5°	372.7	373.4	374.1	374.7	374.8	374.4	374.1	373.7	373.3	372.9	372.6
125°	412.1	412.6	413.0	413.5	413.5	413.2	413.0	412.6	412.3	411.8	411.2
127.5°	449.2	450.1	451.0	452.0	452.3	452.0	451.7	451.3	451.0	450.1	449.3
130°	473.8	474.9	476.1	477.2	477.7	477.2	476.8	476.4	475.9	475.3	474.7
132.5°	498.1	499.3	500.4	501.7	502.0	501.8	501.4	501.1	500.8	500.1	499.4
135°	535.0	535.9	536.8	537.6	538.1	537.9	537.7	537.6	537.4	536.8	536.3
137.5°	569.3	570.0	570.8	571.5	572.0	572.4	572.8	573.2	573.5	572.9	572.3
140°	593.1	593.9	594.6	595.3	595.8	595.9	596.0	596.2	596.4	596.2	596.0
142.5°	614.8	615.5	616.3	617.0	617.5	617.8	618.0	618.3	618.6	618.4	618.3
145°	648.3	648.5	648.8	649.2	649.5	650.0	650.4	650.9	651.3	651.1	650.9
147.5°	678.1	678.7	679.2	679.8	680.2	680.6	681.0	681.4	681.9	681.9	681.9
150°	698.6	698.8	699.2	699.5	699.7	700.0	700.3	700.6	700.9	700.9	700.9
152.5°	715.6	716.0	716.5	716.8	717.1	717.3	717.5	717.6	717.8	718.1	718.4
155°	742.0	742.0	742.0	742.0	742.0	742.2	742.3	742.4	742.6	743.2	743.8
157.5°	764.6	764.4	764.2	764.0	764.0	764.1	764.2	764.4	764.5	765.1	765.7
160°	778.7	778.5	778.1	777.8	777.7	777.7	777.7	777.7	777.7	778.5	779.2
162.5°	791.3	790.9	790.5	790.1	790.0	790.1	790.1	790.3	790.4	791.1	791.8
165°	807.7	807.3	806.8	806.4	806.1	806.1	806.1	806.1	806.1	807.0	807.9
167.5°	820.6	820.1	819.5	818.9	818.7	818.8	818.9	819.0	819.1	820.0	820.9
170°	828.0	827.5	826.9	826.3	826.0	826.0	826.0	826.0	826.0	827.1	828.0
172.5°	833.9	833.3	832.7	832.1	831.8	831.8	831.8	831.8	831.8	832.8	833.7
175°	840.0	839.4	838.8	838.2	837.9	837.9	837.9	837.9	837.9	838.8	839.7
177.5°	842.6	842.1	841.7	841.2	841.0	841.0	841.0	841.0	841.0	841.7	842.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	485.3	485.3	485.3	485.3	485.3	485.3	485.3
2.5°	511.9	511.9	512.6	515.1	515.4	517.5	516.9
5°	562.6	566.5	568.0	574.3	577.9	579.6	576.3
7.5°	624.6	635.7	641.0	647.6	653.3	655.1	650.5
10°	669.8	681.4	691.2	697.2	702.8	706.6	711.3
12.5°	713.5	727.8	737.1	745.6	751.4	756.1	756.9
15°	761.0	782.6	799.0	811.1	817.1	820.2	818.9
17.5°	808.9	828.9	840.6	852.9	861.2	861.7	861.9
20°	836.0	855.5	869.1	878.2	887.5	887.1	889.2
22.5°	854.1	869.5	879.9	886.4	889.7	888.1	888.5
25°	862.6	867.2	865.3	854.7	851.9	842.2	843.9
27.5°	818.9	797.3	774.9	746.2	723.4	705.3	706.2
30°	759.6	721.3	677.7	641.1	608.3	599.1	579.6
32.5°	676.6	619.3	568.2	534.0	506.0	498.3	481.3
35°	536.0	480.3	427.8	396.2	383.7	366.2	366.0
37.5°	416.6	367.6	339.8	316.1	303.7	293.1	292.1
40°	350.4	312.3	291.2	274.2	262.0	254.0	252.2
42.5°	304.3	273.4	253.7	243.2	233.7	229.6	226.6
45°	248.4	227.7	214.0	204.5	200.1	197.0	195.3
47.5°	207.9	193.9	184.6	178.2	174.7	171.4	172.3
50°	185.7	174.3	167.5	161.4	158.7	156.4	156.7
52.5°	167.9	157.7	152.1	147.8	144.5	142.8	142.0
55°	142.5	136.1	130.5	127.3	125.5	123.2	122.6
57.5°	121.5	116.5	112.0	108.5	108.0	105.8	106.1
60°	107.6	103.4	99.7	97.8	96.4	94.5	95.1
62.5°	96.1	92.6	89.3	87.7	86.2	84.9	85.2
65°	78.7	75.4	73.3	72.5	71.9	71.2	70.6
67.5°	62.8	60.7	59.4	57.6	56.4	56.2	55.6
70°	52.8	50.0	47.8	45.5	44.9	44.7	44.9
72.5°	42.3	40.6	39.9	38.9	38.7	38.2	38.5
75°	31.7	31.1	30.8	29.9	29.9	29.9	29.9
77.5°	23.5	23.1	22.8	22.6	22.5	22.1	22.1
80°	18.3	18.1	17.7	17.7	17.5	17.7	17.5
82.5°	13.8	13.7	13.4	13.4	13.1	13.0	13.1
85°	7.0	6.9	7.3	6.9	7.0	6.7	7.0
87.5°	5.5	5.6	5.5	5.6	5.5	5.9	5.6
90°	17.7	18.3	18.6	19.0	19.3	19.5	19.9
92.5°	26.8	27.3	27.5	27.3	27.1	26.9	26.8
95°	50.7	51.4	51.6	51.6	51.6	51.6	51.6
97.5°	78.6	79.4	79.6	79.6	79.5	79.5	79.5
100°	98.6	99.1	99.4	99.7	100.0	100.3	100.6
102.5°	121.9	122.3	122.5	122.5	122.4	122.3	122.3
105°	156.2	156.2	156.3	156.7	156.9	157.2	157.6
107.5°	194.3	194.7	194.9	194.7	194.6	194.4	194.2
110°	219.5	220.1	220.3	220.0	219.6	219.4	219.1



TEST NUMBER: P332395-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	244.8	245.5	245.8	245.8	245.7	245.6	245.6
115°	282.4	282.6	282.6	282.4	282.2	282.1	282.0
117.5°	320.7	320.7	320.6	320.1	319.7	319.3	318.9
120°	346.3	346.3	346.0	345.7	345.4	345.1	344.8
122.5°	372.1	371.8	371.4	371.0	370.5	370.1	369.7
125°	410.5	410.0	409.4	408.8	408.2	407.6	407.1
127.5°	448.5	447.7	446.9	446.3	445.6	445.0	444.3
130°	474.1	473.5	472.7	471.7	470.6	469.7	468.6
132.5°	498.6	497.9	497.2	496.4	495.6	494.8	494.0
135°	535.7	535.1	534.7	534.3	534.0	533.8	533.4
137.5°	571.7	571.1	570.5	570.0	569.4	568.8	568.3
140°	595.9	595.8	595.1	594.1	593.1	592.1	591.0
142.5°	618.1	618.0	617.5	616.7	615.9	615.1	614.3
145°	650.9	650.7	650.3	649.7	649.2	648.5	648.0
147.5°	681.9	681.9	681.4	680.6	679.7	678.8	677.9
150°	700.9	700.9	700.4	699.5	698.7	697.9	697.0
152.5°	718.5	718.8	718.5	717.7	717.0	716.2	715.5
155°	744.4	744.9	744.8	743.7	742.7	741.6	740.7
157.5°	766.3	767.0	766.8	766.0	765.2	764.4	763.5
160°	779.9	780.6	780.7	780.2	779.5	778.9	778.4
162.5°	792.6	793.4	793.3	792.3	791.4	790.4	789.4
165°	808.8	809.7	809.6	808.6	807.5	806.6	805.5
167.5°	821.9	822.8	822.8	821.9	820.9	820.0	819.1
170°	829.1	830.1	830.1	829.1	828.0	827.1	826.0
172.5°	834.6	835.4	835.4	834.4	833.4	832.3	831.3
175°	840.5	841.4	841.4	840.3	839.3	838.3	837.2
177.5°	843.1	843.8	843.7	842.9	842.0	841.2	840.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6

(END OF REPORT)