

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332396-940

Luminaire Tested: **S123RDIW-S340D755U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332396-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3853.2 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	82	84	80	77	74	63	61	60	48	47	45	34	33	32	26
2	85	78	72	68	76	70	66	61	56	52	50	42	40	38	30	29	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5514	5514	5514
5°	5535	5459	5491
10°	5503	5391	5372
15°	5446	5264	5209
20°	5363	5108	4987
25°	5280	4930	4772
30°	5169	4724	4467
35°	5056	4520	4188
40°	4950	4279	3842
45°	4813	4042	3529
50°	4662	3771	3178
55°	4506	3462	2852
60°	4366	3130	2495
65°	4182	2774	2137
70°	3950	2326	1725
75°	3614	1834	1626
80°	3217	1624	1494
85°	2717	1433	1334



TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	1.2
10°-20°	133.9	3.5
20°-30°	192.7	5.0
30°-40°	217.1	5.6
40°-50°	207.7	5.4
50°-60°	170.1	4.4
60°-70°	114.8	3.0
70°-80°	57.7	1.5
80°-90°	17.7	0.5
90°-100°	32.1	0.8
100°-110°	153.0	4.0
110°-120°	367.6	9.5
120°-130°	468.1	12.1
130°-140°	500.2	13.0
140°-150°	467.7	12.1
150°-160°	377.3	9.8
160°-170°	243.5	6.3
170°-180°	83.9	2.2
0°-30°	374.7	9.7
0°-40°	591.8	15.4
0°-60°	969.6	25.2
0°-90°	1159.8	30.1
90°-120°	552.8	14.3
90°-150°	1988.7	51.6
90°-180°	2693.0	69.9
0°-180°	3853.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	512	512	512	512	512	
5°	512	510	505	509	508	49
15°	489	484	472	470	467	138
25°	445	434	415	407	402	204
35°	385	369	344	327	319	241
45°	316	297	266	243	232	244
55°	240	219	184	161	152	215
65°	164	141	109	89	84	162
75°	87	67	44	40	39	93
85°	22	13	12	11	11	25
90°	1	7	16	18	20	3
95°	40	15	20	25	25	49
105°	196	199	144	34	29	207
115°	367	371	377	383	386	362
125°	517	522	525	526	528	462
135°	644	648	650	652	650	495
145°	743	747	749	750	750	465
155°	818	817	818	821	817	377
165°	863	861	860	865	861	244
175°	883	880	881	885	880	84
180°	883	883	883	883	883	



TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	514.0	513.6	513.4	513.1	512.8	512.2	511.3	510.4	509.5	508.6	509.4
5°	512.3	511.8	511.4	511.0	510.4	509.7	508.5	507.5	506.3	505.2	506.0
7.5°	507.6	507.0	506.6	506.0	505.6	504.6	503.2	501.8	500.2	498.8	499.3
10°	503.5	502.9	502.3	501.7	501.0	499.8	498.2	496.5	494.8	493.2	493.3
12.5°	497.9	497.2	496.5	495.8	495.1	493.7	491.6	489.6	487.6	485.5	485.4
15°	488.7	487.6	486.6	485.5	484.6	482.8	480.2	477.6	475.0	472.4	472.0
17.5°	476.9	475.7	474.6	473.3	472.2	469.9	466.6	463.3	460.1	456.8	455.8
20°	468.2	466.8	465.3	463.9	462.4	459.9	456.4	452.8	449.3	445.9	444.6
22.5°	458.6	456.9	455.2	453.5	451.8	449.2	445.4	441.7	437.9	434.2	432.7
25°	444.6	442.3	440.0	437.7	435.3	432.0	427.8	423.6	419.3	415.1	413.1
27.5°	427.6	425.0	422.4	419.9	417.3	413.8	409.0	404.2	399.5	394.8	392.1
30°	415.9	413.1	410.4	407.6	404.8	400.8	395.7	390.5	385.3	380.1	377.0
32.5°	404.3	401.1	398.0	394.8	391.7	387.4	381.9	376.5	371.0	365.5	362.1
35°	384.8	381.4	378.1	374.8	371.5	366.9	361.2	355.4	349.7	344.0	340.1
37.5°	365.0	361.2	357.6	353.9	350.2	345.3	339.2	333.1	327.0	320.8	316.4
40°	352.3	348.3	344.2	340.2	336.1	330.7	324.2	317.6	311.1	304.5	299.8
42.5°	338.0	333.9	329.9	325.8	321.8	316.4	309.6	302.8	296.0	289.3	284.0
45°	316.2	312.0	307.9	303.7	299.5	293.9	286.9	279.7	272.6	265.5	260.2
47.5°	294.4	289.8	285.2	280.6	276.1	270.3	263.1	256.0	249.0	241.8	236.1
50°	278.4	274.0	269.7	265.4	261.0	255.1	247.6	240.1	232.6	225.2	219.5
52.5°	264.1	259.4	254.7	249.9	245.2	239.2	231.8	224.4	217.0	209.6	203.7
55°	240.1	235.6	231.1	226.6	222.0	215.9	208.0	200.2	192.3	184.5	179.1
57.5°	218.0	213.1	208.2	203.2	198.3	191.9	184.0	176.1	168.3	160.4	155.3
60°	202.8	197.7	192.6	187.5	182.4	176.1	168.4	160.8	153.1	145.4	140.4
62.5°	187.4	182.4	177.3	172.3	167.2	160.8	153.1	145.4	137.8	130.1	125.5
65°	164.2	159.1	154.0	148.9	143.8	137.7	130.5	123.2	116.1	108.9	104.3
67.5°	140.8	135.6	130.5	125.4	120.2	114.2	107.3	100.4	93.5	86.6	83.2
70°	125.5	120.5	115.5	110.5	105.6	99.8	93.4	86.9	80.4	73.9	70.7
72.5°	110.2	105.3	100.4	95.4	90.5	85.2	79.3	73.4	67.5	61.6	59.0
75°	86.9	82.4	77.9	73.6	69.1	64.4	59.3	54.2	49.1	44.1	43.2
77.5°	65.5	61.5	57.5	53.5	49.6	45.9	42.6	39.3	36.1	32.8	32.4
80°	51.9	48.2	44.4	40.6	36.8	34.0	32.0	30.1	28.1	26.2	25.9
82.5°	39.0	35.7	32.5	29.2	25.9	23.8	22.9	22.0	21.1	20.2	19.9
85°	22.0	20.0	17.9	16.0	13.9	12.8	12.5	12.2	11.9	11.6	11.4
87.5°	8.1	7.6	7.0	6.5	6.1	6.0	6.3	6.7	7.1	7.5	7.5
90°	0.6	2.1	3.6	5.0	6.5	8.2	10.1	11.9	13.8	15.8	16.3
92.5°	12.2	11.8	11.4	11.0	10.6	11.1	12.5	13.9	15.3	16.8	17.7
95°	40.0	34.1	28.1	22.1	16.1	13.9	15.5	17.1	18.7	20.3	21.4
97.5°	80.4	77.8	75.1	72.4	69.7	63.1	52.6	42.1	31.7	21.1	22.3
100°	110.9	113.8	116.7	119.7	122.5	112.6	89.9	67.1	44.4	21.7	22.8
102.5°	145.5	147.7	149.7	151.9	153.9	142.6	117.7	92.8	68.0	43.2	39.6
105°	195.6	197.2	198.8	200.4	202.0	196.2	183.1	170.0	156.9	143.7	117.9
107.5°	248.3	249.6	250.8	252.2	253.4	255.1	257.2	259.2	261.4	263.4	244.4
110°	283.5	284.6	285.8	287.0	288.1	289.5	291.1	292.7	294.4	296.0	291.1



TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	317.1	318.1	319.1	320.2	321.3	322.6	324.2	325.8	327.4	329.0	329.1
115°	366.8	367.7	368.5	369.4	370.3	371.4	372.7	374.0	375.3	376.7	378.1
117.5°	415.0	416.1	417.1	418.2	419.3	420.2	420.8	421.5	422.1	422.8	424.0
120°	444.9	446.2	447.5	448.8	450.1	451.0	451.5	451.9	452.4	452.7	454.0
122.5°	475.4	476.4	477.5	478.6	479.7	480.5	481.0	481.6	482.1	482.7	483.5
125°	517.1	518.3	519.4	520.6	521.7	522.6	523.2	523.8	524.3	525.0	525.2
127.5°	557.5	558.7	559.8	561.0	562.1	563.1	563.8	564.5	565.2	565.9	566.3
130°	582.6	583.9	585.1	586.2	587.4	588.3	588.8	589.4	590.0	590.6	591.1
132.5°	606.8	608.0	609.1	610.3	611.5	612.3	612.8	613.2	613.7	614.2	614.7
135°	643.7	644.6	645.4	646.3	647.2	647.9	648.5	649.1	649.7	650.2	650.7
137.5°	675.2	676.3	677.4	678.5	679.7	680.4	680.6	681.0	681.4	681.6	682.3
140°	696.2	697.1	697.9	698.8	699.7	700.3	700.8	701.2	701.7	702.1	702.7
142.5°	715.6	716.5	717.4	718.3	719.2	719.8	720.2	720.7	721.1	721.6	722.0
145°	742.8	743.8	744.8	745.8	746.9	747.5	747.8	748.1	748.4	748.7	748.9
147.5°	768.4	769.0	769.7	770.3	771.1	771.5	771.9	772.1	772.4	772.7	773.0
150°	784.2	784.5	785.0	785.4	785.9	786.2	786.6	786.8	787.1	787.4	787.7
152.5°	798.3	798.5	798.7	798.9	799.2	799.3	799.5	799.7	799.9	800.0	800.5
155°	818.2	818.0	817.7	817.3	817.1	817.0	817.2	817.3	817.4	817.6	818.3
157.5°	833.7	833.7	833.7	833.7	833.7	833.6	833.4	833.2	833.1	832.9	833.8
160°	843.2	843.0	842.9	842.8	842.6	842.5	842.3	842.1	842.0	841.9	842.8
162.5°	852.1	851.8	851.3	851.0	850.6	850.3	850.2	850.1	849.9	849.7	850.8
165°	862.9	862.5	862.0	861.6	861.1	860.9	860.7	860.5	860.4	860.2	861.4
167.5°	871.3	870.7	870.1	869.5	869.0	868.6	868.6	868.6	868.6	868.6	869.8
170°	876.0	875.4	874.9	874.2	873.7	873.3	873.3	873.3	873.3	873.3	874.5
172.5°	879.1	878.4	877.7	877.1	876.4	876.0	876.2	876.3	876.4	876.6	877.7
175°	883.2	882.4	881.7	881.0	880.3	880.0	880.1	880.3	880.5	880.6	881.6
177.5°	884.2	883.7	883.1	882.5	881.9	881.7	881.8	881.9	882.1	882.2	883.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2



TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	512.3	512.3	512.3	512.3	512.3	512.3	512.3	512.3
2.5°	510.2	511.0	511.9	512.2	512.1	511.9	511.8	511.7
5°	506.9	507.7	508.5	508.9	508.7	508.5	508.4	508.2
7.5°	499.8	500.2	500.7	500.8	500.4	500.2	499.8	499.5
10°	493.4	493.5	493.6	493.4	492.9	492.5	492.0	491.5
12.5°	485.4	485.4	485.4	485.0	484.5	483.9	483.4	482.9
15°	471.4	471.0	470.6	470.0	469.4	468.7	468.1	467.4
17.5°	454.9	453.9	452.9	451.9	450.9	450.0	449.1	448.1
20°	443.4	442.2	441.0	439.9	438.7	437.7	436.6	435.4
22.5°	431.2	429.7	428.2	427.0	425.9	424.9	423.8	422.8
25°	411.2	409.3	407.3	405.8	404.8	403.9	402.8	401.8
27.5°	389.4	386.7	384.1	381.9	380.3	378.8	377.3	375.7
30°	373.9	370.8	367.7	365.3	363.8	362.4	360.9	359.4
32.5°	358.6	355.3	351.8	349.3	347.8	346.3	344.6	343.1
35°	336.1	332.1	328.1	325.3	323.7	322.0	320.3	318.7
37.5°	311.8	307.3	302.8	299.5	297.5	295.4	293.4	291.3
40°	295.0	290.2	285.3	281.9	279.7	277.7	275.5	273.4
42.5°	278.7	273.6	268.3	264.7	262.8	260.9	259.0	257.1
45°	254.9	249.7	244.4	240.7	238.5	236.3	234.1	231.8
47.5°	230.3	224.6	218.9	215.1	213.1	211.2	209.1	207.1
50°	213.7	208.0	202.3	198.4	196.3	194.1	192.0	189.8
52.5°	197.7	191.7	185.8	181.9	179.9	178.1	176.2	174.2
55°	173.8	168.4	163.1	159.4	157.7	155.8	153.9	152.0
57.5°	150.3	145.2	140.2	136.8	135.3	133.7	132.2	130.5
60°	135.5	130.5	125.5	122.2	120.6	119.0	117.5	115.9
62.5°	120.7	116.1	111.4	108.2	106.6	105.0	103.3	101.7
65°	99.8	95.3	90.8	88.0	86.9	86.0	85.0	83.9
67.5°	79.8	76.4	73.0	70.8	69.7	68.7	67.6	66.5
70°	67.5	64.3	61.0	58.9	57.9	56.9	55.8	54.8
72.5°	56.4	53.8	51.1	49.6	49.1	48.7	48.3	47.9
75°	42.2	41.3	40.3	39.8	39.6	39.4	39.2	39.1
77.5°	31.8	31.3	30.9	30.5	30.3	30.1	30.0	29.8
80°	25.6	25.3	25.1	24.9	24.6	24.4	24.3	24.1
82.5°	19.6	19.4	19.1	18.9	18.9	18.8	18.8	18.8
85°	11.2	11.1	10.9	10.8	10.8	10.8	10.8	10.8
87.5°	7.6	7.6	7.7	7.7	7.7	7.7	7.6	7.6
90°	16.9	17.5	18.1	18.5	18.8	19.1	19.4	19.7
92.5°	18.6	19.6	20.5	21.0	21.2	21.4	21.6	21.8
95°	22.4	23.4	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	23.5	24.6	25.8	26.5	26.6	26.8	26.9	27.0
100°	24.0	25.1	26.3	27.0	27.1	27.3	27.4	27.6
102.5°	35.9	32.4	28.7	27.0	27.3	27.6	27.8	28.1
105°	92.1	66.3	40.5	27.7	28.0	28.3	28.6	28.9
107.5°	225.5	206.6	187.7	168.5	149.0	129.6	110.1	90.7
110°	286.3	281.5	276.7	263.9	243.0	222.1	201.3	180.5



TEST NUMBER: P332396-940

CATALOG NUMBER: S123RDIW-S340D755U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	329.2	329.3	329.4	327.2	322.8	318.4	314.0	309.6
115°	379.6	381.0	382.5	383.5	384.1	384.7	385.2	385.8
117.5°	425.2	426.3	427.5	428.1	428.3	428.4	428.5	428.6
120°	455.1	456.3	457.4	458.0	458.0	458.0	458.0	458.0
122.5°	484.3	485.1	486.0	486.4	486.5	486.6	486.8	486.9
125°	525.5	525.8	526.1	526.4	526.7	527.0	527.3	527.5
127.5°	566.9	567.3	567.8	567.8	567.6	567.2	566.9	566.7
130°	591.7	592.3	592.9	593.1	592.7	592.5	592.2	591.8
132.5°	615.4	615.9	616.5	616.6	616.2	615.8	615.4	614.9
135°	651.1	651.6	652.0	652.0	651.6	651.1	650.7	650.2
137.5°	683.1	683.8	684.5	684.7	684.4	684.0	683.8	683.5
140°	703.3	703.8	704.5	704.6	704.3	704.0	703.7	703.4
142.5°	722.5	722.9	723.4	723.4	723.0	722.6	722.2	721.8
145°	749.3	749.6	749.8	750.0	750.0	750.0	750.0	750.0
147.5°	773.3	773.6	773.9	773.6	773.0	772.3	771.7	771.0
150°	788.0	788.3	788.5	788.5	788.1	787.6	787.2	786.8
152.5°	801.0	801.6	802.1	802.0	801.4	800.7	800.0	799.3
155°	819.0	819.7	820.6	820.5	819.6	818.7	817.8	816.9
157.5°	834.7	835.5	836.4	836.3	835.2	834.0	832.9	831.8
160°	843.6	844.5	845.3	845.3	844.3	843.3	842.2	841.2
162.5°	851.8	852.7	853.7	853.7	852.8	851.9	851.0	850.2
165°	862.6	863.7	864.9	865.0	864.0	862.9	861.9	860.9
167.5°	870.9	872.2	873.3	873.3	872.2	870.9	869.8	868.6
170°	875.7	876.9	878.1	878.1	876.9	875.7	874.5	873.3
172.5°	878.9	880.0	881.2	881.1	879.9	878.6	877.3	876.0
175°	882.6	883.7	884.7	884.6	883.4	882.3	881.1	879.9
177.5°	884.0	884.9	885.9	885.7	884.6	883.4	882.3	881.1
180°	883.2	883.2	883.2	883.2	883.2	883.2	883.2	883.2

(END OF REPORT)