

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332828-930

Luminaire Tested: **S124DIW-S1020D1340U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332828-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1340U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7407.2 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11357	11357	11357
5°	11391	11255	11336
10°	11320	11163	11218
15°	11183	11004	11032
20°	11001	10808	10817
25°	10794	10583	10553
30°	10540	10318	10224
35°	10276	10042	9909
40°	10003	9729	9551
45°	9717	9421	9240
50°	9401	9146	8862
55°	9060	8790	8504
60°	8719	8391	8136
65°	8334	8010	7687
70°	7903	7504	7211
75°	7243	6890	6716
80°	6448	6183	6025
85°	5641	5428	5326



TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	1.8
10°-20°	373.3	5.0
20°-30°	549.4	7.4
30°-40°	638.7	8.6
40°-50°	638.7	8.6
50°-60°	558.7	7.5
60°-70°	414.9	5.6
70°-80°	235.7	3.2
80°-90°	72.1	1.0
90°-100°	90.2	1.2
100°-110°	267.1	3.6
110°-120°	453.4	6.1
120°-130°	597.8	8.1
130°-140°	671.4	9.1
140°-150°	659.8	8.9
150°-160°	554.9	7.5
160°-170°	369.2	5.0
170°-180°	129.3	1.7
0°-30°	1055.2	14.2
0°-40°	1693.9	22.9
0°-60°	2891.3	39.0
0°-90°	3614.1	48.8
90°-120°	810.7	10.9
90°-150°	2739.7	37.0
90°-180°	3793.0	51.2
0°-180°	7407.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1407	1407	1407	1407	1407	
5°	1406	1401	1389	1400	1399	133
15°	1338	1333	1317	1323	1320	377
25°	1212	1204	1188	1189	1185	557
35°	1043	1034	1019	1011	1006	652
45°	851	843	825	813	809	656
55°	644	640	624	611	604	576
65°	436	430	419	408	402	432
75°	232	227	221	217	215	247
85°	61	61	59	59	58	67
90°	3	15	23	29	32	7
95°	63	73	80	83	84	71
105°	246	248	252	255	258	261
115°	461	461	459	458	457	454
125°	671	671	670	668	666	598
135°	866	872	872	870	867	670
145°	1052	1056	1057	1056	1053	658
155°	1205	1205	1204	1208	1204	554
165°	1312	1309	1307	1313	1309	370
175°	1365	1360	1359	1365	1359	130
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1410.4	1409.8	1409.2	1408.6	1408.0	1406.6	1404.4	1402.2	1400.0	1397.7	1399.8
5°	1405.7	1404.7	1403.7	1402.6	1401.7	1399.8	1397.0	1394.2	1391.6	1388.8	1391.6
7.5°	1392.6	1391.6	1390.6	1389.6	1388.6	1386.6	1383.5	1380.5	1377.4	1374.4	1376.6
10°	1380.9	1379.9	1378.8	1377.9	1376.9	1374.8	1371.5	1368.2	1365.0	1361.7	1363.7
12.5°	1365.5	1364.6	1363.5	1362.5	1361.5	1359.3	1355.8	1352.4	1348.9	1345.5	1347.7
15°	1338.1	1337.0	1336.0	1335.1	1334.0	1331.6	1327.9	1324.1	1320.4	1316.6	1318.1
17.5°	1304.9	1303.7	1302.4	1301.1	1299.9	1297.5	1293.9	1290.4	1286.8	1283.3	1284.2
20°	1280.5	1279.3	1278.1	1276.8	1275.5	1273.0	1269.3	1265.5	1261.8	1258.0	1258.7
22.5°	1254.4	1252.7	1251.1	1249.4	1247.8	1245.0	1241.3	1237.5	1233.8	1230.0	1231.4
25°	1211.8	1210.1	1208.3	1206.5	1204.8	1202.2	1198.7	1195.1	1191.6	1188.1	1188.4
27.5°	1163.1	1161.3	1159.4	1157.6	1155.8	1153.3	1150.1	1146.8	1143.5	1140.3	1139.7
30°	1130.7	1128.6	1126.6	1124.6	1122.6	1120.0	1116.7	1113.5	1110.2	1106.9	1106.0
32.5°	1096.3	1094.5	1092.7	1091.0	1089.2	1086.5	1083.0	1079.6	1076.1	1072.7	1071.5
35°	1042.7	1041.0	1039.2	1037.5	1035.7	1033.1	1029.6	1026.1	1022.5	1019.0	1017.2
37.5°	986.1	984.5	982.9	981.3	979.7	977.1	973.2	969.5	965.7	962.0	960.1
40°	949.2	947.1	945.1	943.1	941.1	938.2	934.5	930.7	927.0	923.2	920.7
42.5°	909.5	908.2	907.0	905.9	904.7	902.0	897.8	893.6	889.5	885.3	882.4
45°	851.1	849.3	847.6	845.8	844.1	841.1	837.1	833.2	829.2	825.2	822.4
47.5°	789.9	788.8	787.6	786.4	785.1	782.7	779.0	775.3	771.6	767.8	764.8
50°	748.5	747.5	746.5	745.5	744.4	742.2	738.7	735.2	731.7	728.2	724.7
52.5°	707.9	706.7	705.5	704.3	703.1	700.7	696.9	693.2	689.5	685.8	682.7
55°	643.7	642.9	642.1	641.4	640.7	638.5	635.0	631.5	628.0	624.5	621.5
57.5°	582.4	581.5	580.7	579.8	578.9	576.7	573.3	569.9	566.4	563.0	560.1
60°	540.0	538.7	537.4	536.2	534.9	532.7	529.5	526.2	522.9	519.7	517.4
62.5°	498.5	497.4	496.4	495.3	494.2	492.0	488.5	485.1	481.6	478.2	476.1
65°	436.3	435.0	433.7	432.5	431.2	429.3	426.8	424.4	421.8	419.3	416.9
67.5°	373.6	372.4	371.3	370.1	368.9	367.2	364.8	362.4	360.0	357.6	355.1
70°	334.8	333.0	331.3	329.5	327.8	325.9	323.9	321.9	319.9	317.9	315.8
72.5°	293.3	291.6	289.8	288.0	286.3	284.6	283.0	281.4	279.8	278.2	276.6
75°	232.2	231.0	229.7	228.4	227.2	225.9	224.7	223.5	222.2	220.9	220.0
77.5°	173.8	173.3	172.7	172.2	171.6	170.8	169.7	168.6	167.5	166.4	166.1
80°	138.7	137.9	137.1	136.4	135.7	135.0	134.5	134.0	133.5	133.0	132.5
82.5°	104.4	104.0	103.7	103.3	103.0	102.7	102.6	102.6	102.5	102.3	102.1
85°	60.9	60.9	60.9	60.9	60.9	60.7	60.1	59.6	59.1	58.6	58.6
87.5°	24.1	24.4	24.7	25.0	25.4	25.6	25.8	25.9	26.1	26.3	26.6
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	22.7	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7
95°	63.4	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0
97.5°	110.8	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9
100°	148.1	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2
102.5°	186.9	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0
105°	246.4	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3
107.5°	308.8	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3
110°	351.1	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6



TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.0	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5
115°	461.0	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7
117.5°	523.2	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7
120°	564.6	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5
122.5°	607.7	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2
125°	671.4	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8
127.5°	729.1	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2
130°	769.7	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4
132.5°	811.2	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2
135°	865.9	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9
137.5°	925.6	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6
140°	965.4	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3
142.5°	1001.8	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0
145°	1052.1	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1102.0	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0
150°	1132.5	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.1	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3
157.5°	1242.6	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2
160°	1264.6	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1
162.5°	1284.9	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4
165°	1312.1	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3
167.5°	1333.1	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3
170°	1344.9	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1
172.5°	1353.4	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8
175°	1365.1	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3
177.5°	1368.8	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8	1406.8
2.5°	1401.7	1403.8	1405.8	1406.7	1406.5	1406.3	1406.1	1405.9
5°	1394.2	1397.0	1399.8	1400.9	1400.4	1399.9	1399.4	1398.9
7.5°	1378.8	1381.0	1383.2	1384.1	1383.8	1383.5	1383.2	1382.9
10°	1365.7	1367.7	1369.7	1370.4	1369.9	1369.5	1369.0	1368.5
12.5°	1349.9	1352.1	1354.3	1355.0	1354.4	1353.6	1352.9	1352.3
15°	1319.6	1321.1	1322.7	1323.0	1322.3	1321.5	1320.8	1320.0
17.5°	1285.2	1286.1	1287.0	1287.3	1286.8	1286.3	1285.8	1285.2
20°	1259.5	1260.3	1261.0	1261.1	1260.6	1260.1	1259.6	1259.1
22.5°	1232.7	1234.1	1235.4	1235.7	1234.8	1233.9	1233.0	1232.1
25°	1188.6	1188.9	1189.1	1188.7	1187.7	1186.7	1185.7	1184.7
27.5°	1139.1	1138.5	1137.9	1137.0	1135.7	1134.5	1133.2	1132.0
30°	1105.0	1103.9	1102.9	1101.8	1100.6	1099.3	1098.0	1096.8
32.5°	1070.2	1069.1	1067.9	1066.7	1065.4	1064.1	1062.9	1061.6
35°	1015.5	1013.7	1012.0	1010.5	1009.3	1008.0	1006.7	1005.5
37.5°	958.1	956.3	954.4	952.6	951.0	949.3	947.6	946.0
40°	918.2	915.7	913.2	911.3	910.0	908.8	907.6	906.3
42.5°	879.5	876.6	873.7	871.8	871.0	870.1	869.3	868.5
45°	819.6	816.8	814.1	812.4	811.6	810.9	810.1	809.3
47.5°	761.7	758.6	755.5	752.9	751.1	749.1	747.2	745.3
50°	721.2	717.7	714.2	711.7	710.1	708.7	707.2	705.6
52.5°	679.6	676.5	673.4	670.9	669.0	667.1	665.2	663.2
55°	618.5	615.5	612.5	610.3	608.7	607.2	605.7	604.2
57.5°	557.3	554.4	551.5	549.3	547.9	546.5	545.0	543.6
60°	515.2	512.9	510.6	508.9	507.6	506.4	505.2	503.9
62.5°	474.1	472.0	469.9	468.3	467.1	465.8	464.6	463.3
65°	414.3	411.8	409.3	407.4	406.2	405.0	403.7	402.4
67.5°	352.8	350.3	348.0	346.6	346.2	345.8	345.5	345.2
70°	313.9	311.9	309.9	308.5	307.8	307.0	306.2	305.5
72.5°	275.0	273.4	271.8	270.6	269.9	269.1	268.4	267.6
75°	218.9	217.9	217.0	216.3	216.1	215.8	215.6	215.3
77.5°	165.8	165.5	165.2	164.7	164.0	163.4	162.7	162.1
80°	132.0	131.5	131.0	130.6	130.4	130.1	129.9	129.6
82.5°	101.7	101.4	101.2	100.9	100.6	100.4	100.1	99.9
85°	58.6	58.6	58.6	58.5	58.2	58.0	57.7	57.5
87.5°	26.8	27.1	27.4	27.6	27.7	27.8	27.9	28.0
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	43.5	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	81.8	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	128.8	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	162.7	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	198.6	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.1	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	311.9	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	351.1	350.7	350.3	350.3	351.1	351.7	352.5	353.2



TEST NUMBER: P332828-930

CATALOG NUMBER: S124DIW-S1020D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	393.4	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.4	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	521.0	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	563.4	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	606.3	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.4	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.7	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	772.0	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.7	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	871.4	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	929.0	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	967.0	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.9	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.8	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1165.7	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1241.9	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1263.9	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1283.6	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1309.7	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1331.7	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1343.5	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1352.3	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1367.3	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)