

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332424-940

Luminaire Tested: **S123RDIW-S560D1320U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332424-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1320U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6613.3 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.2
10°-20°	220.1	3.3
20°-30°	316.9	4.8
30°-40°	356.9	5.4
40°-50°	341.4	5.2
50°-60°	279.6	4.2
60°-70°	188.7	2.9
70°-80°	94.9	1.4
80°-90°	29.4	0.4
90°-100°	56.1	0.8
100°-110°	267.4	4.0
110°-120°	642.3	9.7
120°-130°	818.0	12.4
130°-140°	874.0	13.2
140°-150°	817.3	12.4
150°-160°	659.2	10.0
160°-170°	425.5	6.4
170°-180°	146.6	2.2
0°-30°	616.0	9.3
0°-40°	972.9	14.7
0°-60°	1594.0	24.1
0°-90°	1907.0	28.8
90°-120°	965.9	14.6
90°-150°	3475.0	52.5
90°-180°	4706.0	71.2
0°-180°	6613.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	13	28	32	34	5
95°	70	26	36	43	44	86
105°	342	348	251	60	50	362
115°	641	648	658	669	674	632
125°	904	912	917	920	922	807
135°	1125	1132	1136	1139	1136	866
145°	1298	1306	1308	1310	1310	812
155°	1430	1428	1429	1434	1428	658
165°	1508	1504	1503	1511	1504	426
175°	1543	1538	1539	1546	1538	147
180°	1543	1543	1543	1543	1543	



TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.4	12.5	11.7	10.9	10.1	10.0	10.6	11.3	11.9	12.6	12.7
90°	1.2	3.7	6.2	8.8	11.3	14.3	17.6	20.9	24.2	27.6	28.5
92.5°	21.3	20.6	19.9	19.2	18.5	19.4	21.8	24.3	26.8	29.3	30.9
95°	69.9	59.5	49.0	38.6	28.2	24.3	27.1	30.0	32.7	35.6	37.4
97.5°	140.5	135.9	131.2	126.5	121.8	110.3	91.9	73.7	55.3	36.9	39.0
100°	193.8	198.9	203.9	209.0	214.2	196.8	157.1	117.3	77.6	37.8	39.9
102.5°	254.3	258.0	261.6	265.3	269.0	249.1	205.7	162.3	118.9	75.4	69.1
105°	341.7	344.5	347.3	350.1	352.8	342.9	319.9	296.9	274.0	251.1	206.0
107.5°	433.9	436.1	438.4	440.6	442.8	445.8	449.4	453.0	456.6	460.2	427.1
110°	495.3	497.4	499.4	501.4	503.5	505.9	508.7	511.5	514.3	517.1	508.7



TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	554.0	555.9	557.7	559.5	561.3	563.7	566.5	569.3	572.1	574.9	575.1
115°	641.0	642.5	644.0	645.5	647.0	649.0	651.2	653.5	655.9	658.2	660.7
117.5°	725.1	727.0	728.9	730.8	732.6	734.1	735.3	736.6	737.7	738.9	740.9
120°	777.4	779.7	781.9	784.3	786.6	788.1	788.8	789.6	790.4	791.1	793.2
122.5°	830.6	832.5	834.4	836.2	838.1	839.5	840.5	841.5	842.5	843.5	844.9
125°	903.5	905.5	907.6	909.6	911.7	913.2	914.2	915.3	916.2	917.3	917.7
127.5°	974.1	976.2	978.2	980.3	982.3	983.9	985.2	986.4	987.6	988.8	989.6
130°	1018.2	1020.2	1022.3	1024.3	1026.4	1027.9	1028.9	1029.9	1030.9	1031.9	1033.0
132.5°	1060.3	1062.4	1064.4	1066.5	1068.5	1070.0	1070.8	1071.6	1072.4	1073.2	1074.2
135°	1124.8	1126.3	1127.8	1129.4	1131.0	1132.2	1133.2	1134.3	1135.2	1136.3	1137.0
137.5°	1179.8	1181.8	1183.7	1185.6	1187.6	1188.8	1189.4	1190.0	1190.5	1191.1	1192.3
140°	1216.6	1218.1	1219.6	1221.1	1222.6	1223.8	1224.6	1225.3	1226.1	1226.8	1227.9
142.5°	1250.4	1252.0	1253.6	1255.1	1256.6	1257.8	1258.5	1259.3	1260.0	1260.8	1261.6
145°	1298.0	1299.8	1301.5	1303.3	1305.1	1306.2	1306.7	1307.2	1307.8	1308.2	1308.8
147.5°	1342.6	1343.8	1345.0	1346.1	1347.4	1348.2	1348.7	1349.2	1349.7	1350.2	1350.8
150°	1370.2	1370.9	1371.7	1372.4	1373.2	1373.9	1374.4	1374.8	1375.4	1375.9	1376.4
152.5°	1394.9	1395.3	1395.6	1396.0	1396.3	1396.7	1397.0	1397.3	1397.6	1397.9	1398.8
155°	1429.8	1429.3	1428.8	1428.3	1427.7	1427.6	1427.9	1428.2	1428.4	1428.6	1429.9
157.5°	1456.9	1456.8	1456.8	1456.7	1456.6	1456.5	1456.3	1456.0	1455.7	1455.5	1457.0
160°	1473.4	1473.1	1472.8	1472.6	1472.3	1472.1	1471.9	1471.6	1471.3	1471.1	1472.6
162.5°	1489.0	1488.3	1487.6	1486.9	1486.3	1485.9	1485.6	1485.3	1485.1	1484.8	1486.6
165°	1507.8	1507.0	1506.2	1505.5	1504.7	1504.2	1504.0	1503.7	1503.4	1503.2	1505.2
167.5°	1522.4	1521.4	1520.4	1519.4	1518.3	1517.9	1517.9	1517.9	1517.9	1517.9	1519.9
170°	1530.7	1529.6	1528.7	1527.7	1526.6	1526.1	1526.1	1526.1	1526.1	1526.1	1528.1
172.5°	1536.2	1535.0	1533.7	1532.5	1531.3	1530.8	1531.0	1531.2	1531.4	1531.6	1533.7
175°	1543.3	1542.0	1540.8	1539.4	1538.2	1537.7	1537.9	1538.2	1538.5	1538.7	1540.5
177.5°	1545.2	1544.1	1543.1	1542.1	1541.1	1540.7	1540.9	1541.1	1541.2	1541.5	1543.1
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3



TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	12.8	12.8	12.9	12.9	12.9	12.9	12.9	12.9
90°	29.5	30.6	31.6	32.4	32.9	33.3	33.9	34.4
92.5°	32.6	34.2	35.8	36.8	37.2	37.5	37.7	38.1
95°	39.1	40.9	42.7	43.6	43.6	43.6	43.6	43.6
97.5°	41.0	43.1	45.0	46.2	46.5	46.7	47.0	47.3
100°	41.9	44.0	46.0	47.2	47.3	47.6	47.9	48.2
102.5°	62.8	56.4	50.2	47.3	47.7	48.2	48.6	49.0
105°	160.9	115.8	70.7	48.4	49.0	49.4	49.9	50.5
107.5°	394.1	361.1	328.0	294.4	260.5	226.4	192.4	158.5
110°	500.2	491.9	483.5	461.0	424.6	388.2	351.8	315.3



TEST NUMBER: P332424-940

CATALOG NUMBER: S123RDIW-S560D1320U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	575.2	575.3	575.5	571.8	564.0	556.3	548.7	541.0
115°	663.3	665.8	668.3	670.1	671.1	672.2	673.2	674.2
117.5°	743.0	744.9	747.0	748.1	748.3	748.5	748.8	748.9
120°	795.2	797.3	799.3	800.3	800.3	800.3	800.3	800.3
122.5°	846.3	847.7	849.2	850.0	850.2	850.3	850.6	850.8
125°	918.3	918.8	919.3	919.8	920.3	920.9	921.3	921.9
127.5°	990.4	991.2	992.1	992.2	991.8	991.2	990.7	990.2
130°	1033.9	1035.0	1036.0	1036.3	1035.7	1035.3	1034.7	1034.2
132.5°	1075.2	1076.3	1077.3	1077.5	1076.7	1076.0	1075.3	1074.6
135°	1137.8	1138.5	1139.3	1139.3	1138.5	1137.8	1137.0	1136.3
137.5°	1193.6	1194.7	1196.0	1196.3	1195.8	1195.3	1194.8	1194.3
140°	1228.9	1229.9	1230.9	1231.2	1230.7	1230.1	1229.7	1229.1
142.5°	1262.4	1263.2	1264.1	1264.1	1263.4	1262.7	1261.9	1261.2
145°	1309.3	1309.7	1310.3	1310.5	1310.5	1310.5	1310.5	1310.5
147.5°	1351.2	1351.7	1352.3	1351.9	1350.8	1349.6	1348.4	1347.2
150°	1376.9	1377.4	1378.0	1377.8	1377.1	1376.3	1375.6	1374.8
152.5°	1399.7	1400.7	1401.6	1401.5	1400.3	1399.1	1397.9	1396.8
155°	1431.2	1432.4	1433.8	1433.6	1432.1	1430.6	1429.1	1427.5
157.5°	1458.6	1460.1	1461.6	1461.3	1459.4	1457.4	1455.4	1453.4
160°	1474.1	1475.7	1477.2	1477.0	1475.2	1473.5	1471.7	1469.9
162.5°	1488.3	1490.0	1491.7	1491.8	1490.2	1488.7	1487.1	1485.5
165°	1507.3	1509.3	1511.4	1511.4	1509.7	1507.9	1506.1	1504.3
167.5°	1522.0	1523.9	1526.0	1526.0	1523.9	1522.0	1519.9	1517.9
170°	1530.2	1532.2	1534.3	1534.3	1532.2	1530.2	1528.1	1526.1
172.5°	1535.7	1537.8	1539.8	1539.6	1537.4	1535.2	1532.9	1530.7
175°	1542.3	1544.1	1545.9	1545.7	1543.7	1541.7	1539.6	1537.6
177.5°	1544.7	1546.4	1548.0	1547.8	1545.8	1543.7	1541.7	1539.6
180°	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3	1543.3

(END OF REPORT)