

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332429-940

Luminaire Tested: **S123RDIW-S560D1535U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332429-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D1535U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6650.4 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	14
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	1.2
10°-20°	220.1	3.3
20°-30°	316.9	4.8
30°-40°	356.9	5.4
40°-50°	341.4	5.1
50°-60°	279.6	4.2
60°-70°	188.7	2.8
70°-80°	94.9	1.4
80°-90°	30.2	0.5
90°-100°	111.5	1.7
100°-110°	333.8	5.0
110°-120°	567.7	8.5
120°-130°	746.7	11.2
130°-140°	839.3	12.6
140°-150°	825.0	12.4
150°-160°	694.5	10.4
160°-170°	462.3	7.0
170°-180°	161.9	2.4
0°-30°	616.0	9.3
0°-40°	972.9	14.6
0°-60°	1594.0	24.0
0°-90°	1907.7	28.7
90°-120°	1013.0	15.2
90°-150°	3423.9	51.5
90°-180°	4743.0	71.3
0°-180°	6650.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	1	15	32	38	40	7
95°	79	89	100	105	105	89
105°	303	306	317	318	320	324
115°	572	575	573	574	573	565
125°	836	840	838	832	827	746
135°	1085	1093	1092	1087	1084	836
145°	1316	1319	1323	1322	1316	822
155°	1507	1507	1509	1513	1505	694
165°	1642	1638	1638	1645	1636	463
175°	1708	1703	1702	1709	1701	162
180°	1712	1712	1712	1712	1712	



TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.4	12.7	11.9	11.1	10.4	10.4	11.2	12.0	12.8	13.6	13.6
90°	1.3	4.4	7.3	10.3	13.3	16.8	20.6	24.5	28.4	32.3	33.4
92.5°	32.5	34.6	36.6	38.6	40.7	42.8	45.0	47.2	49.4	51.6	52.6
95°	79.4	81.4	83.6	85.6	87.7	90.0	92.3	94.7	97.1	99.5	100.7
97.5°	140.9	142.5	144.0	145.6	147.1	148.7	150.5	152.2	154.0	155.7	157.1
100°	182.9	184.7	186.5	188.2	190.0	191.7	193.1	194.7	196.2	197.7	198.6
102.5°	231.3	232.4	233.4	234.5	235.6	237.1	239.1	241.0	243.0	245.0	245.9
105°	302.6	303.2	303.7	304.3	305.0	306.6	309.2	311.9	314.7	317.4	317.4
107.5°	385.4	385.8	386.1	386.5	386.8	387.5	388.6	389.7	390.7	391.8	392.8
110°	437.0	437.7	438.2	438.8	439.4	440.0	440.6	441.2	441.8	442.4	443.6



TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	490.8	491.2	491.5	491.9	492.2	492.5	492.6	492.7	492.8	492.9	494.4
115°	571.5	572.4	573.3	574.2	575.1	575.2	574.6	574.0	573.5	572.8	573.1
117.5°	652.7	653.3	653.9	654.5	655.1	655.0	654.2	653.4	652.6	651.9	651.8
120°	703.3	705.1	706.9	708.6	710.4	710.6	709.1	707.6	706.1	704.6	704.3
122.5°	756.0	757.2	758.6	759.9	761.3	761.5	760.7	759.9	759.2	758.4	757.6
125°	836.3	837.2	838.2	839.1	840.0	840.1	839.5	838.9	838.3	837.8	836.5
127.5°	910.6	912.5	914.4	916.3	918.3	918.9	918.2	917.6	916.9	916.2	914.5
130°	960.1	962.5	964.8	967.2	969.6	970.4	969.5	968.6	967.7	966.8	965.6
132.5°	1009.6	1011.9	1014.3	1016.7	1019.1	1020.0	1019.3	1018.7	1018.0	1017.4	1015.9
135°	1085.1	1086.9	1088.7	1090.5	1092.3	1093.1	1092.8	1092.4	1092.2	1091.9	1090.7
137.5°	1155.0	1156.5	1158.1	1159.6	1161.0	1162.2	1163.0	1163.7	1164.5	1165.3	1164.0
140°	1203.5	1205.0	1206.5	1207.9	1209.4	1210.3	1210.7	1210.9	1211.2	1211.6	1211.2
142.5°	1247.6	1249.0	1250.5	1252.1	1253.6	1254.5	1255.1	1255.6	1256.2	1256.7	1256.4
145°	1316.4	1317.1	1317.6	1318.2	1318.8	1319.6	1320.4	1321.3	1322.2	1323.1	1322.9
147.5°	1376.6	1377.7	1378.8	1379.9	1381.0	1381.9	1382.8	1383.6	1384.4	1385.3	1385.3
150°	1418.6	1419.2	1419.8	1420.4	1421.0	1421.6	1422.2	1422.8	1423.3	1424.0	1424.0
152.5°	1453.0	1453.8	1454.7	1455.5	1456.3	1457.0	1457.3	1457.7	1458.0	1458.4	1458.9
155°	1507.3	1507.3	1507.3	1507.3	1507.3	1507.5	1507.8	1508.1	1508.4	1508.7	1509.9
157.5°	1553.6	1553.3	1552.9	1552.6	1552.2	1552.1	1552.4	1552.6	1552.8	1553.1	1554.3
160°	1582.7	1582.1	1581.4	1580.8	1580.3	1579.9	1579.9	1579.9	1579.9	1579.9	1581.4
162.5°	1608.5	1607.7	1606.8	1606.0	1605.2	1604.8	1605.1	1605.3	1605.5	1605.8	1607.3
165°	1641.8	1640.9	1640.0	1639.1	1638.3	1637.8	1637.8	1637.8	1637.8	1637.8	1639.6
167.5°	1668.5	1667.2	1666.1	1664.8	1663.7	1663.2	1663.4	1663.7	1663.9	1664.1	1666.0
170°	1683.5	1682.3	1681.1	1679.9	1678.7	1678.1	1678.1	1678.1	1678.1	1678.1	1680.3
172.5°	1695.3	1694.2	1692.9	1691.8	1690.6	1690.0	1690.0	1690.0	1690.0	1690.0	1691.8
175°	1707.7	1706.6	1705.3	1704.1	1702.9	1702.4	1702.4	1702.4	1702.4	1702.4	1704.1
177.5°	1712.8	1711.9	1710.9	1709.9	1709.0	1708.5	1708.5	1708.5	1708.5	1708.5	1709.9
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7



TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	13.8	13.9	14.0	14.1	14.1	14.1	14.1	14.1
90°	34.7	35.8	37.1	38.0	38.5	39.1	39.8	40.3
92.5°	53.5	54.5	55.5	55.7	55.4	55.0	54.7	54.3
95°	101.9	103.1	104.2	104.9	104.9	104.9	104.9	104.9
97.5°	158.5	159.8	161.2	161.8	161.8	161.6	161.5	161.4
100°	199.5	200.4	201.3	202.0	202.6	203.2	203.8	204.4
102.5°	246.8	247.7	248.6	249.0	248.9	248.7	248.6	248.5
105°	317.4	317.4	317.4	317.6	318.3	318.9	319.4	320.0
107.5°	393.8	394.7	395.7	395.9	395.6	395.2	394.8	394.5
110°	444.8	445.9	447.2	447.5	446.8	446.3	445.7	445.1



TEST NUMBER: P332429-940

CATALOG NUMBER: S123RDIW-S560D1535U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	495.8	497.2	498.6	499.4	499.3	499.1	499.0	498.8
115°	573.5	573.7	574.0	574.0	573.7	573.5	573.1	572.8
117.5°	651.8	651.8	651.7	651.2	650.3	649.5	648.7	647.8
120°	704.0	703.7	703.4	702.9	702.4	701.8	701.2	700.5
122.5°	756.8	756.1	755.3	754.5	753.7	752.8	752.0	751.1
125°	835.4	834.1	832.9	831.7	830.5	829.4	828.1	827.0
127.5°	912.9	911.2	909.5	908.0	906.7	905.3	903.9	902.5
130°	964.4	963.2	962.1	960.4	958.3	956.2	954.1	952.0
132.5°	1014.5	1013.1	1011.6	1010.1	1008.5	1006.9	1005.2	1003.6
135°	1089.5	1088.2	1087.1	1086.2	1085.6	1084.9	1084.4	1083.8
137.5°	1162.8	1161.5	1160.3	1159.0	1157.9	1156.8	1155.7	1154.5
140°	1210.9	1210.7	1210.3	1209.2	1207.0	1205.0	1202.8	1200.8
142.5°	1256.2	1255.8	1255.5	1254.5	1252.9	1251.3	1249.7	1248.1
145°	1322.5	1322.2	1322.0	1321.2	1320.0	1318.8	1317.6	1316.4
147.5°	1385.3	1385.3	1385.3	1384.4	1382.6	1380.8	1378.9	1377.2
150°	1424.0	1424.0	1424.0	1423.1	1421.3	1419.5	1417.7	1415.9
152.5°	1459.4	1459.8	1460.4	1459.8	1458.2	1456.7	1455.1	1453.6
155°	1511.1	1512.3	1513.5	1513.1	1510.9	1508.9	1506.7	1504.7
157.5°	1555.6	1556.8	1558.1	1557.9	1556.2	1554.5	1552.8	1551.2
160°	1583.0	1584.5	1585.9	1586.1	1584.9	1583.7	1582.5	1581.3
162.5°	1608.7	1610.3	1611.8	1611.6	1609.6	1607.8	1605.8	1603.9
165°	1641.4	1643.2	1644.9	1644.8	1642.7	1640.7	1638.5	1636.5
167.5°	1667.9	1669.7	1671.5	1671.5	1669.7	1667.9	1666.0	1664.1
170°	1682.3	1684.4	1686.5	1686.5	1684.4	1682.3	1680.3	1678.1
172.5°	1693.6	1695.5	1697.4	1697.3	1695.1	1693.1	1691.0	1688.9
175°	1705.9	1707.7	1709.5	1709.3	1707.3	1705.1	1703.1	1701.0
177.5°	1711.4	1712.8	1714.2	1714.1	1712.4	1710.7	1709.1	1707.4
180°	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7	1711.7

(END OF REPORT)