

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332411-940

Luminaire Tested: **S123RDIW-S560D460U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332411-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D460U940-4F0-1E-UDD-A1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3413.3 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	93	89	93	90	87	84	78	76	74	67	66	64	57	56	55	50
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	51	49	47	43
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33
5	71	60	52	46	66	57	49	44	50	44	40	44	39	36	38	34	32	29
6	66	54	46	41	61	51	44	39	45	39	35	40	35	32	35	31	28	26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	31	38	32	28	33	29	25	29	26	23	21
9	53	41	34	29	50	39	32	28	35	29	25	31	26	23	27	23	21	19
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8587	8587	8587	8587
5°	10237	8625	7595	8625
10°	12783	8575	6862	8575
15°	15004	8487	6257	8487
20°	16745	8356	5743	8356
25°	16476	8219	5428	8219
30°	11844	8090	5102	8090
35°	7908	7926	4892	7926
40°	5826	7727	4675	7727
45°	4886	7377	4460	7377
50°	4312	6921	4163	6921
55°	3781	6397	3755	6397
60°	3367	5896	3442	5896
65°	2957	5359	3202	5359
70°	2319	4881	2924	4881
75°	2046	4263	2670	4263
80°	1779	3620	2628	3620
85°	1433	2902	2791	2902



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	78.5	2.3
10°-20°	245.1	7.2
20°-30°	385.1	11.3
30°-40°	401.8	11.8
40°-50°	343.8	10.1
50°-60°	262.1	7.7
60°-70°	168.0	4.9
70°-80°	80.8	2.4
80°-90°	22.9	0.7
90°-100°	33.5	1.0
100°-110°	100.3	2.9
110°-120°	170.6	5.0
120°-130°	224.4	6.6
130°-140°	252.2	7.4
140°-150°	247.9	7.3
150°-160°	208.7	6.1
160°-170°	138.9	4.1
170°-180°	48.7	1.4
0°-30°	708.7	20.8
0°-40°	1110.4	32.5
0°-60°	1716.3	50.3
0°-90°	1988.0	58.2
90°-120°	304.4	8.9
90°-150°	1029.0	30.1
90°-180°	1425.0	41.7
0°-180°	3413.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	798	798	798	798	798	
5°	947	798	703	798	947	98
15°	1346	762	562	762	1346	382
25°	1387	692	457	692	1387	596
35°	602	603	372	603	602	395
45°	321	485	293	485	321	252
55°	202	341	200	341	202	182
65°	116	210	126	210	116	114
75°	49	102	64	102	49	53
85°	12	24	23	24	12	14
90°	12	0	12	0	12	6
95°	32	24	32	24	32	32
105°	96	91	96	91	96	102
115°	172	172	172	172	172	170
125°	248	251	248	251	248	222
135°	326	326	326	326	326	250
145°	396	396	396	396	396	247
155°	452	453	452	453	452	208
165°	492	493	492	493	492	139
175°	511	513	511	513	511	49
180°	514	514	514	514	514	



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	849.7	850.9	847.3	846.8	842.7	841.6	841.6	835.8	832.2	827.6	824.9
5°	947.4	952.9	950.2	944.1	933.8	931.4	924.9	914.6	903.0	888.7	881.9
7.5°	1069.4	1076.9	1074.0	1064.5	1053.8	1045.1	1026.8	1009.8	986.0	965.1	947.2
10°	1169.5	1161.5	1155.5	1146.2	1136.3	1120.3	1101.2	1074.9	1044.5	1020.6	993.9
12.5°	1244.3	1243.0	1235.2	1225.7	1211.7	1196.5	1173.0	1140.9	1105.6	1071.0	1040.6
15°	1346.4	1348.4	1343.3	1333.4	1313.6	1286.6	1251.1	1237.8	1187.2	1149.6	1112.1
17.5°	1417.0	1416.6	1415.9	1402.1	1382.0	1362.7	1329.8	1294.8	1249.0	1196.1	1145.5
20°	1461.8	1458.4	1459.1	1443.7	1428.7	1406.5	1374.4	1323.5	1285.9	1224.8	1172.5
22.5°	1460.7	1460.0	1462.6	1457.3	1446.4	1429.4	1404.2	1361.2	1313.2	1251.5	1192.8
25°	1387.3	1384.6	1400.7	1405.1	1422.5	1425.6	1418.1	1394.5	1349.1	1285.6	1212.8
27.5°	1161.1	1159.6	1189.4	1226.6	1274.0	1310.7	1346.2	1363.3	1349.1	1303.6	1230.7
30°	952.9	985.0	1000.1	1054.0	1114.1	1185.8	1248.7	1308.4	1323.1	1303.3	1243.6
32.5°	791.1	819.1	831.7	878.1	934.1	1018.1	1112.3	1196.9	1256.8	1271.9	1235.9
35°	601.8	602.2	630.8	651.3	703.2	789.6	881.2	994.5	1107.2	1192.7	1201.6
37.5°	480.2	481.9	499.3	519.7	558.7	604.3	684.9	779.2	909.4	1040.4	1117.3
40°	414.6	417.7	430.7	450.8	478.8	513.4	576.2	664.9	773.6	919.4	1038.7
42.5°	372.6	377.6	384.2	399.8	417.1	449.4	500.2	568.8	667.5	805.5	943.0
45°	321.0	323.8	328.9	336.1	351.8	374.3	408.5	454.6	536.5	647.6	785.2
47.5°	283.2	281.8	287.1	293.0	303.4	318.8	341.7	379.3	437.8	526.8	643.6
50°	257.5	257.2	260.9	265.4	275.3	286.6	305.3	333.7	380.1	453.9	560.8
52.5°	233.4	234.8	237.5	243.0	250.1	259.2	276.1	296.5	336.4	400.1	489.2
55°	201.5	202.5	206.3	209.4	214.5	223.7	234.3	251.4	278.7	323.1	396.5
57.5°	174.4	174.0	177.6	178.3	184.1	191.6	199.8	213.1	232.9	265.9	315.4
60°	156.4	155.4	158.5	160.9	163.9	170.0	176.9	189.9	205.6	229.9	272.2
62.5°	140.0	139.6	141.8	144.2	146.7	152.3	158.1	168.0	180.5	200.9	234.5
65°	116.1	117.2	118.2	119.2	120.6	123.9	129.5	136.3	144.8	159.2	183.4
67.5°	91.2	92.3	92.6	94.7	97.6	99.8	103.2	109.2	115.2	127.2	141.1
70°	73.7	73.4	73.7	74.8	78.6	82.3	86.8	91.2	95.0	103.5	115.1
72.5°	63.4	62.8	63.7	63.8	65.7	66.7	69.6	73.7	78.6	84.4	92.7
75°	49.2	49.2	49.2	49.2	50.6	51.3	52.3	53.3	55.0	57.7	63.8
77.5°	36.4	36.4	36.9	37.2	37.5	37.9	38.5	39.6	40.1	41.6	44.2
80°	28.7	29.1	28.7	29.1	29.1	29.7	30.1	31.1	31.4	33.2	34.2
82.5°	21.6	21.4	21.6	21.9	21.9	22.6	22.6	23.5	23.5	24.3	25.4
85°	11.6	11.0	11.6	11.2	11.9	11.2	11.6	12.3	12.3	12.7	14.0
87.5°	5.2	5.7	5.1	5.4	5.3	5.5	5.4	5.4	5.8	5.5	5.5
90°	12.1	11.9	11.8	11.6	11.4	11.1	10.8	10.4	10.1	9.7	8.6
92.5°	16.3	16.4	16.5	16.7	16.8	16.7	16.4	16.1	15.8	15.5	14.9
95°	31.5	31.5	31.5	31.5	31.5	31.3	30.9	30.6	30.2	29.9	29.2
97.5°	48.5	48.5	48.6	48.6	48.6	48.4	48.1	47.6	47.2	46.8	46.3
100°	61.4	61.3	61.1	60.9	60.7	60.5	60.2	59.9	59.7	59.4	58.9
102.5°	74.6	74.7	74.7	74.8	74.8	74.7	74.5	74.2	73.9	73.7	73.0
105°	96.2	96.0	95.9	95.7	95.4	95.3	95.3	95.3	95.3	95.3	94.5
107.5°	118.6	118.7	118.8	118.9	119.0	118.9	118.6	118.3	118.1	117.8	117.4
110°	133.8	133.9	134.1	134.3	134.5	134.4	134.0	133.7	133.3	133.0	132.8



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	149.9	150.0	150.0	150.0	150.1	149.9	149.5	149.0	148.6	148.1	148.1
115°	172.2	172.3	172.4	172.5	172.5	172.5	172.5	172.4	172.3	172.2	172.4
117.5°	194.7	194.9	195.2	195.5	195.7	195.8	195.8	195.9	195.9	195.9	196.2
120°	210.5	210.7	210.9	211.1	211.2	211.4	211.5	211.6	211.7	211.8	212.2
122.5°	225.7	226.0	226.2	226.5	226.8	226.9	227.2	227.5	227.7	227.9	228.2
125°	248.5	248.9	249.2	249.6	249.9	250.3	250.7	251.0	251.4	251.7	251.9
127.5°	271.3	271.6	272.1	272.5	272.9	273.3	273.8	274.4	274.8	275.4	275.5
130°	286.1	286.8	287.4	288.0	288.6	289.1	289.4	289.8	290.2	290.5	290.8
132.5°	301.6	302.1	302.6	303.1	303.5	304.0	304.4	304.9	305.3	305.8	305.9
135°	325.7	325.9	326.1	326.3	326.5	326.7	327.1	327.4	327.8	328.1	328.2
137.5°	347.0	347.3	347.7	347.9	348.3	348.7	349.1	349.5	349.8	350.2	350.0
140°	360.9	361.5	362.1	362.7	363.4	363.7	363.8	363.9	364.0	364.1	364.0
142.5°	375.1	375.6	376.0	376.6	377.0	377.3	377.4	377.5	377.6	377.6	377.6
145°	395.7	396.0	396.4	396.7	397.1	397.3	397.3	397.4	397.5	397.6	397.3
147.5°	413.8	414.4	414.9	415.5	416.1	416.3	416.3	416.3	416.3	416.3	416.1
150°	425.5	426.1	426.6	427.1	427.7	427.9	427.9	427.9	427.9	427.9	427.8
152.5°	436.8	437.3	437.7	438.3	438.7	438.9	438.7	438.5	438.5	438.3	438.2
155°	452.2	452.8	453.4	454.1	454.7	454.9	454.5	454.1	453.8	453.4	453.3
157.5°	466.2	466.6	467.2	467.7	468.1	468.2	467.9	467.5	467.1	466.7	466.6
160°	475.2	475.5	475.9	476.3	476.6	476.6	476.2	475.7	475.3	474.8	474.8
162.5°	482.0	482.6	483.1	483.8	484.3	484.4	483.9	483.5	483.0	482.6	482.5
165°	491.8	492.4	493.0	493.7	494.3	494.4	493.8	493.3	492.8	492.2	492.2
167.5°	500.1	500.7	501.2	501.8	502.3	502.3	501.8	501.2	500.7	500.1	500.1
170°	504.4	505.0	505.6	506.2	506.8	506.8	506.2	505.6	505.0	504.4	504.4
172.5°	507.6	508.2	508.8	509.4	510.1	510.1	509.5	509.0	508.5	507.8	507.8
175°	511.2	511.8	512.5	513.1	513.7	513.7	513.2	512.6	512.1	511.6	511.6
177.5°	513.1	513.6	514.2	514.6	515.1	515.1	514.8	514.3	513.9	513.4	513.4
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	823.8	823.0	819.1	814.8	809.0	805.2	802.2	800.6	795.7	789.6	785.5
5°	874.7	864.4	853.5	840.2	827.9	815.3	807.4	798.2	786.9	774.3	765.4
7.5°	929.2	909.1	887.4	865.1	843.0	823.2	805.7	790.8	772.8	754.7	742.0
10°	971.0	941.6	911.2	880.1	851.8	825.2	804.7	784.5	763.0	742.2	726.5
12.5°	1009.0	970.4	935.3	897.1	860.9	829.0	799.5	775.8	749.9	727.7	709.8
15°	1057.0	1017.4	975.1	917.0	868.9	828.6	792.7	761.6	730.2	702.9	685.5
17.5°	1102.0	1042.4	985.5	937.0	874.5	824.1	780.3	743.2	708.7	679.8	658.3
20°	1120.6	1062.9	1001.0	939.2	877.8	821.4	770.5	729.5	693.7	660.8	641.1
22.5°	1131.8	1066.4	1001.3	934.9	869.6	811.0	760.7	715.6	676.7	645.6	621.2
25°	1144.9	1066.9	995.2	929.7	863.1	799.5	739.8	692.0	650.0	616.8	590.8
27.5°	1153.4	1061.8	977.0	904.2	836.6	773.4	718.6	667.9	625.3	590.2	562.4
30°	1155.1	1057.7	963.1	884.2	815.6	757.5	699.5	650.9	605.9	568.6	542.7
32.5°	1157.3	1047.7	944.3	860.5	790.2	732.7	680.1	633.7	587.5	550.9	524.4
35°	1148.3	1042.1	915.7	819.4	749.0	693.3	645.9	603.2	557.8	522.2	495.3
37.5°	1109.5	1019.8	886.0	773.0	699.5	647.9	609.2	572.0	530.4	492.0	466.6
40°	1070.4	998.0	863.1	744.9	668.1	615.1	580.2	549.9	509.6	473.7	446.4
42.5°	1012.2	968.2	841.2	715.4	632.5	581.5	552.1	523.6	488.3	451.8	426.1
45°	905.4	911.2	796.5	668.4	583.4	532.1	504.4	484.6	453.3	423.2	396.9
47.5°	771.5	825.8	744.0	618.3	531.5	483.4	459.2	441.9	420.8	391.3	367.3
50°	684.1	761.6	701.9	584.7	499.0	451.2	427.3	413.3	394.8	371.6	348.7
52.5°	603.5	686.8	651.0	547.2	463.8	420.0	396.6	385.1	370.5	348.7	328.0
55°	492.1	576.5	568.3	490.8	410.9	371.6	353.8	340.9	330.9	314.6	298.2
57.5°	398.1	478.0	482.3	427.9	364.3	325.5	310.2	300.4	293.9	281.6	266.4
60°	338.9	412.2	426.6	385.6	330.9	296.8	281.8	273.9	268.8	258.9	247.3
62.5°	289.6	352.1	368.4	338.9	299.0	267.0	255.3	247.7	244.2	235.7	225.4
65°	221.7	273.6	289.3	272.9	252.1	226.4	216.9	210.4	207.3	202.5	195.0
67.5°	166.7	204.6	221.8	210.2	202.7	186.5	180.4	176.9	174.2	170.9	164.6
70°	133.8	161.9	179.7	176.6	170.4	161.9	157.5	155.1	152.3	149.6	144.1
72.5°	107.6	126.9	143.6	145.2	140.1	138.4	134.5	133.5	131.8	128.6	125.6
75°	71.4	84.7	96.3	100.8	102.8	104.5	102.8	102.5	102.1	99.4	97.6
77.5°	46.8	53.9	61.3	68.8	72.1	74.4	74.9	76.2	75.3	73.8	73.0
80°	35.8	37.5	42.7	49.2	54.3	56.4	57.7	58.4	58.1	57.7	56.4
82.5°	26.0	27.5	29.9	34.4	38.7	42.2	43.0	42.8	43.6	43.8	42.7
85°	14.0	14.4	15.1	15.7	18.1	21.8	22.9	23.5	24.3	24.3	22.2
87.5°	5.9	5.4	5.6	5.4	6.1	6.2	7.7	8.8	9.3	8.4	8.6
90°	7.4	6.2	5.0	4.0	3.1	2.2	1.3	0.4	1.3	2.2	3.1
92.5°	14.2	13.6	12.8	12.2	11.6	11.0	10.4	9.8	10.4	11.0	11.6
95°	28.4	27.7	27.0	26.4	25.8	25.1	24.4	23.8	24.4	25.1	25.8
97.5°	45.7	45.2	44.7	44.2	43.8	43.2	42.8	42.4	42.8	43.2	43.8
100°	58.5	58.1	57.6	57.1	56.5	56.0	55.5	54.9	55.5	56.0	56.5
102.5°	72.4	71.9	71.2	70.8	70.4	70.2	69.8	69.5	69.8	70.2	70.4
105°	93.7	92.9	92.1	91.7	91.5	91.3	91.1	91.0	91.1	91.3	91.5
107.5°	117.1	116.8	116.5	116.3	116.1	116.0	115.9	115.8	115.9	116.0	116.1
110°	132.6	132.4	132.2	132.1	131.9	131.7	131.5	131.3	131.5	131.7	131.9





TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	148.1	148.0	148.0	147.9	147.8	147.8	147.6	147.5	147.6	147.8	147.8
115°	172.5	172.7	172.9	172.8	172.5	172.3	172.0	171.7	172.0	172.3	172.5
117.5°	196.4	196.6	196.8	196.9	196.7	196.5	196.4	196.2	196.4	196.5	196.7
120°	212.7	213.1	213.6	213.5	212.9	212.4	211.9	211.3	211.9	212.4	212.9
122.5°	228.4	228.6	228.8	228.7	228.4	228.0	227.6	227.2	227.6	228.0	228.4
125°	252.1	252.3	252.4	252.4	252.2	251.9	251.6	251.4	251.6	251.9	252.2
127.5°	275.7	276.0	276.2	276.0	275.4	274.8	274.2	273.7	274.2	274.8	275.4
130°	291.1	291.3	291.6	291.4	290.7	290.0	289.3	288.6	289.3	290.0	290.7
132.5°	306.1	306.3	306.6	306.3	305.6	304.9	304.1	303.4	304.1	304.9	305.6
135°	328.3	328.4	328.5	328.2	327.7	327.2	326.6	326.1	326.6	327.2	327.7
137.5°	349.7	349.5	349.3	348.9	348.5	348.0	347.6	347.1	347.6	348.0	348.5
140°	363.9	363.8	363.7	363.5	363.0	362.6	362.1	361.7	362.1	362.6	363.0
142.5°	377.4	377.2	377.0	376.7	376.3	375.9	375.4	375.0	375.4	375.9	376.3
145°	397.1	396.8	396.5	396.4	396.2	396.0	395.8	395.7	395.8	396.0	396.2
147.5°	415.8	415.5	415.3	415.0	414.6	414.4	414.0	413.8	414.0	414.4	414.6
150°	427.6	427.4	427.2	427.0	426.9	426.7	426.5	426.3	426.5	426.7	426.9
152.5°	438.1	437.9	437.8	437.7	437.4	437.2	436.9	436.7	436.9	437.2	437.4
155°	453.3	453.2	453.1	453.0	453.0	453.0	453.0	453.0	453.0	453.0	453.0
157.5°	466.6	466.5	466.5	466.5	466.5	466.7	466.8	466.9	466.8	466.7	466.5
160°	474.8	474.8	474.8	474.9	475.1	475.3	475.5	475.6	475.5	475.3	475.1
162.5°	482.4	482.3	482.3	482.4	482.6	482.9	483.1	483.4	483.1	482.9	482.6
165°	492.2	492.2	492.2	492.3	492.6	492.8	493.1	493.4	493.1	492.8	492.6
167.5°	500.0	499.9	499.8	500.0	500.3	500.7	501.1	501.4	501.1	500.7	500.3
170°	504.4	504.4	504.4	504.5	504.9	505.2	505.6	506.0	505.6	505.2	504.9
172.5°	507.8	507.8	507.8	508.0	508.5	508.8	509.2	509.5	509.2	508.8	508.5
175°	511.6	511.6	511.6	511.8	512.1	512.5	512.8	513.2	512.8	512.5	512.1
177.5°	513.4	513.4	513.4	513.6	513.9	514.2	514.4	514.8	514.4	514.2	513.9
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	784.2	780.6	778.2	772.7	769.2	765.4	761.5	763.9	763.7	763.4	763.4
5°	757.9	750.0	742.9	733.6	727.8	720.7	715.2	714.5	715.9	711.1	708.4
7.5°	731.8	721.0	710.9	700.7	689.9	681.3	675.9	673.4	669.9	667.0	663.9
10°	713.5	700.9	690.9	678.3	666.7	656.5	650.0	645.5	643.1	640.7	636.3
12.5°	694.6	682.2	669.6	655.3	644.3	632.4	627.6	622.6	618.0	615.3	609.2
15°	667.0	650.9	637.7	622.6	610.4	598.7	591.9	582.0	580.6	577.2	571.1
17.5°	639.4	622.0	603.6	592.5	578.5	566.5	556.1	552.8	543.0	539.3	534.0
20°	617.5	601.5	587.5	572.7	552.6	541.4	533.2	528.7	520.8	516.0	512.6
22.5°	598.7	582.3	566.1	549.0	532.4	519.8	513.7	506.8	502.6	495.9	492.1
25°	571.8	554.0	534.5	516.0	504.1	494.5	485.0	478.8	472.7	469.6	462.8
27.5°	540.5	521.9	503.7	489.7	475.0	465.6	456.9	451.5	444.1	438.9	435.2
30°	523.3	501.4	485.7	473.1	454.2	445.4	438.9	432.0	426.6	421.2	417.3
32.5°	503.3	483.3	468.4	452.8	438.4	428.7	420.3	414.3	409.7	404.5	400.7
35°	472.0	455.3	439.9	424.2	413.6	403.7	393.8	388.7	384.2	379.4	376.0
37.5°	443.7	428.1	413.5	398.6	385.5	377.4	369.4	365.5	359.5	356.3	352.8
40°	426.2	410.9	395.2	380.8	367.1	361.1	353.8	348.0	342.6	340.2	336.4
42.5°	407.2	391.7	378.5	363.0	351.9	343.5	336.9	330.6	326.5	323.0	320.8
45°	378.8	365.1	352.1	336.8	326.2	319.0	311.5	305.7	301.9	299.5	295.8
47.5°	351.2	337.6	324.4	311.0	300.8	292.6	285.1	281.0	276.1	273.1	270.5
50°	331.3	319.0	305.0	292.7	282.5	274.3	268.1	263.0	258.5	254.8	253.1
52.5°	313.0	299.9	287.8	276.3	265.6	256.2	250.7	245.2	241.9	237.6	235.6
55°	282.8	270.2	259.9	248.6	238.1	230.2	223.4	218.6	215.2	210.4	207.7
57.5°	254.4	243.1	230.9	221.1	210.2	203.6	197.9	191.4	187.3	183.5	180.8
60°	235.3	222.3	211.8	202.5	193.0	184.4	179.3	174.2	169.8	165.9	163.6
62.5°	215.3	204.0	194.0	184.0	175.2	167.7	161.8	157.5	153.6	151.2	148.8
65°	184.8	175.9	165.7	157.5	149.3	143.8	139.0	135.3	132.5	130.8	128.8
67.5°	156.7	148.0	139.1	131.0	125.6	121.4	118.2	115.0	113.7	111.5	110.1
70°	138.3	129.5	121.6	115.5	109.9	106.9	104.9	102.5	101.1	98.4	97.0
72.5°	118.4	112.0	106.3	101.2	96.8	94.1	91.5	88.5	86.3	83.4	81.9
75°	93.3	87.5	83.0	79.5	76.9	73.1	69.4	66.3	65.3	64.2	63.8
77.5°	69.0	65.4	62.2	59.3	55.9	53.1	52.3	51.6	51.5	50.9	50.9
80°	54.3	50.9	48.5	45.1	43.1	43.1	43.1	42.4	42.7	42.7	42.7
82.5°	40.4	37.2	35.9	34.7	34.3	34.6	34.6	34.7	34.5	35.0	34.8
85°	20.9	21.1	21.8	21.5	21.8	21.8	22.6	22.2	22.6	21.8	22.6
87.5°	8.5	9.5	10.0	10.5	11.0	11.0	11.3	11.4	11.7	11.8	11.9
90°	4.0	5.0	6.2	7.4	8.6	9.7	10.1	10.4	10.8	11.1	11.4
92.5°	12.2	12.8	13.6	14.2	14.9	15.5	15.8	16.1	16.4	16.7	16.8
95°	26.4	27.0	27.7	28.4	29.2	29.9	30.2	30.6	30.9	31.3	31.5
97.5°	44.2	44.7	45.2	45.7	46.3	46.8	47.2	47.6	48.1	48.4	48.6
100°	57.1	57.6	58.1	58.5	58.9	59.4	59.7	59.9	60.2	60.5	60.7
102.5°	70.8	71.2	71.9	72.4	73.0	73.7	73.9	74.2	74.5	74.7	74.8
105°	91.7	92.1	92.9	93.7	94.5	95.3	95.3	95.3	95.3	95.3	95.4
107.5°	116.3	116.5	116.8	117.1	117.4	117.8	118.1	118.3	118.6	118.9	119.0
110°	132.1	132.2	132.4	132.6	132.8	133.0	133.3	133.7	134.0	134.4	134.5



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	147.9	148.0	148.0	148.1	148.1	148.1	148.6	149.0	149.5	149.9	150.1
115°	172.8	172.9	172.7	172.5	172.4	172.2	172.3	172.4	172.5	172.5	172.5
117.5°	196.9	196.8	196.6	196.4	196.2	195.9	195.9	195.9	195.8	195.8	195.7
120°	213.5	213.6	213.1	212.7	212.2	211.8	211.7	211.6	211.5	211.4	211.2
122.5°	228.7	228.8	228.6	228.4	228.2	227.9	227.7	227.5	227.2	226.9	226.8
125°	252.4	252.4	252.3	252.1	251.9	251.7	251.4	251.0	250.7	250.3	249.9
127.5°	276.0	276.2	276.0	275.7	275.5	275.4	274.8	274.4	273.8	273.3	272.9
130°	291.4	291.6	291.3	291.1	290.8	290.5	290.2	289.8	289.4	289.1	288.6
132.5°	306.3	306.6	306.3	306.1	305.9	305.8	305.3	304.9	304.4	304.0	303.5
135°	328.2	328.5	328.4	328.3	328.2	328.1	327.8	327.4	327.1	326.7	326.5
137.5°	348.9	349.3	349.5	349.7	350.0	350.2	349.8	349.5	349.1	348.7	348.3
140°	363.5	363.7	363.8	363.9	364.0	364.1	364.0	363.9	363.8	363.7	363.4
142.5°	376.7	377.0	377.2	377.4	377.6	377.6	377.6	377.5	377.4	377.3	377.0
145°	396.4	396.5	396.8	397.1	397.3	397.6	397.5	397.4	397.3	397.3	397.1
147.5°	415.0	415.3	415.5	415.8	416.1	416.3	416.3	416.3	416.3	416.3	416.1
150°	427.0	427.2	427.4	427.6	427.8	427.9	427.9	427.9	427.9	427.9	427.7
152.5°	437.7	437.8	437.9	438.1	438.2	438.3	438.5	438.5	438.7	438.9	438.7
155°	453.0	453.1	453.2	453.3	453.3	453.4	453.8	454.1	454.5	454.9	454.7
157.5°	466.5	466.5	466.5	466.6	466.6	466.7	467.1	467.5	467.9	468.2	468.1
160°	474.9	474.8	474.8	474.8	474.8	474.8	475.3	475.7	476.2	476.6	476.6
162.5°	482.4	482.3	482.3	482.4	482.5	482.6	483.0	483.5	483.9	484.4	484.3
165°	492.3	492.2	492.2	492.2	492.2	492.2	492.8	493.3	493.8	494.4	494.3
167.5°	500.0	499.8	499.9	500.0	500.1	500.1	500.7	501.2	501.8	502.3	502.3
170°	504.5	504.4	504.4	504.4	504.4	504.4	505.0	505.6	506.2	506.8	506.8
172.5°	508.0	507.8	507.8	507.8	507.8	507.8	508.5	509.0	509.5	510.1	510.1
175°	511.8	511.6	511.6	511.6	511.6	511.6	512.1	512.6	513.2	513.7	513.7
177.5°	513.6	513.4	513.4	513.4	513.4	513.4	513.9	514.3	514.8	515.1	515.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	760.1	759.8	760.1	759.0	760.1	759.8	760.1	763.4	763.4	763.7	763.9
5°	707.3	706.9	706.0	702.9	706.0	706.9	707.3	708.4	711.1	715.9	714.5
7.5°	661.2	660.8	657.7	657.8	657.7	660.8	661.2	663.9	667.0	669.9	673.4
10°	633.9	634.3	630.2	627.8	630.2	634.3	633.9	636.3	640.7	643.1	645.5
12.5°	607.4	605.8	602.5	599.9	602.5	605.8	607.4	609.2	615.3	618.0	622.6
15°	572.4	569.0	560.8	561.5	560.8	569.0	572.4	571.1	577.2	580.6	582.0
17.5°	531.2	528.7	528.6	523.8	528.6	528.7	531.2	534.0	539.3	543.0	552.8
20°	507.2	505.5	506.1	501.4	506.1	505.5	507.2	512.6	516.0	520.8	528.7
22.5°	488.3	486.6	483.8	482.2	483.8	486.6	488.3	492.1	495.9	502.6	506.8
25°	460.7	458.0	455.3	457.0	455.3	458.0	460.7	462.8	469.6	472.7	478.8
27.5°	433.1	431.1	428.4	428.0	428.4	431.1	433.1	435.2	438.9	444.1	451.5
30°	415.6	413.6	412.2	410.5	412.2	413.6	415.6	417.3	421.2	426.6	432.0
32.5°	397.9	397.5	395.0	394.7	395.0	397.5	397.9	400.7	404.5	409.7	414.3
35°	374.7	372.6	371.9	372.3	371.9	372.6	374.7	376.0	379.4	384.2	388.7
37.5°	352.6	349.9	348.7	347.4	348.7	349.9	352.6	352.8	356.3	359.5	365.5
40°	336.8	334.0	333.3	332.7	333.3	334.0	336.8	336.4	340.2	342.6	348.0
42.5°	319.0	317.9	317.5	316.3	317.5	317.9	319.0	320.8	323.0	326.5	330.6
45°	294.7	294.4	292.4	293.0	292.4	294.4	294.7	295.8	299.5	301.9	305.7
47.5°	269.2	267.7	266.3	267.2	266.3	267.7	269.2	270.5	273.1	276.1	281.0
50°	251.7	251.0	248.0	248.6	248.0	251.0	251.7	253.1	254.8	258.5	263.0
52.5°	234.3	231.7	230.5	230.1	230.5	231.7	234.3	235.6	237.6	241.9	245.2
55°	205.3	202.2	200.8	200.1	200.8	202.2	205.3	207.7	210.4	215.2	218.6
57.5°	176.8	176.0	175.0	175.7	175.0	176.0	176.8	180.8	183.5	187.3	191.4
60°	160.2	160.2	160.2	159.9	160.2	160.2	160.2	163.6	165.9	169.8	174.2
62.5°	147.3	146.5	146.2	146.7	146.2	146.5	147.3	148.8	151.2	153.6	157.5
65°	127.7	127.4	126.0	125.7	126.0	127.4	127.7	128.8	130.8	132.5	135.3
67.5°	109.2	108.0	107.6	107.1	107.6	108.0	109.2	110.1	111.5	113.7	115.0
70°	95.3	94.6	92.6	92.9	92.6	94.6	95.3	97.0	98.4	101.1	102.5
72.5°	80.3	79.5	79.2	78.6	79.2	79.5	80.3	81.9	83.4	86.3	88.5
75°	63.5	63.2	62.9	64.2	62.9	63.2	63.5	63.8	64.2	65.3	66.3
77.5°	50.9	50.9	51.1	50.6	51.1	50.9	50.9	50.9	50.9	51.5	51.6
80°	42.7	42.7	42.4	42.4	42.4	42.7	42.7	42.7	42.7	42.7	42.4
82.5°	34.2	34.5	34.7	34.2	34.7	34.5	34.2	34.8	35.0	34.5	34.7
85°	22.6	22.2	22.9	22.6	22.9	22.2	22.6	22.6	21.8	22.6	22.2
87.5°	12.4	11.9	11.9	12.2	11.9	11.9	12.4	11.9	11.8	11.7	11.4
90°	11.6	11.8	11.9	12.1	11.9	11.8	11.6	11.4	11.1	10.8	10.4
92.5°	16.7	16.5	16.4	16.3	16.4	16.5	16.7	16.8	16.7	16.4	16.1
95°	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.5	31.3	30.9	30.6
97.5°	48.6	48.6	48.5	48.5	48.5	48.6	48.6	48.6	48.4	48.1	47.6
100°	60.9	61.1	61.3	61.4	61.3	61.1	60.9	60.7	60.5	60.2	59.9
102.5°	74.8	74.7	74.7	74.6	74.7	74.7	74.8	74.8	74.7	74.5	74.2
105°	95.7	95.9	96.0	96.2	96.0	95.9	95.7	95.4	95.3	95.3	95.3
107.5°	118.9	118.8	118.7	118.6	118.7	118.8	118.9	119.0	118.9	118.6	118.3
110°	134.3	134.1	133.9	133.8	133.9	134.1	134.3	134.5	134.4	134.0	133.7



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	150.0	150.0	150.0	149.9	150.0	150.0	150.0	150.1	149.9	149.5	149.0
115°	172.5	172.4	172.3	172.2	172.3	172.4	172.5	172.5	172.5	172.5	172.4
117.5°	195.5	195.2	194.9	194.7	194.9	195.2	195.5	195.7	195.8	195.8	195.9
120°	211.1	210.9	210.7	210.5	210.7	210.9	211.1	211.2	211.4	211.5	211.6
122.5°	226.5	226.2	226.0	225.7	226.0	226.2	226.5	226.8	226.9	227.2	227.5
125°	249.6	249.2	248.9	248.5	248.9	249.2	249.6	249.9	250.3	250.7	251.0
127.5°	272.5	272.1	271.6	271.3	271.6	272.1	272.5	272.9	273.3	273.8	274.4
130°	288.0	287.4	286.8	286.1	286.8	287.4	288.0	288.6	289.1	289.4	289.8
132.5°	303.1	302.6	302.1	301.6	302.1	302.6	303.1	303.5	304.0	304.4	304.9
135°	326.3	326.1	325.9	325.7	325.9	326.1	326.3	326.5	326.7	327.1	327.4
137.5°	347.9	347.7	347.3	347.0	347.3	347.7	347.9	348.3	348.7	349.1	349.5
140°	362.7	362.1	361.5	360.9	361.5	362.1	362.7	363.4	363.7	363.8	363.9
142.5°	376.6	376.0	375.6	375.1	375.6	376.0	376.6	377.0	377.3	377.4	377.5
145°	396.7	396.4	396.0	395.7	396.0	396.4	396.7	397.1	397.3	397.3	397.4
147.5°	415.5	414.9	414.4	413.8	414.4	414.9	415.5	416.1	416.3	416.3	416.3
150°	427.1	426.6	426.1	425.5	426.1	426.6	427.1	427.7	427.9	427.9	427.9
152.5°	438.3	437.7	437.3	436.8	437.3	437.7	438.3	438.7	438.9	438.7	438.5
155°	454.1	453.4	452.8	452.2	452.8	453.4	454.1	454.7	454.9	454.5	454.1
157.5°	467.7	467.2	466.6	466.2	466.6	467.2	467.7	468.1	468.2	467.9	467.5
160°	476.3	475.9	475.5	475.2	475.5	475.9	476.3	476.6	476.6	476.2	475.7
162.5°	483.8	483.1	482.6	482.0	482.6	483.1	483.8	484.3	484.4	483.9	483.5
165°	493.7	493.0	492.4	491.8	492.4	493.0	493.7	494.3	494.4	493.8	493.3
167.5°	501.8	501.2	500.7	500.1	500.7	501.2	501.8	502.3	502.3	501.8	501.2
170°	506.2	505.6	505.0	504.4	505.0	505.6	506.2	506.8	506.8	506.2	505.6
172.5°	509.4	508.8	508.2	507.6	508.2	508.8	509.4	510.1	510.1	509.5	509.0
175°	513.1	512.5	511.8	511.2	511.8	512.5	513.1	513.7	513.7	513.2	512.6
177.5°	514.6	514.2	513.6	513.1	513.6	514.2	514.6	515.1	515.1	514.8	514.3
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	761.5	765.4	769.2	772.7	778.2	780.6	784.2	785.5	789.6	795.7	800.6
5°	715.2	720.7	727.8	733.6	742.9	750.0	757.9	765.4	774.3	786.9	798.2
7.5°	675.9	681.3	689.9	700.7	710.9	721.0	731.8	742.0	754.7	772.8	790.8
10°	650.0	656.5	666.7	678.3	690.9	700.9	713.5	726.5	742.2	763.0	784.5
12.5°	627.6	632.4	644.3	655.3	669.6	682.2	694.6	709.8	727.7	749.9	775.8
15°	591.9	598.7	610.4	622.6	637.7	650.9	667.0	685.5	702.9	730.2	761.6
17.5°	556.1	566.5	578.5	592.5	603.6	622.0	639.4	658.3	679.8	708.7	743.2
20°	533.2	541.4	552.6	572.7	587.5	601.5	617.5	641.1	660.8	693.7	729.5
22.5°	513.7	519.8	532.4	549.0	566.1	582.3	598.7	621.2	645.6	676.7	715.6
25°	485.0	494.5	504.1	516.0	534.5	554.0	571.8	590.8	616.8	650.0	692.0
27.5°	456.9	465.6	475.0	489.7	503.7	521.9	540.5	562.4	590.2	625.3	667.9
30°	438.9	445.4	454.2	473.1	485.7	501.4	523.3	542.7	568.6	605.9	650.9
32.5°	420.3	428.7	438.4	452.8	468.4	483.3	503.3	524.4	550.9	587.5	633.7
35°	393.8	403.7	413.6	424.2	439.9	455.3	472.0	495.3	522.2	557.8	603.2
37.5°	369.4	377.4	385.5	398.6	413.5	428.1	443.7	466.6	492.0	530.4	572.0
40°	353.8	361.1	367.1	380.8	395.2	410.9	426.2	446.4	473.7	509.6	549.9
42.5°	336.9	343.5	351.9	363.0	378.5	391.7	407.2	426.1	451.8	488.3	523.6
45°	311.5	319.0	326.2	336.8	352.1	365.1	378.8	396.9	423.2	453.3	484.6
47.5°	285.1	292.6	300.8	311.0	324.4	337.6	351.2	367.3	391.3	420.8	441.9
50°	268.1	274.3	282.5	292.7	305.0	319.0	331.3	348.7	371.6	394.8	413.3
52.5°	250.7	256.2	265.6	276.3	287.8	299.9	313.0	328.0	348.7	370.5	385.1
55°	223.4	230.2	238.1	248.6	259.9	270.2	282.8	298.2	314.6	330.9	340.9
57.5°	197.9	203.6	210.2	221.1	230.9	243.1	254.4	266.4	281.6	293.9	300.4
60°	179.3	184.4	193.0	202.5	211.8	222.3	235.3	247.3	258.9	268.8	273.9
62.5°	161.8	167.7	175.2	184.0	194.0	204.0	215.3	225.4	235.7	244.2	247.7
65°	139.0	143.8	149.3	157.5	165.7	175.9	184.8	195.0	202.5	207.3	210.4
67.5°	118.2	121.4	125.6	131.0	139.1	148.0	156.7	164.6	170.9	174.2	176.9
70°	104.9	106.9	109.9	115.5	121.6	129.5	138.3	144.1	149.6	152.3	155.1
72.5°	91.5	94.1	96.8	101.2	106.3	112.0	118.4	125.6	128.6	131.8	133.5
75°	69.4	73.1	76.9	79.5	83.0	87.5	93.3	97.6	99.4	102.1	102.5
77.5°	52.3	53.1	55.9	59.3	62.2	65.4	69.0	73.0	73.8	75.3	76.2
80°	43.1	43.1	43.1	45.1	48.5	50.9	54.3	56.4	57.7	58.1	58.4
82.5°	34.6	34.6	34.3	34.7	35.9	37.2	40.4	42.7	43.8	43.6	42.8
85°	22.6	21.8	21.8	21.5	21.8	21.1	20.9	22.2	24.3	24.3	23.5
87.5°	11.3	11.0	11.0	10.5	10.0	9.5	8.5	8.6	8.4	9.3	8.8
90°	10.1	9.7	8.6	7.4	6.2	5.0	4.0	3.1	2.2	1.3	0.4
92.5°	15.8	15.5	14.9	14.2	13.6	12.8	12.2	11.6	11.0	10.4	9.8
95°	30.2	29.9	29.2	28.4	27.7	27.0	26.4	25.8	25.1	24.4	23.8
97.5°	47.2	46.8	46.3	45.7	45.2	44.7	44.2	43.8	43.2	42.8	42.4
100°	59.7	59.4	58.9	58.5	58.1	57.6	57.1	56.5	56.0	55.5	54.9
102.5°	73.9	73.7	73.0	72.4	71.9	71.2	70.8	70.4	70.2	69.8	69.5
105°	95.3	95.3	94.5	93.7	92.9	92.1	91.7	91.5	91.3	91.1	91.0
107.5°	118.1	117.8	117.4	117.1	116.8	116.5	116.3	116.1	116.0	115.9	115.8
110°	133.3	133.0	132.8	132.6	132.4	132.2	132.1	131.9	131.7	131.5	131.3



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	148.6	148.1	148.1	148.1	148.0	148.0	147.9	147.8	147.8	147.6	147.5
115°	172.3	172.2	172.4	172.5	172.7	172.9	172.8	172.5	172.3	172.0	171.7
117.5°	195.9	195.9	196.2	196.4	196.6	196.8	196.9	196.7	196.5	196.4	196.2
120°	211.7	211.8	212.2	212.7	213.1	213.6	213.5	212.9	212.4	211.9	211.3
122.5°	227.7	227.9	228.2	228.4	228.6	228.8	228.7	228.4	228.0	227.6	227.2
125°	251.4	251.7	251.9	252.1	252.3	252.4	252.4	252.2	251.9	251.6	251.4
127.5°	274.8	275.4	275.5	275.7	276.0	276.2	276.0	275.4	274.8	274.2	273.7
130°	290.2	290.5	290.8	291.1	291.3	291.6	291.4	290.7	290.0	289.3	288.6
132.5°	305.3	305.8	305.9	306.1	306.3	306.6	306.3	305.6	304.9	304.1	303.4
135°	327.8	328.1	328.2	328.3	328.4	328.5	328.2	327.7	327.2	326.6	326.1
137.5°	349.8	350.2	350.0	349.7	349.5	349.3	348.9	348.5	348.0	347.6	347.1
140°	364.0	364.1	364.0	363.9	363.8	363.7	363.5	363.0	362.6	362.1	361.7
142.5°	377.6	377.6	377.6	377.4	377.2	377.0	376.7	376.3	375.9	375.4	375.0
145°	397.5	397.6	397.3	397.1	396.8	396.5	396.4	396.2	396.0	395.8	395.7
147.5°	416.3	416.3	416.1	415.8	415.5	415.3	415.0	414.6	414.4	414.0	413.8
150°	427.9	427.9	427.8	427.6	427.4	427.2	427.0	426.9	426.7	426.5	426.3
152.5°	438.5	438.3	438.2	438.1	437.9	437.8	437.7	437.4	437.2	436.9	436.7
155°	453.8	453.4	453.3	453.3	453.2	453.1	453.0	453.0	453.0	453.0	453.0
157.5°	467.1	466.7	466.6	466.6	466.5	466.5	466.5	466.5	466.7	466.8	466.9
160°	475.3	474.8	474.8	474.8	474.8	474.8	474.9	475.1	475.3	475.5	475.6
162.5°	483.0	482.6	482.5	482.4	482.3	482.3	482.4	482.6	482.9	483.1	483.4
165°	492.8	492.2	492.2	492.2	492.2	492.2	492.3	492.6	492.8	493.1	493.4
167.5°	500.7	500.1	500.1	500.0	499.9	499.8	500.0	500.3	500.7	501.1	501.4
170°	505.0	504.4	504.4	504.4	504.4	504.4	504.5	504.9	505.2	505.6	506.0
172.5°	508.5	507.8	507.8	507.8	507.8	507.8	508.0	508.5	508.8	509.2	509.5
175°	512.1	511.6	511.6	511.6	511.6	511.6	511.8	512.1	512.5	512.8	513.2
177.5°	513.9	513.4	513.4	513.4	513.4	513.4	513.6	513.9	514.2	514.4	514.8
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	802.2	805.2	809.0	814.8	819.1	823.0	823.8	824.9	827.6	832.2	835.8
5°	807.4	815.3	827.9	840.2	853.5	864.4	874.7	881.9	888.7	903.0	914.6
7.5°	805.7	823.2	843.0	865.1	887.4	909.1	929.2	947.2	965.1	986.0	1009.8
10°	804.7	825.2	851.8	880.1	911.2	941.6	971.0	993.9	1020.6	1044.5	1074.9
12.5°	799.5	829.0	860.9	897.1	935.3	970.4	1009.0	1040.6	1071.0	1105.6	1140.9
15°	792.7	828.6	868.9	917.0	975.1	1017.4	1057.0	1112.1	1149.6	1187.2	1237.8
17.5°	780.3	824.1	874.5	937.0	985.5	1042.4	1102.0	1145.5	1196.1	1249.0	1294.8
20°	770.5	821.4	877.8	939.2	1001.0	1062.9	1120.6	1172.5	1224.8	1285.9	1323.5
22.5°	760.7	811.0	869.6	934.9	1001.3	1066.4	1131.8	1192.8	1251.5	1313.2	1361.2
25°	739.8	799.5	863.1	929.7	995.2	1066.9	1144.9	1212.8	1285.6	1349.1	1394.5
27.5°	718.6	773.4	836.6	904.2	977.0	1061.8	1153.4	1230.7	1303.6	1349.1	1363.3
30°	699.5	757.5	815.6	884.2	963.1	1057.7	1155.1	1243.6	1303.3	1323.1	1308.4
32.5°	680.1	732.7	790.2	860.5	944.3	1047.7	1157.3	1235.9	1271.9	1256.8	1196.9
35°	645.9	693.3	749.0	819.4	915.7	1042.1	1148.3	1201.6	1192.7	1107.2	994.5
37.5°	609.2	647.9	699.5	773.0	886.0	1019.8	1109.5	1117.3	1040.4	909.4	779.2
40°	580.2	615.1	668.1	744.9	863.1	998.0	1070.4	1038.7	919.4	773.6	664.9
42.5°	552.1	581.5	632.5	715.4	841.2	968.2	1012.2	943.0	805.5	667.5	568.8
45°	504.4	532.1	583.4	668.4	796.5	911.2	905.4	785.2	647.6	536.5	454.6
47.5°	459.2	483.4	531.5	618.3	744.0	825.8	771.5	643.6	526.8	437.8	379.3
50°	427.3	451.2	499.0	584.7	701.9	761.6	684.1	560.8	453.9	380.1	333.7
52.5°	396.6	420.0	463.8	547.2	651.0	686.8	603.5	489.2	400.1	336.4	296.5
55°	353.8	371.6	410.9	490.8	568.3	576.5	492.1	396.5	323.1	278.7	251.4
57.5°	310.2	325.5	364.3	427.9	482.3	478.0	398.1	315.4	265.9	232.9	213.1
60°	281.8	296.8	330.9	385.6	426.6	412.2	338.9	272.2	229.9	205.6	189.9
62.5°	255.3	267.0	299.0	338.9	368.4	352.1	289.6	234.5	200.9	180.5	168.0
65°	216.9	226.4	252.1	272.9	289.3	273.6	221.7	183.4	159.2	144.8	136.3
67.5°	180.4	186.5	202.7	210.2	221.8	204.6	166.7	141.1	127.2	115.2	109.2
70°	157.5	161.9	170.4	176.6	179.7	161.9	133.8	115.1	103.5	95.0	91.2
72.5°	134.5	138.4	140.1	145.2	143.6	126.9	107.6	92.7	84.4	78.6	73.7
75°	102.8	104.5	102.8	100.8	96.3	84.7	71.4	63.8	57.7	55.0	53.3
77.5°	74.9	74.4	72.1	68.8	61.3	53.9	46.8	44.2	41.6	40.1	39.6
80°	57.7	56.4	54.3	49.2	42.7	37.5	35.8	34.2	33.2	31.4	31.1
82.5°	43.0	42.2	38.7	34.4	29.9	27.5	26.0	25.4	24.3	23.5	23.5
85°	22.9	21.8	18.1	15.7	15.1	14.4	14.0	14.0	12.7	12.3	12.3
87.5°	7.7	6.2	6.1	5.4	5.6	5.4	5.9	5.5	5.5	5.8	5.4
90°	1.3	2.2	3.1	4.0	5.0	6.2	7.4	8.6	9.7	10.1	10.4
92.5°	10.4	11.0	11.6	12.2	12.8	13.6	14.2	14.9	15.5	15.8	16.1
95°	24.4	25.1	25.8	26.4	27.0	27.7	28.4	29.2	29.9	30.2	30.6
97.5°	42.8	43.2	43.8	44.2	44.7	45.2	45.7	46.3	46.8	47.2	47.6
100°	55.5	56.0	56.5	57.1	57.6	58.1	58.5	58.9	59.4	59.7	59.9
102.5°	69.8	70.2	70.4	70.8	71.2	71.9	72.4	73.0	73.7	73.9	74.2
105°	91.1	91.3	91.5	91.7	92.1	92.9	93.7	94.5	95.3	95.3	95.3
107.5°	115.9	116.0	116.1	116.3	116.5	116.8	117.1	117.4	117.8	118.1	118.3
110°	131.5	131.7	131.9	132.1	132.2	132.4	132.6	132.8	133.0	133.3	133.7





TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	147.6	147.8	147.8	147.9	148.0	148.0	148.1	148.1	148.1	148.6	149.0
115°	172.0	172.3	172.5	172.8	172.9	172.7	172.5	172.4	172.2	172.3	172.4
117.5°	196.4	196.5	196.7	196.9	196.8	196.6	196.4	196.2	195.9	195.9	195.9
120°	211.9	212.4	212.9	213.5	213.6	213.1	212.7	212.2	211.8	211.7	211.6
122.5°	227.6	228.0	228.4	228.7	228.8	228.6	228.4	228.2	227.9	227.7	227.5
125°	251.6	251.9	252.2	252.4	252.4	252.3	252.1	251.9	251.7	251.4	251.0
127.5°	274.2	274.8	275.4	276.0	276.2	276.0	275.7	275.5	275.4	274.8	274.4
130°	289.3	290.0	290.7	291.4	291.6	291.3	291.1	290.8	290.5	290.2	289.8
132.5°	304.1	304.9	305.6	306.3	306.6	306.3	306.1	305.9	305.8	305.3	304.9
135°	326.6	327.2	327.7	328.2	328.5	328.4	328.3	328.2	328.1	327.8	327.4
137.5°	347.6	348.0	348.5	348.9	349.3	349.5	349.7	350.0	350.2	349.8	349.5
140°	362.1	362.6	363.0	363.5	363.7	363.8	363.9	364.0	364.1	364.0	363.9
142.5°	375.4	375.9	376.3	376.7	377.0	377.2	377.4	377.6	377.6	377.6	377.5
145°	395.8	396.0	396.2	396.4	396.5	396.8	397.1	397.3	397.6	397.5	397.4
147.5°	414.0	414.4	414.6	415.0	415.3	415.5	415.8	416.1	416.3	416.3	416.3
150°	426.5	426.7	426.9	427.0	427.2	427.4	427.6	427.8	427.9	427.9	427.9
152.5°	436.9	437.2	437.4	437.7	437.8	437.9	438.1	438.2	438.3	438.5	438.5
155°	453.0	453.0	453.0	453.0	453.1	453.2	453.3	453.3	453.4	453.8	454.1
157.5°	466.8	466.7	466.5	466.5	466.5	466.5	466.6	466.6	466.7	467.1	467.5
160°	475.5	475.3	475.1	474.9	474.8	474.8	474.8	474.8	474.8	475.3	475.7
162.5°	483.1	482.9	482.6	482.4	482.3	482.3	482.4	482.5	482.6	483.0	483.5
165°	493.1	492.8	492.6	492.3	492.2	492.2	492.2	492.2	492.2	492.8	493.3
167.5°	501.1	500.7	500.3	500.0	499.8	499.9	500.0	500.1	500.1	500.7	501.2
170°	505.6	505.2	504.9	504.5	504.4	504.4	504.4	504.4	504.4	505.0	505.6
172.5°	509.2	508.8	508.5	508.0	507.8	507.8	507.8	507.8	507.8	508.5	509.0
175°	512.8	512.5	512.1	511.8	511.6	511.6	511.6	511.6	511.6	512.1	512.6
177.5°	514.4	514.2	513.9	513.6	513.4	513.4	513.4	513.4	513.4	513.9	514.3
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4	514.4



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	797.8	797.8	797.8	797.8	797.8	797.8	797.8
2.5°	841.6	841.6	842.7	846.8	847.3	850.9	849.7
5°	924.9	931.4	933.8	944.1	950.2	952.9	947.4
7.5°	1026.8	1045.1	1053.8	1064.5	1074.0	1076.9	1069.4
10°	1101.2	1120.3	1136.3	1146.2	1155.5	1161.5	1169.5
12.5°	1173.0	1196.5	1211.7	1225.7	1235.2	1243.0	1244.3
15°	1251.1	1286.6	1313.6	1333.4	1343.3	1348.4	1346.4
17.5°	1329.8	1362.7	1382.0	1402.1	1415.9	1416.6	1417.0
20°	1374.4	1406.5	1428.7	1443.7	1459.1	1458.4	1461.8
22.5°	1404.2	1429.4	1446.4	1457.3	1462.6	1460.0	1460.7
25°	1418.1	1425.6	1422.5	1405.1	1400.7	1384.6	1387.3
27.5°	1346.2	1310.7	1274.0	1226.6	1189.4	1159.6	1161.1
30°	1248.7	1185.8	1114.1	1054.0	1000.1	985.0	952.9
32.5°	1112.3	1018.1	934.1	878.1	831.7	819.1	791.1
35°	881.2	789.6	703.2	651.3	630.8	602.2	601.8
37.5°	684.9	604.3	558.7	519.7	499.3	481.9	480.2
40°	576.2	513.4	478.8	450.8	430.7	417.7	414.6
42.5°	500.2	449.4	417.1	399.8	384.2	377.6	372.6
45°	408.5	374.3	351.8	336.1	328.9	323.8	321.0
47.5°	341.7	318.8	303.4	293.0	287.1	281.8	283.2
50°	305.3	286.6	275.3	265.4	260.9	257.2	257.5
52.5°	276.1	259.2	250.1	243.0	237.5	234.8	233.4
55°	234.3	223.7	214.5	209.4	206.3	202.5	201.5
57.5°	199.8	191.6	184.1	178.3	177.6	174.0	174.4
60°	176.9	170.0	163.9	160.9	158.5	155.4	156.4
62.5°	158.1	152.3	146.7	144.2	141.8	139.6	140.0
65°	129.5	123.9	120.6	119.2	118.2	117.2	116.1
67.5°	103.2	99.8	97.6	94.7	92.6	92.3	91.2
70°	86.8	82.3	78.6	74.8	73.7	73.4	73.7
72.5°	69.6	66.7	65.7	63.8	63.7	62.8	63.4
75°	52.3	51.3	50.6	49.2	49.2	49.2	49.2
77.5°	38.5	37.9	37.5	37.2	36.9	36.4	36.4
80°	30.1	29.7	29.1	29.1	28.7	29.1	28.7
82.5°	22.6	22.6	21.9	21.9	21.6	21.4	21.6
85°	11.6	11.2	11.9	11.2	11.6	11.0	11.6
87.5°	5.4	5.5	5.3	5.4	5.1	5.7	5.2
90°	10.8	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	16.4	16.7	16.8	16.7	16.5	16.4	16.3
95°	30.9	31.3	31.5	31.5	31.5	31.5	31.5
97.5°	48.1	48.4	48.6	48.6	48.6	48.5	48.5
100°	60.2	60.5	60.7	60.9	61.1	61.3	61.4
102.5°	74.5	74.7	74.8	74.8	74.7	74.7	74.6
105°	95.3	95.3	95.4	95.7	95.9	96.0	96.2
107.5°	118.6	118.9	119.0	118.9	118.8	118.7	118.6
110°	134.0	134.4	134.5	134.3	134.1	133.9	133.8



TEST NUMBER: P332411-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	149.5	149.9	150.1	150.0	150.0	150.0	149.9
115°	172.5	172.5	172.5	172.5	172.4	172.3	172.2
117.5°	195.8	195.8	195.7	195.5	195.2	194.9	194.7
120°	211.5	211.4	211.2	211.1	210.9	210.7	210.5
122.5°	227.2	226.9	226.8	226.5	226.2	226.0	225.7
125°	250.7	250.3	249.9	249.6	249.2	248.9	248.5
127.5°	273.8	273.3	272.9	272.5	272.1	271.6	271.3
130°	289.4	289.1	288.6	288.0	287.4	286.8	286.1
132.5°	304.4	304.0	303.5	303.1	302.6	302.1	301.6
135°	327.1	326.7	326.5	326.3	326.1	325.9	325.7
137.5°	349.1	348.7	348.3	347.9	347.7	347.3	347.0
140°	363.8	363.7	363.4	362.7	362.1	361.5	360.9
142.5°	377.4	377.3	377.0	376.6	376.0	375.6	375.1
145°	397.3	397.3	397.1	396.7	396.4	396.0	395.7
147.5°	416.3	416.3	416.1	415.5	414.9	414.4	413.8
150°	427.9	427.9	427.7	427.1	426.6	426.1	425.5
152.5°	438.7	438.9	438.7	438.3	437.7	437.3	436.8
155°	454.5	454.9	454.7	454.1	453.4	452.8	452.2
157.5°	467.9	468.2	468.1	467.7	467.2	466.6	466.2
160°	476.2	476.6	476.6	476.3	475.9	475.5	475.2
162.5°	483.9	484.4	484.3	483.8	483.1	482.6	482.0
165°	493.8	494.4	494.3	493.7	493.0	492.4	491.8
167.5°	501.8	502.3	502.3	501.8	501.2	500.7	500.1
170°	506.2	506.8	506.8	506.2	505.6	505.0	504.4
172.5°	509.5	510.1	510.1	509.4	508.8	508.2	507.6
175°	513.2	513.7	513.7	513.1	512.5	511.8	511.2
177.5°	514.8	515.1	515.1	514.6	514.2	513.6	513.1
180°	514.4	514.4	514.4	514.4	514.4	514.4	514.4

(END OF REPORT)