

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332412-940

Luminaire Tested: **S123RDIW-S560D460U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332412-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D460U940-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3548.6 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51	46
2	90	83	77	72	84	77	72	68	66	63	59	56	54	51	47	45	43	39
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	33
4	76	65	57	51	70	61	54	49	53	47	43	45	41	38	38	35	32	29
5	70	58	50	44	64	54	47	42	47	42	37	40	36	33	34	31	28	25
6	64	52	44	39	59	49	42	37	43	37	33	37	32	29	31	28	25	22
7	60	47	39	34	55	44	37	32	39	33	29	33	29	26	29	25	23	20
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20	18
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9065	9065	9065
5°	9100	8975	9027
10°	9049	8862	8833
15°	8952	8655	8564
20°	8818	8395	8200
25°	8679	8105	7845
30°	8499	7768	7343
35°	8311	7432	6884
40°	8140	7035	6315
45°	7913	6645	5801
50°	7663	6199	5228
55°	7409	5692	4692
60°	7175	5147	4103
65°	6872	4559	3512
70°	6493	3827	2839
75°	5939	3011	2670
80°	5294	2672	2455
85°	4471	2359	2186



TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.1	2.2
10°-20°	220.1	6.2
20°-30°	316.9	8.9
30°-40°	356.9	10.1
40°-50°	341.4	9.6
50°-60°	279.6	7.9
60°-70°	188.7	5.3
70°-80°	94.9	2.7
80°-90°	26.6	0.7
90°-100°	19.6	0.6
100°-110°	93.4	2.6
110°-120°	224.4	6.3
120°-130°	285.8	8.1
130°-140°	305.4	8.6
140°-150°	285.5	8.0
150°-160°	230.3	6.5
160°-170°	148.7	4.2
170°-180°	51.2	1.4
0°-30°	616.0	17.4
0°-40°	972.9	27.4
0°-60°	1594.0	44.9
0°-90°	1904.2	53.7
90°-120°	337.5	9.5
90°-150°	1214.2	34.2
90°-180°	1644.0	46.3
0°-180°	3548.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	842	842	842	842	842	
5°	842	839	831	836	835	80
15°	803	795	777	773	768	226
25°	731	713	682	668	660	336
35°	632	607	566	537	524	396
45°	520	488	436	399	381	401
55°	395	360	303	265	250	354
65°	270	231	179	147	138	267
75°	143	110	72	66	64	152
85°	36	22	19	18	18	41
90°	0	4	10	11	12	3
95°	24	9	12	15	15	30
105°	119	122	88	21	18	127
115°	224	226	230	234	236	221
125°	316	319	320	321	322	282
135°	393	395	397	398	397	302
145°	454	456	457	458	458	284
155°	500	499	499	501	499	230
165°	527	526	525	528	526	149
175°	539	537	538	540	537	51
180°	539	539	539	539	539	



TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	845.0	844.5	844.0	843.5	843.0	842.0	840.6	839.1	837.7	836.2	837.6
5°	842.2	841.5	840.7	840.0	839.2	837.9	836.1	834.3	832.4	830.6	832.0
7.5°	834.5	833.7	832.8	832.0	831.2	829.6	827.2	824.8	822.4	820.1	820.8
10°	827.9	826.8	825.7	824.7	823.7	821.7	819.0	816.3	813.5	810.8	810.9
12.5°	818.6	817.4	816.2	815.0	813.9	811.6	808.2	804.9	801.6	798.3	798.2
15°	803.3	801.6	800.0	798.3	796.7	793.6	789.4	785.2	780.9	776.7	775.9
17.5°	784.0	782.1	780.2	778.2	776.2	772.6	767.1	761.8	756.3	751.0	749.4
20°	769.8	767.4	765.0	762.5	760.1	756.0	750.2	744.5	738.7	732.9	730.9
22.5°	753.9	751.2	748.4	745.6	742.8	738.3	732.2	726.0	720.0	713.8	711.3
25°	730.8	727.1	723.3	719.5	715.7	710.3	703.3	696.3	689.4	682.4	679.2
27.5°	702.8	698.7	694.5	690.3	686.1	680.1	672.3	664.6	656.8	649.1	644.6
30°	683.8	679.2	674.7	670.1	665.6	659.0	650.5	642.0	633.5	625.0	619.8
32.5°	664.6	659.5	654.3	649.2	644.0	636.9	627.9	618.9	609.9	600.9	595.3
35°	632.5	627.1	621.6	616.2	610.6	603.2	593.8	584.4	575.0	565.6	559.0
37.5°	600.0	594.0	587.9	581.8	575.7	567.7	557.6	547.6	537.5	527.4	520.0
40°	579.3	572.6	565.9	559.2	552.5	543.8	533.1	522.3	511.5	500.7	492.8
42.5°	555.7	549.0	542.4	535.7	529.1	520.1	509.0	497.8	486.7	475.5	466.9
45°	519.8	513.0	506.1	499.4	492.5	483.2	471.5	459.9	448.2	436.5	427.8
47.5°	483.8	476.4	468.9	461.4	453.9	444.3	432.6	420.9	409.2	397.5	388.2
50°	457.6	450.5	443.4	436.2	429.1	419.4	407.1	394.8	382.5	370.2	360.8
52.5°	434.2	426.4	418.7	410.9	403.2	393.2	381.0	368.9	356.7	344.6	334.7
55°	394.8	387.4	380.0	372.5	365.1	354.9	342.0	329.1	316.2	303.3	294.4
57.5°	358.5	350.4	342.2	334.1	326.0	315.5	302.6	289.6	276.6	263.7	255.4
60°	333.3	325.0	316.6	308.3	300.0	289.4	276.9	264.3	251.6	239.1	230.9
62.5°	308.2	299.9	291.5	283.1	274.8	264.3	251.7	239.2	226.5	213.9	206.3
65°	269.8	261.4	253.2	244.8	236.4	226.3	214.5	202.7	190.8	179.0	171.6
67.5°	231.4	223.0	214.5	206.1	197.7	187.8	176.4	165.1	153.7	142.3	136.8
70°	206.3	198.0	189.9	181.7	173.5	164.1	153.5	142.9	132.2	121.6	116.3
72.5°	181.1	173.1	165.0	156.9	148.8	140.0	130.4	120.6	111.0	101.4	97.0
75°	142.8	135.5	128.2	120.9	113.6	105.8	97.5	89.1	80.8	72.4	70.9
77.5°	107.8	101.2	94.6	88.0	81.4	75.4	70.1	64.7	59.3	53.9	53.1
80°	85.4	79.2	72.9	66.7	60.5	55.8	52.6	49.4	46.2	43.1	42.5
82.5°	64.1	58.7	53.3	48.0	42.5	39.1	37.6	36.2	34.7	33.2	32.7
85°	36.2	32.9	29.5	26.2	22.8	21.0	20.5	20.1	19.6	19.1	18.8
87.5°	13.2	12.0	10.9	9.7	8.6	8.1	8.3	8.6	8.8	9.0	9.0
90°	0.4	1.2	2.1	3.0	3.9	5.0	6.2	7.3	8.5	9.6	10.0
92.5°	7.5	7.2	7.0	6.7	6.4	6.8	7.7	8.5	9.4	10.3	10.8
95°	24.4	20.8	17.1	13.5	9.8	8.5	9.5	10.4	11.4	12.4	13.0
97.5°	49.1	47.4	45.8	44.2	42.5	38.5	32.1	25.7	19.4	12.9	13.6
100°	67.7	69.5	71.2	73.0	74.8	68.8	54.9	41.0	27.1	13.2	13.9
102.5°	88.8	90.2	91.4	92.7	94.0	87.0	71.9	56.7	41.6	26.4	24.2
105°	119.4	120.4	121.4	122.3	123.3	119.8	111.7	103.8	95.8	87.7	72.0
107.5°	151.6	152.4	153.2	153.9	154.7	155.8	157.0	158.3	159.5	160.8	149.3
110°	173.1	173.8	174.5	175.2	175.9	176.7	177.7	178.7	179.7	180.7	177.7



TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	193.6	194.2	194.8	195.5	196.2	197.0	198.0	198.9	199.9	200.9	200.9
115°	223.9	224.4	225.0	225.5	226.0	226.8	227.6	228.4	229.2	230.0	230.9
117.5°	253.3	254.0	254.7	255.3	256.0	256.5	256.9	257.3	257.8	258.2	258.9
120°	271.6	272.4	273.2	274.0	274.8	275.4	275.6	275.9	276.2	276.4	277.1
122.5°	290.3	290.9	291.5	292.2	292.8	293.4	293.7	294.0	294.4	294.7	295.2
125°	315.7	316.4	317.1	317.8	318.5	319.1	319.4	319.8	320.1	320.5	320.7
127.5°	340.4	341.1	341.8	342.5	343.2	343.8	344.2	344.6	345.1	345.5	345.8
130°	355.8	356.5	357.2	357.9	358.6	359.2	359.5	359.9	360.3	360.5	360.9
132.5°	370.5	371.2	371.9	372.6	373.4	373.8	374.2	374.4	374.7	375.0	375.3
135°	393.0	393.5	394.0	394.6	395.1	395.6	395.9	396.3	396.6	397.0	397.3
137.5°	412.2	413.0	413.6	414.3	414.9	415.4	415.6	415.8	416.0	416.2	416.6
140°	425.1	425.6	426.1	426.7	427.2	427.6	427.8	428.1	428.4	428.6	429.0
142.5°	436.9	437.5	438.0	438.5	439.1	439.4	439.7	440.0	440.2	440.5	440.8
145°	453.5	454.1	454.8	455.4	456.0	456.4	456.6	456.7	456.9	457.1	457.3
147.5°	469.1	469.6	469.9	470.4	470.7	471.1	471.3	471.4	471.6	471.8	472.0
150°	478.8	479.0	479.3	479.6	479.8	480.0	480.2	480.4	480.5	480.7	480.9
152.5°	487.4	487.5	487.7	487.8	487.9	488.0	488.1	488.2	488.3	488.5	488.7
155°	499.5	499.4	499.2	499.1	498.9	498.8	498.9	499.0	499.1	499.2	499.6
157.5°	509.1	509.0	509.0	509.0	509.0	508.9	508.8	508.7	508.6	508.5	509.1
160°	514.8	514.7	514.6	514.5	514.4	514.3	514.2	514.2	514.1	514.0	514.5
162.5°	520.2	520.0	519.8	519.6	519.3	519.2	519.1	519.0	518.9	518.8	519.4
165°	526.8	526.6	526.3	526.0	525.8	525.6	525.5	525.4	525.3	525.2	525.9
167.5°	532.0	531.6	531.3	530.9	530.6	530.4	530.4	530.4	530.4	530.4	531.1
170°	534.8	534.5	534.1	533.8	533.4	533.2	533.2	533.2	533.2	533.2	534.0
172.5°	536.7	536.4	535.9	535.5	535.0	534.8	534.9	535.0	535.1	535.1	535.8
175°	539.2	538.8	538.3	537.9	537.4	537.3	537.3	537.4	537.5	537.6	538.2
177.5°	539.8	539.5	539.1	538.8	538.4	538.3	538.4	538.4	538.5	538.6	539.1
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2



TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	842.2	842.2	842.2	842.2	842.2	842.2	842.2	842.2
2.5°	838.9	840.3	841.6	842.1	841.9	841.6	841.4	841.2
5°	833.3	834.7	836.1	836.6	836.3	836.0	835.7	835.4
7.5°	821.6	822.3	823.1	823.2	822.7	822.2	821.7	821.2
10°	811.1	811.3	811.4	811.1	810.4	809.6	808.9	808.1
12.5°	798.1	798.0	797.9	797.4	796.5	795.6	794.8	793.9
15°	775.2	774.4	773.6	772.7	771.6	770.6	769.5	768.5
17.5°	747.8	746.2	744.5	743.0	741.4	739.8	738.2	736.6
20°	729.0	727.0	725.1	723.2	721.3	719.5	717.6	715.9
22.5°	708.9	706.4	704.0	701.9	700.2	698.5	696.8	695.1
25°	676.0	672.8	669.7	667.2	665.6	663.9	662.2	660.5
27.5°	640.2	635.8	631.3	627.9	625.3	622.8	620.2	617.6
30°	614.7	609.5	604.4	600.6	598.2	595.8	593.3	590.8
32.5°	589.7	584.0	578.4	574.3	571.8	569.2	566.6	564.1
35°	552.5	546.0	539.5	534.8	532.1	529.4	526.6	523.9
37.5°	512.6	505.2	497.8	492.5	489.1	485.7	482.3	478.9
40°	484.9	477.0	469.1	463.4	459.9	456.5	453.0	449.4
42.5°	458.3	449.7	441.0	435.2	432.0	428.9	425.8	422.7
45°	419.2	410.5	401.9	395.7	392.1	388.4	384.8	381.1
47.5°	378.7	369.3	359.9	353.6	350.4	347.1	343.8	340.5
50°	351.4	342.0	332.6	326.1	322.6	319.1	315.7	312.2
52.5°	325.0	315.2	305.4	299.0	295.9	292.7	289.6	286.5
55°	285.7	276.9	268.0	262.2	259.1	256.1	253.1	250.0
57.5°	247.0	238.7	230.4	225.0	222.4	219.8	217.2	214.6
60°	222.7	214.5	206.3	200.9	198.3	195.7	193.1	190.6
62.5°	198.5	190.8	183.1	177.9	175.2	172.5	169.8	167.1
65°	164.1	156.7	149.2	144.6	143.0	141.3	139.6	137.9
67.5°	131.3	125.6	120.1	116.5	114.7	112.9	111.1	109.3
70°	110.9	105.7	100.3	96.8	95.1	93.5	91.8	90.2
72.5°	92.6	88.4	84.0	81.5	80.8	80.1	79.4	78.6
75°	69.4	67.9	66.3	65.5	65.1	64.8	64.5	64.2
77.5°	52.3	51.5	50.6	50.1	49.8	49.5	49.2	48.9
80°	42.1	41.6	41.2	40.8	40.6	40.2	39.9	39.6
82.5°	32.3	31.8	31.4	31.1	31.0	31.0	30.9	30.9
85°	18.5	18.2	17.9	17.7	17.7	17.7	17.7	17.7
87.5°	8.9	8.9	8.8	8.7	8.6	8.6	8.5	8.4
90°	10.3	10.7	11.1	11.3	11.5	11.7	11.9	12.0
92.5°	11.4	11.9	12.6	12.8	13.0	13.1	13.2	13.3
95°	13.6	14.3	14.9	15.2	15.2	15.2	15.2	15.2
97.5°	14.4	15.1	15.8	16.1	16.2	16.3	16.4	16.5
100°	14.6	15.3	16.1	16.5	16.6	16.7	16.8	16.9
102.5°	21.9	19.7	17.6	16.5	16.7	16.9	16.9	17.1
105°	56.2	40.5	24.7	16.9	17.1	17.3	17.5	17.7
107.5°	137.7	126.2	114.6	102.9	91.0	79.1	67.2	55.4
110°	174.8	171.8	168.9	161.1	148.4	135.6	122.9	110.2



TEST NUMBER: P332412-940

CATALOG NUMBER: S123RDIW-S560D460U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	201.0	201.0	201.1	199.7	197.1	194.4	191.7	189.0
115°	231.8	232.6	233.5	234.2	234.5	234.9	235.2	235.6
117.5°	259.6	260.3	261.0	261.4	261.4	261.5	261.6	261.7
120°	277.9	278.6	279.3	279.6	279.6	279.6	279.6	279.6
122.5°	295.7	296.2	296.7	296.9	297.0	297.1	297.2	297.3
125°	320.8	321.0	321.2	321.4	321.6	321.7	321.9	322.1
127.5°	346.1	346.3	346.6	346.7	346.5	346.3	346.2	346.0
130°	361.2	361.6	361.9	362.0	361.9	361.7	361.5	361.3
132.5°	375.7	376.0	376.4	376.5	376.2	375.9	375.7	375.5
135°	397.5	397.8	398.1	398.1	397.8	397.5	397.3	397.0
137.5°	417.1	417.4	417.9	418.0	417.9	417.7	417.5	417.3
140°	429.4	429.7	430.1	430.2	430.0	429.8	429.6	429.4
142.5°	441.1	441.4	441.7	441.7	441.4	441.2	441.0	440.7
145°	457.4	457.6	457.8	457.9	457.9	457.9	457.9	457.9
147.5°	472.2	472.3	472.5	472.3	472.0	471.5	471.2	470.7
150°	481.1	481.3	481.4	481.4	481.2	480.9	480.6	480.4
152.5°	489.1	489.4	489.7	489.6	489.3	488.8	488.5	488.0
155°	500.1	500.5	501.0	500.9	500.3	499.8	499.3	498.8
157.5°	509.6	510.1	510.7	510.6	509.9	509.3	508.5	507.8
160°	515.1	515.6	516.1	516.1	515.5	514.9	514.2	513.6
162.5°	520.0	520.7	521.2	521.3	520.7	520.1	519.6	519.1
165°	526.6	527.4	528.1	528.1	527.4	526.9	526.3	525.7
167.5°	531.8	532.4	533.2	533.2	532.4	531.8	531.1	530.4
170°	534.7	535.4	536.1	536.1	535.4	534.7	534.0	533.2
172.5°	536.5	537.3	538.0	538.0	537.2	536.4	535.7	534.8
175°	538.9	539.5	540.1	540.1	539.4	538.7	538.0	537.3
177.5°	539.8	540.3	540.9	540.8	540.1	539.4	538.7	538.0
180°	539.2	539.2	539.2	539.2	539.2	539.2	539.2	539.2

(END OF REPORT)