

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332863-930

Luminaire Tested: **S124DIW-S1195D1560U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332863-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1195D1560U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9259.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13116	13116	13116
5°	13156	12998	13092
10°	13073	12892	12956
15°	12915	12709	12741
20°	12706	12482	12493
25°	12466	12222	12188
30°	12172	11918	11808
35°	11869	11599	11445
40°	11552	11236	11031
45°	11222	10880	10671
50°	10857	10562	10236
55°	10463	10151	9821
60°	10069	9689	9397
65°	9626	9251	8879
70°	9128	8665	8327
75°	8366	7960	7757
80°	7443	7141	6960
85°	6512	6271	6150



TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.0	1.7
10°-20°	431.1	4.7
20°-30°	634.5	6.9
30°-40°	737.7	8.0
40°-50°	737.7	8.0
50°-60°	645.3	7.0
60°-70°	479.2	5.2
70°-80°	272.3	2.9
80°-90°	83.3	0.9
90°-100°	56.2	0.6
100°-110°	358.5	3.9
110°-120°	685.8	7.4
120°-130°	870.5	9.4
130°-140°	931.4	10.1
140°-150°	871.0	9.4
150°-160°	702.4	7.6
160°-170°	453.0	4.9
170°-180°	156.1	1.7
0°-30°	1218.6	13.2
0°-40°	1956.3	21.1
0°-60°	3339.3	36.1
0°-90°	4174.1	45.1
90°-120°	1100.5	11.9
90°-150°	3773.4	40.8
90°-180°	5085.0	54.9
0°-180°	9259.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1625	1625	1625	1625	1625	
5°	1623	1618	1604	1617	1616	154
15°	1545	1539	1521	1528	1524	435
25°	1400	1390	1372	1373	1368	644
35°	1204	1195	1177	1168	1161	753
45°	983	973	953	939	935	757
55°	743	739	721	706	698	666
65°	504	497	484	472	465	499
75°	268	262	255	250	249	285
85°	70	70	68	68	66	77
90°	4	17	27	34	37	7
95°	68	28	27	34	36	87
105°	370	377	384	392	350	387
115°	691	694	693	696	696	680
125°	971	976	974	977	979	867
135°	1205	1204	1209	1211	1214	928
145°	1389	1393	1393	1394	1397	868
155°	1523	1524	1521	1525	1522	702
165°	1607	1601	1601	1610	1600	454
175°	1644	1637	1638	1647	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1628.9	1628.2	1627.5	1626.8	1626.1	1624.5	1622.0	1619.4	1616.9	1614.4	1616.7
5°	1623.4	1622.3	1621.1	1620.0	1618.9	1616.7	1613.5	1610.3	1607.1	1603.9	1607.1
7.5°	1608.3	1607.2	1606.1	1604.8	1603.7	1601.4	1597.8	1594.3	1590.8	1587.2	1589.8
10°	1594.8	1593.7	1592.5	1591.3	1590.2	1587.7	1584.0	1580.2	1576.5	1572.7	1575.0
12.5°	1577.1	1576.0	1574.8	1573.6	1572.5	1569.9	1565.9	1562.0	1558.0	1554.0	1556.5
15°	1545.3	1544.2	1543.0	1541.9	1540.7	1538.0	1533.6	1529.3	1524.9	1520.6	1522.3
17.5°	1507.1	1505.6	1504.1	1502.8	1501.3	1498.5	1494.4	1490.3	1486.2	1482.1	1483.2
20°	1479.0	1477.5	1476.0	1474.6	1473.2	1470.2	1465.9	1461.6	1457.3	1452.9	1453.8
22.5°	1448.7	1446.8	1445.0	1443.0	1441.1	1437.9	1433.6	1429.3	1425.0	1420.6	1422.2
25°	1399.5	1397.5	1395.5	1393.4	1391.4	1388.4	1384.3	1380.3	1376.2	1372.1	1372.5
27.5°	1343.3	1341.2	1339.1	1337.0	1335.0	1332.0	1328.3	1324.5	1320.8	1317.0	1316.3
30°	1305.8	1303.5	1301.1	1298.9	1296.6	1293.5	1289.7	1286.0	1282.2	1278.5	1277.3
32.5°	1266.2	1264.1	1262.1	1260.0	1257.8	1254.8	1250.8	1246.8	1242.8	1238.8	1237.5
35°	1204.3	1202.2	1200.2	1198.2	1196.1	1193.1	1189.0	1185.0	1181.0	1176.9	1174.8
37.5°	1138.9	1137.0	1135.2	1133.3	1131.5	1128.4	1124.1	1119.7	1115.3	1111.0	1108.8
40°	1096.2	1093.9	1091.5	1089.2	1087.0	1083.6	1079.3	1074.9	1070.6	1066.2	1063.3
42.5°	1050.4	1049.0	1047.6	1046.2	1044.8	1041.7	1036.9	1032.1	1027.3	1022.5	1019.1
45°	982.9	980.9	978.8	976.8	974.9	971.5	966.9	962.2	957.6	953.0	949.8
47.5°	912.3	910.9	909.5	908.2	906.8	904.0	899.7	895.4	891.1	886.9	883.3
50°	864.5	863.3	862.1	861.0	859.8	857.2	853.1	849.1	845.1	841.0	837.0
52.5°	817.6	816.2	814.8	813.4	812.0	809.2	804.9	800.6	796.4	792.1	788.5
55°	743.4	742.5	741.7	740.8	739.9	737.4	733.4	729.4	725.3	721.2	717.8
57.5°	672.5	671.6	670.6	669.6	668.6	666.1	662.1	658.1	654.1	650.1	646.9
60°	623.6	622.2	620.7	619.3	617.8	615.2	611.5	607.7	603.9	600.1	597.5
62.5°	575.7	574.5	573.2	572.0	570.9	568.3	564.3	560.3	556.3	552.3	549.9
65°	503.9	502.4	500.9	499.5	498.1	495.9	493.0	490.1	487.2	484.3	481.4
67.5°	431.5	430.2	428.8	427.5	426.2	424.0	421.3	418.5	415.7	412.9	410.2
70°	386.7	384.7	382.6	380.6	378.5	376.4	374.1	371.8	369.4	367.1	364.8
72.5°	338.8	336.7	334.7	332.6	330.7	328.7	326.9	325.0	323.2	321.3	319.4
75°	268.2	266.8	265.3	263.8	262.4	261.0	259.5	258.0	256.7	255.2	254.0
77.5°	200.7	200.1	199.5	198.9	198.2	197.2	196.0	194.7	193.5	192.2	191.8
80°	160.1	159.2	158.4	157.5	156.7	156.0	155.4	154.7	154.2	153.6	153.0
82.5°	120.6	120.2	119.8	119.4	119.0	118.7	118.5	118.5	118.3	118.2	117.9
85°	70.3	70.3	70.3	70.3	70.3	70.0	69.5	68.9	68.2	67.7	67.7
87.5°	27.8	28.2	28.5	28.9	29.3	29.6	29.8	30.0	30.2	30.4	30.7
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	15.5	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7
95°	67.6	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7
97.5°	143.6	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6
100°	201.6	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5
102.5°	266.5	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5
105°	370.1	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0
107.5°	466.2	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5
110°	531.2	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7



TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	594.1	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1
115°	691.0	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0
117.5°	778.3	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8
120°	837.3	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6
122.5°	892.3	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4
125°	971.3	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6
127.5°	1046.0	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8
130°	1094.3	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4
132.5°	1138.5	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7
135°	1204.9	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2
137.5°	1263.7	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2
140°	1302.0	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8
142.5°	1336.4	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0
145°	1389.4	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3
147.5°	1431.4	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3
150°	1461.9	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6
152.5°	1487.4	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6
155°	1523.4	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0
157.5°	1553.6	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1
160°	1571.3	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1
162.5°	1587.1	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7
165°	1607.0	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0
167.5°	1622.7	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0
170°	1631.6	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6
172.5°	1637.4	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5
175°	1643.8	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1
177.5°	1646.8	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7	1624.7
2.5°	1618.9	1621.3	1623.6	1624.6	1624.4	1624.2	1623.9	1623.7
5°	1610.3	1613.5	1616.7	1618.0	1617.4	1616.8	1616.2	1615.6
7.5°	1592.4	1594.9	1597.4	1598.6	1598.2	1597.8	1597.5	1597.2
10°	1577.3	1579.6	1581.9	1582.8	1582.3	1581.7	1581.0	1580.5
12.5°	1559.0	1561.5	1564.2	1565.0	1564.2	1563.3	1562.5	1561.7
15°	1524.0	1525.8	1527.5	1528.0	1527.1	1526.2	1525.3	1524.5
17.5°	1484.3	1485.4	1486.5	1486.7	1486.1	1485.6	1485.0	1484.4
20°	1454.7	1455.5	1456.4	1456.5	1456.0	1455.4	1454.8	1454.2
22.5°	1423.8	1425.3	1426.9	1427.1	1426.1	1425.1	1424.0	1422.9
25°	1372.8	1373.0	1373.4	1372.9	1371.7	1370.6	1369.5	1368.3
27.5°	1315.6	1314.9	1314.2	1313.1	1311.7	1310.3	1308.8	1307.3
30°	1276.1	1275.0	1273.8	1272.5	1271.1	1269.7	1268.2	1266.7
32.5°	1236.1	1234.7	1233.3	1231.9	1230.4	1229.0	1227.6	1226.1
35°	1172.9	1170.9	1168.8	1167.1	1165.6	1164.2	1162.7	1161.3
37.5°	1106.6	1104.4	1102.2	1100.2	1098.3	1096.3	1094.5	1092.5
40°	1060.5	1057.5	1054.7	1052.5	1051.1	1049.6	1048.1	1046.7
42.5°	1015.8	1012.4	1009.1	1006.9	1005.9	1004.9	1004.0	1003.0
45°	946.6	943.5	940.3	938.2	937.3	936.5	935.6	934.7
47.5°	879.7	876.1	872.5	869.6	867.4	865.2	863.0	860.8
50°	832.9	828.8	824.8	821.9	820.2	818.5	816.7	815.0
52.5°	784.9	781.3	777.7	774.9	772.7	770.5	768.3	766.1
55°	714.3	710.9	707.4	704.7	703.0	701.3	699.5	697.8
57.5°	643.6	640.3	637.0	634.5	632.8	631.1	629.4	627.8
60°	594.9	592.4	589.8	587.7	586.3	584.8	583.4	582.0
62.5°	547.5	545.1	542.7	540.9	539.4	537.9	536.5	535.1
65°	478.5	475.6	472.7	470.6	469.1	467.7	466.2	464.8
67.5°	407.4	404.6	401.9	400.2	399.8	399.4	399.0	398.6
70°	362.5	360.2	357.8	356.3	355.4	354.6	353.7	352.8
72.5°	317.6	315.8	313.9	312.5	311.7	310.8	309.9	309.1
75°	252.8	251.7	250.5	249.8	249.6	249.2	248.9	248.7
77.5°	191.4	191.1	190.8	190.2	189.5	188.7	187.9	187.2
80°	152.5	151.9	151.3	150.9	150.6	150.3	150.0	149.7
82.5°	117.5	117.2	116.8	116.5	116.2	115.9	115.6	115.4
85°	67.7	67.7	67.7	67.6	67.3	66.9	66.7	66.4
87.5°	31.1	31.4	31.7	32.0	32.0	32.1	32.3	32.4
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	29.4	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	30.3	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.8	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	44.8	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	160.5	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	388.5	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	480.7	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.3	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332863-930

CATALOG NUMBER: S124DIW-S1195D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	604.0	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	694.6	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.7	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	897.7	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	975.4	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.6	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1099.8	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.0	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1209.7	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1270.8	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1308.6	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1343.6	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.6	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.5	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.0	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1523.1	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1584.5	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1605.2	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1620.4	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1629.8	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1635.7	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1642.6	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1645.4	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)