

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332734-930

Luminaire Tested: **S124DIW-S350D1340U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332734-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1340U930-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5082.3 lumens  
Efficiency: N/A  
Efficacy: 109.1 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	25
1	92	88	85	81	82	79	76	73	61	59	57	45	43	42	30	29	28	22
2	84	77	71	66	75	69	64	60	54	50	47	39	37	35	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18	13
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14	10
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3760	3760	3760	3760
5°	4428	3770	3327	3770
10°	5302	3754	2995	3754
15°	6273	3716	2751	3716
20°	6985	3677	2533	3677
25°	7098	3619	2382	3619
30°	6040	3566	2335	3566
35°	4644	3476	2335	3476
40°	3620	3371	2380	3371
45°	3017	3214	2419	3214
50°	2656	3022	2501	3022
55°	2434	2792	2601	2792
60°	2280	2585	2722	2585
65°	2122	2355	2823	2355
70°	1940	2127	2887	2127
75°	1734	1871	2854	1871
80°	1450	1534	2762	1534
85°	1074	1112	2640	1112



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	0.9
10°-20°	139.9	2.8
20°-30°	221.8	4.4
30°-40°	246.8	4.9
40°-50°	224.7	4.4
50°-60°	183.6	3.6
60°-70°	131.1	2.6
70°-80°	72.2	1.4
80°-90°	23.8	0.5
90°-100°	90.2	1.8
100°-110°	267.1	5.3
110°-120°	453.4	8.9
120°-130°	597.8	11.8
130°-140°	671.4	13.2
140°-150°	659.8	13.0
150°-160°	554.9	10.9
160°-170°	369.2	7.3
170°-180°	129.3	2.5
0°-30°	407.0	8.0
0°-40°	653.9	12.9
0°-60°	1062.2	20.9
0°-90°	1289.2	25.4
90°-120°	810.7	16.0
90°-150°	2739.7	53.9
90°-180°	3793.0	74.6
0°-180°	5082.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	466	466	466	466	466	
5°	546	465	411	465	546	56
15°	751	445	329	445	751	212
25°	797	406	267	406	797	351
35°	471	353	237	353	471	299
45°	264	282	212	282	264	208
55°	173	198	185	198	173	156
65°	111	123	148	123	111	110
75°	56	60	92	60	56	59
85°	12	12	28	12	12	15
90°	32	3	32	3	32	16
95°	84	63	84	63	84	87
105°	258	246	258	246	258	272
115°	457	461	457	461	457	452
125°	666	671	666	671	666	594
135°	867	866	867	866	867	670
145°	1053	1052	1053	1052	1053	659
155°	1204	1205	1204	1205	1204	554
165°	1309	1312	1309	1312	1309	369
175°	1359	1365	1359	1365	1359	129
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	495.7	495.6	494.1	493.7	492.7	491.3	491.0	488.4	483.6	481.2	480.6
5°	546.4	550.3	545.3	544.3	543.7	537.4	534.1	530.3	521.4	516.2	512.1
7.5°	607.0	607.4	605.2	603.5	598.5	593.0	584.7	575.8	565.2	554.2	545.9
10°	646.8	648.3	645.8	645.5	635.6	629.4	617.1	606.7	594.7	581.4	569.2
12.5°	688.8	686.6	685.3	677.1	675.2	664.0	649.6	639.0	620.4	605.1	589.0
15°	750.6	746.3	743.6	732.3	726.7	711.0	695.8	684.0	659.9	636.9	619.5
17.5°	786.8	791.1	784.9	780.2	765.7	754.7	739.2	714.4	695.6	667.1	645.1
20°	813.1	813.5	810.0	805.2	793.9	779.9	763.0	736.0	713.4	685.0	654.8
22.5°	820.2	820.3	818.8	814.3	805.7	794.4	777.3	754.7	727.4	696.6	666.4
25°	796.9	796.1	797.9	802.9	799.6	796.1	786.3	769.5	744.0	711.4	679.0
27.5°	710.3	715.7	725.5	737.8	749.7	758.7	761.2	757.8	742.1	715.3	681.3
30°	647.9	654.5	661.9	674.2	698.1	711.8	726.8	738.3	731.9	710.5	678.8
32.5°	579.4	581.1	591.9	605.9	627.9	654.2	678.1	701.2	708.9	697.7	671.2
35°	471.2	473.9	485.7	499.5	526.4	558.6	594.5	626.6	653.0	663.6	650.0
37.5°	384.5	392.2	400.6	415.5	439.1	468.1	505.4	546.9	586.3	612.7	617.2
40°	343.5	348.3	354.2	365.7	385.7	414.3	446.3	493.7	535.7	573.5	585.8
42.5°	311.0	313.9	317.6	327.8	343.1	371.5	400.8	442.5	484.5	529.8	550.5
45°	264.3	267.3	273.5	279.4	291.0	310.6	337.9	372.2	414.5	458.0	496.3
47.5°	230.6	232.4	236.1	242.6	252.4	265.4	287.5	316.2	355.3	397.7	438.4
50°	211.5	213.0	215.9	221.7	229.3	240.8	258.9	285.8	316.4	359.1	399.0
52.5°	196.3	197.0	199.1	203.0	209.0	218.7	233.7	255.8	284.4	322.4	362.2
55°	172.9	173.7	175.6	178.5	183.7	189.9	201.2	217.8	242.7	275.7	310.3
57.5°	153.6	154.2	155.7	156.9	161.2	166.2	175.0	186.8	205.6	233.7	264.5
60°	141.2	140.9	142.8	143.7	146.7	150.9	157.7	169.0	185.4	208.0	236.4
62.5°	129.2	128.7	130.3	131.6	133.2	136.8	142.4	151.2	164.6	185.0	209.5
65°	111.1	110.4	111.4	112.9	114.4	116.3	120.4	128.3	138.9	153.6	172.3
67.5°	93.0	93.8	94.0	94.7	95.6	98.2	101.0	106.6	114.1	125.9	141.7
70°	82.2	82.4	83.2	83.2	83.7	86.1	88.4	91.6	99.0	109.8	122.7
72.5°	71.4	72.2	71.9	72.5	73.0	74.5	76.1	79.3	85.5	93.6	104.5
75°	55.6	56.2	56.2	56.3	56.9	57.5	58.9	61.1	65.6	71.6	79.1
77.5°	40.5	40.6	40.8	41.6	41.6	42.5	43.5	45.3	47.5	51.6	56.3
80°	31.2	31.6	31.5	31.9	31.9	32.6	33.0	35.3	36.3	39.0	42.6
82.5°	22.9	23.3	23.2	23.8	24.1	24.3	24.8	25.8	26.7	29.1	30.6
85°	11.6	12.0	11.6	12.0	12.6	12.7	13.3	13.5	14.3	14.8	16.2
87.5°	9.7	10.1	10.0	10.1	10.3	10.3	10.1	9.7	10.0	9.9	10.1
90°	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1	24.7	23.2	21.4
92.5°	47.0	46.6	46.4	46.1	45.8	45.2	44.4	43.5	42.7	41.9	40.5
95°	83.6	83.6	83.6	83.6	83.6	83.2	82.5	81.8	81.0	80.4	78.7
97.5°	130.9	130.9	130.9	130.9	130.9	130.4	129.6	128.8	127.9	127.1	125.1
100°	163.9	163.9	163.9	163.9	163.9	163.6	163.2	162.7	162.2	161.8	159.6
102.5°	201.1	200.9	200.7	200.6	200.3	199.9	199.3	198.6	198.0	197.3	195.3
105°	258.0	257.3	256.6	255.8	255.2	254.5	253.8	253.1	252.3	251.7	250.7
107.5°	313.4	313.5	313.5	313.6	313.6	313.3	312.6	311.9	311.3	310.6	310.5
110°	353.2	352.5	351.7	351.1	350.3	350.3	350.7	351.1	351.6	352.1	352.4



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	393.8	393.6	393.5	393.3	393.2	393.1	393.3	393.4	393.5	393.5	394.0
115°	456.8	457.0	457.2	457.5	457.7	458.0	458.2	458.4	458.7	458.9	459.3
117.5°	516.8	517.3	517.8	518.2	518.7	519.3	520.2	521.0	521.7	522.5	522.9
120°	562.5	562.1	561.6	561.1	560.6	561.0	562.1	563.4	564.5	565.7	566.4
122.5°	600.5	601.4	602.3	603.1	604.0	604.8	605.6	606.3	607.2	608.0	608.3
125°	666.1	666.6	667.1	667.6	668.0	668.5	669.0	669.4	669.8	670.3	670.6
127.5°	726.8	727.2	727.6	728.0	728.3	728.7	729.2	729.7	730.2	730.6	731.0
130°	766.5	767.5	768.4	769.4	770.4	771.0	771.5	772.0	772.4	772.9	772.9
132.5°	808.9	809.3	809.6	810.0	810.4	810.8	811.3	811.7	812.2	812.7	812.9
135°	867.0	867.7	868.5	869.1	869.8	870.4	870.9	871.4	871.9	872.3	872.3
137.5°	928.1	928.0	927.9	927.7	927.6	927.8	928.5	929.0	929.6	930.3	929.8
140°	965.4	965.6	965.8	966.0	966.3	966.5	966.8	967.0	967.3	967.4	967.4
142.5°	1002.6	1002.7	1002.7	1002.7	1002.7	1002.8	1002.9	1002.9	1003.0	1003.0	1003.2
145°	1053.1	1053.9	1054.5	1055.2	1056.0	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1104.3	1104.6	1104.7	1105.0	1105.2	1105.5	1105.6	1105.8	1106.0	1106.2	1106.4
150°	1135.6	1135.8	1136.0	1136.3	1136.5	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1164.3	1165.0	1165.6	1166.2	1166.8	1166.9	1166.3	1165.7	1165.1	1164.6	1164.4
155°	1204.4	1205.3	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4	1204.5
157.5°	1240.1	1240.9	1241.6	1242.4	1243.2	1243.3	1242.6	1241.9	1241.2	1240.5	1240.6
160°	1260.4	1261.5	1262.7	1263.9	1265.0	1265.3	1264.6	1263.9	1263.1	1262.5	1262.7
162.5°	1281.5	1282.7	1283.9	1285.0	1286.2	1286.1	1284.9	1283.6	1282.4	1281.1	1281.3
165°	1309.0	1309.9	1310.8	1311.8	1312.8	1312.6	1311.1	1309.7	1308.3	1306.8	1307.3
167.5°	1328.7	1330.2	1331.5	1333.0	1334.5	1334.5	1333.1	1331.7	1330.3	1328.9	1328.9
170°	1339.7	1341.3	1343.0	1344.6	1346.2	1346.4	1344.9	1343.5	1342.1	1340.7	1340.5
172.5°	1349.0	1350.6	1352.3	1353.9	1355.5	1355.6	1354.0	1352.3	1350.8	1349.2	1349.2
175°	1358.7	1360.3	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7	1358.9
177.5°	1363.8	1365.3	1366.8	1368.3	1369.8	1369.9	1368.6	1367.3	1366.0	1364.6	1364.6
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	480.8	478.6	477.0	475.8	472.5	470.4	468.9	466.8	464.2	461.6	458.4
5°	508.0	501.5	496.7	489.3	482.4	476.6	470.6	465.2	458.7	451.5	446.3
7.5°	536.7	526.9	514.5	503.6	491.4	480.8	471.3	461.6	451.5	441.6	432.7
10°	555.0	542.4	528.5	512.1	496.7	483.0	470.3	457.9	445.9	434.0	423.7
12.5°	574.5	558.9	538.3	519.2	501.9	483.6	468.2	453.1	438.6	426.1	414.2
15°	600.9	578.3	554.6	528.9	506.1	484.7	463.7	444.6	428.4	411.7	400.1
17.5°	617.0	589.1	562.0	535.2	507.6	480.5	457.9	435.9	415.6	399.1	384.5
20°	627.7	599.9	566.1	539.3	506.5	478.7	452.5	428.0	406.8	389.2	374.1
22.5°	636.9	604.9	571.0	535.7	503.1	473.6	444.9	420.3	398.6	380.1	365.7
25°	642.0	605.1	568.4	533.3	496.3	461.4	435.3	406.3	383.2	363.7	348.3
27.5°	642.5	603.1	561.6	522.6	484.4	451.8	419.0	393.1	369.1	348.5	333.6
30°	640.8	599.7	555.1	512.9	474.5	439.2	410.6	382.5	357.9	337.5	322.0
32.5°	635.4	592.6	546.8	502.1	462.3	427.7	398.3	371.5	347.6	327.4	311.2
35°	619.8	577.5	528.7	482.2	441.5	406.6	379.9	352.7	328.8	309.7	294.1
37.5°	595.3	557.2	507.5	459.4	419.4	384.3	357.9	333.4	311.8	292.4	276.4
40°	574.1	540.5	490.6	443.8	400.6	367.2	342.5	319.9	298.5	280.1	264.9
42.5°	549.5	520.2	474.3	424.7	382.9	349.4	325.4	305.1	284.9	268.0	252.7
45°	505.7	486.4	443.2	397.3	353.8	322.2	299.3	281.5	264.6	247.9	235.2
47.5°	455.4	445.8	409.4	365.8	324.7	293.4	273.5	257.1	242.2	228.2	217.0
50°	421.6	416.9	385.6	343.5	304.1	274.8	254.7	240.6	227.9	215.6	204.9
52.5°	388.2	388.1	359.7	321.2	284.8	256.6	236.6	223.5	212.5	202.4	192.9
55°	337.3	342.7	320.5	286.2	253.6	228.0	210.1	198.4	190.6	182.4	175.2
57.5°	290.5	299.5	281.1	250.9	223.6	200.2	184.6	175.8	167.5	162.5	157.3
60°	259.9	268.4	254.1	228.7	203.0	183.0	168.0	160.1	153.0	149.5	145.9
62.5°	232.8	240.3	229.8	206.1	183.8	164.5	152.0	144.4	139.6	135.8	133.4
65°	194.0	200.3	191.2	174.1	154.9	139.5	129.3	123.3	118.7	117.2	114.4
67.5°	156.8	162.6	157.7	143.1	127.8	116.0	108.0	102.3	99.5	98.2	96.3
70°	134.7	140.5	135.3	122.5	110.7	100.9	93.4	90.1	87.2	86.7	84.0
72.5°	116.0	119.9	114.7	104.8	94.7	86.4	80.6	77.1	75.7	74.6	73.1
75°	87.0	90.5	87.0	79.3	72.2	66.4	61.4	60.0	58.3	57.7	56.7
77.5°	61.6	64.6	62.0	57.2	51.8	47.3	44.6	42.9	42.5	41.5	42.0
80°	47.0	49.0	46.5	43.2	39.0	35.9	34.0	33.0	31.9	31.5	32.2
82.5°	33.8	34.7	33.3	31.1	28.0	26.0	24.7	23.6	23.3	23.4	23.4
85°	17.5	17.4	17.2	15.2	14.3	13.0	12.1	12.0	11.7	12.1	12.6
87.5°	9.8	9.5	9.0	8.0	6.9	6.0	5.3	4.6	5.3	6.0	6.7
90°	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2	5.8	8.3	10.9
92.5°	39.2	37.9	36.6	34.5	31.5	28.5	25.6	22.7	25.6	28.5	31.5
95°	77.0	75.4	73.8	71.9	69.8	67.7	65.6	63.4	65.6	67.7	69.8
97.5°	123.3	121.3	119.4	117.6	115.9	114.2	112.5	110.8	112.5	114.2	115.9
100°	157.5	155.4	153.3	151.8	150.8	149.9	149.0	148.1	149.0	149.9	150.8
102.5°	193.5	191.5	189.6	188.4	188.1	187.7	187.4	186.9	187.4	187.7	188.1
105°	249.8	248.8	247.9	247.3	247.0	246.9	246.6	246.4	246.6	246.9	247.0
107.5°	310.4	310.2	310.1	309.9	309.6	309.3	309.0	308.8	309.0	309.3	309.6
110°	352.5	352.8	353.0	352.9	352.5	352.0	351.5	351.1	351.5	352.0	352.5





TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	394.4	394.8	395.3	395.4	395.3	395.2	395.1	395.0	395.1	395.2	395.3
115°	459.8	460.3	460.8	461.0	461.0	461.0	461.0	461.0	461.0	461.0	461.0
117.5°	523.2	523.5	523.8	523.9	523.7	523.6	523.3	523.2	523.3	523.6	523.7
120°	567.1	567.8	568.5	568.3	567.4	566.5	565.6	564.6	565.6	566.5	567.4
122.5°	608.6	608.9	609.3	609.3	608.9	608.5	608.1	607.7	608.1	608.5	608.9
125°	670.8	671.1	671.3	671.4	671.4	671.4	671.4	671.4	671.4	671.4	671.4
127.5°	731.4	731.7	732.1	732.0	731.2	730.6	729.9	729.1	729.9	730.6	731.2
130°	772.9	772.9	772.9	772.6	771.8	771.2	770.5	769.7	770.5	771.2	771.8
132.5°	813.0	813.3	813.4	813.3	812.8	812.2	811.7	811.2	811.7	812.2	812.8
135°	872.3	872.3	872.3	871.6	870.2	868.8	867.4	865.9	867.4	868.8	870.2
137.5°	929.5	929.1	928.8	928.2	927.6	926.9	926.3	925.6	926.3	926.9	927.6
140°	967.4	967.4	967.4	967.3	966.8	966.3	965.8	965.4	965.8	966.3	966.8
142.5°	1003.4	1003.6	1003.7	1003.6	1003.1	1002.7	1002.2	1001.8	1002.2	1002.7	1003.1
145°	1056.9	1056.6	1056.4	1055.8	1054.9	1053.9	1053.0	1052.1	1053.0	1053.9	1054.9
147.5°	1106.6	1106.8	1106.9	1106.4	1105.4	1104.2	1103.1	1102.0	1103.1	1104.2	1105.4
150°	1136.6	1136.6	1136.6	1136.2	1135.2	1134.3	1133.3	1132.5	1133.3	1134.3	1135.2
152.5°	1164.2	1164.0	1163.8	1163.4	1162.9	1162.3	1161.7	1161.1	1161.7	1162.3	1162.9
155°	1204.8	1205.0	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3
157.5°	1240.6	1240.6	1240.6	1240.9	1241.3	1241.8	1242.2	1242.6	1242.2	1241.8	1241.3
160°	1263.0	1263.1	1263.4	1263.6	1263.9	1264.1	1264.4	1264.6	1264.4	1264.1	1263.9
162.5°	1281.6	1281.8	1282.1	1282.5	1283.0	1283.7	1284.3	1284.9	1284.3	1283.7	1283.0
165°	1307.8	1308.3	1308.8	1309.4	1310.0	1310.8	1311.5	1312.1	1311.5	1310.8	1310.0
167.5°	1328.8	1328.8	1328.7	1329.2	1330.2	1331.1	1332.1	1333.1	1332.1	1331.1	1330.2
170°	1340.3	1340.0	1339.8	1340.3	1341.4	1342.6	1343.8	1344.9	1343.8	1342.6	1341.4
172.5°	1349.1	1349.1	1349.0	1349.5	1350.5	1351.4	1352.4	1353.4	1352.4	1351.4	1350.5
175°	1359.2	1359.4	1359.6	1360.3	1361.5	1362.7	1363.8	1365.1	1363.8	1362.7	1361.5
177.5°	1364.6	1364.6	1364.6	1365.1	1366.0	1366.9	1367.9	1368.8	1367.9	1366.9	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	456.8	455.4	453.5	450.7	448.3	445.9	445.2	444.3	446.2	444.7	444.2
5°	441.9	437.8	432.6	426.6	423.1	418.2	417.2	415.2	413.3	413.1	411.2
7.5°	426.0	420.0	413.2	407.2	401.5	396.0	392.4	391.7	388.8	387.1	385.2
10°	415.8	408.5	400.6	394.8	388.2	382.5	378.4	376.1	374.1	372.0	370.1
12.5°	403.8	396.0	389.5	383.2	375.4	371.0	364.4	360.4	360.0	360.0	355.0
15°	389.8	382.0	372.0	363.1	358.9	350.4	346.7	342.1	339.2	336.3	334.0
17.5°	373.7	364.1	356.3	346.1	338.0	331.3	326.4	323.7	319.3	315.2	312.3
20°	363.7	353.5	345.2	334.4	325.5	317.2	313.2	309.3	306.1	302.6	299.3
22.5°	353.5	342.8	332.7	322.2	314.0	305.2	301.3	296.0	292.9	291.0	287.7
25°	337.5	325.9	314.3	304.3	295.8	288.0	282.9	278.8	275.3	273.8	271.7
27.5°	320.0	308.5	297.3	285.9	276.3	270.7	266.5	263.5	261.5	259.4	258.4
30°	308.9	296.9	285.0	274.3	265.5	259.9	256.1	254.0	252.4	251.4	250.5
32.5°	297.7	285.8	273.3	263.6	255.6	250.6	247.7	245.6	244.8	244.5	244.1
35°	279.6	267.7	256.1	247.4	239.9	237.9	235.4	234.2	233.8	235.2	235.8
37.5°	262.1	251.0	240.4	232.0	227.0	224.2	223.3	223.4	224.8	225.9	227.3
40°	250.9	240.0	230.0	222.7	218.0	216.3	215.9	216.9	218.4	219.8	221.4
42.5°	239.9	229.3	220.1	213.3	210.0	208.4	208.6	209.6	211.8	213.4	215.7
45°	222.9	214.0	205.1	199.5	196.8	197.2	197.2	198.9	201.1	203.6	206.1
47.5°	206.8	197.9	190.6	185.9	184.5	184.2	185.2	187.5	190.5	193.6	197.1
50°	196.1	187.5	181.2	176.9	175.4	175.9	177.5	179.6	183.3	187.2	190.9
52.5°	185.1	177.3	171.5	167.5	166.4	167.5	169.0	172.4	175.6	179.8	184.2
55°	168.0	161.5	156.9	154.0	153.6	154.2	155.9	159.6	164.2	169.4	173.7
57.5°	151.2	145.6	141.4	139.4	139.6	140.1	143.0	147.3	152.3	157.8	163.3
60°	139.7	134.7	131.2	129.6	129.9	131.0	134.5	138.5	144.7	150.1	155.9
62.5°	128.9	124.5	121.2	119.8	119.5	122.1	125.4	129.6	135.7	141.8	148.1
65°	111.5	108.0	105.3	104.6	105.2	107.1	111.4	116.9	122.1	128.5	135.1
67.5°	94.6	91.7	89.8	90.2	90.9	93.8	97.3	102.1	108.0	114.6	121.1
70°	83.7	81.0	79.5	79.7	80.9	84.3	87.4	92.2	98.6	105.3	110.7
72.5°	72.6	70.8	69.5	70.3	71.4	73.8	77.7	82.5	88.1	94.4	100.1
75°	55.8	55.8	55.0	55.6	57.3	59.6	62.5	67.5	73.1	78.2	82.8
77.5°	41.3	40.9	41.4	42.2	43.1	45.9	49.2	52.8	57.0	62.0	65.9
80°	31.6	31.9	32.8	34.0	34.3	36.4	39.9	43.2	46.5	50.7	54.4
82.5°	23.8	24.0	24.5	25.9	26.3	28.6	30.8	34.1	37.1	39.9	43.0
85°	13.0	13.0	13.9	14.5	15.4	17.0	18.3	20.3	23.0	24.9	27.8
87.5°	7.7	8.1	9.0	9.8	10.6	11.7	12.3	14.3	15.2	16.3	17.9
90°	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1	27.5	28.9	29.8
92.5°	34.5	36.6	37.9	39.2	40.5	41.9	42.7	43.5	44.4	45.2	45.8
95°	71.9	73.8	75.4	77.0	78.7	80.4	81.0	81.8	82.5	83.2	83.6
97.5°	117.6	119.4	121.3	123.3	125.1	127.1	127.9	128.8	129.6	130.4	130.9
100°	151.8	153.3	155.4	157.5	159.6	161.8	162.2	162.7	163.2	163.6	163.9
102.5°	188.4	189.6	191.5	193.5	195.3	197.3	198.0	198.6	199.3	199.9	200.3
105°	247.3	247.9	248.8	249.8	250.7	251.7	252.3	253.1	253.8	254.5	255.2
107.5°	309.9	310.1	310.2	310.4	310.5	310.6	311.3	311.9	312.6	313.3	313.6
110°	352.9	353.0	352.8	352.5	352.4	352.1	351.6	351.1	350.7	350.3	350.3



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	395.4	395.3	394.8	394.4	394.0	393.5	393.5	393.4	393.3	393.1	393.2
115°	461.0	460.8	460.3	459.8	459.3	458.9	458.7	458.4	458.2	458.0	457.7
117.5°	523.9	523.8	523.5	523.2	522.9	522.5	521.7	521.0	520.2	519.3	518.7
120°	568.3	568.5	567.8	567.1	566.4	565.7	564.5	563.4	562.1	561.0	560.6
122.5°	609.3	609.3	608.9	608.6	608.3	608.0	607.2	606.3	605.6	604.8	604.0
125°	671.4	671.3	671.1	670.8	670.6	670.3	669.8	669.4	669.0	668.5	668.0
127.5°	732.0	732.1	731.7	731.4	731.0	730.6	730.2	729.7	729.2	728.7	728.3
130°	772.6	772.9	772.9	772.9	772.9	772.9	772.4	772.0	771.5	771.0	770.4
132.5°	813.3	813.4	813.3	813.0	812.9	812.7	812.2	811.7	811.3	810.8	810.4
135°	871.6	872.3	872.3	872.3	872.3	872.3	871.9	871.4	870.9	870.4	869.8
137.5°	928.2	928.8	929.1	929.5	929.8	930.3	929.6	929.0	928.5	927.8	927.6
140°	967.3	967.4	967.4	967.4	967.4	967.4	967.3	967.0	966.8	966.5	966.3
142.5°	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0	1002.9	1002.9	1002.8	1002.7
145°	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1	1056.9	1056.6	1056.4	1056.0
147.5°	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0	1105.8	1105.6	1105.5	1105.2
150°	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.5
152.5°	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1	1165.7	1166.3	1166.9	1166.8
155°	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3	1206.2	1207.1	1208.1	1208.1
157.5°	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2	1241.9	1242.6	1243.3	1243.2
160°	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1	1263.9	1264.6	1265.3	1265.0
162.5°	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4	1283.6	1284.9	1286.1	1286.2
165°	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3	1309.7	1311.1	1312.6	1312.8
167.5°	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3	1331.7	1333.1	1334.5	1334.5
170°	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1	1343.5	1344.9	1346.4	1346.2
172.5°	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8	1352.3	1354.0	1355.6	1355.5
175°	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3	1362.0	1363.6	1365.3	1365.3
177.5°	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0	1367.3	1368.6	1369.9	1369.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	443.8	443.6	442.5	442.3	442.5	443.6	443.8	444.2	444.7	446.2	444.3
5°	410.0	409.0	408.5	410.6	408.5	409.0	410.0	411.2	413.1	413.3	415.2
7.5°	384.5	383.8	382.0	381.5	382.0	383.8	384.5	385.2	387.1	388.8	391.7
10°	368.2	367.4	365.8	365.4	365.8	367.4	368.2	370.1	372.0	374.1	376.1
12.5°	352.4	350.9	350.6	351.0	350.6	350.9	352.4	355.0	360.0	360.0	360.4
15°	331.5	330.7	328.6	329.2	328.6	330.7	331.5	334.0	336.3	339.2	342.1
17.5°	310.9	310.0	307.4	309.7	307.4	310.0	310.9	312.3	315.2	319.3	323.7
20°	297.9	296.4	295.1	294.8	295.1	296.4	297.9	299.3	302.6	306.1	309.3
22.5°	285.6	284.2	284.1	282.8	284.1	284.2	285.6	287.7	291.0	292.9	296.0
25°	270.1	268.8	268.4	267.4	268.4	268.8	270.1	271.7	273.8	275.3	278.8
27.5°	258.3	257.6	256.9	257.2	256.9	257.6	258.3	258.4	259.4	261.5	263.5
30°	251.0	250.9	250.5	250.5	250.5	250.9	251.0	250.5	251.4	252.4	254.0
32.5°	245.0	245.0	245.2	245.2	245.2	245.0	245.0	244.1	244.5	244.8	245.6
35°	236.6	237.2	237.5	236.9	237.5	237.2	236.6	235.8	235.2	233.8	234.2
37.5°	228.9	229.5	230.1	230.7	230.1	229.5	228.9	227.3	225.9	224.8	223.4
40°	223.1	224.4	224.8	225.8	224.8	224.4	223.1	221.4	219.8	218.4	216.9
42.5°	217.5	219.0	220.0	220.2	220.0	219.0	217.5	215.7	213.4	211.8	209.6
45°	209.0	210.5	211.9	211.9	211.9	210.5	209.0	206.1	203.6	201.1	198.9
47.5°	200.2	202.4	203.7	204.1	203.7	202.4	200.2	197.1	193.6	190.5	187.5
50°	194.1	196.8	198.2	199.1	198.2	196.8	194.1	190.9	187.2	183.3	179.6
52.5°	188.3	190.9	192.7	193.2	192.7	190.9	188.3	184.2	179.8	175.6	172.4
55°	178.1	182.0	184.1	184.8	184.1	182.0	178.1	173.7	169.4	164.2	159.6
57.5°	168.5	172.1	174.6	175.1	174.6	172.1	168.5	163.3	157.8	152.3	147.3
60°	161.1	165.0	168.0	168.6	168.0	165.0	161.1	155.9	150.1	144.7	138.5
62.5°	153.5	157.6	160.4	161.8	160.4	157.6	153.5	148.1	141.8	135.7	129.6
65°	140.5	144.6	147.2	147.8	147.2	144.6	140.5	135.1	128.5	122.1	116.9
67.5°	126.2	130.3	132.0	133.1	132.0	130.3	126.2	121.1	114.6	108.0	102.1
70°	116.2	119.4	121.4	122.3	121.4	119.4	116.2	110.7	105.3	98.6	92.2
72.5°	104.8	108.2	110.4	110.6	110.4	108.2	104.8	100.1	94.4	88.1	82.5
75°	87.2	90.3	91.5	91.5	91.5	90.3	87.2	82.8	78.2	73.1	67.5
77.5°	69.1	70.6	72.1	72.4	72.1	70.6	69.1	65.9	62.0	57.0	52.8
80°	57.3	58.3	59.4	59.4	59.4	58.3	57.3	54.4	50.7	46.5	43.2
82.5°	45.2	46.1	47.2	47.0	47.2	46.1	45.2	43.0	39.9	37.1	34.1
85°	27.4	29.1	28.9	28.5	28.9	29.1	27.4	27.8	24.9	23.0	20.3
87.5°	18.4	18.7	19.2	19.6	19.2	18.7	18.4	17.9	16.3	15.2	14.3
90°	30.3	30.8	31.2	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1
92.5°	46.1	46.4	46.6	47.0	46.6	46.4	46.1	45.8	45.2	44.4	43.5
95°	83.6	83.6	83.6	83.6	83.6	83.6	83.6	83.6	83.2	82.5	81.8
97.5°	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.9	130.4	129.6	128.8
100°	163.9	163.9	163.9	163.9	163.9	163.9	163.9	163.9	163.6	163.2	162.7
102.5°	200.6	200.7	200.9	201.1	200.9	200.7	200.6	200.3	199.9	199.3	198.6
105°	255.8	256.6	257.3	258.0	257.3	256.6	255.8	255.2	254.5	253.8	253.1
107.5°	313.6	313.5	313.5	313.4	313.5	313.5	313.6	313.6	313.3	312.6	311.9
110°	351.1	351.7	352.5	353.2	352.5	351.7	351.1	350.3	350.3	350.7	351.1



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	393.3	393.5	393.6	393.8	393.6	393.5	393.3	393.2	393.1	393.3	393.4
115°	457.5	457.2	457.0	456.8	457.0	457.2	457.5	457.7	458.0	458.2	458.4
117.5°	518.2	517.8	517.3	516.8	517.3	517.8	518.2	518.7	519.3	520.2	521.0
120°	561.1	561.6	562.1	562.5	562.1	561.6	561.1	560.6	561.0	562.1	563.4
122.5°	603.1	602.3	601.4	600.5	601.4	602.3	603.1	604.0	604.8	605.6	606.3
125°	667.6	667.1	666.6	666.1	666.6	667.1	667.6	668.0	668.5	669.0	669.4
127.5°	728.0	727.6	727.2	726.8	727.2	727.6	728.0	728.3	728.7	729.2	729.7
130°	769.4	768.4	767.5	766.5	767.5	768.4	769.4	770.4	771.0	771.5	772.0
132.5°	810.0	809.6	809.3	808.9	809.3	809.6	810.0	810.4	810.8	811.3	811.7
135°	869.1	868.5	867.7	867.0	867.7	868.5	869.1	869.8	870.4	870.9	871.4
137.5°	927.7	927.9	928.0	928.1	928.0	927.9	927.7	927.6	927.8	928.5	929.0
140°	966.0	965.8	965.6	965.4	965.6	965.8	966.0	966.3	966.5	966.8	967.0
142.5°	1002.7	1002.7	1002.7	1002.6	1002.7	1002.7	1002.7	1002.7	1002.8	1002.9	1002.9
145°	1055.2	1054.5	1053.9	1053.1	1053.9	1054.5	1055.2	1056.0	1056.4	1056.6	1056.9
147.5°	1105.0	1104.7	1104.6	1104.3	1104.6	1104.7	1105.0	1105.2	1105.5	1105.6	1105.8
150°	1136.3	1136.0	1135.8	1135.6	1135.8	1136.0	1136.3	1136.5	1136.6	1136.6	1136.6
152.5°	1166.2	1165.6	1165.0	1164.3	1165.0	1165.6	1166.2	1166.8	1166.9	1166.3	1165.7
155°	1207.1	1206.2	1205.3	1204.4	1205.3	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2
157.5°	1242.4	1241.6	1240.9	1240.1	1240.9	1241.6	1242.4	1243.2	1243.3	1242.6	1241.9
160°	1263.9	1262.7	1261.5	1260.4	1261.5	1262.7	1263.9	1265.0	1265.3	1264.6	1263.9
162.5°	1285.0	1283.9	1282.7	1281.5	1282.7	1283.9	1285.0	1286.2	1286.1	1284.9	1283.6
165°	1311.8	1310.8	1309.9	1309.0	1309.9	1310.8	1311.8	1312.8	1312.6	1311.1	1309.7
167.5°	1333.0	1331.5	1330.2	1328.7	1330.2	1331.5	1333.0	1334.5	1334.5	1333.1	1331.7
170°	1344.6	1343.0	1341.3	1339.7	1341.3	1343.0	1344.6	1346.2	1346.4	1344.9	1343.5
172.5°	1353.9	1352.3	1350.6	1349.0	1350.6	1352.3	1353.9	1355.5	1355.6	1354.0	1352.3
175°	1363.6	1362.0	1360.3	1358.7	1360.3	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0
177.5°	1368.3	1366.8	1365.3	1363.8	1365.3	1366.8	1368.3	1369.8	1369.9	1368.6	1367.3
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	445.2	445.9	448.3	450.7	453.5	455.4	456.8	458.4	461.6	464.2	466.8
5°	417.2	418.2	423.1	426.6	432.6	437.8	441.9	446.3	451.5	458.7	465.2
7.5°	392.4	396.0	401.5	407.2	413.2	420.0	426.0	432.7	441.6	451.5	461.6
10°	378.4	382.5	388.2	394.8	400.6	408.5	415.8	423.7	434.0	445.9	457.9
12.5°	364.4	371.0	375.4	383.2	389.5	396.0	403.8	414.2	426.1	438.6	453.1
15°	346.7	350.4	358.9	363.1	372.0	382.0	389.8	400.1	411.7	428.4	444.6
17.5°	326.4	331.3	338.0	346.1	356.3	364.1	373.7	384.5	399.1	415.6	435.9
20°	313.2	317.2	325.5	334.4	345.2	353.5	363.7	374.1	389.2	406.8	428.0
22.5°	301.3	305.2	314.0	322.2	332.7	342.8	353.5	365.7	380.1	398.6	420.3
25°	282.9	288.0	295.8	304.3	314.3	325.9	337.5	348.3	363.7	383.2	406.3
27.5°	266.5	270.7	276.3	285.9	297.3	308.5	320.0	333.6	348.5	369.1	393.1
30°	256.1	259.9	265.5	274.3	285.0	296.9	308.9	322.0	337.5	357.9	382.5
32.5°	247.7	250.6	255.6	263.6	273.3	285.8	297.7	311.2	327.4	347.6	371.5
35°	235.4	237.9	239.9	247.4	256.1	267.7	279.6	294.1	309.7	328.8	352.7
37.5°	223.3	224.2	227.0	232.0	240.4	251.0	262.1	276.4	292.4	311.8	333.4
40°	215.9	216.3	218.0	222.7	230.0	240.0	250.9	264.9	280.1	298.5	319.9
42.5°	208.6	208.4	210.0	213.3	220.1	229.3	239.9	252.7	268.0	284.9	305.1
45°	197.2	197.2	196.8	199.5	205.1	214.0	222.9	235.2	247.9	264.6	281.5
47.5°	185.2	184.2	184.5	185.9	190.6	197.9	206.8	217.0	228.2	242.2	257.1
50°	177.5	175.9	175.4	176.9	181.2	187.5	196.1	204.9	215.6	227.9	240.6
52.5°	169.0	167.5	166.4	167.5	171.5	177.3	185.1	192.9	202.4	212.5	223.5
55°	155.9	154.2	153.6	154.0	156.9	161.5	168.0	175.2	182.4	190.6	198.4
57.5°	143.0	140.1	139.6	139.4	141.4	145.6	151.2	157.3	162.5	167.5	175.8
60°	134.5	131.0	129.9	129.6	131.2	134.7	139.7	145.9	149.5	153.0	160.1
62.5°	125.4	122.1	119.5	119.8	121.2	124.5	128.9	133.4	135.8	139.6	144.4
65°	111.4	107.1	105.2	104.6	105.3	108.0	111.5	114.4	117.2	118.7	123.3
67.5°	97.3	93.8	90.9	90.2	89.8	91.7	94.6	96.3	98.2	99.5	102.3
70°	87.4	84.3	80.9	79.7	79.5	81.0	83.7	84.0	86.7	87.2	90.1
72.5°	77.7	73.8	71.4	70.3	69.5	70.8	72.6	73.1	74.6	75.7	77.1
75°	62.5	59.6	57.3	55.6	55.0	55.8	55.8	56.7	57.7	58.3	60.0
77.5°	49.2	45.9	43.1	42.2	41.4	40.9	41.3	42.0	41.5	42.5	42.9
80°	39.9	36.4	34.3	34.0	32.8	31.9	31.6	32.2	31.5	31.9	33.0
82.5°	30.8	28.6	26.3	25.9	24.5	24.0	23.8	23.4	23.4	23.3	23.6
85°	18.3	17.0	15.4	14.5	13.9	13.0	13.0	12.6	12.1	11.7	12.0
87.5°	12.3	11.7	10.6	9.8	9.0	8.1	7.7	6.7	6.0	5.3	4.6
90°	24.7	23.2	21.4	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2
92.5°	42.7	41.9	40.5	39.2	37.9	36.6	34.5	31.5	28.5	25.6	22.7
95°	81.0	80.4	78.7	77.0	75.4	73.8	71.9	69.8	67.7	65.6	63.4
97.5°	127.9	127.1	125.1	123.3	121.3	119.4	117.6	115.9	114.2	112.5	110.8
100°	162.2	161.8	159.6	157.5	155.4	153.3	151.8	150.8	149.9	149.0	148.1
102.5°	198.0	197.3	195.3	193.5	191.5	189.6	188.4	188.1	187.7	187.4	186.9
105°	252.3	251.7	250.7	249.8	248.8	247.9	247.3	247.0	246.9	246.6	246.4
107.5°	311.3	310.6	310.5	310.4	310.2	310.1	309.9	309.6	309.3	309.0	308.8
110°	351.6	352.1	352.4	352.5	352.8	353.0	352.9	352.5	352.0	351.5	351.1



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	393.5	393.5	394.0	394.4	394.8	395.3	395.4	395.3	395.2	395.1	395.0
115°	458.7	458.9	459.3	459.8	460.3	460.8	461.0	461.0	461.0	461.0	461.0
117.5°	521.7	522.5	522.9	523.2	523.5	523.8	523.9	523.7	523.6	523.3	523.2
120°	564.5	565.7	566.4	567.1	567.8	568.5	568.3	567.4	566.5	565.6	564.6
122.5°	607.2	608.0	608.3	608.6	608.9	609.3	609.3	608.9	608.5	608.1	607.7
125°	669.8	670.3	670.6	670.8	671.1	671.3	671.4	671.4	671.4	671.4	671.4
127.5°	730.2	730.6	731.0	731.4	731.7	732.1	732.0	731.2	730.6	729.9	729.1
130°	772.4	772.9	772.9	772.9	772.9	772.9	772.6	771.8	771.2	770.5	769.7
132.5°	812.2	812.7	812.9	813.0	813.3	813.4	813.3	812.8	812.2	811.7	811.2
135°	871.9	872.3	872.3	872.3	872.3	872.3	871.6	870.2	868.8	867.4	865.9
137.5°	929.6	930.3	929.8	929.5	929.1	928.8	928.2	927.6	926.9	926.3	925.6
140°	967.3	967.4	967.4	967.4	967.4	967.4	967.3	966.8	966.3	965.8	965.4
142.5°	1003.0	1003.0	1003.2	1003.4	1003.6	1003.7	1003.6	1003.1	1002.7	1002.2	1001.8
145°	1057.1	1057.4	1057.1	1056.9	1056.6	1056.4	1055.8	1054.9	1053.9	1053.0	1052.1
147.5°	1106.0	1106.2	1106.4	1106.6	1106.8	1106.9	1106.4	1105.4	1104.2	1103.1	1102.0
150°	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.2	1135.2	1134.3	1133.3	1132.5
152.5°	1165.1	1164.6	1164.4	1164.2	1164.0	1163.8	1163.4	1162.9	1162.3	1161.7	1161.1
155°	1205.3	1204.4	1204.5	1204.8	1205.0	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3
157.5°	1241.2	1240.5	1240.6	1240.6	1240.6	1240.6	1240.9	1241.3	1241.8	1242.2	1242.6
160°	1263.1	1262.5	1262.7	1263.0	1263.1	1263.4	1263.6	1263.9	1264.1	1264.4	1264.6
162.5°	1282.4	1281.1	1281.3	1281.6	1281.8	1282.1	1282.5	1283.0	1283.7	1284.3	1284.9
165°	1308.3	1306.8	1307.3	1307.8	1308.3	1308.8	1309.4	1310.0	1310.8	1311.5	1312.1
167.5°	1330.3	1328.9	1328.9	1328.8	1328.8	1328.7	1329.2	1330.2	1331.1	1332.1	1333.1
170°	1342.1	1340.7	1340.5	1340.3	1340.0	1339.8	1340.3	1341.4	1342.6	1343.8	1344.9
172.5°	1350.8	1349.2	1349.2	1349.1	1349.1	1349.0	1349.5	1350.5	1351.4	1352.4	1353.4
175°	1360.3	1358.7	1358.9	1359.2	1359.4	1359.6	1360.3	1361.5	1362.7	1363.8	1365.1
177.5°	1366.0	1364.6	1364.6	1364.6	1364.6	1364.6	1365.1	1366.0	1366.9	1367.9	1368.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	468.9	470.4	472.5	475.8	477.0	478.6	480.8	480.6	481.2	483.6	488.4
5°	470.6	476.6	482.4	489.3	496.7	501.5	508.0	512.1	516.2	521.4	530.3
7.5°	471.3	480.8	491.4	503.6	514.5	526.9	536.7	545.9	554.2	565.2	575.8
10°	470.3	483.0	496.7	512.1	528.5	542.4	555.0	569.2	581.4	594.7	606.7
12.5°	468.2	483.6	501.9	519.2	538.3	558.9	574.5	589.0	605.1	620.4	639.0
15°	463.7	484.7	506.1	528.9	554.6	578.3	600.9	619.5	636.9	659.9	684.0
17.5°	457.9	480.5	507.6	535.2	562.0	589.1	617.0	645.1	667.1	695.6	714.4
20°	452.5	478.7	506.5	539.3	566.1	599.9	627.7	654.8	685.0	713.4	736.0
22.5°	444.9	473.6	503.1	535.7	571.0	604.9	636.9	666.4	696.6	727.4	754.7
25°	435.3	461.4	496.3	533.3	568.4	605.1	642.0	679.0	711.4	744.0	769.5
27.5°	419.0	451.8	484.4	522.6	561.6	603.1	642.5	681.3	715.3	742.1	757.8
30°	410.6	439.2	474.5	512.9	555.1	599.7	640.8	678.8	710.5	731.9	738.3
32.5°	398.3	427.7	462.3	502.1	546.8	592.6	635.4	671.2	697.7	708.9	701.2
35°	379.9	406.6	441.5	482.2	528.7	577.5	619.8	650.0	663.6	653.0	626.6
37.5°	357.9	384.3	419.4	459.4	507.5	557.2	595.3	617.2	612.7	586.3	546.9
40°	342.5	367.2	400.6	443.8	490.6	540.5	574.1	585.8	573.5	535.7	493.7
42.5°	325.4	349.4	382.9	424.7	474.3	520.2	549.5	550.5	529.8	484.5	442.5
45°	299.3	322.2	353.8	397.3	443.2	486.4	505.7	496.3	458.0	414.5	372.2
47.5°	273.5	293.4	324.7	365.8	409.4	445.8	455.4	438.4	397.7	355.3	316.2
50°	254.7	274.8	304.1	343.5	385.6	416.9	421.6	399.0	359.1	316.4	285.8
52.5°	236.6	256.6	284.8	321.2	359.7	388.1	388.2	362.2	322.4	284.4	255.8
55°	210.1	228.0	253.6	286.2	320.5	342.7	337.3	310.3	275.7	242.7	217.8
57.5°	184.6	200.2	223.6	250.9	281.1	299.5	290.5	264.5	233.7	205.6	186.8
60°	168.0	183.0	203.0	228.7	254.1	268.4	259.9	236.4	208.0	185.4	169.0
62.5°	152.0	164.5	183.8	206.1	229.8	240.3	232.8	209.5	185.0	164.6	151.2
65°	129.3	139.5	154.9	174.1	191.2	200.3	194.0	172.3	153.6	138.9	128.3
67.5°	108.0	116.0	127.8	143.1	157.7	162.6	156.8	141.7	125.9	114.1	106.6
70°	93.4	100.9	110.7	122.5	135.3	140.5	134.7	122.7	109.8	99.0	91.6
72.5°	80.6	86.4	94.7	104.8	114.7	119.9	116.0	104.5	93.6	85.5	79.3
75°	61.4	66.4	72.2	79.3	87.0	90.5	87.0	79.1	71.6	65.6	61.1
77.5°	44.6	47.3	51.8	57.2	62.0	64.6	61.6	56.3	51.6	47.5	45.3
80°	34.0	35.9	39.0	43.2	46.5	49.0	47.0	42.6	39.0	36.3	35.3
82.5°	24.7	26.0	28.0	31.1	33.3	34.7	33.8	30.6	29.1	26.7	25.8
85°	12.1	13.0	14.3	15.2	17.2	17.4	17.5	16.2	14.8	14.3	13.5
87.5°	5.3	6.0	6.9	8.0	9.0	9.5	9.8	10.1	9.9	10.0	9.7
90°	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1
92.5°	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7	43.5
95°	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0	81.8
97.5°	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9	128.8
100°	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2	162.7
102.5°	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0	198.6
105°	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3	253.1
107.5°	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3	311.9
110°	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6	351.1





TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5	393.4
115°	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7	458.4
117.5°	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7	521.0
120°	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5	563.4
122.5°	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2	606.3
125°	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8	669.4
127.5°	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2	729.7
130°	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4	772.0
132.5°	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2	811.7
135°	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9	871.4
137.5°	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6	929.0
140°	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3	967.0
142.5°	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0	1002.9
145°	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1	1056.9
147.5°	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0	1105.8
150°	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1	1165.7
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3	1206.2
157.5°	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2	1241.9
160°	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1	1263.9
162.5°	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4	1283.6
165°	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3	1309.7
167.5°	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3	1331.7
170°	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1	1343.5
172.5°	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8	1352.3
175°	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3	1362.0
177.5°	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0	1367.3
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	465.8	465.8	465.8	465.8	465.8	465.8	465.8
2.5°	491.0	491.3	492.7	493.7	494.1	495.6	495.7
5°	534.1	537.4	543.7	544.3	545.3	550.3	546.4
7.5°	584.7	593.0	598.5	603.5	605.2	607.4	607.0
10°	617.1	629.4	635.6	645.5	645.8	648.3	646.8
12.5°	649.6	664.0	675.2	677.1	685.3	686.6	688.8
15°	695.8	711.0	726.7	732.3	743.6	746.3	750.6
17.5°	739.2	754.7	765.7	780.2	784.9	791.1	786.8
20°	763.0	779.9	793.9	805.2	810.0	813.5	813.1
22.5°	777.3	794.4	805.7	814.3	818.8	820.3	820.2
25°	786.3	796.1	799.6	802.9	797.9	796.1	796.9
27.5°	761.2	758.7	749.7	737.8	725.5	715.7	710.3
30°	726.8	711.8	698.1	674.2	661.9	654.5	647.9
32.5°	678.1	654.2	627.9	605.9	591.9	581.1	579.4
35°	594.5	558.6	526.4	499.5	485.7	473.9	471.2
37.5°	505.4	468.1	439.1	415.5	400.6	392.2	384.5
40°	446.3	414.3	385.7	365.7	354.2	348.3	343.5
42.5°	400.8	371.5	343.1	327.8	317.6	313.9	311.0
45°	337.9	310.6	291.0	279.4	273.5	267.3	264.3
47.5°	287.5	265.4	252.4	242.6	236.1	232.4	230.6
50°	258.9	240.8	229.3	221.7	215.9	213.0	211.5
52.5°	233.7	218.7	209.0	203.0	199.1	197.0	196.3
55°	201.2	189.9	183.7	178.5	175.6	173.7	172.9
57.5°	175.0	166.2	161.2	156.9	155.7	154.2	153.6
60°	157.7	150.9	146.7	143.7	142.8	140.9	141.2
62.5°	142.4	136.8	133.2	131.6	130.3	128.7	129.2
65°	120.4	116.3	114.4	112.9	111.4	110.4	111.1
67.5°	101.0	98.2	95.6	94.7	94.0	93.8	93.0
70°	88.4	86.1	83.7	83.2	83.2	82.4	82.2
72.5°	76.1	74.5	73.0	72.5	71.9	72.2	71.4
75°	58.9	57.5	56.9	56.3	56.2	56.2	55.6
77.5°	43.5	42.5	41.6	41.6	40.8	40.6	40.5
80°	33.0	32.6	31.9	31.9	31.5	31.6	31.2
82.5°	24.8	24.3	24.1	23.8	23.2	23.3	22.9
85°	13.3	12.7	12.6	12.0	11.6	12.0	11.6
87.5°	10.1	10.3	10.3	10.1	10.0	10.1	9.7
90°	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	350.7	350.3	350.3	351.1	351.7	352.5	353.2



TEST NUMBER: P332734-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)