

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332737-930

Luminaire Tested: **S124DIW-S350D1340U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332737-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1340U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5613.5 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	92	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	26	19
2	83	76	70	65	74	68	63	59	52	49	46	37	35	33	24	22	22	16
3	76	67	60	54	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	19	17	16	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	26	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7
9	46	35	27	23	41	31	25	21	24	20	16	18	15	12	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	0.8
10°-20°	127.8	2.3
20°-30°	188.1	3.4
30°-40°	218.7	3.9
40°-50°	218.7	3.9
50°-60°	191.3	3.4
60°-70°	142.1	2.5
70°-80°	80.7	1.4
80°-90°	27.4	0.5
90°-100°	48.4	0.9
100°-110°	308.3	5.5
110°-120°	589.8	10.5
120°-130°	748.7	13.3
130°-140°	801.1	14.3
140°-150°	749.1	13.3
150°-160°	604.1	10.8
160°-170°	389.6	6.9
170°-180°	134.3	2.4
0°-30°	361.2	6.4
0°-40°	579.9	10.3
0°-60°	989.8	17.6
0°-90°	1240.0	22.1
90°-120°	946.5	16.9
90°-150°	3245.5	57.8
90°-180°	4374.0	77.9
0°-180°	5613.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	3	15	23	29	32	4
95°	58	24	23	29	31	75
105°	318	325	330	337	301	333
115°	594	597	596	598	598	585
125°	835	839	838	841	842	746
135°	1036	1036	1040	1042	1044	798
145°	1195	1198	1198	1199	1201	746
155°	1310	1311	1308	1312	1309	604
165°	1382	1377	1377	1384	1376	390
175°	1414	1408	1409	1417	1405	135
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.6	9.1	9.5	10.0	10.4	10.8	11.2	11.4	11.7	12.1	12.3
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	13.3	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8
95°	58.1	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7
97.5°	123.5	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0
100°	173.4	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6
102.5°	229.3	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1
105°	318.3	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1
107.5°	401.0	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4
110°	456.8	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8



TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.9	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6
115°	594.3	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9
117.5°	669.4	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9
120°	720.2	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8
122.5°	767.5	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8
125°	835.4	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2
127.5°	899.7	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5
130°	941.2	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7
132.5°	979.3	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4
135°	1036.3	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0
137.5°	1086.9	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5
140°	1119.9	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8
142.5°	1149.5	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1
145°	1195.0	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4
147.5°	1231.1	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2
150°	1257.4	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5
152.5°	1279.4	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2
155°	1310.3	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0
157.5°	1336.3	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3
160°	1351.4	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7
162.5°	1365.0	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3
165°	1382.2	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8
167.5°	1395.7	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6
170°	1403.3	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9
172.5°	1408.3	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9
175°	1413.9	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7
177.5°	1416.4	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	12.6	12.9	13.2	13.4	13.5	13.5	13.7	13.8
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	25.3	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	26.1	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.2	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	38.6	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	138.0	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	334.2	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	413.4	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.3	467.7	468.2	468.8	469.5	470.3	470.9	471.7



TEST NUMBER: P332737-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.4	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.4	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.7	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.1	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	838.9	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.4	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	945.8	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.6	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.5	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.0	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1125.5	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1155.6	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.6	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.4	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1281.6	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.0	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1362.8	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1380.6	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1393.7	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1401.7	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1406.8	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1412.8	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1415.2	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)