

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332738-930

Luminaire Tested: **S124DIW-S350D1340U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332738-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S350D1340U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5033.0 lumens  
Efficiency: N/A  
Efficacy: 108.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	25
1	92	88	84	81	82	78	75	72	60	58	57	44	43	42	29	28	28	21
2	84	77	71	66	74	68	63	59	53	50	47	39	37	35	25	24	23	17
3	76	67	60	55	68	60	54	49	47	43	39	34	31	29	22	21	20	15
4	70	59	52	46	62	53	47	42	41	37	33	30	27	25	20	18	17	13
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15	11
6	59	47	39	34	52	42	36	31	33	28	25	24	21	19	16	14	13	10
7	54	42	35	29	48	38	32	27	30	25	22	22	19	16	15	13	11	9
8	50	38	31	26	45	34	28	24	27	22	19	20	17	15	14	12	10	8
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	13	11	9	7
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.4	0.9
10°-20°	127.8	2.5
20°-30°	188.1	3.7
30°-40°	218.7	4.3
40°-50°	218.7	4.3
50°-60°	191.3	3.8
60°-70°	142.1	2.8
70°-80°	80.7	1.6
80°-90°	27.4	0.5
90°-100°	90.2	1.8
100°-110°	267.1	5.3
110°-120°	453.4	9.0
120°-130°	597.8	11.9
130°-140°	671.4	13.3
140°-150°	659.8	13.1
150°-160°	554.9	11.0
160°-170°	369.2	7.3
170°-180°	129.3	2.6
0°-30°	361.2	7.2
0°-40°	579.9	11.5
0°-60°	989.8	19.7
0°-90°	1240.0	24.6
90°-120°	810.7	16.1
90°-150°	2739.7	54.4
90°-180°	3793.0	75.4
0°-180°	5033.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	3	15	23	29	32	5
95°	63	73	80	83	84	71
105°	246	248	252	255	258	261
115°	461	461	459	458	457	454
125°	671	671	670	668	666	598
135°	866	872	872	870	867	670
145°	1052	1056	1057	1056	1053	658
155°	1205	1205	1204	1208	1204	554
165°	1312	1309	1307	1313	1309	370
175°	1365	1360	1359	1365	1359	130
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.6	9.1	9.5	10.0	10.4	10.8	11.2	11.4	11.7	12.1	12.3
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	22.7	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7
95°	63.4	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0
97.5°	110.8	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9
100°	148.1	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2
102.5°	186.9	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0
105°	246.4	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3
107.5°	308.8	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3
110°	351.1	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6



TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.0	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5
115°	461.0	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7
117.5°	523.2	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7
120°	564.6	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5
122.5°	607.7	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2
125°	671.4	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8
127.5°	729.1	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2
130°	769.7	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4
132.5°	811.2	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2
135°	865.9	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9
137.5°	925.6	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6
140°	965.4	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3
142.5°	1001.8	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0
145°	1052.1	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1102.0	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0
150°	1132.5	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.1	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3
157.5°	1242.6	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2
160°	1264.6	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1
162.5°	1284.9	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4
165°	1312.1	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3
167.5°	1333.1	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3
170°	1344.9	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1
172.5°	1353.4	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8
175°	1365.1	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3
177.5°	1368.8	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	12.6	12.9	13.2	13.4	13.5	13.5	13.7	13.8
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	43.5	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	81.8	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	128.8	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	162.7	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	198.6	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.1	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	311.9	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	351.1	350.7	350.3	350.3	351.1	351.7	352.5	353.2





TEST NUMBER: P332738-930

CATALOG NUMBER: S124DIW-S350D1340U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	393.4	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.4	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	521.0	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	563.4	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	606.3	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.4	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.7	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	772.0	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.7	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	871.4	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	929.0	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	967.0	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.9	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.8	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1165.7	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1241.9	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1263.9	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1283.6	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1309.7	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1331.7	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1343.5	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1352.3	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1367.3	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)