

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332743-930

Luminaire Tested: **S124DIW-S350D1560U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332743-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S350D1560U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6325.6 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	47	47	47	28	28	28	20
1	91	87	83	80	80	77	74	71	58	56	54	41	40	38	25	24	24	16
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14
3	75	66	60	54	66	59	53	48	45	41	38	32	29	27	19	18	17	12
4	69	59	51	45	61	52	46	41	40	35	32	28	25	23	17	16	15	10
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9
6	58	46	39	33	51	41	35	30	32	27	24	23	20	17	14	12	11	8
7	53	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7
8	49	38	30	25	44	34	27	23	26	21	18	19	16	13	12	10	9	6
9	46	34	27	22	40	31	24	20	24	19	16	17	14	12	11	9	8	5
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3888	3888	3888
5°	3900	3853	3881
10°	3875	3822	3841
15°	3828	3768	3777
20°	3766	3699	3703
25°	3695	3624	3613
30°	3608	3533	3500
35°	3517	3438	3392
40°	3424	3331	3270
45°	3327	3225	3164
50°	3218	3131	3034
55°	3102	3009	2911
60°	2984	2872	2785
65°	2854	2743	2632
70°	2705	2568	2469
75°	2480	2361	2299
80°	2208	2120	2064
85°	1936	1862	1815



TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	0.7
10°-20°	127.8	2.0
20°-30°	188.1	3.0
30°-40°	218.7	3.5
40°-50°	218.7	3.5
50°-60°	191.3	3.0
60°-70°	142.1	2.2
70°-80°	80.7	1.3
80°-90°	28.0	0.4
90°-100°	56.2	0.9
100°-110°	358.5	5.7
110°-120°	685.8	10.8
120°-130°	870.5	13.8
130°-140°	931.4	14.7
140°-150°	871.0	13.8
150°-160°	702.4	11.1
160°-170°	453.0	7.2
170°-180°	156.1	2.5
0°-30°	361.2	5.7
0°-40°	579.9	9.2
0°-60°	989.8	15.6
0°-90°	1240.6	19.6
90°-120°	1100.5	17.4
90°-150°	3773.4	59.7
90°-180°	5085.0	80.4
0°-180°	6325.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	482	482	482	482	482	
5°	481	480	475	479	479	46
15°	458	456	451	453	452	129
25°	415	412	407	407	406	191
35°	357	354	349	346	344	223
45°	291	288	282	278	277	225
55°	220	219	214	209	207	197
65°	149	147	144	140	138	148
75°	80	78	76	74	74	84
85°	21	21	20	20	20	23
90°	4	17	27	34	37	4
95°	68	28	27	34	36	87
105°	370	377	384	392	350	387
115°	691	694	693	696	696	680
125°	971	976	974	977	979	867
135°	1205	1204	1209	1211	1214	928
145°	1389	1393	1393	1394	1397	868
155°	1523	1524	1521	1525	1522	702
165°	1607	1601	1601	1610	1600	454
175°	1644	1637	1638	1647	1634	156
180°	1644	1644	1644	1644	1644	



TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	482.8	482.7	482.4	482.2	482.0	481.5	480.8	480.0	479.3	478.5	479.2
5°	481.2	480.9	480.5	480.2	479.9	479.2	478.3	477.4	476.4	475.4	476.4
7.5°	476.8	476.4	476.1	475.7	475.4	474.7	473.6	472.6	471.6	470.5	471.2
10°	472.7	472.4	472.1	471.7	471.4	470.7	469.5	468.4	467.3	466.2	466.8
12.5°	467.5	467.2	466.8	466.4	466.1	465.4	464.1	463.0	461.8	460.6	461.4
15°	458.0	457.7	457.4	457.1	456.7	455.9	454.6	453.3	452.0	450.8	451.3
17.5°	446.7	446.3	445.9	445.5	445.0	444.2	443.0	441.7	440.5	439.3	439.6
20°	438.4	438.0	437.6	437.1	436.7	435.9	434.6	433.3	431.9	430.6	431.0
22.5°	429.4	428.8	428.3	427.7	427.1	426.2	424.9	423.7	422.4	421.1	421.6
25°	414.8	414.3	413.7	413.0	412.5	411.6	410.3	409.1	408.0	406.8	406.8
27.5°	398.2	397.5	397.0	396.3	395.7	394.8	393.7	392.6	391.5	390.4	390.2
30°	387.1	386.4	385.7	385.0	384.3	383.4	382.3	381.2	380.1	379.0	378.6
32.5°	375.4	374.7	374.1	373.5	372.8	371.9	370.8	369.6	368.4	367.2	366.8
35°	356.9	356.4	355.8	355.1	354.6	353.7	352.5	351.2	350.1	348.9	348.3
37.5°	337.6	337.0	336.5	336.0	335.4	334.5	333.2	331.9	330.6	329.3	328.6
40°	324.9	324.2	323.6	322.9	322.2	321.2	319.9	318.6	317.3	316.1	315.2
42.5°	311.4	311.0	310.5	310.1	309.7	308.8	307.4	305.9	304.5	303.1	302.1
45°	291.4	290.7	290.2	289.6	288.9	288.0	286.6	285.2	283.9	282.5	281.5
47.5°	270.4	270.0	269.6	269.2	268.8	268.0	266.7	265.4	264.2	262.9	261.8
50°	256.2	255.9	255.6	255.2	254.9	254.1	252.9	251.7	250.5	249.3	248.1
52.5°	242.4	241.9	241.5	241.1	240.7	239.9	238.6	237.3	236.0	234.8	233.7
55°	220.4	220.1	219.8	219.6	219.3	218.6	217.4	216.2	215.0	213.8	212.8
57.5°	199.3	199.1	198.8	198.5	198.2	197.5	196.2	195.1	193.9	192.7	191.8
60°	184.8	184.4	184.0	183.5	183.1	182.4	181.2	180.1	179.0	177.9	177.2
62.5°	170.6	170.3	169.9	169.6	169.2	168.4	167.2	166.1	164.9	163.7	163.0
65°	149.4	149.0	148.5	148.1	147.7	147.0	146.1	145.3	144.4	143.6	142.7
67.5°	127.9	127.5	127.1	126.7	126.3	125.7	124.9	124.1	123.3	122.4	121.6
70°	114.6	114.0	113.4	112.8	112.2	111.5	110.9	110.2	109.5	108.8	108.1
72.5°	100.4	99.8	99.2	98.7	98.0	97.4	96.9	96.4	95.8	95.2	94.7
75°	79.5	79.1	78.7	78.2	77.8	77.4	77.0	76.5	76.1	75.7	75.3
77.5°	59.5	59.4	59.1	58.9	58.8	58.5	58.1	57.7	57.3	57.0	56.8
80°	47.5	47.2	47.0	46.7	46.5	46.2	46.1	45.9	45.7	45.6	45.3
82.5°	35.7	35.6	35.5	35.4	35.2	35.1	35.1	35.1	35.1	35.1	35.0
85°	20.9	20.9	20.9	20.9	20.9	20.8	20.5	20.4	20.2	20.1	20.1
87.5°	8.8	9.3	9.9	10.4	10.9	11.3	11.7	12.1	12.5	12.8	13.1
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	15.5	15.7	15.8	16.0	16.1	17.3	19.5	21.7	23.9	26.1	27.7
95°	67.6	58.3	49.1	39.8	30.5	25.9	26.3	26.5	26.7	27.1	28.7
97.5°	143.6	149.4	155.2	161.0	166.8	154.4	123.9	93.4	62.9	32.4	32.6
100°	201.6	206.6	211.5	216.4	221.3	204.9	167.2	129.5	91.8	54.1	49.5
102.5°	266.5	270.2	273.8	277.4	281.0	280.3	275.4	270.5	265.5	260.7	210.5
105°	370.1	371.7	373.3	375.0	376.7	378.1	379.5	380.9	382.2	383.6	386.0
107.5°	466.2	467.1	467.9	468.7	469.5	470.8	472.7	474.6	476.4	478.3	479.5
110°	531.2	532.0	532.8	533.6	534.4	535.7	537.3	538.9	540.5	542.2	542.7



TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	594.1	595.6	597.0	598.5	600.0	601.1	601.9	602.7	603.4	604.2	604.1
115°	691.0	691.8	692.6	693.4	694.2	694.6	694.2	694.0	693.7	693.4	694.0
117.5°	778.3	779.3	780.5	781.5	782.7	783.5	784.1	784.7	785.3	785.9	785.8
120°	837.3	838.4	839.5	840.6	841.6	842.0	841.8	841.6	841.2	841.0	841.6
122.5°	892.3	893.0	893.6	894.3	895.0	895.5	895.9	896.3	896.7	897.1	897.4
125°	971.3	972.4	973.5	974.6	975.7	975.9	975.4	974.9	974.3	973.8	974.6
127.5°	1046.0	1046.4	1046.6	1046.8	1047.2	1047.9	1049.2	1050.4	1051.7	1053.0	1052.8
130°	1094.3	1094.5	1094.8	1095.1	1095.4	1095.9	1096.7	1097.6	1098.4	1099.2	1099.4
132.5°	1138.5	1139.0	1139.5	1140.0	1140.5	1141.3	1142.3	1143.3	1144.4	1145.4	1145.7
135°	1204.9	1204.6	1204.4	1204.1	1203.8	1204.2	1205.3	1206.4	1207.5	1208.6	1209.2
137.5°	1263.7	1263.8	1263.9	1264.0	1264.1	1264.8	1266.0	1267.2	1268.4	1269.6	1270.2
140°	1302.0	1302.6	1303.2	1303.7	1304.2	1304.8	1305.3	1305.9	1306.4	1306.9	1307.8
142.5°	1336.4	1337.4	1338.5	1339.5	1340.4	1341.1	1341.4	1341.7	1342.1	1342.4	1343.0
145°	1389.4	1390.2	1391.0	1391.8	1392.6	1393.0	1393.0	1393.0	1393.0	1393.0	1393.3
147.5°	1431.4	1432.9	1434.4	1436.0	1437.5	1438.1	1437.9	1437.6	1437.3	1437.0	1437.3
150°	1461.9	1463.0	1464.0	1465.2	1466.2	1466.6	1466.4	1466.2	1465.8	1465.6	1465.6
152.5°	1487.4	1488.3	1489.2	1490.0	1490.9	1491.2	1490.6	1490.1	1489.6	1489.1	1489.6
155°	1523.4	1523.6	1523.9	1524.2	1524.4	1524.2	1523.4	1522.6	1521.8	1520.9	1522.0
157.5°	1553.6	1553.5	1553.3	1553.1	1553.0	1552.4	1551.4	1550.5	1549.6	1548.7	1550.1
160°	1571.3	1570.5	1569.7	1568.9	1568.1	1567.5	1567.2	1566.9	1566.7	1566.4	1568.1
162.5°	1587.1	1586.0	1584.9	1584.0	1582.9	1582.3	1581.9	1581.7	1581.4	1581.1	1582.7
165°	1607.0	1605.6	1604.3	1602.9	1601.5	1600.8	1600.8	1600.8	1600.8	1600.8	1603.0
167.5°	1622.7	1621.3	1619.8	1618.5	1617.0	1616.2	1616.1	1615.9	1615.8	1615.6	1618.0
170°	1631.6	1629.9	1628.2	1626.6	1625.0	1624.3	1624.6	1624.9	1625.1	1625.4	1627.6
172.5°	1637.4	1635.8	1634.2	1632.6	1630.9	1630.2	1630.5	1630.8	1631.0	1631.3	1633.5
175°	1643.8	1642.2	1640.5	1638.9	1637.3	1636.6	1636.9	1637.1	1637.4	1637.7	1640.1
177.5°	1646.8	1645.3	1643.7	1642.2	1640.7	1640.1	1640.5	1641.0	1641.4	1641.8	1643.6
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8



TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6
2.5°	479.9	480.6	481.3	481.6	481.5	481.4	481.4	481.3
5°	477.4	478.3	479.2	479.6	479.4	479.2	479.1	478.9
7.5°	472.0	472.8	473.5	473.9	473.8	473.6	473.5	473.4
10°	467.6	468.2	469.0	469.2	469.0	468.8	468.6	468.5
12.5°	462.1	462.8	463.7	463.9	463.7	463.4	463.2	462.9
15°	451.8	452.2	452.8	452.9	452.7	452.4	452.2	451.9
17.5°	439.9	440.3	440.6	440.7	440.5	440.3	440.2	440.0
20°	431.2	431.5	431.7	431.8	431.5	431.4	431.2	431.0
22.5°	422.0	422.5	423.0	423.1	422.7	422.4	422.1	421.8
25°	406.9	407.0	407.1	407.0	406.6	406.3	405.9	405.6
27.5°	390.0	389.8	389.6	389.2	388.8	388.4	387.9	387.5
30°	378.3	378.0	377.6	377.2	376.7	376.3	375.9	375.5
32.5°	366.4	366.0	365.6	365.2	364.8	364.3	363.9	363.5
35°	347.6	347.1	346.4	345.9	345.5	345.1	344.6	344.2
37.5°	328.0	327.3	326.7	326.1	325.5	325.0	324.4	323.8
40°	314.4	313.5	312.7	312.0	311.5	311.1	310.7	310.3
42.5°	301.1	300.1	299.1	298.5	298.2	297.9	297.6	297.3
45°	280.6	279.6	278.8	278.1	277.9	277.6	277.4	277.1
47.5°	260.7	259.7	258.6	257.8	257.1	256.5	255.8	255.2
50°	246.9	245.7	244.5	243.6	243.1	242.6	242.1	241.6
52.5°	232.7	231.6	230.6	229.7	229.0	228.4	227.7	227.1
55°	211.7	210.7	209.7	208.9	208.4	207.9	207.3	206.8
57.5°	190.8	189.8	188.8	188.1	187.6	187.1	186.6	186.1
60°	176.3	175.6	174.8	174.2	173.8	173.3	172.9	172.5
62.5°	162.3	161.6	160.9	160.3	159.9	159.5	159.1	158.6
65°	141.9	141.0	140.1	139.5	139.1	138.6	138.2	137.8
67.5°	120.7	119.9	119.1	118.6	118.5	118.4	118.3	118.1
70°	107.5	106.8	106.1	105.6	105.3	105.1	104.8	104.6
72.5°	94.2	93.6	93.0	92.6	92.4	92.1	91.9	91.6
75°	74.9	74.6	74.3	74.0	73.9	73.9	73.8	73.7
77.5°	56.7	56.7	56.6	56.4	56.2	55.9	55.7	55.5
80°	45.2	45.0	44.8	44.8	44.6	44.5	44.4	44.4
82.5°	34.8	34.7	34.7	34.6	34.5	34.3	34.2	34.2
85°	20.1	20.1	20.1	20.1	20.0	19.9	19.7	19.6
87.5°	13.5	13.8	14.1	14.3	14.4	14.6	14.7	14.8
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	29.4	31.0	32.6	33.5	33.6	33.8	33.8	33.9
95°	30.3	32.0	33.6	34.6	34.8	35.1	35.4	35.6
97.5°	32.8	32.9	33.1	33.3	33.6	33.9	34.2	34.4
100°	44.8	40.2	35.5	33.3	33.6	33.9	34.2	34.4
102.5°	160.5	110.3	60.3	35.2	35.2	35.3	35.4	35.4
105°	388.5	391.0	393.5	389.7	379.9	370.1	360.3	350.4
107.5°	480.7	481.9	483.1	484.2	485.3	486.2	487.3	488.4
110°	543.3	543.9	544.4	545.1	545.9	546.7	547.6	548.4



TEST NUMBER: P332743-930

CATALOG NUMBER: S124DIW-S350D1560U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	604.0	603.8	603.7	604.2	605.3	606.3	607.3	608.4
115°	694.6	695.0	695.6	695.9	695.9	695.9	695.9	695.9
117.5°	785.7	785.5	785.5	785.4	785.2	785.1	785.1	784.9
120°	842.0	842.6	843.2	843.2	842.6	842.0	841.6	841.0
122.5°	897.7	898.1	898.4	898.2	897.7	897.2	896.6	896.1
125°	975.4	976.2	977.1	977.6	977.9	978.1	978.4	978.7
127.5°	1052.6	1052.5	1052.3	1052.1	1051.9	1051.7	1051.4	1051.2
130°	1099.8	1100.0	1100.2	1100.4	1100.4	1100.4	1100.4	1100.4
132.5°	1146.0	1146.2	1146.5	1146.6	1146.3	1146.1	1145.9	1145.7
135°	1209.7	1210.2	1210.8	1211.4	1211.9	1212.4	1213.0	1213.5
137.5°	1270.8	1271.4	1272.0	1272.2	1272.0	1271.9	1271.7	1271.5
140°	1308.6	1309.5	1310.3	1310.8	1311.1	1311.3	1311.6	1311.9
142.5°	1343.6	1344.2	1344.8	1345.1	1345.2	1345.2	1345.2	1345.3
145°	1393.6	1393.8	1394.1	1394.6	1395.1	1395.6	1396.2	1396.7
147.5°	1437.5	1437.7	1437.9	1438.2	1438.4	1438.7	1439.0	1439.2
150°	1465.6	1465.6	1465.6	1465.7	1466.0	1466.2	1466.6	1466.8
152.5°	1490.0	1490.4	1490.9	1491.0	1490.9	1490.7	1490.5	1490.4
155°	1523.1	1524.2	1525.3	1525.4	1524.6	1523.8	1523.0	1522.2
157.5°	1551.5	1553.0	1554.4	1554.4	1553.0	1551.5	1550.1	1548.7
160°	1569.7	1571.3	1573.0	1573.0	1571.3	1569.7	1568.1	1566.4
162.5°	1584.5	1586.1	1587.7	1587.6	1585.8	1583.9	1582.0	1580.1
165°	1605.2	1607.4	1609.6	1609.4	1607.0	1604.5	1602.1	1599.6
167.5°	1620.4	1622.8	1625.2	1625.1	1622.3	1619.6	1616.8	1614.1
170°	1629.8	1632.0	1634.2	1633.9	1631.2	1628.4	1625.7	1622.9
172.5°	1635.7	1637.9	1640.1	1639.6	1636.7	1633.8	1630.8	1627.8
175°	1642.6	1645.1	1647.6	1647.1	1643.8	1640.5	1637.3	1634.0
177.5°	1645.4	1647.1	1648.9	1648.5	1645.8	1643.2	1640.5	1637.9
180°	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8	1643.8

(END OF REPORT)