

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332437-940

Luminaire Tested: **S123RDIW-S775D755U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332437-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S775D755U940-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4937.7 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	95	91	87	91	88	84	82	75	73	70	63	62	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	46	45	43	38
3	82	73	66	60	76	68	62	57	59	54	50	50	46	43	41	39	37	33
4	76	65	57	51	70	61	54	48	52	47	43	44	40	37	37	34	32	28
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25
6	64	52	44	38	59	49	42	36	42	37	33	36	32	29	31	27	25	22
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22	20
8	55	43	35	30	51	40	33	29	35	30	26	30	26	23	26	22	20	18
9	51	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	16	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12392	12392	12392
5°	12440	12268	12338
10°	12369	12114	12073
15°	12237	11830	11705
20°	12054	11475	11208
25°	11866	11077	10723
30°	11616	10618	10038
35°	11361	10159	9410
40°	11126	9617	8633
45°	10816	9082	7931
50°	10474	8473	7145
55°	10128	7781	6412
60°	9810	7035	5608
65°	9393	6230	4804
70°	8875	5231	3877
75°	8114	4117	3647
80°	7234	3651	3353
85°	6113	3223	3001



TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.1	2.2
10°-20°	300.8	6.1
20°-30°	433.1	8.8
30°-40°	487.9	9.9
40°-50°	466.7	9.5
50°-60°	382.2	7.7
60°-70°	257.9	5.2
70°-80°	129.7	2.6
80°-90°	36.8	0.7
90°-100°	54.9	1.1
100°-110°	164.3	3.3
110°-120°	279.4	5.7
120°-130°	367.5	7.4
130°-140°	413.1	8.4
140°-150°	406.1	8.2
150°-160°	341.9	6.9
160°-170°	227.6	4.6
170°-180°	79.7	1.6
0°-30°	842.0	17.1
0°-40°	1329.9	26.9
0°-60°	2178.8	44.1
0°-90°	2603.3	52.7
90°-120°	498.6	10.1
90°-150°	1685.3	34.1
90°-180°	2334.0	47.3
0°-180°	4937.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1151	1151	1151	1151	1151	
5°	1151	1146	1135	1143	1142	109
15°	1098	1087	1062	1057	1050	309
25°	999	975	933	914	903	459
35°	865	830	773	734	716	541
45°	710	667	597	545	521	548
55°	540	492	415	362	342	484
65°	369	316	245	201	189	365
75°	195	150	99	90	88	208
85°	50	30	26	24	24	56
90°	1	7	16	18	20	5
95°	39	44	49	52	52	44
105°	149	150	156	156	158	159
115°	281	283	282	283	282	278
125°	412	414	412	410	407	367
135°	534	538	537	535	533	411
145°	648	649	651	650	648	405
155°	742	742	743	745	741	341
165°	808	806	806	810	806	228
175°	840	838	838	841	837	80
180°	843	843	843	843	843	



TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1154.9	1154.3	1153.6	1153.0	1152.4	1151.0	1149.0	1147.0	1145.0	1143.0	1144.9
5°	1151.3	1150.2	1149.1	1148.2	1147.1	1145.3	1142.8	1140.3	1137.8	1135.4	1137.2
7.5°	1140.6	1139.5	1138.4	1137.2	1136.1	1133.9	1130.7	1127.5	1124.3	1121.0	1122.0
10°	1131.7	1130.2	1128.7	1127.3	1125.8	1123.2	1119.5	1115.8	1112.1	1108.3	1108.5
12.5°	1118.9	1117.3	1115.7	1114.1	1112.5	1109.4	1104.8	1100.3	1095.6	1091.1	1091.0
15°	1098.1	1095.7	1093.4	1091.2	1088.9	1084.9	1079.1	1073.3	1067.4	1061.6	1060.6
17.5°	1071.7	1069.1	1066.4	1063.7	1061.0	1056.1	1048.7	1041.3	1033.8	1026.5	1024.3
20°	1052.3	1048.9	1045.6	1042.3	1039.0	1033.4	1025.5	1017.6	1009.8	1001.8	999.2
22.5°	1030.6	1026.8	1023.0	1019.1	1015.3	1009.2	1000.9	992.5	984.1	975.7	972.3
25°	999.1	993.9	988.6	983.5	978.3	970.9	961.4	951.8	942.3	932.7	928.4
27.5°	960.7	955.0	949.3	943.6	937.9	929.7	919.1	908.5	897.8	887.2	881.1
30°	934.6	928.4	922.2	916.0	909.7	900.8	889.2	877.5	865.9	854.3	847.3
32.5°	908.5	901.4	894.4	887.3	880.3	870.6	858.3	846.1	833.7	821.4	813.8
35°	864.6	857.1	849.6	842.2	834.7	824.6	811.7	798.8	786.0	773.1	764.2
37.5°	820.2	811.8	803.5	795.2	786.9	776.0	762.2	748.5	734.8	721.0	710.9
40°	791.8	782.7	773.5	764.4	755.3	743.3	728.6	713.9	699.1	684.4	673.6
42.5°	759.6	750.6	741.4	732.3	723.2	711.0	695.7	680.5	665.3	650.1	638.3
45°	710.5	701.2	691.9	682.5	673.2	660.6	644.5	628.6	612.6	596.6	584.8
47.5°	661.5	651.2	641.0	630.7	620.5	607.3	591.4	575.3	559.4	543.4	530.6
50°	625.5	615.8	606.1	596.3	586.6	573.3	556.5	539.7	522.9	506.0	493.2
52.5°	593.4	582.9	572.3	561.7	551.2	537.5	520.8	504.3	487.6	470.9	457.6
55°	539.7	529.5	519.3	509.2	499.0	485.1	467.4	449.9	432.2	414.6	402.5
57.5°	490.0	478.9	467.9	456.7	445.7	431.3	413.6	395.8	378.1	360.4	349.0
60°	455.7	444.3	432.8	421.4	410.0	395.7	378.4	361.2	344.0	326.8	315.6
62.5°	421.2	409.8	398.4	387.0	375.7	361.3	344.1	326.9	309.7	292.4	281.9
65°	368.8	357.4	346.0	334.6	323.2	309.3	293.2	277.0	260.8	244.6	234.4
67.5°	316.4	304.8	293.3	281.7	270.2	256.6	241.1	225.6	210.1	194.6	187.0
70°	282.0	270.8	259.6	248.3	237.2	224.3	209.7	195.3	180.7	166.2	158.9
72.5°	247.6	236.6	225.5	214.5	203.5	191.4	178.2	165.0	151.8	138.6	132.6
75°	195.1	185.2	175.2	165.2	155.3	144.6	133.2	121.8	110.4	99.0	96.9
77.5°	147.3	138.3	129.3	120.3	111.3	103.2	95.8	88.5	81.1	73.7	72.7
80°	116.7	108.2	99.7	91.2	82.7	76.2	71.9	67.5	63.2	58.9	58.2
82.5°	87.6	80.3	72.9	65.5	58.2	53.5	51.5	49.4	47.4	45.4	44.8
85°	49.5	44.9	40.4	35.8	31.2	28.6	28.0	27.4	26.8	26.1	25.8
87.5°	18.1	16.5	15.0	13.5	11.9	11.3	11.8	12.1	12.5	12.9	12.8
90°	0.6	2.1	3.6	5.1	6.5	8.2	10.2	12.0	14.0	15.9	16.5
92.5°	16.1	17.0	18.0	19.0	20.0	21.0	22.1	23.3	24.3	25.4	25.9
95°	39.1	40.0	41.1	42.2	43.2	44.2	45.5	46.6	47.8	49.0	49.6
97.5°	69.4	70.1	70.9	71.7	72.4	73.2	74.1	74.9	75.8	76.7	77.3
100°	90.0	90.9	91.8	92.6	93.5	94.3	95.1	95.9	96.6	97.3	97.7
102.5°	113.9	114.4	114.9	115.4	115.9	116.7	117.7	118.7	119.6	120.6	121.0
105°	148.9	149.2	149.5	149.8	150.1	150.9	152.2	153.6	154.9	156.2	156.2
107.5°	189.7	189.8	190.0	190.2	190.4	190.7	191.3	191.8	192.3	192.9	193.3
110°	215.1	215.4	215.7	216.0	216.2	216.6	216.9	217.1	217.5	217.8	218.4



TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	241.6	241.7	241.9	242.1	242.3	242.4	242.5	242.5	242.5	242.6	243.3
115°	281.3	281.7	282.1	282.6	283.0	283.1	282.9	282.6	282.2	282.0	282.1
117.5°	321.3	321.6	321.8	322.2	322.4	322.4	322.0	321.6	321.3	320.8	320.8
120°	346.2	347.1	347.9	348.8	349.7	349.7	349.0	348.3	347.6	346.8	346.7
122.5°	372.1	372.7	373.4	374.1	374.7	374.8	374.4	374.1	373.7	373.3	372.9
125°	411.7	412.1	412.6	413.0	413.5	413.5	413.2	413.0	412.6	412.3	411.8
127.5°	448.2	449.2	450.1	451.0	452.0	452.3	452.0	451.7	451.3	451.0	450.1
130°	472.6	473.8	474.9	476.1	477.2	477.7	477.2	476.8	476.4	475.9	475.3
132.5°	497.0	498.1	499.3	500.4	501.7	502.0	501.8	501.4	501.1	500.8	500.1
135°	534.1	535.0	535.9	536.8	537.6	538.1	537.9	537.7	537.6	537.4	536.8
137.5°	568.6	569.3	570.0	570.8	571.5	572.0	572.4	572.8	573.2	573.5	572.9
140°	592.4	593.1	593.9	594.6	595.3	595.8	595.9	596.0	596.2	596.4	596.2
142.5°	614.1	614.8	615.5	616.3	617.0	617.5	617.8	618.0	618.3	618.6	618.4
145°	648.0	648.3	648.5	648.8	649.2	649.5	650.0	650.4	650.9	651.3	651.1
147.5°	677.6	678.1	678.7	679.2	679.8	680.2	680.6	681.0	681.4	681.9	681.9
150°	698.3	698.6	698.8	699.2	699.5	699.7	700.0	700.3	700.6	700.9	700.9
152.5°	715.2	715.6	716.0	716.5	716.8	717.1	717.3	717.5	717.6	717.8	718.1
155°	742.0	742.0	742.0	742.0	742.0	742.0	742.2	742.3	742.4	742.6	743.2
157.5°	764.7	764.6	764.4	764.2	764.0	764.0	764.1	764.2	764.4	764.5	765.1
160°	779.0	778.7	778.5	778.1	777.8	777.7	777.7	777.7	777.7	777.7	778.5
162.5°	791.8	791.3	790.9	790.5	790.1	790.0	790.1	790.1	790.3	790.4	791.1
165°	808.2	807.7	807.3	806.8	806.4	806.1	806.1	806.1	806.1	806.1	807.0
167.5°	821.3	820.6	820.1	819.5	818.9	818.7	818.8	818.9	819.0	819.1	820.0
170°	828.7	828.0	827.5	826.9	826.3	826.0	826.0	826.0	826.0	826.0	827.1
172.5°	834.5	833.9	833.3	832.7	832.1	831.8	831.8	831.8	831.8	831.8	832.8
175°	840.5	840.0	839.4	838.8	838.2	837.9	837.9	837.9	837.9	837.9	838.8
177.5°	843.1	842.6	842.1	841.7	841.2	841.0	841.0	841.0	841.0	841.0	841.7
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6



TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3	1151.3
2.5°	1146.7	1148.5	1150.3	1151.1	1150.8	1150.4	1150.0	1149.8
5°	1139.1	1140.9	1142.8	1143.5	1143.2	1142.7	1142.3	1141.9
7.5°	1123.1	1124.1	1125.2	1125.3	1124.6	1123.9	1123.2	1122.5
10°	1108.8	1108.9	1109.1	1108.8	1107.7	1106.6	1105.6	1104.6
12.5°	1090.8	1090.7	1090.7	1089.9	1088.8	1087.5	1086.4	1085.1
15°	1059.5	1058.5	1057.5	1056.2	1054.8	1053.3	1051.9	1050.4
17.5°	1022.1	1019.9	1017.7	1015.6	1013.3	1011.2	1009.1	1006.9
20°	996.5	993.7	991.0	988.5	986.0	983.5	981.0	978.5
22.5°	969.0	965.6	962.2	959.4	957.1	954.8	952.4	950.1
25°	924.1	919.7	915.3	912.0	909.7	907.4	905.2	902.9
27.5°	875.0	869.1	863.0	858.2	854.7	851.2	847.7	844.3
30°	840.3	833.1	826.1	820.9	817.6	814.3	810.9	807.6
32.5°	806.0	798.3	790.6	785.0	781.5	778.0	774.5	771.1
35°	755.3	746.4	737.4	731.1	727.4	723.6	719.9	716.1
37.5°	700.7	690.6	680.5	673.2	668.5	663.9	659.3	654.7
40°	662.8	652.0	641.2	633.5	628.7	623.9	619.1	614.4
42.5°	626.4	614.7	602.9	594.9	590.6	586.3	582.0	577.7
45°	573.0	561.2	549.3	540.9	535.9	530.9	526.0	521.0
47.5°	517.6	504.8	492.0	483.3	478.8	474.4	470.0	465.6
50°	480.4	467.4	454.6	445.8	441.0	436.2	431.5	426.7
52.5°	444.3	430.9	417.5	408.7	404.4	400.1	395.8	391.6
55°	390.5	378.4	366.4	358.3	354.2	350.0	345.9	341.7
57.5°	337.7	326.3	315.0	307.5	304.0	300.4	296.9	293.4
60°	304.3	293.2	282.0	274.6	271.1	267.5	264.0	260.5
62.5°	271.3	260.8	250.3	243.2	239.4	235.8	232.1	228.4
65°	224.3	214.1	203.9	197.7	195.5	193.1	190.9	188.6
67.5°	179.4	171.8	164.2	159.2	156.8	154.3	151.9	149.4
70°	151.7	144.4	137.1	132.4	130.1	127.8	125.6	123.2
72.5°	126.7	120.7	114.9	111.4	110.4	109.5	108.5	107.5
75°	94.8	92.7	90.7	89.4	89.0	88.6	88.2	87.7
77.5°	71.5	70.4	69.3	68.5	68.1	67.7	67.2	66.9
80°	57.6	57.0	56.4	55.8	55.4	55.0	54.6	54.1
82.5°	44.1	43.5	42.9	42.5	42.4	42.4	42.3	42.2
85°	25.3	24.9	24.5	24.3	24.3	24.3	24.3	24.3
87.5°	12.8	12.8	12.7	12.6	12.5	12.4	12.3	12.2
90°	17.0	17.7	18.3	18.6	19.0	19.3	19.5	19.9
92.5°	26.4	26.8	27.3	27.5	27.3	27.1	26.9	26.8
95°	50.1	50.7	51.4	51.6	51.6	51.6	51.6	51.6
97.5°	78.0	78.6	79.4	79.6	79.6	79.5	79.5	79.5
100°	98.2	98.6	99.1	99.4	99.7	100.0	100.3	100.6
102.5°	121.5	121.9	122.3	122.5	122.5	122.4	122.3	122.3
105°	156.2	156.2	156.2	156.3	156.7	156.9	157.2	157.6
107.5°	193.8	194.3	194.7	194.9	194.7	194.6	194.4	194.2
110°	218.9	219.5	220.1	220.3	220.0	219.6	219.4	219.1



TEST NUMBER: P332437-940

CATALOG NUMBER: S123RDIW-S775D755U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	244.1	244.8	245.5	245.8	245.8	245.7	245.6	245.6
115°	282.2	282.4	282.6	282.6	282.4	282.2	282.1	282.0
117.5°	320.8	320.7	320.7	320.6	320.1	319.7	319.3	318.9
120°	346.5	346.3	346.3	346.0	345.7	345.4	345.1	344.8
122.5°	372.6	372.1	371.8	371.4	371.0	370.5	370.1	369.7
125°	411.2	410.5	410.0	409.4	408.8	408.2	407.6	407.1
127.5°	449.3	448.5	447.7	446.9	446.3	445.6	445.0	444.3
130°	474.7	474.1	473.5	472.7	471.7	470.6	469.7	468.6
132.5°	499.4	498.6	497.9	497.2	496.4	495.6	494.8	494.0
135°	536.3	535.7	535.1	534.7	534.3	534.0	533.8	533.4
137.5°	572.3	571.7	571.1	570.5	570.0	569.4	568.8	568.3
140°	596.0	595.9	595.8	595.1	594.1	593.1	592.1	591.0
142.5°	618.3	618.1	618.0	617.5	616.7	615.9	615.1	614.3
145°	650.9	650.9	650.7	650.3	649.7	649.2	648.5	648.0
147.5°	681.9	681.9	681.9	681.4	680.6	679.7	678.8	677.9
150°	700.9	700.9	700.9	700.4	699.5	698.7	697.9	697.0
152.5°	718.4	718.5	718.8	718.5	717.7	717.0	716.2	715.5
155°	743.8	744.4	744.9	744.8	743.7	742.7	741.6	740.7
157.5°	765.7	766.3	767.0	766.8	766.0	765.2	764.4	763.5
160°	779.2	779.9	780.6	780.7	780.2	779.5	778.9	778.4
162.5°	791.8	792.6	793.4	793.3	792.3	791.4	790.4	789.4
165°	807.9	808.8	809.7	809.6	808.6	807.5	806.6	805.5
167.5°	820.9	821.9	822.8	822.8	821.9	820.9	820.0	819.1
170°	828.0	829.1	830.1	830.1	829.1	828.0	827.1	826.0
172.5°	833.7	834.6	835.4	835.4	834.4	833.4	832.3	831.3
175°	839.7	840.5	841.4	841.4	840.3	839.3	838.3	837.2
177.5°	842.4	843.1	843.8	843.7	842.9	842.0	841.2	840.4
180°	842.6	842.6	842.6	842.6	842.6	842.6	842.6	842.6

(END OF REPORT)