

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332767-930

Luminaire Tested: **S124DIW-S575D1340U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332767-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S575D1340U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6409.4 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32								
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27								
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22								
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19								
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16								
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14								
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12								
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11								
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10								
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9								
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6391	6391	6391
5°	6412	6334	6380
10°	6370	6283	6314
15°	6294	6193	6209
20°	6192	6082	6088
25°	6075	5956	5940
30°	5931	5808	5754
35°	5784	5653	5577
40°	5630	5476	5376
45°	5469	5302	5200
50°	5291	5148	4987
55°	5098	4947	4787
60°	4907	4721	4579
65°	4690	4508	4327
70°	4447	4223	4057
75°	4077	3877	3780
80°	3626	3477	3394
85°	3168	3057	3001



TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	1.2
10°-20°	210.1	3.3
20°-30°	309.2	4.8
30°-40°	359.5	5.6
40°-50°	359.5	5.6
50°-60°	314.5	4.9
60°-70°	233.5	3.6
70°-80°	132.7	2.1
80°-90°	42.4	0.7
90°-100°	48.4	0.8
100°-110°	308.3	4.8
110°-120°	589.8	9.2
120°-130°	748.7	11.7
130°-140°	801.1	12.5
140°-150°	749.1	11.7
150°-160°	604.1	9.4
160°-170°	389.6	6.1
170°-180°	134.3	2.1
0°-30°	593.9	9.3
0°-40°	953.4	14.9
0°-60°	1627.3	25.4
0°-90°	2035.9	31.8
90°-120°	946.5	14.8
90°-150°	3245.5	50.6
90°-180°	4374.0	68.2
0°-180°	6409.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	792	792	792	792	792	
5°	791	788	782	788	787	75
15°	753	750	741	744	743	212
25°	682	677	669	669	667	314
35°	587	582	574	569	566	367
45°	479	474	464	458	456	369
55°	362	360	352	344	340	324
65°	246	242	236	230	226	243
75°	131	128	124	122	121	139
85°	34	34	33	33	32	38
90°	3	15	23	29	32	5
95°	58	24	23	29	31	75
105°	318	325	330	337	301	333
115°	594	597	596	598	598	585
125°	835	839	838	841	842	746
135°	1036	1036	1040	1042	1044	798
145°	1195	1198	1198	1199	1201	746
155°	1310	1311	1308	1312	1309	604
165°	1382	1377	1377	1384	1376	390
175°	1414	1408	1409	1417	1405	135
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	793.8	793.4	793.1	792.8	792.5	791.7	790.4	789.2	787.9	786.7	787.8
5°	791.2	790.6	790.0	789.5	788.9	787.8	786.3	784.7	783.2	781.6	783.2
7.5°	783.7	783.2	782.7	782.1	781.5	780.4	778.7	777.0	775.2	773.5	774.8
10°	777.1	776.7	776.1	775.5	774.9	773.7	771.9	770.1	768.3	766.4	767.5
12.5°	768.6	768.0	767.4	766.9	766.3	765.1	763.1	761.2	759.2	757.2	758.5
15°	753.1	752.5	752.0	751.4	750.8	749.5	747.4	745.3	743.1	741.0	741.8
17.5°	734.4	733.7	733.0	732.3	731.6	730.3	728.2	726.3	724.2	722.3	722.8
20°	720.7	720.0	719.3	718.6	717.9	716.5	714.4	712.2	710.1	708.0	708.4
22.5°	706.0	705.1	704.2	703.2	702.3	700.7	698.6	696.5	694.4	692.3	693.1
25°	682.0	681.0	680.0	679.1	678.1	676.6	674.6	672.6	670.7	668.7	668.9
27.5°	654.6	653.6	652.6	651.6	650.5	649.1	647.3	645.5	643.6	641.8	641.5
30°	636.3	635.2	634.1	632.9	631.9	630.3	628.5	626.6	624.8	623.1	622.5
32.5°	617.0	616.0	615.0	614.0	613.0	611.5	609.6	607.6	605.7	603.7	603.1
35°	586.9	585.9	584.9	583.9	582.9	581.4	579.4	577.5	575.5	573.6	572.5
37.5°	555.0	554.1	553.2	552.3	551.4	549.9	547.8	545.7	543.6	541.4	540.4
40°	534.2	533.0	531.9	530.8	529.7	528.1	525.9	523.8	521.7	519.6	518.2
42.5°	511.8	511.2	510.5	509.8	509.2	507.6	505.3	503.0	500.6	498.3	496.7
45°	479.0	478.0	477.0	476.1	475.1	473.4	471.2	468.9	466.7	464.4	462.8
47.5°	444.6	443.9	443.3	442.5	441.9	440.5	438.5	436.3	434.2	432.2	430.4
50°	421.3	420.7	420.1	419.6	419.0	417.8	415.8	413.8	411.8	409.9	407.9
52.5°	398.4	397.8	397.1	396.4	395.7	394.4	392.2	390.2	388.1	386.0	384.3
55°	362.2	361.8	361.4	361.0	360.6	359.4	357.4	355.4	353.4	351.5	349.8
57.5°	327.8	327.3	326.8	326.3	325.8	324.7	322.7	320.7	318.8	316.8	315.2
60°	303.9	303.2	302.5	301.7	301.1	299.8	298.0	296.1	294.3	292.4	291.2
62.5°	280.5	280.0	279.3	278.8	278.2	276.9	275.0	273.0	271.1	269.1	268.0
65°	245.5	244.8	244.1	243.4	242.7	241.7	240.3	238.8	237.4	236.0	234.6
67.5°	210.3	209.6	209.0	208.3	207.7	206.7	205.3	204.0	202.6	201.2	199.9
70°	188.4	187.4	186.5	185.5	184.5	183.4	182.3	181.2	180.0	178.9	177.8
72.5°	165.1	164.1	163.1	162.1	161.1	160.2	159.3	158.4	157.5	156.5	155.6
75°	130.7	130.0	129.3	128.6	127.8	127.2	126.5	125.7	125.1	124.3	123.8
77.5°	97.8	97.5	97.2	96.9	96.6	96.1	95.5	94.9	94.2	93.7	93.4
80°	78.0	77.6	77.2	76.8	76.3	76.0	75.7	75.4	75.2	74.8	74.6
82.5°	58.8	58.5	58.4	58.1	58.0	57.8	57.8	57.7	57.6	57.6	57.4
85°	34.2	34.2	34.2	34.2	34.2	34.1	33.8	33.6	33.3	33.0	33.0
87.5°	13.9	14.3	14.7	15.1	15.4	15.8	16.1	16.3	16.6	16.8	17.1
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	13.3	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8
95°	58.1	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7
97.5°	123.5	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0
100°	173.4	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6
102.5°	229.3	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1
105°	318.3	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1
107.5°	401.0	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4
110°	456.8	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8



TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.9	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6
115°	594.3	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9
117.5°	669.4	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9
120°	720.2	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8
122.5°	767.5	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8
125°	835.4	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2
127.5°	899.7	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5
130°	941.2	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7
132.5°	979.3	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4
135°	1036.3	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0
137.5°	1086.9	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5
140°	1119.9	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8
142.5°	1149.5	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1
145°	1195.0	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4
147.5°	1231.1	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2
150°	1257.4	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5
152.5°	1279.4	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2
155°	1310.3	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0
157.5°	1336.3	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3
160°	1351.4	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7
162.5°	1365.0	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3
165°	1382.2	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8
167.5°	1395.7	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6
170°	1403.3	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9
172.5°	1408.3	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9
175°	1413.9	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7
177.5°	1416.4	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	791.7	791.7	791.7	791.7	791.7	791.7	791.7	791.7
2.5°	789.0	790.1	791.2	791.7	791.6	791.5	791.4	791.2
5°	784.7	786.3	787.8	788.5	788.1	787.9	787.6	787.3
7.5°	776.0	777.2	778.4	779.0	778.9	778.7	778.5	778.3
10°	768.7	769.8	770.9	771.4	771.0	770.8	770.5	770.2
12.5°	759.8	761.0	762.2	762.6	762.2	761.8	761.5	761.1
15°	742.7	743.6	744.4	744.6	744.2	743.8	743.3	742.9
17.5°	723.3	723.8	724.4	724.5	724.2	723.9	723.7	723.4
20°	708.9	709.3	709.7	709.8	709.5	709.2	709.0	708.7
22.5°	693.8	694.6	695.4	695.5	695.0	694.5	694.0	693.4
25°	669.0	669.1	669.3	669.0	668.5	667.9	667.3	666.8
27.5°	641.2	640.7	640.4	639.9	639.2	638.5	637.8	637.1
30°	621.9	621.3	620.8	620.1	619.4	618.7	618.0	617.3
32.5°	602.3	601.7	601.0	600.3	599.7	598.9	598.2	597.5
35°	571.5	570.5	569.6	568.8	568.0	567.3	566.6	565.9
37.5°	539.3	538.2	537.1	536.1	535.2	534.3	533.4	532.4
40°	516.8	515.4	514.0	512.9	512.2	511.5	510.8	510.1
42.5°	495.0	493.3	491.7	490.6	490.2	489.8	489.3	488.8
45°	461.3	459.7	458.2	457.2	456.8	456.4	455.9	455.5
47.5°	428.7	426.9	425.2	423.8	422.7	421.6	420.5	419.5
50°	405.9	403.9	401.9	400.6	399.7	398.8	398.0	397.1
52.5°	382.5	380.7	379.0	377.6	376.5	375.4	374.4	373.3
55°	348.1	346.4	344.7	343.4	342.6	341.8	340.9	340.1
57.5°	313.6	312.0	310.4	309.2	308.3	307.5	306.7	305.9
60°	289.9	288.7	287.4	286.4	285.7	285.0	284.3	283.6
62.5°	266.8	265.6	264.5	263.6	262.9	262.2	261.5	260.7
65°	233.2	231.8	230.4	229.3	228.6	227.9	227.2	226.5
67.5°	198.5	197.2	195.8	195.0	194.9	194.7	194.4	194.3
70°	176.7	175.5	174.4	173.7	173.2	172.8	172.4	171.9
72.5°	154.7	153.8	153.0	152.3	151.9	151.5	151.1	150.6
75°	123.2	122.6	122.1	121.7	121.6	121.5	121.3	121.2
77.5°	93.3	93.1	92.9	92.7	92.3	92.0	91.6	91.2
80°	74.3	74.0	73.7	73.5	73.4	73.2	73.1	73.0
82.5°	57.2	57.1	56.9	56.7	56.7	56.5	56.3	56.2
85°	33.0	33.0	33.0	32.9	32.8	32.6	32.5	32.4
87.5°	17.4	17.7	17.9	18.2	18.3	18.3	18.4	18.5
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	25.3	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	26.1	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.2	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	38.6	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	138.0	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	334.2	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	413.4	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.3	467.7	468.2	468.8	469.5	470.3	470.9	471.7



TEST NUMBER: P332767-930

CATALOG NUMBER: S124DIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.4	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.4	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.7	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.1	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	838.9	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.4	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	945.8	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.6	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.5	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.0	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1125.5	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1155.6	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.6	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.4	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1281.6	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.0	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1362.8	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1380.6	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1393.7	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1401.7	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1406.8	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1412.8	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1415.2	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)