

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332787-930

Luminaire Tested: **S124DIW-S795D1050U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332787-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D1050U930-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6307.4 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				46
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45				39	
2	89	81	75	70	81	75	70	65	63	59	56	52	49	47	41	39	38				33	
3	81	72	64	59	74	66	60	55	55	51	47	46	42	40	37	34	32				28	
4	74	63	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28				24	
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25				21	
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22				19	
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17				15	
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8451	8451	8451	8451
5°	9951	8473	7478	8473
10°	11914	8435	6733	8435
15°	14098	8350	6182	8350
20°	15698	8262	5692	8262
25°	15952	8134	5353	8134
30°	13573	8011	5246	8011
35°	10435	7811	5248	7811
40°	8134	7576	5347	7576
45°	6782	7223	5436	7223
50°	5968	6791	5620	6791
55°	5468	6273	5847	6273
60°	5125	5811	6119	5811
65°	4770	5291	6346	5291
70°	4360	4780	6489	4780
75°	3896	4208	6410	4208
80°	3268	3445	6206	3445
85°	2408	2492	5947	2492



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.0	1.6
10°-20°	314.3	5.0
20°-30°	498.4	7.9
30°-40°	554.7	8.8
40°-50°	504.9	8.0
50°-60°	412.6	6.5
60°-70°	294.6	4.7
70°-80°	162.2	2.6
80°-90°	47.5	0.8
90°-100°	37.8	0.6
100°-110°	240.8	3.8
110°-120°	460.7	7.3
120°-130°	584.9	9.3
130°-140°	625.8	9.9
140°-150°	585.2	9.3
150°-160°	471.9	7.5
160°-170°	304.4	4.8
170°-180°	104.9	1.7
0°-30°	914.7	14.5
0°-40°	1469.4	23.3
0°-60°	2386.9	37.8
0°-90°	2891.1	45.8
90°-120°	739.3	11.7
90°-150°	2535.2	40.2
90°-180°	3416.0	54.2
0°-180°	6307.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1047	1047	1047	1047	1047	
5°	1228	1046	923	1046	1228	125
15°	1687	999	740	999	1687	477
25°	1791	913	601	913	1791	789
35°	1059	793	532	793	1059	672
45°	594	633	476	633	594	468
55°	388	446	415	446	388	351
65°	250	277	332	277	250	247
75°	125	135	206	135	125	133
85°	26	27	64	27	26	32
90°	25	2	25	2	25	12
95°	24	45	24	45	24	19
105°	236	249	236	249	236	205
115°	468	464	468	464	468	463
125°	658	653	658	653	658	586
135°	815	810	815	810	815	628
145°	938	933	938	933	938	586
155°	1023	1023	1023	1023	1023	472
165°	1075	1080	1075	1080	1075	304
175°	1098	1104	1098	1104	1098	105
180°	1104	1104	1104	1104	1104	



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1114.0	1113.7	1110.2	1109.5	1107.1	1104.0	1103.3	1097.7	1086.6	1081.4	1080.0
5°	1228.0	1236.6	1225.4	1223.2	1221.9	1207.6	1200.2	1191.6	1171.6	1159.9	1150.8
7.5°	1364.0	1365.0	1360.1	1356.1	1345.1	1332.5	1313.9	1293.9	1270.2	1245.4	1226.8
10°	1453.4	1456.9	1451.3	1450.4	1428.3	1414.5	1386.7	1363.3	1336.4	1306.4	1279.1
12.5°	1547.8	1543.0	1540.1	1521.5	1517.4	1492.2	1459.9	1435.7	1394.3	1359.9	1323.6
15°	1686.8	1677.2	1671.1	1645.5	1633.0	1597.8	1563.6	1537.2	1482.9	1431.3	1392.3
17.5°	1768.2	1777.8	1763.7	1753.2	1720.7	1696.1	1661.1	1605.6	1563.2	1499.1	1449.8
20°	1827.2	1828.1	1820.3	1809.5	1783.9	1752.6	1714.5	1653.8	1603.0	1539.3	1471.7
22.5°	1843.1	1843.4	1840.0	1829.9	1810.5	1785.3	1746.8	1696.1	1634.6	1565.3	1497.7
25°	1790.8	1789.1	1793.0	1804.3	1796.8	1789.1	1766.9	1729.2	1672.0	1598.7	1525.8
27.5°	1596.2	1608.2	1630.2	1657.9	1684.7	1705.0	1710.7	1703.0	1667.5	1607.3	1531.0
30°	1456.0	1470.8	1487.3	1515.0	1568.8	1599.6	1633.4	1659.0	1644.7	1596.5	1525.4
32.5°	1302.0	1305.7	1330.2	1361.7	1411.0	1470.2	1523.8	1575.7	1593.0	1567.7	1508.5
35°	1058.8	1064.9	1091.4	1122.6	1182.9	1255.3	1335.9	1407.9	1467.3	1491.2	1460.9
37.5°	864.1	881.5	900.2	933.8	986.8	1052.0	1135.8	1228.9	1317.4	1376.8	1386.8
40°	771.8	782.7	796.1	821.7	866.7	931.0	1002.9	1109.6	1203.7	1288.7	1316.5
42.5°	699.0	705.3	713.5	736.7	771.0	834.9	900.6	994.4	1088.9	1190.5	1237.0
45°	594.0	600.5	614.4	627.9	653.9	698.1	759.2	836.4	931.4	1029.4	1115.2
47.5°	518.3	522.4	530.7	545.0	567.1	596.3	646.0	710.5	798.5	893.6	985.1
50°	475.2	478.7	485.2	498.2	515.1	541.1	581.9	642.2	711.1	807.0	896.7
52.5°	441.2	442.6	447.4	456.2	469.7	491.5	525.0	574.9	639.0	724.4	813.8
55°	388.5	390.3	394.6	401.1	412.8	426.6	452.2	489.5	545.5	619.6	697.2
57.5°	345.1	346.3	350.0	352.5	362.2	373.4	393.1	419.7	462.1	525.0	594.3
60°	317.4	316.5	320.9	323.0	329.5	339.1	354.2	379.8	416.7	467.4	531.2
62.5°	290.3	289.1	292.8	295.6	299.4	307.5	319.9	340.0	369.9	415.7	470.8
65°	249.7	248.0	250.2	253.6	257.1	261.5	270.6	288.4	312.2	345.1	387.2
67.5°	209.0	210.8	211.2	212.9	214.9	220.8	227.1	239.6	256.4	282.8	318.5
70°	184.7	185.2	186.9	186.9	188.2	193.4	198.6	205.9	222.4	246.7	275.7
72.5°	160.5	162.2	161.6	163.0	163.9	167.4	171.2	178.2	192.2	210.3	234.8
75°	124.9	126.2	126.2	126.6	127.9	129.2	132.2	137.5	147.4	160.9	177.8
77.5°	91.1	91.2	91.8	93.4	93.4	95.5	97.8	101.9	106.8	116.0	126.4
80°	70.3	71.1	70.7	71.6	71.6	73.3	74.1	79.3	81.5	87.6	95.8
82.5°	51.5	52.3	52.3	53.5	54.2	54.5	55.8	57.8	60.0	65.4	68.7
85°	26.0	26.9	26.0	26.9	28.2	28.6	29.9	30.3	32.1	33.4	36.4
87.5°	12.6	13.5	13.5	13.8	14.3	14.6	14.7	14.1	15.3	15.4	16.6
90°	24.8	24.4	24.1	23.6	23.3	22.6	21.4	20.4	19.2	18.2	16.7
92.5°	22.8	22.7	22.7	22.6	22.5	21.9	20.8	19.7	18.6	17.5	16.1
95°	24.0	23.8	23.6	23.4	23.2	22.6	21.4	20.4	19.2	18.2	18.0
97.5°	23.2	22.9	22.7	22.6	22.4	22.3	22.2	22.0	21.9	21.8	42.3
100°	23.2	22.9	22.7	22.6	22.4	23.9	27.0	30.1	33.3	36.4	61.7
102.5°	23.8	23.7	23.7	23.6	23.6	40.4	74.1	107.8	141.5	175.1	178.4
105°	235.5	242.1	248.7	255.3	261.9	264.3	262.7	261.1	259.3	257.7	256.8
107.5°	328.1	327.4	326.7	326.0	325.3	324.6	323.8	322.9	322.1	321.3	320.1
110°	368.4	367.9	367.3	366.8	366.2	365.7	365.4	365.0	364.7	364.3	363.2



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	408.7	408.1	407.3	406.7	405.9	405.6	405.7	405.8	405.9	405.9	405.4
115°	467.6	467.6	467.6	467.6	467.6	467.3	467.0	466.6	466.3	465.9	466.1
117.5°	527.3	527.4	527.5	527.6	527.7	527.7	527.8	527.8	527.9	528.0	527.6
120°	565.0	565.4	565.7	566.1	566.5	566.5	566.1	565.7	565.4	565.0	565.2
122.5°	602.0	602.4	602.8	603.2	603.5	603.6	603.3	603.2	602.9	602.7	602.4
125°	657.5	657.4	657.1	657.0	656.8	656.4	655.9	655.3	654.8	654.2	654.6
127.5°	706.3	706.4	706.5	706.7	706.9	706.9	707.1	707.2	707.4	707.4	706.5
130°	739.3	739.3	739.3	739.3	739.3	739.2	739.1	738.8	738.7	738.5	737.9
132.5°	769.7	769.9	770.0	770.1	770.3	770.3	770.1	769.9	769.7	769.6	768.8
135°	815.3	815.0	814.6	814.2	813.8	813.5	813.1	812.8	812.4	812.0	811.3
137.5°	854.3	854.4	854.5	854.6	854.8	854.6	854.2	853.8	853.4	853.0	852.2
140°	881.4	881.2	881.0	880.8	880.7	880.3	879.7	879.2	878.6	878.1	877.8
142.5°	903.8	903.8	903.8	903.8	903.7	903.5	903.1	902.7	902.3	901.9	901.6
145°	938.4	938.0	937.7	937.3	936.9	936.6	936.5	936.3	936.1	935.9	935.9
147.5°	966.9	966.8	966.6	966.5	966.2	966.0	965.9	965.8	965.6	965.5	965.6
150°	985.5	985.3	985.1	984.9	984.7	984.6	984.6	984.6	984.6	984.6	984.8
152.5°	1001.4	1001.4	1001.5	1001.7	1001.8	1001.7	1001.4	1001.1	1000.8	1000.5	1000.9
155°	1022.6	1023.2	1023.8	1024.3	1024.8	1024.7	1024.0	1023.3	1022.5	1021.8	1022.4
157.5°	1040.5	1041.5	1042.4	1043.3	1044.3	1044.3	1043.3	1042.4	1041.5	1040.5	1041.1
160°	1052.4	1053.4	1054.6	1055.6	1056.8	1056.8	1055.6	1054.6	1053.4	1052.4	1052.6
162.5°	1061.6	1062.9	1064.1	1065.4	1066.7	1066.7	1065.6	1064.5	1063.4	1062.3	1062.5
165°	1074.6	1076.4	1078.0	1079.6	1081.2	1081.4	1079.9	1078.5	1077.0	1075.5	1075.5
167.5°	1084.4	1086.3	1088.1	1090.0	1091.8	1091.8	1090.3	1088.7	1087.0	1085.4	1085.6
170°	1090.4	1092.2	1094.1	1095.8	1097.7	1097.9	1096.4	1094.9	1093.5	1092.0	1091.8
172.5°	1093.6	1095.7	1097.6	1099.6	1101.6	1101.9	1100.4	1098.9	1097.5	1096.0	1095.8
175°	1097.8	1100.0	1102.2	1104.4	1106.6	1106.9	1105.2	1103.6	1102.0	1100.3	1100.1
177.5°	1100.5	1102.2	1104.0	1105.7	1107.5	1107.8	1106.6	1105.5	1104.2	1103.1	1102.8
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1080.4	1075.5	1072.0	1069.3	1061.7	1057.1	1053.7	1048.8	1043.3	1037.4	1030.0
5°	1141.7	1126.9	1116.1	1099.6	1084.0	1071.0	1057.6	1045.5	1030.7	1014.6	1002.9
7.5°	1206.2	1184.2	1156.1	1131.7	1104.3	1080.4	1059.2	1037.3	1014.6	992.5	972.3
10°	1247.1	1218.9	1187.6	1150.8	1116.1	1085.3	1056.7	1029.0	1002.1	975.2	952.2
12.5°	1291.1	1256.0	1209.8	1166.8	1127.9	1086.7	1052.2	1018.2	985.8	957.5	930.7
15°	1350.2	1299.5	1246.2	1188.5	1137.3	1089.2	1042.0	999.1	962.6	925.3	899.3
17.5°	1386.6	1323.8	1262.8	1202.6	1140.7	1079.9	1029.0	979.4	933.8	896.7	864.0
20°	1410.5	1348.1	1272.2	1211.9	1138.2	1075.8	1016.8	961.7	914.0	874.6	840.7
22.5°	1431.3	1359.2	1283.3	1204.0	1130.6	1064.4	999.8	944.4	895.7	854.1	821.7
25°	1442.6	1359.8	1277.4	1198.5	1115.2	1036.7	978.2	913.2	861.1	817.3	782.7
27.5°	1443.8	1355.3	1262.1	1174.4	1088.4	1015.4	941.4	883.4	829.3	783.0	749.7
30°	1440.0	1347.7	1247.5	1152.5	1066.2	986.9	922.8	859.4	804.4	758.4	723.7
32.5°	1427.8	1331.7	1228.7	1128.2	1038.9	961.2	895.0	834.8	781.1	735.8	699.4
35°	1392.8	1297.8	1188.1	1083.6	992.1	913.6	853.8	792.6	738.9	695.9	660.8
37.5°	1337.8	1252.0	1140.4	1032.3	942.5	863.6	804.4	749.1	700.6	657.0	621.0
40°	1290.0	1214.6	1102.7	997.3	900.2	825.2	769.6	718.9	670.8	629.6	595.3
42.5°	1234.9	1169.1	1065.9	954.3	860.6	785.3	731.2	685.6	640.3	602.2	567.9
45°	1136.4	1093.2	996.0	892.8	795.2	724.1	672.5	632.7	594.5	557.2	528.6
47.5°	1023.4	1001.9	920.1	822.1	729.5	659.4	614.7	577.8	544.4	512.8	487.5
50°	947.5	937.0	866.3	771.8	683.4	617.4	572.3	540.7	512.1	484.4	460.5
52.5°	872.5	872.1	808.5	721.9	640.0	576.5	531.7	502.2	477.4	454.9	433.4
55°	758.0	770.1	720.2	643.0	569.7	512.5	472.2	445.7	428.4	409.8	393.7
57.5°	652.7	672.9	631.8	563.8	502.6	449.9	414.8	394.9	376.4	365.2	353.5
60°	584.1	603.2	571.0	513.8	456.2	411.1	377.6	359.9	343.8	336.1	327.8
62.5°	523.0	540.1	516.2	463.2	413.1	369.8	341.6	324.5	313.6	305.2	299.7
65°	435.8	450.0	429.7	391.1	348.2	313.5	290.5	277.0	266.7	263.2	257.1
67.5°	352.3	365.3	354.2	321.5	287.1	260.7	242.8	229.9	223.7	220.7	216.4
70°	302.6	315.7	303.9	275.3	248.9	226.8	209.9	202.5	196.0	194.7	188.6
72.5°	260.7	269.5	257.8	235.5	212.8	194.2	181.1	173.3	170.0	167.6	164.4
75°	195.6	203.3	195.6	178.2	162.2	149.2	137.9	134.9	130.9	129.6	127.5
77.5°	138.4	145.2	139.2	128.3	116.3	106.3	100.3	96.4	95.5	93.2	94.2
80°	105.8	110.1	104.5	97.1	87.6	80.6	76.3	74.1	71.6	70.7	72.4
82.5°	76.0	77.9	75.0	70.0	62.9	58.5	55.5	53.0	52.5	52.7	52.7
85°	39.5	39.1	38.6	34.2	32.1	29.0	27.3	26.9	26.4	27.3	28.2
87.5°	16.2	16.3	15.7	13.9	12.5	11.0	10.3	9.5	10.3	11.0	11.7
90°	15.2	13.8	12.3	10.5	8.6	6.5	4.5	2.4	4.5	6.5	8.6
92.5°	14.6	13.1	11.7	10.8	10.8	10.6	10.5	10.4	10.5	10.6	10.8
95°	17.8	17.6	17.4	20.5	26.7	32.9	39.2	45.4	39.2	32.9	26.7
97.5°	62.8	83.2	103.8	112.0	108.2	104.3	100.4	96.4	100.4	104.3	108.2
100°	87.0	112.3	137.7	148.7	145.4	142.1	138.8	135.5	138.8	142.1	145.4
102.5°	181.7	185.1	188.3	188.7	186.4	183.9	181.5	179.1	181.5	183.9	186.4
105°	255.9	254.9	254.0	253.1	251.9	250.9	249.7	248.7	249.7	250.9	251.9
107.5°	318.9	317.6	316.3	315.4	314.9	314.3	313.8	313.2	313.8	314.3	314.9
110°	362.1	361.0	359.9	359.1	358.5	357.9	357.4	356.9	357.4	357.9	358.5



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	404.9	404.4	403.9	403.1	402.1	401.1	400.1	399.2	400.1	401.1	402.1
115°	466.3	466.4	466.6	466.4	465.9	465.4	464.8	464.2	464.8	465.4	465.9
117.5°	527.2	526.8	526.4	525.8	525.1	524.3	523.6	522.9	523.6	524.3	525.1
120°	565.4	565.6	565.7	565.5	564.8	564.0	563.3	562.6	563.3	564.0	564.8
122.5°	602.2	601.9	601.7	601.3	600.9	600.4	600.0	599.6	600.0	600.4	600.9
125°	654.9	655.3	655.7	655.5	654.8	654.0	653.3	652.6	653.3	654.0	654.8
127.5°	705.7	704.9	704.0	703.5	703.4	703.2	703.0	702.8	703.0	703.2	703.4
130°	737.4	736.9	736.3	735.9	735.7	735.6	735.4	735.2	735.4	735.6	735.7
132.5°	768.2	767.4	766.8	766.2	765.9	765.6	765.2	764.9	765.2	765.6	765.9
135°	810.6	809.8	809.1	808.8	808.9	809.2	809.3	809.5	809.3	809.2	808.9
137.5°	851.3	850.5	849.7	849.3	849.2	849.1	849.1	849.0	849.1	849.1	849.2
140°	877.3	877.0	876.6	876.3	875.9	875.5	875.1	874.8	875.1	875.5	875.9
142.5°	901.4	901.2	901.0	900.6	899.9	899.2	898.5	897.9	898.5	899.2	899.9
145°	935.9	935.9	935.9	935.6	935.1	934.5	934.0	933.4	934.0	934.5	935.1
147.5°	965.9	966.0	966.2	965.8	964.7	963.8	962.7	961.6	962.7	963.8	964.7
150°	985.0	985.2	985.4	985.1	984.4	983.7	982.9	982.2	982.9	983.7	984.4
152.5°	1001.2	1001.5	1001.8	1001.7	1001.1	1000.5	1000.0	999.3	1000.0	1000.5	1001.1
155°	1023.0	1023.4	1024.0	1024.2	1024.0	1023.9	1023.7	1023.4	1023.7	1023.9	1024.0
157.5°	1041.7	1042.4	1043.0	1043.3	1043.4	1043.6	1043.7	1043.8	1043.7	1043.6	1043.4
160°	1052.7	1053.0	1053.1	1053.4	1054.0	1054.6	1055.2	1055.6	1055.2	1054.6	1054.0
162.5°	1062.7	1062.8	1063.0	1063.5	1064.1	1064.9	1065.6	1066.2	1065.6	1064.9	1064.1
165°	1075.5	1075.5	1075.5	1076.0	1076.8	1077.8	1078.7	1079.6	1078.7	1077.8	1076.8
167.5°	1085.7	1085.7	1085.9	1086.4	1087.4	1088.3	1089.2	1090.2	1089.2	1088.3	1087.4
170°	1091.7	1091.4	1091.3	1091.8	1092.8	1094.0	1095.0	1096.2	1095.0	1094.0	1092.8
172.5°	1095.6	1095.4	1095.3	1095.7	1096.8	1097.9	1099.0	1100.1	1099.0	1097.9	1096.8
175°	1099.9	1099.8	1099.6	1100.0	1101.1	1102.2	1103.3	1104.4	1103.3	1102.2	1101.1
177.5°	1102.5	1102.2	1102.0	1102.3	1103.3	1104.3	1105.4	1106.4	1105.4	1104.3	1103.3
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1026.6	1023.5	1019.0	1012.8	1007.5	1002.0	1000.6	998.5	1002.7	999.2	998.2
5°	993.0	983.8	972.2	958.7	950.9	939.6	937.4	933.1	928.8	928.4	924.0
7.5°	957.3	944.0	928.6	914.9	902.2	889.9	881.9	880.1	873.8	870.0	865.7
10°	934.4	917.9	900.2	887.1	872.5	859.4	850.3	845.1	840.7	836.0	831.7
12.5°	907.3	889.8	875.2	861.1	843.6	833.7	818.7	809.8	808.9	808.9	797.7
15°	875.9	858.5	836.0	816.0	806.5	787.4	779.2	768.7	762.3	755.8	750.6
17.5°	839.9	818.3	800.7	777.8	759.6	744.4	733.6	727.3	717.5	708.3	701.6
20°	817.3	794.3	775.8	751.5	731.5	712.8	703.8	695.0	687.7	679.9	672.5
22.5°	794.4	770.5	747.6	724.1	705.5	685.8	677.0	665.2	658.2	653.9	646.5
25°	758.4	732.4	706.4	683.8	664.7	647.3	635.7	626.6	618.7	615.3	610.5
27.5°	719.2	693.3	668.2	642.6	620.9	608.4	599.0	592.2	587.6	583.0	580.9
30°	694.2	667.3	640.4	616.6	596.6	584.1	575.4	570.6	567.1	565.0	562.8
32.5°	668.9	642.4	614.1	592.3	574.5	563.3	556.7	551.9	550.2	549.3	548.6
35°	628.3	601.4	575.4	555.9	539.0	534.7	529.0	526.4	525.5	528.6	529.9
37.5°	589.0	564.0	540.1	521.2	510.1	503.8	501.8	502.0	505.1	507.8	510.9
40°	563.7	539.4	516.9	500.3	490.0	486.1	485.2	487.4	490.8	493.9	497.3
42.5°	539.1	515.1	494.6	479.2	472.0	468.4	468.9	471.1	475.9	479.6	484.9
45°	500.8	480.9	460.9	448.3	442.3	443.1	443.1	447.0	451.8	457.5	463.1
47.5°	464.8	444.7	428.3	417.8	414.6	413.8	416.3	421.3	428.2	435.2	443.0
50°	440.5	421.4	407.2	397.6	394.1	395.4	398.9	403.7	411.9	420.6	428.8
52.5°	415.9	398.6	385.3	376.4	374.1	376.3	379.8	387.3	394.6	404.0	413.9
55°	377.6	362.9	352.5	346.0	345.1	346.4	350.3	358.6	369.0	380.7	390.3
57.5°	339.6	327.3	317.7	313.2	313.6	314.9	321.3	331.1	342.2	354.7	367.0
60°	314.0	302.6	294.9	291.4	291.8	294.4	302.2	311.4	325.2	337.4	350.3
62.5°	289.7	279.7	272.3	269.2	268.6	274.3	281.8	291.2	305.1	318.6	332.6
65°	250.6	242.8	236.8	235.1	236.4	240.7	250.2	262.8	274.5	288.8	303.5
67.5°	212.5	206.0	201.9	202.7	204.2	210.7	218.7	229.4	242.7	257.6	272.1
70°	188.2	182.1	178.6	179.0	181.6	189.5	196.4	207.2	221.6	236.8	248.9
72.5°	163.2	159.2	156.1	157.9	160.5	165.9	174.6	185.4	198.0	212.1	224.9
75°	125.3	125.3	123.6	124.9	128.8	134.0	140.5	151.7	164.4	175.6	186.1
77.5°	92.9	92.0	93.1	94.7	96.9	103.1	110.6	118.6	128.1	139.3	148.0
80°	71.1	71.6	73.7	76.3	77.2	81.9	89.8	97.1	104.5	114.1	122.3
82.5°	53.4	53.9	55.0	58.3	59.1	64.2	69.3	76.6	83.3	89.8	96.6
85°	29.0	29.0	31.2	32.5	34.7	38.2	41.2	45.5	51.6	55.9	62.5
87.5°	13.2	13.5	15.2	16.2	17.5	19.6	20.5	24.5	26.2	28.1	31.4
90°	10.5	12.3	13.8	15.2	16.7	18.2	19.2	20.4	21.4	22.6	23.3
92.5°	10.8	11.7	13.1	14.6	16.1	17.5	18.6	19.7	20.8	21.9	22.5
95°	20.5	17.4	17.6	17.8	18.0	18.2	19.2	20.4	21.4	22.6	23.2
97.5°	112.0	103.8	83.2	62.8	42.3	21.8	21.9	22.0	22.2	22.3	22.4
100°	148.7	137.7	112.3	87.0	61.7	36.4	33.3	30.1	27.0	23.9	22.4
102.5°	188.7	188.3	185.1	181.7	178.4	175.1	141.5	107.8	74.1	40.4	23.6
105°	253.1	254.0	254.9	255.9	256.8	257.7	259.3	261.1	262.7	264.3	261.9
107.5°	315.4	316.3	317.6	318.9	320.1	321.3	322.1	322.9	323.8	324.6	325.3
110°	359.1	359.9	361.0	362.1	363.2	364.3	364.7	365.0	365.4	365.7	366.2



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	403.1	403.9	404.4	404.9	405.4	405.9	405.9	405.8	405.7	405.6	405.9
115°	466.4	466.6	466.4	466.3	466.1	465.9	466.3	466.6	467.0	467.3	467.6
117.5°	525.8	526.4	526.8	527.2	527.6	528.0	527.9	527.8	527.8	527.7	527.7
120°	565.5	565.7	565.6	565.4	565.2	565.0	565.4	565.7	566.1	566.5	566.5
122.5°	601.3	601.7	601.9	602.2	602.4	602.7	602.9	603.2	603.3	603.6	603.5
125°	655.5	655.7	655.3	654.9	654.6	654.2	654.8	655.3	655.9	656.4	656.8
127.5°	703.5	704.0	704.9	705.7	706.5	707.4	707.4	707.2	707.1	706.9	706.9
130°	735.9	736.3	736.9	737.4	737.9	738.5	738.7	738.8	739.1	739.2	739.3
132.5°	766.2	766.8	767.4	768.2	768.8	769.6	769.7	769.9	770.1	770.3	770.3
135°	808.8	809.1	809.8	810.6	811.3	812.0	812.4	812.8	813.1	813.5	813.8
137.5°	849.3	849.7	850.5	851.3	852.2	853.0	853.4	853.8	854.2	854.6	854.8
140°	876.3	876.6	877.0	877.3	877.8	878.1	878.6	879.2	879.7	880.3	880.7
142.5°	900.6	901.0	901.2	901.4	901.6	901.9	902.3	902.7	903.1	903.5	903.7
145°	935.6	935.9	935.9	935.9	935.9	935.9	936.1	936.3	936.5	936.6	936.9
147.5°	965.8	966.2	966.0	965.9	965.6	965.5	965.6	965.8	965.9	966.0	966.2
150°	985.1	985.4	985.2	985.0	984.8	984.6	984.6	984.6	984.6	984.6	984.7
152.5°	1001.7	1001.8	1001.5	1001.2	1000.9	1000.5	1000.8	1001.1	1001.4	1001.7	1001.8
155°	1024.2	1024.0	1023.4	1023.0	1022.4	1021.8	1022.5	1023.3	1024.0	1024.7	1024.8
157.5°	1043.3	1043.0	1042.4	1041.7	1041.1	1040.5	1041.5	1042.4	1043.3	1044.3	1044.3
160°	1053.4	1053.1	1053.0	1052.7	1052.6	1052.4	1053.4	1054.6	1055.6	1056.8	1056.8
162.5°	1063.5	1063.0	1062.8	1062.7	1062.5	1062.3	1063.4	1064.5	1065.6	1066.7	1066.7
165°	1076.0	1075.5	1075.5	1075.5	1075.5	1075.5	1077.0	1078.5	1079.9	1081.4	1081.2
167.5°	1086.4	1085.9	1085.7	1085.7	1085.6	1085.4	1087.0	1088.7	1090.3	1091.8	1091.8
170°	1091.8	1091.3	1091.4	1091.7	1091.8	1092.0	1093.5	1094.9	1096.4	1097.9	1097.7
172.5°	1095.7	1095.3	1095.4	1095.6	1095.8	1096.0	1097.5	1098.9	1100.4	1101.9	1101.6
175°	1100.0	1099.6	1099.8	1099.9	1100.1	1100.3	1102.0	1103.6	1105.2	1106.9	1106.6
177.5°	1102.3	1102.0	1102.2	1102.5	1102.8	1103.1	1104.2	1105.5	1106.6	1107.8	1107.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	997.4	996.8	994.3	994.0	994.3	996.8	997.4	998.2	999.2	1002.7	998.5
5°	921.5	919.2	917.9	922.8	917.9	919.2	921.5	924.0	928.4	928.8	933.1
7.5°	864.1	862.3	858.5	857.4	858.5	862.3	864.1	865.7	870.0	873.8	880.1
10°	827.3	825.6	822.1	821.3	822.1	825.6	827.3	831.7	836.0	840.7	845.1
12.5°	791.9	788.5	787.7	788.6	787.7	788.5	791.9	797.7	808.9	808.9	809.8
15°	744.9	743.2	738.4	739.7	738.4	743.2	744.9	750.6	755.8	762.3	768.7
17.5°	698.6	696.5	690.7	695.9	690.7	696.5	698.6	701.6	708.3	717.5	727.3
20°	669.5	666.0	663.0	662.5	663.0	666.0	669.5	672.5	679.9	687.7	695.0
22.5°	641.7	638.6	638.4	635.5	638.4	638.6	641.7	646.5	653.9	658.2	665.2
25°	607.1	604.1	603.2	601.0	603.2	604.1	607.1	610.5	615.3	618.7	626.6
27.5°	580.4	578.9	577.4	578.0	577.4	578.9	580.4	580.9	583.0	587.6	592.2
30°	564.1	563.7	562.8	562.8	562.8	563.7	564.1	562.8	565.0	567.1	570.6
32.5°	550.6	550.5	551.1	551.1	551.1	550.5	550.6	548.6	549.3	550.2	551.9
35°	531.6	532.9	533.8	532.5	533.8	532.9	531.6	529.9	528.6	525.5	526.4
37.5°	514.5	515.8	517.0	518.4	517.0	515.8	514.5	510.9	507.8	505.1	502.0
40°	501.2	504.3	505.2	507.4	505.2	504.3	501.2	497.3	493.9	490.8	487.4
42.5°	488.8	492.1	494.4	494.8	494.4	492.1	488.8	484.9	479.6	475.9	471.1
45°	469.6	473.0	476.1	476.1	476.1	473.0	469.6	463.1	457.5	451.8	447.0
47.5°	449.7	454.8	457.8	458.6	457.8	454.8	449.7	443.0	435.2	428.2	421.3
50°	436.2	442.3	445.3	447.5	445.3	442.3	436.2	428.8	420.6	411.9	403.7
52.5°	423.1	429.1	433.2	434.3	433.2	429.1	423.1	413.9	404.0	394.6	387.3
55°	400.2	408.9	413.7	415.4	413.7	408.9	400.2	390.3	380.7	369.0	358.6
57.5°	378.7	386.7	392.2	393.5	392.2	386.7	378.7	367.0	354.7	342.2	331.1
60°	362.1	370.7	377.6	379.0	377.6	370.7	362.1	350.3	337.4	325.2	311.4
62.5°	345.0	354.1	360.4	363.7	360.4	354.1	345.0	332.6	318.6	305.1	291.2
65°	315.7	324.7	330.8	332.2	330.8	324.7	315.7	303.5	288.8	274.5	262.8
67.5°	283.6	292.7	296.7	299.2	296.7	292.7	283.6	272.1	257.6	242.7	229.4
70°	261.1	268.4	272.7	274.9	272.7	268.4	261.1	248.9	236.8	221.6	207.2
72.5°	235.4	243.0	248.1	248.5	248.1	243.0	235.4	224.9	212.1	198.0	185.4
75°	196.0	202.9	205.5	205.5	205.5	202.9	196.0	186.1	175.6	164.4	151.7
77.5°	155.2	158.7	162.0	162.7	162.0	158.7	155.2	148.0	139.3	128.1	118.6
80°	128.8	130.9	133.5	133.5	133.5	130.9	128.8	122.3	114.1	104.5	97.1
82.5°	101.7	103.5	106.2	105.8	106.2	103.5	101.7	96.6	89.8	83.3	76.6
85°	61.6	65.5	65.1	64.2	65.1	65.5	61.6	62.5	55.9	51.6	45.5
87.5°	32.4	32.9	34.0	34.8	34.0	32.9	32.4	31.4	28.1	26.2	24.5
90°	23.6	24.1	24.4	24.8	24.4	24.1	23.6	23.3	22.6	21.4	20.4
92.5°	22.6	22.7	22.7	22.8	22.7	22.7	22.6	22.5	21.9	20.8	19.7
95°	23.4	23.6	23.8	24.0	23.8	23.6	23.4	23.2	22.6	21.4	20.4
97.5°	22.6	22.7	22.9	23.2	22.9	22.7	22.6	22.4	22.3	22.2	22.0
100°	22.6	22.7	22.9	23.2	22.9	22.7	22.6	22.4	23.9	27.0	30.1
102.5°	23.6	23.7	23.7	23.8	23.7	23.7	23.6	23.6	40.4	74.1	107.8
105°	255.3	248.7	242.1	235.5	242.1	248.7	255.3	261.9	264.3	262.7	261.1
107.5°	326.0	326.7	327.4	328.1	327.4	326.7	326.0	325.3	324.6	323.8	322.9
110°	366.8	367.3	367.9	368.4	367.9	367.3	366.8	366.2	365.7	365.4	365.0



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	406.7	407.3	408.1	408.7	408.1	407.3	406.7	405.9	405.6	405.7	405.8
115°	467.6	467.6	467.6	467.6	467.6	467.6	467.6	467.6	467.3	467.0	466.6
117.5°	527.6	527.5	527.4	527.3	527.4	527.5	527.6	527.7	527.7	527.8	527.8
120°	566.1	565.7	565.4	565.0	565.4	565.7	566.1	566.5	566.5	566.1	565.7
122.5°	603.2	602.8	602.4	602.0	602.4	602.8	603.2	603.5	603.6	603.3	603.2
125°	657.0	657.1	657.4	657.5	657.4	657.1	657.0	656.8	656.4	655.9	655.3
127.5°	706.7	706.5	706.4	706.3	706.4	706.5	706.7	706.9	706.9	707.1	707.2
130°	739.3	739.3	739.3	739.3	739.3	739.3	739.3	739.3	739.2	739.1	738.8
132.5°	770.1	770.0	769.9	769.7	769.9	770.0	770.1	770.3	770.3	770.1	769.9
135°	814.2	814.6	815.0	815.3	815.0	814.6	814.2	813.8	813.5	813.1	812.8
137.5°	854.6	854.5	854.4	854.3	854.4	854.5	854.6	854.8	854.6	854.2	853.8
140°	880.8	881.0	881.2	881.4	881.2	881.0	880.8	880.7	880.3	879.7	879.2
142.5°	903.8	903.8	903.8	903.8	903.8	903.8	903.8	903.7	903.5	903.1	902.7
145°	937.3	937.7	938.0	938.4	938.0	937.7	937.3	936.9	936.6	936.5	936.3
147.5°	966.5	966.6	966.8	966.9	966.8	966.6	966.5	966.2	966.0	965.9	965.8
150°	984.9	985.1	985.3	985.5	985.3	985.1	984.9	984.7	984.6	984.6	984.6
152.5°	1001.7	1001.5	1001.4	1001.4	1001.4	1001.5	1001.7	1001.8	1001.7	1001.4	1001.1
155°	1024.3	1023.8	1023.2	1022.6	1023.2	1023.8	1024.3	1024.8	1024.7	1024.0	1023.3
157.5°	1043.3	1042.4	1041.5	1040.5	1041.5	1042.4	1043.3	1044.3	1044.3	1043.3	1042.4
160°	1055.6	1054.6	1053.4	1052.4	1053.4	1054.6	1055.6	1056.8	1056.8	1055.6	1054.6
162.5°	1065.4	1064.1	1062.9	1061.6	1062.9	1064.1	1065.4	1066.7	1066.7	1065.6	1064.5
165°	1079.6	1078.0	1076.4	1074.6	1076.4	1078.0	1079.6	1081.2	1081.4	1079.9	1078.5
167.5°	1090.0	1088.1	1086.3	1084.4	1086.3	1088.1	1090.0	1091.8	1091.8	1090.3	1088.7
170°	1095.8	1094.1	1092.2	1090.4	1092.2	1094.1	1095.8	1097.7	1097.9	1096.4	1094.9
172.5°	1099.6	1097.6	1095.7	1093.6	1095.7	1097.6	1099.6	1101.6	1101.9	1100.4	1098.9
175°	1104.4	1102.2	1100.0	1097.8	1100.0	1102.2	1104.4	1106.6	1106.9	1105.2	1103.6
177.5°	1105.7	1104.0	1102.2	1100.5	1102.2	1104.0	1105.7	1107.5	1107.8	1106.6	1105.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1000.6	1002.0	1007.5	1012.8	1019.0	1023.5	1026.6	1030.0	1037.4	1043.3	1048.8
5°	937.4	939.6	950.9	958.7	972.2	983.8	993.0	1002.9	1014.6	1030.7	1045.5
7.5°	881.9	889.9	902.2	914.9	928.6	944.0	957.3	972.3	992.5	1014.6	1037.3
10°	850.3	859.4	872.5	887.1	900.2	917.9	934.4	952.2	975.2	1002.1	1029.0
12.5°	818.7	833.7	843.6	861.1	875.2	889.8	907.3	930.7	957.5	985.8	1018.2
15°	779.2	787.4	806.5	816.0	836.0	858.5	875.9	899.3	925.3	962.6	999.1
17.5°	733.6	744.4	759.6	777.8	800.7	818.3	839.9	864.0	896.7	933.8	979.4
20°	703.8	712.8	731.5	751.5	775.8	794.3	817.3	840.7	874.6	914.0	961.7
22.5°	677.0	685.8	705.5	724.1	747.6	770.5	794.4	821.7	854.1	895.7	944.4
25°	635.7	647.3	664.7	683.8	706.4	732.4	758.4	782.7	817.3	861.1	913.2
27.5°	599.0	608.4	620.9	642.6	668.2	693.3	719.2	749.7	783.0	829.3	883.4
30°	575.4	584.1	596.6	616.6	640.4	667.3	694.2	723.7	758.4	804.4	859.4
32.5°	556.7	563.3	574.5	592.3	614.1	642.4	668.9	699.4	735.8	781.1	834.8
35°	529.0	534.7	539.0	555.9	575.4	601.4	628.3	660.8	695.9	738.9	792.6
37.5°	501.8	503.8	510.1	521.2	540.1	564.0	589.0	621.0	657.0	700.6	749.1
40°	485.2	486.1	490.0	500.3	516.9	539.4	563.7	595.3	629.6	670.8	718.9
42.5°	468.9	468.4	472.0	479.2	494.6	515.1	539.1	567.9	602.2	640.3	685.6
45°	443.1	443.1	442.3	448.3	460.9	480.9	500.8	528.6	557.2	594.5	632.7
47.5°	416.3	413.8	414.6	417.8	428.3	444.7	464.8	487.5	512.8	544.4	577.8
50°	398.9	395.4	394.1	397.6	407.2	421.4	440.5	460.5	484.4	512.1	540.7
52.5°	379.8	376.3	374.1	376.4	385.3	398.6	415.9	433.4	454.9	477.4	502.2
55°	350.3	346.4	345.1	346.0	352.5	362.9	377.6	393.7	409.8	428.4	445.7
57.5°	321.3	314.9	313.6	313.2	317.7	327.3	339.6	353.5	365.2	376.4	394.9
60°	302.2	294.4	291.8	291.4	294.9	302.6	314.0	327.8	336.1	343.8	359.9
62.5°	281.8	274.3	268.6	269.2	272.3	279.7	289.7	299.7	305.2	313.6	324.5
65°	250.2	240.7	236.4	235.1	236.8	242.8	250.6	257.1	263.2	266.7	277.0
67.5°	218.7	210.7	204.2	202.7	201.9	206.0	212.5	216.4	220.7	223.7	229.9
70°	196.4	189.5	181.6	179.0	178.6	182.1	188.2	188.6	194.7	196.0	202.5
72.5°	174.6	165.9	160.5	157.9	156.1	159.2	163.2	164.4	167.6	170.0	173.3
75°	140.5	134.0	128.8	124.9	123.6	125.3	125.3	127.5	129.6	130.9	134.9
77.5°	110.6	103.1	96.9	94.7	93.1	92.0	92.9	94.2	93.2	95.5	96.4
80°	89.8	81.9	77.2	76.3	73.7	71.6	71.1	72.4	70.7	71.6	74.1
82.5°	69.3	64.2	59.1	58.3	55.0	53.9	53.4	52.7	52.7	52.5	53.0
85°	41.2	38.2	34.7	32.5	31.2	29.0	29.0	28.2	27.3	26.4	26.9
87.5°	20.5	19.6	17.5	16.2	15.2	13.5	13.2	11.7	11.0	10.3	9.5
90°	19.2	18.2	16.7	15.2	13.8	12.3	10.5	8.6	6.5	4.5	2.4
92.5°	18.6	17.5	16.1	14.6	13.1	11.7	10.8	10.8	10.6	10.5	10.4
95°	19.2	18.2	18.0	17.8	17.6	17.4	20.5	26.7	32.9	39.2	45.4
97.5°	21.9	21.8	42.3	62.8	83.2	103.8	112.0	108.2	104.3	100.4	96.4
100°	33.3	36.4	61.7	87.0	112.3	137.7	148.7	145.4	142.1	138.8	135.5
102.5°	141.5	175.1	178.4	181.7	185.1	188.3	188.7	186.4	183.9	181.5	179.1
105°	259.3	257.7	256.8	255.9	254.9	254.0	253.1	251.9	250.9	249.7	248.7
107.5°	322.1	321.3	320.1	318.9	317.6	316.3	315.4	314.9	314.3	313.8	313.2
110°	364.7	364.3	363.2	362.1	361.0	359.9	359.1	358.5	357.9	357.4	356.9



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	405.9	405.9	405.4	404.9	404.4	403.9	403.1	402.1	401.1	400.1	399.2
115°	466.3	465.9	466.1	466.3	466.4	466.6	466.4	465.9	465.4	464.8	464.2
117.5°	527.9	528.0	527.6	527.2	526.8	526.4	525.8	525.1	524.3	523.6	522.9
120°	565.4	565.0	565.2	565.4	565.6	565.7	565.5	564.8	564.0	563.3	562.6
122.5°	602.9	602.7	602.4	602.2	601.9	601.7	601.3	600.9	600.4	600.0	599.6
125°	654.8	654.2	654.6	654.9	655.3	655.7	655.5	654.8	654.0	653.3	652.6
127.5°	707.4	707.4	706.5	705.7	704.9	704.0	703.5	703.4	703.2	703.0	702.8
130°	738.7	738.5	737.9	737.4	736.9	736.3	735.9	735.7	735.6	735.4	735.2
132.5°	769.7	769.6	768.8	768.2	767.4	766.8	766.2	765.9	765.6	765.2	764.9
135°	812.4	812.0	811.3	810.6	809.8	809.1	808.8	808.9	809.2	809.3	809.5
137.5°	853.4	853.0	852.2	851.3	850.5	849.7	849.3	849.2	849.1	849.1	849.0
140°	878.6	878.1	877.8	877.3	877.0	876.6	876.3	875.9	875.5	875.1	874.8
142.5°	902.3	901.9	901.6	901.4	901.2	901.0	900.6	899.9	899.2	898.5	897.9
145°	936.1	935.9	935.9	935.9	935.9	935.9	935.6	935.1	934.5	934.0	933.4
147.5°	965.6	965.5	965.6	965.9	966.0	966.2	965.8	964.7	963.8	962.7	961.6
150°	984.6	984.6	984.8	985.0	985.2	985.4	985.1	984.4	983.7	982.9	982.2
152.5°	1000.8	1000.5	1000.9	1001.2	1001.5	1001.8	1001.7	1001.1	1000.5	1000.0	999.3
155°	1022.5	1021.8	1022.4	1023.0	1023.4	1024.0	1024.2	1024.0	1023.9	1023.7	1023.4
157.5°	1041.5	1040.5	1041.1	1041.7	1042.4	1043.0	1043.3	1043.4	1043.6	1043.7	1043.8
160°	1053.4	1052.4	1052.6	1052.7	1053.0	1053.1	1053.4	1054.0	1054.6	1055.2	1055.6
162.5°	1063.4	1062.3	1062.5	1062.7	1062.8	1063.0	1063.5	1064.1	1064.9	1065.6	1066.2
165°	1077.0	1075.5	1075.5	1075.5	1075.5	1075.5	1076.0	1076.8	1077.8	1078.7	1079.6
167.5°	1087.0	1085.4	1085.6	1085.7	1085.7	1085.9	1086.4	1087.4	1088.3	1089.2	1090.2
170°	1093.5	1092.0	1091.8	1091.7	1091.4	1091.3	1091.8	1092.8	1094.0	1095.0	1096.2
172.5°	1097.5	1096.0	1095.8	1095.6	1095.4	1095.3	1095.7	1096.8	1097.9	1099.0	1100.1
175°	1102.0	1100.3	1100.1	1099.9	1099.8	1099.6	1100.0	1101.1	1102.2	1103.3	1104.4
177.5°	1104.2	1103.1	1102.8	1102.5	1102.2	1102.0	1102.3	1103.3	1104.3	1105.4	1106.4
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1053.7	1057.1	1061.7	1069.3	1072.0	1075.5	1080.4	1080.0	1081.4	1086.6	1097.7
5°	1057.6	1071.0	1084.0	1099.6	1116.1	1126.9	1141.7	1150.8	1159.9	1171.6	1191.6
7.5°	1059.2	1080.4	1104.3	1131.7	1156.1	1184.2	1206.2	1226.8	1245.4	1270.2	1293.9
10°	1056.7	1085.3	1116.1	1150.8	1187.6	1218.9	1247.1	1279.1	1306.4	1336.4	1363.3
12.5°	1052.2	1086.7	1127.9	1166.8	1209.8	1256.0	1291.1	1323.6	1359.9	1394.3	1435.7
15°	1042.0	1089.2	1137.3	1188.5	1246.2	1299.5	1350.2	1392.3	1431.3	1482.9	1537.2
17.5°	1029.0	1079.9	1140.7	1202.6	1262.8	1323.8	1386.6	1449.8	1499.1	1563.2	1605.6
20°	1016.8	1075.8	1138.2	1211.9	1272.2	1348.1	1410.5	1471.7	1539.3	1603.0	1653.8
22.5°	999.8	1064.4	1130.6	1204.0	1283.3	1359.2	1431.3	1497.7	1565.3	1634.6	1696.1
25°	978.2	1036.7	1115.2	1198.5	1277.4	1359.8	1442.6	1525.8	1598.7	1672.0	1729.2
27.5°	941.4	1015.4	1088.4	1174.4	1262.1	1355.3	1443.8	1531.0	1607.3	1667.5	1703.0
30°	922.8	986.9	1066.2	1152.5	1247.5	1347.7	1440.0	1525.4	1596.5	1644.7	1659.0
32.5°	895.0	961.2	1038.9	1128.2	1228.7	1331.7	1427.8	1508.5	1567.7	1593.0	1575.7
35°	853.8	913.6	992.1	1083.6	1188.1	1297.8	1392.8	1460.9	1491.2	1467.3	1407.9
37.5°	804.4	863.6	942.5	1032.3	1140.4	1252.0	1337.8	1386.8	1376.8	1317.4	1228.9
40°	769.6	825.2	900.2	997.3	1102.7	1214.6	1290.0	1316.5	1288.7	1203.7	1109.6
42.5°	731.2	785.3	860.6	954.3	1065.9	1169.1	1234.9	1237.0	1190.5	1088.9	994.4
45°	672.5	724.1	795.2	892.8	996.0	1093.2	1136.4	1115.2	1029.4	931.4	836.4
47.5°	614.7	659.4	729.5	822.1	920.1	1001.9	1023.4	985.1	893.6	798.5	710.5
50°	572.3	617.4	683.4	771.8	866.3	937.0	947.5	896.7	807.0	711.1	642.2
52.5°	531.7	576.5	640.0	721.9	808.5	872.1	872.5	813.8	724.4	639.0	574.9
55°	472.2	512.5	569.7	643.0	720.2	770.1	758.0	697.2	619.6	545.5	489.5
57.5°	414.8	449.9	502.6	563.8	631.8	672.9	652.7	594.3	525.0	462.1	419.7
60°	377.6	411.1	456.2	513.8	571.0	603.2	584.1	531.2	467.4	416.7	379.8
62.5°	341.6	369.8	413.1	463.2	516.2	540.1	523.0	470.8	415.7	369.9	340.0
65°	290.5	313.5	348.2	391.1	429.7	450.0	435.8	387.2	345.1	312.2	288.4
67.5°	242.8	260.7	287.1	321.5	354.2	365.3	352.3	318.5	282.8	256.4	239.6
70°	209.9	226.8	248.9	275.3	303.9	315.7	302.6	275.7	246.7	222.4	205.9
72.5°	181.1	194.2	212.8	235.5	257.8	269.5	260.7	234.8	210.3	192.2	178.2
75°	137.9	149.2	162.2	178.2	195.6	203.3	195.6	177.8	160.9	147.4	137.5
77.5°	100.3	106.3	116.3	128.3	139.2	145.2	138.4	126.4	116.0	106.8	101.9
80°	76.3	80.6	87.6	97.1	104.5	110.1	105.8	95.8	87.6	81.5	79.3
82.5°	55.5	58.5	62.9	70.0	75.0	77.9	76.0	68.7	65.4	60.0	57.8
85°	27.3	29.0	32.1	34.2	38.6	39.1	39.5	36.4	33.4	32.1	30.3
87.5°	10.3	11.0	12.5	13.9	15.7	16.3	16.2	16.6	15.4	15.3	14.1
90°	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2	20.4
92.5°	10.5	10.6	10.8	10.8	11.7	13.1	14.6	16.1	17.5	18.6	19.7
95°	39.2	32.9	26.7	20.5	17.4	17.6	17.8	18.0	18.2	19.2	20.4
97.5°	100.4	104.3	108.2	112.0	103.8	83.2	62.8	42.3	21.8	21.9	22.0
100°	138.8	142.1	145.4	148.7	137.7	112.3	87.0	61.7	36.4	33.3	30.1
102.5°	181.5	183.9	186.4	188.7	188.3	185.1	181.7	178.4	175.1	141.5	107.8
105°	249.7	250.9	251.9	253.1	254.0	254.9	255.9	256.8	257.7	259.3	261.1
107.5°	313.8	314.3	314.9	315.4	316.3	317.6	318.9	320.1	321.3	322.1	322.9
110°	357.4	357.9	358.5	359.1	359.9	361.0	362.1	363.2	364.3	364.7	365.0



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	400.1	401.1	402.1	403.1	403.9	404.4	404.9	405.4	405.9	405.9	405.8
115°	464.8	465.4	465.9	466.4	466.6	466.4	466.3	466.1	465.9	466.3	466.6
117.5°	523.6	524.3	525.1	525.8	526.4	526.8	527.2	527.6	528.0	527.9	527.8
120°	563.3	564.0	564.8	565.5	565.7	565.6	565.4	565.2	565.0	565.4	565.7
122.5°	600.0	600.4	600.9	601.3	601.7	601.9	602.2	602.4	602.7	602.9	603.2
125°	653.3	654.0	654.8	655.5	655.7	655.3	654.9	654.6	654.2	654.8	655.3
127.5°	703.0	703.2	703.4	703.5	704.0	704.9	705.7	706.5	707.4	707.4	707.2
130°	735.4	735.6	735.7	735.9	736.3	736.9	737.4	737.9	738.5	738.7	738.8
132.5°	765.2	765.6	765.9	766.2	766.8	767.4	768.2	768.8	769.6	769.7	769.9
135°	809.3	809.2	808.9	808.8	809.1	809.8	810.6	811.3	812.0	812.4	812.8
137.5°	849.1	849.1	849.2	849.3	849.7	850.5	851.3	852.2	853.0	853.4	853.8
140°	875.1	875.5	875.9	876.3	876.6	877.0	877.3	877.8	878.1	878.6	879.2
142.5°	898.5	899.2	899.9	900.6	901.0	901.2	901.4	901.6	901.9	902.3	902.7
145°	934.0	934.5	935.1	935.6	935.9	935.9	935.9	935.9	935.9	936.1	936.3
147.5°	962.7	963.8	964.7	965.8	966.2	966.0	965.9	965.6	965.5	965.6	965.8
150°	982.9	983.7	984.4	985.1	985.4	985.2	985.0	984.8	984.6	984.6	984.6
152.5°	1000.0	1000.5	1001.1	1001.7	1001.8	1001.5	1001.2	1000.9	1000.5	1000.8	1001.1
155°	1023.7	1023.9	1024.0	1024.2	1024.0	1023.4	1023.0	1022.4	1021.8	1022.5	1023.3
157.5°	1043.7	1043.6	1043.4	1043.3	1043.0	1042.4	1041.7	1041.1	1040.5	1041.5	1042.4
160°	1055.2	1054.6	1054.0	1053.4	1053.1	1053.0	1052.7	1052.6	1052.4	1053.4	1054.6
162.5°	1065.6	1064.9	1064.1	1063.5	1063.0	1062.8	1062.7	1062.5	1062.3	1063.4	1064.5
165°	1078.7	1077.8	1076.8	1076.0	1075.5	1075.5	1075.5	1075.5	1075.5	1077.0	1078.5
167.5°	1089.2	1088.3	1087.4	1086.4	1085.9	1085.7	1085.7	1085.6	1085.4	1087.0	1088.7
170°	1095.0	1094.0	1092.8	1091.8	1091.3	1091.4	1091.7	1091.8	1092.0	1093.5	1094.9
172.5°	1099.0	1097.9	1096.8	1095.7	1095.3	1095.4	1095.6	1095.8	1096.0	1097.5	1098.9
175°	1103.3	1102.2	1101.1	1100.0	1099.6	1099.8	1099.9	1100.1	1100.3	1102.0	1103.6
177.5°	1105.4	1104.3	1103.3	1102.3	1102.0	1102.2	1102.5	1102.8	1103.1	1104.2	1105.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1103.3	1104.0	1107.1	1109.5	1110.2	1113.7	1114.0
5°	1200.2	1207.6	1221.9	1223.2	1225.4	1236.6	1228.0
7.5°	1313.9	1332.5	1345.1	1356.1	1360.1	1365.0	1364.0
10°	1386.7	1414.5	1428.3	1450.4	1451.3	1456.9	1453.4
12.5°	1459.9	1492.2	1517.4	1521.5	1540.1	1543.0	1547.8
15°	1563.6	1597.8	1633.0	1645.5	1671.1	1677.2	1686.8
17.5°	1661.1	1696.1	1720.7	1753.2	1763.7	1777.8	1768.2
20°	1714.5	1752.6	1783.9	1809.5	1820.3	1828.1	1827.2
22.5°	1746.8	1785.3	1810.5	1829.9	1840.0	1843.4	1843.1
25°	1766.9	1789.1	1796.8	1804.3	1793.0	1789.1	1790.8
27.5°	1710.7	1705.0	1684.7	1657.9	1630.2	1608.2	1596.2
30°	1633.4	1599.6	1568.8	1515.0	1487.3	1470.8	1456.0
32.5°	1523.8	1470.2	1411.0	1361.7	1330.2	1305.7	1302.0
35°	1335.9	1255.3	1182.9	1122.6	1091.4	1064.9	1058.8
37.5°	1135.8	1052.0	986.8	933.8	900.2	881.5	864.1
40°	1002.9	931.0	866.7	821.7	796.1	782.7	771.8
42.5°	900.6	834.9	771.0	736.7	713.5	705.3	699.0
45°	759.2	698.1	653.9	627.9	614.4	600.5	594.0
47.5°	646.0	596.3	567.1	545.0	530.7	522.4	518.3
50°	581.9	541.1	515.1	498.2	485.2	478.7	475.2
52.5°	525.0	491.5	469.7	456.2	447.4	442.6	441.2
55°	452.2	426.6	412.8	401.1	394.6	390.3	388.5
57.5°	393.1	373.4	362.2	352.5	350.0	346.3	345.1
60°	354.2	339.1	329.5	323.0	320.9	316.5	317.4
62.5°	319.9	307.5	299.4	295.6	292.8	289.1	290.3
65°	270.6	261.5	257.1	253.6	250.2	248.0	249.7
67.5°	227.1	220.8	214.9	212.9	211.2	210.8	209.0
70°	198.6	193.4	188.2	186.9	186.9	185.2	184.7
72.5°	171.2	167.4	163.9	163.0	161.6	162.2	160.5
75°	132.2	129.2	127.9	126.6	126.2	126.2	124.9
77.5°	97.8	95.5	93.4	93.4	91.8	91.2	91.1
80°	74.1	73.3	71.6	71.6	70.7	71.1	70.3
82.5°	55.8	54.5	54.2	53.5	52.3	52.3	51.5
85°	29.9	28.6	28.2	26.9	26.0	26.9	26.0
87.5°	14.7	14.6	14.3	13.8	13.5	13.5	12.6
90°	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	20.8	21.9	22.5	22.6	22.7	22.7	22.8
95°	21.4	22.6	23.2	23.4	23.6	23.8	24.0
97.5°	22.2	22.3	22.4	22.6	22.7	22.9	23.2
100°	27.0	23.9	22.4	22.6	22.7	22.9	23.2
102.5°	74.1	40.4	23.6	23.6	23.7	23.7	23.8
105°	262.7	264.3	261.9	255.3	248.7	242.1	235.5
107.5°	323.8	324.6	325.3	326.0	326.7	327.4	328.1
110°	365.4	365.7	366.2	366.8	367.3	367.9	368.4



TEST NUMBER: P332787-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	405.7	405.6	405.9	406.7	407.3	408.1	408.7
115°	467.0	467.3	467.6	467.6	467.6	467.6	467.6
117.5°	527.8	527.7	527.7	527.6	527.5	527.4	527.3
120°	566.1	566.5	566.5	566.1	565.7	565.4	565.0
122.5°	603.3	603.6	603.5	603.2	602.8	602.4	602.0
125°	655.9	656.4	656.8	657.0	657.1	657.4	657.5
127.5°	707.1	706.9	706.9	706.7	706.5	706.4	706.3
130°	739.1	739.2	739.3	739.3	739.3	739.3	739.3
132.5°	770.1	770.3	770.3	770.1	770.0	769.9	769.7
135°	813.1	813.5	813.8	814.2	814.6	815.0	815.3
137.5°	854.2	854.6	854.8	854.6	854.5	854.4	854.3
140°	879.7	880.3	880.7	880.8	881.0	881.2	881.4
142.5°	903.1	903.5	903.7	903.8	903.8	903.8	903.8
145°	936.5	936.6	936.9	937.3	937.7	938.0	938.4
147.5°	965.9	966.0	966.2	966.5	966.6	966.8	966.9
150°	984.6	984.6	984.7	984.9	985.1	985.3	985.5
152.5°	1001.4	1001.7	1001.8	1001.7	1001.5	1001.4	1001.4
155°	1024.0	1024.7	1024.8	1024.3	1023.8	1023.2	1022.6
157.5°	1043.3	1044.3	1044.3	1043.3	1042.4	1041.5	1040.5
160°	1055.6	1056.8	1056.8	1055.6	1054.6	1053.4	1052.4
162.5°	1065.6	1066.7	1066.7	1065.4	1064.1	1062.9	1061.6
165°	1079.9	1081.4	1081.2	1079.6	1078.0	1076.4	1074.6
167.5°	1090.3	1091.8	1091.8	1090.0	1088.1	1086.3	1084.4
170°	1096.4	1097.9	1097.7	1095.8	1094.1	1092.2	1090.4
172.5°	1100.4	1101.9	1101.6	1099.6	1097.6	1095.7	1093.6
175°	1105.2	1106.9	1106.6	1104.4	1102.2	1100.0	1097.8
177.5°	1106.6	1107.8	1107.5	1105.7	1104.0	1102.2	1100.5
180°	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4	1104.4

(END OF REPORT)