

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332792-930

Luminaire Tested: **S124DIW-S795D1050U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332792-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D1050U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5743.4 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8737	8737	8737
5°	8763	8658	8721
10°	8708	8588	8630
15°	8603	8466	8487
20°	8463	8314	8322
25°	8304	8141	8118
30°	8108	7938	7866
35°	7906	7727	7624
40°	7695	7484	7347
45°	7476	7247	7108
50°	7232	7036	6818
55°	6970	6763	6542
60°	6707	6455	6260
65°	6411	6162	5914
70°	6080	5773	5549
75°	5571	5303	5168
80°	4956	4756	4635
85°	4335	4177	4094



TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.9	1.8
10°-20°	287.2	5.0
20°-30°	422.7	7.4
30°-40°	491.4	8.6
40°-50°	491.4	8.6
50°-60°	429.8	7.5
60°-70°	319.2	5.6
70°-80°	181.4	3.2
80°-90°	55.5	1.0
90°-100°	70.4	1.2
100°-110°	208.7	3.6
110°-120°	354.2	6.2
120°-130°	467.0	8.1
130°-140°	524.5	9.1
140°-150°	515.4	9.0
150°-160°	433.5	7.5
160°-170°	288.4	5.0
170°-180°	101.0	1.8
0°-30°	811.8	14.1
0°-40°	1303.1	22.7
0°-60°	2224.4	38.7
0°-90°	2780.5	48.4
90°-120°	633.2	11.0
90°-150°	2140.1	37.3
90°-180°	2963.0	51.6
0°-180°	5743.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1081	1078	1068	1077	1076	103
15°	1029	1025	1013	1018	1016	290
25°	932	926	914	915	911	429
35°	802	796	784	778	774	501
45°	655	648	635	626	623	505
55°	495	492	480	470	465	443
65°	336	331	323	314	310	332
75°	179	174	170	167	166	190
85°	47	47	45	45	44	52
90°	2	11	18	23	25	6
95°	50	57	63	65	65	55
105°	192	193	197	199	202	204
115°	360	360	358	358	357	355
125°	524	524	524	522	520	467
135°	676	681	681	680	677	523
145°	822	825	826	825	823	514
155°	942	942	941	944	941	433
165°	1025	1023	1021	1025	1022	289
175°	1066	1062	1061	1066	1061	101
180°	1068	1068	1068	1068	1068	



TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1085.1	1084.6	1084.1	1083.7	1083.2	1082.1	1080.4	1078.7	1077.0	1075.4	1076.8
5°	1081.4	1080.7	1079.9	1079.1	1078.3	1076.8	1074.7	1072.6	1070.5	1068.4	1070.5
7.5°	1071.4	1070.6	1069.8	1069.0	1068.3	1066.7	1064.4	1062.0	1059.6	1057.3	1059.0
10°	1062.3	1061.6	1060.8	1060.1	1059.2	1057.6	1055.1	1052.6	1050.1	1047.6	1049.1
12.5°	1050.5	1049.8	1049.0	1048.2	1047.5	1045.7	1043.1	1040.4	1037.8	1035.1	1036.8
15°	1029.4	1028.6	1027.8	1027.0	1026.3	1024.5	1021.6	1018.7	1015.8	1012.9	1014.1
17.5°	1003.9	1002.9	1001.9	1001.0	1000.0	998.2	995.5	992.7	989.9	987.2	988.0
20°	985.1	984.1	983.3	982.3	981.3	979.3	976.5	973.5	970.7	967.8	968.4
22.5°	965.1	963.8	962.5	961.2	959.9	957.9	955.0	952.1	949.2	946.3	947.4
25°	932.2	930.9	929.5	928.2	926.8	924.8	922.1	919.4	916.7	914.0	914.2
27.5°	894.8	893.4	892.0	890.6	889.2	887.3	884.8	882.3	879.8	877.3	876.8
30°	869.8	868.3	866.7	865.2	863.6	861.6	859.1	856.6	854.1	851.6	850.8
32.5°	843.4	842.0	840.7	839.3	837.9	835.8	833.2	830.5	827.9	825.2	824.3
35°	802.2	800.8	799.5	798.1	796.8	794.8	792.1	789.4	786.7	784.0	782.6
37.5°	758.6	757.4	756.2	755.0	753.7	751.6	748.8	745.8	743.0	740.0	738.6
40°	730.2	728.6	727.1	725.5	724.0	721.8	718.9	716.0	713.1	710.2	708.3
42.5°	699.7	698.7	697.8	696.9	695.9	693.9	690.7	687.5	684.3	681.1	678.9
45°	654.8	653.4	652.1	650.7	649.4	647.1	644.1	641.0	637.9	634.8	632.7
47.5°	607.7	606.8	605.9	605.0	604.1	602.2	599.3	596.5	593.6	590.8	588.3
50°	575.8	575.0	574.3	573.5	572.7	571.0	568.3	565.7	562.9	560.2	557.5
52.5°	544.6	543.7	542.7	541.8	540.9	539.0	536.1	533.3	530.4	527.6	525.2
55°	495.2	494.6	494.0	493.4	492.8	491.2	488.5	485.8	483.1	480.5	478.1
57.5°	448.0	447.4	446.7	446.1	445.4	443.7	441.1	438.4	435.8	433.1	430.9
60°	415.4	414.4	413.4	412.5	411.6	409.8	407.3	404.8	402.3	399.8	398.0
62.5°	383.5	382.7	381.9	381.1	380.3	378.5	375.9	373.2	370.6	367.9	366.3
65°	335.6	334.7	333.7	332.7	331.7	330.3	328.4	326.4	324.5	322.6	320.7
67.5°	287.4	286.5	285.6	284.7	283.9	282.5	280.6	278.8	277.0	275.1	273.2
70°	257.6	256.2	254.9	253.5	252.2	250.7	249.2	247.6	246.1	244.6	243.0
72.5°	225.7	224.3	223.0	221.6	220.2	219.0	217.8	216.5	215.2	214.0	212.8
75°	178.6	177.7	176.8	175.8	174.8	173.8	172.8	171.9	171.0	170.0	169.2
77.5°	133.7	133.3	132.9	132.5	132.0	131.4	130.5	129.7	128.8	128.0	127.8
80°	106.6	106.1	105.5	104.9	104.4	103.9	103.5	103.1	102.7	102.3	101.9
82.5°	80.3	80.1	79.7	79.5	79.2	79.1	79.0	78.9	78.8	78.8	78.5
85°	46.8	46.8	46.8	46.8	46.8	46.6	46.2	45.9	45.5	45.1	45.1
87.5°	18.5	18.8	19.0	19.3	19.6	19.7	19.9	20.0	20.1	20.3	20.5
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	17.7	20.0	22.3	24.6	26.9	28.6	29.6	30.7	31.7	32.7	33.3
95°	49.6	51.2	52.8	54.5	56.2	57.6	58.9	60.2	61.5	62.8	63.3
97.5°	86.6	87.9	89.2	90.5	91.9	93.3	94.7	96.3	97.8	99.3	100.0
100°	115.6	116.3	117.1	117.8	118.5	119.8	121.4	123.0	124.7	126.4	126.7
102.5°	146.0	146.3	146.6	146.9	147.2	148.1	149.6	151.1	152.6	154.1	154.7
105°	192.4	192.7	192.8	193.0	193.1	193.6	194.4	195.1	195.8	196.6	197.1
107.5°	241.2	241.4	241.6	241.8	242.1	242.2	242.3	242.5	242.6	242.6	243.2
110°	274.2	274.6	274.9	275.3	275.7	275.7	275.6	275.4	275.2	275.0	274.7



TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.6	308.7	308.8	308.8	308.8	308.8	308.4	308.1	307.8	307.4	307.4
115°	360.1	360.1	360.1	360.1	360.1	360.0	359.5	359.2	358.8	358.5	358.2
117.5°	408.7	408.8	409.0	409.1	409.3	409.2	409.0	408.7	408.5	408.1	407.6
120°	441.1	441.8	442.5	443.3	444.0	444.1	443.5	443.0	442.5	441.9	441.0
122.5°	474.7	475.1	475.3	475.6	475.9	476.0	475.6	475.4	475.2	474.9	474.3
125°	524.5	524.5	524.5	524.5	524.5	524.4	524.2	524.0	523.8	523.7	523.3
127.5°	569.6	570.1	570.6	571.2	571.8	571.9	571.6	571.3	571.0	570.7	570.4
130°	601.3	601.9	602.3	602.9	603.5	603.7	603.7	603.7	603.7	603.7	603.4
132.5°	633.7	634.1	634.5	634.9	635.3	635.4	635.3	635.1	635.0	634.8	634.5
135°	676.5	677.5	678.7	679.7	680.9	681.4	681.4	681.4	681.4	681.4	681.0
137.5°	723.0	723.5	724.1	724.6	725.0	725.5	725.8	726.1	726.4	726.7	726.2
140°	754.1	754.5	754.8	755.2	755.5	755.7	755.7	755.7	755.7	755.7	755.5
142.5°	782.5	782.9	783.3	783.6	784.0	784.1	783.9	783.7	783.7	783.5	783.4
145°	821.8	822.6	823.3	824.0	824.8	825.2	825.4	825.6	825.7	825.9	825.7
147.5°	860.8	861.7	862.6	863.4	864.3	864.7	864.5	864.4	864.2	864.1	864.0
150°	884.6	885.3	886.1	886.8	887.5	887.9	887.9	887.9	887.9	887.9	887.9
152.5°	907.0	907.5	907.9	908.3	908.8	909.1	909.2	909.4	909.5	909.7	910.1
155°	941.6	941.6	941.6	941.6	941.6	941.5	941.3	941.1	940.9	940.8	941.5
157.5°	970.6	970.3	970.0	969.6	969.3	969.1	969.1	969.1	969.0	969.0	969.6
160°	987.8	987.7	987.4	987.2	987.1	986.9	986.7	986.5	986.3	986.2	986.7
162.5°	1003.6	1003.2	1002.7	1002.2	1001.8	1001.4	1001.3	1001.1	1000.9	1000.7	1001.7
165°	1025.0	1024.4	1023.9	1023.4	1022.8	1022.3	1022.0	1021.6	1021.2	1020.8	1022.0
167.5°	1041.3	1040.6	1039.8	1039.0	1038.3	1037.9	1038.0	1038.0	1038.0	1038.0	1039.1
170°	1050.6	1049.7	1048.7	1047.8	1046.9	1046.5	1046.8	1046.9	1047.1	1047.3	1048.4
172.5°	1057.2	1056.4	1055.6	1054.9	1054.1	1053.8	1053.8	1053.9	1053.9	1053.9	1055.2
175°	1066.2	1065.4	1064.5	1063.6	1062.6	1062.1	1061.8	1061.7	1061.5	1061.4	1062.6
177.5°	1069.3	1068.5	1067.8	1067.1	1066.3	1065.9	1065.9	1065.9	1065.9	1065.9	1067.0
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0



TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1078.4	1079.9	1081.5	1082.2	1082.1	1081.9	1081.7	1081.6
5°	1072.6	1074.7	1076.8	1077.7	1077.3	1077.0	1076.6	1076.2
7.5°	1060.7	1062.4	1064.0	1064.8	1064.6	1064.4	1064.1	1063.9
10°	1050.7	1052.2	1053.8	1054.3	1053.9	1053.5	1053.2	1052.8
12.5°	1038.5	1040.2	1041.9	1042.4	1042.0	1041.4	1040.8	1040.3
15°	1015.2	1016.4	1017.5	1017.8	1017.2	1016.7	1016.1	1015.5
17.5°	988.7	989.4	990.2	990.3	989.9	989.5	989.2	988.8
20°	969.0	969.6	970.1	970.2	969.8	969.5	969.1	968.7
22.5°	948.4	949.4	950.5	950.6	949.9	949.3	948.5	947.9
25°	914.4	914.6	914.8	914.5	913.8	913.0	912.2	911.4
27.5°	876.4	875.9	875.4	874.7	873.8	872.8	871.8	870.8
30°	850.0	849.3	848.5	847.7	846.7	845.7	844.7	843.8
32.5°	823.4	822.5	821.6	820.6	819.6	818.6	817.7	816.8
35°	781.3	779.9	778.5	777.4	776.4	775.5	774.5	773.6
37.5°	737.1	735.6	734.3	732.9	731.6	730.3	729.0	727.7
40°	706.4	704.5	702.5	701.1	700.1	699.2	698.2	697.2
42.5°	676.6	674.4	672.1	670.7	670.1	669.4	668.8	668.1
45°	630.6	628.4	626.3	625.0	624.4	623.8	623.2	622.6
47.5°	586.0	583.6	581.1	579.3	577.8	576.3	574.9	573.4
50°	554.8	552.1	549.4	547.5	546.3	545.2	544.0	542.9
52.5°	522.9	520.4	518.0	516.2	514.7	513.2	511.8	510.3
55°	475.8	473.5	471.2	469.4	468.3	467.2	465.9	464.8
57.5°	428.7	426.5	424.3	422.7	421.5	420.4	419.3	418.2
60°	396.3	394.6	392.8	391.5	390.5	389.6	388.6	387.7
62.5°	364.7	363.1	361.6	360.3	359.3	358.3	357.4	356.4
65°	318.8	316.8	314.9	313.5	312.5	311.5	310.5	309.6
67.5°	271.4	269.5	267.7	266.6	266.4	266.1	265.8	265.5
70°	241.5	239.9	238.4	237.3	236.8	236.2	235.6	235.1
72.5°	211.6	210.3	209.1	208.2	207.6	207.0	206.4	205.9
75°	168.4	167.6	166.9	166.4	166.2	166.0	165.8	165.7
77.5°	127.5	127.3	127.1	126.7	126.2	125.7	125.2	124.7
80°	101.6	101.2	100.8	100.5	100.3	100.1	100.0	99.7
82.5°	78.3	78.0	77.8	77.6	77.5	77.2	77.0	76.8
85°	45.1	45.1	45.1	45.0	44.8	44.6	44.4	44.2
87.5°	20.7	21.0	21.2	21.3	21.4	21.4	21.5	21.6
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	34.0	34.7	35.4	35.8	36.0	36.2	36.4	36.7
95°	63.8	64.4	65.0	65.2	65.2	65.2	65.2	65.2
97.5°	100.6	101.3	101.9	102.2	102.2	102.2	102.2	102.2
100°	127.1	127.4	127.8	128.0	128.0	128.0	128.0	128.0
102.5°	155.2	155.6	156.2	156.5	156.6	156.8	156.9	157.1
105°	197.7	198.2	198.8	199.3	199.9	200.4	201.0	201.5
107.5°	243.7	244.2	244.8	244.9	244.9	244.9	244.8	244.8
110°	274.3	273.9	273.5	273.7	274.2	274.8	275.3	275.9





TEST NUMBER: P332792-930

CATALOG NUMBER: S124DIW-S795D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	307.3	307.2	307.1	307.1	307.3	307.4	307.4	307.6
115°	358.1	357.9	357.8	357.5	357.3	357.2	357.0	356.8
117.5°	406.9	406.3	405.7	405.2	404.8	404.5	404.1	403.7
120°	440.0	439.1	438.2	437.9	438.3	438.6	439.0	439.4
122.5°	473.7	473.0	472.4	471.7	471.1	470.4	469.8	469.1
125°	522.9	522.5	522.2	521.8	521.5	521.1	520.7	520.3
127.5°	570.0	569.6	569.2	568.9	568.6	568.3	568.0	567.8
130°	603.0	602.7	602.3	601.8	601.0	600.3	599.6	598.8
132.5°	634.1	633.7	633.3	633.0	632.8	632.4	632.1	631.9
135°	680.7	680.3	680.0	679.5	678.9	678.3	677.8	677.3
137.5°	725.7	725.2	724.7	724.6	724.6	724.8	724.9	725.0
140°	755.4	755.2	755.0	754.8	754.6	754.5	754.2	754.1
142.5°	783.4	783.3	783.3	783.3	783.3	783.3	783.2	783.2
145°	825.6	825.4	825.2	824.8	824.3	823.7	823.2	822.6
147.5°	863.8	863.6	863.5	863.3	863.2	863.0	862.7	862.6
150°	887.9	887.9	887.9	887.8	887.6	887.5	887.2	887.0
152.5°	910.5	911.0	911.4	911.4	910.9	910.4	910.0	909.5
155°	942.2	943.0	943.7	943.7	943.0	942.2	941.5	940.8
157.5°	970.1	970.6	971.2	971.2	970.5	969.9	969.3	968.7
160°	987.2	987.8	988.4	988.1	987.2	986.3	985.5	984.5
162.5°	1002.7	1003.6	1004.7	1004.7	1003.8	1002.9	1001.9	1001.0
165°	1023.0	1024.2	1025.2	1025.4	1024.7	1023.9	1023.2	1022.5
167.5°	1040.2	1041.3	1042.4	1042.4	1041.3	1040.2	1039.0	1037.9
170°	1049.5	1050.6	1051.7	1051.6	1050.4	1049.0	1047.7	1046.4
172.5°	1056.4	1057.6	1058.9	1058.8	1057.6	1056.3	1055.0	1053.7
175°	1063.9	1065.2	1066.5	1066.5	1065.2	1063.9	1062.6	1061.4
177.5°	1068.0	1069.0	1070.1	1070.0	1068.8	1067.6	1066.5	1065.3
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0

(END OF REPORT)