

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332782-930

Luminaire Tested: **S124DIW-S795D770U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332782-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S795D770U930-4F0-1E-UDD-A1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5061.0 lumens  
Efficiency: N/A  
Efficacy: 112.5 lumens/watt  
Spacing Criteria (0/90/45): 1.31 / 1.23 / 1.41  
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332782-930  
CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	100	95	91	88	93	89	86	83	77	74	72	66	64	63	56	55	53	49
2	91	84	77	72	84	78	73	68	68	64	60	58	55	53	49	47	45	41
3	83	74	66	61	77	69	63	57	60	55	51	52	48	45	44	41	39	35
4	76	65	58	52	71	61	54	49	53	48	44	46	42	39	39	36	34	30
5	70	58	50	44	65	55	48	42	48	42	38	42	37	34	36	32	30	27
6	65	53	44	39	60	49	42	37	43	38	33	38	33	30	32	29	26	23
7	60	48	40	34	56	45	38	32	39	34	29	34	30	26	30	26	23	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	27	24	21	19
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	22	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8451	8451	8451	8451
5°	9951	8473	7478	8473
10°	11914	8435	6733	8435
15°	14098	8350	6182	8350
20°	15698	8262	5692	8262
25°	15952	8134	5353	8134
30°	13573	8011	5246	8011
35°	10435	7811	5248	7811
40°	8134	7576	5347	7576
45°	6782	7223	5436	7223
50°	5968	6791	5620	6791
55°	5468	6273	5847	6273
60°	5125	5811	6119	5811
65°	4770	5291	6346	5291
70°	4360	4780	6489	4780
75°	3896	4208	6410	4208
80°	3268	3445	6206	3445
85°	2408	2492	5947	2492



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.0	2.0
10°-20°	314.3	6.2
20°-30°	498.4	9.8
30°-40°	554.7	11.0
40°-50°	504.9	10.0
50°-60°	412.6	8.2
60°-70°	294.6	5.8
70°-80°	162.2	3.2
80°-90°	46.6	0.9
90°-100°	51.6	1.0
100°-110°	152.9	3.0
110°-120°	259.5	5.1
120°-130°	342.1	6.8
130°-140°	384.2	7.6
140°-150°	377.6	7.5
150°-160°	317.6	6.3
160°-170°	211.3	4.2
170°-180°	74.0	1.5
0°-30°	914.7	18.1
0°-40°	1469.4	29.0
0°-60°	2386.9	47.2
0°-90°	2890.3	57.1
90°-120°	463.9	9.2
90°-150°	1567.9	31.0
90°-180°	2171.0	42.9
0°-180°	5061.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1047	1047	1047	1047	1047	
5°	1228	1046	923	1046	1228	125
15°	1687	999	740	999	1687	477
25°	1791	913	601	913	1791	789
35°	1059	793	532	793	1059	672
45°	594	633	476	633	594	468
55°	388	446	415	446	388	351
65°	250	277	332	277	250	247
75°	125	135	206	135	125	133
85°	26	27	64	27	26	32
90°	18	2	18	2	18	10
95°	48	36	48	36	48	50
105°	148	141	148	141	148	156
115°	261	264	261	264	261	258
125°	381	384	381	384	381	340
135°	496	496	496	496	496	383
145°	603	602	603	602	603	377
155°	689	690	689	690	689	317
165°	749	751	749	751	749	211
175°	778	781	778	781	778	74
180°	782	782	782	782	782	



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1114.0	1113.7	1110.2	1109.5	1107.1	1104.0	1103.3	1097.7	1086.6	1081.4	1080.0
5°	1228.0	1236.6	1225.4	1223.2	1221.9	1207.6	1200.2	1191.6	1171.6	1159.9	1150.8
7.5°	1364.0	1365.0	1360.1	1356.1	1345.1	1332.5	1313.9	1293.9	1270.2	1245.4	1226.8
10°	1453.4	1456.9	1451.3	1450.4	1428.3	1414.5	1386.7	1363.3	1336.4	1306.4	1279.1
12.5°	1547.8	1543.0	1540.1	1521.5	1517.4	1492.2	1459.9	1435.7	1394.3	1359.9	1323.6
15°	1686.8	1677.2	1671.1	1645.5	1633.0	1597.8	1563.6	1537.2	1482.9	1431.3	1392.3
17.5°	1768.2	1777.8	1763.7	1753.2	1720.7	1696.1	1661.1	1605.6	1563.2	1499.1	1449.8
20°	1827.2	1828.1	1820.3	1809.5	1783.9	1752.6	1714.5	1653.8	1603.0	1539.3	1471.7
22.5°	1843.1	1843.4	1840.0	1829.9	1810.5	1785.3	1746.8	1696.1	1634.6	1565.3	1497.7
25°	1790.8	1789.1	1793.0	1804.3	1796.8	1789.1	1766.9	1729.2	1672.0	1598.7	1525.8
27.5°	1596.2	1608.2	1630.2	1657.9	1684.7	1705.0	1710.7	1703.0	1667.5	1607.3	1531.0
30°	1456.0	1470.8	1487.3	1515.0	1568.8	1599.6	1633.4	1659.0	1644.7	1596.5	1525.4
32.5°	1302.0	1305.7	1330.2	1361.7	1411.0	1470.2	1523.8	1575.7	1593.0	1567.7	1508.5
35°	1058.8	1064.9	1091.4	1122.6	1182.9	1255.3	1335.9	1407.9	1467.3	1491.2	1460.9
37.5°	864.1	881.5	900.2	933.8	986.8	1052.0	1135.8	1228.9	1317.4	1376.8	1386.8
40°	771.8	782.7	796.1	821.7	866.7	931.0	1002.9	1109.6	1203.7	1288.7	1316.5
42.5°	699.0	705.3	713.5	736.7	771.0	834.9	900.6	994.4	1088.9	1190.5	1237.0
45°	594.0	600.5	614.4	627.9	653.9	698.1	759.2	836.4	931.4	1029.4	1115.2
47.5°	518.3	522.4	530.7	545.0	567.1	596.3	646.0	710.5	798.5	893.6	985.1
50°	475.2	478.7	485.2	498.2	515.1	541.1	581.9	642.2	711.1	807.0	896.7
52.5°	441.2	442.6	447.4	456.2	469.7	491.5	525.0	574.9	639.0	724.4	813.8
55°	388.5	390.3	394.6	401.1	412.8	426.6	452.2	489.5	545.5	619.6	697.2
57.5°	345.1	346.3	350.0	352.5	362.2	373.4	393.1	419.7	462.1	525.0	594.3
60°	317.4	316.5	320.9	323.0	329.5	339.1	354.2	379.8	416.7	467.4	531.2
62.5°	290.3	289.1	292.8	295.6	299.4	307.5	319.9	340.0	369.9	415.7	470.8
65°	249.7	248.0	250.2	253.6	257.1	261.5	270.6	288.4	312.2	345.1	387.2
67.5°	209.0	210.8	211.2	212.9	214.9	220.8	227.1	239.6	256.4	282.8	318.5
70°	184.7	185.2	186.9	186.9	188.2	193.4	198.6	205.9	222.4	246.7	275.7
72.5°	160.5	162.2	161.6	163.0	163.9	167.4	171.2	178.2	192.2	210.3	234.8
75°	124.9	126.2	126.2	126.6	127.9	129.2	132.2	137.5	147.4	160.9	177.8
77.5°	91.1	91.2	91.8	93.4	93.4	95.5	97.8	101.9	106.8	116.0	126.4
80°	70.3	71.1	70.7	71.6	71.6	73.3	74.1	79.3	81.5	87.6	95.8
82.5°	51.5	52.3	52.3	53.5	54.2	54.5	55.8	57.8	60.0	65.4	68.7
85°	26.0	26.9	26.0	26.9	28.2	28.6	29.9	30.3	32.1	33.4	36.4
87.5°	11.3	12.2	12.2	12.5	13.1	13.4	13.5	13.0	14.3	14.4	15.7
90°	18.2	17.9	17.6	17.4	17.0	16.6	15.7	14.9	14.1	13.3	12.2
92.5°	26.9	26.7	26.6	26.4	26.3	25.9	25.4	24.9	24.5	24.0	23.2
95°	47.8	47.8	47.8	47.8	47.8	47.6	47.2	46.8	46.4	46.0	45.1
97.5°	74.9	74.9	74.9	74.9	74.9	74.7	74.2	73.7	73.2	72.7	71.7
100°	93.8	93.8	93.8	93.8	93.8	93.7	93.4	93.1	92.9	92.6	91.4
102.5°	115.1	115.0	114.9	114.8	114.6	114.4	114.1	113.7	113.3	112.9	111.8
105°	147.7	147.2	146.8	146.4	146.0	145.6	145.2	144.8	144.4	144.0	143.5
107.5°	179.4	179.4	179.4	179.4	179.4	179.3	178.9	178.6	178.1	177.8	177.7
110°	202.1	201.7	201.3	200.9	200.5	200.4	200.7	201.0	201.2	201.5	201.6



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	225.3	225.3	225.2	225.1	225.0	225.0	225.0	225.1	225.2	225.2	225.4
115°	261.4	261.5	261.7	261.8	262.0	262.0	262.2	262.4	262.4	262.6	262.9
117.5°	295.8	296.0	296.3	296.6	296.9	297.2	297.7	298.2	298.6	299.1	299.2
120°	321.9	321.6	321.4	321.1	320.8	321.1	321.7	322.4	323.0	323.8	324.2
122.5°	343.7	344.2	344.6	345.1	345.6	346.1	346.6	347.0	347.5	348.0	348.1
125°	381.2	381.5	381.7	382.0	382.3	382.5	382.9	383.1	383.4	383.6	383.8
127.5°	416.0	416.1	416.4	416.6	416.8	417.0	417.4	417.6	417.8	418.2	418.3
130°	438.7	439.2	439.8	440.3	440.8	441.2	441.5	441.8	442.1	442.3	442.3
132.5°	462.9	463.1	463.3	463.6	463.7	464.0	464.3	464.6	464.8	465.0	465.2
135°	496.2	496.6	497.0	497.4	497.8	498.1	498.4	498.6	499.0	499.2	499.2
137.5°	531.2	531.1	531.0	530.9	530.8	531.0	531.3	531.7	532.0	532.4	532.1
140°	552.4	552.6	552.7	552.9	553.0	553.1	553.3	553.4	553.5	553.7	553.7
142.5°	573.7	573.8	573.8	573.8	573.9	573.9	573.9	574.0	574.0	574.0	574.1
145°	602.7	603.1	603.5	603.9	604.3	604.5	604.7	604.9	605.0	605.1	605.0
147.5°	631.9	632.1	632.3	632.3	632.5	632.6	632.8	632.8	632.9	633.1	633.2
150°	649.9	650.0	650.1	650.3	650.4	650.5	650.5	650.5	650.5	650.5	650.5
152.5°	666.3	666.7	667.1	667.4	667.7	667.7	667.4	667.1	666.8	666.4	666.3
155°	689.3	689.7	690.3	690.8	691.4	691.4	690.8	690.3	689.7	689.3	689.3
157.5°	709.6	710.1	710.6	711.0	711.5	711.5	711.1	710.7	710.3	709.9	710.0
160°	721.3	721.9	722.6	723.3	724.0	724.1	723.7	723.3	722.9	722.5	722.6
162.5°	733.4	734.1	734.7	735.4	736.1	736.1	735.3	734.6	733.9	733.1	733.3
165°	749.1	749.7	750.2	750.7	751.3	751.1	750.3	749.5	748.7	747.9	748.2
167.5°	760.3	761.2	762.1	762.9	763.7	763.7	762.9	762.1	761.3	760.5	760.4
170°	766.7	767.6	768.6	769.5	770.5	770.5	769.7	768.9	768.1	767.3	767.1
172.5°	772.0	772.9	773.9	774.8	775.8	775.8	774.9	774.0	773.1	772.1	772.1
175°	777.6	778.5	779.4	780.4	781.3	781.3	780.4	779.4	778.5	777.6	777.7
177.5°	780.5	781.3	782.2	783.0	783.9	784.0	783.2	782.4	781.7	781.0	781.0
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1080.4	1075.5	1072.0	1069.3	1061.7	1057.1	1053.7	1048.8	1043.3	1037.4	1030.0
5°	1141.7	1126.9	1116.1	1099.6	1084.0	1071.0	1057.6	1045.5	1030.7	1014.6	1002.9
7.5°	1206.2	1184.2	1156.1	1131.7	1104.3	1080.4	1059.2	1037.3	1014.6	992.5	972.3
10°	1247.1	1218.9	1187.6	1150.8	1116.1	1085.3	1056.7	1029.0	1002.1	975.2	952.2
12.5°	1291.1	1256.0	1209.8	1166.8	1127.9	1086.7	1052.2	1018.2	985.8	957.5	930.7
15°	1350.2	1299.5	1246.2	1188.5	1137.3	1089.2	1042.0	999.1	962.6	925.3	899.3
17.5°	1386.6	1323.8	1262.8	1202.6	1140.7	1079.9	1029.0	979.4	933.8	896.7	864.0
20°	1410.5	1348.1	1272.2	1211.9	1138.2	1075.8	1016.8	961.7	914.0	874.6	840.7
22.5°	1431.3	1359.2	1283.3	1204.0	1130.6	1064.4	999.8	944.4	895.7	854.1	821.7
25°	1442.6	1359.8	1277.4	1198.5	1115.2	1036.7	978.2	913.2	861.1	817.3	782.7
27.5°	1443.8	1355.3	1262.1	1174.4	1088.4	1015.4	941.4	883.4	829.3	783.0	749.7
30°	1440.0	1347.7	1247.5	1152.5	1066.2	986.9	922.8	859.4	804.4	758.4	723.7
32.5°	1427.8	1331.7	1228.7	1128.2	1038.9	961.2	895.0	834.8	781.1	735.8	699.4
35°	1392.8	1297.8	1188.1	1083.6	992.1	913.6	853.8	792.6	738.9	695.9	660.8
37.5°	1337.8	1252.0	1140.4	1032.3	942.5	863.6	804.4	749.1	700.6	657.0	621.0
40°	1290.0	1214.6	1102.7	997.3	900.2	825.2	769.6	718.9	670.8	629.6	595.3
42.5°	1234.9	1169.1	1065.9	954.3	860.6	785.3	731.2	685.6	640.3	602.2	567.9
45°	1136.4	1093.2	996.0	892.8	795.2	724.1	672.5	632.7	594.5	557.2	528.6
47.5°	1023.4	1001.9	920.1	822.1	729.5	659.4	614.7	577.8	544.4	512.8	487.5
50°	947.5	937.0	866.3	771.8	683.4	617.4	572.3	540.7	512.1	484.4	460.5
52.5°	872.5	872.1	808.5	721.9	640.0	576.5	531.7	502.2	477.4	454.9	433.4
55°	758.0	770.1	720.2	643.0	569.7	512.5	472.2	445.7	428.4	409.8	393.7
57.5°	652.7	672.9	631.8	563.8	502.6	449.9	414.8	394.9	376.4	365.2	353.5
60°	584.1	603.2	571.0	513.8	456.2	411.1	377.6	359.9	343.8	336.1	327.8
62.5°	523.0	540.1	516.2	463.2	413.1	369.8	341.6	324.5	313.6	305.2	299.7
65°	435.8	450.0	429.7	391.1	348.2	313.5	290.5	277.0	266.7	263.2	257.1
67.5°	352.3	365.3	354.2	321.5	287.1	260.7	242.8	229.9	223.7	220.7	216.4
70°	302.6	315.7	303.9	275.3	248.9	226.8	209.9	202.5	196.0	194.7	188.6
72.5°	260.7	269.5	257.8	235.5	212.8	194.2	181.1	173.3	170.0	167.6	164.4
75°	195.6	203.3	195.6	178.2	162.2	149.2	137.9	134.9	130.9	129.6	127.5
77.5°	138.4	145.2	139.2	128.3	116.3	106.3	100.3	96.4	95.5	93.2	94.2
80°	105.8	110.1	104.5	97.1	87.6	80.6	76.3	74.1	71.6	70.7	72.4
82.5°	76.0	77.9	75.0	70.0	62.9	58.5	55.5	53.0	52.5	52.7	52.7
85°	39.5	39.1	38.6	34.2	32.1	29.0	27.3	26.9	26.4	27.3	28.2
87.5°	15.4	15.6	15.0	13.4	12.0	10.7	10.0	9.4	10.0	10.7	11.3
90°	11.2	10.1	9.0	7.7	6.3	4.8	3.3	1.8	3.3	4.8	6.3
92.5°	22.4	21.7	21.0	19.7	18.0	16.3	14.7	13.0	14.7	16.3	18.0
95°	44.1	43.1	42.2	41.2	39.9	38.7	37.5	36.3	37.5	38.7	39.9
97.5°	70.5	69.5	68.3	67.3	66.3	65.4	64.4	63.4	64.4	65.4	66.3
100°	90.2	88.9	87.7	86.8	86.3	85.8	85.3	84.7	85.3	85.8	86.3
102.5°	110.7	109.6	108.5	107.9	107.6	107.4	107.2	107.0	107.2	107.4	107.6
105°	142.9	142.4	141.9	141.5	141.4	141.3	141.1	141.0	141.1	141.3	141.4
107.5°	177.7	177.6	177.5	177.3	177.2	177.0	176.8	176.7	176.8	177.0	177.2
110°	201.8	201.9	202.0	201.9	201.7	201.5	201.1	200.9	201.1	201.5	201.7





TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	225.7	225.9	226.2	226.2	226.2	226.2	226.1	226.1	226.1	226.2	226.2
115°	263.2	263.4	263.7	263.8	263.8	263.8	263.8	263.8	263.8	263.8	263.8
117.5°	299.5	299.6	299.8	299.9	299.7	299.6	299.5	299.4	299.5	299.6	299.7
120°	324.6	325.0	325.3	325.3	324.7	324.2	323.7	323.1	323.7	324.2	324.7
122.5°	348.3	348.5	348.7	348.7	348.5	348.2	348.1	347.8	348.1	348.2	348.5
125°	383.9	384.0	384.2	384.3	384.3	384.3	384.3	384.3	384.3	384.3	384.3
127.5°	418.6	418.7	419.0	418.9	418.5	418.1	417.7	417.3	417.7	418.1	418.5
130°	442.3	442.3	442.3	442.1	441.7	441.3	440.9	440.5	440.9	441.3	441.7
132.5°	465.3	465.4	465.5	465.5	465.1	464.8	464.6	464.2	464.6	464.8	465.1
135°	499.2	499.2	499.2	498.8	498.0	497.2	496.4	495.6	496.4	497.2	498.0
137.5°	531.9	531.7	531.5	531.2	530.8	530.4	530.1	529.7	530.1	530.4	530.8
140°	553.7	553.7	553.7	553.5	553.3	553.0	552.7	552.4	552.7	553.0	553.3
142.5°	574.2	574.3	574.5	574.4	574.1	573.8	573.6	573.2	573.6	573.8	574.1
145°	604.9	604.7	604.5	604.2	603.7	603.2	602.6	602.1	602.6	603.2	603.7
147.5°	633.2	633.4	633.5	633.2	632.6	631.9	631.3	630.6	631.3	631.9	632.6
150°	650.5	650.5	650.5	650.2	649.7	649.1	648.6	648.1	648.6	649.1	649.7
152.5°	666.3	666.1	666.0	665.9	665.5	665.2	664.9	664.6	664.9	665.2	665.5
155°	689.5	689.6	689.7	689.8	689.8	689.8	689.8	689.8	689.8	689.8	689.8
157.5°	710.0	710.0	710.0	710.1	710.4	710.6	710.9	711.1	710.9	710.6	710.4
160°	722.8	722.9	723.0	723.2	723.3	723.4	723.6	723.7	723.6	723.4	723.3
162.5°	733.4	733.5	733.7	733.9	734.3	734.6	735.0	735.3	735.0	734.6	734.3
165°	748.4	748.7	749.0	749.3	749.7	750.2	750.6	751.0	750.6	750.2	749.7
167.5°	760.4	760.4	760.3	760.7	761.2	761.8	762.4	762.9	762.4	761.8	761.2
170°	767.0	766.9	766.7	767.0	767.7	768.3	769.0	769.7	769.0	768.3	767.7
172.5°	772.1	772.0	772.0	772.3	772.8	773.4	774.0	774.5	774.0	773.4	772.8
175°	777.8	778.0	778.1	778.5	779.2	779.8	780.5	781.2	780.5	779.8	779.2
177.5°	781.0	781.0	781.0	781.2	781.8	782.3	782.9	783.3	782.9	782.3	781.8
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1026.6	1023.5	1019.0	1012.8	1007.5	1002.0	1000.6	998.5	1002.7	999.2	998.2
5°	993.0	983.8	972.2	958.7	950.9	939.6	937.4	933.1	928.8	928.4	924.0
7.5°	957.3	944.0	928.6	914.9	902.2	889.9	881.9	880.1	873.8	870.0	865.7
10°	934.4	917.9	900.2	887.1	872.5	859.4	850.3	845.1	840.7	836.0	831.7
12.5°	907.3	889.8	875.2	861.1	843.6	833.7	818.7	809.8	808.9	808.9	797.7
15°	875.9	858.5	836.0	816.0	806.5	787.4	779.2	768.7	762.3	755.8	750.6
17.5°	839.9	818.3	800.7	777.8	759.6	744.4	733.6	727.3	717.5	708.3	701.6
20°	817.3	794.3	775.8	751.5	731.5	712.8	703.8	695.0	687.7	679.9	672.5
22.5°	794.4	770.5	747.6	724.1	705.5	685.8	677.0	665.2	658.2	653.9	646.5
25°	758.4	732.4	706.4	683.8	664.7	647.3	635.7	626.6	618.7	615.3	610.5
27.5°	719.2	693.3	668.2	642.6	620.9	608.4	599.0	592.2	587.6	583.0	580.9
30°	694.2	667.3	640.4	616.6	596.6	584.1	575.4	570.6	567.1	565.0	562.8
32.5°	668.9	642.4	614.1	592.3	574.5	563.3	556.7	551.9	550.2	549.3	548.6
35°	628.3	601.4	575.4	555.9	539.0	534.7	529.0	526.4	525.5	528.6	529.9
37.5°	589.0	564.0	540.1	521.2	510.1	503.8	501.8	502.0	505.1	507.8	510.9
40°	563.7	539.4	516.9	500.3	490.0	486.1	485.2	487.4	490.8	493.9	497.3
42.5°	539.1	515.1	494.6	479.2	472.0	468.4	468.9	471.1	475.9	479.6	484.9
45°	500.8	480.9	460.9	448.3	442.3	443.1	443.1	447.0	451.8	457.5	463.1
47.5°	464.8	444.7	428.3	417.8	414.6	413.8	416.3	421.3	428.2	435.2	443.0
50°	440.5	421.4	407.2	397.6	394.1	395.4	398.9	403.7	411.9	420.6	428.8
52.5°	415.9	398.6	385.3	376.4	374.1	376.3	379.8	387.3	394.6	404.0	413.9
55°	377.6	362.9	352.5	346.0	345.1	346.4	350.3	358.6	369.0	380.7	390.3
57.5°	339.6	327.3	317.7	313.2	313.6	314.9	321.3	331.1	342.2	354.7	367.0
60°	314.0	302.6	294.9	291.4	291.8	294.4	302.2	311.4	325.2	337.4	350.3
62.5°	289.7	279.7	272.3	269.2	268.6	274.3	281.8	291.2	305.1	318.6	332.6
65°	250.6	242.8	236.8	235.1	236.4	240.7	250.2	262.8	274.5	288.8	303.5
67.5°	212.5	206.0	201.9	202.7	204.2	210.7	218.7	229.4	242.7	257.6	272.1
70°	188.2	182.1	178.6	179.0	181.6	189.5	196.4	207.2	221.6	236.8	248.9
72.5°	163.2	159.2	156.1	157.9	160.5	165.9	174.6	185.4	198.0	212.1	224.9
75°	125.3	125.3	123.6	124.9	128.8	134.0	140.5	151.7	164.4	175.6	186.1
77.5°	92.9	92.0	93.1	94.7	96.9	103.1	110.6	118.6	128.1	139.3	148.0
80°	71.1	71.6	73.7	76.3	77.2	81.9	89.8	97.1	104.5	114.1	122.3
82.5°	53.4	53.9	55.0	58.3	59.1	64.2	69.3	76.6	83.3	89.8	96.6
85°	29.0	29.0	31.2	32.5	34.7	38.2	41.2	45.5	51.6	55.9	62.5
87.5°	12.6	12.9	14.5	15.4	16.6	18.6	19.5	23.5	25.0	26.9	30.2
90°	7.7	9.0	10.1	11.2	12.2	13.3	14.1	14.9	15.7	16.6	17.0
92.5°	19.7	21.0	21.7	22.4	23.2	24.0	24.5	24.9	25.4	25.9	26.3
95°	41.2	42.2	43.1	44.1	45.1	46.0	46.4	46.8	47.2	47.6	47.8
97.5°	67.3	68.3	69.5	70.5	71.7	72.7	73.2	73.7	74.2	74.7	74.9
100°	86.8	87.7	88.9	90.2	91.4	92.6	92.9	93.1	93.4	93.7	93.8
102.5°	107.9	108.5	109.6	110.7	111.8	112.9	113.3	113.7	114.1	114.4	114.6
105°	141.5	141.9	142.4	142.9	143.5	144.0	144.4	144.8	145.2	145.6	146.0
107.5°	177.3	177.5	177.6	177.7	177.7	177.8	178.1	178.6	178.9	179.3	179.4
110°	201.9	202.0	201.9	201.8	201.6	201.5	201.2	201.0	200.7	200.4	200.5



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	226.2	226.2	225.9	225.7	225.4	225.2	225.2	225.1	225.0	225.0	225.0
115°	263.8	263.7	263.4	263.2	262.9	262.6	262.4	262.4	262.2	262.0	262.0
117.5°	299.9	299.8	299.6	299.5	299.2	299.1	298.6	298.2	297.7	297.2	296.9
120°	325.3	325.3	325.0	324.6	324.2	323.8	323.0	322.4	321.7	321.1	320.8
122.5°	348.7	348.7	348.5	348.3	348.1	348.0	347.5	347.0	346.6	346.1	345.6
125°	384.3	384.2	384.0	383.9	383.8	383.6	383.4	383.1	382.9	382.5	382.3
127.5°	418.9	419.0	418.7	418.6	418.3	418.2	417.8	417.6	417.4	417.0	416.8
130°	442.1	442.3	442.3	442.3	442.3	442.3	442.1	441.8	441.5	441.2	440.8
132.5°	465.5	465.5	465.4	465.3	465.2	465.0	464.8	464.6	464.3	464.0	463.7
135°	498.8	499.2	499.2	499.2	499.2	499.2	499.0	498.6	498.4	498.1	497.8
137.5°	531.2	531.5	531.7	531.9	532.1	532.4	532.0	531.7	531.3	531.0	530.8
140°	553.5	553.7	553.7	553.7	553.7	553.7	553.5	553.4	553.3	553.1	553.0
142.5°	574.4	574.5	574.3	574.2	574.1	574.0	574.0	574.0	573.9	573.9	573.9
145°	604.2	604.5	604.7	604.9	605.0	605.1	605.0	604.9	604.7	604.5	604.3
147.5°	633.2	633.5	633.4	633.2	633.2	633.1	632.9	632.8	632.8	632.6	632.5
150°	650.2	650.5	650.5	650.5	650.5	650.5	650.5	650.5	650.5	650.5	650.4
152.5°	665.9	666.0	666.1	666.3	666.3	666.4	666.8	667.1	667.4	667.7	667.7
155°	689.8	689.7	689.6	689.5	689.3	689.3	689.7	690.3	690.8	691.4	691.4
157.5°	710.1	710.0	710.0	710.0	710.0	709.9	710.3	710.7	711.1	711.5	711.5
160°	723.2	723.0	722.9	722.8	722.6	722.5	722.9	723.3	723.7	724.1	724.0
162.5°	733.9	733.7	733.5	733.4	733.3	733.1	733.9	734.6	735.3	736.1	736.1
165°	749.3	749.0	748.7	748.4	748.2	747.9	748.7	749.5	750.3	751.1	751.3
167.5°	760.7	760.3	760.4	760.4	760.4	760.5	761.3	762.1	762.9	763.7	763.7
170°	767.0	766.7	766.9	767.0	767.1	767.3	768.1	768.9	769.7	770.5	770.5
172.5°	772.3	772.0	772.0	772.1	772.1	772.1	773.1	774.0	774.9	775.8	775.8
175°	778.5	778.1	778.0	777.8	777.7	777.6	778.5	779.4	780.4	781.3	781.3
177.5°	781.2	781.0	781.0	781.0	781.0	781.0	781.7	782.4	783.2	784.0	783.9
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	997.4	996.8	994.3	994.0	994.3	996.8	997.4	998.2	999.2	1002.7	998.5
5°	921.5	919.2	917.9	922.8	917.9	919.2	921.5	924.0	928.4	928.8	933.1
7.5°	864.1	862.3	858.5	857.4	858.5	862.3	864.1	865.7	870.0	873.8	880.1
10°	827.3	825.6	822.1	821.3	822.1	825.6	827.3	831.7	836.0	840.7	845.1
12.5°	791.9	788.5	787.7	788.6	787.7	788.5	791.9	797.7	808.9	808.9	809.8
15°	744.9	743.2	738.4	739.7	738.4	743.2	744.9	750.6	755.8	762.3	768.7
17.5°	698.6	696.5	690.7	695.9	690.7	696.5	698.6	701.6	708.3	717.5	727.3
20°	669.5	666.0	663.0	662.5	663.0	666.0	669.5	672.5	679.9	687.7	695.0
22.5°	641.7	638.6	638.4	635.5	638.4	638.6	641.7	646.5	653.9	658.2	665.2
25°	607.1	604.1	603.2	601.0	603.2	604.1	607.1	610.5	615.3	618.7	626.6
27.5°	580.4	578.9	577.4	578.0	577.4	578.9	580.4	580.9	583.0	587.6	592.2
30°	564.1	563.7	562.8	562.8	562.8	563.7	564.1	562.8	565.0	567.1	570.6
32.5°	550.6	550.5	551.1	551.1	551.1	550.5	550.6	548.6	549.3	550.2	551.9
35°	531.6	532.9	533.8	532.5	533.8	532.9	531.6	529.9	528.6	525.5	526.4
37.5°	514.5	515.8	517.0	518.4	517.0	515.8	514.5	510.9	507.8	505.1	502.0
40°	501.2	504.3	505.2	507.4	505.2	504.3	501.2	497.3	493.9	490.8	487.4
42.5°	488.8	492.1	494.4	494.8	494.4	492.1	488.8	484.9	479.6	475.9	471.1
45°	469.6	473.0	476.1	476.1	476.1	473.0	469.6	463.1	457.5	451.8	447.0
47.5°	449.7	454.8	457.8	458.6	457.8	454.8	449.7	443.0	435.2	428.2	421.3
50°	436.2	442.3	445.3	447.5	445.3	442.3	436.2	428.8	420.6	411.9	403.7
52.5°	423.1	429.1	433.2	434.3	433.2	429.1	423.1	413.9	404.0	394.6	387.3
55°	400.2	408.9	413.7	415.4	413.7	408.9	400.2	390.3	380.7	369.0	358.6
57.5°	378.7	386.7	392.2	393.5	392.2	386.7	378.7	367.0	354.7	342.2	331.1
60°	362.1	370.7	377.6	379.0	377.6	370.7	362.1	350.3	337.4	325.2	311.4
62.5°	345.0	354.1	360.4	363.7	360.4	354.1	345.0	332.6	318.6	305.1	291.2
65°	315.7	324.7	330.8	332.2	330.8	324.7	315.7	303.5	288.8	274.5	262.8
67.5°	283.6	292.7	296.7	299.2	296.7	292.7	283.6	272.1	257.6	242.7	229.4
70°	261.1	268.4	272.7	274.9	272.7	268.4	261.1	248.9	236.8	221.6	207.2
72.5°	235.4	243.0	248.1	248.5	248.1	243.0	235.4	224.9	212.1	198.0	185.4
75°	196.0	202.9	205.5	205.5	205.5	202.9	196.0	186.1	175.6	164.4	151.7
77.5°	155.2	158.7	162.0	162.7	162.0	158.7	155.2	148.0	139.3	128.1	118.6
80°	128.8	130.9	133.5	133.5	133.5	130.9	128.8	122.3	114.1	104.5	97.1
82.5°	101.7	103.5	106.2	105.8	106.2	103.5	101.7	96.6	89.8	83.3	76.6
85°	61.6	65.5	65.1	64.2	65.1	65.5	61.6	62.5	55.9	51.6	45.5
87.5°	31.2	31.6	32.7	33.4	32.7	31.6	31.2	30.2	26.9	25.0	23.5
90°	17.4	17.6	17.9	18.2	17.9	17.6	17.4	17.0	16.6	15.7	14.9
92.5°	26.4	26.6	26.7	26.9	26.7	26.6	26.4	26.3	25.9	25.4	24.9
95°	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.8	47.6	47.2	46.8
97.5°	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.9	74.7	74.2	73.7
100°	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.7	93.4	93.1
102.5°	114.8	114.9	115.0	115.1	115.0	114.9	114.8	114.6	114.4	114.1	113.7
105°	146.4	146.8	147.2	147.7	147.2	146.8	146.4	146.0	145.6	145.2	144.8
107.5°	179.4	179.4	179.4	179.4	179.4	179.4	179.4	179.4	179.3	178.9	178.6
110°	200.9	201.3	201.7	202.1	201.7	201.3	200.9	200.5	200.4	200.7	201.0



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	225.1	225.2	225.3	225.3	225.3	225.2	225.1	225.0	225.0	225.0	225.1
115°	261.8	261.7	261.5	261.4	261.5	261.7	261.8	262.0	262.0	262.2	262.4
117.5°	296.6	296.3	296.0	295.8	296.0	296.3	296.6	296.9	297.2	297.7	298.2
120°	321.1	321.4	321.6	321.9	321.6	321.4	321.1	320.8	321.1	321.7	322.4
122.5°	345.1	344.6	344.2	343.7	344.2	344.6	345.1	345.6	346.1	346.6	347.0
125°	382.0	381.7	381.5	381.2	381.5	381.7	382.0	382.3	382.5	382.9	383.1
127.5°	416.6	416.4	416.1	416.0	416.1	416.4	416.6	416.8	417.0	417.4	417.6
130°	440.3	439.8	439.2	438.7	439.2	439.8	440.3	440.8	441.2	441.5	441.8
132.5°	463.6	463.3	463.1	462.9	463.1	463.3	463.6	463.7	464.0	464.3	464.6
135°	497.4	497.0	496.6	496.2	496.6	497.0	497.4	497.8	498.1	498.4	498.6
137.5°	530.9	531.0	531.1	531.2	531.1	531.0	530.9	530.8	531.0	531.3	531.7
140°	552.9	552.7	552.6	552.4	552.6	552.7	552.9	553.0	553.1	553.3	553.4
142.5°	573.8	573.8	573.8	573.7	573.8	573.8	573.8	573.9	573.9	573.9	574.0
145°	603.9	603.5	603.1	602.7	603.1	603.5	603.9	604.3	604.5	604.7	604.9
147.5°	632.3	632.3	632.1	631.9	632.1	632.3	632.3	632.5	632.6	632.8	632.8
150°	650.3	650.1	650.0	649.9	650.0	650.1	650.3	650.4	650.5	650.5	650.5
152.5°	667.4	667.1	666.7	666.3	666.7	667.1	667.4	667.7	667.7	667.4	667.1
155°	690.8	690.3	689.7	689.3	689.7	690.3	690.8	691.4	691.4	690.8	690.3
157.5°	711.0	710.6	710.1	709.6	710.1	710.6	711.0	711.5	711.5	711.1	710.7
160°	723.3	722.6	721.9	721.3	721.9	722.6	723.3	724.0	724.1	723.7	723.3
162.5°	735.4	734.7	734.1	733.4	734.1	734.7	735.4	736.1	736.1	735.3	734.6
165°	750.7	750.2	749.7	749.1	749.7	750.2	750.7	751.3	751.1	750.3	749.5
167.5°	762.9	762.1	761.2	760.3	761.2	762.1	762.9	763.7	763.7	762.9	762.1
170°	769.5	768.6	767.6	766.7	767.6	768.6	769.5	770.5	770.5	769.7	768.9
172.5°	774.8	773.9	772.9	772.0	772.9	773.9	774.8	775.8	775.8	774.9	774.0
175°	780.4	779.4	778.5	777.6	778.5	779.4	780.4	781.3	781.3	780.4	779.4
177.5°	783.0	782.2	781.3	780.5	781.3	782.2	783.0	783.9	784.0	783.2	782.4
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1000.6	1002.0	1007.5	1012.8	1019.0	1023.5	1026.6	1030.0	1037.4	1043.3	1048.8
5°	937.4	939.6	950.9	958.7	972.2	983.8	993.0	1002.9	1014.6	1030.7	1045.5
7.5°	881.9	889.9	902.2	914.9	928.6	944.0	957.3	972.3	992.5	1014.6	1037.3
10°	850.3	859.4	872.5	887.1	900.2	917.9	934.4	952.2	975.2	1002.1	1029.0
12.5°	818.7	833.7	843.6	861.1	875.2	889.8	907.3	930.7	957.5	985.8	1018.2
15°	779.2	787.4	806.5	816.0	836.0	858.5	875.9	899.3	925.3	962.6	999.1
17.5°	733.6	744.4	759.6	777.8	800.7	818.3	839.9	864.0	896.7	933.8	979.4
20°	703.8	712.8	731.5	751.5	775.8	794.3	817.3	840.7	874.6	914.0	961.7
22.5°	677.0	685.8	705.5	724.1	747.6	770.5	794.4	821.7	854.1	895.7	944.4
25°	635.7	647.3	664.7	683.8	706.4	732.4	758.4	782.7	817.3	861.1	913.2
27.5°	599.0	608.4	620.9	642.6	668.2	693.3	719.2	749.7	783.0	829.3	883.4
30°	575.4	584.1	596.6	616.6	640.4	667.3	694.2	723.7	758.4	804.4	859.4
32.5°	556.7	563.3	574.5	592.3	614.1	642.4	668.9	699.4	735.8	781.1	834.8
35°	529.0	534.7	539.0	555.9	575.4	601.4	628.3	660.8	695.9	738.9	792.6
37.5°	501.8	503.8	510.1	521.2	540.1	564.0	589.0	621.0	657.0	700.6	749.1
40°	485.2	486.1	490.0	500.3	516.9	539.4	563.7	595.3	629.6	670.8	718.9
42.5°	468.9	468.4	472.0	479.2	494.6	515.1	539.1	567.9	602.2	640.3	685.6
45°	443.1	443.1	442.3	448.3	460.9	480.9	500.8	528.6	557.2	594.5	632.7
47.5°	416.3	413.8	414.6	417.8	428.3	444.7	464.8	487.5	512.8	544.4	577.8
50°	398.9	395.4	394.1	397.6	407.2	421.4	440.5	460.5	484.4	512.1	540.7
52.5°	379.8	376.3	374.1	376.4	385.3	398.6	415.9	433.4	454.9	477.4	502.2
55°	350.3	346.4	345.1	346.0	352.5	362.9	377.6	393.7	409.8	428.4	445.7
57.5°	321.3	314.9	313.6	313.2	317.7	327.3	339.6	353.5	365.2	376.4	394.9
60°	302.2	294.4	291.8	291.4	294.9	302.6	314.0	327.8	336.1	343.8	359.9
62.5°	281.8	274.3	268.6	269.2	272.3	279.7	289.7	299.7	305.2	313.6	324.5
65°	250.2	240.7	236.4	235.1	236.8	242.8	250.6	257.1	263.2	266.7	277.0
67.5°	218.7	210.7	204.2	202.7	201.9	206.0	212.5	216.4	220.7	223.7	229.9
70°	196.4	189.5	181.6	179.0	178.6	182.1	188.2	188.6	194.7	196.0	202.5
72.5°	174.6	165.9	160.5	157.9	156.1	159.2	163.2	164.4	167.6	170.0	173.3
75°	140.5	134.0	128.8	124.9	123.6	125.3	125.3	127.5	129.6	130.9	134.9
77.5°	110.6	103.1	96.9	94.7	93.1	92.0	92.9	94.2	93.2	95.5	96.4
80°	89.8	81.9	77.2	76.3	73.7	71.6	71.1	72.4	70.7	71.6	74.1
82.5°	69.3	64.2	59.1	58.3	55.0	53.9	53.4	52.7	52.7	52.5	53.0
85°	41.2	38.2	34.7	32.5	31.2	29.0	29.0	28.2	27.3	26.4	26.9
87.5°	19.5	18.6	16.6	15.4	14.5	12.9	12.6	11.3	10.7	10.0	9.4
90°	14.1	13.3	12.2	11.2	10.1	9.0	7.7	6.3	4.8	3.3	1.8
92.5°	24.5	24.0	23.2	22.4	21.7	21.0	19.7	18.0	16.3	14.7	13.0
95°	46.4	46.0	45.1	44.1	43.1	42.2	41.2	39.9	38.7	37.5	36.3
97.5°	73.2	72.7	71.7	70.5	69.5	68.3	67.3	66.3	65.4	64.4	63.4
100°	92.9	92.6	91.4	90.2	88.9	87.7	86.8	86.3	85.8	85.3	84.7
102.5°	113.3	112.9	111.8	110.7	109.6	108.5	107.9	107.6	107.4	107.2	107.0
105°	144.4	144.0	143.5	142.9	142.4	141.9	141.5	141.4	141.3	141.1	141.0
107.5°	178.1	177.8	177.7	177.7	177.6	177.5	177.3	177.2	177.0	176.8	176.7
110°	201.2	201.5	201.6	201.8	201.9	202.0	201.9	201.7	201.5	201.1	200.9



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	225.2	225.2	225.4	225.7	225.9	226.2	226.2	226.2	226.2	226.1	226.1
115°	262.4	262.6	262.9	263.2	263.4	263.7	263.8	263.8	263.8	263.8	263.8
117.5°	298.6	299.1	299.2	299.5	299.6	299.8	299.9	299.7	299.6	299.5	299.4
120°	323.0	323.8	324.2	324.6	325.0	325.3	325.3	324.7	324.2	323.7	323.1
122.5°	347.5	348.0	348.1	348.3	348.5	348.7	348.7	348.5	348.2	348.1	347.8
125°	383.4	383.6	383.8	383.9	384.0	384.2	384.3	384.3	384.3	384.3	384.3
127.5°	417.8	418.2	418.3	418.6	418.7	419.0	418.9	418.5	418.1	417.7	417.3
130°	442.1	442.3	442.3	442.3	442.3	442.3	442.1	441.7	441.3	440.9	440.5
132.5°	464.8	465.0	465.2	465.3	465.4	465.5	465.5	465.1	464.8	464.6	464.2
135°	499.0	499.2	499.2	499.2	499.2	499.2	498.8	498.0	497.2	496.4	495.6
137.5°	532.0	532.4	532.1	531.9	531.7	531.5	531.2	530.8	530.4	530.1	529.7
140°	553.5	553.7	553.7	553.7	553.7	553.7	553.5	553.3	553.0	552.7	552.4
142.5°	574.0	574.0	574.1	574.2	574.3	574.5	574.4	574.1	573.8	573.6	573.2
145°	605.0	605.1	605.0	604.9	604.7	604.5	604.2	603.7	603.2	602.6	602.1
147.5°	632.9	633.1	633.2	633.2	633.4	633.5	633.2	632.6	631.9	631.3	630.6
150°	650.5	650.5	650.5	650.5	650.5	650.5	650.2	649.7	649.1	648.6	648.1
152.5°	666.8	666.4	666.3	666.3	666.1	666.0	665.9	665.5	665.2	664.9	664.6
155°	689.7	689.3	689.3	689.5	689.6	689.7	689.8	689.8	689.8	689.8	689.8
157.5°	710.3	709.9	710.0	710.0	710.0	710.0	710.1	710.4	710.6	710.9	711.1
160°	722.9	722.5	722.6	722.8	722.9	723.0	723.2	723.3	723.4	723.6	723.7
162.5°	733.9	733.1	733.3	733.4	733.5	733.7	733.9	734.3	734.6	735.0	735.3
165°	748.7	747.9	748.2	748.4	748.7	749.0	749.3	749.7	750.2	750.6	751.0
167.5°	761.3	760.5	760.4	760.4	760.4	760.3	760.7	761.2	761.8	762.4	762.9
170°	768.1	767.3	767.1	767.0	766.9	766.7	767.0	767.7	768.3	769.0	769.7
172.5°	773.1	772.1	772.1	772.1	772.0	772.0	772.3	772.8	773.4	774.0	774.5
175°	778.5	777.6	777.7	777.8	778.0	778.1	778.5	779.2	779.8	780.5	781.2
177.5°	781.7	781.0	781.0	781.0	781.0	781.0	781.2	781.8	782.3	782.9	783.3
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1053.7	1057.1	1061.7	1069.3	1072.0	1075.5	1080.4	1080.0	1081.4	1086.6	1097.7
5°	1057.6	1071.0	1084.0	1099.6	1116.1	1126.9	1141.7	1150.8	1159.9	1171.6	1191.6
7.5°	1059.2	1080.4	1104.3	1131.7	1156.1	1184.2	1206.2	1226.8	1245.4	1270.2	1293.9
10°	1056.7	1085.3	1116.1	1150.8	1187.6	1218.9	1247.1	1279.1	1306.4	1336.4	1363.3
12.5°	1052.2	1086.7	1127.9	1166.8	1209.8	1256.0	1291.1	1323.6	1359.9	1394.3	1435.7
15°	1042.0	1089.2	1137.3	1188.5	1246.2	1299.5	1350.2	1392.3	1431.3	1482.9	1537.2
17.5°	1029.0	1079.9	1140.7	1202.6	1262.8	1323.8	1386.6	1449.8	1499.1	1563.2	1605.6
20°	1016.8	1075.8	1138.2	1211.9	1272.2	1348.1	1410.5	1471.7	1539.3	1603.0	1653.8
22.5°	999.8	1064.4	1130.6	1204.0	1283.3	1359.2	1431.3	1497.7	1565.3	1634.6	1696.1
25°	978.2	1036.7	1115.2	1198.5	1277.4	1359.8	1442.6	1525.8	1598.7	1672.0	1729.2
27.5°	941.4	1015.4	1088.4	1174.4	1262.1	1355.3	1443.8	1531.0	1607.3	1667.5	1703.0
30°	922.8	986.9	1066.2	1152.5	1247.5	1347.7	1440.0	1525.4	1596.5	1644.7	1659.0
32.5°	895.0	961.2	1038.9	1128.2	1228.7	1331.7	1427.8	1508.5	1567.7	1593.0	1575.7
35°	853.8	913.6	992.1	1083.6	1188.1	1297.8	1392.8	1460.9	1491.2	1467.3	1407.9
37.5°	804.4	863.6	942.5	1032.3	1140.4	1252.0	1337.8	1386.8	1376.8	1317.4	1228.9
40°	769.6	825.2	900.2	997.3	1102.7	1214.6	1290.0	1316.5	1288.7	1203.7	1109.6
42.5°	731.2	785.3	860.6	954.3	1065.9	1169.1	1234.9	1237.0	1190.5	1088.9	994.4
45°	672.5	724.1	795.2	892.8	996.0	1093.2	1136.4	1115.2	1029.4	931.4	836.4
47.5°	614.7	659.4	729.5	822.1	920.1	1001.9	1023.4	985.1	893.6	798.5	710.5
50°	572.3	617.4	683.4	771.8	866.3	937.0	947.5	896.7	807.0	711.1	642.2
52.5°	531.7	576.5	640.0	721.9	808.5	872.1	872.5	813.8	724.4	639.0	574.9
55°	472.2	512.5	569.7	643.0	720.2	770.1	758.0	697.2	619.6	545.5	489.5
57.5°	414.8	449.9	502.6	563.8	631.8	672.9	652.7	594.3	525.0	462.1	419.7
60°	377.6	411.1	456.2	513.8	571.0	603.2	584.1	531.2	467.4	416.7	379.8
62.5°	341.6	369.8	413.1	463.2	516.2	540.1	523.0	470.8	415.7	369.9	340.0
65°	290.5	313.5	348.2	391.1	429.7	450.0	435.8	387.2	345.1	312.2	288.4
67.5°	242.8	260.7	287.1	321.5	354.2	365.3	352.3	318.5	282.8	256.4	239.6
70°	209.9	226.8	248.9	275.3	303.9	315.7	302.6	275.7	246.7	222.4	205.9
72.5°	181.1	194.2	212.8	235.5	257.8	269.5	260.7	234.8	210.3	192.2	178.2
75°	137.9	149.2	162.2	178.2	195.6	203.3	195.6	177.8	160.9	147.4	137.5
77.5°	100.3	106.3	116.3	128.3	139.2	145.2	138.4	126.4	116.0	106.8	101.9
80°	76.3	80.6	87.6	97.1	104.5	110.1	105.8	95.8	87.6	81.5	79.3
82.5°	55.5	58.5	62.9	70.0	75.0	77.9	76.0	68.7	65.4	60.0	57.8
85°	27.3	29.0	32.1	34.2	38.6	39.1	39.5	36.4	33.4	32.1	30.3
87.5°	10.0	10.7	12.0	13.4	15.0	15.6	15.4	15.7	14.4	14.3	13.0
90°	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1	14.9
92.5°	14.7	16.3	18.0	19.7	21.0	21.7	22.4	23.2	24.0	24.5	24.9
95°	37.5	38.7	39.9	41.2	42.2	43.1	44.1	45.1	46.0	46.4	46.8
97.5°	64.4	65.4	66.3	67.3	68.3	69.5	70.5	71.7	72.7	73.2	73.7
100°	85.3	85.8	86.3	86.8	87.7	88.9	90.2	91.4	92.6	92.9	93.1
102.5°	107.2	107.4	107.6	107.9	108.5	109.6	110.7	111.8	112.9	113.3	113.7
105°	141.1	141.3	141.4	141.5	141.9	142.4	142.9	143.5	144.0	144.4	144.8
107.5°	176.8	177.0	177.2	177.3	177.5	177.6	177.7	177.7	177.8	178.1	178.6
110°	201.1	201.5	201.7	201.9	202.0	201.9	201.8	201.6	201.5	201.2	201.0





TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	226.1	226.2	226.2	226.2	226.2	225.9	225.7	225.4	225.2	225.2	225.1
115°	263.8	263.8	263.8	263.8	263.7	263.4	263.2	262.9	262.6	262.4	262.4
117.5°	299.5	299.6	299.7	299.9	299.8	299.6	299.5	299.2	299.1	298.6	298.2
120°	323.7	324.2	324.7	325.3	325.3	325.0	324.6	324.2	323.8	323.0	322.4
122.5°	348.1	348.2	348.5	348.7	348.7	348.5	348.3	348.1	348.0	347.5	347.0
125°	384.3	384.3	384.3	384.3	384.2	384.0	383.9	383.8	383.6	383.4	383.1
127.5°	417.7	418.1	418.5	418.9	419.0	418.7	418.6	418.3	418.2	417.8	417.6
130°	440.9	441.3	441.7	442.1	442.3	442.3	442.3	442.3	442.3	442.1	441.8
132.5°	464.6	464.8	465.1	465.5	465.5	465.4	465.3	465.2	465.0	464.8	464.6
135°	496.4	497.2	498.0	498.8	499.2	499.2	499.2	499.2	499.2	499.0	498.6
137.5°	530.1	530.4	530.8	531.2	531.5	531.7	531.9	532.1	532.4	532.0	531.7
140°	552.7	553.0	553.3	553.5	553.7	553.7	553.7	553.7	553.7	553.5	553.4
142.5°	573.6	573.8	574.1	574.4	574.5	574.3	574.2	574.1	574.0	574.0	574.0
145°	602.6	603.2	603.7	604.2	604.5	604.7	604.9	605.0	605.1	605.0	604.9
147.5°	631.3	631.9	632.6	633.2	633.5	633.4	633.2	633.2	633.1	632.9	632.8
150°	648.6	649.1	649.7	650.2	650.5	650.5	650.5	650.5	650.5	650.5	650.5
152.5°	664.9	665.2	665.5	665.9	666.0	666.1	666.3	666.3	666.4	666.8	667.1
155°	689.8	689.8	689.8	689.8	689.7	689.6	689.5	689.3	689.3	689.7	690.3
157.5°	710.9	710.6	710.4	710.1	710.0	710.0	710.0	710.0	709.9	710.3	710.7
160°	723.6	723.4	723.3	723.2	723.0	722.9	722.8	722.6	722.5	722.9	723.3
162.5°	735.0	734.6	734.3	733.9	733.7	733.5	733.4	733.3	733.1	733.9	734.6
165°	750.6	750.2	749.7	749.3	749.0	748.7	748.4	748.2	747.9	748.7	749.5
167.5°	762.4	761.8	761.2	760.7	760.3	760.4	760.4	760.4	760.5	761.3	762.1
170°	769.0	768.3	767.7	767.0	766.7	766.9	767.0	767.1	767.3	768.1	768.9
172.5°	774.0	773.4	772.8	772.3	772.0	772.0	772.1	772.1	772.1	773.1	774.0
175°	780.5	779.8	779.2	778.5	778.1	778.0	777.8	777.7	777.6	778.5	779.4
177.5°	782.9	782.3	781.8	781.2	781.0	781.0	781.0	781.0	781.0	781.7	782.4
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8	1046.8
2.5°	1103.3	1104.0	1107.1	1109.5	1110.2	1113.7	1114.0
5°	1200.2	1207.6	1221.9	1223.2	1225.4	1236.6	1228.0
7.5°	1313.9	1332.5	1345.1	1356.1	1360.1	1365.0	1364.0
10°	1386.7	1414.5	1428.3	1450.4	1451.3	1456.9	1453.4
12.5°	1459.9	1492.2	1517.4	1521.5	1540.1	1543.0	1547.8
15°	1563.6	1597.8	1633.0	1645.5	1671.1	1677.2	1686.8
17.5°	1661.1	1696.1	1720.7	1753.2	1763.7	1777.8	1768.2
20°	1714.5	1752.6	1783.9	1809.5	1820.3	1828.1	1827.2
22.5°	1746.8	1785.3	1810.5	1829.9	1840.0	1843.4	1843.1
25°	1766.9	1789.1	1796.8	1804.3	1793.0	1789.1	1790.8
27.5°	1710.7	1705.0	1684.7	1657.9	1630.2	1608.2	1596.2
30°	1633.4	1599.6	1568.8	1515.0	1487.3	1470.8	1456.0
32.5°	1523.8	1470.2	1411.0	1361.7	1330.2	1305.7	1302.0
35°	1335.9	1255.3	1182.9	1122.6	1091.4	1064.9	1058.8
37.5°	1135.8	1052.0	986.8	933.8	900.2	881.5	864.1
40°	1002.9	931.0	866.7	821.7	796.1	782.7	771.8
42.5°	900.6	834.9	771.0	736.7	713.5	705.3	699.0
45°	759.2	698.1	653.9	627.9	614.4	600.5	594.0
47.5°	646.0	596.3	567.1	545.0	530.7	522.4	518.3
50°	581.9	541.1	515.1	498.2	485.2	478.7	475.2
52.5°	525.0	491.5	469.7	456.2	447.4	442.6	441.2
55°	452.2	426.6	412.8	401.1	394.6	390.3	388.5
57.5°	393.1	373.4	362.2	352.5	350.0	346.3	345.1
60°	354.2	339.1	329.5	323.0	320.9	316.5	317.4
62.5°	319.9	307.5	299.4	295.6	292.8	289.1	290.3
65°	270.6	261.5	257.1	253.6	250.2	248.0	249.7
67.5°	227.1	220.8	214.9	212.9	211.2	210.8	209.0
70°	198.6	193.4	188.2	186.9	186.9	185.2	184.7
72.5°	171.2	167.4	163.9	163.0	161.6	162.2	160.5
75°	132.2	129.2	127.9	126.6	126.2	126.2	124.9
77.5°	97.8	95.5	93.4	93.4	91.8	91.2	91.1
80°	74.1	73.3	71.6	71.6	70.7	71.1	70.3
82.5°	55.8	54.5	54.2	53.5	52.3	52.3	51.5
85°	29.9	28.6	28.2	26.9	26.0	26.9	26.0
87.5°	13.5	13.4	13.1	12.5	12.2	12.2	11.3
90°	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	25.4	25.9	26.3	26.4	26.6	26.7	26.9
95°	47.2	47.6	47.8	47.8	47.8	47.8	47.8
97.5°	74.2	74.7	74.9	74.9	74.9	74.9	74.9
100°	93.4	93.7	93.8	93.8	93.8	93.8	93.8
102.5°	114.1	114.4	114.6	114.8	114.9	115.0	115.1
105°	145.2	145.6	146.0	146.4	146.8	147.2	147.7
107.5°	178.9	179.3	179.4	179.4	179.4	179.4	179.4
110°	200.7	200.4	200.5	200.9	201.3	201.7	202.1



TEST NUMBER: P332782-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	225.0	225.0	225.0	225.1	225.2	225.3	225.3
115°	262.2	262.0	262.0	261.8	261.7	261.5	261.4
117.5°	297.7	297.2	296.9	296.6	296.3	296.0	295.8
120°	321.7	321.1	320.8	321.1	321.4	321.6	321.9
122.5°	346.6	346.1	345.6	345.1	344.6	344.2	343.7
125°	382.9	382.5	382.3	382.0	381.7	381.5	381.2
127.5°	417.4	417.0	416.8	416.6	416.4	416.1	416.0
130°	441.5	441.2	440.8	440.3	439.8	439.2	438.7
132.5°	464.3	464.0	463.7	463.6	463.3	463.1	462.9
135°	498.4	498.1	497.8	497.4	497.0	496.6	496.2
137.5°	531.3	531.0	530.8	530.9	531.0	531.1	531.2
140°	553.3	553.1	553.0	552.9	552.7	552.6	552.4
142.5°	573.9	573.9	573.9	573.8	573.8	573.8	573.7
145°	604.7	604.5	604.3	603.9	603.5	603.1	602.7
147.5°	632.8	632.6	632.5	632.3	632.3	632.1	631.9
150°	650.5	650.5	650.4	650.3	650.1	650.0	649.9
152.5°	667.4	667.7	667.7	667.4	667.1	666.7	666.3
155°	690.8	691.4	691.4	690.8	690.3	689.7	689.3
157.5°	711.1	711.5	711.5	711.0	710.6	710.1	709.6
160°	723.7	724.1	724.0	723.3	722.6	721.9	721.3
162.5°	735.3	736.1	736.1	735.4	734.7	734.1	733.4
165°	750.3	751.1	751.3	750.7	750.2	749.7	749.1
167.5°	762.9	763.7	763.7	762.9	762.1	761.2	760.3
170°	769.7	770.5	770.5	769.5	768.6	767.6	766.7
172.5°	774.9	775.8	775.8	774.8	773.9	772.9	772.0
175°	780.4	781.3	781.3	780.4	779.4	778.5	777.6
177.5°	783.2	784.0	783.9	783.0	782.2	781.3	780.5
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4

(END OF REPORT)