

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332786-930

Luminaire Tested: **S124DIW-S795D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332786-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S795D770U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4950.3 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332786-930
CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332786-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	74	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	50	47	43	43	40	37	33
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8737	8737	8737
5°	8763	8658	8721
10°	8708	8588	8630
15°	8603	8466	8487
20°	8463	8314	8322
25°	8304	8141	8118
30°	8108	7938	7866
35°	7906	7727	7624
40°	7695	7484	7347
45°	7476	7247	7108
50°	7232	7036	6818
55°	6970	6763	6542
60°	6707	6455	6260
65°	6411	6162	5914
70°	6080	5773	5549
75°	5571	5303	5168
80°	4956	4756	4635
85°	4335	4177	4094



TEST NUMBER: P332786-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	2.1
10°-20°	287.2	5.8
20°-30°	422.7	8.5
30°-40°	491.4	9.9
40°-50°	491.4	9.9
50°-60°	429.8	8.7
60°-70°	319.2	6.4
70°-80°	181.4	3.7
80°-90°	54.7	1.1
90°-100°	51.6	1.0
100°-110°	152.9	3.1
110°-120°	259.5	5.2
120°-130°	342.1	6.9
130°-140°	384.2	7.8
140°-150°	377.6	7.6
150°-160°	317.6	6.4
160°-170°	211.3	4.3
170°-180°	74.0	1.5
0°-30°	811.8	16.4
0°-40°	1303.1	26.3
0°-60°	2224.4	44.9
0°-90°	2779.6	56.2
90°-120°	463.9	9.4
90°-150°	1567.9	31.7
90°-180°	2171.0	43.9
0°-180°	4950.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1082	1082	1082	1082	1082	
5°	1081	1078	1068	1077	1076	103
15°	1029	1025	1013	1018	1016	290
25°	932	926	914	915	911	429
35°	802	796	784	778	774	501
45°	655	648	635	626	623	505
55°	495	492	480	470	465	443
65°	336	331	323	314	310	332
75°	179	174	170	167	166	190
85°	47	47	45	45	44	52
90°	2	8	13	17	18	5
95°	36	42	46	48	48	40
105°	141	142	144	146	148	150
115°	264	264	263	262	261	260
125°	384	384	384	382	381	342
135°	496	499	499	498	496	383
145°	602	604	605	604	603	377
155°	690	690	689	691	689	317
165°	751	749	748	751	749	212
175°	781	778	778	781	778	74
180°	782	782	782	782	782	



TEST NUMBER: P332786-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1085.1	1084.6	1084.1	1083.7	1083.2	1082.1	1080.4	1078.7	1077.0	1075.4	1076.8
5°	1081.4	1080.7	1079.9	1079.1	1078.3	1076.8	1074.7	1072.6	1070.5	1068.4	1070.5
7.5°	1071.4	1070.6	1069.8	1069.0	1068.3	1066.7	1064.4	1062.0	1059.6	1057.3	1059.0
10°	1062.3	1061.6	1060.8	1060.1	1059.2	1057.6	1055.1	1052.6	1050.1	1047.6	1049.1
12.5°	1050.5	1049.8	1049.0	1048.2	1047.5	1045.7	1043.1	1040.4	1037.8	1035.1	1036.8
15°	1029.4	1028.6	1027.8	1027.0	1026.3	1024.5	1021.6	1018.7	1015.8	1012.9	1014.1
17.5°	1003.9	1002.9	1001.9	1001.0	1000.0	998.2	995.5	992.7	989.9	987.2	988.0
20°	985.1	984.1	983.3	982.3	981.3	979.3	976.5	973.5	970.7	967.8	968.4
22.5°	965.1	963.8	962.5	961.2	959.9	957.9	955.0	952.1	949.2	946.3	947.4
25°	932.2	930.9	929.5	928.2	926.8	924.8	922.1	919.4	916.7	914.0	914.2
27.5°	894.8	893.4	892.0	890.6	889.2	887.3	884.8	882.3	879.8	877.3	876.8
30°	869.8	868.3	866.7	865.2	863.6	861.6	859.1	856.6	854.1	851.6	850.8
32.5°	843.4	842.0	840.7	839.3	837.9	835.8	833.2	830.5	827.9	825.2	824.3
35°	802.2	800.8	799.5	798.1	796.8	794.8	792.1	789.4	786.7	784.0	782.6
37.5°	758.6	757.4	756.2	755.0	753.7	751.6	748.8	745.8	743.0	740.0	738.6
40°	730.2	728.6	727.1	725.5	724.0	721.8	718.9	716.0	713.1	710.2	708.3
42.5°	699.7	698.7	697.8	696.9	695.9	693.9	690.7	687.5	684.3	681.1	678.9
45°	654.8	653.4	652.1	650.7	649.4	647.1	644.1	641.0	637.9	634.8	632.7
47.5°	607.7	606.8	605.9	605.0	604.1	602.2	599.3	596.5	593.6	590.8	588.3
50°	575.8	575.0	574.3	573.5	572.7	571.0	568.3	565.7	562.9	560.2	557.5
52.5°	544.6	543.7	542.7	541.8	540.9	539.0	536.1	533.3	530.4	527.6	525.2
55°	495.2	494.6	494.0	493.4	492.8	491.2	488.5	485.8	483.1	480.5	478.1
57.5°	448.0	447.4	446.7	446.1	445.4	443.7	441.1	438.4	435.8	433.1	430.9
60°	415.4	414.4	413.4	412.5	411.6	409.8	407.3	404.8	402.3	399.8	398.0
62.5°	383.5	382.7	381.9	381.1	380.3	378.5	375.9	373.2	370.6	367.9	366.3
65°	335.6	334.7	333.7	332.7	331.7	330.3	328.4	326.4	324.5	322.6	320.7
67.5°	287.4	286.5	285.6	284.7	283.9	282.5	280.6	278.8	277.0	275.1	273.2
70°	257.6	256.2	254.9	253.5	252.2	250.7	249.2	247.6	246.1	244.6	243.0
72.5°	225.7	224.3	223.0	221.6	220.2	219.0	217.8	216.5	215.2	214.0	212.8
75°	178.6	177.7	176.8	175.8	174.8	173.8	172.8	171.9	171.0	170.0	169.2
77.5°	133.7	133.3	132.9	132.5	132.0	131.4	130.5	129.7	128.8	128.0	127.8
80°	106.6	106.1	105.5	104.9	104.4	103.9	103.5	103.1	102.7	102.3	101.9
82.5°	80.3	80.1	79.7	79.5	79.2	79.1	79.0	78.9	78.8	78.8	78.5
85°	46.8	46.8	46.8	46.8	46.8	46.6	46.2	45.9	45.5	45.1	45.1
87.5°	18.4	18.5	18.7	18.8	19.0	19.1	19.2	19.2	19.2	19.3	19.5
90°	1.8	3.3	4.8	6.3	7.7	9.0	10.1	11.2	12.2	13.3	14.1
92.5°	13.0	14.7	16.3	18.0	19.7	21.0	21.7	22.4	23.2	24.0	24.5
95°	36.3	37.5	38.7	39.9	41.2	42.2	43.1	44.1	45.1	46.0	46.4
97.5°	63.4	64.4	65.4	66.3	67.3	68.3	69.5	70.5	71.7	72.7	73.2
100°	84.7	85.3	85.8	86.3	86.8	87.7	88.9	90.2	91.4	92.6	92.9
102.5°	107.0	107.2	107.4	107.6	107.9	108.5	109.6	110.7	111.8	112.9	113.3
105°	141.0	141.1	141.3	141.4	141.5	141.9	142.4	142.9	143.5	144.0	144.4
107.5°	176.7	176.8	177.0	177.2	177.3	177.5	177.6	177.7	177.7	177.8	178.1
110°	200.9	201.1	201.5	201.7	201.9	202.0	201.9	201.8	201.6	201.5	201.2



TEST NUMBER: P332786-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	226.1	226.1	226.2	226.2	226.2	226.2	225.9	225.7	225.4	225.2	225.2
115°	263.8	263.8	263.8	263.8	263.8	263.7	263.4	263.2	262.9	262.6	262.4
117.5°	299.4	299.5	299.6	299.7	299.9	299.8	299.6	299.5	299.2	299.1	298.6
120°	323.1	323.7	324.2	324.7	325.3	325.3	325.0	324.6	324.2	323.8	323.0
122.5°	347.8	348.1	348.2	348.5	348.7	348.7	348.5	348.3	348.1	348.0	347.5
125°	384.3	384.3	384.3	384.3	384.3	384.2	384.0	383.9	383.8	383.6	383.4
127.5°	417.3	417.7	418.1	418.5	418.9	419.0	418.7	418.6	418.3	418.2	417.8
130°	440.5	440.9	441.3	441.7	442.1	442.3	442.3	442.3	442.3	442.3	442.1
132.5°	464.2	464.6	464.8	465.1	465.5	465.5	465.4	465.3	465.2	465.0	464.8
135°	495.6	496.4	497.2	498.0	498.8	499.2	499.2	499.2	499.2	499.2	499.0
137.5°	529.7	530.1	530.4	530.8	531.2	531.5	531.7	531.9	532.1	532.4	532.0
140°	552.4	552.7	553.0	553.3	553.5	553.7	553.7	553.7	553.7	553.7	553.5
142.5°	573.2	573.6	573.8	574.1	574.4	574.5	574.3	574.2	574.1	574.0	574.0
145°	602.1	602.6	603.2	603.7	604.2	604.5	604.7	604.9	605.0	605.1	605.0
147.5°	630.6	631.3	631.9	632.6	633.2	633.5	633.4	633.2	633.2	633.1	632.9
150°	648.1	648.6	649.1	649.7	650.2	650.5	650.5	650.5	650.5	650.5	650.5
152.5°	664.6	664.9	665.2	665.5	665.9	666.0	666.1	666.3	666.3	666.4	666.8
155°	689.8	689.8	689.8	689.8	689.8	689.7	689.6	689.5	689.3	689.3	689.7
157.5°	711.1	710.9	710.6	710.4	710.1	710.0	710.0	710.0	710.0	709.9	710.3
160°	723.7	723.6	723.4	723.3	723.2	723.0	722.9	722.8	722.6	722.5	722.9
162.5°	735.3	735.0	734.6	734.3	733.9	733.7	733.5	733.4	733.3	733.1	733.9
165°	751.0	750.6	750.2	749.7	749.3	749.0	748.7	748.4	748.2	747.9	748.7
167.5°	762.9	762.4	761.8	761.2	760.7	760.3	760.4	760.4	760.4	760.5	761.3
170°	769.7	769.0	768.3	767.7	767.0	766.7	766.9	767.0	767.1	767.3	768.1
172.5°	774.5	774.0	773.4	772.8	772.3	772.0	772.0	772.1	772.1	772.1	773.1
175°	781.2	780.5	779.8	779.2	778.5	778.1	778.0	777.8	777.7	777.6	778.5
177.5°	783.3	782.9	782.3	781.8	781.2	781.0	781.0	781.0	781.0	781.0	781.7
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4



TEST NUMBER: P332786-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3	1082.3
2.5°	1078.4	1079.9	1081.5	1082.2	1082.1	1081.9	1081.7	1081.6
5°	1072.6	1074.7	1076.8	1077.7	1077.3	1077.0	1076.6	1076.2
7.5°	1060.7	1062.4	1064.0	1064.8	1064.6	1064.4	1064.1	1063.9
10°	1050.7	1052.2	1053.8	1054.3	1053.9	1053.5	1053.2	1052.8
12.5°	1038.5	1040.2	1041.9	1042.4	1042.0	1041.4	1040.8	1040.3
15°	1015.2	1016.4	1017.5	1017.8	1017.2	1016.7	1016.1	1015.5
17.5°	988.7	989.4	990.2	990.3	989.9	989.5	989.2	988.8
20°	969.0	969.6	970.1	970.2	969.8	969.5	969.1	968.7
22.5°	948.4	949.4	950.5	950.6	949.9	949.3	948.5	947.9
25°	914.4	914.6	914.8	914.5	913.8	913.0	912.2	911.4
27.5°	876.4	875.9	875.4	874.7	873.8	872.8	871.8	870.8
30°	850.0	849.3	848.5	847.7	846.7	845.7	844.7	843.8
32.5°	823.4	822.5	821.6	820.6	819.6	818.6	817.7	816.8
35°	781.3	779.9	778.5	777.4	776.4	775.5	774.5	773.6
37.5°	737.1	735.6	734.3	732.9	731.6	730.3	729.0	727.7
40°	706.4	704.5	702.5	701.1	700.1	699.2	698.2	697.2
42.5°	676.6	674.4	672.1	670.7	670.1	669.4	668.8	668.1
45°	630.6	628.4	626.3	625.0	624.4	623.8	623.2	622.6
47.5°	586.0	583.6	581.1	579.3	577.8	576.3	574.9	573.4
50°	554.8	552.1	549.4	547.5	546.3	545.2	544.0	542.9
52.5°	522.9	520.4	518.0	516.2	514.7	513.2	511.8	510.3
55°	475.8	473.5	471.2	469.4	468.3	467.2	465.9	464.8
57.5°	428.7	426.5	424.3	422.7	421.5	420.4	419.3	418.2
60°	396.3	394.6	392.8	391.5	390.5	389.6	388.6	387.7
62.5°	364.7	363.1	361.6	360.3	359.3	358.3	357.4	356.4
65°	318.8	316.8	314.9	313.5	312.5	311.5	310.5	309.6
67.5°	271.4	269.5	267.7	266.6	266.4	266.1	265.8	265.5
70°	241.5	239.9	238.4	237.3	236.8	236.2	235.6	235.1
72.5°	211.6	210.3	209.1	208.2	207.6	207.0	206.4	205.9
75°	168.4	167.6	166.9	166.4	166.2	166.0	165.8	165.7
77.5°	127.5	127.3	127.1	126.7	126.2	125.7	125.2	124.7
80°	101.6	101.2	100.8	100.5	100.3	100.1	100.0	99.7
82.5°	78.3	78.0	77.8	77.6	77.5	77.2	77.0	76.8
85°	45.1	45.1	45.1	45.0	44.8	44.6	44.4	44.2
87.5°	19.6	19.8	20.0	20.1	20.1	20.1	20.2	20.3
90°	14.9	15.7	16.6	17.0	17.4	17.6	17.9	18.2
92.5°	24.9	25.4	25.9	26.3	26.4	26.6	26.7	26.9
95°	46.8	47.2	47.6	47.8	47.8	47.8	47.8	47.8
97.5°	73.7	74.2	74.7	74.9	74.9	74.9	74.9	74.9
100°	93.1	93.4	93.7	93.8	93.8	93.8	93.8	93.8
102.5°	113.7	114.1	114.4	114.6	114.8	114.9	115.0	115.1
105°	144.8	145.2	145.6	146.0	146.4	146.8	147.2	147.7
107.5°	178.6	178.9	179.3	179.4	179.4	179.4	179.4	179.4
110°	201.0	200.7	200.4	200.5	200.9	201.3	201.7	202.1



TEST NUMBER: P332786-930

CATALOG NUMBER: S124DIW-S795D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.1	225.0	225.0	225.0	225.1	225.2	225.3	225.3
115°	262.4	262.2	262.0	262.0	261.8	261.7	261.5	261.4
117.5°	298.2	297.7	297.2	296.9	296.6	296.3	296.0	295.8
120°	322.4	321.7	321.1	320.8	321.1	321.4	321.6	321.9
122.5°	347.0	346.6	346.1	345.6	345.1	344.6	344.2	343.7
125°	383.1	382.9	382.5	382.3	382.0	381.7	381.5	381.2
127.5°	417.6	417.4	417.0	416.8	416.6	416.4	416.1	416.0
130°	441.8	441.5	441.2	440.8	440.3	439.8	439.2	438.7
132.5°	464.6	464.3	464.0	463.7	463.6	463.3	463.1	462.9
135°	498.6	498.4	498.1	497.8	497.4	497.0	496.6	496.2
137.5°	531.7	531.3	531.0	530.8	530.9	531.0	531.1	531.2
140°	553.4	553.3	553.1	553.0	552.9	552.7	552.6	552.4
142.5°	574.0	573.9	573.9	573.9	573.8	573.8	573.8	573.7
145°	604.9	604.7	604.5	604.3	603.9	603.5	603.1	602.7
147.5°	632.8	632.8	632.6	632.5	632.3	632.3	632.1	631.9
150°	650.5	650.5	650.5	650.4	650.3	650.1	650.0	649.9
152.5°	667.1	667.4	667.7	667.7	667.4	667.1	666.7	666.3
155°	690.3	690.8	691.4	691.4	690.8	690.3	689.7	689.3
157.5°	710.7	711.1	711.5	711.5	711.0	710.6	710.1	709.6
160°	723.3	723.7	724.1	724.0	723.3	722.6	721.9	721.3
162.5°	734.6	735.3	736.1	736.1	735.4	734.7	734.1	733.4
165°	749.5	750.3	751.1	751.3	750.7	750.2	749.7	749.1
167.5°	762.1	762.9	763.7	763.7	762.9	762.1	761.2	760.3
170°	768.9	769.7	770.5	770.5	769.5	768.6	767.6	766.7
172.5°	774.0	774.9	775.8	775.8	774.8	773.9	772.9	772.0
175°	779.4	780.4	781.3	781.3	780.4	779.4	778.5	777.6
177.5°	782.4	783.2	784.0	783.9	783.0	782.2	781.3	780.5
180°	782.4	782.4	782.4	782.4	782.4	782.4	782.4	782.4

(END OF REPORT)