

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333107-930

Luminaire Tested: **S124RDIW-S1195D1340U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333107-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1340U930-4F0-1E-UDD-A
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8461.6 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333107-930
CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	98	94	90	87	90	86	83	80	73	71	69	60	59	57	49	48	47	42
2	89	82	76	71	82	76	71	67	64	61	57	54	51	49	44	42	40	36
3	82	73	66	60	75	67	61	56	57	53	49	48	44	42	39	37	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30	27
5	69	58	50	44	63	54	47	41	46	40	36	39	35	31	32	29	27	23
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13043	13043	13043	13043
5°	15129	13083	11563	13083
10°	17898	13025	10320	13025
15°	20674	12904	8868	12904
20°	23018	12740	8019	12740
25°	23762	12577	7445	12577
30°	20801	12379	7100	12379
35°	16192	12086	6890	12086
40°	12142	11751	6777	11751
45°	9587	11215	6719	11215
50°	8093	10595	6523	10595
55°	7054	9913	6175	9913
60°	6347	9206	5465	9206
65°	5595	8443	4701	8443
70°	5039	7652	4242	7652
75°	4223	6781	3615	6781
80°	3570	5779	3389	5779
85°	3010	4520	3010	4520



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.5	1.9
10°-20°	472.2	5.6
20°-30°	738.6	8.7
30°-40°	821.0	9.7
40°-50°	728.5	8.6
50°-60°	567.6	6.7
60°-70°	371.6	4.4
70°-80°	182.8	2.2
80°-90°	49.2	0.6
90°-100°	48.4	0.6
100°-110°	308.3	3.6
110°-120°	589.8	7.0
120°-130°	748.7	8.8
130°-140°	801.1	9.5
140°-150°	749.1	8.9
150°-160°	604.1	7.1
160°-170°	389.6	4.6
170°-180°	134.3	1.6
0°-30°	1367.3	16.2
0°-40°	2188.4	25.9
0°-60°	3484.5	41.2
0°-90°	4088.0	48.3
90°-120°	946.5	11.2
90°-150°	3245.5	38.4
90°-180°	4374.0	51.7
0°-180°	8461.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1616	1616	1616	1616	1616	
5°	1867	1614	1427	1614	1867	189
15°	2474	1544	1061	1544	2474	703
25°	2668	1412	836	1412	2668	1183
35°	1643	1226	699	1226	1643	1030
45°	840	982	588	982	840	665
55°	501	704	439	704	501	456
65°	293	442	246	442	293	295
75°	135	217	116	217	135	149
85°	32	49	32	49	32	37
90°	32	3	32	3	32	15
95°	31	58	31	58	31	24
105°	301	318	301	318	301	263
115°	598	594	598	594	598	592
125°	842	835	842	835	842	750
135°	1044	1036	1044	1036	1044	803
145°	1201	1195	1201	1195	1201	751
155°	1309	1310	1309	1310	1309	604
165°	1376	1382	1376	1382	1376	389
175°	1405	1414	1405	1414	1405	134
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1704.1	1708.9	1704.1	1703.6	1698.4	1696.9	1694.8	1688.0	1675.5	1668.3	1669.8
5°	1866.9	1883.2	1874.0	1872.7	1858.5	1844.1	1835.0	1814.2	1792.0	1777.1	1764.7
7.5°	2055.1	2064.5	2058.8	2049.7	2026.5	2013.4	1992.3	1964.8	1925.1	1894.8	1867.0
10°	2183.3	2191.0	2188.5	2171.5	2154.6	2120.1	2100.6	2062.2	2012.1	1972.4	1935.3
12.5°	2309.3	2317.7	2294.7	2295.5	2263.4	2236.3	2205.3	2157.0	2099.1	2047.9	2001.4
15°	2473.6	2463.2	2463.2	2450.1	2414.3	2376.6	2344.7	2293.9	2221.0	2159.8	2095.4
17.5°	2602.2	2605.9	2600.5	2569.8	2541.7	2502.6	2444.2	2384.9	2317.2	2235.1	2169.2
20°	2679.3	2679.3	2673.4	2652.6	2616.1	2574.5	2511.4	2446.9	2360.9	2278.3	2204.1
22.5°	2710.5	2712.6	2705.7	2688.5	2655.8	2615.1	2561.3	2495.9	2407.3	2314.2	2222.3
25°	2667.6	2680.0	2681.2	2676.7	2666.9	2642.1	2596.0	2528.9	2449.5	2348.6	2249.7
27.5°	2449.1	2464.7	2478.4	2500.9	2530.9	2546.5	2548.5	2514.5	2445.2	2348.1	2248.5
30°	2231.4	2244.4	2286.8	2342.1	2385.1	2424.1	2458.0	2467.1	2428.0	2340.8	2236.0
32.5°	1989.8	2007.5	2049.8	2109.3	2180.9	2247.0	2323.1	2361.8	2360.9	2308.5	2211.5
35°	1643.0	1656.0	1695.1	1757.5	1843.5	1941.8	2062.2	2155.9	2219.7	2215.2	2155.9
37.5°	1325.0	1339.8	1379.2	1431.0	1514.3	1636.1	1752.6	1881.7	1999.7	2066.0	2046.2
40°	1152.2	1152.8	1191.2	1244.6	1322.7	1428.8	1555.8	1698.9	1830.4	1937.9	1958.7
42.5°	1015.7	1015.9	1041.2	1098.8	1155.0	1254.9	1376.1	1518.3	1672.2	1796.2	1851.4
45°	839.7	845.5	866.4	900.9	945.2	1029.8	1126.7	1258.9	1431.4	1578.5	1670.3
47.5°	711.1	719.7	733.0	761.1	796.4	852.7	932.9	1051.7	1192.0	1353.8	1484.4
50°	644.4	645.7	662.7	678.2	708.9	753.8	824.1	923.0	1051.9	1207.5	1352.7
52.5°	587.2	586.9	597.0	616.9	641.7	676.7	733.4	823.5	937.8	1077.3	1227.2
55°	501.2	504.5	512.3	527.9	546.8	571.5	616.4	684.1	774.0	893.1	1029.2
57.5°	435.9	437.6	443.7	450.3	467.7	485.6	519.3	566.3	642.1	739.6	866.4
60°	393.1	393.8	395.7	405.5	419.2	436.1	458.9	498.6	562.4	651.6	751.9
62.5°	351.5	352.7	355.7	362.8	373.4	385.1	409.0	440.8	493.7	569.8	660.1
65°	292.9	293.6	298.2	300.8	309.2	319.6	337.2	358.7	395.1	458.9	527.3
67.5°	244.8	244.8	245.0	248.5	254.4	261.3	271.8	289.0	316.5	355.7	416.0
70°	213.5	213.5	214.8	216.8	220.0	225.8	231.7	244.8	265.0	296.9	343.1
72.5°	184.3	184.8	186.1	186.5	188.3	193.1	197.4	205.7	220.7	244.8	282.1
75°	135.4	137.4	140.6	143.2	146.4	145.8	150.3	155.6	160.1	174.5	195.9
77.5°	100.8	99.7	100.1	102.3	102.7	103.4	106.6	110.6	114.1	120.8	128.5
80°	76.8	76.8	78.8	79.4	78.8	79.4	82.7	84.6	85.9	88.5	95.7
82.5°	58.0	59.1	58.5	59.1	59.5	60.2	62.9	63.3	64.6	65.6	68.6
85°	32.5	33.2	33.8	32.5	32.5	32.5	33.8	34.5	35.8	35.1	36.4
87.5°	17.8	17.2	17.6	17.5	17.9	17.2	17.4	18.3	16.9	17.1	16.8
90°	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1	24.7	23.2	21.4
92.5°	29.2	29.1	29.0	28.9	28.8	28.0	26.7	25.3	23.8	22.4	20.5
95°	30.7	30.4	30.2	29.9	29.8	28.9	27.5	26.1	24.7	23.2	23.0
97.5°	29.6	29.4	29.1	28.9	28.7	28.5	28.4	28.2	28.0	27.9	54.1
100°	29.6	29.4	29.1	28.9	28.7	30.6	34.6	38.6	42.6	46.6	78.9
102.5°	30.5	30.4	30.3	30.3	30.2	51.8	94.9	138.0	181.1	224.2	228.4
105°	301.4	309.8	318.3	326.8	335.3	338.4	336.3	334.2	332.1	330.0	328.7
107.5°	420.0	419.1	418.2	417.4	416.5	415.5	414.5	413.4	412.4	411.4	409.8
110°	471.7	470.9	470.3	469.5	468.8	468.2	467.7	467.3	466.8	466.4	465.0



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	523.3	522.4	521.5	520.6	519.7	519.3	519.3	519.4	519.6	519.7	519.0
115°	598.5	598.5	598.5	598.5	598.5	598.3	597.9	597.4	596.9	596.4	596.6
117.5°	675.1	675.2	675.3	675.4	675.5	675.6	675.6	675.7	675.9	676.0	675.4
120°	723.3	723.8	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3	723.6
122.5°	770.7	771.2	771.6	772.1	772.6	772.7	772.4	772.1	771.8	771.5	771.2
125°	841.8	841.6	841.3	841.1	840.8	840.3	839.7	838.9	838.2	837.6	838.0
127.5°	904.2	904.3	904.5	904.7	904.9	905.1	905.2	905.4	905.5	905.6	904.6
130°	946.5	946.5	946.5	946.5	946.5	946.3	946.1	945.8	945.7	945.4	944.7
132.5°	985.4	985.5	985.8	985.9	986.1	986.1	985.9	985.6	985.4	985.1	984.2
135°	1043.7	1043.3	1042.8	1042.4	1041.9	1041.4	1040.9	1040.5	1040.0	1039.5	1038.6
137.5°	1093.6	1093.8	1094.0	1094.1	1094.2	1094.1	1093.5	1093.0	1092.5	1091.9	1091.0
140°	1128.4	1128.1	1127.9	1127.6	1127.4	1126.9	1126.3	1125.5	1124.8	1124.1	1123.6
142.5°	1157.1	1157.1	1157.0	1157.0	1156.9	1156.7	1156.1	1155.6	1155.1	1154.5	1154.3
145°	1201.3	1200.9	1200.4	1199.9	1199.5	1199.1	1198.8	1198.6	1198.4	1198.2	1198.2
147.5°	1237.9	1237.6	1237.5	1237.2	1237.0	1236.7	1236.6	1236.4	1236.2	1236.0	1236.2
150°	1261.6	1261.3	1261.1	1260.9	1260.6	1260.5	1260.5	1260.5	1260.5	1260.5	1260.8
152.5°	1281.9	1282.1	1282.1	1282.3	1282.5	1282.3	1282.0	1281.6	1281.2	1280.8	1281.2
155°	1309.2	1309.9	1310.6	1311.3	1312.0	1311.9	1310.9	1310.0	1309.0	1308.1	1308.8
157.5°	1332.0	1333.3	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0	1332.9
160°	1347.3	1348.7	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3	1347.4
162.5°	1359.1	1360.7	1362.3	1363.9	1365.5	1365.5	1364.2	1362.8	1361.3	1359.9	1360.2
165°	1375.8	1377.9	1380.1	1382.2	1384.2	1384.4	1382.5	1380.6	1378.8	1376.9	1376.9
167.5°	1388.3	1390.7	1392.9	1395.3	1397.7	1397.8	1395.7	1393.7	1391.6	1389.5	1389.7
170°	1395.9	1398.2	1400.6	1403.0	1405.2	1405.5	1403.6	1401.7	1399.9	1398.0	1397.7
172.5°	1400.1	1402.6	1405.2	1407.7	1410.3	1410.6	1408.8	1406.8	1404.9	1403.0	1402.8
175°	1405.4	1408.2	1411.0	1413.9	1416.7	1417.1	1415.0	1412.8	1410.7	1408.6	1408.3
177.5°	1408.8	1411.0	1413.3	1415.5	1417.8	1418.2	1416.7	1415.2	1413.6	1412.2	1411.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1664.6	1657.3	1653.7	1645.4	1635.4	1630.2	1625.5	1618.8	1609.9	1600.5	1593.7
5°	1749.1	1733.5	1713.9	1690.5	1669.7	1649.5	1631.9	1614.4	1594.2	1573.4	1552.5
7.5°	1835.8	1805.1	1771.9	1733.5	1696.1	1662.2	1630.8	1600.9	1567.1	1536.8	1509.1
10°	1896.2	1854.6	1808.3	1759.5	1710.7	1668.3	1626.7	1588.9	1547.3	1510.2	1479.0
12.5°	1945.1	1896.2	1840.6	1779.8	1721.1	1669.9	1622.0	1572.8	1525.4	1485.2	1443.6
15°	2026.3	1959.3	1884.5	1811.6	1735.4	1665.7	1601.3	1544.0	1490.0	1433.4	1393.7
17.5°	2082.3	2002.7	1911.7	1824.1	1734.1	1652.0	1577.6	1509.4	1447.1	1389.3	1342.0
20°	2115.5	2027.6	1926.8	1827.2	1726.3	1638.4	1558.4	1482.9	1418.4	1355.9	1307.1
22.5°	2134.3	2037.0	1926.8	1822.5	1718.0	1622.8	1534.9	1456.3	1386.1	1323.6	1269.6
25°	2140.3	2036.1	1923.5	1803.8	1689.2	1588.3	1497.1	1411.9	1333.7	1271.3	1214.0
27.5°	2132.0	2009.3	1894.0	1771.1	1652.9	1546.5	1450.8	1361.2	1283.0	1215.9	1157.2
30°	2119.5	1987.9	1864.3	1736.8	1616.9	1514.7	1413.8	1328.0	1246.6	1176.9	1117.7
32.5°	2092.4	1961.9	1828.9	1698.2	1576.9	1471.5	1375.8	1289.4	1209.6	1138.4	1075.5
35°	2038.7	1906.6	1762.1	1628.0	1508.9	1399.5	1309.7	1226.4	1150.2	1074.1	1007.6
37.5°	1968.1	1833.0	1689.3	1542.5	1423.2	1320.0	1237.5	1159.4	1085.0	1015.5	941.9
40°	1901.4	1778.4	1629.9	1484.2	1361.8	1262.2	1186.0	1115.1	1040.2	971.2	897.6
42.5°	1820.7	1715.9	1565.9	1419.6	1298.8	1202.8	1131.9	1062.5	994.4	927.5	850.8
45°	1686.0	1606.5	1465.9	1325.4	1203.6	1108.6	1043.5	982.3	922.3	858.6	786.4
47.5°	1531.5	1477.7	1356.4	1212.4	1099.8	1014.3	951.5	901.4	850.8	787.0	723.6
50°	1424.2	1389.8	1272.6	1141.1	1033.7	955.0	890.5	843.6	801.3	740.1	683.5
52.5°	1309.7	1291.4	1192.4	1066.7	962.9	885.7	830.6	788.4	745.6	694.8	641.8
55°	1135.2	1145.0	1061.0	952.4	854.7	789.6	739.5	704.3	667.9	624.9	583.9
57.5°	956.9	992.5	936.2	840.7	749.3	689.1	651.3	621.7	591.2	555.5	520.5
60°	850.1	880.0	848.2	764.2	684.1	628.2	593.0	570.2	539.6	507.1	480.4
62.5°	746.0	778.0	759.1	691.3	616.9	568.8	537.8	516.6	493.8	465.5	437.7
65°	615.1	635.9	626.9	580.0	527.3	486.2	457.6	442.0	421.2	400.3	375.6
67.5°	471.2	511.4	506.1	481.2	435.6	403.6	384.8	371.0	352.0	336.6	319.8
70°	387.3	424.4	423.8	403.6	378.9	348.9	335.9	324.2	307.2	292.3	278.6
72.5°	317.0	351.0	356.0	340.6	323.7	301.0	288.5	280.5	264.0	253.7	242.6
75°	222.0	246.7	253.2	253.2	245.4	233.7	222.7	217.4	205.7	196.6	190.0
77.5°	145.5	161.2	171.3	173.7	174.9	171.0	161.8	158.2	149.2	145.9	139.7
80°	102.8	113.2	125.0	128.9	132.2	130.9	126.9	124.3	115.9	112.6	110.0
82.5°	71.1	76.8	86.4	95.1	94.1	97.5	94.1	92.0	85.7	84.5	81.9
85°	37.1	37.7	39.1	44.9	48.2	49.5	50.1	48.8	46.9	46.9	42.3
87.5°	16.4	15.5	16.1	15.7	15.7	17.3	18.3	18.3	17.3	16.2	15.2
90°	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2	5.8	8.3	10.9
92.5°	18.7	16.8	14.9	13.9	13.8	13.6	13.5	13.3	13.5	13.6	13.8
95°	22.8	22.6	22.3	26.2	34.2	42.2	50.1	58.1	50.1	42.2	34.2
97.5°	80.4	106.6	132.8	143.4	138.4	133.5	128.5	123.5	128.5	133.5	138.4
100°	111.4	143.8	176.3	190.4	186.1	181.9	177.7	173.4	177.7	181.9	186.1
102.5°	232.7	236.8	241.1	241.7	238.6	235.5	232.4	229.3	232.4	235.5	238.6
105°	327.6	326.4	325.2	323.9	322.5	321.1	319.7	318.3	319.7	321.1	322.5
107.5°	408.1	406.6	405.0	403.8	403.1	402.4	401.7	401.0	401.7	402.4	403.1
110°	463.5	462.1	460.7	459.7	458.9	458.3	457.5	456.8	457.5	458.3	458.9



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	518.4	517.7	517.0	516.1	514.8	513.6	512.3	510.9	512.3	513.6	514.8
115°	596.9	597.1	597.4	597.1	596.4	595.7	595.0	594.3	595.0	595.7	596.4
117.5°	674.9	674.4	673.8	673.1	672.2	671.2	670.3	669.4	670.3	671.2	672.2
120°	723.8	724.1	724.2	723.9	723.0	722.0	721.1	720.2	721.1	722.0	723.0
122.5°	770.9	770.5	770.2	769.8	769.2	768.7	768.1	767.5	768.1	768.7	769.2
125°	838.5	838.9	839.4	839.2	838.2	837.3	836.3	835.4	836.3	837.3	838.2
127.5°	903.4	902.4	901.3	900.7	900.4	900.2	899.9	899.7	899.9	900.2	900.4
130°	944.0	943.3	942.6	942.1	941.8	941.7	941.4	941.2	941.4	941.7	941.8
132.5°	983.3	982.5	981.6	980.9	980.5	980.1	979.7	979.3	979.7	980.1	980.5
135°	1037.6	1036.7	1035.8	1035.4	1035.7	1035.8	1036.1	1036.3	1036.1	1035.8	1035.7
137.5°	1089.9	1088.8	1087.9	1087.3	1087.2	1087.0	1087.0	1086.9	1087.0	1087.0	1087.2
140°	1123.2	1122.7	1122.3	1121.8	1121.3	1120.8	1120.4	1119.9	1120.4	1120.8	1121.3
142.5°	1154.0	1153.7	1153.4	1152.9	1152.0	1151.2	1150.3	1149.5	1150.3	1151.2	1152.0
145°	1198.2	1198.2	1198.2	1197.8	1197.1	1196.4	1195.6	1195.0	1195.6	1196.4	1197.1
147.5°	1236.5	1236.7	1237.0	1236.4	1235.1	1233.8	1232.4	1231.1	1232.4	1233.8	1235.1
150°	1261.0	1261.3	1261.4	1261.1	1260.2	1259.2	1258.3	1257.4	1258.3	1259.2	1260.2
152.5°	1281.7	1282.1	1282.5	1282.4	1281.6	1280.8	1280.1	1279.4	1280.1	1280.8	1281.6
155°	1309.5	1310.3	1310.9	1311.2	1310.9	1310.7	1310.4	1310.3	1310.4	1310.7	1310.9
157.5°	1333.6	1334.4	1335.2	1335.7	1335.8	1335.9	1336.1	1336.3	1336.1	1335.9	1335.8
160°	1347.7	1347.9	1348.2	1348.7	1349.3	1350.1	1350.8	1351.4	1350.8	1350.1	1349.3
162.5°	1360.4	1360.7	1360.9	1361.5	1362.4	1363.3	1364.1	1365.0	1364.1	1363.3	1362.4
165°	1376.9	1376.9	1376.9	1377.4	1378.6	1379.8	1381.0	1382.2	1381.0	1379.8	1378.6
167.5°	1389.8	1390.0	1390.1	1390.8	1392.0	1393.3	1394.5	1395.7	1394.5	1393.3	1392.0
170°	1397.5	1397.3	1397.1	1397.7	1399.1	1400.4	1401.9	1403.3	1401.9	1400.4	1399.1
172.5°	1402.6	1402.4	1402.2	1402.7	1404.1	1405.6	1407.0	1408.3	1407.0	1405.6	1404.1
175°	1408.1	1407.9	1407.6	1408.2	1409.7	1411.0	1412.4	1413.9	1412.4	1411.0	1409.7
177.5°	1411.4	1411.0	1410.6	1411.1	1412.4	1413.7	1415.1	1416.4	1415.1	1413.7	1412.4
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1586.5	1581.3	1574.5	1566.7	1557.3	1549.0	1545.3	1548.5	1550.0	1545.9	1545.3
5°	1538.1	1521.9	1508.9	1489.4	1473.7	1460.7	1451.6	1447.7	1449.0	1438.6	1436.0
7.5°	1483.9	1464.6	1443.2	1420.1	1398.5	1379.3	1369.3	1363.8	1352.8	1348.1	1340.2
10°	1449.0	1422.9	1402.2	1374.8	1350.1	1327.3	1316.2	1307.1	1296.0	1290.8	1279.8
12.5°	1413.1	1382.8	1359.9	1331.5	1306.3	1278.9	1268.3	1251.4	1234.0	1223.1	1208.9
15°	1362.4	1326.0	1298.0	1264.1	1234.2	1203.0	1174.9	1143.7	1132.0	1107.3	1092.9
17.5°	1303.2	1266.2	1231.6	1186.2	1140.0	1101.1	1071.3	1041.4	1023.4	1007.6	1000.4
20°	1264.1	1230.3	1182.1	1129.4	1078.0	1035.0	1010.9	991.4	971.8	960.8	953.0
22.5°	1227.2	1183.9	1128.0	1071.1	1019.6	986.0	965.6	945.6	929.7	919.2	908.7
25°	1165.2	1108.6	1049.3	984.2	949.1	919.8	897.6	881.3	871.6	857.9	852.7
27.5°	1101.6	1032.9	967.6	923.8	887.2	860.4	841.1	828.9	816.5	807.8	801.0
30°	1052.6	982.9	924.3	882.6	845.5	823.5	807.8	793.5	783.7	776.6	771.4
32.5°	1004.1	934.5	885.3	840.5	811.2	789.6	772.9	762.2	754.6	745.3	742.2
35°	934.1	872.3	829.3	789.0	759.0	739.5	726.4	715.4	708.9	706.3	704.3
37.5°	866.8	816.1	770.0	736.9	710.2	694.8	679.5	674.0	669.5	664.9	667.0
40°	824.1	776.6	735.6	700.4	678.9	662.0	652.9	646.4	642.5	642.5	642.5
42.5°	787.1	740.6	700.7	669.2	647.7	633.4	623.2	617.8	616.4	616.0	619.1
45°	729.7	686.7	646.4	620.4	602.1	587.8	582.0	577.4	577.4	580.0	580.7
47.5°	672.8	632.6	600.1	571.0	554.3	545.4	540.3	537.9	538.2	540.8	543.8
50°	637.9	598.2	566.3	540.3	524.6	516.2	511.6	510.4	511.6	511.6	516.2
52.5°	599.9	564.4	533.0	511.1	493.4	485.5	483.0	481.2	481.9	484.0	486.0
55°	544.2	512.3	482.3	461.5	448.5	443.3	437.4	438.1	436.8	438.1	438.1
57.5°	488.4	459.7	431.9	415.3	403.8	396.3	389.9	391.8	389.8	389.6	388.5
60°	452.4	421.2	399.0	384.1	371.0	364.5	358.7	360.0	358.0	356.7	354.1
62.5°	413.4	387.3	366.2	351.8	341.4	333.8	327.9	326.6	322.1	317.6	311.9
65°	356.7	335.3	316.3	302.7	292.9	287.1	282.5	278.6	268.8	258.4	253.2
67.5°	301.7	286.2	268.6	257.0	249.1	241.4	232.7	226.0	216.9	211.2	207.9
70°	266.2	251.3	236.3	225.2	216.8	209.6	199.8	195.3	188.7	186.1	183.0
72.5°	232.4	218.4	204.6	194.5	185.5	179.9	172.3	167.7	164.9	163.8	160.5
75°	181.0	169.9	159.5	150.3	143.2	139.3	136.1	132.8	131.5	125.6	122.4
77.5°	132.0	124.7	118.2	111.7	106.6	104.0	97.8	94.0	91.8	89.0	88.4
80°	102.8	97.7	91.2	87.2	80.1	77.5	74.8	74.2	73.5	72.9	72.2
82.5°	77.4	72.2	65.6	63.3	61.3	59.8	58.2	57.6	56.9	57.3	57.2
85°	39.1	36.4	36.4	35.8	35.1	34.5	33.8	33.8	33.2	33.8	33.2
87.5°	15.7	15.7	16.1	15.3	16.2	16.6	16.4	16.7	17.4	16.7	16.9
90°	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1	27.5	28.9	29.8
92.5°	13.9	14.9	16.8	18.7	20.5	22.4	23.8	25.3	26.7	28.0	28.8
95°	26.2	22.3	22.6	22.8	23.0	23.2	24.7	26.1	27.5	28.9	29.8
97.5°	143.4	132.8	106.6	80.4	54.1	27.9	28.0	28.2	28.4	28.5	28.7
100°	190.4	176.3	143.8	111.4	78.9	46.6	42.6	38.6	34.6	30.6	28.7
102.5°	241.7	241.1	236.8	232.7	228.4	224.2	181.1	138.0	94.9	51.8	30.2
105°	323.9	325.2	326.4	327.6	328.7	330.0	332.1	334.2	336.3	338.4	335.3
107.5°	403.8	405.0	406.6	408.1	409.8	411.4	412.4	413.4	414.5	415.5	416.5
110°	459.7	460.7	462.1	463.5	465.0	466.4	466.8	467.3	467.7	468.2	468.8



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	516.1	517.0	517.7	518.4	519.0	519.7	519.6	519.4	519.3	519.3	519.7
115°	597.1	597.4	597.1	596.9	596.6	596.4	596.9	597.4	597.9	598.3	598.5
117.5°	673.1	673.8	674.4	674.9	675.4	676.0	675.9	675.7	675.6	675.6	675.5
120°	723.9	724.2	724.1	723.8	723.6	723.3	723.8	724.2	724.7	725.2	725.2
122.5°	769.8	770.2	770.5	770.9	771.2	771.5	771.8	772.1	772.4	772.7	772.6
125°	839.2	839.4	838.9	838.5	838.0	837.6	838.2	838.9	839.7	840.3	840.8
127.5°	900.7	901.3	902.4	903.4	904.6	905.6	905.5	905.4	905.2	905.1	904.9
130°	942.1	942.6	943.3	944.0	944.7	945.4	945.7	945.8	946.1	946.3	946.5
132.5°	980.9	981.6	982.5	983.3	984.2	985.1	985.4	985.6	985.9	986.1	986.1
135°	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0	1040.5	1040.9	1041.4	1041.9
137.5°	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5	1093.0	1093.5	1094.1	1094.2
140°	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8	1125.5	1126.3	1126.9	1127.4
142.5°	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1	1155.6	1156.1	1156.7	1156.9
145°	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4	1198.6	1198.8	1199.1	1199.5
147.5°	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2	1236.4	1236.6	1236.7	1237.0
150°	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5	1260.5	1260.5	1260.5	1260.6
152.5°	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2	1281.6	1282.0	1282.3	1282.5
155°	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0	1310.0	1310.9	1311.9	1312.0
157.5°	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3	1334.5	1335.7	1336.9	1336.9
160°	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7	1350.1	1351.4	1352.9	1352.9
162.5°	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3	1362.8	1364.2	1365.5	1365.5
165°	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8	1380.6	1382.5	1384.4	1384.2
167.5°	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6	1393.7	1395.7	1397.8	1397.7
170°	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9	1401.7	1403.6	1405.5	1405.2
172.5°	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9	1406.8	1408.8	1410.6	1410.3
175°	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7	1412.8	1415.0	1417.1	1416.7
177.5°	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6	1415.2	1416.7	1418.2	1417.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333107-930
 CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1542.2	1543.3	1539.6	1538.6	1539.6	1543.3	1542.2	1545.3	1545.9	1550.0	1548.5
5°	1430.8	1429.5	1426.2	1426.9	1426.2	1429.5	1430.8	1436.0	1438.6	1449.0	1447.7
7.5°	1335.5	1330.4	1331.8	1326.7	1331.8	1330.4	1335.5	1340.2	1348.1	1352.8	1363.8
10°	1277.2	1270.0	1264.1	1258.9	1264.1	1270.0	1277.2	1279.8	1290.8	1296.0	1307.1
12.5°	1197.5	1191.3	1183.4	1185.0	1183.4	1191.3	1197.5	1208.9	1223.1	1234.0	1251.4
15°	1084.4	1074.7	1059.1	1061.0	1059.1	1074.7	1084.4	1092.9	1107.3	1132.0	1143.7
17.5°	988.8	988.9	981.8	983.4	981.8	988.9	988.8	1000.4	1007.6	1023.4	1041.4
20°	939.3	934.7	935.4	933.4	935.4	934.7	939.3	953.0	960.8	971.8	991.4
22.5°	904.9	899.4	894.8	890.7	894.8	899.4	904.9	908.7	919.2	929.7	945.6
25°	846.9	842.9	837.1	835.8	837.1	842.9	846.9	852.7	857.9	871.6	881.3
27.5°	795.8	795.1	792.7	789.7	792.7	795.1	795.8	801.0	807.8	816.5	828.9
30°	766.1	764.8	763.5	761.6	763.5	764.8	766.1	771.4	776.6	783.7	793.5
32.5°	739.6	738.8	737.5	737.7	737.5	738.8	739.6	742.2	745.3	754.6	762.2
35°	701.7	701.1	699.8	699.1	699.8	701.1	701.7	704.3	706.3	708.9	715.4
37.5°	666.3	668.0	667.2	667.1	667.2	668.0	666.3	667.0	664.9	669.5	674.0
40°	641.8	642.5	643.8	643.1	643.8	642.5	641.8	642.5	642.5	642.5	646.4
42.5°	621.5	621.7	623.5	621.3	623.5	621.7	621.5	619.1	616.0	616.4	617.8
45°	585.2	589.1	588.5	588.5	588.5	589.1	585.2	580.7	580.0	577.4	577.4
47.5°	545.5	548.9	549.8	549.7	549.8	548.9	545.5	543.8	540.8	538.2	537.9
50°	519.4	518.1	520.1	519.4	520.1	518.1	519.4	516.2	511.6	511.6	510.4
52.5°	487.7	488.0	487.8	487.1	487.8	488.0	487.7	486.0	484.0	481.9	481.2
55°	438.7	439.4	438.1	438.7	438.1	439.4	438.7	438.1	438.1	436.8	438.1
57.5°	385.6	382.5	383.8	382.2	383.8	382.5	385.6	388.5	389.6	389.8	391.8
60°	347.6	342.4	341.1	338.5	341.1	342.4	347.6	354.1	356.7	358.0	360.0
62.5°	304.9	301.3	296.9	298.9	296.9	301.3	304.9	311.9	317.6	322.1	326.6
65°	248.0	245.4	243.4	246.1	243.4	245.4	248.0	253.2	258.4	268.8	278.6
67.5°	205.3	203.9	203.9	202.6	203.9	203.9	205.3	207.9	211.2	216.9	226.0
70°	183.0	181.0	181.0	179.7	181.0	181.0	183.0	183.0	186.1	188.7	195.3
72.5°	160.0	158.1	158.6	157.8	158.6	158.1	160.0	160.5	163.8	164.9	167.7
75°	118.5	115.2	115.2	115.9	115.2	115.2	118.5	122.4	125.6	131.5	132.8
77.5°	88.4	87.7	88.6	87.5	88.6	87.7	88.4	88.4	89.0	91.8	94.0
80°	72.2	71.6	70.9	72.9	70.9	71.6	72.2	72.2	72.9	73.5	74.2
82.5°	56.1	56.0	55.8	58.3	55.8	56.0	56.1	57.2	57.3	56.9	57.6
85°	33.8	32.5	33.8	32.5	33.8	32.5	33.8	33.2	33.8	33.2	33.8
87.5°	18.0	17.6	17.2	17.8	17.2	17.6	18.0	16.9	16.7	17.4	16.7
90°	30.3	30.8	31.2	31.7	31.2	30.8	30.3	29.8	28.9	27.5	26.1
92.5°	28.9	29.0	29.1	29.2	29.1	29.0	28.9	28.8	28.0	26.7	25.3
95°	29.9	30.2	30.4	30.7	30.4	30.2	29.9	29.8	28.9	27.5	26.1
97.5°	28.9	29.1	29.4	29.6	29.4	29.1	28.9	28.7	28.5	28.4	28.2
100°	28.9	29.1	29.4	29.6	29.4	29.1	28.9	28.7	30.6	34.6	38.6
102.5°	30.3	30.3	30.4	30.5	30.4	30.3	30.3	30.2	51.8	94.9	138.0
105°	326.8	318.3	309.8	301.4	309.8	318.3	326.8	335.3	338.4	336.3	334.2
107.5°	417.4	418.2	419.1	420.0	419.1	418.2	417.4	416.5	415.5	414.5	413.4
110°	469.5	470.3	470.9	471.7	470.9	470.3	469.5	468.8	468.2	467.7	467.3



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	520.6	521.5	522.4	523.3	522.4	521.5	520.6	519.7	519.3	519.3	519.4
115°	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.5	598.3	597.9	597.4
117.5°	675.4	675.3	675.2	675.1	675.2	675.3	675.4	675.5	675.6	675.6	675.7
120°	724.7	724.2	723.8	723.3	723.8	724.2	724.7	725.2	725.2	724.7	724.2
122.5°	772.1	771.6	771.2	770.7	771.2	771.6	772.1	772.6	772.7	772.4	772.1
125°	841.1	841.3	841.6	841.8	841.6	841.3	841.1	840.8	840.3	839.7	838.9
127.5°	904.7	904.5	904.3	904.2	904.3	904.5	904.7	904.9	905.1	905.2	905.4
130°	946.5	946.5	946.5	946.5	946.5	946.5	946.5	946.5	946.3	946.1	945.8
132.5°	985.9	985.8	985.5	985.4	985.5	985.8	985.9	986.1	986.1	985.9	985.6
135°	1042.4	1042.8	1043.3	1043.7	1043.3	1042.8	1042.4	1041.9	1041.4	1040.9	1040.5
137.5°	1094.1	1094.0	1093.8	1093.6	1093.8	1094.0	1094.1	1094.2	1094.1	1093.5	1093.0
140°	1127.6	1127.9	1128.1	1128.4	1128.1	1127.9	1127.6	1127.4	1126.9	1126.3	1125.5
142.5°	1157.0	1157.0	1157.1	1157.1	1157.1	1157.0	1157.0	1156.9	1156.7	1156.1	1155.6
145°	1199.9	1200.4	1200.9	1201.3	1200.9	1200.4	1199.9	1199.5	1199.1	1198.8	1198.6
147.5°	1237.2	1237.5	1237.6	1237.9	1237.6	1237.5	1237.2	1237.0	1236.7	1236.6	1236.4
150°	1260.9	1261.1	1261.3	1261.6	1261.3	1261.1	1260.9	1260.6	1260.5	1260.5	1260.5
152.5°	1282.3	1282.1	1282.1	1281.9	1282.1	1282.1	1282.3	1282.5	1282.3	1282.0	1281.6
155°	1311.3	1310.6	1309.9	1309.2	1309.9	1310.6	1311.3	1312.0	1311.9	1310.9	1310.0
157.5°	1335.7	1334.5	1333.3	1332.0	1333.3	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5
160°	1351.4	1350.1	1348.7	1347.3	1348.7	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1
162.5°	1363.9	1362.3	1360.7	1359.1	1360.7	1362.3	1363.9	1365.5	1365.5	1364.2	1362.8
165°	1382.2	1380.1	1377.9	1375.8	1377.9	1380.1	1382.2	1384.2	1384.4	1382.5	1380.6
167.5°	1395.3	1392.9	1390.7	1388.3	1390.7	1392.9	1395.3	1397.7	1397.8	1395.7	1393.7
170°	1403.0	1400.6	1398.2	1395.9	1398.2	1400.6	1403.0	1405.2	1405.5	1403.6	1401.7
172.5°	1407.7	1405.2	1402.6	1400.1	1402.6	1405.2	1407.7	1410.3	1410.6	1408.8	1406.8
175°	1413.9	1411.0	1408.2	1405.4	1408.2	1411.0	1413.9	1416.7	1417.1	1415.0	1412.8
177.5°	1415.5	1413.3	1411.0	1408.8	1411.0	1413.3	1415.5	1417.8	1418.2	1416.7	1415.2
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1545.3	1549.0	1557.3	1566.7	1574.5	1581.3	1586.5	1593.7	1600.5	1609.9	1618.8
5°	1451.6	1460.7	1473.7	1489.4	1508.9	1521.9	1538.1	1552.5	1573.4	1594.2	1614.4
7.5°	1369.3	1379.3	1398.5	1420.1	1443.2	1464.6	1483.9	1509.1	1536.8	1567.1	1600.9
10°	1316.2	1327.3	1350.1	1374.8	1402.2	1422.9	1449.0	1479.0	1510.2	1547.3	1588.9
12.5°	1268.3	1278.9	1306.3	1331.5	1359.9	1382.8	1413.1	1443.6	1485.2	1525.4	1572.8
15°	1174.9	1203.0	1234.2	1264.1	1298.0	1326.0	1362.4	1393.7	1433.4	1490.0	1544.0
17.5°	1071.3	1101.1	1140.0	1186.2	1231.6	1266.2	1303.2	1342.0	1389.3	1447.1	1509.4
20°	1010.9	1035.0	1078.0	1129.4	1182.1	1230.3	1264.1	1307.1	1355.9	1418.4	1482.9
22.5°	965.6	986.0	1019.6	1071.1	1128.0	1183.9	1227.2	1269.6	1323.6	1386.1	1456.3
25°	897.6	919.8	949.1	984.2	1049.3	1108.6	1165.2	1214.0	1271.3	1333.7	1411.9
27.5°	841.1	860.4	887.2	923.8	967.6	1032.9	1101.6	1157.2	1215.9	1283.0	1361.2
30°	807.8	823.5	845.5	882.6	924.3	982.9	1052.6	1117.7	1176.9	1246.6	1328.0
32.5°	772.9	789.6	811.2	840.5	885.3	934.5	1004.1	1075.5	1138.4	1209.6	1289.4
35°	726.4	739.5	759.0	789.0	829.3	872.3	934.1	1007.6	1074.1	1150.2	1226.4
37.5°	679.5	694.8	710.2	736.9	770.0	816.1	866.8	941.9	1015.5	1085.0	1159.4
40°	652.9	662.0	678.9	700.4	735.6	776.6	824.1	897.6	971.2	1040.2	1115.1
42.5°	623.2	633.4	647.7	669.2	700.7	740.6	787.1	850.8	927.5	994.4	1062.5
45°	582.0	587.8	602.1	620.4	646.4	686.7	729.7	786.4	858.6	922.3	982.3
47.5°	540.3	545.4	554.3	571.0	600.1	632.6	672.8	723.6	787.0	850.8	901.4
50°	511.6	516.2	524.6	540.3	566.3	598.2	637.9	683.5	740.1	801.3	843.6
52.5°	483.0	485.5	493.4	511.1	533.0	564.4	599.9	641.8	694.8	745.6	788.4
55°	437.4	443.3	448.5	461.5	482.3	512.3	544.2	583.9	624.9	667.9	704.3
57.5°	389.9	396.3	403.8	415.3	431.9	459.7	488.4	520.5	555.5	591.2	621.7
60°	358.7	364.5	371.0	384.1	399.0	421.2	452.4	480.4	507.1	539.6	570.2
62.5°	327.9	333.8	341.4	351.8	366.2	387.3	413.4	437.7	465.5	493.8	516.6
65°	282.5	287.1	292.9	302.7	316.3	335.3	356.7	375.6	400.3	421.2	442.0
67.5°	232.7	241.4	249.1	257.0	268.6	286.2	301.7	319.8	336.6	352.0	371.0
70°	199.8	209.6	216.8	225.2	236.3	251.3	266.2	278.6	292.3	307.2	324.2
72.5°	172.3	179.9	185.5	194.5	204.6	218.4	232.4	242.6	253.7	264.0	280.5
75°	136.1	139.3	143.2	150.3	159.5	169.9	181.0	190.0	196.6	205.7	217.4
77.5°	97.8	104.0	106.6	111.7	118.2	124.7	132.0	139.7	145.9	149.2	158.2
80°	74.8	77.5	80.1	87.2	91.2	97.7	102.8	110.0	112.6	115.9	124.3
82.5°	58.2	59.8	61.3	63.3	65.6	72.2	77.4	81.9	84.5	85.7	92.0
85°	33.8	34.5	35.1	35.8	36.4	36.4	39.1	42.3	46.9	46.9	48.8
87.5°	16.4	16.6	16.2	15.3	16.1	15.7	15.7	15.2	16.2	17.3	18.3
90°	24.7	23.2	21.4	19.5	17.6	15.7	13.5	10.9	8.3	5.8	3.2
92.5°	23.8	22.4	20.5	18.7	16.8	14.9	13.9	13.8	13.6	13.5	13.3
95°	24.7	23.2	23.0	22.8	22.6	22.3	26.2	34.2	42.2	50.1	58.1
97.5°	28.0	27.9	54.1	80.4	106.6	132.8	143.4	138.4	133.5	128.5	123.5
100°	42.6	46.6	78.9	111.4	143.8	176.3	190.4	186.1	181.9	177.7	173.4
102.5°	181.1	224.2	228.4	232.7	236.8	241.1	241.7	238.6	235.5	232.4	229.3
105°	332.1	330.0	328.7	327.6	326.4	325.2	323.9	322.5	321.1	319.7	318.3
107.5°	412.4	411.4	409.8	408.1	406.6	405.0	403.8	403.1	402.4	401.7	401.0
110°	466.8	466.4	465.0	463.5	462.1	460.7	459.7	458.9	458.3	457.5	456.8



TEST NUMBER: P333107-930
 CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	519.6	519.7	519.0	518.4	517.7	517.0	516.1	514.8	513.6	512.3	510.9
115°	596.9	596.4	596.6	596.9	597.1	597.4	597.1	596.4	595.7	595.0	594.3
117.5°	675.9	676.0	675.4	674.9	674.4	673.8	673.1	672.2	671.2	670.3	669.4
120°	723.8	723.3	723.6	723.8	724.1	724.2	723.9	723.0	722.0	721.1	720.2
122.5°	771.8	771.5	771.2	770.9	770.5	770.2	769.8	769.2	768.7	768.1	767.5
125°	838.2	837.6	838.0	838.5	838.9	839.4	839.2	838.2	837.3	836.3	835.4
127.5°	905.5	905.6	904.6	903.4	902.4	901.3	900.7	900.4	900.2	899.9	899.7
130°	945.7	945.4	944.7	944.0	943.3	942.6	942.1	941.8	941.7	941.4	941.2
132.5°	985.4	985.1	984.2	983.3	982.5	981.6	980.9	980.5	980.1	979.7	979.3
135°	1040.0	1039.5	1038.6	1037.6	1036.7	1035.8	1035.4	1035.7	1035.8	1036.1	1036.3
137.5°	1092.5	1091.9	1091.0	1089.9	1088.8	1087.9	1087.3	1087.2	1087.0	1087.0	1086.9
140°	1124.8	1124.1	1123.6	1123.2	1122.7	1122.3	1121.8	1121.3	1120.8	1120.4	1119.9
142.5°	1155.1	1154.5	1154.3	1154.0	1153.7	1153.4	1152.9	1152.0	1151.2	1150.3	1149.5
145°	1198.4	1198.2	1198.2	1198.2	1198.2	1198.2	1197.8	1197.1	1196.4	1195.6	1195.0
147.5°	1236.2	1236.0	1236.2	1236.5	1236.7	1237.0	1236.4	1235.1	1233.8	1232.4	1231.1
150°	1260.5	1260.5	1260.8	1261.0	1261.3	1261.4	1261.1	1260.2	1259.2	1258.3	1257.4
152.5°	1281.2	1280.8	1281.2	1281.7	1282.1	1282.5	1282.4	1281.6	1280.8	1280.1	1279.4
155°	1309.0	1308.1	1308.8	1309.5	1310.3	1310.9	1311.2	1310.9	1310.7	1310.4	1310.3
157.5°	1333.3	1332.0	1332.9	1333.6	1334.4	1335.2	1335.7	1335.8	1335.9	1336.1	1336.3
160°	1348.7	1347.3	1347.4	1347.7	1347.9	1348.2	1348.7	1349.3	1350.1	1350.8	1351.4
162.5°	1361.3	1359.9	1360.2	1360.4	1360.7	1360.9	1361.5	1362.4	1363.3	1364.1	1365.0
165°	1378.8	1376.9	1376.9	1376.9	1376.9	1376.9	1377.4	1378.6	1379.8	1381.0	1382.2
167.5°	1391.6	1389.5	1389.7	1389.8	1390.0	1390.1	1390.8	1392.0	1393.3	1394.5	1395.7
170°	1399.9	1398.0	1397.7	1397.5	1397.3	1397.1	1397.7	1399.1	1400.4	1401.9	1403.3
172.5°	1404.9	1403.0	1402.8	1402.6	1402.4	1402.2	1402.7	1404.1	1405.6	1407.0	1408.3
175°	1410.7	1408.6	1408.3	1408.1	1407.9	1407.6	1408.2	1409.7	1411.0	1412.4	1413.9
177.5°	1413.6	1412.2	1411.8	1411.4	1411.0	1410.6	1411.1	1412.4	1413.7	1415.1	1416.4
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1625.5	1630.2	1635.4	1645.4	1653.7	1657.3	1664.6	1669.8	1668.3	1675.5	1688.0
5°	1631.9	1649.5	1669.7	1690.5	1713.9	1733.5	1749.1	1764.7	1777.1	1792.0	1814.2
7.5°	1630.8	1662.2	1696.1	1733.5	1771.9	1805.1	1835.8	1867.0	1894.8	1925.1	1964.8
10°	1626.7	1668.3	1710.7	1759.5	1808.3	1854.6	1896.2	1935.3	1972.4	2012.1	2062.2
12.5°	1622.0	1669.9	1721.1	1779.8	1840.6	1896.2	1945.1	2001.4	2047.9	2099.1	2157.0
15°	1601.3	1665.7	1735.4	1811.6	1884.5	1959.3	2026.3	2095.4	2159.8	2221.0	2293.9
17.5°	1577.6	1652.0	1734.1	1824.1	1911.7	2002.7	2082.3	2169.2	2235.1	2317.2	2384.9
20°	1558.4	1638.4	1726.3	1827.2	1926.8	2027.6	2115.5	2204.1	2278.3	2360.9	2446.9
22.5°	1534.9	1622.8	1718.0	1822.5	1926.8	2037.0	2134.3	2222.3	2314.2	2407.3	2495.9
25°	1497.1	1588.3	1689.2	1803.8	1923.5	2036.1	2140.3	2249.7	2348.6	2449.5	2528.9
27.5°	1450.8	1546.5	1652.9	1771.1	1894.0	2009.3	2132.0	2248.5	2348.1	2445.2	2514.5
30°	1413.8	1514.7	1616.9	1736.8	1864.3	1987.9	2119.5	2236.0	2340.8	2428.0	2467.1
32.5°	1375.8	1471.5	1576.9	1698.2	1828.9	1961.9	2092.4	2211.5	2308.5	2360.9	2361.8
35°	1309.7	1399.5	1508.9	1628.0	1762.1	1906.6	2038.7	2155.9	2215.2	2219.7	2155.9
37.5°	1237.5	1320.0	1423.2	1542.5	1689.3	1833.0	1968.1	2046.2	2066.0	1999.7	1881.7
40°	1186.0	1262.2	1361.8	1484.2	1629.9	1778.4	1901.4	1958.7	1937.9	1830.4	1698.9
42.5°	1131.9	1202.8	1298.8	1419.6	1565.9	1715.9	1820.7	1851.4	1796.2	1672.2	1518.3
45°	1043.5	1108.6	1203.6	1325.4	1465.9	1606.5	1686.0	1670.3	1578.5	1431.4	1258.9
47.5°	951.5	1014.3	1099.8	1212.4	1356.4	1477.7	1531.5	1484.4	1353.8	1192.0	1051.7
50°	890.5	955.0	1033.7	1141.1	1272.6	1389.8	1424.2	1352.7	1207.5	1051.9	923.0
52.5°	830.6	885.7	962.9	1066.7	1192.4	1291.4	1309.7	1227.2	1077.3	937.8	823.5
55°	739.5	789.6	854.7	952.4	1061.0	1145.0	1135.2	1029.2	893.1	774.0	684.1
57.5°	651.3	689.1	749.3	840.7	936.2	992.5	956.9	866.4	739.6	642.1	566.3
60°	593.0	628.2	684.1	764.2	848.2	880.0	850.1	751.9	651.6	562.4	498.6
62.5°	537.8	568.8	616.9	691.3	759.1	778.0	746.0	660.1	569.8	493.7	440.8
65°	457.6	486.2	527.3	580.0	626.9	635.9	615.1	527.3	458.9	395.1	358.7
67.5°	384.8	403.6	435.6	481.2	506.1	511.4	471.2	416.0	355.7	316.5	289.0
70°	335.9	348.9	378.9	403.6	423.8	424.4	387.3	343.1	296.9	265.0	244.8
72.5°	288.5	301.0	323.7	340.6	356.0	351.0	317.0	282.1	244.8	220.7	205.7
75°	222.7	233.7	245.4	253.2	253.2	246.7	222.0	195.9	174.5	160.1	155.6
77.5°	161.8	171.0	174.9	173.7	171.3	161.2	145.5	128.5	120.8	114.1	110.6
80°	126.9	130.9	132.2	128.9	125.0	113.2	102.8	95.7	88.5	85.9	84.6
82.5°	94.1	97.5	94.1	95.1	86.4	76.8	71.1	68.6	65.6	64.6	63.3
85°	50.1	49.5	48.2	44.9	39.1	37.7	37.1	36.4	35.1	35.8	34.5
87.5°	18.3	17.3	15.7	15.7	16.1	15.5	16.4	16.8	17.1	16.9	18.3
90°	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7	26.1
92.5°	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8	25.3
95°	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7	26.1
97.5°	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0	28.2
100°	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6	38.6
102.5°	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1	138.0
105°	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1	334.2
107.5°	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4	413.4
110°	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8	467.3



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6	519.4
115°	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9	597.4
117.5°	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9	675.7
120°	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8	724.2
122.5°	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8	772.1
125°	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2	838.9
127.5°	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5	905.4
130°	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7	945.8
132.5°	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4	985.6
135°	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0	1040.5
137.5°	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5	1093.0
140°	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8	1125.5
142.5°	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1	1155.6
145°	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4	1198.6
147.5°	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2	1236.4
150°	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5	1260.5
152.5°	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2	1281.6
155°	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0	1310.0
157.5°	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3	1334.5
160°	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7	1350.1
162.5°	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3	1362.8
165°	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8	1380.6
167.5°	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6	1393.7
170°	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9	1401.7
172.5°	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9	1406.8
175°	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7	1412.8
177.5°	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6	1415.2
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7	1615.7
2.5°	1694.8	1696.9	1698.4	1703.6	1704.1	1708.9	1704.1
5°	1835.0	1844.1	1858.5	1872.7	1874.0	1883.2	1866.9
7.5°	1992.3	2013.4	2026.5	2049.7	2058.8	2064.5	2055.1
10°	2100.6	2120.1	2154.6	2171.5	2188.5	2191.0	2183.3
12.5°	2205.3	2236.3	2263.4	2295.5	2294.7	2317.7	2309.3
15°	2344.7	2376.6	2414.3	2450.1	2463.2	2463.2	2473.6
17.5°	2444.2	2502.6	2541.7	2569.8	2600.5	2605.9	2602.2
20°	2511.4	2574.5	2616.1	2652.6	2673.4	2679.3	2679.3
22.5°	2561.3	2615.1	2655.8	2688.5	2705.7	2712.6	2710.5
25°	2596.0	2642.1	2666.9	2676.7	2681.2	2680.0	2667.6
27.5°	2548.5	2546.5	2530.9	2500.9	2478.4	2464.7	2449.1
30°	2458.0	2424.1	2385.1	2342.1	2286.8	2244.4	2231.4
32.5°	2323.1	2247.0	2180.9	2109.3	2049.8	2007.5	1989.8
35°	2062.2	1941.8	1843.5	1757.5	1695.1	1656.0	1643.0
37.5°	1752.6	1636.1	1514.3	1431.0	1379.2	1339.8	1325.0
40°	1555.8	1428.8	1322.7	1244.6	1191.2	1152.8	1152.2
42.5°	1376.1	1254.9	1155.0	1098.8	1041.2	1015.9	1015.7
45°	1126.7	1029.8	945.2	900.9	866.4	845.5	839.7
47.5°	932.9	852.7	796.4	761.1	733.0	719.7	711.1
50°	824.1	753.8	708.9	678.2	662.7	645.7	644.4
52.5°	733.4	676.7	641.7	616.9	597.0	586.9	587.2
55°	616.4	571.5	546.8	527.9	512.3	504.5	501.2
57.5°	519.3	485.6	467.7	450.3	443.7	437.6	435.9
60°	458.9	436.1	419.2	405.5	395.7	393.8	393.1
62.5°	409.0	385.1	373.4	362.8	355.7	352.7	351.5
65°	337.2	319.6	309.2	300.8	298.2	293.6	292.9
67.5°	271.8	261.3	254.4	248.5	245.0	244.8	244.8
70°	231.7	225.8	220.0	216.8	214.8	213.5	213.5
72.5°	197.4	193.1	188.3	186.5	186.1	184.8	184.3
75°	150.3	145.8	146.4	143.2	140.6	137.4	135.4
77.5°	106.6	103.4	102.7	102.3	100.1	99.7	100.8
80°	82.7	79.4	78.8	79.4	78.8	76.8	76.8
82.5°	62.9	60.2	59.5	59.1	58.5	59.1	58.0
85°	33.8	32.5	32.5	32.5	33.8	33.2	32.5
87.5°	17.4	17.2	17.9	17.5	17.6	17.2	17.8
90°	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.7	468.2	468.8	469.5	470.3	470.9	471.7



TEST NUMBER: P333107-930

CATALOG NUMBER: S124RDIW-S1195D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)