

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333114-930

Luminaire Tested: **S124RDIW-S1195D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333114-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8343.1 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	16
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	1.9
10°-20°	445.4	5.3
20°-30°	643.1	7.7
30°-40°	729.0	8.7
40°-50°	704.0	8.4
50°-60°	585.4	7.0
60°-70°	404.2	4.8
70°-80°	204.9	2.5
80°-90°	57.3	0.7
90°-100°	104.8	1.3
100°-110°	310.6	3.7
110°-120°	527.1	6.3
120°-130°	695.1	8.3
130°-140°	780.6	9.4
140°-150°	767.1	9.2
150°-160°	645.2	7.7
160°-170°	429.2	5.1
170°-180°	150.3	1.8
0°-30°	1248.2	15.0
0°-40°	1977.3	23.7
0°-60°	3266.6	39.2
0°-90°	3933.0	47.1
90°-120°	942.5	11.3
90°-150°	3185.3	38.2
90°-180°	4410.0	52.9
0°-180°	8343.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	4	17	27	34	37	8
95°	74	85	93	97	97	82
105°	286	288	293	296	300	304
115°	536	536	534	532	531	528
125°	781	781	779	777	774	695
135°	1007	1014	1014	1012	1008	779
145°	1223	1228	1229	1228	1224	765
155°	1401	1401	1400	1405	1400	645
165°	1526	1522	1520	1526	1522	430
175°	1587	1581	1580	1587	1580	151
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.7	23.5	22.2	21.0	19.7	19.2	19.4	19.6	19.8	20.0	20.1
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	26.3	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7
95°	73.8	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2
97.5°	128.8	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7
100°	172.1	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7
102.5°	217.4	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2
105°	286.4	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4
107.5°	359.0	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9
110°	408.1	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8



TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.3	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5
115°	536.0	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3
117.5°	608.3	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6
120°	656.5	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3
122.5°	706.6	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0
125°	780.6	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9
127.5°	847.7	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9
130°	895.0	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1
132.5°	943.1	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4
135°	1006.8	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7
137.5°	1076.2	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8
140°	1122.4	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5
142.5°	1164.7	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1
145°	1223.2	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1281.2	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9
150°	1316.6	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.1	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6
155°	1401.4	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3
157.5°	1444.7	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1
160°	1470.3	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7
162.5°	1493.9	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9
165°	1525.6	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1
167.5°	1550.0	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7
170°	1563.7	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4
172.5°	1573.5	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5
175°	1587.1	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6
177.5°	1591.5	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	20.2	20.3	20.4	20.6	21.0	21.3	21.6	21.9
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	50.6	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.1	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	149.8	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.1	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	230.9	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	294.2	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	362.7	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	408.3	407.7	407.2	407.3	408.1	409.0	409.8	410.6



TEST NUMBER: P333114-930

CATALOG NUMBER: S124RDIW-S1195D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.3	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	533.0	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	605.7	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	654.9	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	705.0	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	778.3	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	848.4	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.6	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.8	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1013.1	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1080.2	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.3	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.8	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.7	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.3	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1443.9	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1469.5	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1492.4	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1522.7	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1548.3	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1562.1	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1572.4	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1589.7	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)