

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333097-930

Luminaire Tested: **S124RDIW-S1195D470U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333097-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S1195D470U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1195 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5457.8 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	76	76	76	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	61
2	94	87	81	75	89	83	77	72	75	70	66	67	64	61	60	58	56	52
3	86	77	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	45
4	79	68	60	54	75	65	58	52	59	53	48	54	49	45	48	45	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36	34
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	36	32	30
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23	22
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13726	13726	13726
5°	13757	13588	13674
10°	13671	13426	13426
15°	13514	13143	13046
20°	13298	12773	12538
25°	13023	12339	12026
30°	12755	11882	11384
35°	12458	11406	10738
40°	12101	10866	10043
45°	11772	10330	9334
50°	11396	9712	8584
55°	10994	9070	7769
60°	10551	8365	6936
65°	10147	7484	6117
70°	9557	6515	5193
75°	8812	5402	4223
80°	7685	4114	3873
85°	6512	3742	3492



TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.7	2.9
10°-20°	445.4	8.2
20°-30°	643.1	11.8
30°-40°	729.0	13.4
40°-50°	704.0	12.9
50°-60°	585.4	10.7
60°-70°	404.2	7.4
70°-80°	204.9	3.8
80°-90°	54.0	1.0
90°-100°	16.9	0.3
100°-110°	107.7	2.0
110°-120°	206.1	3.8
120°-130°	261.6	4.8
130°-140°	279.9	5.1
140°-150°	261.7	4.8
150°-160°	211.1	3.9
160°-170°	136.1	2.5
170°-180°	46.9	0.9
0°-30°	1248.2	22.9
0°-40°	1977.3	36.2
0°-60°	3266.6	59.9
0°-90°	3929.7	72.0
90°-120°	330.7	6.1
90°-150°	1134.0	20.8
90°-180°	1528.0	28.0
0°-180°	5457.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1700	1700	1700	1700	1700	
5°	1698	1692	1677	1689	1687	161
15°	1617	1604	1573	1570	1561	455
25°	1462	1437	1385	1364	1350	673
35°	1264	1221	1157	1114	1090	790
45°	1031	981	905	843	818	795
55°	781	727	644	579	552	698
65°	531	474	392	338	320	524
75°	282	234	173	144	135	298
85°	70	46	40	38	38	79
90°	1	5	8	10	11	4
95°	20	8	8	10	11	26
105°	111	113	115	118	105	116
115°	208	209	208	209	209	204
125°	292	293	293	294	294	261
135°	362	362	363	364	365	279
145°	418	419	419	419	420	261
155°	458	458	457	458	458	211
165°	483	481	481	484	481	136
175°	494	492	492	495	491	47
180°	494	494	494	494	494	



TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1704.4	1703.5	1702.6	1701.6	1700.7	1699.0	1696.5	1693.9	1691.3	1688.8	1691.3
5°	1697.6	1696.5	1695.3	1694.2	1693.1	1690.7	1687.3	1683.8	1680.3	1676.8	1679.7
7.5°	1682.3	1681.1	1679.8	1678.6	1677.4	1674.5	1670.1	1665.6	1661.0	1656.5	1658.4
10°	1667.7	1666.2	1664.8	1663.4	1661.9	1658.6	1653.4	1648.2	1643.0	1637.8	1638.9
12.5°	1648.9	1647.3	1645.6	1643.9	1642.3	1638.3	1632.2	1626.1	1619.9	1613.8	1614.5
15°	1616.9	1614.3	1611.8	1609.2	1606.5	1601.6	1594.4	1587.1	1579.9	1572.6	1572.1
17.5°	1578.2	1574.3	1570.6	1566.8	1563.1	1556.9	1548.2	1539.5	1530.8	1522.2	1520.5
20°	1547.9	1544.2	1540.4	1536.7	1532.9	1526.1	1516.3	1506.4	1496.6	1486.8	1484.4
22.5°	1514.6	1510.4	1506.2	1501.9	1497.7	1490.4	1479.8	1469.3	1458.7	1448.2	1444.7
25°	1462.0	1456.8	1451.6	1446.4	1441.2	1432.6	1420.8	1408.9	1397.1	1385.2	1380.3
27.5°	1406.8	1400.3	1393.8	1387.2	1380.6	1371.1	1358.4	1345.7	1333.0	1320.4	1314.3
30°	1368.3	1361.1	1353.8	1346.5	1339.4	1328.9	1315.3	1301.7	1288.2	1274.6	1267.3
32.5°	1327.6	1319.5	1311.3	1303.2	1295.0	1283.9	1269.8	1255.8	1241.7	1227.7	1219.3
35°	1264.1	1254.8	1245.6	1236.3	1227.1	1215.2	1200.8	1186.3	1171.8	1157.4	1147.5
37.5°	1196.2	1186.6	1177.0	1167.5	1158.0	1145.2	1129.2	1113.1	1097.1	1081.1	1070.1
40°	1148.3	1138.7	1129.2	1119.7	1110.0	1097.1	1080.6	1064.0	1047.6	1031.1	1019.0
42.5°	1102.4	1092.4	1082.4	1072.4	1062.4	1048.8	1031.6	1014.4	997.3	980.1	967.7
45°	1031.1	1020.3	1009.7	999.0	988.3	974.2	956.9	939.6	922.2	904.8	890.6
47.5°	957.4	946.3	935.3	924.2	913.2	898.6	880.6	862.5	844.5	826.5	811.7
50°	907.4	896.1	884.8	873.6	862.3	847.3	828.8	810.3	791.8	773.3	758.9
52.5°	856.4	845.3	834.3	823.2	812.2	797.1	778.2	759.2	740.2	721.2	706.5
55°	781.1	769.6	758.0	746.4	734.8	719.7	700.8	682.1	663.2	644.4	629.4
57.5°	706.6	694.6	682.6	670.6	658.5	643.3	624.8	606.2	587.7	569.2	553.9
60°	653.5	642.0	630.4	618.8	607.2	592.2	573.7	555.2	536.6	518.1	503.1
62.5°	605.6	593.6	581.6	569.6	557.5	542.0	523.0	504.0	485.0	466.1	452.2
65°	531.2	518.7	506.3	493.8	481.4	465.9	447.4	428.9	410.4	391.8	379.4
67.5°	453.8	441.9	430.0	418.1	406.2	391.6	374.4	357.3	340.1	322.9	312.2
70°	404.9	392.7	380.6	368.4	356.3	341.9	325.5	309.0	292.5	276.0	266.4
72.5°	352.8	341.9	330.8	319.8	308.8	295.5	280.0	264.4	248.8	233.3	225.1
75°	282.5	271.8	261.1	250.4	239.7	227.6	213.9	200.3	186.8	173.2	166.5
77.5°	211.2	202.1	193.0	183.9	174.8	164.8	153.8	142.8	131.8	120.8	116.9
80°	165.3	156.9	148.5	140.1	131.8	123.3	114.5	105.9	97.2	88.5	87.6
82.5°	125.8	118.1	110.4	102.6	95.0	88.6	83.6	78.7	73.7	68.7	68.1
85°	70.3	64.5	58.7	52.9	47.1	43.9	43.0	42.1	41.3	40.4	39.8
87.5°	24.2	22.5	20.9	19.2	17.5	16.6	16.5	16.4	16.3	16.2	16.1
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	4.6	4.7	4.7	4.8	4.9	5.2	5.9	6.5	7.2	7.8	8.3
95°	20.3	17.5	14.8	12.0	9.1	7.8	7.9	8.0	8.1	8.2	8.6
97.5°	43.1	44.9	46.6	48.3	50.1	46.4	37.3	28.0	18.9	9.8	9.8
100°	60.6	62.0	63.6	65.1	66.5	61.6	50.2	38.9	27.6	16.2	14.8
102.5°	80.1	81.2	82.3	83.3	84.5	84.2	82.8	81.3	79.8	78.4	63.3
105°	111.2	111.7	112.2	112.7	113.2	113.7	114.1	114.5	114.9	115.3	116.0
107.5°	140.1	140.4	140.6	140.9	141.1	141.5	142.0	142.6	143.2	143.7	144.1
110°	159.6	159.9	160.1	160.4	160.6	160.9	161.4	162.0	162.5	163.0	163.1



TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	178.6	179.0	179.4	179.9	180.3	180.7	180.9	181.1	181.3	181.6	181.6
115°	207.7	207.9	208.1	208.4	208.6	208.7	208.6	208.6	208.5	208.4	208.6
117.5°	233.9	234.2	234.6	234.9	235.2	235.5	235.6	235.8	236.0	236.2	236.1
120°	251.6	251.9	252.3	252.6	252.9	253.1	253.0	252.9	252.8	252.7	252.9
122.5°	268.2	268.4	268.6	268.8	269.0	269.1	269.2	269.4	269.5	269.6	269.7
125°	291.9	292.2	292.5	292.9	293.2	293.3	293.1	292.9	292.8	292.6	292.9
127.5°	314.4	314.5	314.5	314.6	314.7	315.0	315.3	315.7	316.1	316.4	316.4
130°	328.8	328.9	329.1	329.1	329.2	329.4	329.6	329.9	330.1	330.4	330.4
132.5°	342.2	342.3	342.4	342.6	342.8	343.0	343.3	343.6	343.9	344.2	344.3
135°	362.1	362.0	361.9	361.8	361.7	361.9	362.2	362.6	362.9	363.2	363.4
137.5°	379.8	379.8	379.8	379.8	379.9	380.1	380.4	380.8	381.2	381.6	381.7
140°	391.3	391.4	391.6	391.8	391.9	392.1	392.2	392.5	392.6	392.8	393.1
142.5°	401.6	401.9	402.3	402.5	402.8	403.0	403.1	403.2	403.3	403.4	403.6
145°	417.5	417.8	418.0	418.2	418.5	418.7	418.7	418.7	418.7	418.7	418.7
147.5°	430.2	430.6	431.0	431.5	432.0	432.2	432.1	432.0	431.9	431.9	431.9
150°	439.4	439.7	440.0	440.3	440.7	440.8	440.7	440.6	440.5	440.4	440.4
152.5°	447.0	447.3	447.5	447.8	448.1	448.1	448.0	447.8	447.7	447.5	447.7
155°	457.8	457.9	458.0	458.0	458.1	458.0	457.8	457.5	457.3	457.1	457.4
157.5°	466.9	466.8	466.8	466.8	466.7	466.5	466.3	465.9	465.7	465.5	465.9
160°	472.2	472.0	471.7	471.5	471.2	471.1	471.0	470.9	470.8	470.8	471.2
162.5°	477.0	476.6	476.3	476.0	475.7	475.5	475.4	475.3	475.2	475.2	475.6
165°	482.9	482.5	482.1	481.7	481.3	481.1	481.1	481.1	481.1	481.1	481.8
167.5°	487.6	487.2	486.8	486.4	485.9	485.7	485.7	485.6	485.6	485.5	486.2
170°	490.3	489.8	489.3	488.9	488.4	488.1	488.2	488.3	488.4	488.4	489.1
172.5°	492.1	491.6	491.1	490.6	490.2	489.9	490.0	490.1	490.2	490.2	490.9
175°	494.0	493.5	493.0	492.5	492.0	491.9	492.0	492.0	492.1	492.2	492.9
177.5°	494.9	494.5	494.0	493.5	493.1	492.9	493.0	493.2	493.3	493.4	493.9
180°	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0



TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2	1700.2
2.5°	1693.9	1696.5	1699.0	1700.1	1699.9	1699.7	1699.4	1699.2
5°	1682.6	1685.5	1688.4	1689.5	1689.0	1688.4	1687.8	1687.3
7.5°	1660.2	1662.1	1663.9	1664.4	1663.5	1662.6	1661.6	1660.7
10°	1640.1	1641.2	1642.4	1642.4	1641.2	1640.1	1638.9	1637.8
12.5°	1615.2	1615.9	1616.6	1616.1	1614.5	1612.9	1611.3	1609.6
15°	1571.5	1570.9	1570.3	1569.0	1567.0	1565.0	1563.0	1561.0
17.5°	1518.9	1517.3	1515.6	1513.4	1510.3	1507.2	1504.1	1501.0
20°	1482.1	1479.8	1477.5	1474.5	1470.7	1467.0	1463.1	1459.4
22.5°	1441.3	1437.8	1434.4	1431.1	1428.0	1424.9	1421.9	1418.8
25°	1375.3	1370.4	1365.5	1361.6	1358.7	1355.8	1352.9	1350.1
27.5°	1308.2	1302.1	1296.1	1290.9	1286.8	1282.6	1278.5	1274.3
30°	1260.0	1252.9	1245.6	1239.7	1235.0	1230.4	1225.8	1221.2
32.5°	1210.9	1202.5	1194.1	1187.7	1183.3	1178.9	1174.5	1170.1
35°	1137.7	1127.9	1118.0	1110.5	1105.3	1100.1	1094.9	1089.6
37.5°	1059.1	1048.1	1037.1	1029.0	1023.8	1018.6	1013.4	1008.2
40°	1006.8	994.7	982.5	973.8	968.6	963.4	958.2	953.0
42.5°	955.3	942.9	930.5	921.6	916.2	910.8	905.3	899.8
45°	876.4	862.3	848.1	838.4	833.2	828.0	822.8	817.6
47.5°	797.0	782.4	767.7	757.4	751.7	746.0	740.2	734.5
50°	744.4	729.9	715.4	705.5	700.0	694.5	689.0	683.5
52.5°	691.9	677.2	662.4	652.2	646.5	640.8	635.0	629.3
55°	614.3	599.3	584.2	574.0	568.5	563.0	557.5	552.0
57.5°	538.7	523.3	508.1	498.4	494.2	490.0	485.8	481.7
60°	488.0	473.0	458.0	448.2	443.5	438.9	434.2	429.6
62.5°	438.3	424.4	410.5	401.7	398.0	394.4	390.6	386.9
65°	367.0	354.6	342.1	334.1	330.7	327.2	323.8	320.2
67.5°	301.5	290.7	280.1	272.8	269.0	265.1	261.3	257.5
70°	256.9	247.4	237.8	231.6	228.7	225.8	222.9	220.0
72.5°	217.0	208.8	200.6	195.3	192.6	190.0	187.3	184.6
75°	159.9	153.2	146.5	142.4	140.6	138.8	137.1	135.4
77.5°	113.1	109.2	105.3	103.1	102.6	102.1	101.6	101.0
80°	86.8	85.9	85.0	84.5	84.2	83.9	83.6	83.3
82.5°	67.5	66.9	66.2	65.7	65.5	65.1	64.9	64.6
85°	39.2	38.6	38.1	37.7	37.7	37.7	37.7	37.7
87.5°	16.0	15.8	15.7	15.7	16.0	16.3	16.6	16.8
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	8.8	9.3	9.8	10.0	10.1	10.1	10.2	10.2
95°	9.1	9.6	10.1	10.4	10.4	10.5	10.6	10.7
97.5°	9.9	9.9	9.9	10.0	10.1	10.2	10.3	10.4
100°	13.5	12.1	10.7	10.0	10.1	10.2	10.3	10.4
102.5°	48.2	33.2	18.1	10.6	10.6	10.6	10.6	10.7
105°	116.8	117.5	118.2	117.2	114.1	111.2	108.3	105.3
107.5°	144.5	144.8	145.2	145.5	145.9	146.1	146.4	146.8
110°	163.3	163.5	163.6	163.8	164.0	164.3	164.5	164.8



TEST NUMBER: P333097-930

CATALOG NUMBER: S124RDIW-S1195D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	181.5	181.5	181.4	181.6	181.9	182.2	182.5	182.8
115°	208.7	208.9	209.0	209.1	209.1	209.1	209.1	209.1
117.5°	236.1	236.1	236.0	236.0	235.9	235.9	235.9	235.9
120°	253.1	253.2	253.4	253.4	253.2	253.1	252.9	252.7
122.5°	269.8	269.9	269.9	269.9	269.8	269.6	269.5	269.3
125°	293.1	293.3	293.6	293.8	293.8	293.9	294.0	294.1
127.5°	316.3	316.3	316.3	316.2	316.1	316.0	316.0	315.9
130°	330.5	330.6	330.7	330.7	330.7	330.7	330.7	330.7
132.5°	344.4	344.5	344.5	344.5	344.5	344.5	344.4	344.3
135°	363.5	363.7	363.9	364.0	364.2	364.4	364.5	364.7
137.5°	381.9	382.0	382.3	382.3	382.3	382.2	382.2	382.1
140°	393.3	393.5	393.8	394.0	394.0	394.1	394.2	394.3
142.5°	403.7	404.0	404.1	404.2	404.2	404.3	404.3	404.3
145°	418.8	418.9	419.0	419.1	419.2	419.4	419.6	419.7
147.5°	432.0	432.0	432.1	432.2	432.3	432.4	432.4	432.5
150°	440.4	440.4	440.4	440.5	440.6	440.7	440.8	440.8
152.5°	447.8	447.9	448.1	448.1	448.1	448.0	447.9	447.9
155°	457.7	458.0	458.4	458.4	458.2	458.0	457.7	457.5
157.5°	466.3	466.7	467.1	467.1	466.7	466.3	465.9	465.5
160°	471.7	472.2	472.7	472.7	472.2	471.7	471.2	470.8
162.5°	476.1	476.6	477.1	477.1	476.5	476.0	475.4	474.9
165°	482.4	483.1	483.7	483.6	482.9	482.2	481.4	480.7
167.5°	487.0	487.7	488.4	488.4	487.5	486.7	485.9	485.1
170°	489.8	490.4	491.1	491.1	490.2	489.3	488.5	487.7
172.5°	491.5	492.2	492.8	492.8	491.9	491.0	490.1	489.2
175°	493.7	494.4	495.1	495.0	494.0	493.0	492.0	491.1
177.5°	494.5	495.0	495.5	495.4	494.6	493.8	493.0	492.3
180°	494.0	494.0	494.0	494.0	494.0	494.0	494.0	494.0

(END OF REPORT)