

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333026-930

Luminaire Tested: **S124RDIW-S350D1050U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333026-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S350D1050U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4130.5 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	63	60	59	47	45	44	32	31	31	24				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	20				
3	77	68	61	56	69	62	56	51	49	44	41	36	34	32	25	24	22	17				
4	71	61	53	47	63	54	48	43	43	39	35	33	29	27	23	21	19	15				
5	65	54	46	40	58	49	42	37	39	34	30	29	26	23	20	18	17	13				
6	60	48	40	35	53	44	37	32	35	30	26	26	23	20	19	17	15	12				
7	55	43	36	30	49	39	33	28	31	26	23	24	21	18	17	15	13	10				
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	16	13	12	9				
9	47	36	29	24	42	32	26	22	26	21	18	20	17	14	14	12	11	8				
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.3	1.1
10°-20°	132.0	3.2
20°-30°	190.6	4.6
30°-40°	216.1	5.2
40°-50°	208.7	5.1
50°-60°	173.5	4.2
60°-70°	119.8	2.9
70°-80°	60.7	1.5
80°-90°	18.8	0.5
90°-100°	70.4	1.7
100°-110°	208.7	5.1
110°-120°	354.2	8.6
120°-130°	467.0	11.3
130°-140°	524.5	12.7
140°-150°	515.4	12.5
150°-160°	433.5	10.5
160°-170°	288.4	7.0
170°-180°	101.0	2.4
0°-30°	370.0	9.0
0°-40°	586.1	14.2
0°-60°	968.3	23.4
0°-90°	1167.6	28.3
90°-120°	633.2	15.3
90°-150°	2140.1	51.8
90°-180°	2963.0	71.7
0°-180°	4130.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	24
90°	2	11	18	23	25	4
95°	50	57	63	65	65	55
105°	192	193	197	199	202	204
115°	360	360	358	358	357	355
125°	524	524	524	522	520	467
135°	676	681	681	680	677	523
145°	822	825	826	825	823	514
155°	942	942	941	944	941	433
165°	1025	1023	1021	1025	1022	289
175°	1066	1062	1061	1066	1061	101
180°	1068	1068	1068	1068	1068	



TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.6	7.4	7.3	7.2	7.0	7.1	7.3	7.5	7.7	8.0	8.1
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	17.7	20.0	22.3	24.6	26.9	28.6	29.6	30.7	31.7	32.7	33.3
95°	49.6	51.2	52.8	54.5	56.2	57.6	58.9	60.2	61.5	62.8	63.3
97.5°	86.6	87.9	89.2	90.5	91.9	93.3	94.7	96.3	97.8	99.3	100.0
100°	115.6	116.3	117.1	117.8	118.5	119.8	121.4	123.0	124.7	126.4	126.7
102.5°	146.0	146.3	146.6	146.9	147.2	148.1	149.6	151.1	152.6	154.1	154.7
105°	192.4	192.7	192.8	193.0	193.1	193.6	194.4	195.1	195.8	196.6	197.1
107.5°	241.2	241.4	241.6	241.8	242.1	242.2	242.3	242.5	242.6	242.6	243.2
110°	274.2	274.6	274.9	275.3	275.7	275.7	275.6	275.4	275.2	275.0	274.7



TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.6	308.7	308.8	308.8	308.8	308.8	308.4	308.1	307.8	307.4	307.4
115°	360.1	360.1	360.1	360.1	360.1	360.0	359.5	359.2	358.8	358.5	358.2
117.5°	408.7	408.8	409.0	409.1	409.3	409.2	409.0	408.7	408.5	408.1	407.6
120°	441.1	441.8	442.5	443.3	444.0	444.1	443.5	443.0	442.5	441.9	441.0
122.5°	474.7	475.1	475.3	475.6	475.9	476.0	475.6	475.4	475.2	474.9	474.3
125°	524.5	524.5	524.5	524.5	524.5	524.4	524.2	524.0	523.8	523.7	523.3
127.5°	569.6	570.1	570.6	571.2	571.8	571.9	571.6	571.3	571.0	570.7	570.4
130°	601.3	601.9	602.3	602.9	603.5	603.7	603.7	603.7	603.7	603.7	603.4
132.5°	633.7	634.1	634.5	634.9	635.3	635.4	635.3	635.1	635.0	634.8	634.5
135°	676.5	677.5	678.7	679.7	680.9	681.4	681.4	681.4	681.4	681.4	681.0
137.5°	723.0	723.5	724.1	724.6	725.0	725.5	725.8	726.1	726.4	726.7	726.2
140°	754.1	754.5	754.8	755.2	755.5	755.7	755.7	755.7	755.7	755.7	755.5
142.5°	782.5	782.9	783.3	783.6	784.0	784.1	783.9	783.7	783.7	783.5	783.4
145°	821.8	822.6	823.3	824.0	824.8	825.2	825.4	825.6	825.7	825.9	825.7
147.5°	860.8	861.7	862.6	863.4	864.3	864.7	864.5	864.4	864.2	864.1	864.0
150°	884.6	885.3	886.1	886.8	887.5	887.9	887.9	887.9	887.9	887.9	887.9
152.5°	907.0	907.5	907.9	908.3	908.8	909.1	909.2	909.4	909.5	909.7	910.1
155°	941.6	941.6	941.6	941.6	941.6	941.5	941.3	941.1	940.9	940.8	941.5
157.5°	970.6	970.3	970.0	969.6	969.3	969.1	969.1	969.1	969.0	969.0	969.6
160°	987.8	987.7	987.4	987.2	987.1	986.9	986.7	986.5	986.3	986.2	986.7
162.5°	1003.6	1003.2	1002.7	1002.2	1001.8	1001.4	1001.3	1001.1	1000.9	1000.7	1001.7
165°	1025.0	1024.4	1023.9	1023.4	1022.8	1022.3	1022.0	1021.6	1021.2	1020.8	1022.0
167.5°	1041.3	1040.6	1039.8	1039.0	1038.3	1037.9	1038.0	1038.0	1038.0	1038.0	1039.1
170°	1050.6	1049.7	1048.7	1047.8	1046.9	1046.5	1046.8	1046.9	1047.1	1047.3	1048.4
172.5°	1057.2	1056.4	1055.6	1054.9	1054.1	1053.8	1053.8	1053.9	1053.9	1053.9	1055.2
175°	1066.2	1065.4	1064.5	1063.6	1062.6	1062.1	1061.8	1061.7	1061.5	1061.4	1062.6
177.5°	1069.3	1068.5	1067.8	1067.1	1066.3	1065.9	1065.9	1065.9	1065.9	1065.9	1067.0
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0



TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	8.2	8.4	8.6	8.7	8.9	9.0	9.1	9.3
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	34.0	34.7	35.4	35.8	36.0	36.2	36.4	36.7
95°	63.8	64.4	65.0	65.2	65.2	65.2	65.2	65.2
97.5°	100.6	101.3	101.9	102.2	102.2	102.2	102.2	102.2
100°	127.1	127.4	127.8	128.0	128.0	128.0	128.0	128.0
102.5°	155.2	155.6	156.2	156.5	156.6	156.8	156.9	157.1
105°	197.7	198.2	198.8	199.3	199.9	200.4	201.0	201.5
107.5°	243.7	244.2	244.8	244.9	244.9	244.9	244.8	244.8
110°	274.3	273.9	273.5	273.7	274.2	274.8	275.3	275.9





TEST NUMBER: P333026-930

CATALOG NUMBER: S124RDIW-S350D1050U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	307.3	307.2	307.1	307.1	307.3	307.4	307.4	307.6
115°	358.1	357.9	357.8	357.5	357.3	357.2	357.0	356.8
117.5°	406.9	406.3	405.7	405.2	404.8	404.5	404.1	403.7
120°	440.0	439.1	438.2	437.9	438.3	438.6	439.0	439.4
122.5°	473.7	473.0	472.4	471.7	471.1	470.4	469.8	469.1
125°	522.9	522.5	522.2	521.8	521.5	521.1	520.7	520.3
127.5°	570.0	569.6	569.2	568.9	568.6	568.3	568.0	567.8
130°	603.0	602.7	602.3	601.8	601.0	600.3	599.6	598.8
132.5°	634.1	633.7	633.3	633.0	632.8	632.4	632.1	631.9
135°	680.7	680.3	680.0	679.5	678.9	678.3	677.8	677.3
137.5°	725.7	725.2	724.7	724.6	724.6	724.8	724.9	725.0
140°	755.4	755.2	755.0	754.8	754.6	754.5	754.2	754.1
142.5°	783.4	783.3	783.3	783.3	783.3	783.3	783.2	783.2
145°	825.6	825.4	825.2	824.8	824.3	823.7	823.2	822.6
147.5°	863.8	863.6	863.5	863.3	863.2	863.0	862.7	862.6
150°	887.9	887.9	887.9	887.8	887.6	887.5	887.2	887.0
152.5°	910.5	911.0	911.4	911.4	910.9	910.4	910.0	909.5
155°	942.2	943.0	943.7	943.7	943.0	942.2	941.5	940.8
157.5°	970.1	970.6	971.2	971.2	970.5	969.9	969.3	968.7
160°	987.2	987.8	988.4	988.1	987.2	986.3	985.5	984.5
162.5°	1002.7	1003.6	1004.7	1004.7	1003.8	1002.9	1001.9	1001.0
165°	1023.0	1024.2	1025.2	1025.4	1024.7	1023.9	1023.2	1022.5
167.5°	1040.2	1041.3	1042.4	1042.4	1041.3	1040.2	1039.0	1037.9
170°	1049.5	1050.6	1051.7	1051.6	1050.4	1049.0	1047.7	1046.4
172.5°	1056.4	1057.6	1058.9	1058.8	1057.6	1056.3	1055.0	1053.7
175°	1063.9	1065.2	1066.5	1066.5	1065.2	1063.9	1062.6	1061.4
177.5°	1068.0	1069.0	1070.1	1070.0	1068.8	1067.6	1066.5	1065.3
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0

(END OF REPORT)