

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333030-930

Luminaire Tested: **S124RDIW-S350D1340U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333030-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1340U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4961.6 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27
2	84	77	71	66	74	68	64	60	53	50	47	38	36	35	25	24	23
3	76	68	61	55	68	60	54	50	47	43	39	34	31	29	22	21	20
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	20	18	17
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	32	25	21	25	20	17	19	15	13	13	11	9
10	44	32	25	21	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	1.0
10°-20°	132.0	2.7
20°-30°	190.6	3.8
30°-40°	216.1	4.4
40°-50°	208.7	4.2
50°-60°	173.5	3.5
60°-70°	119.8	2.4
70°-80°	60.7	1.2
80°-90°	19.7	0.4
90°-100°	90.2	1.8
100°-110°	267.1	5.4
110°-120°	453.4	9.1
120°-130°	597.8	12.0
130°-140°	671.4	13.5
140°-150°	659.8	13.3
150°-160°	554.9	11.2
160°-170°	369.2	7.4
170°-180°	129.3	2.6
0°-30°	370.0	7.5
0°-40°	586.1	11.8
0°-60°	968.3	19.5
0°-90°	1168.5	23.6
90°-120°	810.7	16.3
90°-150°	2739.7	55.2
90°-180°	3793.0	76.4
0°-180°	4961.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	24
90°	3	15	23	29	32	5
95°	63	73	80	83	84	71
105°	246	248	252	255	258	261
115°	461	461	459	458	457	454
125°	671	671	670	668	666	598
135°	866	872	872	870	867	670
145°	1052	1056	1057	1056	1053	658
155°	1205	1205	1204	1208	1204	554
165°	1312	1309	1307	1313	1309	370
175°	1365	1360	1359	1365	1359	130
180°	1367	1367	1367	1367	1367	



TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.7	7.7	7.7	7.7	7.6	7.7	8.1	8.4	8.6	9.0	9.2
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	22.7	25.6	28.5	31.5	34.5	36.6	37.9	39.2	40.5	41.9	42.7
95°	63.4	65.6	67.7	69.8	71.9	73.8	75.4	77.0	78.7	80.4	81.0
97.5°	110.8	112.5	114.2	115.9	117.6	119.4	121.3	123.3	125.1	127.1	127.9
100°	148.1	149.0	149.9	150.8	151.8	153.3	155.4	157.5	159.6	161.8	162.2
102.5°	186.9	187.4	187.7	188.1	188.4	189.6	191.5	193.5	195.3	197.3	198.0
105°	246.4	246.6	246.9	247.0	247.3	247.9	248.8	249.8	250.7	251.7	252.3
107.5°	308.8	309.0	309.3	309.6	309.9	310.1	310.2	310.4	310.5	310.6	311.3
110°	351.1	351.5	352.0	352.5	352.9	353.0	352.8	352.5	352.4	352.1	351.6



TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	395.0	395.1	395.2	395.3	395.4	395.3	394.8	394.4	394.0	393.5	393.5
115°	461.0	461.0	461.0	461.0	461.0	460.8	460.3	459.8	459.3	458.9	458.7
117.5°	523.2	523.3	523.6	523.7	523.9	523.8	523.5	523.2	522.9	522.5	521.7
120°	564.6	565.6	566.5	567.4	568.3	568.5	567.8	567.1	566.4	565.7	564.5
122.5°	607.7	608.1	608.5	608.9	609.3	609.3	608.9	608.6	608.3	608.0	607.2
125°	671.4	671.4	671.4	671.4	671.4	671.3	671.1	670.8	670.6	670.3	669.8
127.5°	729.1	729.9	730.6	731.2	732.0	732.1	731.7	731.4	731.0	730.6	730.2
130°	769.7	770.5	771.2	771.8	772.6	772.9	772.9	772.9	772.9	772.9	772.4
132.5°	811.2	811.7	812.2	812.8	813.3	813.4	813.3	813.0	812.9	812.7	812.2
135°	865.9	867.4	868.8	870.2	871.6	872.3	872.3	872.3	872.3	872.3	871.9
137.5°	925.6	926.3	926.9	927.6	928.2	928.8	929.1	929.5	929.8	930.3	929.6
140°	965.4	965.8	966.3	966.8	967.3	967.4	967.4	967.4	967.4	967.4	967.3
142.5°	1001.8	1002.2	1002.7	1003.1	1003.6	1003.7	1003.6	1003.4	1003.2	1003.0	1003.0
145°	1052.1	1053.0	1053.9	1054.9	1055.8	1056.4	1056.6	1056.9	1057.1	1057.4	1057.1
147.5°	1102.0	1103.1	1104.2	1105.4	1106.4	1106.9	1106.8	1106.6	1106.4	1106.2	1106.0
150°	1132.5	1133.3	1134.3	1135.2	1136.2	1136.6	1136.6	1136.6	1136.6	1136.6	1136.6
152.5°	1161.1	1161.7	1162.3	1162.9	1163.4	1163.8	1164.0	1164.2	1164.4	1164.6	1165.1
155°	1205.3	1205.3	1205.3	1205.3	1205.3	1205.3	1205.0	1204.8	1204.5	1204.4	1205.3
157.5°	1242.6	1242.2	1241.8	1241.3	1240.9	1240.6	1240.6	1240.6	1240.6	1240.5	1241.2
160°	1264.6	1264.4	1264.1	1263.9	1263.6	1263.4	1263.1	1263.0	1262.7	1262.5	1263.1
162.5°	1284.9	1284.3	1283.7	1283.0	1282.5	1282.1	1281.8	1281.6	1281.3	1281.1	1282.4
165°	1312.1	1311.5	1310.8	1310.0	1309.4	1308.8	1308.3	1307.8	1307.3	1306.8	1308.3
167.5°	1333.1	1332.1	1331.1	1330.2	1329.2	1328.7	1328.8	1328.8	1328.9	1328.9	1330.3
170°	1344.9	1343.8	1342.6	1341.4	1340.3	1339.8	1340.0	1340.3	1340.5	1340.7	1342.1
172.5°	1353.4	1352.4	1351.4	1350.5	1349.5	1349.0	1349.1	1349.1	1349.2	1349.2	1350.8
175°	1365.1	1363.8	1362.7	1361.5	1360.3	1359.6	1359.4	1359.2	1358.9	1358.7	1360.3
177.5°	1368.8	1367.9	1366.9	1366.0	1365.1	1364.6	1364.6	1364.6	1364.6	1364.6	1366.0
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2



TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	9.4	9.6	9.9	10.0	10.2	10.4	10.5	10.7
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	43.5	44.4	45.2	45.8	46.1	46.4	46.6	47.0
95°	81.8	82.5	83.2	83.6	83.6	83.6	83.6	83.6
97.5°	128.8	129.6	130.4	130.9	130.9	130.9	130.9	130.9
100°	162.7	163.2	163.6	163.9	163.9	163.9	163.9	163.9
102.5°	198.6	199.3	199.9	200.3	200.6	200.7	200.9	201.1
105°	253.1	253.8	254.5	255.2	255.8	256.6	257.3	258.0
107.5°	311.9	312.6	313.3	313.6	313.6	313.5	313.5	313.4
110°	351.1	350.7	350.3	350.3	351.1	351.7	352.5	353.2



TEST NUMBER: P333030-930

CATALOG NUMBER: S124RDIW-S350D1340U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	393.4	393.3	393.1	393.2	393.3	393.5	393.6	393.8
115°	458.4	458.2	458.0	457.7	457.5	457.2	457.0	456.8
117.5°	521.0	520.2	519.3	518.7	518.2	517.8	517.3	516.8
120°	563.4	562.1	561.0	560.6	561.1	561.6	562.1	562.5
122.5°	606.3	605.6	604.8	604.0	603.1	602.3	601.4	600.5
125°	669.4	669.0	668.5	668.0	667.6	667.1	666.6	666.1
127.5°	729.7	729.2	728.7	728.3	728.0	727.6	727.2	726.8
130°	772.0	771.5	771.0	770.4	769.4	768.4	767.5	766.5
132.5°	811.7	811.3	810.8	810.4	810.0	809.6	809.3	808.9
135°	871.4	870.9	870.4	869.8	869.1	868.5	867.7	867.0
137.5°	929.0	928.5	927.8	927.6	927.7	927.9	928.0	928.1
140°	967.0	966.8	966.5	966.3	966.0	965.8	965.6	965.4
142.5°	1002.9	1002.9	1002.8	1002.7	1002.7	1002.7	1002.7	1002.6
145°	1056.9	1056.6	1056.4	1056.0	1055.2	1054.5	1053.9	1053.1
147.5°	1105.8	1105.6	1105.5	1105.2	1105.0	1104.7	1104.6	1104.3
150°	1136.6	1136.6	1136.6	1136.5	1136.3	1136.0	1135.8	1135.6
152.5°	1165.7	1166.3	1166.9	1166.8	1166.2	1165.6	1165.0	1164.3
155°	1206.2	1207.1	1208.1	1208.1	1207.1	1206.2	1205.3	1204.4
157.5°	1241.9	1242.6	1243.3	1243.2	1242.4	1241.6	1240.9	1240.1
160°	1263.9	1264.6	1265.3	1265.0	1263.9	1262.7	1261.5	1260.4
162.5°	1283.6	1284.9	1286.1	1286.2	1285.0	1283.9	1282.7	1281.5
165°	1309.7	1311.1	1312.6	1312.8	1311.8	1310.8	1309.9	1309.0
167.5°	1331.7	1333.1	1334.5	1334.5	1333.0	1331.5	1330.2	1328.7
170°	1343.5	1344.9	1346.4	1346.2	1344.6	1343.0	1341.3	1339.7
172.5°	1352.3	1354.0	1355.6	1355.5	1353.9	1352.3	1350.6	1349.0
175°	1362.0	1363.6	1365.3	1365.3	1363.6	1362.0	1360.3	1358.7
177.5°	1367.3	1368.6	1369.9	1369.8	1368.3	1366.8	1365.3	1363.8
180°	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2	1367.2

(END OF REPORT)