

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333034-930

Luminaire Tested: **S124RDIW-S350D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333034-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S350D1560U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 350 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5579.2 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4069	4069	4069
5°	4078	4028	4053
10°	4052	3980	3980
15°	4006	3896	3867
20°	3942	3786	3716
25°	3861	3657	3564
30°	3781	3522	3375
35°	3693	3381	3183
40°	3587	3222	2977
45°	3490	3062	2767
50°	3378	2880	2545
55°	3258	2688	2303
60°	3127	2480	2055
65°	3007	2220	1813
70°	2832	1931	1539
75°	2611	1603	1251
80°	2278	1223	1148
85°	1936	1112	1037



TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	0.8
10°-20°	132.0	2.4
20°-30°	190.6	3.4
30°-40°	216.1	3.9
40°-50°	208.7	3.7
50°-60°	173.5	3.1
60°-70°	119.8	2.1
70°-80°	60.7	1.1
80°-90°	20.3	0.4
90°-100°	104.8	1.9
100°-110°	310.6	5.6
110°-120°	527.1	9.4
120°-130°	695.1	12.5
130°-140°	780.6	14.0
140°-150°	767.1	13.7
150°-160°	645.2	11.6
160°-170°	429.2	7.7
170°-180°	150.3	2.7
0°-30°	370.0	6.6
0°-40°	586.1	10.5
0°-60°	968.3	17.4
0°-90°	1169.2	21.0
90°-120°	942.5	16.9
90°-150°	3185.3	57.1
90°-180°	4410.0	79.0
0°-180°	5579.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	504	504	504	504	504	
5°	503	502	497	501	500	48
15°	479	475	466	465	463	135
25°	433	426	411	404	400	200
35°	375	362	343	330	323	234
45°	306	291	268	250	242	236
55°	232	216	191	172	164	207
65°	157	140	116	100	95	155
75°	84	69	51	43	40	88
85°	21	13	12	11	11	24
90°	4	17	27	34	37	6
95°	74	85	93	97	97	82
105°	286	288	293	296	300	304
115°	536	536	534	532	531	528
125°	781	781	779	777	774	695
135°	1007	1014	1014	1012	1008	779
145°	1223	1228	1229	1228	1224	765
155°	1401	1401	1400	1405	1400	645
165°	1526	1522	1520	1526	1522	430
175°	1587	1581	1580	1587	1580	151
180°	1590	1590	1590	1590	1590	



TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	505.2	504.9	504.7	504.4	504.1	503.6	502.9	502.1	501.3	500.6	501.3
5°	503.2	502.9	502.6	502.2	501.8	501.2	500.1	499.1	498.1	497.1	497.9
7.5°	498.6	498.3	498.0	497.6	497.3	496.4	495.0	493.7	492.4	491.1	491.5
10°	494.3	493.9	493.5	493.1	492.6	491.6	490.1	488.5	487.0	485.5	485.8
12.5°	488.8	488.3	487.8	487.3	486.8	485.7	483.8	482.0	480.2	478.3	478.6
15°	479.3	478.5	477.8	477.0	476.2	474.7	472.6	470.4	468.3	466.2	466.0
17.5°	467.8	466.7	465.5	464.5	463.3	461.5	458.9	456.3	453.8	451.2	450.7
20°	458.9	457.7	456.6	455.5	454.4	452.4	449.5	446.5	443.6	440.7	440.0
22.5°	449.0	447.7	446.5	445.2	443.9	441.7	438.6	435.5	432.4	429.3	428.3
25°	433.4	431.9	430.3	428.8	427.2	424.7	421.2	417.7	414.1	410.6	409.1
27.5°	417.0	415.1	413.1	411.2	409.3	406.4	402.7	398.9	395.2	391.4	389.6
30°	405.6	403.4	401.3	399.2	397.1	394.0	389.9	385.9	381.8	377.8	375.7
32.5°	393.5	391.1	388.7	386.3	383.8	380.6	376.4	372.3	368.1	363.9	361.4
35°	374.7	371.9	369.2	366.5	363.7	360.2	356.0	351.6	347.4	343.1	340.1
37.5°	354.6	351.7	348.9	346.1	343.2	339.5	334.7	330.0	325.2	320.5	317.2
40°	340.4	337.5	334.7	331.9	329.1	325.2	320.3	315.4	310.5	305.7	302.1
42.5°	326.8	323.8	320.8	317.9	315.0	310.9	305.8	300.7	295.6	290.5	286.8
45°	305.7	302.5	299.3	296.1	292.9	288.8	283.6	278.5	273.4	268.2	264.0
47.5°	283.8	280.5	277.3	273.9	270.7	266.4	261.1	255.7	250.3	245.0	240.6
50°	269.0	265.6	262.3	258.9	255.6	251.2	245.7	240.2	234.7	229.3	224.9
52.5°	253.9	250.5	247.3	244.0	240.8	236.3	230.6	225.0	219.4	213.8	209.5
55°	231.5	228.1	224.7	221.3	217.8	213.3	207.7	202.2	196.6	191.0	186.5
57.5°	209.5	205.9	202.4	198.8	195.2	190.7	185.2	179.7	174.2	168.7	164.2
60°	193.7	190.3	186.9	183.4	180.0	175.5	170.1	164.5	159.1	153.6	149.1
62.5°	179.5	175.9	172.4	168.8	165.3	160.7	155.1	149.4	143.8	138.2	134.0
65°	157.4	153.8	150.1	146.4	142.7	138.1	132.6	127.1	121.6	116.2	112.5
67.5°	134.5	131.0	127.4	123.9	120.4	116.1	111.0	105.9	100.8	95.7	92.5
70°	120.0	116.4	112.8	109.3	105.6	101.3	96.4	91.6	86.7	81.8	79.0
72.5°	104.6	101.3	98.1	94.8	91.6	87.6	83.0	78.4	73.8	69.1	66.8
75°	83.7	80.6	77.4	74.2	71.0	67.4	63.4	59.4	55.4	51.4	49.3
77.5°	62.6	59.9	57.2	54.5	51.9	48.8	45.6	42.3	39.1	35.8	34.7
80°	49.0	46.6	44.0	41.6	39.1	36.5	34.0	31.4	28.8	26.3	26.0
82.5°	37.3	35.0	32.7	30.4	28.1	26.3	24.8	23.3	21.9	20.4	20.2
85°	20.9	19.2	17.4	15.7	13.9	13.0	12.7	12.5	12.2	12.0	11.8
87.5°	7.8	7.9	7.9	8.0	8.1	8.2	8.6	9.0	9.4	9.7	10.0
90°	3.7	6.7	9.7	12.7	15.7	18.3	20.5	22.7	24.9	27.1	28.7
92.5°	26.3	29.8	33.2	36.6	40.1	42.6	44.1	45.7	47.1	48.7	49.7
95°	73.8	76.2	78.7	81.1	83.6	85.8	87.7	89.6	91.6	93.4	94.2
97.5°	128.8	130.8	132.7	134.8	136.7	138.8	141.0	143.2	145.5	147.7	148.7
100°	172.1	173.2	174.3	175.4	176.5	178.2	180.8	183.2	185.6	188.1	188.7
102.5°	217.4	217.8	218.3	218.7	219.1	220.5	222.7	224.9	227.1	229.4	230.2
105°	286.4	286.7	287.0	287.2	287.6	288.2	289.3	290.4	291.5	292.6	293.4
107.5°	359.0	359.3	359.6	360.0	360.3	360.5	360.7	360.9	361.0	361.2	361.9
110°	408.1	408.7	409.2	409.8	410.3	410.5	410.2	409.9	409.6	409.4	408.8



TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.3	459.4	459.5	459.6	459.7	459.5	459.0	458.5	458.0	457.5	457.5
115°	536.0	536.0	536.0	536.0	536.0	535.7	535.2	534.6	534.1	533.5	533.3
117.5°	608.3	608.5	608.7	608.9	609.2	609.1	608.7	608.3	607.9	607.6	606.6
120°	656.5	657.5	658.7	659.7	660.8	661.0	660.1	659.3	658.5	657.7	656.3
122.5°	706.6	707.0	707.5	707.9	708.3	708.4	708.0	707.6	707.3	706.9	706.0
125°	780.6	780.6	780.6	780.6	780.6	780.5	780.2	779.9	779.7	779.4	778.9
127.5°	847.7	848.6	849.4	850.2	851.0	851.3	850.8	850.4	849.9	849.5	848.9
130°	895.0	895.8	896.6	897.4	898.2	898.6	898.6	898.6	898.6	898.6	898.1
132.5°	943.1	943.8	944.4	944.9	945.6	945.7	945.5	945.3	945.1	944.9	944.4
135°	1006.8	1008.4	1010.1	1011.8	1013.4	1014.2	1014.2	1014.2	1014.2	1014.2	1013.7
137.5°	1076.2	1076.9	1077.7	1078.5	1079.2	1079.9	1080.3	1080.7	1081.2	1081.6	1080.8
140°	1122.4	1122.9	1123.5	1124.1	1124.5	1124.9	1124.9	1124.9	1124.9	1124.9	1124.5
142.5°	1164.7	1165.2	1165.8	1166.3	1166.9	1167.0	1166.8	1166.6	1166.4	1166.1	1166.1
145°	1223.2	1224.3	1225.4	1226.5	1227.6	1228.2	1228.5	1228.8	1229.1	1229.3	1229.1
147.5°	1281.2	1282.5	1283.9	1285.2	1286.5	1287.0	1286.8	1286.5	1286.4	1286.1	1285.9
150°	1316.6	1317.7	1318.8	1319.9	1321.0	1321.5	1321.5	1321.5	1321.5	1321.5	1321.5
152.5°	1350.1	1350.7	1351.4	1352.0	1352.7	1353.2	1353.3	1353.6	1353.8	1354.0	1354.6
155°	1401.4	1401.4	1401.4	1401.4	1401.4	1401.3	1401.0	1400.8	1400.5	1400.2	1401.3
157.5°	1444.7	1444.2	1443.7	1443.2	1442.8	1442.5	1442.4	1442.3	1442.3	1442.3	1443.1
160°	1470.3	1470.0	1469.7	1469.5	1469.2	1468.9	1468.7	1468.4	1468.1	1467.9	1468.7
162.5°	1493.9	1493.2	1492.5	1491.8	1491.0	1490.5	1490.3	1490.0	1489.7	1489.5	1490.9
165°	1525.6	1524.8	1524.0	1523.1	1522.3	1521.7	1521.1	1520.5	1520.0	1519.5	1521.1
167.5°	1550.0	1548.8	1547.7	1546.5	1545.4	1544.8	1544.9	1544.9	1545.0	1545.1	1546.7
170°	1563.7	1562.4	1561.0	1559.6	1558.3	1557.7	1558.0	1558.3	1558.5	1558.8	1560.4
172.5°	1573.5	1572.4	1571.2	1570.1	1569.0	1568.4	1568.5	1568.6	1568.6	1568.6	1570.5
175°	1587.1	1585.7	1584.4	1583.0	1581.6	1580.8	1580.5	1580.2	1580.0	1579.7	1581.6
177.5°	1591.5	1590.4	1589.3	1588.2	1587.1	1586.6	1586.6	1586.6	1586.6	1586.6	1588.1
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5



TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	504.0	504.0	504.0	504.0	504.0	504.0	504.0	504.0
2.5°	502.1	502.9	503.6	503.9	503.9	503.9	503.8	503.7
5°	498.8	499.6	500.5	500.8	500.7	500.5	500.3	500.1
7.5°	492.1	492.7	493.3	493.3	493.1	492.8	492.5	492.3
10°	486.2	486.5	486.8	486.8	486.5	486.2	485.8	485.5
12.5°	478.7	479.0	479.2	479.1	478.6	478.1	477.6	477.1
15°	465.9	465.7	465.5	465.1	464.5	463.9	463.3	462.7
17.5°	450.2	449.8	449.3	448.6	447.7	446.8	445.9	445.0
20°	439.4	438.6	438.0	437.1	435.9	434.8	433.7	432.6
22.5°	427.2	426.2	425.2	424.2	423.3	422.4	421.5	420.5
25°	407.6	406.3	404.8	403.7	402.8	401.9	401.0	400.1
27.5°	387.8	386.0	384.2	382.7	381.4	380.2	379.0	377.7
30°	373.5	371.4	369.2	367.5	366.1	364.8	363.4	362.0
32.5°	359.0	356.4	354.0	352.0	350.7	349.4	348.1	346.8
35°	337.2	334.4	331.4	329.2	327.7	326.1	324.6	323.0
37.5°	314.0	310.7	307.4	305.0	303.5	301.9	300.4	298.8
40°	298.4	294.8	291.2	288.7	287.1	285.6	284.1	282.5
42.5°	283.2	279.5	275.8	273.2	271.6	269.9	268.3	266.8
45°	259.8	255.6	251.4	248.5	247.0	245.4	243.9	242.4
47.5°	236.3	231.9	227.6	224.5	222.8	221.1	219.4	217.8
50°	220.6	216.4	212.1	209.1	207.5	205.9	204.2	202.6
52.5°	205.0	200.7	196.4	193.3	191.7	190.0	188.3	186.5
55°	182.1	177.7	173.2	170.2	168.5	166.9	165.3	163.6
57.5°	159.6	155.2	150.6	147.7	146.5	145.3	144.0	142.8
60°	144.6	140.2	135.7	132.8	131.4	130.1	128.7	127.3
62.5°	130.0	125.8	121.7	119.1	118.0	116.9	115.8	114.7
65°	108.8	105.1	101.4	99.1	98.0	97.0	96.0	94.9
67.5°	89.4	86.2	83.0	80.9	79.7	78.6	77.5	76.3
70°	76.1	73.3	70.5	68.6	67.8	66.9	66.0	65.2
72.5°	64.3	61.9	59.5	57.9	57.1	56.3	55.5	54.7
75°	47.4	45.4	43.5	42.2	41.7	41.2	40.7	40.1
77.5°	33.5	32.4	31.2	30.6	30.4	30.2	30.1	29.9
80°	25.8	25.4	25.2	25.0	24.9	24.9	24.8	24.7
82.5°	20.0	19.8	19.6	19.5	19.4	19.3	19.2	19.2
85°	11.7	11.4	11.3	11.2	11.2	11.2	11.2	11.2
87.5°	10.3	10.5	10.8	11.0	11.2	11.3	11.5	11.7
90°	30.3	32.0	33.6	34.7	35.2	35.8	36.4	36.9
92.5°	50.6	51.6	52.6	53.2	53.6	53.9	54.2	54.5
95°	95.1	95.9	96.7	97.1	97.1	97.1	97.1	97.1
97.5°	149.8	150.7	151.7	152.2	152.2	152.2	152.2	152.2
100°	189.1	189.7	190.3	190.5	190.5	190.5	190.5	190.5
102.5°	230.9	231.7	232.4	232.9	233.2	233.4	233.6	233.8
105°	294.2	295.1	295.9	296.7	297.5	298.3	299.1	299.9
107.5°	362.7	363.5	364.3	364.6	364.5	364.5	364.4	364.4
110°	408.3	407.7	407.2	407.3	408.1	409.0	409.8	410.6



TEST NUMBER: P333034-930

CATALOG NUMBER: S124RDIW-S350D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.3	457.2	457.1	457.1	457.3	457.5	457.6	457.8
115°	533.0	532.7	532.5	532.1	531.9	531.7	531.3	531.1
117.5°	605.7	604.8	603.8	603.1	602.5	602.0	601.4	600.9
120°	654.9	653.6	652.2	651.8	652.4	652.9	653.5	654.0
122.5°	705.0	704.1	703.2	702.2	701.2	700.3	699.3	698.3
125°	778.3	777.8	777.2	776.7	776.1	775.6	775.0	774.5
127.5°	848.4	847.8	847.3	846.8	846.4	846.0	845.5	845.1
130°	897.6	897.0	896.4	895.6	894.5	893.5	892.3	891.3
132.5°	943.8	943.2	942.6	942.2	941.8	941.3	940.9	940.4
135°	1013.1	1012.6	1012.0	1011.3	1010.5	1009.7	1008.9	1008.0
137.5°	1080.2	1079.5	1078.7	1078.5	1078.6	1078.8	1079.0	1079.1
140°	1124.3	1124.1	1123.7	1123.5	1123.2	1122.9	1122.7	1122.4
142.5°	1166.0	1166.0	1166.0	1165.9	1165.8	1165.8	1165.7	1165.6
145°	1228.8	1228.5	1228.2	1227.7	1226.9	1226.0	1225.2	1224.4
147.5°	1285.7	1285.5	1285.2	1285.0	1284.7	1284.5	1284.2	1283.9
150°	1321.5	1321.5	1321.5	1321.4	1321.1	1320.9	1320.6	1320.3
152.5°	1355.3	1355.9	1356.6	1356.6	1355.8	1355.2	1354.5	1353.7
155°	1402.4	1403.5	1404.6	1404.6	1403.5	1402.4	1401.3	1400.2
157.5°	1443.9	1444.7	1445.5	1445.4	1444.5	1443.7	1442.7	1441.8
160°	1469.5	1470.3	1471.1	1470.8	1469.5	1468.1	1466.7	1465.3
162.5°	1492.4	1493.9	1495.3	1495.4	1494.0	1492.7	1491.3	1490.0
165°	1522.7	1524.4	1526.0	1526.3	1525.2	1524.1	1523.0	1521.9
167.5°	1548.3	1550.0	1551.6	1551.6	1549.9	1548.2	1546.5	1544.7
170°	1562.1	1563.7	1565.4	1565.2	1563.3	1561.4	1559.5	1557.5
172.5°	1572.4	1574.2	1576.1	1576.1	1574.1	1572.2	1570.3	1568.4
175°	1583.6	1585.4	1587.4	1587.4	1585.4	1583.6	1581.6	1579.7
177.5°	1589.7	1591.1	1592.7	1592.6	1590.8	1589.1	1587.4	1585.6
180°	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5	1589.5

(END OF REPORT)