

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333046-930

Luminaire Tested: **S124RDIW-S575D1050U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333046-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1050U930-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4880.4 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	34	28
3	80	70	63	58	72	64	58	53	53	49	45	42	39	37	33	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	26	22	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.6
10°-20°	217.0	4.4
20°-30°	313.4	6.4
30°-40°	355.3	7.3
40°-50°	343.1	7.0
50°-60°	285.3	5.8
60°-70°	197.0	4.0
70°-80°	99.8	2.0
80°-90°	28.8	0.6
90°-100°	70.4	1.4
100°-110°	208.7	4.3
110°-120°	354.2	7.3
120°-130°	467.0	9.6
130°-140°	524.5	10.7
140°-150°	515.4	10.6
150°-160°	433.5	8.9
160°-170°	288.4	5.9
170°-180°	101.0	2.1
0°-30°	608.3	12.5
0°-40°	963.6	19.7
0°-60°	1591.9	32.6
0°-90°	1917.5	39.3
90°-120°	633.2	13.0
90°-150°	2140.1	43.8
90°-180°	2963.0	60.7
0°-180°	4880.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	2	11	18	23	25	5
95°	50	57	63	65	65	55
105°	192	193	197	199	202	204
115°	360	360	358	358	357	355
125°	524	524	524	522	520	467
135°	676	681	681	680	677	523
145°	822	825	826	825	823	514
155°	942	942	941	944	941	433
165°	1025	1023	1021	1025	1022	289
175°	1066	1062	1061	1066	1061	101
180°	1068	1068	1068	1068	1068	



TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.1	11.7	11.2	10.7	10.2	10.0	10.2	10.4	10.6	10.8	10.8
90°	2.4	4.5	6.5	8.6	10.5	12.3	13.8	15.2	16.7	18.2	19.2
92.5°	17.7	20.0	22.3	24.6	26.9	28.6	29.6	30.7	31.7	32.7	33.3
95°	49.6	51.2	52.8	54.5	56.2	57.6	58.9	60.2	61.5	62.8	63.3
97.5°	86.6	87.9	89.2	90.5	91.9	93.3	94.7	96.3	97.8	99.3	100.0
100°	115.6	116.3	117.1	117.8	118.5	119.8	121.4	123.0	124.7	126.4	126.7
102.5°	146.0	146.3	146.6	146.9	147.2	148.1	149.6	151.1	152.6	154.1	154.7
105°	192.4	192.7	192.8	193.0	193.1	193.6	194.4	195.1	195.8	196.6	197.1
107.5°	241.2	241.4	241.6	241.8	242.1	242.2	242.3	242.5	242.6	242.6	243.2
110°	274.2	274.6	274.9	275.3	275.7	275.7	275.6	275.4	275.2	275.0	274.7



TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	308.6	308.7	308.8	308.8	308.8	308.8	308.4	308.1	307.8	307.4	307.4
115°	360.1	360.1	360.1	360.1	360.1	360.0	359.5	359.2	358.8	358.5	358.2
117.5°	408.7	408.8	409.0	409.1	409.3	409.2	409.0	408.7	408.5	408.1	407.6
120°	441.1	441.8	442.5	443.3	444.0	444.1	443.5	443.0	442.5	441.9	441.0
122.5°	474.7	475.1	475.3	475.6	475.9	476.0	475.6	475.4	475.2	474.9	474.3
125°	524.5	524.5	524.5	524.5	524.5	524.4	524.2	524.0	523.8	523.7	523.3
127.5°	569.6	570.1	570.6	571.2	571.8	571.9	571.6	571.3	571.0	570.7	570.4
130°	601.3	601.9	602.3	602.9	603.5	603.7	603.7	603.7	603.7	603.7	603.4
132.5°	633.7	634.1	634.5	634.9	635.3	635.4	635.3	635.1	635.0	634.8	634.5
135°	676.5	677.5	678.7	679.7	680.9	681.4	681.4	681.4	681.4	681.4	681.0
137.5°	723.0	723.5	724.1	724.6	725.0	725.5	725.8	726.1	726.4	726.7	726.2
140°	754.1	754.5	754.8	755.2	755.5	755.7	755.7	755.7	755.7	755.7	755.5
142.5°	782.5	782.9	783.3	783.6	784.0	784.1	783.9	783.7	783.7	783.5	783.4
145°	821.8	822.6	823.3	824.0	824.8	825.2	825.4	825.6	825.7	825.9	825.7
147.5°	860.8	861.7	862.6	863.4	864.3	864.7	864.5	864.4	864.2	864.1	864.0
150°	884.6	885.3	886.1	886.8	887.5	887.9	887.9	887.9	887.9	887.9	887.9
152.5°	907.0	907.5	907.9	908.3	908.8	909.1	909.2	909.4	909.5	909.7	910.1
155°	941.6	941.6	941.6	941.6	941.6	941.5	941.3	941.1	940.9	940.8	941.5
157.5°	970.6	970.3	970.0	969.6	969.3	969.1	969.1	969.1	969.0	969.0	969.6
160°	987.8	987.7	987.4	987.2	987.1	986.9	986.7	986.5	986.3	986.2	986.7
162.5°	1003.6	1003.2	1002.7	1002.2	1001.8	1001.4	1001.3	1001.1	1000.9	1000.7	1001.7
165°	1025.0	1024.4	1023.9	1023.4	1022.8	1022.3	1022.0	1021.6	1021.2	1020.8	1022.0
167.5°	1041.3	1040.6	1039.8	1039.0	1038.3	1037.9	1038.0	1038.0	1038.0	1038.0	1039.1
170°	1050.6	1049.7	1048.7	1047.8	1046.9	1046.5	1046.8	1046.9	1047.1	1047.3	1048.4
172.5°	1057.2	1056.4	1055.6	1054.9	1054.1	1053.8	1053.8	1053.9	1053.9	1053.9	1055.2
175°	1066.2	1065.4	1064.5	1063.6	1062.6	1062.1	1061.8	1061.7	1061.5	1061.4	1062.6
177.5°	1069.3	1068.5	1067.8	1067.1	1066.3	1065.9	1065.9	1065.9	1065.9	1065.9	1067.0
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0



TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	10.9	11.1	11.2	11.3	11.5	11.7	11.9	12.1
90°	20.4	21.4	22.6	23.3	23.6	24.1	24.4	24.8
92.5°	34.0	34.7	35.4	35.8	36.0	36.2	36.4	36.7
95°	63.8	64.4	65.0	65.2	65.2	65.2	65.2	65.2
97.5°	100.6	101.3	101.9	102.2	102.2	102.2	102.2	102.2
100°	127.1	127.4	127.8	128.0	128.0	128.0	128.0	128.0
102.5°	155.2	155.6	156.2	156.5	156.6	156.8	156.9	157.1
105°	197.7	198.2	198.8	199.3	199.9	200.4	201.0	201.5
107.5°	243.7	244.2	244.8	244.9	244.9	244.9	244.8	244.8
110°	274.3	273.9	273.5	273.7	274.2	274.8	275.3	275.9



TEST NUMBER: P333046-930

CATALOG NUMBER: S124RDIW-S575D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	307.3	307.2	307.1	307.1	307.3	307.4	307.4	307.6
115°	358.1	357.9	357.8	357.5	357.3	357.2	357.0	356.8
117.5°	406.9	406.3	405.7	405.2	404.8	404.5	404.1	403.7
120°	440.0	439.1	438.2	437.9	438.3	438.6	439.0	439.4
122.5°	473.7	473.0	472.4	471.7	471.1	470.4	469.8	469.1
125°	522.9	522.5	522.2	521.8	521.5	521.1	520.7	520.3
127.5°	570.0	569.6	569.2	568.9	568.6	568.3	568.0	567.8
130°	603.0	602.7	602.3	601.8	601.0	600.3	599.6	598.8
132.5°	634.1	633.7	633.3	633.0	632.8	632.4	632.1	631.9
135°	680.7	680.3	680.0	679.5	678.9	678.3	677.8	677.3
137.5°	725.7	725.2	724.7	724.6	724.6	724.8	724.9	725.0
140°	755.4	755.2	755.0	754.8	754.6	754.5	754.2	754.1
142.5°	783.4	783.3	783.3	783.3	783.3	783.3	783.2	783.2
145°	825.6	825.4	825.2	824.8	824.3	823.7	823.2	822.6
147.5°	863.8	863.6	863.5	863.3	863.2	863.0	862.7	862.6
150°	887.9	887.9	887.9	887.8	887.6	887.5	887.2	887.0
152.5°	910.5	911.0	911.4	911.4	910.9	910.4	910.0	909.5
155°	942.2	943.0	943.7	943.7	943.0	942.2	941.5	940.8
157.5°	970.1	970.6	971.2	971.2	970.5	969.9	969.3	968.7
160°	987.2	987.8	988.4	988.1	987.2	986.3	985.5	984.5
162.5°	1002.7	1003.6	1004.7	1004.7	1003.8	1002.9	1001.9	1001.0
165°	1023.0	1024.2	1025.2	1025.4	1024.7	1023.9	1023.2	1022.5
167.5°	1040.2	1041.3	1042.4	1042.4	1041.3	1040.2	1039.0	1037.9
170°	1049.5	1050.6	1051.7	1051.6	1050.4	1049.0	1047.7	1046.4
172.5°	1056.4	1057.6	1058.9	1058.8	1057.6	1056.3	1055.0	1053.7
175°	1063.9	1065.2	1066.5	1066.5	1065.2	1063.9	1062.6	1061.4
177.5°	1068.0	1069.0	1070.1	1070.0	1068.8	1067.6	1066.5	1065.3
180°	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0	1068.0

(END OF REPORT)