

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333049-930

Luminaire Tested: **S124RDIW-S575D1340U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333049-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D1340U930-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6291.9 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38	30
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	72	67	76	70	66	61	56	53	50	42	40	38	30	29	28	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6689	6689	6689
5°	6704	6622	6663
10°	6662	6542	6542
15°	6586	6405	6358
20°	6480	6225	6110
25°	6347	6013	5860
30°	6216	5790	5547
35°	6071	5558	5233
40°	5896	5296	4894
45°	5737	5034	4548
50°	5554	4732	4182
55°	5358	4421	3786
60°	5142	4077	3381
65°	4946	3647	2980
70°	4657	3175	2530
75°	4295	2633	2059
80°	3747	2004	1888
85°	3168	1815	1704



TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.8	1.2
10°-20°	217.0	3.4
20°-30°	313.4	5.0
30°-40°	355.3	5.6
40°-50°	343.1	5.5
50°-60°	285.3	4.5
60°-70°	197.0	3.1
70°-80°	99.8	1.6
80°-90°	29.7	0.5
90°-100°	48.4	0.8
100°-110°	308.3	4.9
110°-120°	589.8	9.4
120°-130°	748.7	11.9
130°-140°	801.1	12.7
140°-150°	749.1	11.9
150°-160°	604.1	9.6
160°-170°	389.6	6.2
170°-180°	134.3	2.1
0°-30°	608.3	9.7
0°-40°	963.6	15.3
0°-60°	1591.9	25.3
0°-90°	1918.4	30.5
90°-120°	946.5	15.0
90°-150°	3245.5	51.6
90°-180°	4374.0	69.5
0°-180°	6291.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	829	829	829	829	829	
5°	827	824	817	823	822	78
15°	788	782	766	765	761	222
25°	712	700	675	664	658	328
35°	616	595	564	543	531	385
45°	502	478	441	411	398	387
55°	381	354	314	282	269	340
65°	259	231	191	165	156	256
75°	138	114	84	70	66	145
85°	34	22	20	18	18	39
90°	3	15	23	29	32	4
95°	58	24	23	29	31	75
105°	318	325	330	337	301	333
115°	594	597	596	598	598	585
125°	835	839	838	841	842	746
135°	1036	1036	1040	1042	1044	798
145°	1195	1198	1198	1199	1201	746
155°	1310	1311	1308	1312	1309	604
165°	1382	1377	1377	1384	1376	390
175°	1414	1408	1409	1417	1405	135
180°	1414	1414	1414	1414	1414	



TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	830.6	830.1	829.7	829.2	828.8	827.9	826.7	825.5	824.2	823.0	824.2
5°	827.3	826.7	826.1	825.6	825.1	823.9	822.2	820.5	818.8	817.2	818.6
7.5°	819.8	819.2	818.6	818.1	817.4	816.0	813.8	811.6	809.4	807.2	808.1
10°	812.7	812.0	811.3	810.6	809.9	808.3	805.8	803.2	800.6	798.1	798.7
12.5°	803.6	802.7	801.9	801.1	800.3	798.4	795.4	792.4	789.5	786.4	786.8
15°	788.0	786.7	785.5	784.2	782.9	780.5	777.0	773.5	769.9	766.4	766.1
17.5°	769.1	767.2	765.4	763.5	761.7	758.7	754.5	750.2	746.0	741.8	741.0
20°	754.3	752.5	750.6	748.9	747.0	743.7	738.9	734.1	729.3	724.6	723.4
22.5°	738.1	736.1	734.0	731.9	729.9	726.3	721.1	716.0	710.9	705.7	704.0
25°	712.5	710.0	707.4	704.8	702.3	698.1	692.4	686.6	680.8	675.1	672.6
27.5°	685.6	682.4	679.2	676.0	672.8	668.1	661.9	655.8	649.6	643.4	640.5
30°	666.8	663.2	659.7	656.2	652.7	647.6	641.0	634.4	627.7	621.1	617.6
32.5°	647.0	643.0	639.0	635.0	631.1	625.7	618.8	612.0	605.1	598.3	594.2
35°	616.0	611.6	607.0	602.5	598.0	592.2	585.1	578.1	571.0	564.0	559.2
37.5°	582.9	578.3	573.6	569.0	564.3	558.1	550.2	542.4	534.7	526.8	521.5
40°	559.5	554.9	550.2	545.6	541.0	534.6	526.6	518.5	510.5	502.5	496.5
42.5°	537.2	532.4	527.5	522.6	517.7	511.1	502.7	494.3	486.0	477.6	471.6
45°	502.5	497.3	492.0	486.8	481.6	474.7	466.3	457.9	449.4	440.9	434.0
47.5°	466.6	461.2	455.8	450.4	445.0	437.9	429.1	420.4	411.6	402.8	395.6
50°	442.2	436.7	431.2	425.7	420.2	412.9	403.9	394.9	385.9	376.8	369.8
52.5°	417.4	412.0	406.6	401.2	395.7	388.5	379.2	370.0	360.7	351.5	344.3
55°	380.7	375.0	369.4	363.7	358.1	350.7	341.5	332.4	323.2	314.1	306.7
57.5°	344.4	338.5	332.6	326.8	320.9	313.5	304.4	295.4	286.4	277.4	269.9
60°	318.5	312.8	307.2	301.6	296.0	288.6	279.6	270.5	261.5	252.5	245.2
62.5°	295.1	289.3	283.4	277.5	271.7	264.2	254.9	245.6	236.4	227.1	220.4
65°	258.9	252.8	246.7	240.7	234.6	227.1	218.0	209.0	200.0	190.9	184.9
67.5°	221.2	215.3	209.5	203.7	198.0	190.9	182.5	174.1	165.8	157.4	152.1
70°	197.3	191.4	185.5	179.5	173.7	166.6	158.6	150.6	142.5	134.5	129.9
72.5°	171.9	166.6	161.2	155.9	150.5	144.1	136.5	128.9	121.2	113.7	109.7
75°	137.7	132.5	127.3	122.1	116.8	110.9	104.3	97.6	91.0	84.4	81.1
77.5°	102.9	98.5	94.1	89.6	85.2	80.3	74.9	69.6	64.2	58.9	57.0
80°	80.6	76.5	72.4	68.3	64.2	60.1	55.8	51.6	47.4	43.1	42.7
82.5°	61.3	57.6	53.8	50.1	46.3	43.2	40.8	38.3	36.0	33.5	33.2
85°	34.2	31.5	28.6	25.8	23.0	21.4	21.0	20.5	20.1	19.6	19.4
87.5°	12.3	11.9	11.6	11.2	10.8	10.7	11.0	11.3	11.5	11.7	11.9
90°	3.2	5.8	8.3	10.9	13.5	15.7	17.6	19.5	21.4	23.2	24.7
92.5°	13.3	13.5	13.6	13.8	13.9	14.9	16.8	18.7	20.5	22.4	23.8
95°	58.1	50.1	42.2	34.2	26.2	22.3	22.6	22.8	23.0	23.2	24.7
97.5°	123.5	128.5	133.5	138.4	143.4	132.8	106.6	80.4	54.1	27.9	28.0
100°	173.4	177.7	181.9	186.1	190.4	176.3	143.8	111.4	78.9	46.6	42.6
102.5°	229.3	232.4	235.5	238.6	241.7	241.1	236.8	232.7	228.4	224.2	181.1
105°	318.3	319.7	321.1	322.5	323.9	325.2	326.4	327.6	328.7	330.0	332.1
107.5°	401.0	401.7	402.4	403.1	403.8	405.0	406.6	408.1	409.8	411.4	412.4
110°	456.8	457.5	458.3	458.9	459.7	460.7	462.1	463.5	465.0	466.4	466.8



TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	510.9	512.3	513.6	514.8	516.1	517.0	517.7	518.4	519.0	519.7	519.6
115°	594.3	595.0	595.7	596.4	597.1	597.4	597.1	596.9	596.6	596.4	596.9
117.5°	669.4	670.3	671.2	672.2	673.1	673.8	674.4	674.9	675.4	676.0	675.9
120°	720.2	721.1	722.0	723.0	723.9	724.2	724.1	723.8	723.6	723.3	723.8
122.5°	767.5	768.1	768.7	769.2	769.8	770.2	770.5	770.9	771.2	771.5	771.8
125°	835.4	836.3	837.3	838.2	839.2	839.4	838.9	838.5	838.0	837.6	838.2
127.5°	899.7	899.9	900.2	900.4	900.7	901.3	902.4	903.4	904.6	905.6	905.5
130°	941.2	941.4	941.7	941.8	942.1	942.6	943.3	944.0	944.7	945.4	945.7
132.5°	979.3	979.7	980.1	980.5	980.9	981.6	982.5	983.3	984.2	985.1	985.4
135°	1036.3	1036.1	1035.8	1035.7	1035.4	1035.8	1036.7	1037.6	1038.6	1039.5	1040.0
137.5°	1086.9	1087.0	1087.0	1087.2	1087.3	1087.9	1088.8	1089.9	1091.0	1091.9	1092.5
140°	1119.9	1120.4	1120.8	1121.3	1121.8	1122.3	1122.7	1123.2	1123.6	1124.1	1124.8
142.5°	1149.5	1150.3	1151.2	1152.0	1152.9	1153.4	1153.7	1154.0	1154.3	1154.5	1155.1
145°	1195.0	1195.6	1196.4	1197.1	1197.8	1198.2	1198.2	1198.2	1198.2	1198.2	1198.4
147.5°	1231.1	1232.4	1233.8	1235.1	1236.4	1237.0	1236.7	1236.5	1236.2	1236.0	1236.2
150°	1257.4	1258.3	1259.2	1260.2	1261.1	1261.4	1261.3	1261.0	1260.8	1260.5	1260.5
152.5°	1279.4	1280.1	1280.8	1281.6	1282.4	1282.5	1282.1	1281.7	1281.2	1280.8	1281.2
155°	1310.3	1310.4	1310.7	1310.9	1311.2	1310.9	1310.3	1309.5	1308.8	1308.1	1309.0
157.5°	1336.3	1336.1	1335.9	1335.8	1335.7	1335.2	1334.4	1333.6	1332.9	1332.0	1333.3
160°	1351.4	1350.8	1350.1	1349.3	1348.7	1348.2	1347.9	1347.7	1347.4	1347.3	1348.7
162.5°	1365.0	1364.1	1363.3	1362.4	1361.5	1360.9	1360.7	1360.4	1360.2	1359.9	1361.3
165°	1382.2	1381.0	1379.8	1378.6	1377.4	1376.9	1376.9	1376.9	1376.9	1376.9	1378.8
167.5°	1395.7	1394.5	1393.3	1392.0	1390.8	1390.1	1390.0	1389.8	1389.7	1389.5	1391.6
170°	1403.3	1401.9	1400.4	1399.1	1397.7	1397.1	1397.3	1397.5	1397.7	1398.0	1399.9
172.5°	1408.3	1407.0	1405.6	1404.1	1402.7	1402.2	1402.4	1402.6	1402.8	1403.0	1404.9
175°	1413.9	1412.4	1411.0	1409.7	1408.2	1407.6	1407.9	1408.1	1408.3	1408.6	1410.7
177.5°	1416.4	1415.1	1413.7	1412.4	1411.1	1410.6	1411.0	1411.4	1411.8	1412.2	1413.6
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9



TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	828.6	828.6	828.6	828.6	828.6	828.6	828.6	828.6
2.5°	825.5	826.7	827.9	828.5	828.4	828.3	828.2	828.1
5°	819.9	821.4	822.8	823.4	823.0	822.8	822.5	822.2
7.5°	809.0	809.9	810.9	811.1	810.7	810.2	809.8	809.3
10°	799.2	799.8	800.4	800.4	799.8	799.2	798.7	798.1
12.5°	787.1	787.4	787.8	787.6	786.8	786.0	785.2	784.4
15°	765.8	765.6	765.2	764.7	763.6	762.6	761.7	760.7
17.5°	740.2	739.4	738.6	737.4	736.0	734.5	733.0	731.5
20°	722.3	721.1	720.0	718.5	716.7	714.9	713.1	711.2
22.5°	702.4	700.7	699.0	697.4	695.9	694.4	692.9	691.4
25°	670.3	667.8	665.4	663.6	662.1	660.7	659.3	657.9
27.5°	637.5	634.5	631.6	629.1	627.0	625.0	623.1	621.0
30°	614.1	610.5	607.0	604.1	601.9	599.6	597.4	595.1
32.5°	590.1	586.0	581.9	578.8	576.7	574.5	572.3	570.2
35°	554.4	549.6	544.9	541.2	538.7	536.1	533.5	531.0
37.5°	516.1	510.8	505.4	501.5	498.9	496.4	493.8	491.3
40°	490.6	484.7	478.7	474.6	472.0	469.4	466.9	464.4
42.5°	465.5	459.5	453.5	449.1	446.5	443.8	441.2	438.5
45°	427.1	420.2	413.3	408.5	406.0	403.5	401.0	398.4
47.5°	388.4	381.2	374.1	369.1	366.3	363.5	360.8	357.9
50°	362.7	355.7	348.6	343.8	341.1	338.4	335.7	333.0
52.5°	337.1	330.0	322.9	317.9	315.0	312.3	309.5	306.7
55°	299.4	292.0	284.7	279.7	277.0	274.3	271.7	269.0
57.5°	262.4	255.0	247.6	242.9	240.8	238.8	236.8	234.7
60°	237.8	230.5	223.1	218.4	216.1	213.9	211.7	209.4
62.5°	213.6	206.8	200.1	195.8	194.0	192.2	190.4	188.6
65°	178.9	172.8	166.7	162.8	161.2	159.5	157.8	156.0
67.5°	146.9	141.7	136.5	133.0	131.1	129.2	127.3	125.5
70°	125.2	120.6	115.9	112.8	111.5	110.1	108.6	107.2
72.5°	105.7	101.7	97.8	95.1	93.8	92.5	91.2	89.9
75°	77.9	74.7	71.4	69.4	68.5	67.7	66.9	66.0
77.5°	55.1	53.2	51.3	50.2	50.0	49.7	49.5	49.2
80°	42.3	41.9	41.4	41.2	41.0	40.8	40.8	40.6
82.5°	32.9	32.5	32.3	32.0	31.9	31.7	31.6	31.5
85°	19.1	18.8	18.5	18.4	18.4	18.4	18.4	18.4
87.5°	12.1	12.2	12.5	12.6	12.8	13.0	13.2	13.5
90°	26.1	27.5	28.9	29.8	30.3	30.8	31.2	31.7
92.5°	25.3	26.7	28.0	28.8	28.9	29.0	29.1	29.2
95°	26.1	27.5	28.9	29.8	29.9	30.2	30.4	30.7
97.5°	28.2	28.4	28.5	28.7	28.9	29.1	29.4	29.6
100°	38.6	34.6	30.6	28.7	28.9	29.1	29.4	29.6
102.5°	138.0	94.9	51.8	30.2	30.3	30.3	30.4	30.5
105°	334.2	336.3	338.4	335.3	326.8	318.3	309.8	301.4
107.5°	413.4	414.5	415.5	416.5	417.4	418.2	419.1	420.0
110°	467.3	467.7	468.2	468.8	469.5	470.3	470.9	471.7



TEST NUMBER: P333049-930

CATALOG NUMBER: S124RDIW-S575D1340U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	519.4	519.3	519.3	519.7	520.6	521.5	522.4	523.3
115°	597.4	597.9	598.3	598.5	598.5	598.5	598.5	598.5
117.5°	675.7	675.6	675.6	675.5	675.4	675.3	675.2	675.1
120°	724.2	724.7	725.2	725.2	724.7	724.2	723.8	723.3
122.5°	772.1	772.4	772.7	772.6	772.1	771.6	771.2	770.7
125°	838.9	839.7	840.3	840.8	841.1	841.3	841.6	841.8
127.5°	905.4	905.2	905.1	904.9	904.7	904.5	904.3	904.2
130°	945.8	946.1	946.3	946.5	946.5	946.5	946.5	946.5
132.5°	985.6	985.9	986.1	986.1	985.9	985.8	985.5	985.4
135°	1040.5	1040.9	1041.4	1041.9	1042.4	1042.8	1043.3	1043.7
137.5°	1093.0	1093.5	1094.1	1094.2	1094.1	1094.0	1093.8	1093.6
140°	1125.5	1126.3	1126.9	1127.4	1127.6	1127.9	1128.1	1128.4
142.5°	1155.6	1156.1	1156.7	1156.9	1157.0	1157.0	1157.1	1157.1
145°	1198.6	1198.8	1199.1	1199.5	1199.9	1200.4	1200.9	1201.3
147.5°	1236.4	1236.6	1236.7	1237.0	1237.2	1237.5	1237.6	1237.9
150°	1260.5	1260.5	1260.5	1260.6	1260.9	1261.1	1261.3	1261.6
152.5°	1281.6	1282.0	1282.3	1282.5	1282.3	1282.1	1282.1	1281.9
155°	1310.0	1310.9	1311.9	1312.0	1311.3	1310.6	1309.9	1309.2
157.5°	1334.5	1335.7	1336.9	1336.9	1335.7	1334.5	1333.3	1332.0
160°	1350.1	1351.4	1352.9	1352.9	1351.4	1350.1	1348.7	1347.3
162.5°	1362.8	1364.2	1365.5	1365.5	1363.9	1362.3	1360.7	1359.1
165°	1380.6	1382.5	1384.4	1384.2	1382.2	1380.1	1377.9	1375.8
167.5°	1393.7	1395.7	1397.8	1397.7	1395.3	1392.9	1390.7	1388.3
170°	1401.7	1403.6	1405.5	1405.2	1403.0	1400.6	1398.2	1395.9
172.5°	1406.8	1408.8	1410.6	1410.3	1407.7	1405.2	1402.6	1400.1
175°	1412.8	1415.0	1417.1	1416.7	1413.9	1411.0	1408.2	1405.4
177.5°	1415.2	1416.7	1418.2	1417.8	1415.5	1413.3	1411.0	1408.8
180°	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9	1413.9

(END OF REPORT)