

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333058-930

Luminaire Tested: **S124RDIW-S795D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333058-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D470U930-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3943.4 lumens  
Efficiency: N/A  
Efficacy: 104.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20						20								20		
RC	80					70						30								10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10	0
RCR																						
0	111	111	111	111		105	105	105	105		92	92	92		81	81	81		71	71	71	66
1	102	98	94	90		96	92	89	86		82	79	77		72	70	69		64	62	61	57
2	93	86	79	74		87	81	75	71		72	68	64		64	61	58		56	54	52	48
3	85	76	68	62		80	72	65	60		64	59	54		57	53	49		50	47	44	41
4	78	67	59	53		73	64	56	51		57	51	47		51	46	43		45	42	39	35
5	72	60	52	46		67	57	50	44		51	45	41		46	41	37		41	37	34	31
6	66	54	46	40		62	51	44	39		46	40	36		42	37	33		37	33	30	27
7	61	49	41	35		58	47	39	34		42	36	32		38	33	29		34	30	27	24
8	57	45	37	31		54	43	35	30		39	33	28		35	30	26		31	27	24	22
9	53	41	33	28		50	39	32	27		36	30	25		32	27	24		29	25	22	20
10	50	38	30	26		47	36	29	25		33	27	23		30	25	22		27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9143	9143	9143
5°	9164	9052	9108
10°	9107	8943	8943
15°	9002	8756	8690
20°	8858	8508	8352
25°	8675	8219	8011
30°	8496	7914	7582
35°	8298	7597	7154
40°	8061	7238	6690
45°	7841	6882	6218
50°	7592	6469	5718
55°	7323	6042	5175
60°	7030	5572	4621
65°	6758	4988	4076
70°	6366	4338	3460
75°	5870	3599	2813
80°	5119	2738	2580
85°	4335	2492	2325



TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.4	2.7
10°-20°	296.7	7.5
20°-30°	428.4	10.9
30°-40°	485.6	12.3
40°-50°	468.9	11.9
50°-60°	389.9	9.9
60°-70°	269.3	6.8
70°-80°	136.5	3.5
80°-90°	36.4	0.9
90°-100°	31.5	0.8
100°-110°	93.3	2.4
110°-120°	158.4	4.0
120°-130°	208.9	5.3
130°-140°	234.6	5.9
140°-150°	230.5	5.8
150°-160°	193.9	4.9
160°-170°	129.0	3.3
170°-180°	45.2	1.1
0°-30°	831.5	21.1
0°-40°	1317.1	33.4
0°-60°	2176.0	55.2
0°-90°	2618.1	66.4
90°-120°	283.3	7.2
90°-150°	957.2	24.3
90°-180°	1325.0	33.6
0°-180°	3943.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1133	1133	1133	1133	1133	
5°	1131	1127	1117	1125	1124	107
15°	1077	1069	1048	1046	1040	303
25°	974	957	923	908	899	449
35°	842	813	771	742	726	526
45°	687	654	603	562	545	529
55°	520	484	429	386	368	465
65°	354	316	261	225	213	349
75°	188	156	115	96	90	199
85°	47	30	27	25	25	53
90°	1	5	8	10	11	4
95°	22	25	28	29	29	25
105°	86	86	88	89	90	91
115°	161	161	160	160	160	159
125°	235	235	234	234	233	209
135°	303	305	305	304	303	234
145°	368	369	369	369	368	230
155°	421	421	421	422	421	194
165°	458	457	457	459	457	129
175°	477	475	475	477	475	45
180°	478	478	478	478	478	



TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1135.4	1134.7	1134.1	1133.5	1132.9	1131.7	1130.0	1128.4	1126.7	1124.9	1126.7
5°	1130.8	1130.1	1129.3	1128.5	1127.7	1126.3	1123.9	1121.6	1119.2	1117.0	1118.9
7.5°	1120.6	1119.8	1119.0	1118.2	1117.4	1115.5	1112.5	1109.5	1106.4	1103.4	1104.6
10°	1110.9	1109.9	1109.0	1108.0	1107.0	1104.8	1101.4	1097.9	1094.5	1091.0	1091.7
12.5°	1098.4	1097.3	1096.2	1095.0	1094.0	1091.4	1087.3	1083.1	1079.0	1075.0	1075.5
15°	1077.1	1075.4	1073.6	1071.9	1070.2	1066.9	1062.0	1057.2	1052.4	1047.6	1047.2
17.5°	1051.2	1048.7	1046.2	1043.7	1041.2	1037.1	1031.3	1025.5	1019.7	1013.9	1012.8
20°	1031.1	1028.6	1026.1	1023.6	1021.1	1016.6	1010.0	1003.5	996.9	990.3	988.8
22.5°	1008.9	1006.1	1003.3	1000.5	997.7	992.7	985.7	978.7	971.7	964.7	962.4
25°	973.9	970.4	966.9	963.4	960.0	954.3	946.4	938.5	930.6	922.7	919.4
27.5°	937.1	932.8	928.4	924.1	919.7	913.3	904.8	896.4	887.9	879.5	875.5
30°	911.4	906.6	901.8	897.0	892.2	885.3	876.2	867.2	858.0	849.0	844.2
32.5°	884.4	879.0	873.5	868.0	862.7	855.2	845.9	836.5	827.1	817.7	812.2
35°	842.0	835.9	829.7	823.5	817.4	809.5	799.9	790.2	780.6	770.9	764.4
37.5°	796.8	790.4	784.1	777.7	771.4	762.9	752.2	741.5	730.8	720.2	712.8
40°	764.9	758.6	752.2	745.8	739.5	730.8	719.7	708.8	697.8	686.8	678.7
42.5°	734.3	727.7	721.1	714.4	707.7	698.6	687.2	675.7	664.3	652.8	644.6
45°	686.8	679.7	672.5	665.4	658.3	649.0	637.4	625.8	614.2	602.8	593.3
47.5°	637.7	630.4	623.1	615.6	608.3	598.6	586.6	574.5	562.6	550.5	540.7
50°	604.5	597.0	589.4	581.9	574.4	564.4	552.1	539.8	527.4	515.1	505.5
52.5°	570.5	563.1	555.7	548.4	541.0	531.0	518.4	505.7	493.1	480.5	470.7
55°	520.3	512.6	504.9	497.2	489.5	479.4	466.8	454.3	441.8	429.3	419.2
57.5°	470.8	462.7	454.7	446.7	438.6	428.4	416.1	403.8	391.5	379.1	369.0
60°	435.4	427.6	420.0	412.2	404.5	394.5	382.1	369.8	357.5	345.1	335.1
62.5°	403.4	395.4	387.4	379.4	371.4	361.0	348.4	335.7	323.1	310.5	301.2
65°	353.8	345.5	337.2	329.0	320.7	310.4	298.0	285.7	273.4	261.1	252.7
67.5°	302.3	294.4	286.4	278.5	270.5	260.9	249.4	238.0	226.5	215.1	207.9
70°	269.7	261.6	253.5	245.4	237.3	227.8	216.8	205.8	194.9	183.8	177.5
72.5°	235.1	227.7	220.4	213.0	205.7	196.9	186.5	176.1	165.8	155.4	149.9
75°	188.2	181.1	173.9	166.8	159.6	151.6	142.5	133.5	124.4	115.4	110.9
77.5°	140.6	134.6	128.6	122.5	116.4	109.7	102.5	95.1	87.8	80.5	77.9
80°	110.1	104.5	99.0	93.4	87.8	82.1	76.3	70.5	64.7	58.9	58.4
82.5°	83.8	78.7	73.5	68.4	63.3	59.0	55.8	52.4	49.1	45.8	45.3
85°	46.8	43.0	39.1	35.3	31.4	29.2	28.6	28.0	27.5	26.9	26.5
87.5°	16.1	15.2	14.1	13.0	12.0	11.4	11.4	11.4	11.3	11.3	11.3
90°	1.1	2.0	2.9	3.8	4.7	5.5	6.2	6.8	7.5	8.2	8.6
92.5°	7.9	9.0	9.9	11.0	12.1	12.8	13.3	13.7	14.2	14.6	14.9
95°	22.2	22.9	23.6	24.4	25.1	25.8	26.3	26.9	27.5	28.0	28.3
97.5°	38.7	39.3	39.9	40.5	41.1	41.7	42.4	43.0	43.7	44.4	44.7
100°	51.7	52.0	52.3	52.7	53.1	53.6	54.3	55.0	55.8	56.5	56.7
102.5°	65.3	65.5	65.6	65.7	65.9	66.3	66.9	67.6	68.2	69.0	69.1
105°	86.1	86.2	86.3	86.3	86.4	86.6	86.9	87.2	87.6	87.9	88.1
107.5°	107.9	107.9	108.1	108.2	108.3	108.4	108.4	108.4	108.5	108.5	108.8
110°	122.6	122.8	122.9	123.1	123.3	123.4	123.3	123.2	123.1	123.0	122.9



TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.0	138.0	138.1	138.1	138.2	138.1	137.9	137.8	137.6	137.5	137.5
115°	161.1	161.1	161.1	161.1	161.1	161.0	160.9	160.7	160.5	160.4	160.3
117.5°	182.8	182.9	183.0	183.0	183.0	183.0	183.0	182.8	182.7	182.5	182.3
120°	197.3	197.6	198.0	198.3	198.6	198.6	198.4	198.1	197.9	197.6	197.2
122.5°	212.4	212.5	212.6	212.7	212.9	212.9	212.8	212.6	212.5	212.5	212.1
125°	234.6	234.6	234.6	234.6	234.6	234.6	234.5	234.4	234.3	234.2	234.1
127.5°	254.8	255.0	255.3	255.5	255.8	255.8	255.7	255.5	255.4	255.3	255.1
130°	269.0	269.2	269.5	269.7	269.9	270.0	270.0	270.0	270.0	270.0	269.9
132.5°	283.4	283.6	283.8	284.0	284.1	284.2	284.1	284.1	284.1	284.0	283.8
135°	302.6	303.0	303.5	304.0	304.5	304.8	304.8	304.8	304.8	304.8	304.6
137.5°	323.4	323.7	323.8	324.1	324.3	324.5	324.7	324.8	324.9	325.1	324.8
140°	337.3	337.5	337.6	337.8	337.9	338.0	338.0	338.0	338.0	338.0	337.9
142.5°	350.0	350.2	350.3	350.5	350.7	350.7	350.7	350.6	350.5	350.4	350.4
145°	367.6	367.9	368.3	368.6	368.9	369.1	369.2	369.2	369.3	369.4	369.3
147.5°	385.1	385.4	385.8	386.2	386.6	386.8	386.7	386.6	386.6	386.5	386.5
150°	395.7	396.0	396.3	396.6	397.0	397.1	397.1	397.1	397.1	397.1	397.1
152.5°	405.7	405.9	406.1	406.3	406.5	406.7	406.7	406.8	406.8	406.9	407.1
155°	421.2	421.2	421.2	421.2	421.2	421.1	421.0	420.9	420.9	420.8	421.1
157.5°	434.1	434.0	433.9	433.7	433.6	433.5	433.5	433.5	433.4	433.4	433.7
160°	441.9	441.8	441.7	441.6	441.6	441.5	441.4	441.3	441.2	441.2	441.4
162.5°	449.0	448.7	448.5	448.3	448.1	447.9	447.8	447.8	447.7	447.6	448.1
165°	458.4	458.2	458.0	457.7	457.5	457.3	457.1	457.0	456.8	456.6	457.1
167.5°	465.8	465.5	465.1	464.8	464.4	464.2	464.2	464.3	464.3	464.3	464.8
170°	469.9	469.5	469.1	468.7	468.3	468.1	468.2	468.3	468.4	468.5	469.0
172.5°	472.9	472.5	472.2	471.9	471.5	471.3	471.3	471.4	471.4	471.4	472.0
175°	477.0	476.5	476.1	475.7	475.3	475.1	475.0	474.9	474.8	474.7	475.3
177.5°	478.3	477.9	477.6	477.3	477.0	476.8	476.8	476.8	476.8	476.8	477.3
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7



TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6	1132.6
2.5°	1128.4	1130.0	1131.7	1132.5	1132.4	1132.2	1132.0	1131.9
5°	1120.8	1122.7	1124.7	1125.4	1125.0	1124.7	1124.3	1123.9
7.5°	1105.9	1107.2	1108.4	1108.6	1108.1	1107.4	1106.9	1106.2
10°	1092.5	1093.2	1094.1	1094.1	1093.2	1092.5	1091.7	1091.0
12.5°	1076.0	1076.4	1076.8	1076.5	1075.5	1074.4	1073.3	1072.2
15°	1046.8	1046.4	1046.0	1045.2	1043.8	1042.4	1041.1	1039.8
17.5°	1011.8	1010.7	1009.6	1008.0	1006.0	1004.0	1001.9	999.9
20°	987.2	985.7	984.1	982.2	979.7	977.1	974.6	972.2
22.5°	960.1	957.7	955.4	953.2	951.2	949.2	947.1	945.1
25°	916.2	912.9	909.6	907.0	905.1	903.2	901.2	899.3
27.5°	871.4	867.4	863.3	859.9	857.1	854.4	851.6	848.8
30°	839.4	834.5	829.7	825.7	822.7	819.6	816.5	813.4
32.5°	806.6	801.0	795.4	791.2	788.2	785.3	782.4	779.4
35°	757.8	751.3	744.8	739.7	736.3	732.8	729.3	725.9
37.5°	705.5	698.1	690.8	685.4	682.0	678.5	675.1	671.6
40°	670.7	662.5	654.4	648.7	645.2	641.7	638.3	634.8
42.5°	636.3	628.1	619.9	613.9	610.3	606.7	603.1	599.4
45°	583.8	574.4	564.9	558.5	555.0	551.5	548.0	544.6
47.5°	530.9	521.1	511.4	504.5	500.8	496.9	493.1	489.3
50°	495.9	486.2	476.5	469.9	466.3	462.6	458.9	455.3
52.5°	460.9	451.1	441.2	434.5	430.6	426.8	423.1	419.2
55°	409.2	399.2	389.2	382.4	378.7	375.0	371.4	367.7
57.5°	358.8	348.6	338.4	332.0	329.2	326.4	323.7	320.9
60°	325.1	315.1	305.1	298.5	295.5	292.4	289.3	286.2
62.5°	292.0	282.7	273.5	267.6	265.1	262.7	260.2	257.7
65°	244.4	236.2	227.9	222.6	220.3	217.9	215.6	213.4
67.5°	200.8	193.7	186.5	181.7	179.2	176.6	174.1	171.5
70°	171.1	164.8	158.4	154.3	152.4	150.4	148.5	146.6
72.5°	144.6	139.1	133.6	130.0	128.3	126.5	124.7	122.9
75°	106.5	102.1	97.6	94.8	93.7	92.5	91.3	90.2
77.5°	75.3	72.7	70.1	68.6	68.3	68.0	67.7	67.3
80°	57.8	57.2	56.7	56.3	56.1	55.8	55.7	55.5
82.5°	44.9	44.5	44.1	43.8	43.6	43.4	43.2	43.0
85°	26.1	25.8	25.4	25.1	25.1	25.1	25.1	25.1
87.5°	11.3	11.2	11.1	11.2	11.3	11.6	11.7	11.9
90°	9.1	9.6	10.1	10.4	10.6	10.8	10.9	11.1
92.5°	15.2	15.5	15.8	16.0	16.1	16.2	16.3	16.4
95°	28.5	28.8	29.0	29.2	29.2	29.2	29.2	29.2
97.5°	45.0	45.3	45.6	45.7	45.7	45.7	45.7	45.7
100°	56.8	57.0	57.2	57.2	57.2	57.2	57.2	57.2
102.5°	69.4	69.6	69.9	70.0	70.0	70.1	70.2	70.3
105°	88.5	88.7	88.9	89.2	89.4	89.7	89.9	90.2
107.5°	109.0	109.3	109.5	109.6	109.6	109.6	109.5	109.5
110°	122.7	122.5	122.4	122.4	122.6	122.9	123.1	123.4





TEST NUMBER: P333058-930

CATALOG NUMBER: S124RDIW-S795D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	137.5	137.4	137.4	137.4	137.5	137.5	137.5	137.5
115°	160.2	160.1	160.0	160.0	159.9	159.8	159.7	159.6
117.5°	182.1	181.7	181.5	181.2	181.1	180.9	180.8	180.6
120°	196.8	196.4	196.0	195.9	196.1	196.2	196.4	196.6
122.5°	211.9	211.6	211.3	211.0	210.8	210.4	210.1	209.9
125°	233.9	233.7	233.6	233.4	233.3	233.1	232.9	232.8
127.5°	254.9	254.8	254.6	254.5	254.4	254.2	254.1	254.0
130°	269.7	269.5	269.4	269.1	268.8	268.5	268.2	267.8
132.5°	283.6	283.5	283.3	283.2	283.0	282.9	282.7	282.7
135°	304.4	304.3	304.1	303.9	303.7	303.5	303.2	303.0
137.5°	324.6	324.4	324.2	324.1	324.2	324.2	324.2	324.3
140°	337.9	337.8	337.7	337.6	337.5	337.5	337.4	337.3
142.5°	350.4	350.4	350.4	350.3	350.3	350.3	350.3	350.3
145°	369.2	369.2	369.1	368.9	368.7	368.4	368.2	367.9
147.5°	386.4	386.3	386.3	386.2	386.1	386.0	386.0	385.9
150°	397.1	397.1	397.1	397.1	397.1	397.0	396.9	396.8
152.5°	407.3	407.5	407.7	407.6	407.5	407.2	407.1	406.8
155°	421.4	421.8	422.1	422.1	421.8	421.4	421.1	420.8
157.5°	433.9	434.1	434.4	434.4	434.1	433.8	433.6	433.3
160°	441.6	441.9	442.1	442.1	441.6	441.2	440.8	440.3
162.5°	448.5	449.0	449.4	449.4	449.0	448.6	448.2	447.8
165°	457.6	458.1	458.6	458.7	458.4	458.0	457.7	457.4
167.5°	465.3	465.8	466.3	466.3	465.8	465.3	464.7	464.2
170°	469.4	469.9	470.4	470.3	469.8	469.2	468.6	468.1
172.5°	472.5	473.1	473.6	473.6	473.0	472.5	471.9	471.3
175°	475.9	476.5	477.0	477.0	476.5	475.9	475.3	474.7
177.5°	477.8	478.2	478.7	478.6	478.1	477.6	477.0	476.5
180°	477.7	477.7	477.7	477.7	477.7	477.7	477.7	477.7

(END OF REPORT)