

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332822

Luminaire Tested: **S124DIW-S1020D1050U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332822
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1050U835-4F0-1E-UDD-F1
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8065.9 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	91	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22	19
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.0
10°-20°	457.8	5.7
20°-30°	673.9	8.4
30°-40°	783.4	9.7
40°-50°	783.4	9.7
50°-60°	685.3	8.5
60°-70°	508.9	6.3
70°-80°	289.1	3.6
80°-90°	87.4	1.1
90°-100°	86.4	1.1
100°-110°	255.9	3.2
110°-120°	434.4	5.4
120°-130°	572.8	7.1
130°-140°	643.3	8.0
140°-150°	632.1	7.8
150°-160°	531.7	6.6
160°-170°	353.7	4.4
170°-180°	123.9	1.5
0°-30°	1294.2	16.0
0°-40°	2077.6	25.8
0°-60°	3546.4	44.0
0°-90°	4431.8	54.9
90°-120°	776.7	9.6
90°-150°	2624.9	32.5
90°-180°	3634.0	45.1
0°-180°	8065.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	3	14	22	28	30	8
95°	61	70	77	80	80	68
105°	236	237	241	244	247	250
115°	442	442	440	439	438	435
125°	643	643	642	640	638	573
135°	830	835	836	834	831	642
145°	1008	1012	1013	1012	1009	631
155°	1155	1155	1154	1158	1154	531
165°	1257	1254	1252	1258	1254	354
175°	1308	1303	1302	1308	1302	124
180°	1310	1310	1310	1310	1310	



TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.4	29.6	29.9	30.1	30.4	30.5	30.7	30.8	30.9	31.0	31.3
90°	3.0	5.5	8.0	10.5	12.9	15.1	16.9	18.7	20.5	22.3	23.6
92.5°	21.7	24.5	27.4	30.2	33.0	35.1	36.3	37.6	38.9	40.1	40.9
95°	60.8	62.8	64.8	66.9	68.9	70.7	72.3	73.8	75.4	77.0	77.7
97.5°	106.2	107.8	109.4	111.0	112.7	114.4	116.2	118.1	119.9	121.8	122.6
100°	141.8	142.7	143.6	144.5	145.4	146.9	148.9	150.9	153.0	155.0	155.4
102.5°	179.1	179.5	179.8	180.2	180.5	181.6	183.5	185.3	187.2	189.0	189.7
105°	236.0	236.3	236.5	236.7	236.9	237.5	238.4	239.3	240.2	241.1	241.8
107.5°	295.8	296.1	296.3	296.6	296.9	297.1	297.2	297.4	297.5	297.6	298.3
110°	336.3	336.8	337.2	337.7	338.1	338.2	338.0	337.8	337.6	337.3	336.9



TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	378.5	378.6	378.7	378.7	378.8	378.7	378.3	377.9	377.5	377.1	377.0
115°	441.7	441.7	441.7	441.7	441.7	441.5	441.0	440.6	440.1	439.7	439.4
117.5°	501.3	501.4	501.6	501.8	502.0	501.9	501.6	501.3	501.0	500.6	499.9
120°	541.0	541.9	542.8	543.7	544.6	544.7	544.0	543.3	542.7	542.0	540.9
122.5°	582.3	582.7	583.0	583.4	583.7	583.8	583.4	583.1	582.8	582.5	581.7
125°	643.3	643.3	643.3	643.3	643.3	643.2	642.9	642.7	642.5	642.3	641.8
127.5°	698.6	699.3	699.9	700.6	701.3	701.5	701.1	700.7	700.4	700.0	699.6
130°	737.5	738.2	738.8	739.5	740.2	740.5	740.5	740.5	740.5	740.5	740.1
132.5°	777.2	777.7	778.2	778.7	779.2	779.3	779.2	779.0	778.8	778.6	778.2
135°	829.7	831.0	832.4	833.7	835.1	835.8	835.8	835.8	835.8	835.8	835.3
137.5°	886.8	887.4	888.1	888.7	889.3	889.8	890.2	890.6	890.9	891.3	890.7
140°	924.9	925.4	925.8	926.3	926.7	926.9	926.9	926.9	926.9	926.9	926.7
142.5°	959.8	960.2	960.7	961.1	961.6	961.7	961.5	961.3	961.2	961.0	960.9
145°	1008.0	1008.9	1009.8	1010.7	1011.6	1012.1	1012.4	1012.6	1012.8	1013.0	1012.8
147.5°	1055.8	1056.9	1058.0	1059.0	1060.1	1060.6	1060.4	1060.2	1060.0	1059.8	1059.7
150°	1085.0	1085.9	1086.8	1087.7	1088.6	1089.0	1089.0	1089.0	1089.0	1089.0	1089.0
152.5°	1112.5	1113.1	1113.6	1114.1	1114.7	1115.0	1115.2	1115.4	1115.6	1115.8	1116.3
155°	1154.9	1154.9	1154.9	1154.9	1154.9	1154.8	1154.5	1154.3	1154.1	1153.9	1154.8
157.5°	1190.5	1190.1	1189.7	1189.3	1188.9	1188.7	1188.6	1188.6	1188.5	1188.5	1189.2
160°	1211.6	1211.4	1211.1	1210.9	1210.7	1210.5	1210.2	1210.0	1209.8	1209.6	1210.2
162.5°	1231.0	1230.5	1229.9	1229.3	1228.7	1228.3	1228.1	1227.9	1227.6	1227.4	1228.6
165°	1257.2	1256.5	1255.8	1255.2	1254.5	1253.9	1253.5	1253.0	1252.6	1252.1	1253.5
167.5°	1277.2	1276.3	1275.4	1274.4	1273.5	1273.0	1273.1	1273.1	1273.1	1273.2	1274.5
170°	1288.6	1287.5	1286.3	1285.2	1284.1	1283.6	1283.9	1284.1	1284.3	1284.5	1285.9
172.5°	1296.7	1295.7	1294.8	1293.9	1292.9	1292.5	1292.5	1292.6	1292.6	1292.6	1294.2
175°	1307.8	1306.7	1305.6	1304.5	1303.3	1302.7	1302.4	1302.2	1302.0	1301.8	1303.3
177.5°	1311.5	1310.6	1309.7	1308.8	1307.9	1307.4	1307.4	1307.4	1307.4	1307.4	1308.7
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9



TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	31.5	31.8	32.1	32.3	32.4	32.4	32.5	32.6
90°	25.0	26.3	27.7	28.6	29.0	29.5	29.9	30.4
92.5°	41.7	42.5	43.4	43.9	44.2	44.4	44.7	45.0
95°	78.3	79.0	79.7	80.0	80.0	80.0	80.0	80.0
97.5°	123.4	124.2	125.0	125.4	125.4	125.4	125.4	125.4
100°	155.9	156.3	156.8	157.0	157.0	157.0	157.0	157.0
102.5°	190.3	190.9	191.6	192.0	192.1	192.3	192.5	192.7
105°	242.5	243.1	243.8	244.5	245.2	245.8	246.5	247.2
107.5°	298.9	299.5	300.2	300.4	300.4	300.4	300.3	300.3
110°	336.4	336.0	335.5	335.7	336.3	337.0	337.7	338.4



TEST NUMBER: P332822

CATALOG NUMBER: S124DIW-S1020D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	376.9	376.8	376.7	376.7	376.9	377.0	377.1	377.3
115°	439.2	439.0	438.8	438.5	438.3	438.1	437.9	437.6
117.5°	499.1	498.3	497.6	497.0	496.5	496.1	495.6	495.2
120°	539.7	538.6	537.5	537.1	537.6	538.0	538.5	538.9
122.5°	581.0	580.2	579.4	578.6	577.8	577.0	576.2	575.4
125°	641.4	640.9	640.5	640.0	639.6	639.1	638.7	638.2
127.5°	699.1	698.7	698.2	697.8	697.4	697.1	696.7	696.4
130°	739.6	739.2	738.7	738.1	737.2	736.3	735.4	734.5
132.5°	777.7	777.3	776.8	776.4	776.1	775.7	775.3	775.0
135°	834.9	834.4	834.0	833.4	832.7	832.0	831.4	830.7
137.5°	890.1	889.5	888.9	888.7	888.8	889.0	889.1	889.2
140°	926.5	926.3	926.0	925.8	925.6	925.4	925.1	924.9
142.5°	960.9	960.8	960.8	960.7	960.7	960.7	960.6	960.6
145°	1012.6	1012.4	1012.1	1011.7	1011.0	1010.3	1009.7	1009.0
147.5°	1059.5	1059.3	1059.1	1058.9	1058.7	1058.5	1058.2	1058.0
150°	1089.0	1089.0	1089.0	1088.9	1088.7	1088.5	1088.2	1088.0
152.5°	1116.8	1117.4	1117.9	1117.9	1117.3	1116.7	1116.1	1115.6
155°	1155.7	1156.6	1157.5	1157.5	1156.6	1155.7	1154.8	1153.9
157.5°	1189.9	1190.5	1191.2	1191.2	1190.4	1189.6	1188.9	1188.1
160°	1210.9	1211.6	1212.3	1212.0	1210.9	1209.8	1208.7	1207.5
162.5°	1229.8	1231.0	1232.3	1232.3	1231.2	1230.1	1228.9	1227.8
165°	1254.8	1256.2	1257.5	1257.7	1256.8	1255.9	1255.0	1254.1
167.5°	1275.9	1277.2	1278.6	1278.6	1277.2	1275.8	1274.4	1273.0
170°	1287.2	1288.6	1289.9	1289.8	1288.3	1286.7	1285.1	1283.5
172.5°	1295.7	1297.2	1298.8	1298.7	1297.2	1295.6	1294.0	1292.4
175°	1304.9	1306.5	1308.1	1308.1	1306.5	1304.9	1303.3	1301.8
177.5°	1310.0	1311.2	1312.5	1312.4	1310.9	1309.5	1308.1	1306.6
180°	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)