

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332827

Luminaire Tested: **S124DIW-S1020D1340U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332827
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1340U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9797.2 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	92	88	85	88	85	81	78	71	68	66	58	56	55	46	45	44	38				
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32				
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27				
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23				
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20				
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18				
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16				
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14				
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13				
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.7
10°-20°	457.8	4.7
20°-30°	673.9	6.9
30°-40°	783.4	8.0
40°-50°	783.4	8.0
50°-60°	685.3	7.0
60°-70°	508.9	5.2
70°-80°	289.1	3.0
80°-90°	88.5	0.9
90°-100°	59.3	0.6
100°-110°	378.2	3.9
110°-120°	723.4	7.4
120°-130°	918.4	9.4
130°-140°	982.6	10.0
140°-150°	918.8	9.4
150°-160°	741.0	7.6
160°-170°	477.9	4.9
170°-180°	164.7	1.7
0°-30°	1294.2	13.2
0°-40°	2077.6	21.2
0°-60°	3546.4	36.2
0°-90°	4432.9	45.2
90°-120°	1160.9	11.8
90°-150°	3980.7	40.6
90°-180°	5364.0	54.8
0°-180°	9797.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	4	18	28	36	39	7
95°	71	30	28	36	38	92
105°	390	398	405	413	370	408
115°	729	733	732	734	734	717
125°	1025	1029	1027	1031	1032	914
135°	1271	1270	1275	1278	1280	979
145°	1466	1469	1470	1471	1474	916
155°	1607	1608	1604	1609	1606	741
165°	1695	1689	1689	1698	1688	479
175°	1734	1727	1728	1738	1724	165
180°	1734	1734	1734	1734	1734	



TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.5	29.9	30.3	30.7	31.1	31.4	31.6	31.8	32.0	32.3	32.6
90°	3.9	7.1	10.2	13.4	16.6	19.3	21.6	23.9	26.2	28.5	30.3
92.5°	16.3	16.5	16.7	16.9	17.0	18.3	20.6	22.9	25.2	27.5	29.2
95°	71.3	61.5	51.7	41.9	32.1	27.4	27.7	28.0	28.2	28.5	30.3
97.5°	151.5	157.6	163.7	169.8	175.9	162.9	130.7	98.6	66.4	34.2	34.4
100°	212.7	217.9	223.1	228.3	233.5	216.2	176.4	136.6	96.8	57.1	52.2
102.5°	281.2	285.0	288.8	292.6	296.4	295.7	290.5	285.4	280.2	275.0	222.1
105°	390.4	392.1	393.9	395.6	397.3	398.9	400.4	401.8	403.2	404.7	407.3
107.5°	491.8	492.7	493.6	494.4	495.3	496.7	498.7	500.6	502.6	504.6	505.8
110°	560.3	561.2	562.1	562.9	563.8	565.1	566.8	568.5	570.3	572.0	572.6



TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	626.7	628.3	629.9	631.4	633.0	634.1	635.0	635.8	636.6	637.4	637.3
115°	728.9	729.8	730.7	731.5	732.4	732.7	732.4	732.1	731.8	731.5	732.1
117.5°	821.0	822.2	823.3	824.5	825.6	826.5	827.2	827.8	828.4	829.1	829.0
120°	883.3	884.4	885.6	886.8	887.9	888.3	888.1	887.8	887.5	887.2	887.8
122.5°	941.4	942.1	942.8	943.5	944.2	944.7	945.1	945.5	945.9	946.3	946.7
125°	1024.7	1025.8	1027.0	1028.1	1029.3	1029.6	1029.0	1028.4	1027.8	1027.3	1028.1
127.5°	1103.5	1103.8	1104.1	1104.4	1104.7	1105.5	1106.8	1108.1	1109.5	1110.8	1110.6
130°	1154.4	1154.7	1155.0	1155.2	1155.5	1156.1	1157.0	1157.8	1158.7	1159.6	1159.9
132.5°	1201.1	1201.6	1202.1	1202.6	1203.1	1204.0	1205.1	1206.1	1207.2	1208.3	1208.6
135°	1271.1	1270.8	1270.5	1270.3	1270.0	1270.4	1271.5	1272.7	1273.9	1275.0	1275.6
137.5°	1333.1	1333.2	1333.3	1333.5	1333.6	1334.3	1335.5	1336.8	1338.1	1339.3	1340.0
140°	1373.6	1374.2	1374.7	1375.3	1375.9	1376.5	1377.0	1377.6	1378.2	1378.8	1379.6
142.5°	1409.9	1410.9	1412.0	1413.0	1414.1	1414.7	1415.1	1415.4	1415.8	1416.1	1416.8
145°	1465.7	1466.5	1467.4	1468.3	1469.1	1469.6	1469.6	1469.6	1469.6	1469.6	1469.9
147.5°	1510.0	1511.6	1513.3	1514.9	1516.5	1517.2	1516.9	1516.6	1516.3	1516.0	1516.2
150°	1542.2	1543.4	1544.5	1545.7	1546.8	1547.2	1547.0	1546.7	1546.4	1546.1	1546.1
152.5°	1569.2	1570.1	1571.0	1571.9	1572.9	1573.1	1572.6	1572.0	1571.5	1571.0	1571.5
155°	1607.1	1607.3	1607.6	1607.9	1608.2	1607.9	1607.1	1606.2	1605.3	1604.5	1605.6
157.5°	1639.0	1638.8	1638.6	1638.4	1638.3	1637.7	1636.7	1635.7	1634.8	1633.8	1635.3
160°	1657.6	1656.8	1655.9	1655.0	1654.2	1653.6	1653.3	1653.0	1652.7	1652.5	1654.2
162.5°	1674.2	1673.1	1672.1	1671.0	1669.9	1669.2	1668.9	1668.6	1668.3	1668.0	1669.7
165°	1695.3	1693.8	1692.4	1690.9	1689.5	1688.8	1688.8	1688.8	1688.8	1688.8	1691.1
167.5°	1711.9	1710.4	1708.9	1707.4	1705.9	1705.0	1704.9	1704.7	1704.5	1704.3	1706.9
170°	1721.2	1719.5	1717.7	1716.0	1714.3	1713.6	1713.8	1714.1	1714.4	1714.7	1717.0
172.5°	1727.4	1725.7	1724.0	1722.2	1720.5	1719.8	1720.1	1720.4	1720.6	1720.9	1723.2
175°	1734.2	1732.4	1730.7	1729.0	1727.2	1726.5	1726.8	1727.1	1727.4	1727.7	1730.3
177.5°	1737.3	1735.7	1734.0	1732.4	1730.8	1730.2	1730.7	1731.2	1731.6	1732.1	1733.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2



TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	32.9	33.3	33.6	33.9	34.0	34.1	34.2	34.3
90°	32.0	33.7	35.5	36.6	37.2	37.8	38.3	38.9
92.5°	31.0	32.7	34.4	35.3	35.5	35.6	35.7	35.8
95°	32.0	33.7	35.5	36.5	36.7	37.0	37.3	37.6
97.5°	34.6	34.8	34.9	35.2	35.5	35.7	36.0	36.3
100°	47.3	42.4	37.5	35.2	35.5	35.7	36.0	36.3
102.5°	169.3	116.4	63.5	37.1	37.2	37.2	37.3	37.4
105°	409.9	412.5	415.1	411.2	400.8	390.4	380.0	369.7
107.5°	507.1	508.4	509.6	510.8	511.9	513.0	514.1	515.2
110°	573.2	573.7	574.3	575.0	575.9	576.8	577.6	578.5



TEST NUMBER: P332827

CATALOG NUMBER: S124DIW-S1020D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	637.1	637.0	636.9	637.4	638.5	639.6	640.7	641.8
115°	732.7	733.3	733.8	734.1	734.1	734.1	734.1	734.1
117.5°	828.8	828.7	828.6	828.5	828.4	828.3	828.2	828.0
120°	888.3	888.9	889.5	889.5	888.9	888.3	887.8	887.2
122.5°	947.0	947.4	947.7	947.6	947.0	946.4	945.9	945.3
125°	1029.0	1029.9	1030.7	1031.3	1031.6	1031.9	1032.2	1032.5
127.5°	1110.5	1110.3	1110.1	1109.9	1109.7	1109.4	1109.2	1109.0
130°	1160.1	1160.4	1160.7	1160.9	1160.9	1160.9	1160.9	1160.9
132.5°	1208.9	1209.2	1209.5	1209.5	1209.3	1209.1	1208.8	1208.6
135°	1276.2	1276.7	1277.3	1277.9	1278.5	1279.0	1279.6	1280.2
137.5°	1340.6	1341.2	1341.9	1342.1	1341.9	1341.8	1341.6	1341.4
140°	1380.5	1381.4	1382.2	1382.8	1383.1	1383.4	1383.7	1384.0
142.5°	1417.4	1418.0	1418.7	1419.0	1419.1	1419.1	1419.2	1419.2
145°	1470.1	1470.4	1470.7	1471.2	1471.7	1472.3	1472.9	1473.5
147.5°	1516.5	1516.7	1516.9	1517.2	1517.5	1517.8	1518.0	1518.3
150°	1546.1	1546.1	1546.1	1546.2	1546.5	1546.8	1547.1	1547.4
152.5°	1571.9	1572.4	1572.8	1573.0	1572.8	1572.6	1572.5	1572.3
155°	1606.8	1607.9	1609.1	1609.2	1608.4	1607.5	1606.6	1605.8
157.5°	1636.8	1638.3	1639.8	1639.8	1638.3	1636.8	1635.3	1633.8
160°	1655.9	1657.6	1659.4	1659.4	1657.6	1655.9	1654.2	1652.5
162.5°	1671.5	1673.2	1674.9	1674.8	1672.9	1670.9	1668.9	1667.0
165°	1693.4	1695.7	1698.0	1697.8	1695.3	1692.7	1690.1	1687.5
167.5°	1709.4	1711.9	1714.5	1714.3	1711.4	1708.5	1705.7	1702.8
170°	1719.3	1721.6	1723.9	1723.6	1720.8	1717.9	1715.0	1712.1
172.5°	1725.5	1727.9	1730.2	1729.8	1726.6	1723.5	1720.4	1717.3
175°	1732.9	1735.5	1738.1	1737.6	1734.2	1730.7	1727.2	1723.8
177.5°	1735.8	1737.6	1739.5	1739.0	1736.2	1733.5	1730.7	1727.9
180°	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2	1734.2

(END OF REPORT)