

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P334086

Luminaire Tested: **S123RDW-S560D940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P334086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-25)
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDW-S560D940-4F0-1E-UDD-F
Description: DEFINE 3 REGRESSED DIRECT LED LUMINAIRE, FLUSH SATIN WHITE DIFFUSER
PENDANT/SURFACE/WALL MOUNT, 560 LUMENS PER FOOT
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1783.5 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Direct


Input Watts (W): 18.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P334086

CATALOG NUMBER: S123RDW-S560D940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P334086

CATALOG NUMBER: S123RDW-S560D940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	110	105	101	98	107	103	99	96	99	96	93	95	93	90	91	89	88	86					86			
2	100	93	86	81	98	91	85	80	87	83	78	84	80	77	81	78	75	73					73			
3	92	82	75	68	90	81	74	68	78	72	67	75	70	66	73	68	64	62					62			
4	85	73	65	59	83	72	64	58	70	63	58	67	62	57	65	60	56	54					54			
5	78	66	57	51	76	65	57	51	63	56	50	61	55	50	59	54	49	47					47			
6	73	60	51	45	71	59	51	45	57	50	45	55	49	44	54	48	44	42					42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	44	39	37					37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	34					34			
9	59	46	38	33	58	45	38	33	44	37	32	43	37	32	42	36	32	30					30			
10	55	43	35	30	54	42	35	30	41	34	30	40	34	29	39	34	29	28					28			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8498	8498	8498
5°	8531	8413	8461
10°	8482	8307	8278
15°	8391	8113	8027
20°	8266	7869	7686
25°	8137	7596	7353
30°	7966	7281	6883
35°	7791	6966	6453
40°	7630	6594	5920
45°	7416	6228	5439
50°	7184	5811	4900
55°	6945	5335	4397
60°	6727	4824	3845
65°	6441	4274	3293
70°	6087	3588	2659
75°	5565	2824	2504
80°	4959	2498	2300
85°	4187	2211	2050



TEST NUMBER: P334086

CATALOG NUMBER: S123RDW-S560D940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.2	4.2
10°-20°	206.4	11.6
20°-30°	297.2	16.7
30°-40°	334.7	18.8
40°-50°	320.2	18.0
50°-60°	262.1	14.7
60°-70°	176.7	9.9
70°-80°	88.6	5.0
80°-90°	23.2	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.9	32.4
0°-40°	912.7	51.2
0°-60°	1495.0	83.8
0°-90°	1783.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1783.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	790	790	790	790	790	
5°	790	786	779	784	783	75
15°	753	746	728	725	720	212
25°	685	669	640	626	619	315
35°	593	570	530	503	491	371
45°	487	458	409	373	357	376
55°	370	339	284	247	234	332
65°	253	218	168	136	129	250
75°	134	103	68	62	60	143
85°	34	20	18	17	17	39
90°	0	0	0	0	0	



TEST NUMBER: P334086

CATALOG NUMBER: S123RDW-S560D940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	789.5	789.5	789.5	789.5	789.5
2.5°	792.7	790.1	782.4	789.5	788.2
5°	789.5	786.3	778.6	784.3	783.1
7.5°	783.7	780.5	770.9	774.7	772.8
10°	776.0	771.5	760.0	760.6	757.4
12.5°	765.1	760.0	745.3	744.6	740.8
15°	753.0	745.9	728.0	724.8	720.3
17.5°	738.2	730.6	708.1	701.7	695.3
20°	721.6	711.3	687.0	678.7	671.0
22.5°	703.0	690.9	664.6	653.7	646.7
25°	685.1	669.1	639.6	626.2	619.1
27.5°	663.3	646.0	614.0	596.1	585.2
30°	640.9	621.7	585.8	564.1	553.8
32.5°	618.5	596.1	557.7	533.3	522.5
35°	592.9	569.8	530.1	502.6	491.1
37.5°	567.3	542.3	500.7	470.0	455.9
40°	543.0	514.8	469.3	436.0	421.3
42.5°	515.4	487.2	439.9	402.7	389.9
45°	487.2	458.4	409.1	372.6	357.3
47.5°	459.7	427.7	379.0	339.3	325.9
50°	429.0	398.9	347.0	307.3	292.6
52.5°	401.5	368.2	316.9	275.3	262.5
55°	370.1	338.7	284.3	247.1	234.3
57.5°	341.9	308.0	252.9	217.7	206.8
60°	312.5	277.2	224.1	189.5	178.6
62.5°	283.0	247.8	194.6	162.6	151.1
65°	252.9	217.7	167.8	136.4	129.3
67.5°	222.8	187.0	138.3	114.6	106.9
70°	193.4	158.8	114.0	91.6	84.5
72.5°	163.9	130.0	90.3	73.0	71.1
75°	133.8	103.1	67.9	61.5	60.2
77.5°	106.3	78.1	53.1	49.3	48.0
80°	80.0	53.8	40.3	38.4	37.1
82.5°	55.1	33.3	28.8	26.9	26.9
85°	33.9	19.8	17.9	16.6	16.6
87.5°	15.4	8.3	8.3	7.7	7.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)