

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332833

Luminaire Tested: **S124DIW-S1020D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332833
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1560U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10670.6 lumens
Efficiency: N/A
Efficacy: 139.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42																				
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35																				
2	87	80	74	69	79	73	68	63	60	57	53	48	46	44	38	36	34	29																				
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25																				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	32	30	27	25	21																				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18																				
6	61	50	42	36	56	46	38	33	38	33	29	31	27	24	24	21	19	16																				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14																				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																				
9	49	37	30	25	45	34	27	23	29	23	20	24	20	17	19	16	14	12																				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	1.5
10°-20°	457.8	4.3
20°-30°	673.9	6.3
30°-40°	783.4	7.3
40°-50°	783.4	7.3
50°-60°	685.3	6.4
60°-70°	508.9	4.8
70°-80°	289.1	2.7
80°-90°	89.3	0.8
90°-100°	69.0	0.6
100°-110°	439.7	4.1
110°-120°	841.1	7.9
120°-130°	1067.8	10.0
130°-140°	1142.4	10.7
140°-150°	1068.3	10.0
150°-160°	861.5	8.1
160°-170°	555.6	5.2
170°-180°	191.5	1.8
0°-30°	1294.2	12.1
0°-40°	2077.6	19.5
0°-60°	3546.4	33.2
0°-90°	4433.7	41.6
90°-120°	1349.8	12.6
90°-150°	4628.2	43.4
90°-180°	6237.0	58.5
0°-180°	10670.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	4	21	33	42	45	8
95°	83	35	33	42	44	107
105°	454	463	470	480	430	475
115°	848	852	850	853	854	834
125°	1191	1197	1194	1199	1200	1063
135°	1478	1477	1482	1485	1488	1138
145°	1704	1708	1709	1710	1713	1064
155°	1868	1870	1865	1871	1867	861
165°	1971	1964	1964	1974	1962	557
175°	2016	2008	2009	2021	2004	192
180°	2016	2016	2016	2016	2016	



TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.7	30.2	30.6	31.1	31.6	32.0	32.3	32.6	32.9	33.2	33.6
90°	4.5	8.2	11.9	15.6	19.3	22.5	25.1	27.8	30.5	33.2	35.2
92.5°	19.0	19.2	19.4	19.6	19.8	21.2	23.9	26.6	29.3	32.0	34.0
95°	82.9	71.5	60.2	48.8	37.4	31.8	32.2	32.5	32.8	33.2	35.2
97.5°	176.1	183.2	190.3	197.5	204.6	189.4	152.0	114.6	77.2	39.8	40.0
100°	247.3	253.4	259.4	265.4	271.4	251.3	205.1	158.8	112.6	66.4	60.7
102.5°	326.9	331.4	335.8	340.2	344.6	343.8	337.8	331.8	325.7	319.7	258.2
105°	453.9	455.9	457.9	460.0	462.0	463.8	465.5	467.2	468.8	470.5	473.5
107.5°	571.8	572.9	573.9	574.9	575.9	577.5	579.8	582.1	584.3	586.6	588.1
110°	651.5	652.5	653.5	654.5	655.5	657.0	659.0	661.0	663.0	665.0	665.7



TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	728.7	730.5	732.3	734.1	735.9	737.3	738.2	739.2	740.1	741.1	740.9
115°	847.5	848.5	849.5	850.5	851.5	851.9	851.5	851.2	850.9	850.5	851.2
117.5°	954.6	955.9	957.3	958.6	960.0	961.0	961.7	962.5	963.2	963.9	963.8
120°	1027.0	1028.3	1029.7	1031.0	1032.3	1032.8	1032.5	1032.2	1031.8	1031.5	1032.2
122.5°	1094.5	1095.3	1096.1	1096.9	1097.8	1098.4	1098.9	1099.3	1099.8	1100.3	1100.7
125°	1191.4	1192.7	1194.0	1195.4	1196.7	1197.0	1196.4	1195.7	1195.0	1194.4	1195.4
127.5°	1283.0	1283.4	1283.7	1284.0	1284.4	1285.3	1286.9	1288.4	1289.9	1291.5	1291.3
130°	1342.2	1342.5	1342.8	1343.2	1343.5	1344.2	1345.2	1346.2	1347.2	1348.2	1348.5
132.5°	1396.4	1397.0	1397.7	1398.3	1398.9	1399.8	1401.1	1402.3	1403.6	1404.9	1405.2
135°	1477.9	1477.5	1477.2	1476.9	1476.5	1477.0	1478.4	1479.7	1481.1	1482.4	1483.1
137.5°	1550.0	1550.1	1550.2	1550.4	1550.5	1551.3	1552.8	1554.3	1555.7	1557.2	1557.9
140°	1597.0	1597.7	1598.4	1599.0	1599.7	1600.4	1601.0	1601.7	1602.4	1603.0	1604.1
142.5°	1639.2	1640.4	1641.7	1642.9	1644.1	1644.9	1645.3	1645.7	1646.1	1646.5	1647.2
145°	1704.1	1705.1	1706.1	1707.1	1708.1	1708.6	1708.6	1708.6	1708.6	1708.6	1708.9
147.5°	1755.7	1757.5	1759.4	1761.3	1763.2	1763.9	1763.6	1763.6	1762.9	1762.6	1762.9
150°	1793.1	1794.4	1795.7	1797.1	1798.4	1798.9	1798.6	1798.3	1797.9	1797.6	1797.6
152.5°	1824.4	1825.5	1826.6	1827.6	1828.7	1829.0	1828.3	1827.7	1827.1	1826.5	1827.1
155°	1868.5	1868.8	1869.1	1869.5	1869.8	1869.5	1868.5	1867.5	1866.5	1865.4	1866.8
157.5°	1905.6	1905.4	1905.2	1905.0	1904.8	1904.1	1902.9	1901.8	1900.7	1899.5	1901.3
160°	1927.3	1926.3	1925.3	1924.3	1923.3	1922.6	1922.2	1921.9	1921.6	1921.2	1923.3
162.5°	1946.6	1945.3	1944.0	1942.8	1941.5	1940.7	1940.3	1940.0	1939.7	1939.3	1941.3
165°	1971.0	1969.3	1967.7	1966.0	1964.3	1963.5	1963.5	1963.5	1963.5	1963.5	1966.1
167.5°	1990.3	1988.6	1986.8	1985.1	1983.3	1982.4	1982.2	1982.0	1981.8	1981.6	1984.5
170°	2001.2	1999.2	1997.1	1995.1	1993.1	1992.3	1992.6	1993.0	1993.3	1993.6	1996.3
172.5°	2008.4	2006.4	2004.4	2002.4	2000.4	1999.5	1999.9	2000.2	2000.5	2000.9	2003.5
175°	2016.2	2014.2	2012.2	2010.2	2008.2	2007.4	2007.7	2008.0	2008.4	2008.7	2011.7
177.5°	2019.9	2018.0	2016.1	2014.2	2012.4	2011.7	2012.2	2012.8	2013.3	2013.8	2016.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2



TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	34.0	34.4	34.8	35.1	35.2	35.3	35.5	35.6
90°	37.2	39.2	41.2	42.6	43.2	43.9	44.6	45.2
92.5°	36.0	38.0	40.0	41.1	41.2	41.4	41.5	41.6
95°	37.2	39.2	41.2	42.4	42.7	43.1	43.4	43.7
97.5°	40.2	40.4	40.6	40.9	41.2	41.6	41.9	42.2
100°	55.0	49.3	43.6	40.9	41.2	41.6	41.9	42.2
102.5°	196.8	135.3	73.9	43.2	43.2	43.3	43.4	43.4
105°	476.5	479.6	482.6	478.0	466.0	453.9	441.9	429.8
107.5°	589.6	591.1	592.5	593.9	595.2	596.4	597.7	599.0
110°	666.4	667.1	667.7	668.6	669.6	670.6	671.6	672.6



TEST NUMBER: P332833

CATALOG NUMBER: S124DIW-S1020D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	740.8	740.6	740.5	741.1	742.4	743.6	744.9	746.2
115°	851.9	852.5	853.2	853.6	853.6	853.6	853.6	853.6
117.5°	963.7	963.5	963.4	963.3	963.1	963.0	962.9	962.7
120°	1032.8	1033.5	1034.2	1034.2	1033.5	1032.8	1032.2	1031.5
122.5°	1101.1	1101.5	1101.9	1101.7	1101.1	1100.4	1099.7	1099.1
125°	1196.4	1197.4	1198.4	1199.1	1199.4	1199.7	1200.1	1200.4
127.5°	1291.1	1290.9	1290.7	1290.4	1290.2	1289.9	1289.6	1289.4
130°	1348.9	1349.2	1349.5	1349.7	1349.7	1349.7	1349.7	1349.7
132.5°	1405.6	1405.9	1406.2	1406.3	1406.0	1405.7	1405.5	1405.2
135°	1483.7	1484.4	1485.1	1485.8	1486.4	1487.1	1487.8	1488.4
137.5°	1558.7	1559.4	1560.2	1560.4	1560.2	1560.0	1559.8	1559.6
140°	1605.1	1606.1	1607.1	1607.7	1608.1	1608.4	1608.7	1609.1
142.5°	1648.0	1648.7	1649.4	1649.8	1649.9	1650.0	1650.0	1650.1
145°	1709.3	1709.6	1709.9	1710.5	1711.1	1711.8	1712.5	1713.1
147.5°	1763.1	1763.4	1763.7	1764.0	1764.3	1764.6	1765.0	1765.3
150°	1797.6	1797.6	1797.6	1797.8	1798.1	1798.4	1798.8	1799.1
152.5°	1827.6	1828.1	1828.7	1828.8	1828.6	1828.4	1828.2	1828.0
155°	1868.1	1869.5	1870.8	1871.0	1870.0	1869.0	1868.0	1867.0
157.5°	1903.0	1904.8	1906.5	1906.5	1904.8	1903.0	1901.3	1899.5
160°	1925.3	1927.3	1929.3	1929.3	1927.3	1925.3	1923.3	1921.2
162.5°	1943.4	1945.4	1947.4	1947.2	1945.0	1942.7	1940.4	1938.1
165°	1968.8	1971.5	1974.2	1974.0	1971.0	1968.0	1965.0	1962.0
167.5°	1987.5	1990.4	1993.4	1993.2	1989.8	1986.5	1983.1	1979.8
170°	1999.0	2001.7	2004.4	2004.0	2000.7	1997.3	1994.0	1990.6
172.5°	2006.2	2008.9	2011.6	2011.1	2007.5	2003.9	2000.3	1996.6
175°	2014.7	2017.8	2020.8	2020.3	2016.2	2012.2	2008.2	2004.2
177.5°	2018.1	2020.3	2022.4	2021.9	2018.7	2015.4	2012.2	2009.0
180°	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2	2016.2

(END OF REPORT)