

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332815

Luminaire Tested: **S124DIW-S1020D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332815
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D770U835-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7500.7 lumens
Efficiency: N/A
Efficacy: 139.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332815
CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332815

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	95	91	88	93	89	86	83	77	75	73	67	65	63	57	56	54	50				
2	91	83	77	72	85	78	72	68	68	64	60	59	56	53	50	48	46	42				
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	44	41	39	35				
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30				
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	32	29	26				
6	64	52	44	38	60	49	41	36	43	37	33	38	33	29	32	29	26	23				
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20				
8	55	43	35	29	51	40	33	28	36	30	26	31	27	23	27	23	21	18				
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16				
10	48	36	28	24	45	34	27	23	30	25	21	27	22	19	23	20	17	15				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332815

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.5	2.2
10°-20°	457.8	6.1
20°-30°	673.9	9.0
30°-40°	783.4	10.4
40°-50°	783.4	10.4
50°-60°	685.3	9.1
60°-70°	508.9	6.8
70°-80°	289.1	3.9
80°-90°	86.3	1.2
90°-100°	33.9	0.5
100°-110°	216.4	2.9
110°-120°	414.0	5.5
120°-130°	525.6	7.0
130°-140°	562.3	7.5
140°-150°	525.8	7.0
150°-160°	424.0	5.7
160°-170°	273.5	3.6
170°-180°	94.3	1.3
0°-30°	1294.2	17.3
0°-40°	2077.6	27.7
0°-60°	3546.4	47.3
0°-90°	4430.7	59.1
90°-120°	664.4	8.9
90°-150°	2278.1	30.4
90°-180°	3070.0	40.9
0°-180°	7500.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	2	10	16	21	22	6
95°	41	17	16	21	22	52
105°	223	228	232	236	212	234
115°	417	419	419	420	420	410
125°	586	589	588	590	591	523
135°	727	727	730	731	733	560
145°	839	841	841	842	843	524
155°	920	920	918	921	919	424
165°	970	967	966	972	966	274
175°	992	988	989	995	986	94
180°	992	992	992	992	992	



TEST NUMBER: P332815

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.2	29.3	29.4	29.6	29.7	29.7	29.8	29.8	29.8	29.8	30.0
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	9.4	9.5	9.6	9.6	9.7	10.5	11.8	13.1	14.4	15.7	16.7
95°	40.8	35.2	29.6	24.0	18.4	15.7	15.8	16.0	16.2	16.3	17.3
97.5°	86.7	90.2	93.7	97.2	100.7	93.2	74.8	56.4	38.0	19.6	19.7
100°	121.7	124.7	127.7	130.6	133.6	123.7	101.0	78.2	55.4	32.7	29.9
102.5°	160.9	163.1	165.3	167.5	169.6	169.2	166.3	163.3	160.3	157.4	127.1
105°	223.4	224.4	225.4	226.4	227.4	228.3	229.1	229.9	230.8	231.6	233.1
107.5°	281.5	282.0	282.5	283.0	283.5	284.3	285.4	286.5	287.6	288.7	289.5
110°	320.7	321.2	321.7	322.2	322.6	323.4	324.4	325.4	326.4	327.3	327.7



TEST NUMBER: P332815

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	358.7	359.6	360.5	361.3	362.2	362.9	363.4	363.8	364.3	364.8	364.7
115°	417.2	417.7	418.2	418.6	419.1	419.3	419.1	419.0	418.8	418.6	419.0
117.5°	469.9	470.5	471.2	471.8	472.5	473.0	473.4	473.7	474.1	474.5	474.4
120°	505.5	506.2	506.8	507.5	508.1	508.4	508.2	508.1	507.9	507.7	508.1
122.5°	538.8	539.1	539.5	539.9	540.3	540.6	540.9	541.1	541.3	541.6	541.8
125°	586.4	587.1	587.7	588.4	589.0	589.2	588.9	588.6	588.2	587.9	588.4
127.5°	631.5	631.7	631.9	632.0	632.2	632.7	633.4	634.2	634.9	635.7	635.6
130°	660.6	660.8	661.0	661.1	661.3	661.6	662.1	662.6	663.1	663.6	663.8
132.5°	687.4	687.7	688.0	688.2	688.5	689.0	689.6	690.3	690.9	691.5	691.7
135°	727.4	727.3	727.1	726.9	726.8	727.0	727.7	728.3	729.0	729.7	730.0
137.5°	762.9	763.0	763.1	763.1	763.2	763.6	764.3	765.0	765.8	766.5	766.8
140°	786.1	786.4	786.7	787.1	787.4	787.7	788.1	788.4	788.7	789.1	789.5
142.5°	806.9	807.5	808.1	808.6	809.2	809.6	809.8	810.0	810.2	810.4	810.8
145°	838.8	839.3	839.8	840.3	840.8	841.0	841.0	841.0	841.0	841.0	841.2
147.5°	864.2	865.1	866.0	866.9	867.9	868.2	868.1	867.9	867.7	867.6	867.7
150°	882.6	883.2	883.9	884.6	885.2	885.5	885.3	885.1	885.0	884.8	884.8
152.5°	898.0	898.5	899.1	899.6	900.1	900.2	899.9	899.7	899.4	899.1	899.3
155°	919.7	919.9	920.0	920.2	920.4	920.2	919.7	919.2	918.7	918.2	918.9
157.5°	938.0	937.9	937.8	937.7	937.6	937.2	936.7	936.1	935.5	935.0	935.8
160°	948.6	948.1	947.7	947.2	946.7	946.3	946.2	946.0	945.8	945.7	946.7
162.5°	958.1	957.5	956.9	956.3	955.6	955.2	955.1	954.9	954.7	954.6	955.6
165°	970.2	969.3	968.5	967.7	966.9	966.5	966.5	966.5	966.5	966.5	967.8
167.5°	979.7	978.8	978.0	977.1	976.2	975.8	975.7	975.6	975.5	975.4	976.8
170°	985.0	984.0	983.0	982.0	981.1	980.6	980.8	981.0	981.1	981.3	982.6
172.5°	988.6	987.6	986.6	985.6	984.6	984.2	984.4	984.5	984.7	984.9	986.2
175°	992.4	991.4	990.5	989.5	988.5	988.1	988.2	988.4	988.6	988.7	990.2
177.5°	994.2	993.3	992.4	991.4	990.5	990.2	990.5	990.7	991.0	991.2	992.3
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4



TEST NUMBER: P332815

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	30.2	30.4	30.6	30.7	30.8	30.9	30.9	31.0
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	17.7	18.7	19.7	20.2	20.3	20.4	20.4	20.5
95°	18.3	19.3	20.3	20.9	21.0	21.2	21.4	21.5
97.5°	19.8	19.9	20.0	20.1	20.3	20.5	20.6	20.8
100°	27.1	24.2	21.4	20.1	20.3	20.5	20.6	20.8
102.5°	96.9	66.6	36.4	21.2	21.3	21.3	21.3	21.4
105°	234.6	236.0	237.5	235.3	229.4	223.4	217.5	211.6
107.5°	290.2	290.9	291.7	292.3	293.0	293.6	294.2	294.8
110°	328.0	328.3	328.7	329.1	329.6	330.1	330.6	331.1



TEST NUMBER: P332815

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	364.6	364.6	364.5	364.8	365.4	366.0	366.7	367.3
115°	419.3	419.6	420.0	420.1	420.1	420.1	420.1	420.1
117.5°	474.3	474.3	474.2	474.1	474.1	474.0	473.9	473.9
120°	508.4	508.7	509.0	509.0	508.7	508.4	508.1	507.7
122.5°	542.0	542.2	542.4	542.3	542.0	541.6	541.3	541.0
125°	588.9	589.4	589.9	590.2	590.4	590.5	590.7	590.9
127.5°	635.5	635.4	635.3	635.2	635.1	634.9	634.8	634.7
130°	663.9	664.1	664.3	664.3	664.3	664.3	664.3	664.3
132.5°	691.8	692.0	692.2	692.2	692.1	691.9	691.8	691.7
135°	730.3	730.7	731.0	731.3	731.6	732.0	732.3	732.6
137.5°	767.2	767.6	767.9	768.1	768.0	767.9	767.8	767.7
140°	790.0	790.5	791.0	791.4	791.5	791.7	791.9	792.0
142.5°	811.2	811.5	811.9	812.1	812.1	812.1	812.2	812.2
145°	841.3	841.5	841.7	841.9	842.2	842.6	842.9	843.2
147.5°	867.8	868.0	868.1	868.3	868.4	868.6	868.8	868.9
150°	884.8	884.8	884.8	884.9	885.1	885.2	885.4	885.5
152.5°	899.6	899.8	900.1	900.2	900.1	900.0	899.9	899.8
155°	919.5	920.2	920.8	920.9	920.4	919.9	919.4	919.0
157.5°	936.7	937.6	938.4	938.4	937.6	936.7	935.8	935.0
160°	947.7	948.6	949.6	949.6	948.6	947.7	946.7	945.7
162.5°	956.6	957.5	958.5	958.5	957.4	956.2	955.1	954.0
165°	969.1	970.4	971.7	971.7	970.2	968.7	967.2	965.7
167.5°	978.3	979.7	981.2	981.1	979.4	977.8	976.1	974.5
170°	983.9	985.3	986.6	986.4	984.8	983.1	981.5	979.8
172.5°	987.5	988.8	990.1	989.9	988.1	986.4	984.6	982.8
175°	991.7	993.2	994.7	994.4	992.4	990.5	988.5	986.5
177.5°	993.4	994.4	995.5	995.2	993.6	992.0	990.5	988.9
180°	992.4	992.4	992.4	992.4	992.4	992.4	992.4	992.4

(END OF REPORT)