

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332816

Luminaire Tested: **S124DIW-S1020D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332816  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124DIW-S1020D770U835-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7093.2 lumens  
Efficiency: N/A  
Efficacy: 132.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	62																												
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57	53																												
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	52	50	48	44																												
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	43	41	37																												
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35	32																												
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	37	34	31	28																												
6	65	52	44	38	60	49	42	37	44	38	33	39	34	30	34	30	27	24																												
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	22																												
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	29	25	22	19																												
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20	17																												
10	49	36	29	24	46	34	28	23	31	25	21	28	23	19	25	21	18	16																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13930	13930	13930
5°	13972	13804	13904
10°	13884	13691	13759
15°	13717	13497	13531
20°	13493	13256	13268
25°	13239	12981	12944
30°	12928	12656	12541
35°	12604	12318	12154
40°	12269	11934	11715
45°	11918	11555	11334
50°	11531	11218	10870
55°	11112	10781	10431
60°	10693	10291	9978
65°	10222	9824	9429
70°	9692	9203	8844
75°	8883	8453	8238
80°	7908	7583	7392
85°	6919	6660	6530



TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	162.5	2.3
10°-20°	457.8	6.5
20°-30°	673.9	9.5
30°-40°	783.4	11.0
40°-50°	783.4	11.0
50°-60°	685.3	9.7
60°-70°	508.9	7.2
70°-80°	289.1	4.1
80°-90°	86.3	1.2
90°-100°	63.3	0.9
100°-110°	187.5	2.6
110°-120°	318.2	4.5
120°-130°	419.6	5.9
130°-140°	471.3	6.6
140°-150°	463.1	6.5
150°-160°	389.5	5.5
160°-170°	259.1	3.7
170°-180°	90.7	1.3
0°-30°	1294.2	18.2
0°-40°	2077.6	29.3
0°-60°	3546.4	50.0
0°-90°	4430.7	62.5
90°-120°	569.0	8.0
90°-150°	1923.1	27.1
90°-180°	2662.0	37.5
0°-180°	7093.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1726	1726	1726	1726	1726	
5°	1724	1718	1703	1718	1716	163
15°	1641	1635	1615	1622	1619	462
25°	1486	1476	1457	1458	1453	684
35°	1279	1269	1250	1240	1233	799
45°	1044	1034	1012	997	993	804
55°	790	784	766	750	741	707
65°	535	528	514	501	494	530
75°	285	278	271	266	264	303
85°	75	75	72	72	70	82
90°	2	10	16	21	22	7
95°	44	51	56	58	59	50
105°	173	174	177	179	181	183
115°	324	324	322	321	321	319
125°	471	471	470	469	468	420
135°	608	612	612	611	609	470
145°	738	741	742	741	739	462
155°	846	846	845	848	845	389
165°	921	919	917	921	919	260
175°	958	955	954	958	954	91
180°	960	960	960	960	960	



TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1729.9	1729.2	1728.4	1727.7	1727.0	1725.2	1722.5	1719.8	1717.1	1714.4	1716.9
5°	1724.1	1722.9	1721.7	1720.4	1719.2	1716.9	1713.5	1710.1	1706.8	1703.4	1706.8
7.5°	1708.1	1706.8	1705.6	1704.4	1703.2	1700.7	1696.9	1693.2	1689.4	1685.7	1688.4
10°	1693.7	1692.5	1691.2	1690.0	1688.8	1686.2	1682.2	1678.2	1674.2	1670.2	1672.6
12.5°	1674.9	1673.7	1672.4	1671.2	1670.0	1667.2	1663.0	1658.8	1654.5	1650.3	1653.0
15°	1641.2	1639.9	1638.7	1637.5	1636.2	1633.3	1628.7	1624.1	1619.5	1614.9	1616.7
17.5°	1600.5	1599.0	1597.4	1595.9	1594.4	1591.4	1587.0	1582.7	1578.3	1574.0	1575.1
20°	1570.6	1569.1	1567.6	1566.0	1564.5	1561.4	1556.8	1552.2	1547.6	1543.0	1543.9
22.5°	1538.6	1536.5	1534.5	1532.5	1530.5	1527.1	1522.5	1517.9	1513.3	1508.7	1510.4
25°	1486.3	1484.2	1482.0	1479.8	1477.7	1474.5	1470.2	1465.9	1461.6	1457.3	1457.6
27.5°	1426.6	1424.4	1422.1	1419.9	1417.7	1414.6	1410.6	1406.6	1402.6	1398.6	1397.9
30°	1386.8	1384.3	1381.8	1379.4	1376.9	1373.7	1369.7	1365.7	1361.7	1357.7	1356.5
32.5°	1344.7	1342.5	1340.3	1338.1	1335.9	1332.6	1328.4	1324.2	1319.9	1315.7	1314.2
35°	1278.9	1276.8	1274.6	1272.5	1270.3	1267.1	1262.8	1258.5	1254.2	1249.9	1247.7
37.5°	1209.5	1207.5	1205.6	1203.6	1201.6	1198.4	1193.7	1189.1	1184.5	1179.9	1177.6
40°	1164.2	1161.7	1159.2	1156.8	1154.3	1150.8	1146.2	1141.6	1137.0	1132.4	1129.3
42.5°	1115.5	1114.0	1112.5	1111.1	1109.6	1106.3	1101.2	1096.1	1091.0	1085.9	1082.3
45°	1043.9	1041.7	1039.6	1037.4	1035.3	1031.7	1026.8	1021.9	1017.0	1012.1	1008.7
47.5°	968.9	967.5	966.0	964.5	963.0	960.0	955.5	950.9	946.4	941.8	938.0
50°	918.1	916.8	915.6	914.4	913.1	910.4	906.1	901.8	897.5	893.2	888.9
52.5°	868.3	866.8	865.3	863.9	862.4	859.4	854.8	850.3	845.7	841.2	837.4
55°	789.5	788.5	787.6	786.7	785.8	783.2	778.9	774.6	770.3	766.0	762.3
57.5°	714.3	713.2	712.2	711.1	710.1	707.4	703.2	699.0	694.7	690.5	687.0
60°	662.3	660.7	659.2	657.7	656.1	653.4	649.4	645.4	641.4	637.4	634.6
62.5°	611.4	610.1	608.8	607.5	606.2	603.5	599.2	595.0	590.7	586.5	584.0
65°	535.1	533.5	532.0	530.5	528.9	526.6	523.5	520.5	517.4	514.3	511.3
67.5°	458.2	456.8	455.4	454.0	452.5	450.4	447.4	444.5	441.5	438.6	435.6
70°	410.6	408.5	406.3	404.2	402.0	399.7	397.3	394.8	392.4	389.9	387.4
72.5°	359.8	357.6	355.5	353.3	351.2	349.1	347.1	345.2	343.2	341.2	339.3
75°	284.8	283.3	281.7	280.2	278.7	277.1	275.6	274.1	272.5	271.0	269.8
77.5°	213.2	212.5	211.8	211.2	210.5	209.5	208.1	206.8	205.4	204.1	203.7
80°	170.1	169.1	168.2	167.3	166.4	165.6	165.0	164.4	163.8	163.1	162.5
82.5°	128.0	127.6	127.2	126.7	126.3	126.0	125.9	125.8	125.7	125.5	125.2
85°	74.7	74.7	74.7	74.7	74.7	74.4	73.7	73.1	72.5	71.9	71.9
87.5°	29.2	29.3	29.4	29.6	29.7	29.7	29.8	29.8	29.8	29.8	30.0
90°	2.2	4.0	5.9	7.7	9.5	11.1	12.4	13.7	15.0	16.3	17.3
92.5°	15.9	18.0	20.0	22.1	24.2	25.7	26.6	27.5	28.5	29.4	30.0
95°	44.5	46.0	47.5	49.0	50.5	51.8	52.9	54.1	55.3	56.4	56.9
97.5°	77.8	79.0	80.2	81.3	82.5	83.8	85.2	86.5	87.9	89.2	89.8
100°	103.9	104.6	105.2	105.9	106.5	107.6	109.1	110.6	112.1	113.6	113.9
102.5°	131.2	131.5	131.7	132.0	132.3	133.1	134.4	135.8	137.1	138.5	139.0
105°	172.9	173.1	173.3	173.4	173.6	174.0	174.7	175.3	176.0	176.6	177.1
107.5°	216.7	216.9	217.1	217.3	217.5	217.7	217.8	217.9	218.0	218.1	218.5
110°	246.4	246.7	247.1	247.4	247.7	247.8	247.6	247.5	247.3	247.1	246.8



TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	277.3	277.3	277.4	277.5	277.5	277.4	277.1	276.8	276.5	276.2	276.2
115°	323.6	323.6	323.6	323.6	323.6	323.4	323.1	322.8	322.4	322.1	321.9
117.5°	367.2	367.4	367.5	367.6	367.8	367.7	367.5	367.3	367.0	366.8	366.2
120°	396.3	397.0	397.6	398.3	399.0	399.0	398.6	398.1	397.6	397.1	396.2
122.5°	426.6	426.9	427.1	427.4	427.7	427.7	427.5	427.2	427.0	426.8	426.2
125°	471.3	471.3	471.3	471.3	471.3	471.2	471.0	470.9	470.7	470.5	470.2
127.5°	511.8	512.3	512.8	513.3	513.8	513.9	513.6	513.4	513.1	512.9	512.5
130°	540.3	540.8	541.3	541.8	542.3	542.5	542.5	542.5	542.5	542.5	542.2
132.5°	569.4	569.8	570.1	570.5	570.9	571.0	570.8	570.7	570.6	570.4	570.1
135°	607.9	608.8	609.8	610.8	611.8	612.3	612.3	612.3	612.3	612.3	612.0
137.5°	649.7	650.2	650.6	651.1	651.6	651.9	652.2	652.4	652.7	653.0	652.5
140°	677.6	677.9	678.3	678.6	678.9	679.1	679.1	679.1	679.1	679.1	678.9
142.5°	703.1	703.5	703.8	704.1	704.5	704.6	704.4	704.3	704.2	704.0	704.0
145°	738.5	739.1	739.8	740.5	741.1	741.5	741.7	741.9	742.0	742.2	742.0
147.5°	773.5	774.3	775.1	775.9	776.7	777.0	776.9	776.7	776.6	776.5	776.3
150°	794.9	795.5	796.2	796.9	797.5	797.9	797.9	797.9	797.9	797.9	797.9
152.5°	815.1	815.5	815.9	816.3	816.7	816.9	817.0	817.2	817.3	817.4	817.8
155°	846.1	846.1	846.1	846.1	846.1	846.0	845.8	845.7	845.5	845.4	846.0
157.5°	872.2	871.9	871.6	871.3	871.0	870.9	870.8	870.8	870.8	870.7	871.2
160°	887.7	887.5	887.3	887.2	887.0	886.8	886.7	886.5	886.3	886.2	886.7
162.5°	901.9	901.5	901.0	900.6	900.2	899.9	899.7	899.6	899.4	899.2	900.1
165°	921.1	920.6	920.1	919.6	919.1	918.7	918.3	918.0	917.7	917.3	918.3
167.5°	935.7	935.1	934.4	933.7	933.0	932.6	932.7	932.7	932.7	932.8	933.8
170°	944.1	943.2	942.4	941.6	940.8	940.4	940.6	940.8	940.9	941.1	942.1
172.5°	950.0	949.3	948.6	947.9	947.2	946.9	946.9	947.0	947.0	947.0	948.2
175°	958.2	957.3	956.5	955.7	954.9	954.4	954.2	954.0	953.9	953.7	954.9
177.5°	960.8	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	958.8
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6



TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5	1725.5
2.5°	1719.3	1721.8	1724.3	1725.4	1725.1	1724.9	1724.6	1724.4
5°	1710.1	1713.5	1716.9	1718.3	1717.7	1717.0	1716.4	1715.8
7.5°	1691.1	1693.8	1696.5	1697.7	1697.3	1696.9	1696.5	1696.2
10°	1675.1	1677.6	1680.0	1680.9	1680.3	1679.7	1679.1	1678.5
12.5°	1655.7	1658.4	1661.1	1662.0	1661.2	1660.3	1659.4	1658.6
15°	1618.6	1620.4	1622.3	1622.7	1621.8	1620.9	1620.0	1619.0
17.5°	1576.3	1577.5	1578.6	1578.9	1578.3	1577.7	1577.1	1576.4
20°	1544.8	1545.8	1546.7	1546.8	1546.2	1545.6	1545.0	1544.4
22.5°	1512.0	1513.7	1515.3	1515.6	1514.5	1513.4	1512.3	1511.2
25°	1457.9	1458.2	1458.5	1458.0	1456.8	1455.6	1454.3	1453.1
27.5°	1397.2	1396.4	1395.7	1394.6	1393.0	1391.5	1389.9	1388.4
30°	1355.3	1354.0	1352.8	1351.4	1349.9	1348.3	1346.8	1345.3
32.5°	1312.7	1311.3	1309.8	1308.3	1306.7	1305.2	1303.7	1302.1
35°	1245.6	1243.4	1241.3	1239.4	1237.9	1236.4	1234.8	1233.3
37.5°	1175.2	1172.9	1170.6	1168.4	1166.4	1164.3	1162.3	1160.3
40°	1126.2	1123.1	1120.1	1117.8	1116.2	1114.7	1113.2	1111.6
42.5°	1078.8	1075.2	1071.6	1069.3	1068.3	1067.2	1066.2	1065.2
45°	1005.3	1001.9	998.5	996.4	995.5	994.6	993.6	992.7
47.5°	934.2	930.4	926.6	923.5	921.2	918.8	916.5	914.2
50°	884.6	880.3	876.0	872.9	871.0	869.2	867.4	865.5
52.5°	833.6	829.7	825.9	822.9	820.5	818.2	815.9	813.5
55°	758.6	754.9	751.2	748.5	746.6	744.8	742.9	741.1
57.5°	683.5	680.0	676.5	673.8	672.0	670.3	668.5	666.7
60°	631.9	629.1	626.3	624.2	622.6	621.1	619.6	618.0
62.5°	581.5	578.9	576.4	574.4	572.9	571.3	569.8	568.3
65°	508.2	505.1	502.0	499.7	498.2	496.7	495.1	493.6
67.5°	432.7	429.7	426.8	425.1	424.6	424.2	423.8	423.4
70°	385.0	382.5	380.1	378.4	377.5	376.5	375.6	374.7
72.5°	337.3	335.3	333.4	331.9	331.0	330.1	329.2	328.2
75°	268.5	267.3	266.1	265.3	265.0	264.7	264.4	264.1
77.5°	203.3	203.0	202.6	202.0	201.2	200.4	199.6	198.8
80°	161.9	161.3	160.7	160.2	159.9	159.6	159.3	159.0
82.5°	124.8	124.4	124.1	123.7	123.4	123.1	122.8	122.5
85°	71.9	71.9	71.9	71.7	71.4	71.1	70.8	70.5
87.5°	30.2	30.4	30.6	30.7	30.8	30.9	30.9	31.0
90°	18.3	19.3	20.3	20.9	21.3	21.6	21.9	22.3
92.5°	30.6	31.2	31.8	32.2	32.4	32.6	32.8	33.0
95°	57.4	57.9	58.4	58.6	58.6	58.6	58.6	58.6
97.5°	90.4	91.0	91.6	91.9	91.9	91.9	91.9	91.9
100°	114.2	114.5	114.9	115.0	115.0	115.0	115.0	115.0
102.5°	139.4	139.9	140.3	140.6	140.8	140.9	141.0	141.2
105°	177.6	178.1	178.6	179.1	179.6	180.1	180.6	181.1
107.5°	219.0	219.4	219.9	220.1	220.1	220.1	220.0	220.0
110°	246.5	246.2	245.8	245.9	246.4	246.9	247.4	247.9





TEST NUMBER: P332816

CATALOG NUMBER: S124DIW-S1020D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	276.1	276.0	276.0	276.0	276.1	276.2	276.3	276.4
115°	321.8	321.6	321.4	321.3	321.1	321.0	320.8	320.6
117.5°	365.7	365.1	364.5	364.1	363.8	363.4	363.1	362.8
120°	395.4	394.6	393.8	393.5	393.9	394.2	394.5	394.8
122.5°	425.6	425.1	424.5	423.9	423.3	422.7	422.2	421.6
125°	469.9	469.6	469.2	468.9	468.6	468.2	467.9	467.6
127.5°	512.2	511.9	511.5	511.2	511.0	510.7	510.4	510.2
130°	541.9	541.5	541.2	540.7	540.1	539.4	538.7	538.1
132.5°	569.8	569.5	569.1	568.8	568.6	568.3	568.0	567.8
135°	611.6	611.3	611.0	610.6	610.1	609.6	609.1	608.6
137.5°	652.1	651.7	651.3	651.1	651.2	651.3	651.4	651.5
140°	678.8	678.6	678.4	678.3	678.1	677.9	677.8	677.6
142.5°	704.0	703.9	703.9	703.9	703.8	703.8	703.8	703.7
145°	741.9	741.7	741.5	741.2	740.7	740.2	739.7	739.2
147.5°	776.2	776.1	775.9	775.8	775.6	775.5	775.3	775.1
150°	797.9	797.9	797.9	797.8	797.6	797.4	797.3	797.1
152.5°	818.2	818.6	819.0	819.0	818.6	818.2	817.7	817.3
155°	846.7	847.3	848.0	848.0	847.3	846.7	846.0	845.4
157.5°	871.7	872.2	872.7	872.7	872.1	871.6	871.0	870.4
160°	887.2	887.7	888.2	888.0	887.2	886.3	885.5	884.7
162.5°	901.0	901.9	902.8	902.8	902.0	901.2	900.4	899.5
165°	919.3	920.3	921.3	921.5	920.8	920.1	919.5	918.8
167.5°	934.8	935.7	936.7	936.7	935.7	934.7	933.7	932.6
170°	943.1	944.1	945.1	945.0	943.8	942.7	941.5	940.4
172.5°	949.3	950.4	951.5	951.5	950.3	949.2	948.0	946.9
175°	956.0	957.2	958.3	958.3	957.2	956.0	954.9	953.7
177.5°	959.7	960.6	961.6	961.5	960.4	959.4	958.3	957.3
180°	959.6	959.6	959.6	959.6	959.6	959.6	959.6	959.6

(END OF REPORT)