

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332827-927

Luminaire Tested: **S124DIW-S1020D1340U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332827-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124DIW-S1020D1340U927-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1020 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7761.2 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.3
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	92	88	85	88	85	81	78	71	68	66	58	56	55	46	45	44	38
2	88	81	75	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	29	29	26	23	20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11035	11035	11035
5°	11068	10935	11015
10°	10999	10846	10900
15°	10866	10692	10719
20°	10689	10501	10510
25°	10488	10283	10253
30°	10241	10026	9934
35°	9984	9758	9629
40°	9720	9454	9280
45°	9442	9154	8978
50°	9134	8887	8611
55°	8802	8541	8263
60°	8472	8152	7905
65°	8097	7782	7469
70°	7678	7291	7006
75°	7037	6697	6525
80°	6267	6007	5858
85°	5483	5280	5169



TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.7	1.7
10°-20°	362.7	4.7
20°-30°	533.8	6.9
30°-40°	620.6	8.0
40°-50°	620.6	8.0
50°-60°	542.9	7.0
60°-70°	403.2	5.2
70°-80°	229.1	3.0
80°-90°	70.1	0.9
90°-100°	47.0	0.6
100°-110°	299.6	3.9
110°-120°	573.1	7.4
120°-130°	727.5	9.4
130°-140°	778.4	10.0
140°-150°	727.9	9.4
150°-160°	587.0	7.6
160°-170°	378.6	4.9
170°-180°	130.5	1.7
0°-30°	1025.2	13.2
0°-40°	1645.9	21.2
0°-60°	2809.4	36.2
0°-90°	3511.7	45.2
90°-120°	919.7	11.8
90°-150°	3153.4	40.6
90°-180°	4250.0	54.8
0°-180°	7761.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1367	1367	1367	1367	1367	
5°	1366	1361	1349	1361	1359	129
15°	1300	1295	1279	1285	1282	366
25°	1177	1169	1154	1155	1151	541
35°	1013	1005	990	983	977	633
45°	827	819	802	790	786	637
55°	625	621	607	594	587	560
65°	424	418	407	397	391	420
75°	226	220	215	210	209	240
85°	59	59	57	57	56	65
90°	3	14	23	29	31	6
95°	56	24	23	28	30	73
105°	309	315	321	327	293	324
115°	577	580	580	581	582	568
125°	812	816	814	817	818	724
135°	1007	1006	1010	1012	1014	776
145°	1161	1164	1164	1165	1167	725
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1345	1337	379
175°	1374	1368	1369	1377	1366	131
180°	1374	1374	1374	1374	1374	



TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1370.4	1369.8	1369.2	1368.7	1368.1	1366.7	1364.5	1362.4	1360.3	1358.1	1360.1
5°	1365.8	1364.9	1363.9	1362.9	1361.9	1360.1	1357.4	1354.7	1352.1	1349.4	1352.1
7.5°	1353.1	1352.1	1351.1	1350.2	1349.2	1347.3	1344.3	1341.3	1338.3	1335.4	1337.5
10°	1341.7	1340.8	1339.7	1338.8	1337.8	1335.8	1332.6	1329.4	1326.3	1323.1	1325.0
12.5°	1326.8	1325.9	1324.8	1323.9	1322.9	1320.7	1317.4	1314.1	1310.7	1307.3	1309.5
15°	1300.1	1299.1	1298.1	1297.2	1296.2	1293.9	1290.2	1286.6	1282.9	1279.3	1280.7
17.5°	1267.9	1266.7	1265.4	1264.2	1263.1	1260.7	1257.2	1253.8	1250.3	1246.9	1247.8
20°	1244.2	1243.0	1241.8	1240.6	1239.4	1236.9	1233.3	1229.6	1226.0	1222.3	1223.1
22.5°	1218.9	1217.2	1215.6	1214.0	1212.4	1209.7	1206.1	1202.5	1198.8	1195.2	1196.5
25°	1177.4	1175.8	1174.0	1172.3	1170.6	1168.1	1164.7	1161.3	1157.9	1154.4	1154.7
27.5°	1130.1	1128.4	1126.6	1124.8	1123.1	1120.6	1117.5	1114.3	1111.1	1107.9	1107.4
30°	1098.6	1096.6	1094.6	1092.7	1090.8	1088.2	1085.1	1081.9	1078.7	1075.5	1074.6
32.5°	1065.2	1063.5	1061.8	1060.0	1058.3	1055.7	1052.3	1049.0	1045.6	1042.3	1041.1
35°	1013.1	1011.5	1009.7	1008.1	1006.3	1003.8	1000.4	997.0	993.6	990.1	988.4
37.5°	958.1	956.6	955.1	953.5	951.9	949.4	945.6	942.0	938.3	934.7	932.9
40°	922.3	920.3	918.3	916.4	914.4	911.6	908.0	904.4	900.7	897.1	894.6
42.5°	883.7	882.5	881.3	880.2	879.0	876.4	872.4	868.3	864.3	860.2	857.4
45°	827.0	825.2	823.6	821.8	820.1	817.3	813.4	809.5	805.6	801.8	799.1
47.5°	767.5	766.4	765.2	764.1	762.9	760.5	756.9	753.3	749.7	746.1	743.1
50°	727.3	726.3	725.3	724.4	723.3	721.2	717.8	714.4	711.0	707.6	704.2
52.5°	687.9	686.7	685.5	684.4	683.2	680.8	677.2	673.6	669.9	666.4	663.4
55°	625.4	624.6	623.9	623.2	622.5	620.4	617.0	613.6	610.2	606.8	603.9
57.5°	565.9	565.0	564.2	563.3	562.5	560.4	557.1	553.7	550.3	547.0	544.2
60°	524.7	523.4	522.2	521.0	519.8	517.6	514.4	511.3	508.1	504.9	502.7
62.5°	484.3	483.3	482.3	481.3	480.2	478.1	474.7	471.3	467.9	464.6	462.6
65°	423.9	422.6	421.4	420.3	419.0	417.2	414.7	412.3	409.9	407.4	405.0
67.5°	363.0	361.9	360.8	359.7	358.5	356.8	354.4	352.1	349.7	347.5	345.1
70°	325.3	323.6	321.9	320.2	318.5	316.6	314.7	312.8	310.9	308.9	306.9
72.5°	285.0	283.3	281.6	279.9	278.2	276.6	275.0	273.5	271.9	270.3	268.8
75°	225.6	224.4	223.2	222.0	220.8	219.5	218.3	217.1	215.9	214.7	213.7
77.5°	168.9	168.3	167.8	167.3	166.8	166.0	164.9	163.8	162.7	161.7	161.4
80°	134.8	134.0	133.2	132.5	131.8	131.2	130.7	130.2	129.8	129.2	128.7
82.5°	101.4	101.1	100.8	100.4	100.1	99.8	99.7	99.7	99.6	99.4	99.2
85°	59.2	59.2	59.2	59.2	59.2	58.9	58.4	57.9	57.4	57.0	57.0
87.5°	23.4	23.7	24.0	24.3	24.6	24.9	25.0	25.2	25.3	25.6	25.8
90°	3.1	5.6	8.1	10.6	13.2	15.3	17.1	18.9	20.8	22.6	24.0
92.5°	12.9	13.1	13.2	13.4	13.5	14.5	16.3	18.1	20.0	21.8	23.1
95°	56.5	48.7	41.0	33.2	25.4	21.7	21.9	22.2	22.3	22.6	24.0
97.5°	120.0	124.8	129.7	134.5	139.3	129.0	103.5	78.1	52.6	27.1	27.3
100°	168.5	172.6	176.7	180.9	185.0	171.3	139.7	108.2	76.7	45.2	41.4
102.5°	222.8	225.8	228.8	231.8	234.8	234.2	230.1	226.1	222.0	217.9	175.9
105°	309.3	310.6	312.0	313.4	314.7	316.0	317.2	318.3	319.4	320.6	322.7
107.5°	389.6	390.3	391.0	391.7	392.4	393.5	395.1	396.6	398.2	399.7	400.7
110°	443.9	444.6	445.3	445.9	446.6	447.7	449.0	450.4	451.8	453.1	453.6



TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	496.5	497.7	499.0	500.2	501.5	502.3	503.0	503.7	504.3	504.9	504.9
115°	577.4	578.1	578.8	579.5	580.2	580.4	580.2	580.0	579.7	579.5	580.0
117.5°	650.4	651.3	652.2	653.2	654.0	654.7	655.3	655.8	656.2	656.8	656.7
120°	699.7	700.6	701.6	702.5	703.4	703.7	703.5	703.3	703.1	702.8	703.3
122.5°	745.8	746.3	746.9	747.4	748.0	748.4	748.7	749.0	749.3	749.6	750.0
125°	811.7	812.6	813.6	814.4	815.4	815.6	815.2	814.7	814.2	813.8	814.4
127.5°	874.2	874.4	874.6	874.9	875.1	875.8	876.8	877.8	878.9	880.0	879.8
130°	914.5	914.7	915.0	915.1	915.4	915.8	916.6	917.2	917.9	918.6	918.9
132.5°	951.5	951.9	952.3	952.7	953.1	953.8	954.7	955.5	956.3	957.2	957.4
135°	1006.9	1006.7	1006.5	1006.3	1006.1	1006.4	1007.3	1008.2	1009.2	1010.0	1010.5
137.5°	1056.1	1056.1	1056.2	1056.4	1056.5	1057.0	1058.0	1059.0	1060.0	1061.0	1061.5
140°	1088.1	1088.6	1089.0	1089.5	1090.0	1090.4	1090.8	1091.3	1091.8	1092.3	1092.9
142.5°	1116.9	1117.7	1118.6	1119.4	1120.2	1120.7	1121.0	1121.3	1121.6	1121.8	1122.4
145°	1161.1	1161.7	1162.4	1163.2	1163.8	1164.2	1164.2	1164.2	1164.2	1164.2	1164.4
147.5°	1196.2	1197.5	1198.8	1200.1	1201.3	1201.9	1201.7	1201.4	1201.2	1200.9	1201.1
150°	1221.7	1222.7	1223.5	1224.5	1225.3	1225.7	1225.5	1225.3	1225.0	1224.8	1224.8
152.5°	1243.1	1243.8	1244.5	1245.2	1246.0	1246.2	1245.8	1245.3	1244.9	1244.5	1244.9
155°	1273.1	1273.3	1273.5	1273.7	1274.0	1273.7	1273.1	1272.4	1271.7	1271.1	1271.9
157.5°	1298.4	1298.2	1298.1	1297.9	1297.8	1297.4	1296.6	1295.8	1295.1	1294.3	1295.5
160°	1313.1	1312.5	1311.8	1311.1	1310.4	1310.0	1309.7	1309.5	1309.2	1309.1	1310.4
162.5°	1326.3	1325.4	1324.6	1323.7	1322.9	1322.3	1322.1	1321.8	1321.6	1321.4	1322.7
165°	1343.0	1341.8	1340.7	1339.5	1338.4	1337.8	1337.8	1337.8	1337.8	1337.8	1339.7
167.5°	1356.1	1354.9	1353.8	1352.6	1351.4	1350.7	1350.6	1350.4	1350.3	1350.1	1352.2
170°	1363.5	1362.2	1360.7	1359.4	1358.0	1357.5	1357.6	1357.9	1358.1	1358.4	1360.2
172.5°	1368.4	1367.1	1365.7	1364.3	1362.9	1362.4	1362.6	1362.9	1363.0	1363.3	1365.1
175°	1373.8	1372.4	1371.0	1369.7	1368.3	1367.7	1367.9	1368.2	1368.4	1368.7	1370.7
177.5°	1376.3	1375.0	1373.6	1372.4	1371.1	1370.6	1371.0	1371.4	1371.7	1372.1	1373.6
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8



TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9	1366.9
2.5°	1362.0	1364.0	1366.0	1366.8	1366.6	1366.4	1366.2	1366.0
5°	1354.7	1357.4	1360.1	1361.2	1360.7	1360.2	1359.7	1359.2
7.5°	1339.7	1341.8	1343.9	1344.9	1344.6	1344.3	1343.9	1343.7
10°	1327.0	1329.0	1330.9	1331.6	1331.1	1330.6	1330.2	1329.7
12.5°	1311.6	1313.8	1315.9	1316.6	1316.0	1315.3	1314.5	1313.9
15°	1282.2	1283.7	1285.2	1285.5	1284.8	1284.0	1283.3	1282.5
17.5°	1248.7	1249.7	1250.5	1250.8	1250.3	1249.8	1249.4	1248.8
20°	1223.8	1224.6	1225.3	1225.3	1224.9	1224.4	1223.9	1223.4
22.5°	1197.8	1199.1	1200.4	1200.6	1199.8	1198.9	1198.0	1197.1
25°	1154.9	1155.2	1155.4	1155.0	1154.1	1153.1	1152.1	1151.1
27.5°	1106.8	1106.2	1105.6	1104.8	1103.5	1102.3	1101.1	1099.9
30°	1073.6	1072.6	1071.7	1070.6	1069.4	1068.1	1066.9	1065.7
32.5°	1039.9	1038.8	1037.6	1036.4	1035.1	1034.0	1032.8	1031.5
35°	986.7	985.0	983.3	981.8	980.6	979.5	978.2	977.0
37.5°	931.0	929.2	927.3	925.6	924.0	922.3	920.8	919.2
40°	892.2	889.7	887.3	885.5	884.2	883.0	881.9	880.6
42.5°	854.6	851.8	848.9	847.1	846.3	845.4	844.6	843.8
45°	796.4	793.7	791.0	789.3	788.6	787.9	787.1	786.4
47.5°	740.1	737.0	734.0	731.6	729.8	727.9	726.0	724.2
50°	700.8	697.4	694.0	691.5	690.0	688.6	687.1	685.6
52.5°	660.4	657.3	654.3	651.9	650.0	648.2	646.3	644.4
55°	600.9	598.0	595.1	592.9	591.4	590.0	588.5	587.1
57.5°	541.5	538.7	535.9	533.8	532.3	531.0	529.6	528.1
60°	500.6	498.4	496.1	494.5	493.2	492.0	490.8	489.6
62.5°	460.7	458.6	456.6	455.0	453.8	452.6	451.4	450.2
65°	402.6	400.1	397.7	395.9	394.7	393.5	392.2	391.0
67.5°	342.8	340.4	338.1	336.8	336.4	336.0	335.7	335.4
70°	305.0	303.0	301.1	299.8	299.0	298.3	297.5	296.8
72.5°	267.2	265.6	264.1	262.9	262.2	261.5	260.8	260.0
75°	212.7	211.8	210.8	210.2	209.9	209.7	209.5	209.2
77.5°	161.1	160.8	160.5	160.0	159.4	158.8	158.1	157.5
80°	128.3	127.8	127.3	126.9	126.7	126.4	126.2	126.0
82.5°	98.9	98.5	98.3	98.0	97.8	97.5	97.3	97.0
85°	57.0	57.0	57.0	56.8	56.6	56.3	56.1	55.8
87.5°	26.1	26.4	26.6	26.9	26.9	27.0	27.1	27.2
90°	25.3	26.7	28.1	29.0	29.5	29.9	30.3	30.8
92.5°	24.6	25.9	27.3	28.0	28.1	28.2	28.3	28.4
95°	25.3	26.7	28.1	28.9	29.1	29.3	29.5	29.8
97.5°	27.4	27.6	27.6	27.9	28.1	28.3	28.5	28.8
100°	37.5	33.6	29.7	27.9	28.1	28.3	28.5	28.8
102.5°	134.1	92.2	50.3	29.4	29.5	29.5	29.5	29.6
105°	324.7	326.8	328.8	325.7	317.5	309.3	301.0	292.9
107.5°	401.7	402.7	403.7	404.6	405.5	406.4	407.3	408.1
110°	454.1	454.5	455.0	455.5	456.2	456.9	457.6	458.3



TEST NUMBER: P332827-927

CATALOG NUMBER: S124DIW-S1020D1340U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	504.7	504.6	504.5	504.9	505.8	506.7	507.6	508.4
115°	580.4	580.9	581.3	581.5	581.5	581.5	581.5	581.5
117.5°	656.6	656.5	656.4	656.3	656.2	656.2	656.1	655.9
120°	703.7	704.2	704.6	704.6	704.2	703.7	703.3	702.8
122.5°	750.2	750.5	750.8	750.7	750.2	749.7	749.3	748.8
125°	815.2	815.9	816.5	817.0	817.2	817.5	817.7	817.9
127.5°	879.7	879.6	879.4	879.2	879.1	878.8	878.7	878.5
130°	919.0	919.2	919.5	919.6	919.6	919.6	919.6	919.6
132.5°	957.7	957.9	958.1	958.1	958.0	957.8	957.6	957.4
135°	1011.0	1011.4	1011.9	1012.3	1012.8	1013.2	1013.7	1014.2
137.5°	1062.0	1062.5	1063.0	1063.2	1063.0	1063.0	1062.8	1062.6
140°	1093.6	1094.3	1095.0	1095.4	1095.7	1095.9	1096.1	1096.4
142.5°	1122.8	1123.3	1123.9	1124.1	1124.2	1124.2	1124.3	1124.3
145°	1164.6	1164.8	1165.1	1165.5	1165.9	1166.3	1166.8	1167.3
147.5°	1201.3	1201.5	1201.7	1201.9	1202.1	1202.4	1202.5	1202.8
150°	1224.8	1224.8	1224.8	1224.9	1225.1	1225.3	1225.6	1225.8
152.5°	1245.2	1245.6	1245.9	1246.1	1245.9	1245.8	1245.7	1245.5
155°	1272.9	1273.7	1274.7	1274.8	1274.1	1273.4	1272.7	1272.1
157.5°	1296.6	1297.8	1299.0	1299.0	1297.8	1296.6	1295.5	1294.3
160°	1311.8	1313.1	1314.5	1314.5	1313.1	1311.8	1310.4	1309.1
162.5°	1324.1	1325.5	1326.8	1326.7	1325.2	1323.7	1322.1	1320.6
165°	1341.5	1343.3	1345.1	1345.0	1343.0	1340.9	1338.9	1336.8
167.5°	1354.2	1356.1	1358.2	1358.0	1355.7	1353.4	1351.2	1348.9
170°	1362.0	1363.8	1365.6	1365.4	1363.2	1360.9	1358.6	1356.3
172.5°	1366.9	1368.8	1370.6	1370.3	1367.8	1365.3	1362.9	1360.4
175°	1372.8	1374.8	1376.9	1376.5	1373.8	1371.0	1368.3	1365.6
177.5°	1375.1	1376.5	1378.0	1377.6	1375.4	1373.2	1371.0	1368.8
180°	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)